

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332412

Luminaire Tested: **S123RDIW-S560D460U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332412
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3979.5 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	23	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	2.2
10°-20°	246.8	6.2
20°-30°	355.3	8.9
30°-40°	400.3	10.1
40°-50°	382.9	9.6
50°-60°	313.6	7.9
60°-70°	211.6	5.3
70°-80°	106.4	2.7
80°-90°	29.9	0.8
90°-100°	22.0	0.6
100°-110°	104.8	2.6
110°-120°	251.7	6.3
120°-130°	320.5	8.1
130°-140°	342.4	8.6
140°-150°	320.2	8.0
150°-160°	258.3	6.5
160°-170°	166.7	4.2
170°-180°	57.5	1.4
0°-30°	690.8	17.4
0°-40°	1091.1	27.4
0°-60°	1787.6	44.9
0°-90°	2135.4	53.7
90°-120°	378.5	9.5
90°-150°	1361.6	34.2
90°-180°	1844.0	46.3
0°-180°	3979.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	0	5	11	13	14	3
95°	27	10	14	17	17	34
105°	134	136	98	23	20	142
115°	251	254	258	262	264	248
125°	354	358	359	360	361	316
135°	441	443	445	446	445	339
145°	509	512	513	513	514	318
155°	560	559	560	562	559	258
165°	591	590	589	592	590	167
175°	605	603	603	606	602	58
180°	605	605	605	605	605	



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	14.8	13.5	12.2	10.9	9.6	9.1	9.3	9.6	9.9	10.1	10.1
90°	0.4	1.4	2.4	3.4	4.4	5.6	6.9	8.2	9.5	10.8	11.2
92.5°	8.4	8.1	7.8	7.5	7.2	7.6	8.6	9.5	10.5	11.5	12.1
95°	27.4	23.3	19.2	15.1	11.0	9.5	10.6	11.7	12.8	13.9	14.6
97.5°	55.1	53.2	51.4	49.6	47.7	43.2	36.0	28.8	21.7	14.5	15.3
100°	75.9	77.9	79.9	81.9	83.9	77.1	61.6	46.0	30.4	14.8	15.6
102.5°	99.6	101.1	102.5	104.0	105.4	97.6	80.6	63.6	46.6	29.6	27.1
105°	133.9	135.0	136.1	137.2	138.3	134.3	125.3	116.4	107.4	98.4	80.7
107.5°	170.0	170.9	171.8	172.6	173.5	174.7	176.1	177.5	178.9	180.3	167.4
110°	194.1	194.9	195.7	196.5	197.3	198.2	199.3	200.4	201.5	202.6	199.3



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.1	217.8	218.5	219.2	220.0	220.9	222.0	223.1	224.2	225.3	225.3
115°	251.1	251.7	252.3	252.9	253.5	254.3	255.2	256.1	257.0	257.9	258.9
117.5°	284.1	284.9	285.6	286.3	287.1	287.7	288.1	288.6	289.1	289.5	290.3
120°	304.6	305.5	306.4	307.3	308.2	308.8	309.1	309.4	309.7	310.0	310.8
122.5°	325.5	326.2	326.9	327.7	328.4	329.0	329.4	329.7	330.1	330.5	331.0
125°	354.0	354.8	355.6	356.4	357.2	357.8	358.2	358.6	359.0	359.4	359.6
127.5°	381.7	382.5	383.3	384.1	384.9	385.5	386.0	386.5	387.0	387.5	387.8
130°	399.0	399.8	400.6	401.4	402.2	402.8	403.2	403.6	404.0	404.3	404.7
132.5°	415.5	416.3	417.1	417.9	418.7	419.2	419.6	419.9	420.2	420.5	420.9
135°	440.7	441.3	441.9	442.5	443.1	443.6	444.0	444.4	444.8	445.2	445.5
137.5°	462.3	463.1	463.8	464.6	465.3	465.8	466.1	466.3	466.5	466.7	467.2
140°	476.7	477.3	477.9	478.5	479.1	479.5	479.8	480.1	480.4	480.7	481.1
142.5°	490.0	490.6	491.2	491.8	492.4	492.8	493.1	493.4	493.7	494.0	494.3
145°	508.6	509.3	510.0	510.7	511.4	511.8	512.0	512.2	512.4	512.6	512.8
147.5°	526.1	526.6	527.0	527.5	527.9	528.3	528.5	528.7	528.9	529.1	529.3
150°	536.9	537.2	537.5	537.8	538.1	538.3	538.5	538.7	538.9	539.1	539.3
152.5°	546.6	546.7	546.9	547.0	547.2	547.3	547.4	547.5	547.6	547.8	548.1
155°	560.2	560.0	559.8	559.7	559.5	559.4	559.5	559.6	559.7	559.8	560.3
157.5°	570.9	570.8	570.8	570.8	570.8	570.7	570.6	570.5	570.4	570.3	570.9
160°	577.3	577.2	577.1	577.0	576.9	576.8	576.7	576.6	576.5	576.4	577.0
162.5°	583.4	583.2	582.9	582.7	582.4	582.2	582.1	582.0	581.9	581.8	582.5
165°	590.8	590.5	590.2	589.9	589.6	589.4	589.3	589.2	589.1	589.0	589.8
167.5°	596.6	596.2	595.8	595.4	595.0	594.8	594.8	594.8	594.8	594.8	595.6
170°	599.8	599.4	599.0	598.6	598.2	598.0	598.0	598.0	598.0	598.0	598.8
172.5°	601.9	601.5	601.0	600.5	600.0	599.8	599.9	600.0	600.1	600.1	600.9
175°	604.7	604.2	603.7	603.2	602.7	602.5	602.6	602.7	602.8	602.9	603.6
177.5°	605.4	605.0	604.6	604.2	603.8	603.7	603.8	603.8	603.9	604.0	604.6
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	10.0	10.0	9.9	9.8	9.7	9.6	9.5	9.4
90°	11.6	12.0	12.4	12.7	12.9	13.1	13.3	13.5
92.5°	12.8	13.4	14.1	14.4	14.6	14.7	14.8	14.9
95°	15.3	16.0	16.7	17.1	17.1	17.1	17.1	17.1
97.5°	16.1	16.9	17.7	18.1	18.2	18.3	18.4	18.5
100°	16.4	17.2	18.0	18.5	18.6	18.7	18.8	18.9
102.5°	24.6	22.1	19.7	18.5	18.7	18.9	19.0	19.2
105°	63.0	45.4	27.7	19.0	19.2	19.4	19.6	19.8
107.5°	154.4	141.5	128.5	115.4	102.0	88.7	75.4	62.1
110°	196.0	192.7	189.4	180.7	166.4	152.1	137.8	123.6



TEST NUMBER: P332412

CATALOG NUMBER: S123RDIW-S560D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.4	225.4	225.5	224.0	221.0	218.0	215.0	212.0
115°	259.9	260.9	261.9	262.6	263.0	263.4	263.8	264.2
117.5°	291.1	291.9	292.7	293.1	293.2	293.3	293.4	293.5
120°	311.6	312.4	313.2	313.6	313.6	313.6	313.6	313.6
122.5°	331.6	332.2	332.7	333.0	333.1	333.2	333.3	333.4
125°	359.8	360.0	360.2	360.4	360.6	360.8	361.0	361.2
127.5°	388.1	388.4	388.7	388.8	388.6	388.4	388.2	388.0
130°	405.1	405.5	405.9	406.0	405.8	405.6	405.4	405.2
132.5°	421.3	421.7	422.1	422.2	421.9	421.6	421.3	421.1
135°	445.8	446.1	446.4	446.4	446.1	445.8	445.5	445.2
137.5°	467.7	468.1	468.6	468.8	468.6	468.4	468.2	468.0
140°	481.5	481.9	482.3	482.4	482.2	482.0	481.8	481.6
142.5°	494.7	495.0	495.3	495.3	495.0	494.8	494.5	494.2
145°	513.0	513.2	513.4	513.5	513.5	513.5	513.5	513.5
147.5°	529.5	529.7	529.9	529.7	529.3	528.8	528.4	527.9
150°	539.5	539.7	539.9	539.9	539.6	539.3	539.0	538.7
152.5°	548.5	548.8	549.2	549.1	548.7	548.2	547.8	547.3
155°	560.8	561.3	561.8	561.7	561.1	560.5	559.9	559.4
157.5°	571.5	572.1	572.7	572.6	571.8	571.1	570.3	569.5
160°	577.6	578.2	578.8	578.8	578.1	577.4	576.7	576.0
162.5°	583.2	583.9	584.5	584.6	583.9	583.3	582.7	582.1
165°	590.6	591.4	592.2	592.2	591.5	590.9	590.2	589.5
167.5°	596.4	597.1	597.9	597.9	597.1	596.4	595.6	594.8
170°	599.6	600.4	601.2	601.2	600.4	599.6	598.8	598.0
172.5°	601.7	602.5	603.3	603.3	602.4	601.5	600.7	599.8
175°	604.3	605.0	605.7	605.7	604.9	604.1	603.3	602.5
177.5°	605.3	605.9	606.6	606.5	605.7	604.9	604.1	603.3
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7

(END OF REPORT)