

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332443-927

Luminaire Tested: **S123RDIW-S775D1320U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332443-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1320U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6040.0 lumens  
Efficiency: N/A  
Efficacy: 98.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																				
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35																				
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30																				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	30	26																				
4	74	63	56	50	67	58	52	47	48	43	40	39	36	33	30	28	26	22																				
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20																				
6	62	51	43	38	57	47	40	35	39	34	30	32	28	25	25	23	21	18																				
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	20	18	16																				
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13																				
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	1.6
10°-20°	297.7	4.9
20°-30°	467.6	7.7
30°-40°	487.9	8.1
40°-50°	417.5	6.9
50°-60°	318.2	5.3
60°-70°	204.0	3.4
70°-80°	98.1	1.6
80°-90°	29.8	0.5
90°-100°	85.2	1.4
100°-110°	255.0	4.2
110°-120°	433.8	7.2
120°-130°	570.5	9.4
130°-140°	641.3	10.6
140°-150°	630.4	10.4
150°-160°	530.7	8.8
160°-170°	353.3	5.8
170°-180°	123.7	2.0
0°-30°	860.6	14.2
0°-40°	1348.4	22.3
0°-60°	2084.2	34.5
0°-90°	2416.1	40.0
90°-120°	774.0	12.8
90°-150°	2616.2	43.3
90°-180°	3624.0	60.0
0°-180°	6040.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	31	1	31	1	31	15
95°	80	61	80	61	80	82
105°	244	231	244	231	244	259
115°	438	437	438	437	438	433
125°	632	639	632	639	632	565
135°	828	829	828	829	828	637
145°	1006	1006	1006	1006	1006	628
155°	1150	1152	1150	1152	1150	529
165°	1250	1254	1250	1254	1250	353
175°	1300	1305	1300	1305	1300	123
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	9.5	10.1	9.3	9.5	9.4	9.7	9.4	9.3	9.7	9.3	9.0
90°	30.8	30.3	29.9	29.5	29.0	28.3	27.4	26.5	25.6	24.6	21.7
92.5°	41.5	41.7	42.1	42.3	42.6	42.4	41.7	40.9	40.2	39.5	37.8
95°	80.2	80.2	80.2	80.2	80.2	79.7	78.7	77.9	76.9	76.0	74.2
97.5°	123.3	123.4	123.5	123.6	123.7	123.2	122.2	121.0	120.0	119.0	117.6
100°	156.1	155.7	155.3	154.8	154.3	153.8	153.0	152.4	151.7	151.1	149.9
102.5°	189.9	190.0	190.0	190.1	190.2	190.0	189.3	188.5	187.9	187.2	185.7
105°	244.5	244.1	243.6	243.2	242.7	242.5	242.5	242.5	242.5	242.5	240.4
107.5°	301.4	301.7	302.0	302.3	302.5	302.3	301.6	300.9	300.2	299.4	298.6
110°	340.1	340.6	341.0	341.4	341.9	341.7	340.8	339.8	339.0	338.0	337.5



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.2	381.3	381.4	381.4	381.5	381.0	379.9	378.8	377.8	376.7	376.6
115°	437.7	437.9	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7	438.2
117.5°	495.0	495.7	496.3	496.9	497.6	497.9	498.0	498.0	498.0	498.1	498.7
120°	535.3	535.8	536.2	536.7	537.1	537.5	537.7	537.9	538.1	538.4	539.6
122.5°	573.9	574.6	575.2	575.8	576.5	577.1	577.7	578.3	578.8	579.5	580.0
125°	631.8	632.8	633.7	634.6	635.6	636.4	637.4	638.3	639.2	640.1	640.6
127.5°	689.6	690.7	691.7	692.8	693.8	695.0	696.2	697.5	698.8	700.1	700.6
130°	727.5	729.0	730.6	732.2	733.8	735.1	736.0	736.9	737.8	738.7	739.4
132.5°	766.9	768.1	769.4	770.6	771.8	773.0	774.0	775.2	776.3	777.4	777.8
135°	828.1	828.5	829.0	829.5	830.0	830.6	831.6	832.4	833.4	834.2	834.5
137.5°	882.2	883.0	883.9	884.8	885.7	886.5	887.5	888.4	889.4	890.4	889.8
140°	917.5	919.1	920.7	922.3	923.9	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.7	954.9	956.2	957.4	958.6	959.3	959.6	959.8	960.0	960.3	959.8
145°	1005.8	1006.8	1007.7	1008.6	1009.6	1010.1	1010.3	1010.5	1010.7	1011.0	1010.3
147.5°	1052.3	1053.7	1055.0	1056.5	1057.8	1058.4	1058.4	1058.4	1058.4	1058.4	1057.8
150°	1081.9	1083.2	1084.7	1086.0	1087.3	1088.1	1088.1	1088.1	1088.1	1088.1	1087.6
152.5°	1110.6	1111.8	1113.0	1114.2	1115.4	1115.8	1115.5	1115.1	1114.8	1114.4	1114.1
155°	1149.7	1151.3	1152.9	1154.5	1156.1	1156.4	1155.6	1154.6	1153.7	1152.8	1152.5
157.5°	1185.3	1186.5	1187.8	1189.1	1190.3	1190.6	1189.5	1188.6	1187.6	1186.7	1186.5
160°	1208.2	1209.2	1210.1	1211.0	1212.0	1211.8	1210.7	1209.5	1208.4	1207.2	1207.2
162.5°	1225.5	1227.0	1228.4	1229.9	1231.4	1231.5	1230.4	1229.2	1228.1	1226.9	1226.8
165°	1250.4	1252.0	1253.6	1255.2	1256.8	1256.9	1255.5	1254.2	1252.8	1251.4	1251.4
167.5°	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5	1271.4
170°	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2	1282.2
172.5°	1290.5	1292.0	1293.6	1295.3	1296.9	1297.0	1295.5	1294.1	1292.7	1291.3	1291.3
175°	1299.7	1301.3	1302.9	1304.5	1306.1	1306.2	1304.9	1303.5	1302.1	1300.8	1300.8
177.5°	1304.6	1305.9	1307.2	1308.4	1309.8	1309.9	1308.8	1307.7	1306.5	1305.4	1305.4
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	9.0	8.2	8.2	7.7	8.2	8.1	9.6	10.9	11.6	10.8	11.2
90°	18.7	15.8	12.8	10.1	7.8	5.6	3.3	1.0	3.3	5.6	7.8
92.5°	36.0	34.4	32.7	31.1	29.5	28.0	26.4	24.9	26.4	28.0	29.5
95°	72.4	70.6	68.8	67.0	65.4	63.8	62.2	60.6	62.2	63.8	65.4
97.5°	116.3	115.0	113.7	112.4	111.2	110.0	108.8	107.7	108.8	110.0	111.2
100°	148.8	147.6	146.5	145.2	143.9	142.4	141.1	139.7	141.1	142.4	143.9
102.5°	184.2	182.7	181.2	180.0	179.2	178.4	177.5	176.7	177.5	178.4	179.2
105°	238.4	236.3	234.2	233.0	232.5	232.1	231.6	231.2	231.6	232.1	232.5
107.5°	297.8	296.9	296.1	295.6	295.3	295.0	294.8	294.5	294.8	295.0	295.3
110°	337.2	336.7	336.2	335.7	335.3	334.9	334.4	333.9	334.4	334.9	335.3





TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	376.4	376.4	376.3	376.1	375.8	375.6	375.3	375.0	375.3	375.6	375.8
115°	438.6	439.0	439.5	439.4	438.7	438.0	437.4	436.7	437.4	438.0	438.7
117.5°	499.3	499.9	500.5	500.6	500.1	499.6	499.2	498.8	499.2	499.6	500.1
120°	540.7	541.8	543.0	542.8	541.5	540.1	538.7	537.3	538.7	540.1	541.5
122.5°	580.7	581.2	581.9	581.6	580.7	579.6	578.6	577.7	578.6	579.6	580.7
125°	641.0	641.4	641.9	641.8	641.1	640.4	639.8	639.1	639.8	640.4	641.1
127.5°	701.1	701.6	702.1	701.6	700.1	698.7	697.3	695.8	697.3	698.7	700.1
130°	740.1	740.8	741.5	740.9	739.1	737.3	735.4	733.6	735.4	737.3	739.1
132.5°	778.4	778.9	779.3	778.7	776.9	775.1	773.2	771.4	773.2	775.1	776.9
135°	834.7	835.0	835.2	834.6	833.2	831.9	830.5	829.2	830.5	831.9	833.2
137.5°	889.2	888.6	888.0	887.2	886.0	884.9	883.7	882.6	883.7	884.9	886.0
140°	925.3	925.0	924.8	924.2	923.0	921.9	920.7	919.6	920.7	921.9	923.0
142.5°	959.4	959.0	958.6	957.8	956.7	955.5	954.4	953.2	954.4	955.5	956.7
145°	1009.6	1008.9	1008.3	1007.7	1007.3	1006.8	1006.3	1005.8	1006.3	1006.8	1007.3
147.5°	1057.2	1056.5	1055.9	1055.2	1054.4	1053.5	1052.7	1051.9	1052.7	1053.5	1054.4
150°	1087.1	1086.7	1086.2	1085.8	1085.3	1084.9	1084.4	1083.9	1084.4	1084.9	1085.3
152.5°	1113.8	1113.6	1113.3	1112.8	1112.1	1111.5	1110.9	1110.2	1110.9	1111.5	1112.1
155°	1152.3	1152.1	1151.9	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8	1151.8
157.5°	1186.3	1186.1	1186.0	1186.0	1186.3	1186.5	1186.8	1187.1	1186.8	1186.5	1186.3
160°	1207.2	1207.2	1207.2	1207.4	1207.9	1208.4	1208.9	1209.3	1208.9	1208.4	1207.9
162.5°	1226.6	1226.5	1226.2	1226.5	1227.1	1227.7	1228.4	1229.0	1228.4	1227.7	1227.1
165°	1251.4	1251.4	1251.4	1251.8	1252.4	1253.2	1253.8	1254.5	1253.8	1253.2	1252.4
167.5°	1271.2	1271.0	1270.8	1271.2	1272.1	1273.0	1273.9	1274.9	1273.9	1273.0	1272.1
170°	1282.2	1282.2	1282.2	1282.7	1283.7	1284.5	1285.5	1286.3	1285.5	1284.5	1283.7
172.5°	1291.3	1291.3	1291.3	1291.7	1292.7	1293.6	1294.5	1295.4	1294.5	1293.6	1292.7
175°	1300.8	1300.8	1300.8	1301.2	1302.1	1303.1	1303.9	1304.9	1303.9	1303.1	1302.1
177.5°	1305.4	1305.4	1305.4	1305.8	1306.5	1307.3	1308.1	1308.8	1308.1	1307.3	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.3	12.8	13.8	14.7	15.6	15.8	16.4	16.6	17.1	17.3	17.4
90°	10.1	12.8	15.8	18.7	21.7	24.6	25.6	26.5	27.4	28.3	29.0
92.5°	31.1	32.7	34.4	36.0	37.8	39.5	40.2	40.9	41.7	42.4	42.6
95°	67.0	68.8	70.6	72.4	74.2	76.0	76.9	77.9	78.7	79.7	80.2
97.5°	112.4	113.7	115.0	116.3	117.6	119.0	120.0	121.0	122.2	123.2	123.7
100°	145.2	146.5	147.6	148.8	149.9	151.1	151.7	152.4	153.0	153.8	154.3
102.5°	180.0	181.2	182.7	184.2	185.7	187.2	187.9	188.5	189.3	190.0	190.2
105°	233.0	234.2	236.3	238.4	240.4	242.5	242.5	242.5	242.5	242.5	242.7
107.5°	295.6	296.1	296.9	297.8	298.6	299.4	300.2	300.9	301.6	302.3	302.5
110°	335.7	336.2	336.7	337.2	337.5	338.0	339.0	339.8	340.8	341.7	341.9



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	376.1	376.3	376.4	376.4	376.6	376.7	377.8	378.8	379.9	381.0	381.5
115°	439.4	439.5	439.0	438.6	438.2	437.7	437.9	438.2	438.4	438.6	438.6
117.5°	500.6	500.5	499.9	499.3	498.7	498.1	498.0	498.0	498.0	497.9	497.6
120°	542.8	543.0	541.8	540.7	539.6	538.4	538.1	537.9	537.7	537.5	537.1
122.5°	581.6	581.9	581.2	580.7	580.0	579.5	578.8	578.3	577.7	577.1	576.5
125°	641.8	641.9	641.4	641.0	640.6	640.1	639.2	638.3	637.4	636.4	635.6
127.5°	701.6	702.1	701.6	701.1	700.6	700.1	698.8	697.5	696.2	695.0	693.8
130°	740.9	741.5	740.8	740.1	739.4	738.7	737.8	736.9	736.0	735.1	733.8
132.5°	778.7	779.3	778.9	778.4	777.8	777.4	776.3	775.2	774.0	773.0	771.8
135°	834.6	835.2	835.0	834.7	834.5	834.2	833.4	832.4	831.6	830.6	830.0
137.5°	887.2	888.0	888.6	889.2	889.8	890.4	889.4	888.4	887.5	886.5	885.7
140°	924.2	924.8	925.0	925.3	925.5	925.7	925.5	925.3	925.0	924.8	923.9
142.5°	957.8	958.6	959.0	959.4	959.8	960.3	960.0	959.8	959.6	959.3	958.6
145°	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7	1010.5	1010.3	1010.1	1009.6
147.5°	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4	1058.4	1058.4	1058.4	1057.8
150°	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1	1088.1	1088.1	1088.1	1087.3
152.5°	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8	1115.1	1115.5	1115.8	1115.4
155°	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7	1154.6	1155.6	1156.4	1156.1
157.5°	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6	1188.6	1189.5	1190.6	1190.3
160°	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4	1209.5	1210.7	1211.8	1212.0
162.5°	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1	1229.2	1230.4	1231.5	1231.4
165°	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8	1254.2	1255.5	1256.9	1256.8
167.5°	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2
170°	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6
172.5°	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7	1294.1	1295.5	1297.0	1296.9
175°	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1	1303.5	1304.9	1306.2	1306.1
177.5°	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5	1307.7	1308.8	1309.9	1309.8
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	18.1	17.6	17.7	18.1	17.7	17.6	18.1	17.4	17.3	17.1	16.6
90°	29.5	29.9	30.3	30.8	30.3	29.9	29.5	29.0	28.3	27.4	26.5
92.5°	42.3	42.1	41.7	41.5	41.7	42.1	42.3	42.6	42.4	41.7	40.9
95°	80.2	80.2	80.2	80.2	80.2	80.2	80.2	80.2	79.7	78.7	77.9
97.5°	123.6	123.5	123.4	123.3	123.4	123.5	123.6	123.7	123.2	122.2	121.0
100°	154.8	155.3	155.7	156.1	155.7	155.3	154.8	154.3	153.8	153.0	152.4
102.5°	190.1	190.0	190.0	189.9	190.0	190.0	190.1	190.2	190.0	189.3	188.5
105°	243.2	243.6	244.1	244.5	244.1	243.6	243.2	242.7	242.5	242.5	242.5
107.5°	302.3	302.0	301.7	301.4	301.7	302.0	302.3	302.5	302.3	301.6	300.9
110°	341.4	341.0	340.6	340.1	340.6	341.0	341.4	341.9	341.7	340.8	339.8



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	381.4	381.4	381.3	381.2	381.3	381.4	381.4	381.5	381.0	379.9	378.8
115°	438.4	438.2	437.9	437.7	437.9	438.2	438.4	438.6	438.6	438.4	438.2
117.5°	496.9	496.3	495.7	495.0	495.7	496.3	496.9	497.6	497.9	498.0	498.0
120°	536.7	536.2	535.8	535.3	535.8	536.2	536.7	537.1	537.5	537.7	537.9
122.5°	575.8	575.2	574.6	573.9	574.6	575.2	575.8	576.5	577.1	577.7	578.3
125°	634.6	633.7	632.8	631.8	632.8	633.7	634.6	635.6	636.4	637.4	638.3
127.5°	692.8	691.7	690.7	689.6	690.7	691.7	692.8	693.8	695.0	696.2	697.5
130°	732.2	730.6	729.0	727.5	729.0	730.6	732.2	733.8	735.1	736.0	736.9
132.5°	770.6	769.4	768.1	766.9	768.1	769.4	770.6	771.8	773.0	774.0	775.2
135°	829.5	829.0	828.5	828.1	828.5	829.0	829.5	830.0	830.6	831.6	832.4
137.5°	884.8	883.9	883.0	882.2	883.0	883.9	884.8	885.7	886.5	887.5	888.4
140°	922.3	920.7	919.1	917.5	919.1	920.7	922.3	923.9	924.8	925.0	925.3
142.5°	957.4	956.2	954.9	953.7	954.9	956.2	957.4	958.6	959.3	959.6	959.8
145°	1008.6	1007.7	1006.8	1005.8	1006.8	1007.7	1008.6	1009.6	1010.1	1010.3	1010.5
147.5°	1056.5	1055.0	1053.7	1052.3	1053.7	1055.0	1056.5	1057.8	1058.4	1058.4	1058.4
150°	1086.0	1084.7	1083.2	1081.9	1083.2	1084.7	1086.0	1087.3	1088.1	1088.1	1088.1
152.5°	1114.2	1113.0	1111.8	1110.6	1111.8	1113.0	1114.2	1115.4	1115.8	1115.5	1115.1
155°	1154.5	1152.9	1151.3	1149.7	1151.3	1152.9	1154.5	1156.1	1156.4	1155.6	1154.6
157.5°	1189.1	1187.8	1186.5	1185.3	1186.5	1187.8	1189.1	1190.3	1190.6	1189.5	1188.6
160°	1211.0	1210.1	1209.2	1208.2	1209.2	1210.1	1211.0	1212.0	1211.8	1210.7	1209.5
162.5°	1229.9	1228.4	1227.0	1225.5	1227.0	1228.4	1229.9	1231.4	1231.5	1230.4	1229.2
165°	1255.2	1253.6	1252.0	1250.4	1252.0	1253.6	1255.2	1256.8	1256.9	1255.5	1254.2
167.5°	1275.8	1274.4	1273.0	1271.5	1273.0	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4
170°	1287.1	1285.5	1283.8	1282.2	1283.8	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5
172.5°	1295.3	1293.6	1292.0	1290.5	1292.0	1293.6	1295.3	1296.9	1297.0	1295.5	1294.1
175°	1304.5	1302.9	1301.3	1299.7	1301.3	1302.9	1304.5	1306.1	1306.2	1304.9	1303.5
177.5°	1308.4	1307.2	1305.9	1304.6	1305.9	1307.2	1308.4	1309.8	1309.9	1308.8	1307.7
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	16.4	15.8	15.6	14.7	13.8	12.8	11.3	11.2	10.8	11.6	10.9
90°	25.6	24.6	21.7	18.7	15.8	12.8	10.1	7.8	5.6	3.3	1.0
92.5°	40.2	39.5	37.8	36.0	34.4	32.7	31.1	29.5	28.0	26.4	24.9
95°	76.9	76.0	74.2	72.4	70.6	68.8	67.0	65.4	63.8	62.2	60.6
97.5°	120.0	119.0	117.6	116.3	115.0	113.7	112.4	111.2	110.0	108.8	107.7
100°	151.7	151.1	149.9	148.8	147.6	146.5	145.2	143.9	142.4	141.1	139.7
102.5°	187.9	187.2	185.7	184.2	182.7	181.2	180.0	179.2	178.4	177.5	176.7
105°	242.5	242.5	240.4	238.4	236.3	234.2	233.0	232.5	232.1	231.6	231.2
107.5°	300.2	299.4	298.6	297.8	296.9	296.1	295.6	295.3	295.0	294.8	294.5
110°	339.0	338.0	337.5	337.2	336.7	336.2	335.7	335.3	334.9	334.4	333.9



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	377.8	376.7	376.6	376.4	376.4	376.3	376.1	375.8	375.6	375.3	375.0
115°	437.9	437.7	438.2	438.6	439.0	439.5	439.4	438.7	438.0	437.4	436.7
117.5°	498.0	498.1	498.7	499.3	499.9	500.5	500.6	500.1	499.6	499.2	498.8
120°	538.1	538.4	539.6	540.7	541.8	543.0	542.8	541.5	540.1	538.7	537.3
122.5°	578.8	579.5	580.0	580.7	581.2	581.9	581.6	580.7	579.6	578.6	577.7
125°	639.2	640.1	640.6	641.0	641.4	641.9	641.8	641.1	640.4	639.8	639.1
127.5°	698.8	700.1	700.6	701.1	701.6	702.1	701.6	700.1	698.7	697.3	695.8
130°	737.8	738.7	739.4	740.1	740.8	741.5	740.9	739.1	737.3	735.4	733.6
132.5°	776.3	777.4	777.8	778.4	778.9	779.3	778.7	776.9	775.1	773.2	771.4
135°	833.4	834.2	834.5	834.7	835.0	835.2	834.6	833.2	831.9	830.5	829.2
137.5°	889.4	890.4	889.8	889.2	888.6	888.0	887.2	886.0	884.9	883.7	882.6
140°	925.5	925.7	925.5	925.3	925.0	924.8	924.2	923.0	921.9	920.7	919.6
142.5°	960.0	960.3	959.8	959.4	959.0	958.6	957.8	956.7	955.5	954.4	953.2
145°	1010.7	1011.0	1010.3	1009.6	1008.9	1008.3	1007.7	1007.3	1006.8	1006.3	1005.8
147.5°	1058.4	1058.4	1057.8	1057.2	1056.5	1055.9	1055.2	1054.4	1053.5	1052.7	1051.9
150°	1088.1	1088.1	1087.6	1087.1	1086.7	1086.2	1085.8	1085.3	1084.9	1084.4	1083.9
152.5°	1114.8	1114.4	1114.1	1113.8	1113.6	1113.3	1112.8	1112.1	1111.5	1110.9	1110.2
155°	1153.7	1152.8	1152.5	1152.3	1152.1	1151.9	1151.8	1151.8	1151.8	1151.8	1151.8
157.5°	1187.6	1186.7	1186.5	1186.3	1186.1	1186.0	1186.0	1186.3	1186.5	1186.8	1187.1
160°	1208.4	1207.2	1207.2	1207.2	1207.2	1207.2	1207.4	1207.9	1208.4	1208.9	1209.3
162.5°	1228.1	1226.9	1226.8	1226.6	1226.5	1226.2	1226.5	1227.1	1227.7	1228.4	1229.0
165°	1252.8	1251.4	1251.4	1251.4	1251.4	1251.4	1251.8	1252.4	1253.2	1253.8	1254.5
167.5°	1273.0	1271.5	1271.4	1271.2	1271.0	1270.8	1271.2	1272.1	1273.0	1273.9	1274.9
170°	1283.8	1282.2	1282.2	1282.2	1282.2	1282.2	1282.7	1283.7	1284.5	1285.5	1286.3
172.5°	1292.7	1291.3	1291.3	1291.3	1291.3	1291.3	1291.7	1292.7	1293.6	1294.5	1295.4
175°	1302.1	1300.8	1300.8	1300.8	1300.8	1300.8	1301.2	1302.1	1303.1	1303.9	1304.9
177.5°	1306.5	1305.4	1305.4	1305.4	1305.4	1305.4	1305.8	1306.5	1307.3	1308.1	1308.8
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.6	8.1	8.2	7.7	8.2	8.2	9.0	9.0	9.3	9.7	9.3
90°	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6	26.5
92.5°	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2	40.9
95°	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9	77.9
97.5°	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0	121.0
100°	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7	152.4
102.5°	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9	188.5
105°	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5	242.5
107.5°	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2	300.9
110°	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0	339.8





TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8	378.8
115°	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9	438.2
117.5°	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0	498.0
120°	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1	537.9
122.5°	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8	578.3
125°	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2	638.3
127.5°	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8	697.5
130°	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8	736.9
132.5°	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3	775.2
135°	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4	832.4
137.5°	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4	888.4
140°	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5	925.3
142.5°	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0	959.8
145°	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7	1010.5
147.5°	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4	1058.4
150°	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1	1088.1
152.5°	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8	1115.1
155°	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7	1154.6
157.5°	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6	1188.6
160°	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4	1209.5
162.5°	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1	1229.2
165°	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8	1254.2
167.5°	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0	1274.4
170°	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8	1285.5
172.5°	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7	1294.1
175°	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1	1303.5
177.5°	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5	1307.7
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	9.4	9.7	9.4	9.5	9.3	10.1	9.5
90°	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	340.8	341.7	341.9	341.4	341.0	340.6	340.1



TEST NUMBER: P332443-927

CATALOG NUMBER: S123RDIW-S775D1320U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)