

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332440

Luminaire Tested: **S123RDIW-S775D1030U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332440  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1030U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7043.1 lumens  
Efficiency: N/A  
Efficacy: 133.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41																			
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35																			
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30																			
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26																			
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22																			
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20																			
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17																			
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15																			
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14																			
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13																			
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	1.7
10°-20°	337.3	4.8
20°-30°	485.7	6.9
30°-40°	547.1	7.8
40°-50°	523.4	7.4
50°-60°	428.6	6.1
60°-70°	289.2	4.1
70°-80°	145.5	2.1
80°-90°	42.3	0.6
90°-100°	49.2	0.7
100°-110°	234.3	3.3
110°-120°	562.7	8.0
120°-130°	716.5	10.2
130°-140°	765.6	10.9
140°-150°	715.9	10.2
150°-160°	577.5	8.2
160°-170°	372.7	5.3
170°-180°	128.4	1.8
0°-30°	944.3	13.4
0°-40°	1491.4	21.2
0°-60°	2443.4	34.7
0°-90°	2920.4	41.5
90°-120°	846.1	12.0
90°-150°	3044.1	43.2
90°-180°	4123.0	58.5
0°-180°	7043.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	11	24	28	30	6
95°	61	23	31	38	38	76
105°	299	305	220	52	44	317
115°	562	568	576	586	591	554
125°	792	799	804	806	808	707
135°	985	991	995	998	995	758
145°	1137	1144	1146	1148	1148	711
155°	1252	1251	1252	1256	1250	577
165°	1321	1318	1317	1324	1318	373
175°	1352	1347	1348	1354	1347	129
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.7	17.1	15.5	13.9	13.4	14.0	14.6	15.1	15.7	15.7
90°	1.0	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0
92.5°	18.7	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1
95°	61.3	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7
97.5°	123.1	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1
100°	169.7	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9
102.5°	222.8	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6
105°	299.3	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5
107.5°	380.1	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2
110°	433.9	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6



TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.3	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7
115°	561.5	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8
117.5°	635.2	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0
120°	681.0	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8
122.5°	727.6	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1
125°	791.5	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0
127.5°	853.3	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9
130°	891.9	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9
132.5°	928.9	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0
135°	985.3	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0
137.5°	1033.5	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4
140°	1065.7	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6
142.5°	1095.4	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2
145°	1137.0	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5
147.5°	1176.2	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2
150°	1200.3	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7
152.5°	1222.0	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4
155°	1252.5	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6
157.5°	1276.2	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3
160°	1290.7	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0
162.5°	1304.3	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2
165°	1320.8	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6
167.5°	1333.6	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4
170°	1340.9	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6
172.5°	1345.7	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5
175°	1351.9	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5
177.5°	1353.5	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	15.7	15.7	15.7	15.6	15.5	15.4	15.3	15.2
90°	25.9	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	28.6	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	34.3	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	35.9	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	36.7	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	55.0	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	141.0	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	345.2	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	438.3	430.9	423.5	403.9	372.0	340.0	308.1	276.2





TEST NUMBER: P332440

CATALOG NUMBER: S123RDIW-S775D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.9	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	581.0	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	650.8	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	696.6	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	741.3	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.4	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	867.6	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	905.8	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	941.9	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1045.5	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1076.5	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1105.9	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1146.9	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1183.7	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.2	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1226.2	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1253.7	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1277.7	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1291.3	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1303.7	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1320.3	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1345.3	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1351.0	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1353.2	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)