

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332446-927

Luminaire Tested: **S123RDIW-S775D1535U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332446-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1535U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7277.9 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	79	76	65	63	61	50	49	48	37	36	35	29
2	86	79	74	69	78	72	67	63	58	54	51	45	42	40	33	31	30	25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	29	28	26	21
4	72	62	55	49	65	56	50	45	46	41	37	36	32	30	26	24	23	19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15
7	57	45	37	32	51	41	34	30	33	29	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	1.3
10°-20°	297.7	4.1
20°-30°	467.6	6.4
30°-40°	487.9	6.7
40°-50°	417.5	5.7
50°-60°	318.2	4.4
60°-70°	204.0	2.8
70°-80°	98.1	1.3
80°-90°	30.4	0.4
90°-100°	58.0	0.8
100°-110°	276.2	3.8
110°-120°	663.5	9.1
120°-130°	844.9	11.6
130°-140°	902.7	12.4
140°-150°	844.1	11.6
150°-160°	680.9	9.4
160°-170°	439.5	6.0
170°-180°	151.5	2.1
0°-30°	860.6	11.8
0°-40°	1348.4	18.5
0°-60°	2084.2	28.6
0°-90°	2416.7	33.2
90°-120°	997.6	13.7
90°-150°	3589.3	49.3
90°-180°	4861.0	66.8
0°-180°	7277.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	36	1	36	1	36	17
95°	45	72	45	72	45	38
105°	52	353	52	353	52	119
115°	696	662	696	662	696	643
125°	952	933	952	933	952	850
135°	1174	1162	1174	1162	1174	905
145°	1354	1341	1354	1341	1354	845
155°	1474	1477	1474	1477	1474	680
165°	1554	1557	1554	1557	1554	439
175°	1588	1594	1588	1594	1588	151
180°	1594	1594	1594	1594	1594	



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	10.5	11.0	10.2	10.5	10.3	10.5	10.3	10.1	10.5	10.0	9.7
90°	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5	29.5	28.4	25.0
92.5°	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7	32.0	30.3	27.7
95°	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4	38.6	36.7	33.8
97.5°	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4	40.2	38.1	35.1
100°	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3	41.2	39.1	37.2
102.5°	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9	71.4	78.0	122.8
105°	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2	212.8	259.4	283.0
107.5°	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0	441.2	475.4	471.7
110°	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7	525.5	534.1	531.2



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1	594.0	593.8	590.9
115°	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1	682.4	679.8	677.4
117.5°	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4	765.2	763.2	761.9
120°	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4	819.3	817.1	816.3
122.5°	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1	872.7	871.2	870.1
125°	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5	948.0	947.5	946.4
127.5°	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0	1022.2	1021.4	1020.1
130°	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9	1066.9	1065.9	1064.9
132.5°	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6	1109.5	1108.5	1107.6
135°	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6	1172.6
137.5°	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8	1231.5	1230.3	1229.7
140°	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3	1268.3	1267.2	1266.4
142.5°	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9	1303.1	1302.3	1301.5
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3	1351.8	1351.3	1350.8
147.5°	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7	1395.2	1394.6	1394.1
150°	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2	1421.7	1421.2	1420.6
152.5°	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8	1444.9	1443.9	1443.6
155°	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3	1476.9	1475.6	1475.4
157.5°	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5	1504.9	1503.3	1503.6
160°	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7	1521.1	1519.5	1519.7
162.5°	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2	1535.5	1533.7	1533.9
165°	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8	1554.7	1552.6	1552.9
167.5°	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8	1567.8
170°	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3	1576.3
172.5°	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2	1584.1	1582.0	1581.8
175°	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0	1591.2	1589.4	1589.0
177.5°	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5	1593.9	1592.2	1592.0
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	9.6	8.6	8.6	8.0	8.5	8.2	9.7	10.9	11.7	10.9	11.4
90°	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2	3.8	6.4	9.1
92.5°	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0	21.3	20.5	19.8
95°	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2	61.5	50.7	39.8
97.5°	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2	140.4	135.5	130.6
100°	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2	205.4	210.6	215.9
102.5°	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7	266.5	270.3	274.0
105°	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9	355.8	358.7	361.6
107.5°	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1	450.4	452.7	455.1
110°	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6	513.7	515.8	517.9





TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3	574.2	576.1	578.0
115°	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0	663.6	665.2	666.8
117.5°	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9	750.9	752.8	754.8
120°	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0	805.3	807.7	810.1
122.5°	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9	859.8	861.8	863.7
125°	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2	935.3	937.5	939.5
127.5°	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2	1008.3	1010.4	1012.5
130°	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6	1053.8	1055.9	1058.0
132.5°	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3	1097.3	1099.5	1101.5
135°	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8	1163.4	1165.0	1166.6
137.5°	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6	1220.7	1222.7	1224.6
140°	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6	1258.1	1259.7	1261.3
142.5°	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6	1293.2	1294.7	1296.3
145°	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6	1342.4	1344.3	1346.2
147.5°	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8	1388.1	1389.3	1390.4
150°	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2	1416.0	1416.8	1417.6
152.5°	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8	1441.2	1441.5	1441.9
155°	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8	1476.3	1475.8	1475.3
157.5°	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8	1504.8	1504.7	1504.6
160°	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9	1521.5	1521.3	1521.1
162.5°	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9	1537.2	1536.6	1535.9
165°	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4	1556.6	1555.8	1555.0
167.5°	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5	1571.5	1570.4	1569.4
170°	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0	1580.0	1578.9	1577.9
172.5°	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7	1585.5	1584.2	1582.9
175°	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0	1592.8	1591.4	1590.1
177.5°	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9	1594.9	1593.9	1592.8
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	11.6	13.2	14.3	15.3	16.3	16.6	17.2	17.3	17.9	18.1	18.3
90°	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5	31.6	32.6	33.4
92.5°	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7	35.4	37.1	38.0
95°	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4	42.2	44.0	45.0
97.5°	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4	44.4	46.6	47.8
100°	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3	45.4	47.5	48.7
102.5°	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9	58.4	51.8	48.8
105°	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2	119.6	73.0	50.0
107.5°	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0	372.9	338.7	304.1
110°	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7	508.0	499.4	476.2



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1	594.3	594.5	590.6
115°	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1	687.7	690.3	692.1
117.5°	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4	769.4	771.6	772.8
120°	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4	823.5	825.6	826.6
122.5°	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1	875.6	877.1	877.9
125°	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5	949.0	949.5	950.1
127.5°	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0	1023.9	1024.7	1024.8
130°	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9	1069.1	1070.1	1070.3
132.5°	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6	1111.7	1112.7	1112.9
135°	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8
137.5°	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8	1234.1	1235.3	1235.6
140°	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3	1270.3	1271.4	1271.7
142.5°	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9	1304.8	1305.6	1305.7
145°	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3	1352.9	1353.4	1353.7
147.5°	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7	1396.2	1396.8	1396.4
150°	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2	1422.8	1423.2	1423.2
152.5°	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8	1446.8	1447.7	1447.6
155°	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3	1479.6	1480.9	1480.7
157.5°	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5	1508.1	1509.7	1509.4
160°	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7	1524.2	1525.7	1525.7
162.5°	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2	1539.1	1540.8	1540.9
165°	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8	1558.9	1561.1	1561.2
167.5°	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2
170°	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8
172.5°	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2	1588.3	1590.4	1590.3
175°	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0	1594.8	1596.7	1596.6
177.5°	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5	1597.2	1598.9	1598.7
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	19.1	18.5	18.6	19.0	18.6	18.5	19.1	18.3	18.1	17.9	17.3
90°	34.0	34.5	35.0	35.5	35.0	34.5	34.0	33.4	32.6	31.6	30.5
92.5°	38.3	38.7	39.0	39.3	39.0	38.7	38.3	38.0	37.1	35.4	33.7
95°	45.0	45.0	45.0	45.0	45.0	45.0	45.0	45.0	44.0	42.2	40.4
97.5°	48.0	48.2	48.6	48.8	48.6	48.2	48.0	47.8	46.6	44.4	42.4
100°	49.0	49.2	49.5	49.7	49.5	49.2	49.0	48.7	47.5	45.4	43.3
102.5°	49.3	49.7	50.2	50.7	50.2	49.7	49.3	48.8	51.8	58.4	64.9
105°	50.5	51.1	51.6	52.1	51.6	51.1	50.5	50.0	73.0	119.6	166.2
107.5°	269.0	233.9	198.8	163.7	198.8	233.9	269.0	304.1	338.7	372.9	407.0
110°	438.6	400.9	363.3	325.7	363.3	400.9	438.6	476.2	499.4	508.0	516.7



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	582.6	574.6	566.7	558.7	566.7	574.6	582.6	590.6	594.5	594.3	594.1
115°	693.2	694.3	695.3	696.4	695.3	694.3	693.2	692.1	690.3	687.7	685.1
117.5°	772.9	773.2	773.4	773.6	773.4	773.2	772.9	772.8	771.6	769.4	767.4
120°	826.6	826.6	826.6	826.6	826.6	826.6	826.6	826.6	825.6	823.5	821.4
122.5°	878.1	878.3	878.5	878.8	878.5	878.3	878.1	877.9	877.1	875.6	874.1
125°	950.6	951.1	951.6	952.2	951.6	951.1	950.6	950.1	949.5	949.0	948.5
127.5°	1024.4	1023.8	1023.3	1022.8	1023.3	1023.8	1024.4	1024.8	1024.7	1023.9	1023.0
130°	1069.8	1069.3	1068.7	1068.3	1068.7	1069.3	1069.8	1070.3	1070.1	1069.1	1067.9
132.5°	1112.1	1111.4	1110.6	1109.9	1110.6	1111.4	1112.1	1112.9	1112.7	1111.7	1110.6
135°	1176.0	1175.2	1174.4	1173.6	1174.4	1175.2	1176.0	1176.8	1176.8	1176.0	1175.2
137.5°	1235.2	1234.6	1234.1	1233.6	1234.1	1234.6	1235.2	1235.6	1235.3	1234.1	1232.8
140°	1271.1	1270.7	1270.1	1269.6	1270.1	1270.7	1271.1	1271.7	1271.4	1270.3	1269.3
142.5°	1305.0	1304.2	1303.5	1302.7	1303.5	1304.2	1305.0	1305.7	1305.6	1304.8	1303.9
145°	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.7	1353.4	1352.9	1352.3
147.5°	1395.2	1394.0	1392.7	1391.5	1392.7	1394.0	1395.2	1396.4	1396.8	1396.2	1395.7
150°	1422.4	1421.6	1420.8	1420.0	1420.8	1421.6	1422.4	1423.2	1423.2	1422.8	1422.2
152.5°	1446.4	1445.1	1443.9	1442.7	1443.9	1445.1	1446.4	1447.6	1447.7	1446.8	1445.8
155°	1479.2	1477.6	1476.0	1474.5	1476.0	1477.6	1479.2	1480.7	1480.9	1479.6	1478.3
157.5°	1507.4	1505.3	1503.2	1501.2	1503.2	1505.3	1507.4	1509.4	1509.7	1508.1	1506.5
160°	1523.8	1521.9	1520.1	1518.3	1520.1	1521.9	1523.8	1525.7	1525.7	1524.2	1522.7
162.5°	1539.3	1537.6	1536.0	1534.4	1536.0	1537.6	1539.3	1540.9	1540.8	1539.1	1537.2
165°	1559.3	1557.5	1555.6	1553.8	1555.6	1557.5	1559.3	1561.2	1561.1	1558.9	1556.8
167.5°	1574.1	1572.0	1569.9	1567.8	1569.9	1572.0	1574.1	1576.2	1576.2	1574.1	1572.0
170°	1582.6	1580.5	1578.4	1576.3	1578.4	1580.5	1582.6	1584.8	1584.8	1582.6	1580.5
172.5°	1588.0	1585.7	1583.3	1581.0	1583.3	1585.7	1588.0	1590.3	1590.4	1588.3	1586.2
175°	1594.4	1592.4	1590.2	1588.2	1590.2	1592.4	1594.4	1596.6	1596.7	1594.8	1593.0
177.5°	1596.6	1594.5	1592.4	1590.3	1592.4	1594.5	1596.6	1598.7	1598.9	1597.2	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	17.2	16.6	16.3	15.3	14.3	13.2	11.6	11.4	10.9	11.7	10.9
90°	29.5	28.4	25.0	21.5	18.1	14.7	11.7	9.1	6.4	3.8	1.2
92.5°	32.0	30.3	27.7	25.2	22.6	20.0	19.1	19.8	20.5	21.3	22.0
95°	38.6	36.7	33.8	30.9	28.0	25.1	29.1	39.8	50.7	61.5	72.2
97.5°	40.2	38.1	57.1	76.0	95.0	113.9	125.8	130.6	135.5	140.4	145.2
100°	41.2	39.1	80.2	121.2	162.2	203.3	221.2	215.9	210.6	205.4	200.2
102.5°	71.4	78.0	122.8	167.6	212.5	257.3	277.8	274.0	270.3	266.5	262.7
105°	212.8	259.4	283.0	306.7	330.4	354.1	364.5	361.6	358.7	355.8	352.9
107.5°	441.2	475.4	471.7	467.9	464.1	460.4	457.4	455.1	452.7	450.4	448.1
110°	525.5	534.1	531.2	528.3	525.5	522.5	520.1	517.9	515.8	513.7	511.6



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	594.0	593.8	590.9	588.0	585.1	582.3	579.8	578.0	576.1	574.2	572.3
115°	682.4	679.8	677.4	675.0	672.7	670.3	668.4	666.8	665.2	663.6	662.0
117.5°	765.2	763.2	761.9	760.7	759.5	758.4	756.8	754.8	752.8	750.9	748.9
120°	819.3	817.1	816.3	815.6	814.8	814.0	812.5	810.1	807.7	805.3	803.0
122.5°	872.7	871.2	870.1	869.2	868.2	867.2	865.7	863.7	861.8	859.8	857.9
125°	948.0	947.5	946.4	945.3	944.3	943.3	941.7	939.5	937.5	935.3	933.2
127.5°	1022.2	1021.4	1020.1	1018.8	1017.6	1016.3	1014.6	1012.5	1010.4	1008.3	1006.2
130°	1066.9	1065.9	1064.9	1063.7	1062.7	1061.7	1060.1	1058.0	1055.9	1053.8	1051.6
132.5°	1109.5	1108.5	1107.6	1106.8	1106.0	1105.2	1103.7	1101.5	1099.5	1097.3	1095.3
135°	1174.4	1173.6	1172.6	1171.6	1170.4	1169.4	1168.2	1166.6	1165.0	1163.4	1161.8
137.5°	1231.5	1230.3	1229.7	1229.1	1228.5	1228.0	1226.6	1224.6	1222.7	1220.7	1218.6
140°	1268.3	1267.2	1266.4	1265.6	1264.8	1264.0	1262.9	1261.3	1259.7	1258.1	1256.6
142.5°	1303.1	1302.3	1301.5	1300.7	1299.9	1299.1	1297.9	1296.3	1294.7	1293.2	1291.6
145°	1351.8	1351.3	1350.8	1350.2	1349.7	1349.2	1348.0	1346.2	1344.3	1342.4	1340.6
147.5°	1395.2	1394.6	1394.1	1393.6	1393.1	1392.5	1391.6	1390.4	1389.3	1388.1	1386.8
150°	1421.7	1421.2	1420.6	1420.1	1419.6	1419.0	1418.4	1417.6	1416.8	1416.0	1415.2
152.5°	1444.9	1443.9	1443.6	1443.3	1443.0	1442.6	1442.3	1441.9	1441.5	1441.2	1440.8
155°	1476.9	1475.6	1475.4	1475.1	1474.9	1474.6	1474.7	1475.3	1475.8	1476.3	1476.8
157.5°	1504.9	1503.3	1503.6	1503.9	1504.1	1504.4	1504.6	1504.6	1504.7	1504.8	1504.8
160°	1521.1	1519.5	1519.7	1520.0	1520.3	1520.5	1520.8	1521.1	1521.3	1521.5	1521.9
162.5°	1535.5	1533.7	1533.9	1534.2	1534.5	1534.7	1535.2	1535.9	1536.6	1537.2	1537.9
165°	1554.7	1552.6	1552.9	1553.2	1553.4	1553.7	1554.2	1555.0	1555.8	1556.6	1557.4
167.5°	1569.9	1567.8	1567.8	1567.8	1567.8	1567.8	1568.3	1569.4	1570.4	1571.5	1572.5
170°	1578.4	1576.3	1576.3	1576.3	1576.3	1576.3	1576.8	1577.9	1578.9	1580.0	1581.0
172.5°	1584.1	1582.0	1581.8	1581.6	1581.4	1581.1	1581.7	1582.9	1584.2	1585.5	1586.7
175°	1591.2	1589.4	1589.0	1588.8	1588.6	1588.2	1588.8	1590.1	1591.4	1592.8	1594.0
177.5°	1593.9	1592.2	1592.0	1591.7	1591.6	1591.3	1591.7	1592.8	1593.9	1594.9	1595.9
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.7	8.2	8.5	8.0	8.6	8.6	9.6	9.7	10.0	10.5	10.1
90°	3.8	6.4	9.1	11.7	14.7	18.1	21.5	25.0	28.4	29.5	30.5
92.5°	21.3	20.5	19.8	19.1	20.0	22.6	25.2	27.7	30.3	32.0	33.7
95°	61.5	50.7	39.8	29.1	25.1	28.0	30.9	33.8	36.7	38.6	40.4
97.5°	140.4	135.5	130.6	125.8	113.9	95.0	76.0	57.1	38.1	40.2	42.4
100°	205.4	210.6	215.9	221.2	203.3	162.2	121.2	80.2	39.1	41.2	43.3
102.5°	266.5	270.3	274.0	277.8	257.3	212.5	167.6	122.8	78.0	71.4	64.9
105°	355.8	358.7	361.6	364.5	354.1	330.4	306.7	283.0	259.4	212.8	166.2
107.5°	450.4	452.7	455.1	457.4	460.4	464.1	467.9	471.7	475.4	441.2	407.0
110°	513.7	515.8	517.9	520.1	522.5	525.5	528.3	531.2	534.1	525.5	516.7





TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	574.2	576.1	578.0	579.8	582.3	585.1	588.0	590.9	593.8	594.0	594.1
115°	663.6	665.2	666.8	668.4	670.3	672.7	675.0	677.4	679.8	682.4	685.1
117.5°	750.9	752.8	754.8	756.8	758.4	759.5	760.7	761.9	763.2	765.2	767.4
120°	805.3	807.7	810.1	812.5	814.0	814.8	815.6	816.3	817.1	819.3	821.4
122.5°	859.8	861.8	863.7	865.7	867.2	868.2	869.2	870.1	871.2	872.7	874.1
125°	935.3	937.5	939.5	941.7	943.3	944.3	945.3	946.4	947.5	948.0	948.5
127.5°	1008.3	1010.4	1012.5	1014.6	1016.3	1017.6	1018.8	1020.1	1021.4	1022.2	1023.0
130°	1053.8	1055.9	1058.0	1060.1	1061.7	1062.7	1063.7	1064.9	1065.9	1066.9	1067.9
132.5°	1097.3	1099.5	1101.5	1103.7	1105.2	1106.0	1106.8	1107.6	1108.5	1109.5	1110.6
135°	1163.4	1165.0	1166.6	1168.2	1169.4	1170.4	1171.6	1172.6	1173.6	1174.4	1175.2
137.5°	1220.7	1222.7	1224.6	1226.6	1228.0	1228.5	1229.1	1229.7	1230.3	1231.5	1232.8
140°	1258.1	1259.7	1261.3	1262.9	1264.0	1264.8	1265.6	1266.4	1267.2	1268.3	1269.3
142.5°	1293.2	1294.7	1296.3	1297.9	1299.1	1299.9	1300.7	1301.5	1302.3	1303.1	1303.9
145°	1342.4	1344.3	1346.2	1348.0	1349.2	1349.7	1350.2	1350.8	1351.3	1351.8	1352.3
147.5°	1388.1	1389.3	1390.4	1391.6	1392.5	1393.1	1393.6	1394.1	1394.6	1395.2	1395.7
150°	1416.0	1416.8	1417.6	1418.4	1419.0	1419.6	1420.1	1420.6	1421.2	1421.7	1422.2
152.5°	1441.2	1441.5	1441.9	1442.3	1442.6	1443.0	1443.3	1443.6	1443.9	1444.9	1445.8
155°	1476.3	1475.8	1475.3	1474.7	1474.6	1474.9	1475.1	1475.4	1475.6	1476.9	1478.3
157.5°	1504.8	1504.7	1504.6	1504.6	1504.4	1504.1	1503.9	1503.6	1503.3	1504.9	1506.5
160°	1521.5	1521.3	1521.1	1520.8	1520.5	1520.3	1520.0	1519.7	1519.5	1521.1	1522.7
162.5°	1537.2	1536.6	1535.9	1535.2	1534.7	1534.5	1534.2	1533.9	1533.7	1535.5	1537.2
165°	1556.6	1555.8	1555.0	1554.2	1553.7	1553.4	1553.2	1552.9	1552.6	1554.7	1556.8
167.5°	1571.5	1570.4	1569.4	1568.3	1567.8	1567.8	1567.8	1567.8	1567.8	1569.9	1572.0
170°	1580.0	1578.9	1577.9	1576.8	1576.3	1576.3	1576.3	1576.3	1576.3	1578.4	1580.5
172.5°	1585.5	1584.2	1582.9	1581.7	1581.1	1581.4	1581.6	1581.8	1582.0	1584.1	1586.2
175°	1592.8	1591.4	1590.1	1588.8	1588.2	1588.6	1588.8	1589.0	1589.4	1591.2	1593.0
177.5°	1594.9	1593.9	1592.8	1591.7	1591.3	1591.6	1591.7	1592.0	1592.2	1593.9	1595.5
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	10.3	10.5	10.3	10.5	10.2	11.0	10.5
90°	31.6	32.6	33.4	34.0	34.5	35.0	35.5
92.5°	35.4	37.1	38.0	38.3	38.7	39.0	39.3
95°	42.2	44.0	45.0	45.0	45.0	45.0	45.0
97.5°	44.4	46.6	47.8	48.0	48.2	48.6	48.8
100°	45.4	47.5	48.7	49.0	49.2	49.5	49.7
102.5°	58.4	51.8	48.8	49.3	49.7	50.2	50.7
105°	119.6	73.0	50.0	50.5	51.1	51.6	52.1
107.5°	372.9	338.7	304.1	269.0	233.9	198.8	163.7
110°	508.0	499.4	476.2	438.6	400.9	363.3	325.7



TEST NUMBER: P332446-927

CATALOG NUMBER: S123RDIW-S775D1535U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	594.3	594.5	590.6	582.6	574.6	566.7	558.7
115°	687.7	690.3	692.1	693.2	694.3	695.3	696.4
117.5°	769.4	771.6	772.8	772.9	773.2	773.4	773.6
120°	823.5	825.6	826.6	826.6	826.6	826.6	826.6
122.5°	875.6	877.1	877.9	878.1	878.3	878.5	878.8
125°	949.0	949.5	950.1	950.6	951.1	951.6	952.2
127.5°	1023.9	1024.7	1024.8	1024.4	1023.8	1023.3	1022.8
130°	1069.1	1070.1	1070.3	1069.8	1069.3	1068.7	1068.3
132.5°	1111.7	1112.7	1112.9	1112.1	1111.4	1110.6	1109.9
135°	1176.0	1176.8	1176.8	1176.0	1175.2	1174.4	1173.6
137.5°	1234.1	1235.3	1235.6	1235.2	1234.6	1234.1	1233.6
140°	1270.3	1271.4	1271.7	1271.1	1270.7	1270.1	1269.6
142.5°	1304.8	1305.6	1305.7	1305.0	1304.2	1303.5	1302.7
145°	1352.9	1353.4	1353.7	1353.7	1353.7	1353.7	1353.7
147.5°	1396.2	1396.8	1396.4	1395.2	1394.0	1392.7	1391.5
150°	1422.8	1423.2	1423.2	1422.4	1421.6	1420.8	1420.0
152.5°	1446.8	1447.7	1447.6	1446.4	1445.1	1443.9	1442.7
155°	1479.6	1480.9	1480.7	1479.2	1477.6	1476.0	1474.5
157.5°	1508.1	1509.7	1509.4	1507.4	1505.3	1503.2	1501.2
160°	1524.2	1525.7	1525.7	1523.8	1521.9	1520.1	1518.3
162.5°	1539.1	1540.8	1540.9	1539.3	1537.6	1536.0	1534.4
165°	1558.9	1561.1	1561.2	1559.3	1557.5	1555.6	1553.8
167.5°	1574.1	1576.2	1576.2	1574.1	1572.0	1569.9	1567.8
170°	1582.6	1584.8	1584.8	1582.6	1580.5	1578.4	1576.3
172.5°	1588.3	1590.4	1590.3	1588.0	1585.7	1583.3	1581.0
175°	1594.8	1596.7	1596.6	1594.4	1592.4	1590.2	1588.2
177.5°	1597.2	1598.9	1598.7	1596.6	1594.5	1592.4	1590.3
180°	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0	1594.0

(END OF REPORT)