

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332442

Luminaire Tested: **S123RDIW-S775D1320U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332442
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D1320U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8327.8 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37								
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	39	38	32								
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27								
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24								
4	73	63	55	50	66	57	51	46	47	42	39	37	34	31	28	26	25	21								
5	67	56	48	43	61	51	45	39	42	37	33	34	30	27	26	23	22	18								
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	23	21	19	16								
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14								
8	53	41	34	29	48	38	31	27	31	27	23	25	22	19	20	17	15	13								
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14	12								
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.3	1.4
10°-20°	375.7	4.5
20°-30°	590.3	7.1
30°-40°	615.9	7.4
40°-50°	527.1	6.3
50°-60°	401.7	4.8
60°-70°	257.5	3.1
70°-80°	123.9	1.5
80°-90°	37.6	0.5
90°-100°	62.9	0.8
100°-110°	299.9	3.6
110°-120°	720.3	8.6
120°-130°	917.3	11.0
130°-140°	980.1	11.8
140°-150°	916.5	11.0
150°-160°	739.3	8.9
160°-170°	477.1	5.7
170°-180°	164.4	2.0
0°-30°	1086.3	13.0
0°-40°	1702.2	20.4
0°-60°	2631.0	31.6
0°-90°	3049.9	36.6
90°-120°	1083.2	13.0
90°-150°	3897.1	46.8
90°-180°	5278.0	63.4
0°-180°	8327.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	39	1	39	1	39	18
95°	49	78	49	78	49	41
105°	57	383	57	383	57	129
115°	756	719	756	719	756	699
125°	1034	1013	1034	1013	1034	923
135°	1274	1261	1274	1261	1274	983
145°	1470	1456	1470	1456	1470	917
155°	1601	1603	1601	1603	1601	738
165°	1687	1691	1687	1691	1687	476
175°	1724	1731	1724	1731	1724	164
180°	1731	1731	1731	1731	1731	



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	11.9	12.6	11.7	12.0	11.9	12.1	11.9	11.7	12.3	11.6	11.3
90°	38.6	38.0	37.4	36.9	36.3	35.4	34.3	33.1	32.0	30.9	27.1
92.5°	42.7	42.3	42.0	41.7	41.3	40.2	38.4	36.6	34.7	32.9	30.1
95°	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9	41.9	39.9	36.7
97.5°	53.0	52.7	52.4	52.1	51.8	50.5	48.3	46.0	43.7	41.4	38.0
100°	54.0	53.7	53.4	53.1	52.9	51.6	49.3	47.0	44.7	42.4	39.0
102.5°	55.0	54.5	54.0	53.5	53.0	52.3	50.4	48.1	45.8	43.5	40.0
105°	56.6	56.0	55.4	54.9	54.3	53.6	51.7	49.4	47.1	44.8	41.5
107.5°	177.7	215.8	253.9	292.1	330.2	367.8	404.9	442.0	479.0	516.1	553.2
110°	353.6	394.5	435.3	476.2	517.0	557.8	598.7	639.6	680.5	721.4	762.3



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	606.7	615.3	623.9	632.5	641.2	645.4	645.2	645.1	644.9	644.7	641.6
115°	756.1	754.9	753.8	752.6	751.5	749.5	746.6	743.8	740.9	738.1	735.5
117.5°	839.9	839.7	839.4	839.2	839.0	837.7	835.4	833.2	830.9	828.6	827.3
120°	897.5	897.5	897.5	897.5	897.5	896.4	894.1	891.8	889.5	887.2	886.4
122.5°	954.1	953.9	953.6	953.4	953.2	952.3	950.7	949.1	947.5	945.9	944.8
125°	1033.8	1033.2	1032.7	1032.1	1031.5	1030.9	1030.4	1029.8	1029.2	1028.7	1027.5
127.5°	1110.4	1111.0	1111.6	1112.2	1112.7	1112.6	1111.6	1110.7	1109.8	1108.9	1107.5
130°	1159.8	1160.4	1161.0	1161.5	1162.1	1161.8	1160.7	1159.5	1158.4	1157.2	1156.1
132.5°	1205.1	1205.9	1206.7	1207.5	1208.3	1208.1	1207.0	1205.8	1204.7	1203.5	1202.6
135°	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3	1273.1
137.5°	1339.3	1339.9	1340.5	1341.0	1341.6	1341.2	1339.8	1338.5	1337.1	1335.7	1335.1
140°	1378.4	1379.0	1379.5	1380.1	1380.7	1380.4	1379.3	1378.1	1377.0	1375.8	1375.0
142.5°	1414.4	1415.2	1416.0	1416.8	1417.6	1417.6	1416.6	1415.7	1414.8	1413.9	1413.0
145°	1469.7	1469.7	1469.7	1469.7	1469.7	1469.4	1468.8	1468.3	1467.7	1467.1	1466.6
147.5°	1510.8	1512.2	1513.5	1514.8	1516.1	1516.5	1515.9	1515.3	1514.8	1514.2	1513.6
150°	1541.7	1542.6	1543.4	1544.3	1545.1	1545.3	1544.7	1544.1	1543.6	1543.0	1542.4
152.5°	1566.4	1567.7	1569.0	1570.3	1571.7	1571.8	1570.8	1569.7	1568.7	1567.7	1567.3
155°	1600.9	1602.6	1604.3	1606.0	1607.7	1607.9	1606.4	1605.0	1603.6	1602.1	1601.9
157.5°	1629.9	1632.1	1634.4	1636.6	1638.8	1639.1	1637.4	1635.7	1633.9	1632.2	1632.5
160°	1648.4	1650.4	1652.4	1654.4	1656.4	1656.6	1654.9	1653.1	1651.4	1649.7	1650.0
162.5°	1665.9	1667.7	1669.5	1671.2	1673.0	1672.9	1671.0	1669.0	1667.1	1665.1	1665.4
165°	1687.0	1689.0	1691.0	1693.0	1695.0	1694.9	1692.6	1690.3	1688.0	1685.7	1686.0
167.5°	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2	1702.2
170°	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4	1711.4
172.5°	1716.6	1719.1	1721.6	1724.1	1726.6	1726.8	1724.5	1722.2	1719.9	1717.6	1717.4
175°	1724.3	1726.6	1728.9	1731.2	1733.4	1733.6	1731.6	1729.6	1727.6	1725.6	1725.3
177.5°	1726.6	1728.9	1731.2	1733.5	1735.8	1736.0	1734.2	1732.3	1730.5	1728.7	1728.4
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	11.4	10.2	10.3	9.7	10.3	10.2	12.1	13.7	14.7	13.5	14.1
90°	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3	4.1	7.0	9.9
92.5°	27.3	24.5	21.7	20.7	21.5	22.3	23.1	23.9	23.1	22.3	21.5
95°	33.6	30.4	27.3	31.6	43.3	55.0	66.7	78.4	66.7	55.0	43.3
97.5°	82.6	103.1	123.7	136.6	141.9	147.1	152.4	157.6	152.4	147.1	141.9
100°	131.6	176.2	220.7	240.2	234.4	228.7	223.0	217.3	223.0	228.7	234.4
102.5°	182.0	230.7	279.4	301.7	297.5	293.4	289.3	285.2	289.3	293.4	297.5
105°	333.0	358.7	384.5	395.7	392.6	389.5	386.3	383.2	386.3	389.5	392.6
107.5°	508.0	504.0	499.9	496.6	494.1	491.6	489.1	486.6	489.1	491.6	494.1
110°	573.6	570.5	567.3	564.6	562.3	560.0	557.8	555.5	557.8	560.0	562.3



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	638.4	635.3	632.1	629.5	627.5	625.4	623.4	621.3	623.4	625.4	627.5
115°	732.9	730.3	727.8	725.6	723.9	722.2	720.5	718.8	720.5	722.2	723.9
117.5°	826.0	824.6	823.3	821.6	819.5	817.4	815.3	813.2	815.3	817.4	819.5
120°	885.5	884.6	883.8	882.1	879.5	876.9	874.4	871.8	874.4	876.9	879.5
122.5°	943.7	942.6	941.5	939.9	937.8	935.7	933.6	931.5	933.6	935.7	937.8
125°	1026.4	1025.2	1024.1	1022.4	1020.1	1017.8	1015.5	1013.2	1015.5	1017.8	1020.1
127.5°	1106.2	1104.8	1103.4	1101.6	1099.3	1097.0	1094.7	1092.4	1094.7	1097.0	1099.3
130°	1155.0	1153.8	1152.7	1151.0	1148.7	1146.4	1144.1	1141.8	1144.1	1146.4	1148.7
132.5°	1201.7	1200.8	1199.9	1198.3	1196.0	1193.7	1191.4	1189.1	1191.4	1193.7	1196.0
135°	1272.0	1270.8	1269.7	1268.3	1266.5	1264.8	1263.1	1261.4	1263.1	1264.8	1266.5
137.5°	1334.5	1333.8	1333.2	1331.8	1329.6	1327.5	1325.3	1323.1	1325.3	1327.5	1329.6
140°	1374.1	1373.3	1372.4	1371.1	1369.4	1367.7	1366.0	1364.3	1366.0	1367.7	1369.4
142.5°	1412.2	1411.3	1410.5	1409.2	1407.5	1405.8	1404.0	1402.3	1404.0	1405.8	1407.5
145°	1466.0	1465.4	1464.8	1463.6	1461.6	1459.6	1457.6	1455.6	1457.6	1459.6	1461.6
147.5°	1513.0	1512.5	1511.9	1511.0	1509.6	1508.3	1507.0	1505.7	1507.0	1508.3	1509.6
150°	1541.8	1541.3	1540.7	1540.0	1539.1	1538.3	1537.4	1536.6	1537.4	1538.3	1539.1
152.5°	1567.0	1566.7	1566.3	1565.9	1565.5	1565.1	1564.7	1564.3	1564.7	1565.1	1565.5
155°	1601.6	1601.3	1601.0	1601.1	1601.7	1602.3	1602.9	1603.4	1602.9	1602.3	1601.7
157.5°	1632.8	1633.1	1633.4	1633.5	1633.6	1633.7	1633.7	1633.8	1633.7	1633.7	1633.6
160°	1650.3	1650.6	1650.9	1651.1	1651.4	1651.7	1652.0	1652.3	1652.0	1651.7	1651.4
162.5°	1665.7	1666.0	1666.3	1666.8	1667.5	1668.3	1669.0	1669.8	1669.0	1668.3	1667.5
165°	1686.3	1686.6	1686.9	1687.4	1688.3	1689.1	1690.0	1690.9	1690.0	1689.1	1688.3
167.5°	1702.2	1702.2	1702.2	1702.7	1703.9	1705.0	1706.2	1707.3	1706.2	1705.0	1703.9
170°	1711.4	1711.4	1711.4	1712.0	1713.2	1714.3	1715.4	1716.6	1715.4	1714.3	1713.2
172.5°	1717.2	1716.9	1716.7	1717.3	1718.6	1720.0	1721.4	1722.8	1721.4	1720.0	1718.6
175°	1725.0	1724.7	1724.4	1725.0	1726.4	1727.9	1729.3	1730.7	1729.3	1727.9	1726.4
177.5°	1728.2	1728.0	1727.8	1728.2	1729.4	1730.5	1731.6	1732.8	1731.6	1730.5	1729.4
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	14.3	16.2	17.3	18.5	19.7	20.0	20.6	20.9	21.5	21.7	21.9
90°	12.7	16.0	19.7	23.4	27.1	30.9	32.0	33.1	34.3	35.4	36.3
92.5°	20.7	21.7	24.5	27.3	30.1	32.9	34.7	36.6	38.4	40.2	41.3
95°	31.6	27.3	30.4	33.6	36.7	39.9	41.9	43.9	45.9	47.9	48.9
97.5°	136.6	123.7	103.1	82.6	62.0	41.4	43.7	46.0	48.3	50.5	51.8
100°	240.2	220.7	176.2	131.6	87.0	42.4	44.7	47.0	49.3	51.6	52.9
102.5°	301.7	279.4	230.7	182.0	133.3	84.6	77.5	70.4	63.3	56.3	53.0
105°	395.7	384.5	358.7	333.0	307.3	281.6	231.0	180.4	129.9	79.3	54.3
107.5°	496.6	499.9	504.0	508.0	512.1	516.1	479.0	442.0	404.9	367.8	330.2
110°	564.6	567.3	570.5	573.6	576.8	579.9	570.5	561.0	551.6	542.2	517.0



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	629.5	632.1	635.3	638.4	641.6	644.7	644.9	645.1	645.2	645.4	641.2
115°	725.6	727.8	730.3	732.9	735.5	738.1	740.9	743.8	746.6	749.5	751.5
117.5°	821.6	823.3	824.6	826.0	827.3	828.6	830.9	833.2	835.4	837.7	839.0
120°	882.1	883.8	884.6	885.5	886.4	887.2	889.5	891.8	894.1	896.4	897.5
122.5°	939.9	941.5	942.6	943.7	944.8	945.9	947.5	949.1	950.7	952.3	953.2
125°	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2	1029.8	1030.4	1030.9	1031.5
127.5°	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8	1110.7	1111.6	1112.6	1112.7
130°	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4	1159.5	1160.7	1161.8	1162.1
132.5°	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7	1205.8	1207.0	1208.1	1208.3
135°	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7
137.5°	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1	1338.5	1339.8	1341.2	1341.6
140°	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0	1378.1	1379.3	1380.4	1380.7
142.5°	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8	1415.7	1416.6	1417.6	1417.6
145°	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7	1468.3	1468.8	1469.4	1469.7
147.5°	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.3	1515.9	1516.5	1516.1
150°	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6	1544.1	1544.7	1545.3	1545.1
152.5°	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7	1569.7	1570.8	1571.8	1571.7
155°	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6	1605.0	1606.4	1607.9	1607.7
157.5°	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9	1635.7	1637.4	1639.1	1638.8
160°	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4	1653.1	1654.9	1656.6	1656.4
162.5°	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1	1669.0	1671.0	1672.9	1673.0
165°	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0	1690.3	1692.6	1694.9	1695.0
167.5°	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3
170°	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6
172.5°	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9	1722.2	1724.5	1726.8	1726.6
175°	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6	1729.6	1731.6	1733.6	1733.4
177.5°	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5	1732.3	1734.2	1736.0	1735.8
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	22.9	22.1	22.3	22.8	22.3	22.1	22.9	21.9	21.7	21.5	20.9
90°	36.9	37.4	38.0	38.6	38.0	37.4	36.9	36.3	35.4	34.3	33.1
92.5°	41.7	42.0	42.3	42.7	42.3	42.0	41.7	41.3	40.2	38.4	36.6
95°	48.9	48.9	48.9	48.9	48.9	48.9	48.9	48.9	47.9	45.9	43.9
97.5°	52.1	52.4	52.7	53.0	52.7	52.4	52.1	51.8	50.5	48.3	46.0
100°	53.1	53.4	53.7	54.0	53.7	53.4	53.1	52.9	51.6	49.3	47.0
102.5°	53.5	54.0	54.5	55.0	54.5	54.0	53.5	53.0	56.3	63.3	70.4
105°	54.9	55.4	56.0	56.6	56.0	55.4	54.9	54.3	79.3	129.9	180.4
107.5°	292.1	253.9	215.8	177.7	215.8	253.9	292.1	330.2	367.8	404.9	442.0
110°	476.2	435.3	394.5	353.6	394.5	435.3	476.2	517.0	542.2	551.6	561.0



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	632.5	623.9	615.3	606.7	615.3	623.9	632.5	641.2	645.4	645.2	645.1
115°	752.6	753.8	754.9	756.1	754.9	753.8	752.6	751.5	749.5	746.6	743.8
117.5°	839.2	839.4	839.7	839.9	839.7	839.4	839.2	839.0	837.7	835.4	833.2
120°	897.5	897.5	897.5	897.5	897.5	897.5	897.5	897.5	896.4	894.1	891.8
122.5°	953.4	953.6	953.9	954.1	953.9	953.6	953.4	953.2	952.3	950.7	949.1
125°	1032.1	1032.7	1033.2	1033.8	1033.2	1032.7	1032.1	1031.5	1030.9	1030.4	1029.8
127.5°	1112.2	1111.6	1111.0	1110.4	1111.0	1111.6	1112.2	1112.7	1112.6	1111.6	1110.7
130°	1161.5	1161.0	1160.4	1159.8	1160.4	1161.0	1161.5	1162.1	1161.8	1160.7	1159.5
132.5°	1207.5	1206.7	1205.9	1205.1	1205.9	1206.7	1207.5	1208.3	1208.1	1207.0	1205.8
135°	1276.8	1276.0	1275.1	1274.3	1275.1	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0
137.5°	1341.0	1340.5	1339.9	1339.3	1339.9	1340.5	1341.0	1341.6	1341.2	1339.8	1338.5
140°	1380.1	1379.5	1379.0	1378.4	1379.0	1379.5	1380.1	1380.7	1380.4	1379.3	1378.1
142.5°	1416.8	1416.0	1415.2	1414.4	1415.2	1416.0	1416.8	1417.6	1417.6	1416.6	1415.7
145°	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.7	1469.4	1468.8	1468.3
147.5°	1514.8	1513.5	1512.2	1510.8	1512.2	1513.5	1514.8	1516.1	1516.5	1515.9	1515.3
150°	1544.3	1543.4	1542.6	1541.7	1542.6	1543.4	1544.3	1545.1	1545.3	1544.7	1544.1
152.5°	1570.3	1569.0	1567.7	1566.4	1567.7	1569.0	1570.3	1571.7	1571.8	1570.8	1569.7
155°	1606.0	1604.3	1602.6	1600.9	1602.6	1604.3	1606.0	1607.7	1607.9	1606.4	1605.0
157.5°	1636.6	1634.4	1632.1	1629.9	1632.1	1634.4	1636.6	1638.8	1639.1	1637.4	1635.7
160°	1654.4	1652.4	1650.4	1648.4	1650.4	1652.4	1654.4	1656.4	1656.6	1654.9	1653.1
162.5°	1671.2	1669.5	1667.7	1665.9	1667.7	1669.5	1671.2	1673.0	1672.9	1671.0	1669.0
165°	1693.0	1691.0	1689.0	1687.0	1689.0	1691.0	1693.0	1695.0	1694.9	1692.6	1690.3
167.5°	1709.0	1706.8	1704.5	1702.2	1704.5	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8
170°	1718.3	1716.0	1713.7	1711.4	1713.7	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0
172.5°	1724.1	1721.6	1719.1	1716.6	1719.1	1721.6	1724.1	1726.6	1726.8	1724.5	1722.2
175°	1731.2	1728.9	1726.6	1724.3	1726.6	1728.9	1731.2	1733.4	1733.6	1731.6	1729.6
177.5°	1733.5	1731.2	1728.9	1726.6	1728.9	1731.2	1733.5	1735.8	1736.0	1734.2	1732.3
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	20.6	20.0	19.7	18.5	17.3	16.2	14.3	14.1	13.5	14.7	13.7
90°	32.0	30.9	27.1	23.4	19.7	16.0	12.7	9.9	7.0	4.1	1.3
92.5°	34.7	32.9	30.1	27.3	24.5	21.7	20.7	21.5	22.3	23.1	23.9
95°	41.9	39.9	36.7	33.6	30.4	27.3	31.6	43.3	55.0	66.7	78.4
97.5°	43.7	41.4	62.0	82.6	103.1	123.7	136.6	141.9	147.1	152.4	157.6
100°	44.7	42.4	87.0	131.6	176.2	220.7	240.2	234.4	228.7	223.0	217.3
102.5°	77.5	84.6	133.3	182.0	230.7	279.4	301.7	297.5	293.4	289.3	285.2
105°	231.0	281.6	307.3	333.0	358.7	384.5	395.7	392.6	389.5	386.3	383.2
107.5°	479.0	516.1	512.1	508.0	504.0	499.9	496.6	494.1	491.6	489.1	486.6
110°	570.5	579.9	576.8	573.6	570.5	567.3	564.6	562.3	560.0	557.8	555.5



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	644.9	644.7	641.6	638.4	635.3	632.1	629.5	627.5	625.4	623.4	621.3
115°	740.9	738.1	735.5	732.9	730.3	727.8	725.6	723.9	722.2	720.5	718.8
117.5°	830.9	828.6	827.3	826.0	824.6	823.3	821.6	819.5	817.4	815.3	813.2
120°	889.5	887.2	886.4	885.5	884.6	883.8	882.1	879.5	876.9	874.4	871.8
122.5°	947.5	945.9	944.8	943.7	942.6	941.5	939.9	937.8	935.7	933.6	931.5
125°	1029.2	1028.7	1027.5	1026.4	1025.2	1024.1	1022.4	1020.1	1017.8	1015.5	1013.2
127.5°	1109.8	1108.9	1107.5	1106.2	1104.8	1103.4	1101.6	1099.3	1097.0	1094.7	1092.4
130°	1158.4	1157.2	1156.1	1155.0	1153.8	1152.7	1151.0	1148.7	1146.4	1144.1	1141.8
132.5°	1204.7	1203.5	1202.6	1201.7	1200.8	1199.9	1198.3	1196.0	1193.7	1191.4	1189.1
135°	1275.1	1274.3	1273.1	1272.0	1270.8	1269.7	1268.3	1266.5	1264.8	1263.1	1261.4
137.5°	1337.1	1335.7	1335.1	1334.5	1333.8	1333.2	1331.8	1329.6	1327.5	1325.3	1323.1
140°	1377.0	1375.8	1375.0	1374.1	1373.3	1372.4	1371.1	1369.4	1367.7	1366.0	1364.3
142.5°	1414.8	1413.9	1413.0	1412.2	1411.3	1410.5	1409.2	1407.5	1405.8	1404.0	1402.3
145°	1467.7	1467.1	1466.6	1466.0	1465.4	1464.8	1463.6	1461.6	1459.6	1457.6	1455.6
147.5°	1514.8	1514.2	1513.6	1513.0	1512.5	1511.9	1511.0	1509.6	1508.3	1507.0	1505.7
150°	1543.6	1543.0	1542.4	1541.8	1541.3	1540.7	1540.0	1539.1	1538.3	1537.4	1536.6
152.5°	1568.7	1567.7	1567.3	1567.0	1566.7	1566.3	1565.9	1565.5	1565.1	1564.7	1564.3
155°	1603.6	1602.1	1601.9	1601.6	1601.3	1601.0	1601.1	1601.7	1602.3	1602.9	1603.4
157.5°	1633.9	1632.2	1632.5	1632.8	1633.1	1633.4	1633.5	1633.6	1633.7	1633.7	1633.8
160°	1651.4	1649.7	1650.0	1650.3	1650.6	1650.9	1651.1	1651.4	1651.7	1652.0	1652.3
162.5°	1667.1	1665.1	1665.4	1665.7	1666.0	1666.3	1666.8	1667.5	1668.3	1669.0	1669.8
165°	1688.0	1685.7	1686.0	1686.3	1686.6	1686.9	1687.4	1688.3	1689.1	1690.0	1690.9
167.5°	1704.5	1702.2	1702.2	1702.2	1702.2	1702.2	1702.7	1703.9	1705.0	1706.2	1707.3
170°	1713.7	1711.4	1711.4	1711.4	1711.4	1711.4	1712.0	1713.2	1714.3	1715.4	1716.6
172.5°	1719.9	1717.6	1717.4	1717.2	1716.9	1716.7	1717.3	1718.6	1720.0	1721.4	1722.8
175°	1727.6	1725.6	1725.3	1725.0	1724.7	1724.4	1725.0	1726.4	1727.9	1729.3	1730.7
177.5°	1730.5	1728.7	1728.4	1728.2	1728.0	1727.8	1728.2	1729.4	1730.5	1731.6	1732.8
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	12.1	10.2	10.3	9.7	10.3	10.2	11.4	11.3	11.6	12.3	11.7
90°	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.1	30.9	32.0	33.1
92.5°	23.1	22.3	21.5	20.7	21.7	24.5	27.3	30.1	32.9	34.7	36.6
95°	66.7	55.0	43.3	31.6	27.3	30.4	33.6	36.7	39.9	41.9	43.9
97.5°	152.4	147.1	141.9	136.6	123.7	103.1	82.6	62.0	41.4	43.7	46.0
100°	223.0	228.7	234.4	240.2	220.7	176.2	131.6	87.0	42.4	44.7	47.0
102.5°	289.3	293.4	297.5	301.7	279.4	230.7	182.0	133.3	84.6	77.5	70.4
105°	386.3	389.5	392.6	395.7	384.5	358.7	333.0	307.3	281.6	231.0	180.4
107.5°	489.1	491.6	494.1	496.6	499.9	504.0	508.0	512.1	516.1	479.0	442.0
110°	557.8	560.0	562.3	564.6	567.3	570.5	573.6	576.8	579.9	570.5	561.0



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	623.4	625.4	627.5	629.5	632.1	635.3	638.4	641.6	644.7	644.9	645.1
115°	720.5	722.2	723.9	725.6	727.8	730.3	732.9	735.5	738.1	740.9	743.8
117.5°	815.3	817.4	819.5	821.6	823.3	824.6	826.0	827.3	828.6	830.9	833.2
120°	874.4	876.9	879.5	882.1	883.8	884.6	885.5	886.4	887.2	889.5	891.8
122.5°	933.6	935.7	937.8	939.9	941.5	942.6	943.7	944.8	945.9	947.5	949.1
125°	1015.5	1017.8	1020.1	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2	1029.8
127.5°	1094.7	1097.0	1099.3	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8	1110.7
130°	1144.1	1146.4	1148.7	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4	1159.5
132.5°	1191.4	1193.7	1196.0	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7	1205.8
135°	1263.1	1264.8	1266.5	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1	1276.0
137.5°	1325.3	1327.5	1329.6	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1	1338.5
140°	1366.0	1367.7	1369.4	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0	1378.1
142.5°	1404.0	1405.8	1407.5	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8	1415.7
145°	1457.6	1459.6	1461.6	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7	1468.3
147.5°	1507.0	1508.3	1509.6	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.3
150°	1537.4	1538.3	1539.1	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6	1544.1
152.5°	1564.7	1565.1	1565.5	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7	1569.7
155°	1602.9	1602.3	1601.7	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6	1605.0
157.5°	1633.7	1633.7	1633.6	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9	1635.7
160°	1652.0	1651.7	1651.4	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4	1653.1
162.5°	1669.0	1668.3	1667.5	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1	1669.0
165°	1690.0	1689.1	1688.3	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0	1690.3
167.5°	1706.2	1705.0	1703.9	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5	1706.8
170°	1715.4	1714.3	1713.2	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7	1716.0
172.5°	1721.4	1720.0	1718.6	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9	1722.2
175°	1729.3	1727.9	1726.4	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6	1729.6
177.5°	1731.6	1730.5	1729.4	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5	1732.3
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	11.9	12.1	11.9	12.0	11.7	12.6	11.9
90°	34.3	35.4	36.3	36.9	37.4	38.0	38.6
92.5°	38.4	40.2	41.3	41.7	42.0	42.3	42.7
95°	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	48.3	50.5	51.8	52.1	52.4	52.7	53.0
100°	49.3	51.6	52.9	53.1	53.4	53.7	54.0
102.5°	63.3	56.3	53.0	53.5	54.0	54.5	55.0
105°	129.9	79.3	54.3	54.9	55.4	56.0	56.6
107.5°	404.9	367.8	330.2	292.1	253.9	215.8	177.7
110°	551.6	542.2	517.0	476.2	435.3	394.5	353.6



TEST NUMBER: P332442

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	645.2	645.4	641.2	632.5	623.9	615.3	606.7
115°	746.6	749.5	751.5	752.6	753.8	754.9	756.1
117.5°	835.4	837.7	839.0	839.2	839.4	839.7	839.9
120°	894.1	896.4	897.5	897.5	897.5	897.5	897.5
122.5°	950.7	952.3	953.2	953.4	953.6	953.9	954.1
125°	1030.4	1030.9	1031.5	1032.1	1032.7	1033.2	1033.8
127.5°	1111.6	1112.6	1112.7	1112.2	1111.6	1111.0	1110.4
130°	1160.7	1161.8	1162.1	1161.5	1161.0	1160.4	1159.8
132.5°	1207.0	1208.1	1208.3	1207.5	1206.7	1205.9	1205.1
135°	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3
137.5°	1339.8	1341.2	1341.6	1341.0	1340.5	1339.9	1339.3
140°	1379.3	1380.4	1380.7	1380.1	1379.5	1379.0	1378.4
142.5°	1416.6	1417.6	1417.6	1416.8	1416.0	1415.2	1414.4
145°	1468.8	1469.4	1469.7	1469.7	1469.7	1469.7	1469.7
147.5°	1515.9	1516.5	1516.1	1514.8	1513.5	1512.2	1510.8
150°	1544.7	1545.3	1545.1	1544.3	1543.4	1542.6	1541.7
152.5°	1570.8	1571.8	1571.7	1570.3	1569.0	1567.7	1566.4
155°	1606.4	1607.9	1607.7	1606.0	1604.3	1602.6	1600.9
157.5°	1637.4	1639.1	1638.8	1636.6	1634.4	1632.1	1629.9
160°	1654.9	1656.6	1656.4	1654.4	1652.4	1650.4	1648.4
162.5°	1671.0	1672.9	1673.0	1671.2	1669.5	1667.7	1665.9
165°	1692.6	1694.9	1695.0	1693.0	1691.0	1689.0	1687.0
167.5°	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2
170°	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4
172.5°	1724.5	1726.8	1726.6	1724.1	1721.6	1719.1	1716.6
175°	1731.6	1733.6	1733.4	1731.2	1728.9	1726.6	1724.3
177.5°	1734.2	1736.0	1735.8	1733.5	1731.2	1728.9	1726.6
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7

(END OF REPORT)