

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332432-927

Luminaire Tested: **S123RDIW-S775D460U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332432-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D460U927-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3772.7 lumens  
Efficiency: N/A  
Efficacy: 100.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	66	66	66
1	101	96	93	89	94	90	87	84	79	77	75	69	67	65	59	58	57
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	53	51	49
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42
4	77	67	59	53	72	63	56	50	55	50	45	49	44	41	42	39	36
5	71	60	51	45	66	56	49	43	50	44	39	44	39	36	38	35	32
6	66	54	45	40	61	51	43	38	45	39	35	40	35	31	35	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	44	36	31	53	42	35	30	37	32	27	33	29	25	29	26	23
9	53	41	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21
10	49	37	30	25	46	35	29	24	32	26	22	28	24	21	25	22	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	2.5
10°-20°	267.2	7.1
20°-30°	384.8	10.2
30°-40°	433.4	11.5
40°-50°	414.6	11.0
50°-60°	339.6	9.0
60°-70°	229.1	6.1
70°-80°	115.3	3.1
80°-90°	31.8	0.8
90°-100°	17.4	0.5
100°-110°	83.0	2.2
110°-120°	199.4	5.3
120°-130°	253.9	6.7
130°-140°	271.3	7.2
140°-150°	253.7	6.7
150°-160°	204.6	5.4
160°-170°	132.1	3.5
170°-180°	45.5	1.2
0°-30°	748.0	19.8
0°-40°	1181.5	31.3
0°-60°	1935.6	51.3
0°-90°	2311.8	61.3
90°-120°	299.8	7.9
90°-150°	1078.7	28.6
90°-180°	1461.0	38.7
0°-180°	3772.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	0	4	9	10	11	3
95°	22	8	11	13	14	27
105°	106	108	78	18	16	112
115°	199	201	204	208	209	196
125°	280	283	285	285	286	250
135°	349	351	353	354	353	269
145°	403	405	406	407	407	252
155°	444	443	444	445	443	204
165°	468	467	467	469	467	132
175°	479	477	478	480	477	46
180°	479	479	479	479	479	



TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.0	14.5	13.1	11.6	10.1	9.5	9.7	9.9	10.1	10.3	10.2
90°	0.3	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9
92.5°	6.7	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6
95°	21.7	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6
97.5°	43.6	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1
100°	60.1	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4
102.5°	78.9	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5
105°	106.1	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9
107.5°	134.7	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6
110°	153.8	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9



TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.0	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5
115°	198.9	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1
117.5°	225.1	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0
120°	241.3	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2
122.5°	257.9	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2
125°	280.4	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9
127.5°	302.4	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2
130°	316.1	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6
132.5°	329.2	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4
135°	349.1	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9
137.5°	366.2	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1
140°	377.6	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1
142.5°	388.2	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6
145°	402.9	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2
147.5°	416.8	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3
150°	425.3	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2
152.5°	433.0	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2
155°	443.8	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9
157.5°	452.3	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3
160°	457.3	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1
162.5°	462.2	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4
165°	468.0	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2
167.5°	472.6	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8
170°	475.2	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4
172.5°	476.8	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0
175°	479.0	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2
177.5°	479.6	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	10.1	10.1	10.0	9.9	9.7	9.7	9.6	9.4
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.1	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.1	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	12.8	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	19.5	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	49.9	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	122.3	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	155.3	152.7	150.0	143.1	131.8	120.5	109.2	97.9





TEST NUMBER: P332432-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.6	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	205.9	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	230.6	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	246.8	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	262.7	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.0	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.4	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	320.9	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	333.7	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.5	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.4	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	391.9	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.4	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.5	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.4	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.5	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.3	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	452.7	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	457.6	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.0	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	467.9	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	476.7	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	478.7	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	479.5	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)