

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332433-927

Luminaire Tested: **S123RDIW-S775D460U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332433-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D460U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3578.0 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	90	95	92	88	85	81	78	76	71	69	68	62	61	60	55
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	80	71	65	60	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	50	44	51	45	40	45	41	37	40	36	33	31
6	66	54	46	40	62	51	44	39	46	40	36	41	36	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	33	29	26	24
8	57	45	37	32	54	43	35	30	38	32	28	34	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	29	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	2.7
10°-20°	267.2	7.5
20°-30°	384.8	10.8
30°-40°	433.4	12.1
40°-50°	414.6	11.6
50°-60°	339.6	9.5
60°-70°	229.1	6.4
70°-80°	115.3	3.2
80°-90°	31.8	0.9
90°-100°	29.8	0.8
100°-110°	89.1	2.5
110°-120°	151.6	4.2
120°-130°	199.4	5.6
130°-140°	224.1	6.3
140°-150°	220.3	6.2
150°-160°	185.4	5.2
160°-170°	123.4	3.4
170°-180°	43.2	1.2
0°-30°	748.0	20.9
0°-40°	1181.5	33.0
0°-60°	1935.6	54.1
0°-90°	2311.8	64.6
90°-120°	270.4	7.6
90°-150°	914.1	25.5
90°-180°	1266.0	35.4
0°-180°	3578.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	0	4	9	10	11	3
95°	21	24	26	28	28	24
105°	81	82	85	85	86	87
115°	153	154	153	153	153	151
125°	223	224	224	222	221	199
135°	290	292	292	290	289	223
145°	352	352	353	353	352	219
155°	402	402	403	404	402	185
165°	438	437	437	439	437	124
175°	456	455	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.0	14.5	13.1	11.6	10.1	9.5	9.7	9.9	10.1	10.4	10.3
90°	0.4	1.2	2.0	2.8	3.6	4.4	5.5	6.6	7.6	8.6	9.0
92.5°	8.7	9.3	9.7	10.3	10.9	11.4	12.0	12.6	13.2	13.8	14.0
95°	21.2	21.7	22.3	22.9	23.4	24.0	24.6	25.3	25.9	26.5	26.9
97.5°	37.6	38.0	38.4	38.9	39.3	39.7	40.2	40.6	41.1	41.6	41.9
100°	48.8	49.3	49.7	50.2	50.7	51.2	51.6	52.0	52.4	52.8	53.0
102.5°	61.7	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	65.7
105°	80.8	81.0	81.1	81.3	81.4	81.8	82.5	83.3	84.0	84.7	84.7
107.5°	102.9	103.0	103.1	103.1	103.3	103.5	103.8	104.0	104.3	104.6	104.9
110°	116.7	116.8	117.0	117.2	117.3	117.5	117.6	117.8	118.0	118.1	118.4



TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.0	131.1	131.3	131.3	131.4	131.5	131.5	131.6	131.6	131.6	132.0
115°	152.6	152.8	153.0	153.3	153.5	153.6	153.4	153.3	153.1	153.0	153.0
117.5°	174.3	174.4	174.6	174.8	174.9	174.8	174.7	174.4	174.3	174.0	174.0
120°	187.7	188.2	188.7	189.2	189.6	189.7	189.3	188.9	188.5	188.1	188.1
122.5°	201.8	202.2	202.6	202.9	203.2	203.3	203.1	202.9	202.7	202.5	202.2
125°	223.3	223.6	223.8	224.0	224.3	224.3	224.1	223.9	223.8	223.6	223.3
127.5°	243.1	243.6	244.2	244.6	245.2	245.3	245.2	244.9	244.8	244.6	244.2
130°	256.4	257.0	257.6	258.3	258.9	259.0	258.8	258.6	258.3	258.1	257.8
132.5°	269.5	270.1	270.8	271.5	272.1	272.4	272.1	272.0	271.8	271.6	271.2
135°	289.7	290.2	290.7	291.1	291.6	291.8	291.8	291.7	291.6	291.5	291.2
137.5°	308.4	308.8	309.2	309.6	310.0	310.3	310.5	310.7	310.9	311.1	310.8
140°	321.3	321.7	322.1	322.5	322.9	323.1	323.2	323.3	323.4	323.4	323.4
142.5°	333.1	333.5	333.9	334.3	334.7	334.9	335.1	335.3	335.4	335.5	335.4
145°	351.5	351.6	351.8	352.0	352.1	352.3	352.5	352.8	353.0	353.2	353.2
147.5°	367.6	367.8	368.1	368.4	368.7	368.9	369.2	369.4	369.6	369.9	369.9
150°	378.7	378.9	379.1	379.2	379.4	379.5	379.7	379.9	380.0	380.2	380.2
152.5°	387.9	388.2	388.4	388.6	388.8	389.0	389.0	389.2	389.3	389.4	389.5
155°	402.4	402.4	402.4	402.4	402.4	402.5	402.6	402.7	402.7	402.8	403.1
157.5°	414.8	414.7	414.6	414.5	414.4	414.4	414.5	414.5	414.5	414.6	414.9
160°	422.6	422.4	422.2	422.1	421.9	421.8	421.8	421.8	421.8	421.8	422.2
162.5°	429.4	429.2	429.0	428.7	428.6	428.5	428.5	428.6	428.6	428.7	429.1
165°	438.3	438.1	437.8	437.6	437.4	437.3	437.3	437.3	437.3	437.3	437.8
167.5°	445.4	445.1	444.8	444.5	444.2	444.0	444.1	444.2	444.3	444.3	444.8
170°	449.5	449.2	448.9	448.5	448.2	448.1	448.1	448.1	448.1	448.1	448.6
172.5°	452.7	452.3	452.0	451.7	451.3	451.1	451.1	451.1	451.1	451.1	451.7
175°	455.9	455.6	455.3	455.0	454.6	454.5	454.5	454.5	454.5	454.5	455.0
177.5°	457.3	457.0	456.8	456.5	456.3	456.1	456.1	456.1	456.1	456.1	456.5
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0



TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	10.2	10.1	10.0	9.9	9.8	9.7	9.6	9.4
90°	9.3	9.6	9.9	10.1	10.3	10.5	10.6	10.8
92.5°	14.3	14.6	14.8	14.9	14.8	14.7	14.6	14.5
95°	27.2	27.5	27.8	28.0	28.0	28.0	28.0	28.0
97.5°	42.3	42.7	43.0	43.2	43.2	43.2	43.1	43.1
100°	53.2	53.5	53.7	53.9	54.1	54.3	54.4	54.6
102.5°	65.9	66.1	66.4	66.5	66.5	66.4	66.4	66.3
105°	84.7	84.7	84.7	84.8	85.0	85.2	85.3	85.5
107.5°	105.1	105.4	105.6	105.7	105.6	105.5	105.4	105.4
110°	118.7	119.1	119.4	119.5	119.3	119.1	119.0	118.8





TEST NUMBER: P332433-927

CATALOG NUMBER: S123RDIW-S775D460U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.4	132.8	133.2	133.3	133.2	133.2	133.2	133.2
115°	153.1	153.2	153.3	153.3	153.2	153.1	153.0	153.0
117.5°	174.0	174.0	174.0	173.9	173.6	173.4	173.2	172.9
120°	188.0	187.9	187.8	187.7	187.5	187.4	187.2	187.0
122.5°	202.1	201.8	201.6	201.5	201.2	201.0	200.7	200.5
125°	223.0	222.7	222.4	222.0	221.7	221.4	221.1	220.8
127.5°	243.8	243.3	242.8	242.4	242.1	241.7	241.3	241.0
130°	257.5	257.1	256.8	256.4	255.9	255.3	254.8	254.1
132.5°	270.8	270.5	270.1	269.7	269.3	268.8	268.4	267.9
135°	290.9	290.6	290.3	290.0	289.9	289.7	289.5	289.4
137.5°	310.5	310.1	309.7	309.4	309.1	308.9	308.6	308.2
140°	323.3	323.2	323.1	322.8	322.3	321.7	321.2	320.6
142.5°	335.3	335.3	335.2	334.9	334.5	334.1	333.7	333.2
145°	353.1	353.0	352.9	352.8	352.4	352.1	351.8	351.5
147.5°	369.9	369.9	369.9	369.6	369.2	368.6	368.1	367.7
150°	380.2	380.2	380.2	379.9	379.5	379.0	378.5	378.0
152.5°	389.6	389.8	389.9	389.8	389.4	388.9	388.5	388.1
155°	403.5	403.8	404.1	403.9	403.4	402.8	402.3	401.7
157.5°	415.3	415.7	416.0	415.9	415.5	415.0	414.5	414.2
160°	422.6	423.0	423.4	423.4	423.1	422.8	422.5	422.2
162.5°	429.5	429.9	430.3	430.2	429.8	429.2	428.7	428.2
165°	438.2	438.7	439.2	439.1	438.6	438.0	437.4	436.9
167.5°	445.3	445.8	446.2	446.2	445.8	445.3	444.8	444.3
170°	449.2	449.7	450.3	450.3	449.7	449.2	448.6	448.1
172.5°	452.2	452.7	453.1	453.1	452.6	452.0	451.5	450.9
175°	455.4	455.9	456.4	456.4	455.8	455.3	454.7	454.2
177.5°	456.9	457.3	457.6	457.6	457.2	456.8	456.3	455.8
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)