

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332444

Luminaire Tested: **S123RDIW-S775D1320U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332444  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D1320U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8199.3 lumens  
Efficiency: N/A  
Efficacy: 133.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	30	28	27	22
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	20	17
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	45	37	32	51	41	34	29	34	28	25	27	23	20	20	18	16	13
8	52	40	33	28	47	37	30	26	31	26	22	24	21	18	19	16	14	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	1.5
10°-20°	337.3	4.1
20°-30°	485.7	5.9
30°-40°	547.1	6.7
40°-50°	523.4	6.4
50°-60°	428.6	5.2
60°-70°	289.2	3.5
70°-80°	145.5	1.8
80°-90°	43.3	0.5
90°-100°	62.9	0.8
100°-110°	299.9	3.7
110°-120°	720.3	8.8
120°-130°	917.3	11.2
130°-140°	980.1	12.0
140°-150°	916.5	11.2
150°-160°	739.3	9.0
160°-170°	477.1	5.8
170°-180°	164.4	2.0
0°-30°	944.3	11.5
0°-40°	1491.4	18.2
0°-60°	2443.4	29.8
0°-90°	2921.4	35.6
90°-120°	1083.2	13.2
90°-150°	3897.1	47.5
90°-180°	5278.0	64.4
0°-180°	8199.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	14	31	36	39	6
95°	78	29	40	48	49	97
105°	383	390	282	67	57	406
115°	719	727	738	750	756	709
125°	1013	1023	1029	1031	1034	905
135°	1261	1269	1274	1278	1274	971
145°	1456	1464	1467	1470	1470	911
155°	1603	1601	1602	1608	1601	738
165°	1691	1687	1686	1695	1687	478
175°	1731	1725	1726	1734	1724	165
180°	1731	1731	1731	1731	1731	



TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.4	18.9	17.4	15.9	14.5	14.1	14.8	15.6	16.3	17.1	17.1
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.1	30.9	32.0
92.5°	23.9	23.1	22.3	21.5	20.7	21.7	24.5	27.3	30.1	32.9	34.7
95°	78.4	66.7	55.0	43.3	31.6	27.3	30.4	33.6	36.7	39.9	41.9
97.5°	157.6	152.4	147.1	141.9	136.6	123.7	103.1	82.6	62.0	41.4	43.7
100°	217.3	223.0	228.7	234.4	240.2	220.7	176.2	131.6	87.0	42.4	44.7
102.5°	285.2	289.3	293.4	297.5	301.7	279.4	230.7	182.0	133.3	84.6	77.5
105°	383.2	386.3	389.5	392.6	395.7	384.5	358.7	333.0	307.3	281.6	231.0
107.5°	486.6	489.1	491.6	494.1	496.6	499.9	504.0	508.0	512.1	516.1	479.0
110°	555.5	557.8	560.0	562.3	564.6	567.3	570.5	573.6	576.8	579.9	570.5



TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	621.3	623.4	625.4	627.5	629.5	632.1	635.3	638.4	641.6	644.7	644.9
115°	718.8	720.5	722.2	723.9	725.6	727.8	730.3	732.9	735.5	738.1	740.9
117.5°	813.2	815.3	817.4	819.5	821.6	823.3	824.6	826.0	827.3	828.6	830.9
120°	871.8	874.4	876.9	879.5	882.1	883.8	884.6	885.5	886.4	887.2	889.5
122.5°	931.5	933.6	935.7	937.8	939.9	941.5	942.6	943.7	944.8	945.9	947.5
125°	1013.2	1015.5	1017.8	1020.1	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2
127.5°	1092.4	1094.7	1097.0	1099.3	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8
130°	1141.8	1144.1	1146.4	1148.7	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4
132.5°	1189.1	1191.4	1193.7	1196.0	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7
135°	1261.4	1263.1	1264.8	1266.5	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1
137.5°	1323.1	1325.3	1327.5	1329.6	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1
140°	1364.3	1366.0	1367.7	1369.4	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0
142.5°	1402.3	1404.0	1405.8	1407.5	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8
145°	1455.6	1457.6	1459.6	1461.6	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7
147.5°	1505.7	1507.0	1508.3	1509.6	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8
150°	1536.6	1537.4	1538.3	1539.1	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6
152.5°	1564.3	1564.7	1565.1	1565.5	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7
155°	1603.4	1602.9	1602.3	1601.7	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6
157.5°	1633.8	1633.7	1633.7	1633.6	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9
160°	1652.3	1652.0	1651.7	1651.4	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4
162.5°	1669.8	1669.0	1668.3	1667.5	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1
165°	1690.9	1690.0	1689.1	1688.3	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0
167.5°	1707.3	1706.2	1705.0	1703.9	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5
170°	1716.6	1715.4	1714.3	1713.2	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7
172.5°	1722.8	1721.4	1720.0	1718.6	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9
175°	1730.7	1729.3	1727.9	1726.4	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6
177.5°	1732.8	1731.6	1730.5	1729.4	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	17.1	17.2	17.2	17.2	17.1	17.1	17.0	16.9
90°	33.1	34.3	35.4	36.3	36.9	37.4	38.0	38.6
92.5°	36.6	38.4	40.2	41.3	41.7	42.0	42.3	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.0	48.3	50.5	51.8	52.1	52.4	52.7	53.0
100°	47.0	49.3	51.6	52.9	53.1	53.4	53.7	54.0
102.5°	70.4	63.3	56.3	53.0	53.5	54.0	54.5	55.0
105°	180.4	129.9	79.3	54.3	54.9	55.4	56.0	56.6
107.5°	442.0	404.9	367.8	330.2	292.1	253.9	215.8	177.7
110°	561.0	551.6	542.2	517.0	476.2	435.3	394.5	353.6





TEST NUMBER: P332444

CATALOG NUMBER: S123RDIW-S775D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.1	645.2	645.4	641.2	632.5	623.9	615.3	606.7
115°	743.8	746.6	749.5	751.5	752.6	753.8	754.9	756.1
117.5°	833.2	835.4	837.7	839.0	839.2	839.4	839.7	839.9
120°	891.8	894.1	896.4	897.5	897.5	897.5	897.5	897.5
122.5°	949.1	950.7	952.3	953.2	953.4	953.6	953.9	954.1
125°	1029.8	1030.4	1030.9	1031.5	1032.1	1032.7	1033.2	1033.8
127.5°	1110.7	1111.6	1112.6	1112.7	1112.2	1111.6	1111.0	1110.4
130°	1159.5	1160.7	1161.8	1162.1	1161.5	1161.0	1160.4	1159.8
132.5°	1205.8	1207.0	1208.1	1208.3	1207.5	1206.7	1205.9	1205.1
135°	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3
137.5°	1338.5	1339.8	1341.2	1341.6	1341.0	1340.5	1339.9	1339.3
140°	1378.1	1379.3	1380.4	1380.7	1380.1	1379.5	1379.0	1378.4
142.5°	1415.7	1416.6	1417.6	1417.6	1416.8	1416.0	1415.2	1414.4
145°	1468.3	1468.8	1469.4	1469.7	1469.7	1469.7	1469.7	1469.7
147.5°	1515.3	1515.9	1516.5	1516.1	1514.8	1513.5	1512.2	1510.8
150°	1544.1	1544.7	1545.3	1545.1	1544.3	1543.4	1542.6	1541.7
152.5°	1569.7	1570.8	1571.8	1571.7	1570.3	1569.0	1567.7	1566.4
155°	1605.0	1606.4	1607.9	1607.7	1606.0	1604.3	1602.6	1600.9
157.5°	1635.7	1637.4	1639.1	1638.8	1636.6	1634.4	1632.1	1629.9
160°	1653.1	1654.9	1656.6	1656.4	1654.4	1652.4	1650.4	1648.4
162.5°	1669.0	1671.0	1672.9	1673.0	1671.2	1669.5	1667.7	1665.9
165°	1690.3	1692.6	1694.9	1695.0	1693.0	1691.0	1689.0	1687.0
167.5°	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2
170°	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4
172.5°	1722.2	1724.5	1726.8	1726.6	1724.1	1721.6	1719.1	1716.6
175°	1729.6	1731.6	1733.6	1733.4	1731.2	1728.9	1726.6	1724.3
177.5°	1732.3	1734.2	1736.0	1735.8	1733.5	1731.2	1728.9	1726.6
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7

(END OF REPORT)