

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332435-927

Luminaire Tested: **S123RDIW-S775D755U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332435-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D755U927-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4488.3 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	44	40
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	38	35
4	77	66	58	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	46	65	55	48	43	48	43	39	42	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10428	10428	10428	10428
5°	12431	10472	9223	10472
10°	15522	10413	8332	10413
15°	18219	10307	7598	10307
20°	20333	10148	6975	10148
25°	20009	9980	6590	9980
30°	14382	9825	6196	9825
35°	9603	9625	5941	9625
40°	7075	9382	5675	9382
45°	5934	8958	5416	8958
50°	5238	8403	5056	8403
55°	4592	7767	4560	7767
60°	4090	7160	4179	7160
65°	3591	6507	3889	6507
70°	2820	5926	3550	5926
75°	2483	5178	3244	5178
80°	2163	4395	3186	4395
85°	1741	3532	3384	3532



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	2.1
10°-20°	297.7	6.6
20°-30°	467.6	10.4
30°-40°	487.9	10.9
40°-50°	417.5	9.3
50°-60°	318.2	7.1
60°-70°	204.0	4.5
70°-80°	98.1	2.2
80°-90°	28.2	0.6
90°-100°	48.8	1.1
100°-110°	145.9	3.3
110°-120°	248.2	5.5
120°-130°	326.5	7.3
130°-140°	367.0	8.2
140°-150°	360.7	8.0
150°-160°	303.7	6.8
160°-170°	202.2	4.5
170°-180°	70.8	1.6
0°-30°	860.6	19.2
0°-40°	1348.4	30.0
0°-60°	2084.2	46.4
0°-90°	2414.5	53.8
90°-120°	442.9	9.9
90°-150°	1497.2	33.4
90°-180°	2074.0	46.2
0°-180°	4488.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1150	969	854	969	1150	119
15°	1635	925	682	925	1635	464
25°	1685	840	555	840	1685	724
35°	731	732	452	732	731	479
45°	390	588	356	588	390	307
55°	245	414	243	414	245	221
65°	141	256	153	256	141	139
75°	60	124	78	124	60	64
85°	14	29	27	29	14	17
90°	18	1	18	1	18	9
95°	46	35	46	35	46	47
105°	140	132	140	132	140	149
115°	250	250	250	250	250	248
125°	362	366	362	366	362	323
135°	474	474	474	474	474	364
145°	576	576	576	576	576	359
155°	658	659	658	659	658	303
165°	716	718	716	718	716	202
175°	744	747	744	747	744	71
180°	748	748	748	748	748	



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1031.9	1033.2	1028.9	1028.3	1023.3	1021.9	1021.9	1014.9	1010.7	1005.0	1001.7
5°	1150.5	1157.1	1153.8	1146.4	1133.9	1131.0	1123.2	1110.7	1096.6	1079.2	1070.9
7.5°	1298.6	1307.7	1304.2	1292.7	1279.7	1269.2	1246.9	1226.2	1197.3	1171.9	1150.2
10°	1420.1	1410.6	1403.1	1391.9	1379.9	1360.3	1337.1	1305.2	1268.3	1239.3	1206.9
12.5°	1511.0	1509.4	1500.0	1488.4	1471.5	1452.9	1424.4	1385.5	1342.6	1300.7	1263.7
15°	1634.9	1637.4	1631.2	1619.1	1595.1	1562.3	1519.2	1503.0	1441.7	1396.1	1350.4
17.5°	1720.7	1720.2	1719.4	1702.7	1678.2	1654.9	1614.9	1572.3	1516.7	1452.5	1391.0
20°	1775.1	1771.0	1771.8	1753.1	1734.9	1707.9	1669.0	1607.2	1561.5	1487.3	1423.8
22.5°	1773.8	1773.0	1776.2	1769.7	1756.4	1735.8	1705.1	1653.0	1594.7	1519.8	1448.3
25°	1684.7	1681.4	1700.9	1706.3	1727.4	1731.2	1722.0	1693.4	1638.2	1561.1	1472.7
27.5°	1410.0	1408.2	1444.3	1489.6	1547.0	1591.7	1634.7	1655.6	1638.2	1583.0	1494.5
30°	1157.1	1196.1	1214.4	1279.9	1352.9	1440.0	1516.3	1588.9	1606.7	1582.7	1510.1
32.5°	960.8	994.7	1010.0	1066.2	1134.2	1236.3	1350.8	1453.5	1526.1	1544.5	1500.8
35°	730.8	731.2	766.0	790.9	854.0	958.9	1070.1	1207.8	1344.6	1448.3	1459.0
37.5°	583.1	585.2	606.3	631.1	678.3	733.9	831.7	946.2	1104.3	1263.5	1356.8
40°	503.5	507.2	523.0	547.5	581.5	623.4	699.7	807.6	939.4	1116.5	1261.2
42.5°	452.4	458.4	466.6	485.4	506.5	545.7	607.4	690.7	810.6	978.1	1145.1
45°	389.8	393.2	399.4	408.1	427.2	454.6	496.1	552.0	651.6	786.4	953.5
47.5°	343.9	342.1	348.7	355.8	368.4	387.1	414.9	460.7	531.6	639.8	781.6
50°	312.8	312.3	316.9	322.3	334.3	348.0	370.8	405.2	461.6	551.2	681.0
52.5°	283.5	285.1	288.4	295.1	303.7	314.8	335.3	360.0	408.5	485.8	594.1
55°	244.7	246.0	250.5	254.2	260.5	271.6	284.6	305.2	338.4	392.4	481.5
57.5°	211.8	211.3	215.6	216.6	223.6	232.7	242.7	258.8	282.9	322.9	382.9
60°	190.0	188.7	192.4	195.4	199.1	206.5	214.8	230.6	249.7	279.1	330.6
62.5°	170.1	169.4	172.2	175.1	178.2	185.0	191.9	204.1	219.1	244.0	284.8
65°	141.0	142.3	143.5	144.7	146.4	150.5	157.2	165.5	175.9	193.3	222.7
67.5°	110.8	112.1	112.5	115.0	118.6	121.2	125.2	132.6	139.8	154.6	171.3
70°	89.6	89.2	89.6	90.9	95.4	100.0	105.4	110.7	115.3	125.6	139.7
72.5°	77.0	76.2	77.3	77.6	79.8	81.0	84.4	89.5	95.4	102.4	112.6
75°	59.7	59.7	59.7	59.7	61.4	62.2	63.5	64.7	66.8	70.1	77.6
77.5°	44.1	44.2	44.8	45.2	45.6	46.0	46.8	48.0	48.8	50.5	53.8
80°	34.9	35.3	34.9	35.3	35.3	36.0	36.5	37.7	38.2	40.2	41.5
82.5°	26.2	26.0	26.2	26.6	26.6	27.5	27.6	28.4	28.5	29.6	30.9
85°	14.1	13.3	14.1	13.7	14.5	13.7	14.1	14.9	14.9	15.4	17.0
87.5°	6.8	7.4	6.7	7.1	7.0	7.2	7.1	7.1	7.6	7.1	7.1
90°	17.7	17.3	17.1	16.9	16.6	16.2	15.7	15.1	14.7	14.1	12.4
92.5°	23.8	23.9	24.1	24.2	24.4	24.2	23.8	23.4	23.0	22.6	21.6
95°	45.9	45.9	45.9	45.9	45.9	45.6	45.1	44.5	44.0	43.5	42.5
97.5°	70.6	70.6	70.7	70.7	70.7	70.5	69.9	69.3	68.7	68.1	67.3
100°	89.4	89.1	88.9	88.6	88.3	88.0	87.6	87.2	86.8	86.4	85.8
102.5°	108.7	108.7	108.8	108.8	108.8	108.7	108.3	107.9	107.5	107.1	106.2
105°	140.0	139.7	139.4	139.2	138.9	138.8	138.8	138.8	138.8	138.8	137.6
107.5°	172.5	172.7	172.9	173.0	173.2	173.0	172.6	172.1	171.7	171.3	170.9
110°	194.6	194.9	195.1	195.4	195.7	195.5	195.0	194.5	194.0	193.5	193.2



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	218.2	218.2	218.2	218.3	218.3	218.1	217.5	216.8	216.2	215.6	215.5
115°	250.5	250.6	250.7	250.9	251.0	251.0	250.9	250.7	250.6	250.5	250.7
117.5°	283.3	283.7	284.0	284.4	284.8	284.9	284.9	285.0	285.0	285.0	285.4
120°	306.3	306.6	306.9	307.1	307.4	307.6	307.7	307.8	308.0	308.1	308.8
122.5°	328.4	328.8	329.2	329.5	329.9	330.3	330.6	331.0	331.3	331.6	332.0
125°	361.6	362.1	362.7	363.2	363.7	364.2	364.7	365.3	365.8	366.3	366.5
127.5°	394.7	395.3	395.9	396.5	397.0	397.8	398.5	399.2	399.9	400.7	400.9
130°	416.3	417.2	418.1	419.1	419.9	420.6	421.2	421.8	422.2	422.8	423.2
132.5°	438.9	439.6	440.3	441.0	441.7	442.4	443.0	443.6	444.3	444.9	445.1
135°	473.9	474.2	474.4	474.7	475.0	475.4	475.9	476.4	476.9	477.4	477.6
137.5°	504.9	505.3	505.8	506.4	506.8	507.4	507.9	508.4	509.0	509.5	509.2
140°	525.1	526.0	526.9	527.8	528.7	529.3	529.4	529.5	529.7	529.8	529.7
142.5°	545.7	546.4	547.2	547.9	548.6	549.0	549.1	549.3	549.4	549.5	549.3
145°	575.7	576.2	576.7	577.2	577.7	578.1	578.2	578.3	578.5	578.6	578.2
147.5°	602.2	603.0	603.8	604.6	605.4	605.8	605.8	605.8	605.8	605.8	605.4
150°	619.2	620.0	620.8	621.5	622.3	622.7	622.7	622.7	622.7	622.7	622.4
152.5°	635.6	636.3	637.0	637.6	638.3	638.6	638.3	638.2	637.9	637.7	637.5
155°	658.0	658.9	659.8	660.7	661.6	661.8	661.3	660.8	660.3	659.7	659.6
157.5°	678.3	679.1	679.8	680.5	681.2	681.4	680.8	680.2	679.7	679.1	679.1
160°	691.5	692.0	692.5	693.1	693.6	693.5	692.8	692.2	691.6	690.9	690.9
162.5°	701.3	702.2	703.1	703.9	704.7	704.8	704.2	703.5	702.8	702.2	702.1
165°	715.6	716.5	717.4	718.4	719.2	719.3	718.5	717.7	716.9	716.1	716.1
167.5°	727.7	728.5	729.3	730.2	730.9	730.9	730.2	729.3	728.5	727.7	727.6
170°	733.8	734.7	735.6	736.6	737.4	737.4	736.6	735.6	734.7	733.8	733.8
172.5°	738.6	739.4	740.4	741.2	742.2	742.2	741.4	740.6	739.8	738.9	738.9
175°	743.8	744.7	745.6	746.6	747.5	747.5	746.7	746.0	745.2	744.4	744.4
177.5°	746.6	747.3	748.1	748.8	749.6	749.6	749.0	748.4	747.7	747.1	747.1
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1000.4	999.3	994.7	989.4	982.5	977.8	974.1	972.2	966.2	958.9	953.9
5°	1062.2	1049.7	1036.5	1020.3	1005.4	990.0	980.5	969.2	955.6	940.2	929.5
7.5°	1128.4	1104.0	1077.7	1050.6	1023.7	999.7	978.5	960.3	938.5	916.5	901.1
10°	1179.2	1143.4	1106.5	1068.8	1034.4	1002.0	977.2	952.7	926.5	901.3	882.2
12.5°	1225.3	1178.3	1135.8	1089.4	1045.4	1006.7	970.8	942.1	910.6	883.7	861.9
15°	1283.7	1235.6	1184.1	1113.6	1055.1	1006.2	962.7	924.9	886.8	853.6	832.4
17.5°	1338.2	1265.8	1196.7	1137.9	1061.9	1000.8	947.6	902.5	860.6	825.5	799.4
20°	1360.8	1290.7	1215.6	1140.6	1065.9	997.4	935.6	885.9	842.3	802.6	778.5
22.5°	1374.4	1295.0	1215.9	1135.3	1056.0	984.8	923.8	868.9	821.8	783.9	754.2
25°	1390.2	1295.7	1208.6	1128.9	1048.1	970.9	898.3	840.3	789.3	749.0	717.5
27.5°	1400.7	1289.4	1186.5	1098.0	1016.0	939.1	872.6	811.1	759.3	716.8	682.9
30°	1402.6	1284.4	1169.6	1073.8	990.4	919.9	849.4	790.5	735.8	690.5	659.0
32.5°	1405.3	1272.2	1146.7	1044.9	959.6	889.7	825.9	769.6	713.5	669.0	636.8
35°	1394.4	1265.4	1111.9	995.0	909.5	841.9	784.3	732.5	677.3	634.1	601.3
37.5°	1347.3	1238.4	1075.9	938.7	849.4	786.8	739.8	694.6	644.0	597.5	566.6
40°	1299.8	1211.9	1048.1	904.6	811.3	746.9	704.6	667.7	618.8	575.3	542.1
42.5°	1229.2	1175.8	1021.5	868.7	768.1	706.2	670.5	635.9	592.9	548.7	517.5
45°	1099.5	1106.5	967.2	811.7	708.4	646.2	612.6	588.5	550.4	513.9	482.0
47.5°	936.9	1002.8	903.4	750.8	645.4	587.0	557.7	536.7	511.0	475.2	446.0
50°	830.8	924.9	852.3	710.0	605.9	547.9	518.9	501.8	479.4	451.2	423.4
52.5°	732.8	834.0	790.6	664.6	563.2	510.1	481.7	467.7	449.9	423.3	398.2
55°	597.6	700.1	690.1	596.0	498.9	451.2	429.7	413.9	401.9	382.0	362.1
57.5°	483.5	580.6	585.7	519.7	442.4	395.2	376.7	364.8	357.0	341.9	323.5
60°	411.5	500.6	518.0	468.3	401.9	360.4	342.1	332.6	326.4	314.4	300.3
62.5°	351.7	427.6	447.3	411.5	363.1	324.2	310.0	300.8	296.5	286.1	273.7
65°	269.2	332.2	351.3	331.4	306.1	275.0	263.4	255.5	251.8	246.0	236.8
67.5°	202.4	248.3	269.3	255.2	246.1	226.5	219.0	214.8	211.5	207.6	199.9
70°	162.6	196.6	218.2	214.4	207.0	196.6	191.2	188.3	185.0	181.6	175.0
72.5°	130.7	154.2	174.4	176.3	170.2	168.0	163.3	162.1	160.1	156.1	152.5
75°	86.7	102.8	116.9	122.3	124.8	126.9	124.8	124.5	124.0	120.7	118.6
77.5°	56.8	65.5	74.4	83.6	87.5	90.3	91.0	92.5	91.4	89.7	88.6
80°	43.6	45.6	51.8	59.7	65.9	68.4	70.1	70.9	70.5	70.1	68.4
82.5°	31.6	33.4	36.3	41.8	47.1	51.2	52.2	52.0	52.9	53.2	51.8
85°	17.0	17.4	18.2	19.1	21.9	26.5	27.8	28.6	29.5	29.5	26.9
87.5°	7.4	6.8	7.1	6.8	7.5	7.6	9.3	10.8	11.3	10.3	10.5
90°	10.7	9.0	7.3	5.8	4.5	3.2	1.9	0.6	1.9	3.2	4.5
92.5°	20.7	19.6	18.7	17.7	16.9	16.0	15.1	14.3	15.1	16.0	16.9
95°	41.4	40.4	39.3	38.3	37.5	36.5	35.6	34.7	35.6	36.5	37.5
97.5°	66.5	65.8	65.0	64.3	63.7	63.0	62.3	61.6	62.3	63.0	63.7
100°	85.2	84.4	83.8	83.1	82.3	81.5	80.7	79.9	80.7	81.5	82.3
102.5°	105.4	104.6	103.7	103.0	102.5	102.1	101.6	101.2	101.6	102.1	102.5
105°	136.4	135.2	134.0	133.3	133.1	132.8	132.5	132.3	132.5	132.8	133.1
107.5°	170.4	169.9	169.4	169.1	169.0	168.8	168.7	168.5	168.7	168.8	169.0
110°	192.9	192.7	192.4	192.1	191.9	191.6	191.4	191.1	191.4	191.6	191.9





TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	215.5	215.4	215.3	215.2	215.1	214.9	214.8	214.6	214.8	214.9	215.1
115°	251.0	251.3	251.5	251.4	251.0	250.6	250.3	249.9	250.3	250.6	251.0
117.5°	285.7	286.1	286.5	286.5	286.2	285.9	285.7	285.4	285.7	285.9	286.2
120°	309.4	310.1	310.7	310.7	309.9	309.1	308.3	307.5	308.3	309.1	309.9
122.5°	332.3	332.6	333.0	332.9	332.3	331.7	331.1	330.6	331.1	331.7	332.3
125°	366.9	367.1	367.3	367.3	366.9	366.5	366.1	365.8	366.1	366.5	366.9
127.5°	401.2	401.6	401.8	401.6	400.7	399.9	399.0	398.2	399.0	399.9	400.7
130°	423.6	424.0	424.4	424.0	422.9	421.9	420.9	419.9	420.9	421.9	422.9
132.5°	445.4	445.8	446.0	445.7	444.6	443.5	442.5	441.5	442.5	443.5	444.6
135°	477.7	477.8	478.0	477.6	476.9	476.1	475.3	474.5	475.3	476.1	476.9
137.5°	508.9	508.5	508.2	507.7	507.1	506.4	505.7	505.1	505.7	506.4	507.1
140°	529.5	529.4	529.3	528.9	528.2	527.6	526.9	526.2	526.9	527.6	528.2
142.5°	549.1	548.8	548.6	548.1	547.5	546.8	546.2	545.6	546.2	546.8	547.5
145°	577.8	577.4	577.0	576.7	576.4	576.2	575.9	575.7	575.9	576.2	576.4
147.5°	605.0	604.7	604.3	603.9	603.4	602.9	602.5	602.0	602.5	602.9	603.4
150°	622.2	621.9	621.6	621.4	621.2	620.8	620.6	620.4	620.6	620.8	621.2
152.5°	637.4	637.2	637.1	636.8	636.5	636.1	635.7	635.4	635.7	636.1	636.5
155°	659.5	659.3	659.2	659.2	659.2	659.2	659.2	659.2	659.2	659.2	659.2
157.5°	678.9	678.8	678.7	678.7	678.9	679.1	679.2	679.4	679.2	679.1	678.9
160°	690.9	690.9	690.9	691.0	691.3	691.6	691.8	692.1	691.8	691.6	691.3
162.5°	702.0	701.9	701.8	701.9	702.3	702.6	703.0	703.4	703.0	702.6	702.3
165°	716.1	716.1	716.1	716.4	716.8	717.2	717.6	718.0	717.6	717.2	716.8
167.5°	727.5	727.4	727.3	727.5	728.0	728.6	729.0	729.6	729.0	728.6	728.0
170°	733.8	733.8	733.8	734.0	734.6	735.1	735.6	736.2	735.6	735.1	734.6
172.5°	738.9	738.9	738.9	739.3	739.7	740.3	740.8	741.3	740.8	740.3	739.7
175°	744.4	744.4	744.4	744.7	745.2	745.7	746.2	746.7	746.2	745.7	745.2
177.5°	747.1	747.1	747.1	747.3	747.7	748.1	748.5	749.0	748.5	748.1	747.7
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	952.3	947.9	945.0	938.3	934.0	929.4	924.7	927.7	927.4	927.0	927.0
5°	920.4	910.8	902.1	890.9	883.8	875.1	868.5	867.7	869.3	863.5	860.2
7.5°	888.7	875.6	863.2	850.9	837.8	827.4	820.8	817.7	813.5	809.9	806.2
10°	866.4	851.0	839.0	823.7	809.6	797.2	789.3	783.9	780.9	778.1	772.7
12.5°	843.5	828.5	813.2	795.8	782.4	767.9	762.1	756.0	750.4	747.2	739.8
15°	810.0	790.5	774.4	756.1	741.2	727.1	718.7	706.7	705.0	700.9	693.5
17.5°	776.4	755.3	732.9	719.5	702.6	687.9	675.3	671.2	659.3	654.9	648.4
20°	749.9	730.4	713.4	695.5	671.1	657.4	647.5	642.1	632.5	626.7	622.5
22.5°	727.0	707.2	687.5	666.7	646.5	631.1	623.8	615.4	610.3	602.1	597.6
25°	694.3	672.7	649.1	626.7	612.2	600.6	588.9	581.5	574.0	570.3	562.0
27.5°	656.3	633.7	611.6	594.7	576.9	565.4	554.8	548.2	539.2	533.0	528.4
30°	635.4	608.9	589.8	574.4	551.6	540.8	533.0	524.7	518.0	511.4	506.8
32.5°	611.2	586.9	568.9	549.9	532.3	520.6	510.4	503.1	497.4	491.2	486.6
35°	573.1	552.9	534.2	515.1	502.2	490.2	478.2	472.0	466.6	460.8	456.6
37.5°	538.8	519.8	502.1	484.0	468.1	458.3	448.6	443.9	436.6	432.7	428.4
40°	517.6	498.9	479.8	462.5	445.8	438.4	429.7	422.6	416.0	413.1	408.5
42.5°	494.4	475.7	459.6	440.8	427.3	417.2	409.1	401.4	396.4	392.2	389.6
45°	459.9	443.4	427.6	408.9	396.1	387.4	378.3	371.2	366.6	363.8	359.2
47.5°	426.5	410.0	394.0	377.6	365.2	355.3	346.2	341.3	335.2	331.6	328.6
50°	402.3	387.4	370.3	355.5	343.0	333.0	325.6	319.3	313.9	309.4	307.4
52.5°	380.1	364.2	349.4	335.6	322.4	311.2	304.4	297.8	293.7	288.5	286.1
55°	343.4	328.0	315.6	301.9	289.1	279.6	271.2	265.5	261.3	255.5	252.2
57.5°	309.0	295.2	280.4	268.5	255.2	247.2	240.3	232.4	227.4	222.8	219.6
60°	285.7	270.0	257.1	246.0	234.3	223.9	217.8	211.5	206.1	201.5	198.7
62.5°	261.6	247.8	235.6	223.4	212.8	203.7	196.5	191.3	186.6	183.6	180.8
65°	224.3	213.6	201.1	191.2	181.3	174.6	168.8	164.2	160.9	158.8	156.4
67.5°	190.2	179.7	168.9	159.1	152.5	147.4	143.6	139.7	138.0	135.4	133.7
70°	167.9	157.2	147.7	140.2	133.6	129.8	127.3	124.5	122.8	119.5	117.8
72.5°	143.8	135.9	129.0	122.9	117.6	114.2	111.1	107.5	104.9	101.2	99.6
75°	113.2	106.2	100.8	96.6	93.3	88.7	84.2	80.5	79.2	78.0	77.6
77.5°	83.9	79.4	75.5	72.0	67.9	64.6	63.5	62.7	62.4	61.8	61.8
80°	65.9	61.8	58.9	54.7	52.3	52.3	52.3	51.4	51.8	51.8	51.8
82.5°	49.0	45.2	43.6	42.1	41.7	42.0	42.0	42.1	41.9	42.5	42.2
85°	25.3	25.7	26.5	26.1	26.5	26.5	27.4	26.9	27.4	26.5	27.4
87.5°	10.5	11.7	12.4	13.1	13.8	13.8	14.2	14.3	14.7	14.8	14.9
90°	5.8	7.3	9.0	10.7	12.4	14.1	14.7	15.1	15.7	16.2	16.6
92.5°	17.7	18.7	19.6	20.7	21.6	22.6	23.0	23.4	23.8	24.2	24.4
95°	38.3	39.3	40.4	41.4	42.5	43.5	44.0	44.5	45.1	45.6	45.9
97.5°	64.3	65.0	65.8	66.5	67.3	68.1	68.7	69.3	69.9	70.5	70.7
100°	83.1	83.8	84.4	85.2	85.8	86.4	86.8	87.2	87.6	88.0	88.3
102.5°	103.0	103.7	104.6	105.4	106.2	107.1	107.5	107.9	108.3	108.7	108.8
105°	133.3	134.0	135.2	136.4	137.6	138.8	138.8	138.8	138.8	138.8	138.9
107.5°	169.1	169.4	169.9	170.4	170.9	171.3	171.7	172.1	172.6	173.0	173.2
110°	192.1	192.4	192.7	192.9	193.2	193.5	194.0	194.5	195.0	195.5	195.7



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	215.2	215.3	215.4	215.5	215.5	215.6	216.2	216.8	217.5	218.1	218.3
115°	251.4	251.5	251.3	251.0	250.7	250.5	250.6	250.7	250.9	251.0	251.0
117.5°	286.5	286.5	286.1	285.7	285.4	285.0	285.0	285.0	284.9	284.9	284.8
120°	310.7	310.7	310.1	309.4	308.8	308.1	308.0	307.8	307.7	307.6	307.4
122.5°	332.9	333.0	332.6	332.3	332.0	331.6	331.3	331.0	330.6	330.3	329.9
125°	367.3	367.3	367.1	366.9	366.5	366.3	365.8	365.3	364.7	364.2	363.7
127.5°	401.6	401.8	401.6	401.2	400.9	400.7	399.9	399.2	398.5	397.8	397.0
130°	424.0	424.4	424.0	423.6	423.2	422.8	422.2	421.8	421.2	420.6	419.9
132.5°	445.7	446.0	445.8	445.4	445.1	444.9	444.3	443.6	443.0	442.4	441.7
135°	477.6	478.0	477.8	477.7	477.6	477.4	476.9	476.4	475.9	475.4	475.0
137.5°	507.7	508.2	508.5	508.9	509.2	509.5	509.0	508.4	507.9	507.4	506.8
140°	528.9	529.3	529.4	529.5	529.7	529.8	529.7	529.5	529.4	529.3	528.7
142.5°	548.1	548.6	548.8	549.1	549.3	549.5	549.4	549.3	549.1	549.0	548.6
145°	576.7	577.0	577.4	577.8	578.2	578.6	578.5	578.3	578.2	578.1	577.7
147.5°	603.9	604.3	604.7	605.0	605.4	605.8	605.8	605.8	605.8	605.8	605.4
150°	621.4	621.6	621.9	622.2	622.4	622.7	622.7	622.7	622.7	622.7	622.3
152.5°	636.8	637.1	637.2	637.4	637.5	637.7	637.9	638.2	638.3	638.6	638.3
155°	659.2	659.2	659.3	659.5	659.6	659.7	660.3	660.8	661.3	661.8	661.6
157.5°	678.7	678.7	678.8	678.9	679.1	679.1	679.7	680.2	680.8	681.4	681.2
160°	691.0	690.9	690.9	690.9	690.9	690.9	691.6	692.2	692.8	693.5	693.6
162.5°	701.9	701.8	701.9	702.0	702.1	702.2	702.8	703.5	704.2	704.8	704.7
165°	716.4	716.1	716.1	716.1	716.1	716.1	716.9	717.7	718.5	719.3	719.2
167.5°	727.5	727.3	727.4	727.5	727.6	727.7	728.5	729.3	730.2	730.9	730.9
170°	734.0	733.8	733.8	733.8	733.8	733.8	734.7	735.6	736.6	737.4	737.4
172.5°	739.3	738.9	738.9	738.9	738.9	738.9	739.8	740.6	741.4	742.2	742.2
175°	744.7	744.4	744.4	744.4	744.4	744.4	745.2	746.0	746.7	747.5	747.5
177.5°	747.3	747.1	747.1	747.1	747.1	747.1	747.7	748.4	749.0	749.6	749.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	923.1	922.7	923.1	921.7	923.1	922.7	923.1	927.0	927.0	927.4	927.7
5°	859.0	858.5	857.3	853.6	857.3	858.5	859.0	860.2	863.5	869.3	867.7
7.5°	803.0	802.4	798.8	798.8	798.8	802.4	803.0	806.2	809.9	813.5	817.7
10°	769.8	770.2	765.2	762.3	765.2	770.2	769.8	772.7	778.1	780.9	783.9
12.5°	737.6	735.7	731.7	728.5	731.7	735.7	737.6	739.8	747.2	750.4	756.0
15°	695.1	690.9	681.0	681.8	681.0	690.9	695.1	693.5	700.9	705.0	706.7
17.5°	645.1	642.1	641.8	636.0	641.8	642.1	645.1	648.4	654.9	659.3	671.2
20°	615.9	613.9	614.7	608.9	614.7	613.9	615.9	622.5	626.7	632.5	642.1
22.5°	593.0	591.0	587.5	585.7	587.5	591.0	593.0	597.6	602.1	610.3	615.4
25°	559.5	556.2	552.9	554.9	552.9	556.2	559.5	562.0	570.3	574.0	581.5
27.5°	526.0	523.5	520.1	519.8	520.1	523.5	526.0	528.4	533.0	539.2	548.2
30°	504.8	502.2	500.6	498.5	500.6	502.2	504.8	506.8	511.4	518.0	524.7
32.5°	483.2	482.7	479.7	479.3	479.7	482.7	483.2	486.6	491.2	497.4	503.1
35°	455.0	452.5	451.6	452.1	451.6	452.5	455.0	456.6	460.8	466.6	472.0
37.5°	428.2	424.8	423.3	421.9	423.3	424.8	428.2	428.4	432.7	436.6	443.9
40°	408.9	405.6	404.8	403.9	404.8	405.6	408.9	408.5	413.1	416.0	422.6
42.5°	387.4	386.0	385.6	384.0	385.6	386.0	387.4	389.6	392.2	396.4	401.4
45°	357.9	357.5	355.1	355.8	355.1	357.5	357.9	359.2	363.8	366.6	371.2
47.5°	326.9	325.1	323.4	324.5	323.4	325.1	326.9	328.6	331.6	335.2	341.3
50°	305.7	304.8	301.1	301.9	301.1	304.8	305.7	307.4	309.4	313.9	319.3
52.5°	284.5	281.3	279.9	279.4	279.9	281.3	284.5	286.1	288.5	293.7	297.8
55°	249.3	245.5	243.8	243.0	243.8	245.5	249.3	252.2	255.5	261.3	265.5
57.5°	214.8	213.7	212.5	213.3	212.5	213.7	214.8	219.6	222.8	227.4	232.4
60°	194.5	194.5	194.5	194.1	194.5	194.5	194.5	198.7	201.5	206.1	211.5
62.5°	179.0	177.9	177.6	178.2	177.6	177.9	179.0	180.8	183.6	186.6	191.3
65°	155.1	154.7	153.0	152.7	153.0	154.7	155.1	156.4	158.8	160.9	164.2
67.5°	132.6	131.1	130.6	130.1	130.6	131.1	132.6	133.7	135.4	138.0	139.7
70°	115.7	114.9	112.4	112.8	112.4	114.9	115.7	117.8	119.5	122.8	124.5
72.5°	97.4	96.6	96.2	95.5	96.2	96.6	97.4	99.6	101.2	104.9	107.5
75°	77.2	76.8	76.3	78.0	76.3	76.8	77.2	77.6	78.0	79.2	80.5
77.5°	61.8	61.8	62.0	61.4	62.0	61.8	61.8	61.8	61.8	62.4	62.7
80°	51.8	51.8	51.4	51.4	51.4	51.8	51.8	51.8	51.8	51.8	51.4
82.5°	41.6	41.9	42.1	41.5	42.1	41.9	41.6	42.2	42.5	41.9	42.1
85°	27.4	26.9	27.8	27.4	27.8	26.9	27.4	27.4	26.5	27.4	26.9
87.5°	15.7	15.1	15.1	15.4	15.1	15.1	15.7	14.9	14.8	14.7	14.3
90°	16.9	17.1	17.3	17.7	17.3	17.1	16.9	16.6	16.2	15.7	15.1
92.5°	24.2	24.1	23.9	23.8	23.9	24.1	24.2	24.4	24.2	23.8	23.4
95°	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.9	45.6	45.1	44.5
97.5°	70.7	70.7	70.6	70.6	70.6	70.7	70.7	70.7	70.5	69.9	69.3
100°	88.6	88.9	89.1	89.4	89.1	88.9	88.6	88.3	88.0	87.6	87.2
102.5°	108.8	108.8	108.7	108.7	108.7	108.8	108.8	108.8	108.7	108.3	107.9
105°	139.2	139.4	139.7	140.0	139.7	139.4	139.2	138.9	138.8	138.8	138.8
107.5°	173.0	172.9	172.7	172.5	172.7	172.9	173.0	173.2	173.0	172.6	172.1
110°	195.4	195.1	194.9	194.6	194.9	195.1	195.4	195.7	195.5	195.0	194.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	218.3	218.2	218.2	218.2	218.2	218.2	218.3	218.3	218.1	217.5	216.8
115°	250.9	250.7	250.6	250.5	250.6	250.7	250.9	251.0	251.0	250.9	250.7
117.5°	284.4	284.0	283.7	283.3	283.7	284.0	284.4	284.8	284.9	284.9	285.0
120°	307.1	306.9	306.6	306.3	306.6	306.9	307.1	307.4	307.6	307.7	307.8
122.5°	329.5	329.2	328.8	328.4	328.8	329.2	329.5	329.9	330.3	330.6	331.0
125°	363.2	362.7	362.1	361.6	362.1	362.7	363.2	363.7	364.2	364.7	365.3
127.5°	396.5	395.9	395.3	394.7	395.3	395.9	396.5	397.0	397.8	398.5	399.2
130°	419.1	418.1	417.2	416.3	417.2	418.1	419.1	419.9	420.6	421.2	421.8
132.5°	441.0	440.3	439.6	438.9	439.6	440.3	441.0	441.7	442.4	443.0	443.6
135°	474.7	474.4	474.2	473.9	474.2	474.4	474.7	475.0	475.4	475.9	476.4
137.5°	506.4	505.8	505.3	504.9	505.3	505.8	506.4	506.8	507.4	507.9	508.4
140°	527.8	526.9	526.0	525.1	526.0	526.9	527.8	528.7	529.3	529.4	529.5
142.5°	547.9	547.2	546.4	545.7	546.4	547.2	547.9	548.6	549.0	549.1	549.3
145°	577.2	576.7	576.2	575.7	576.2	576.7	577.2	577.7	578.1	578.2	578.3
147.5°	604.6	603.8	603.0	602.2	603.0	603.8	604.6	605.4	605.8	605.8	605.8
150°	621.5	620.8	620.0	619.2	620.0	620.8	621.5	622.3	622.7	622.7	622.7
152.5°	637.6	637.0	636.3	635.6	636.3	637.0	637.6	638.3	638.6	638.3	638.2
155°	660.7	659.8	658.9	658.0	658.9	659.8	660.7	661.6	661.8	661.3	660.8
157.5°	680.5	679.8	679.1	678.3	679.1	679.8	680.5	681.2	681.4	680.8	680.2
160°	693.1	692.5	692.0	691.5	692.0	692.5	693.1	693.6	693.5	692.8	692.2
162.5°	703.9	703.1	702.2	701.3	702.2	703.1	703.9	704.7	704.8	704.2	703.5
165°	718.4	717.4	716.5	715.6	716.5	717.4	718.4	719.2	719.3	718.5	717.7
167.5°	730.2	729.3	728.5	727.7	728.5	729.3	730.2	730.9	730.9	730.2	729.3
170°	736.6	735.6	734.7	733.8	734.7	735.6	736.6	737.4	737.4	736.6	735.6
172.5°	741.2	740.4	739.4	738.6	739.4	740.4	741.2	742.2	742.2	741.4	740.6
175°	746.6	745.6	744.7	743.8	744.7	745.6	746.6	747.5	747.5	746.7	746.0
177.5°	748.8	748.1	747.3	746.6	747.3	748.1	748.8	749.6	749.6	749.0	748.4
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	924.7	929.4	934.0	938.3	945.0	947.9	952.3	953.9	958.9	966.2	972.2
5°	868.5	875.1	883.8	890.9	902.1	910.8	920.4	929.5	940.2	955.6	969.2
7.5°	820.8	827.4	837.8	850.9	863.2	875.6	888.7	901.1	916.5	938.5	960.3
10°	789.3	797.2	809.6	823.7	839.0	851.0	866.4	882.2	901.3	926.5	952.7
12.5°	762.1	767.9	782.4	795.8	813.2	828.5	843.5	861.9	883.7	910.6	942.1
15°	718.7	727.1	741.2	756.1	774.4	790.5	810.0	832.4	853.6	886.8	924.9
17.5°	675.3	687.9	702.6	719.5	732.9	755.3	776.4	799.4	825.5	860.6	902.5
20°	647.5	657.4	671.1	695.5	713.4	730.4	749.9	778.5	802.6	842.3	885.9
22.5°	623.8	631.1	646.5	666.7	687.5	707.2	727.0	754.2	783.9	821.8	868.9
25°	588.9	600.6	612.2	626.7	649.1	672.7	694.3	717.5	749.0	789.3	840.3
27.5°	554.8	565.4	576.9	594.7	611.6	633.7	656.3	682.9	716.8	759.3	811.1
30°	533.0	540.8	551.6	574.4	589.8	608.9	635.4	659.0	690.5	735.8	790.5
32.5°	510.4	520.6	532.3	549.9	568.9	586.9	611.2	636.8	669.0	713.5	769.6
35°	478.2	490.2	502.2	515.1	534.2	552.9	573.1	601.3	634.1	677.3	732.5
37.5°	448.6	458.3	468.1	484.0	502.1	519.8	538.8	566.6	597.5	644.0	694.6
40°	429.7	438.4	445.8	462.5	479.8	498.9	517.6	542.1	575.3	618.8	667.7
42.5°	409.1	417.2	427.3	440.8	459.6	475.7	494.4	517.5	548.7	592.9	635.9
45°	378.3	387.4	396.1	408.9	427.6	443.4	459.9	482.0	513.9	550.4	588.5
47.5°	346.2	355.3	365.2	377.6	394.0	410.0	426.5	446.0	475.2	511.0	536.7
50°	325.6	333.0	343.0	355.5	370.3	387.4	402.3	423.4	451.2	479.4	501.8
52.5°	304.4	311.2	322.4	335.6	349.4	364.2	380.1	398.2	423.3	449.9	467.7
55°	271.2	279.6	289.1	301.9	315.6	328.0	343.4	362.1	382.0	401.9	413.9
57.5°	240.3	247.2	255.2	268.5	280.4	295.2	309.0	323.5	341.9	357.0	364.8
60°	217.8	223.9	234.3	246.0	257.1	270.0	285.7	300.3	314.4	326.4	332.6
62.5°	196.5	203.7	212.8	223.4	235.6	247.8	261.6	273.7	286.1	296.5	300.8
65°	168.8	174.6	181.3	191.2	201.1	213.6	224.3	236.8	246.0	251.8	255.5
67.5°	143.6	147.4	152.5	159.1	168.9	179.7	190.2	199.9	207.6	211.5	214.8
70°	127.3	129.8	133.6	140.2	147.7	157.2	167.9	175.0	181.6	185.0	188.3
72.5°	111.1	114.2	117.6	122.9	129.0	135.9	143.8	152.5	156.1	160.1	162.1
75°	84.2	88.7	93.3	96.6	100.8	106.2	113.2	118.6	120.7	124.0	124.5
77.5°	63.5	64.6	67.9	72.0	75.5	79.4	83.9	88.6	89.7	91.4	92.5
80°	52.3	52.3	52.3	54.7	58.9	61.8	65.9	68.4	70.1	70.5	70.9
82.5°	42.0	42.0	41.7	42.1	43.6	45.2	49.0	51.8	53.2	52.9	52.0
85°	27.4	26.5	26.5	26.1	26.5	25.7	25.3	26.9	29.5	29.5	28.6
87.5°	14.2	13.8	13.8	13.1	12.4	11.7	10.5	10.5	10.3	11.3	10.8
90°	14.7	14.1	12.4	10.7	9.0	7.3	5.8	4.5	3.2	1.9	0.6
92.5°	23.0	22.6	21.6	20.7	19.6	18.7	17.7	16.9	16.0	15.1	14.3
95°	44.0	43.5	42.5	41.4	40.4	39.3	38.3	37.5	36.5	35.6	34.7
97.5°	68.7	68.1	67.3	66.5	65.8	65.0	64.3	63.7	63.0	62.3	61.6
100°	86.8	86.4	85.8	85.2	84.4	83.8	83.1	82.3	81.5	80.7	79.9
102.5°	107.5	107.1	106.2	105.4	104.6	103.7	103.0	102.5	102.1	101.6	101.2
105°	138.8	138.8	137.6	136.4	135.2	134.0	133.3	133.1	132.8	132.5	132.3
107.5°	171.7	171.3	170.9	170.4	169.9	169.4	169.1	169.0	168.8	168.7	168.5
110°	194.0	193.5	193.2	192.9	192.7	192.4	192.1	191.9	191.6	191.4	191.1



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	216.2	215.6	215.5	215.5	215.4	215.3	215.2	215.1	214.9	214.8	214.6
115°	250.6	250.5	250.7	251.0	251.3	251.5	251.4	251.0	250.6	250.3	249.9
117.5°	285.0	285.0	285.4	285.7	286.1	286.5	286.5	286.2	285.9	285.7	285.4
120°	308.0	308.1	308.8	309.4	310.1	310.7	310.7	309.9	309.1	308.3	307.5
122.5°	331.3	331.6	332.0	332.3	332.6	333.0	332.9	332.3	331.7	331.1	330.6
125°	365.8	366.3	366.5	366.9	367.1	367.3	367.3	366.9	366.5	366.1	365.8
127.5°	399.9	400.7	400.9	401.2	401.6	401.8	401.6	400.7	399.9	399.0	398.2
130°	422.2	422.8	423.2	423.6	424.0	424.4	424.0	422.9	421.9	420.9	419.9
132.5°	444.3	444.9	445.1	445.4	445.8	446.0	445.7	444.6	443.5	442.5	441.5
135°	476.9	477.4	477.6	477.7	477.8	478.0	477.6	476.9	476.1	475.3	474.5
137.5°	509.0	509.5	509.2	508.9	508.5	508.2	507.7	507.1	506.4	505.7	505.1
140°	529.7	529.8	529.7	529.5	529.4	529.3	528.9	528.2	527.6	526.9	526.2
142.5°	549.4	549.5	549.3	549.1	548.8	548.6	548.1	547.5	546.8	546.2	545.6
145°	578.5	578.6	578.2	577.8	577.4	577.0	576.7	576.4	576.2	575.9	575.7
147.5°	605.8	605.8	605.4	605.0	604.7	604.3	603.9	603.4	602.9	602.5	602.0
150°	622.7	622.7	622.4	622.2	621.9	621.6	621.4	621.2	620.8	620.6	620.4
152.5°	637.9	637.7	637.5	637.4	637.2	637.1	636.8	636.5	636.1	635.7	635.4
155°	660.3	659.7	659.6	659.5	659.3	659.2	659.2	659.2	659.2	659.2	659.2
157.5°	679.7	679.1	679.1	678.9	678.8	678.7	678.7	678.9	679.1	679.2	679.4
160°	691.6	690.9	690.9	690.9	690.9	690.9	691.0	691.3	691.6	691.8	692.1
162.5°	702.8	702.2	702.1	702.0	701.9	701.8	701.9	702.3	702.6	703.0	703.4
165°	716.9	716.1	716.1	716.1	716.1	716.1	716.4	716.8	717.2	717.6	718.0
167.5°	728.5	727.7	727.6	727.5	727.4	727.3	727.5	728.0	728.6	729.0	729.6
170°	734.7	733.8	733.8	733.8	733.8	733.8	734.0	734.6	735.1	735.6	736.2
172.5°	739.8	738.9	738.9	738.9	738.9	738.9	739.3	739.7	740.3	740.8	741.3
175°	745.2	744.4	744.4	744.4	744.4	744.4	744.7	745.2	745.7	746.2	746.7
177.5°	747.7	747.1	747.1	747.1	747.1	747.1	747.3	747.7	748.1	748.5	749.0
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	974.1	977.8	982.5	989.4	994.7	999.3	1000.4	1001.7	1005.0	1010.7	1014.9
5°	980.5	990.0	1005.4	1020.3	1036.5	1049.7	1062.2	1070.9	1079.2	1096.6	1110.7
7.5°	978.5	999.7	1023.7	1050.6	1077.7	1104.0	1128.4	1150.2	1171.9	1197.3	1226.2
10°	977.2	1002.0	1034.4	1068.8	1106.5	1143.4	1179.2	1206.9	1239.3	1268.3	1305.2
12.5°	970.8	1006.7	1045.4	1089.4	1135.8	1178.3	1225.3	1263.7	1300.7	1342.6	1385.5
15°	962.7	1006.2	1055.1	1113.6	1184.1	1235.6	1283.7	1350.4	1396.1	1441.7	1503.0
17.5°	947.6	1000.8	1061.9	1137.9	1196.7	1265.8	1338.2	1391.0	1452.5	1516.7	1572.3
20°	935.6	997.4	1065.9	1140.6	1215.6	1290.7	1360.8	1423.8	1487.3	1561.5	1607.2
22.5°	923.8	984.8	1056.0	1135.3	1215.9	1295.0	1374.4	1448.3	1519.8	1594.7	1653.0
25°	898.3	970.9	1048.1	1128.9	1208.6	1295.7	1390.2	1472.7	1561.1	1638.2	1693.4
27.5°	872.6	939.1	1016.0	1098.0	1186.5	1289.4	1400.7	1494.5	1583.0	1638.2	1655.6
30°	849.4	919.9	990.4	1073.8	1169.6	1284.4	1402.6	1510.1	1582.7	1606.7	1588.9
32.5°	825.9	889.7	959.6	1044.9	1146.7	1272.2	1405.3	1500.8	1544.5	1526.1	1453.5
35°	784.3	841.9	909.5	995.0	1111.9	1265.4	1394.4	1459.0	1448.3	1344.6	1207.8
37.5°	739.8	786.8	849.4	938.7	1075.9	1238.4	1347.3	1356.8	1263.5	1104.3	946.2
40°	704.6	746.9	811.3	904.6	1048.1	1211.9	1299.8	1261.2	1116.5	939.4	807.6
42.5°	670.5	706.2	768.1	868.7	1021.5	1175.8	1229.2	1145.1	978.1	810.6	690.7
45°	612.6	646.2	708.4	811.7	967.2	1106.5	1099.5	953.5	786.4	651.6	552.0
47.5°	557.7	587.0	645.4	750.8	903.4	1002.8	936.9	781.6	639.8	531.6	460.7
50°	518.9	547.9	605.9	710.0	852.3	924.9	830.8	681.0	551.2	461.6	405.2
52.5°	481.7	510.1	563.2	664.6	790.6	834.0	732.8	594.1	485.8	408.5	360.0
55°	429.7	451.2	498.9	596.0	690.1	700.1	597.6	481.5	392.4	338.4	305.2
57.5°	376.7	395.2	442.4	519.7	585.7	580.6	483.5	382.9	322.9	282.9	258.8
60°	342.1	360.4	401.9	468.3	518.0	500.6	411.5	330.6	279.1	249.7	230.6
62.5°	310.0	324.2	363.1	411.5	447.3	427.6	351.7	284.8	244.0	219.1	204.1
65°	263.4	275.0	306.1	331.4	351.3	332.2	269.2	222.7	193.3	175.9	165.5
67.5°	219.0	226.5	246.1	255.2	269.3	248.3	202.4	171.3	154.6	139.8	132.6
70°	191.2	196.6	207.0	214.4	218.2	196.6	162.6	139.7	125.6	115.3	110.7
72.5°	163.3	168.0	170.2	176.3	174.4	154.2	130.7	112.6	102.4	95.4	89.5
75°	124.8	126.9	124.8	122.3	116.9	102.8	86.7	77.6	70.1	66.8	64.7
77.5°	91.0	90.3	87.5	83.6	74.4	65.5	56.8	53.8	50.5	48.8	48.0
80°	70.1	68.4	65.9	59.7	51.8	45.6	43.6	41.5	40.2	38.2	37.7
82.5°	52.2	51.2	47.1	41.8	36.3	33.4	31.6	30.9	29.6	28.5	28.4
85°	27.8	26.5	21.9	19.1	18.2	17.4	17.0	17.0	15.4	14.9	14.9
87.5°	9.3	7.6	7.5	6.8	7.1	6.8	7.4	7.1	7.1	7.6	7.1
90°	1.9	3.2	4.5	5.8	7.3	9.0	10.7	12.4	14.1	14.7	15.1
92.5°	15.1	16.0	16.9	17.7	18.7	19.6	20.7	21.6	22.6	23.0	23.4
95°	35.6	36.5	37.5	38.3	39.3	40.4	41.4	42.5	43.5	44.0	44.5
97.5°	62.3	63.0	63.7	64.3	65.0	65.8	66.5	67.3	68.1	68.7	69.3
100°	80.7	81.5	82.3	83.1	83.8	84.4	85.2	85.8	86.4	86.8	87.2
102.5°	101.6	102.1	102.5	103.0	103.7	104.6	105.4	106.2	107.1	107.5	107.9
105°	132.5	132.8	133.1	133.3	134.0	135.2	136.4	137.6	138.8	138.8	138.8
107.5°	168.7	168.8	169.0	169.1	169.4	169.9	170.4	170.9	171.3	171.7	172.1
110°	191.4	191.6	191.9	192.1	192.4	192.7	192.9	193.2	193.5	194.0	194.5





TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	214.8	214.9	215.1	215.2	215.3	215.4	215.5	215.5	215.6	216.2	216.8
115°	250.3	250.6	251.0	251.4	251.5	251.3	251.0	250.7	250.5	250.6	250.7
117.5°	285.7	285.9	286.2	286.5	286.5	286.1	285.7	285.4	285.0	285.0	285.0
120°	308.3	309.1	309.9	310.7	310.7	310.1	309.4	308.8	308.1	308.0	307.8
122.5°	331.1	331.7	332.3	332.9	333.0	332.6	332.3	332.0	331.6	331.3	331.0
125°	366.1	366.5	366.9	367.3	367.3	367.1	366.9	366.5	366.3	365.8	365.3
127.5°	399.0	399.9	400.7	401.6	401.8	401.6	401.2	400.9	400.7	399.9	399.2
130°	420.9	421.9	422.9	424.0	424.4	424.0	423.6	423.2	422.8	422.2	421.8
132.5°	442.5	443.5	444.6	445.7	446.0	445.8	445.4	445.1	444.9	444.3	443.6
135°	475.3	476.1	476.9	477.6	478.0	477.8	477.7	477.6	477.4	476.9	476.4
137.5°	505.7	506.4	507.1	507.7	508.2	508.5	508.9	509.2	509.5	509.0	508.4
140°	526.9	527.6	528.2	528.9	529.3	529.4	529.5	529.7	529.8	529.7	529.5
142.5°	546.2	546.8	547.5	548.1	548.6	548.8	549.1	549.3	549.5	549.4	549.3
145°	575.9	576.2	576.4	576.7	577.0	577.4	577.8	578.2	578.6	578.5	578.3
147.5°	602.5	602.9	603.4	603.9	604.3	604.7	605.0	605.4	605.8	605.8	605.8
150°	620.6	620.8	621.2	621.4	621.6	621.9	622.2	622.4	622.7	622.7	622.7
152.5°	635.7	636.1	636.5	636.8	637.1	637.2	637.4	637.5	637.7	637.9	638.2
155°	659.2	659.2	659.2	659.2	659.2	659.3	659.5	659.6	659.7	660.3	660.8
157.5°	679.2	679.1	678.9	678.7	678.7	678.8	678.9	679.1	679.1	679.7	680.2
160°	691.8	691.6	691.3	691.0	690.9	690.9	690.9	690.9	690.9	691.6	692.2
162.5°	703.0	702.6	702.3	701.9	701.8	701.9	702.0	702.1	702.2	702.8	703.5
165°	717.6	717.2	716.8	716.4	716.1	716.1	716.1	716.1	716.1	716.9	717.7
167.5°	729.0	728.6	728.0	727.5	727.3	727.4	727.5	727.6	727.7	728.5	729.3
170°	735.6	735.1	734.6	734.0	733.8	733.8	733.8	733.8	733.8	734.7	735.6
172.5°	740.8	740.3	739.7	739.3	738.9	738.9	738.9	738.9	738.9	739.8	740.6
175°	746.2	745.7	745.2	744.7	744.4	744.4	744.4	744.4	744.4	745.2	746.0
177.5°	748.5	748.1	747.7	747.3	747.1	747.1	747.1	747.1	747.1	747.7	748.4
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	968.8	968.8	968.8	968.8	968.8	968.8	968.8
2.5°	1021.9	1021.9	1023.3	1028.3	1028.9	1033.2	1031.9
5°	1123.2	1131.0	1133.9	1146.4	1153.8	1157.1	1150.5
7.5°	1246.9	1269.2	1279.7	1292.7	1304.2	1307.7	1298.6
10°	1337.1	1360.3	1379.9	1391.9	1403.1	1410.6	1420.1
12.5°	1424.4	1452.9	1471.5	1488.4	1500.0	1509.4	1511.0
15°	1519.2	1562.3	1595.1	1619.1	1631.2	1637.4	1634.9
17.5°	1614.9	1654.9	1678.2	1702.7	1719.4	1720.2	1720.7
20°	1669.0	1707.9	1734.9	1753.1	1771.8	1771.0	1775.1
22.5°	1705.1	1735.8	1756.4	1769.7	1776.2	1773.0	1773.8
25°	1722.0	1731.2	1727.4	1706.3	1700.9	1681.4	1684.7
27.5°	1634.7	1591.7	1547.0	1489.6	1444.3	1408.2	1410.0
30°	1516.3	1440.0	1352.9	1279.9	1214.4	1196.1	1157.1
32.5°	1350.8	1236.3	1134.2	1066.2	1010.0	994.7	960.8
35°	1070.1	958.9	854.0	790.9	766.0	731.2	730.8
37.5°	831.7	733.9	678.3	631.1	606.3	585.2	583.1
40°	699.7	623.4	581.5	547.5	523.0	507.2	503.5
42.5°	607.4	545.7	506.5	485.4	466.6	458.4	452.4
45°	496.1	454.6	427.2	408.1	399.4	393.2	389.8
47.5°	414.9	387.1	368.4	355.8	348.7	342.1	343.9
50°	370.8	348.0	334.3	322.3	316.9	312.3	312.8
52.5°	335.3	314.8	303.7	295.1	288.4	285.1	283.5
55°	284.6	271.6	260.5	254.2	250.5	246.0	244.7
57.5°	242.7	232.7	223.6	216.6	215.6	211.3	211.8
60°	214.8	206.5	199.1	195.4	192.4	188.7	190.0
62.5°	191.9	185.0	178.2	175.1	172.2	169.4	170.1
65°	157.2	150.5	146.4	144.7	143.5	142.3	141.0
67.5°	125.2	121.2	118.6	115.0	112.5	112.1	110.8
70°	105.4	100.0	95.4	90.9	89.6	89.2	89.6
72.5°	84.4	81.0	79.8	77.6	77.3	76.2	77.0
75°	63.5	62.2	61.4	59.7	59.7	59.7	59.7
77.5°	46.8	46.0	45.6	45.2	44.8	44.2	44.1
80°	36.5	36.0	35.3	35.3	34.9	35.3	34.9
82.5°	27.6	27.5	26.6	26.6	26.2	26.0	26.2
85°	14.1	13.7	14.5	13.7	14.1	13.3	14.1
87.5°	7.1	7.2	7.0	7.1	6.7	7.4	6.8
90°	15.7	16.2	16.6	16.9	17.1	17.3	17.7
92.5°	23.8	24.2	24.4	24.2	24.1	23.9	23.8
95°	45.1	45.6	45.9	45.9	45.9	45.9	45.9
97.5°	69.9	70.5	70.7	70.7	70.7	70.6	70.6
100°	87.6	88.0	88.3	88.6	88.9	89.1	89.4
102.5°	108.3	108.7	108.8	108.8	108.8	108.7	108.7
105°	138.8	138.8	138.9	139.2	139.4	139.7	140.0
107.5°	172.6	173.0	173.2	173.0	172.9	172.7	172.5
110°	195.0	195.5	195.7	195.4	195.1	194.9	194.6



TEST NUMBER: P332435-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	217.5	218.1	218.3	218.3	218.2	218.2	218.2
115°	250.9	251.0	251.0	250.9	250.7	250.6	250.5
117.5°	284.9	284.9	284.8	284.4	284.0	283.7	283.3
120°	307.7	307.6	307.4	307.1	306.9	306.6	306.3
122.5°	330.6	330.3	329.9	329.5	329.2	328.8	328.4
125°	364.7	364.2	363.7	363.2	362.7	362.1	361.6
127.5°	398.5	397.8	397.0	396.5	395.9	395.3	394.7
130°	421.2	420.6	419.9	419.1	418.1	417.2	416.3
132.5°	443.0	442.4	441.7	441.0	440.3	439.6	438.9
135°	475.9	475.4	475.0	474.7	474.4	474.2	473.9
137.5°	507.9	507.4	506.8	506.4	505.8	505.3	504.9
140°	529.4	529.3	528.7	527.8	526.9	526.0	525.1
142.5°	549.1	549.0	548.6	547.9	547.2	546.4	545.7
145°	578.2	578.1	577.7	577.2	576.7	576.2	575.7
147.5°	605.8	605.8	605.4	604.6	603.8	603.0	602.2
150°	622.7	622.7	622.3	621.5	620.8	620.0	619.2
152.5°	638.3	638.6	638.3	637.6	637.0	636.3	635.6
155°	661.3	661.8	661.6	660.7	659.8	658.9	658.0
157.5°	680.8	681.4	681.2	680.5	679.8	679.1	678.3
160°	692.8	693.5	693.6	693.1	692.5	692.0	691.5
162.5°	704.2	704.8	704.7	703.9	703.1	702.2	701.3
165°	718.5	719.3	719.2	718.4	717.4	716.5	715.6
167.5°	730.2	730.9	730.9	730.2	729.3	728.5	727.7
170°	736.6	737.4	737.4	736.6	735.6	734.7	733.8
172.5°	741.4	742.2	742.2	741.2	740.4	739.4	738.6
175°	746.7	747.5	747.5	746.6	745.6	744.7	743.8
177.5°	749.0	749.6	749.6	748.8	748.1	747.3	746.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5

(END OF REPORT)