

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332435

Luminaire Tested: **S123RDIW-S775D755U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332435  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S775D755U835-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5665.8 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	74	71	64	63	61	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	44	40
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	38	35
4	77	66	58	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	46	65	55	48	43	48	43	39	42	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	35	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13164	13164	13164	13164
5°	15692	13220	11642	13220
10°	19593	13144	10518	13144
15°	22998	13010	9591	13010
20°	25668	12810	8804	12810
25°	25258	12598	8320	12598
30°	18155	12403	7822	12403
35°	12122	12150	7499	12150
40°	8931	11844	7165	11844
45°	7491	11309	6838	11309
50°	6611	10608	6382	10608
55°	5797	9805	5758	9805
60°	5162	9040	5274	9040
65°	4534	8214	4908	8214
70°	3559	7481	4482	7481
75°	3136	6534	4092	6534
80°	2727	5548	4023	5548
85°	2198	4458	4273	4458



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	120.3	2.1
10°-20°	375.7	6.6
20°-30°	590.3	10.4
30°-40°	615.9	10.9
40°-50°	527.1	9.3
50°-60°	401.7	7.1
60°-70°	257.5	4.5
70°-80°	123.9	2.2
80°-90°	35.6	0.6
90°-100°	61.6	1.1
100°-110°	184.2	3.3
110°-120°	313.4	5.5
120°-130°	412.2	7.3
130°-140°	463.3	8.2
140°-150°	455.4	8.0
150°-160°	383.4	6.8
160°-170°	255.2	4.5
170°-180°	89.4	1.6
0°-30°	1086.3	19.2
0°-40°	1702.2	30.0
0°-60°	2631.0	46.4
0°-90°	3047.9	53.8
90°-120°	559.2	9.9
90°-150°	1890.0	33.4
90°-180°	2618.0	46.2
0°-180°	5665.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1452	1224	1078	1224	1452	150
15°	2064	1168	861	1168	2064	585
25°	2127	1061	700	1061	2127	914
35°	922	925	571	925	922	605
45°	492	743	449	743	492	387
55°	309	522	307	522	309	279
65°	178	322	193	322	178	175
75°	75	157	98	157	75	81
85°	18	36	35	36	18	21
90°	22	1	22	1	22	11
95°	58	44	58	44	58	59
105°	177	167	177	167	177	187
115°	316	316	316	316	316	313
125°	456	462	456	462	456	408
135°	598	599	598	599	598	460
145°	727	727	727	727	727	454
155°	831	832	831	832	831	382
165°	903	906	903	906	903	255
175°	939	943	939	943	939	89
180°	945	945	945	945	945	



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1302.6	1304.3	1298.8	1298.0	1291.7	1290.0	1290.0	1281.2	1275.8	1268.7	1264.5
5°	1452.3	1460.7	1456.5	1447.1	1431.4	1427.7	1417.8	1402.1	1384.3	1362.3	1351.8
7.5°	1639.3	1650.8	1646.4	1631.8	1615.4	1602.1	1574.0	1547.9	1511.4	1479.3	1451.9
10°	1792.6	1780.6	1771.2	1757.0	1741.9	1717.2	1687.9	1647.6	1601.0	1564.4	1523.5
12.5°	1907.4	1905.4	1893.5	1878.9	1857.5	1834.1	1798.1	1749.0	1694.8	1641.9	1595.2
15°	2063.8	2067.0	2059.1	2043.9	2013.6	1972.2	1917.8	1897.3	1819.9	1762.3	1704.7
17.5°	2172.1	2171.5	2170.4	2149.4	2118.4	2089.0	2038.5	1984.8	1914.6	1833.5	1755.9
20°	2240.8	2235.6	2236.6	2213.0	2190.0	2156.0	2106.8	2028.8	1971.2	1877.5	1797.3
22.5°	2239.1	2238.1	2242.1	2234.0	2217.2	2191.2	2152.4	2086.6	2013.1	1918.5	1828.3
25°	2126.7	2122.5	2147.1	2153.9	2180.6	2185.3	2173.8	2137.7	2068.0	1970.6	1859.1
27.5°	1779.9	1777.6	1823.2	1880.4	1952.8	2009.2	2063.6	2089.9	2068.0	1998.3	1886.6
30°	1460.7	1509.9	1533.0	1615.7	1707.8	1817.8	1914.1	2005.7	2028.2	1997.9	1906.2
32.5°	1212.8	1255.7	1274.9	1345.9	1431.8	1560.6	1705.1	1834.8	1926.5	1949.7	1894.5
35°	922.5	923.0	967.0	998.4	1078.0	1210.4	1350.8	1524.6	1697.3	1828.2	1841.8
37.5°	736.1	738.7	765.3	796.6	856.3	926.4	1049.9	1194.4	1394.0	1594.9	1712.7
40°	635.6	640.3	660.2	691.1	734.0	786.9	883.2	1019.4	1185.8	1409.4	1592.1
42.5°	571.1	578.7	589.0	612.8	639.4	688.9	766.8	871.9	1023.3	1234.7	1445.5
45°	492.1	496.3	504.2	515.2	539.3	573.8	626.2	696.8	822.5	992.7	1203.6
47.5°	434.1	431.9	440.2	449.1	465.1	488.7	523.8	581.5	671.1	807.6	986.6
50°	394.8	394.2	400.0	406.8	422.0	439.3	468.1	511.5	582.7	695.8	859.7
52.5°	357.9	359.9	364.0	372.5	383.4	397.4	423.2	454.5	515.7	613.3	749.9
55°	308.9	310.5	316.2	320.9	328.8	342.9	359.2	385.3	427.2	495.3	607.8
57.5°	267.4	266.7	272.2	273.4	282.3	293.8	306.4	326.7	357.1	407.6	483.4
60°	239.8	238.2	242.9	246.6	251.3	260.7	271.2	291.1	315.2	352.3	417.3
62.5°	214.7	213.9	217.4	221.0	224.9	233.5	242.3	257.6	276.6	308.0	359.5
65°	178.0	179.6	181.1	182.7	184.8	190.0	198.4	208.9	222.0	244.0	281.1
67.5°	139.9	141.5	142.0	145.2	149.7	153.0	158.1	167.4	176.5	195.1	216.2
70°	113.1	112.6	113.1	114.7	120.4	126.2	133.0	139.8	145.5	158.6	176.4
72.5°	97.2	96.2	97.6	97.9	100.7	102.3	106.6	113.0	120.4	129.3	142.1
75°	75.4	75.4	75.4	75.4	77.5	78.5	80.1	81.7	84.3	88.5	97.9
77.5°	55.7	55.8	56.5	57.1	57.5	58.1	59.1	60.6	61.6	63.8	67.9
80°	44.0	44.5	44.0	44.5	44.5	45.5	46.1	47.6	48.2	50.8	52.4
82.5°	33.1	32.8	33.1	33.6	33.6	34.7	34.8	35.9	36.0	37.4	39.0
85°	17.8	16.8	17.8	17.3	18.3	17.3	17.8	18.8	18.8	19.4	21.5
87.5°	8.6	9.4	8.5	8.9	8.8	9.1	9.0	8.9	9.6	9.0	9.0
90°	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1	18.5	17.8	15.7
92.5°	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6	29.0	28.5	27.3
95°	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2	55.6	54.9	53.6
97.5°	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5	86.7	86.0	85.0
100°	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1	109.6	109.1	108.3
102.5°	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2	135.7	135.2	134.1
105°	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2	175.2	175.2	173.7
107.5°	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3	216.8	216.3	215.7
110°	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5	244.9	244.2	243.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7	272.9	272.1	272.0
115°	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5	316.4	316.2	316.5
117.5°	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8	359.8	359.8	360.3
120°	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6	388.8	388.9	389.8
122.5°	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8	418.2	418.6	419.1
125°	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1	461.8	462.4	462.7
127.5°	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9	504.8	505.8	506.1
130°	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4	533.0	533.7	534.2
132.5°	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0	560.8	561.6	561.9
135°	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4	602.0	602.7	602.9
137.5°	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8	642.5	643.2	642.8
140°	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4	668.6	668.8	668.6
142.5°	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4	693.5	693.7	693.4
145°	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0	730.2	730.4	729.9
147.5°	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0	786.0	786.0	785.7
152.5°	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6	805.3	805.0	804.8
155°	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1	833.5	832.8	832.6
157.5°	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7	858.0	857.3	857.2
160°	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8	873.0	872.1	872.1
162.5°	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0	887.2	886.4	886.3
165°	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0	905.0	904.0	904.0
167.5°	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6	919.6	918.6	918.5
170°	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6	927.5	926.3	926.3
172.5°	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9	933.9	932.8	932.8
175°	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7	940.7	939.7	939.7
177.5°	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7	943.9	943.1	943.1
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1262.8	1261.5	1255.7	1249.0	1240.2	1234.3	1229.7	1227.2	1219.7	1210.4	1204.2
5°	1340.8	1325.1	1308.4	1287.9	1269.1	1249.7	1237.7	1223.5	1206.3	1186.9	1173.3
7.5°	1424.4	1393.6	1360.4	1326.2	1292.3	1262.0	1235.2	1212.2	1184.7	1156.9	1137.5
10°	1488.5	1443.4	1396.8	1349.2	1305.7	1264.9	1233.5	1202.6	1169.6	1137.7	1113.6
12.5°	1546.7	1487.4	1433.7	1375.2	1319.6	1270.8	1225.5	1189.2	1149.5	1115.5	1088.0
15°	1620.4	1559.7	1494.7	1405.7	1331.9	1270.1	1215.2	1167.5	1119.4	1077.5	1050.8
17.5°	1689.3	1597.9	1510.7	1436.4	1340.5	1263.3	1196.2	1139.2	1086.4	1042.0	1009.1
20°	1717.8	1629.3	1534.5	1439.8	1345.5	1259.1	1181.1	1118.3	1063.3	1013.1	982.7
22.5°	1734.9	1634.7	1534.9	1433.1	1333.0	1243.2	1166.1	1096.9	1037.4	989.6	952.1
25°	1754.9	1635.6	1525.6	1425.1	1323.0	1225.6	1134.0	1060.7	996.3	945.5	905.7
27.5°	1768.1	1627.7	1497.8	1386.0	1282.5	1185.5	1101.5	1023.9	958.5	904.8	862.1
30°	1770.6	1621.4	1476.4	1355.5	1250.2	1161.2	1072.2	997.9	928.8	871.7	831.9
32.5°	1774.0	1605.9	1447.5	1319.0	1211.3	1123.1	1042.5	971.5	900.7	844.5	803.9
35°	1760.2	1597.4	1403.6	1256.0	1148.1	1062.8	990.0	924.6	855.0	800.5	759.1
37.5°	1700.7	1563.3	1358.2	1185.0	1072.2	993.2	933.9	876.8	813.0	754.2	715.3
40°	1640.8	1529.8	1323.0	1141.9	1024.1	942.9	889.5	842.9	781.1	726.2	684.3
42.5°	1551.6	1484.2	1289.5	1096.6	969.6	891.4	846.4	802.7	748.5	692.7	653.3
45°	1387.9	1396.8	1220.9	1024.6	894.2	815.7	773.3	742.9	694.8	648.7	608.4
47.5°	1182.7	1265.9	1140.4	947.8	814.7	741.0	704.0	677.5	645.0	599.8	563.0
50°	1048.7	1167.5	1075.9	896.3	764.9	691.6	655.0	633.5	605.2	569.6	534.5
52.5°	925.1	1052.8	998.0	838.9	710.9	643.9	608.1	590.4	567.9	534.4	502.7
55°	754.4	883.8	871.2	752.3	629.8	569.6	542.4	522.5	507.3	482.2	457.1
57.5°	610.3	732.9	739.4	656.0	558.4	498.9	475.5	460.5	450.6	431.6	408.4
60°	519.4	631.9	653.9	591.1	507.3	455.0	431.9	419.9	412.0	396.9	379.1
62.5°	444.0	539.8	564.7	519.5	458.3	409.3	391.3	379.7	374.3	361.2	345.5
65°	339.8	419.4	443.4	418.3	386.4	347.1	332.5	322.5	317.8	310.5	298.9
67.5°	255.5	313.5	339.9	322.2	310.7	285.9	276.5	271.2	267.0	262.0	252.4
70°	205.2	248.2	275.4	270.7	261.3	248.2	241.4	237.7	233.5	229.3	220.9
72.5°	165.0	194.6	220.1	222.5	214.8	212.1	206.2	204.6	202.1	197.1	192.5
75°	109.4	129.8	147.6	154.4	157.6	160.2	157.6	157.1	156.5	152.4	149.7
77.5°	71.7	82.7	93.9	105.5	110.5	114.0	114.9	116.8	115.4	113.2	111.9
80°	55.0	57.6	65.4	75.4	83.2	86.4	88.5	89.5	89.0	88.5	86.4
82.5°	39.9	42.1	45.8	52.8	59.4	64.6	65.9	65.7	66.8	67.1	65.4
85°	21.5	22.0	23.0	24.1	27.7	33.5	35.1	36.1	37.2	37.2	34.0
87.5°	9.4	8.6	9.0	8.6	9.5	9.6	11.8	13.6	14.3	13.0	13.3
90°	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7	2.4	4.0	5.7
92.5°	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0	19.1	20.2	21.3
95°	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8	44.9	46.1	47.3
97.5°	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8	78.6	79.5	80.4
100°	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9	101.9	102.9	103.9
102.5°	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7	128.3	128.9	129.4
105°	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0	167.3	167.7	168.0
107.5°	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7	212.9	213.1	213.3
110°	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2	241.6	241.9	242.2





TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9	271.1	271.3	271.5
115°	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5	315.9	316.4	316.9
117.5°	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3	360.6	360.9	361.3
120°	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2	389.2	390.2	391.2
122.5°	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3	418.0	418.7	419.5
125°	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7	462.2	462.7	463.2
127.5°	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6	503.7	504.8	505.8
130°	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0	531.3	532.6	533.9
132.5°	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3	558.6	559.9	561.2
135°	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0	600.0	601.0	602.0
137.5°	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6	638.4	639.2	640.1
140°	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3	665.1	666.0	666.8
142.5°	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7	689.5	690.3	691.1
145°	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7	727.0	727.3	727.6
147.5°	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9	760.5	761.1	761.7
150°	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1	783.4	783.7	784.1
152.5°	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1	802.5	803.0	803.5
155°	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6	857.4	857.2	857.0
160°	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6	873.3	873.0	872.6
162.5°	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9	887.4	886.9	886.5
165°	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3	905.8	905.3	904.8
167.5°	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0	920.3	919.7	919.0
170°	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3	928.6	928.0	927.3
172.5°	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8	935.2	934.5	933.8
175°	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6	942.0	941.3	940.7
177.5°	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5	944.9	944.4	943.9
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1202.1	1196.6	1192.9	1184.5	1179.0	1173.2	1167.3	1171.1	1170.7	1170.2	1170.2
5°	1161.8	1149.7	1138.7	1124.6	1115.7	1104.7	1096.3	1095.3	1097.4	1090.0	1085.8
7.5°	1121.8	1105.3	1089.7	1074.1	1057.6	1044.4	1036.1	1032.2	1026.9	1022.4	1017.7
10°	1093.7	1074.3	1059.1	1039.8	1022.0	1006.3	996.3	989.5	985.8	982.2	975.4
12.5°	1064.8	1045.8	1026.5	1004.6	987.6	969.4	962.0	954.3	947.3	943.2	933.9
15°	1022.5	997.9	977.5	954.4	935.6	917.8	907.3	892.1	890.0	884.8	875.4
17.5°	980.1	953.4	925.2	908.2	886.9	868.4	852.4	847.3	832.3	826.7	818.5
20°	946.6	922.0	900.5	878.0	847.1	829.8	817.3	810.5	798.4	791.1	785.8
22.5°	917.7	892.7	867.8	841.6	816.1	796.7	787.5	776.9	770.4	760.1	754.4
25°	876.4	849.2	819.4	791.1	772.8	758.1	743.4	734.0	724.6	719.9	709.4
27.5°	828.5	800.0	772.1	750.7	728.2	713.7	700.4	692.0	680.7	672.8	667.0
30°	802.1	768.6	744.5	725.1	696.3	682.7	672.8	662.3	653.9	645.5	639.8
32.5°	771.5	740.9	718.1	694.1	672.0	657.2	644.3	635.1	627.9	620.0	614.2
35°	723.5	697.9	674.3	650.2	634.0	618.8	603.7	595.8	589.0	581.7	576.4
37.5°	680.2	656.2	633.8	611.0	590.9	578.5	566.3	560.3	551.1	546.2	540.8
40°	653.4	629.8	605.7	583.8	562.8	553.4	542.4	533.5	525.1	521.5	515.7
42.5°	624.1	600.5	580.2	556.5	539.4	526.6	516.4	506.7	500.4	495.1	491.8
45°	580.6	559.7	539.8	516.2	500.0	489.0	477.5	468.6	462.8	459.2	453.4
47.5°	538.4	517.5	497.3	476.7	461.0	448.5	437.0	430.8	423.1	418.6	414.8
50°	507.8	489.0	467.5	448.7	433.0	420.4	411.0	403.1	396.3	390.6	388.0
52.5°	479.8	459.7	441.1	423.6	407.0	392.8	384.2	375.9	370.8	364.2	361.1
55°	433.5	414.1	398.4	381.1	364.9	352.9	342.4	335.1	329.8	322.5	318.3
57.5°	390.0	372.7	353.9	338.9	322.2	312.0	303.3	293.4	287.0	281.3	277.2
60°	360.7	340.8	324.6	310.5	295.8	282.7	274.9	267.0	260.2	254.4	250.8
62.5°	330.2	312.8	297.4	282.0	268.6	257.2	248.1	241.5	235.5	231.8	228.2
65°	283.2	269.6	253.9	241.4	228.8	220.4	213.1	207.3	203.1	200.5	197.4
67.5°	240.1	226.9	213.2	200.8	192.5	186.1	181.3	176.3	174.2	170.9	168.8
70°	212.0	198.4	186.4	177.0	168.6	163.9	160.7	157.1	155.0	150.8	148.7
72.5°	181.5	171.6	162.9	155.2	148.5	144.2	140.2	135.7	132.4	127.7	125.7
75°	142.9	134.0	127.2	122.0	117.8	112.0	106.3	101.6	100.0	98.4	97.9
77.5°	105.9	100.2	95.3	90.9	85.7	81.5	80.2	79.2	78.8	78.0	78.0
80°	83.2	78.0	74.3	69.1	66.0	66.0	66.0	64.9	65.4	65.4	65.4
82.5°	61.9	57.1	55.1	53.2	52.6	53.0	53.0	53.2	52.9	53.7	53.3
85°	31.9	32.5	33.5	33.0	33.5	33.5	34.6	34.0	34.6	33.5	34.6
87.5°	13.2	14.8	15.7	16.5	17.4	17.4	17.9	18.1	18.6	18.7	18.8
90°	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1	19.8	20.5	20.9
92.5°	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6	30.1	30.6	30.8
95°	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2	56.9	57.6	57.9
97.5°	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5	88.2	89.0	89.3
100°	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1	110.6	111.1	111.5
102.5°	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2	136.7	137.2	137.4
105°	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2	175.2	175.2	175.3
107.5°	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3	217.9	218.4	218.6
110°	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5	246.2	246.8	247.0



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7	274.5	275.3	275.6
115°	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5	316.7	316.9	316.9
117.5°	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8	359.7	359.7	359.5
120°	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6	388.4	388.3	388.0
122.5°	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8	417.3	416.9	416.5
125°	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1	460.4	459.8	459.1
127.5°	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9	503.0	502.1	501.2
130°	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4	531.7	531.0	530.1
132.5°	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0	559.2	558.4	557.6
135°	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4	600.7	600.1	599.6
137.5°	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8	641.1	640.5	639.8
140°	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4	668.3	668.1	667.4
142.5°	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4	693.2	693.0	692.5
145°	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0	729.9	729.7	729.3
147.5°	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7	764.7	764.7	764.2
150°	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0	786.0	786.0	785.5
152.5°	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6	805.8	806.1	805.8
155°	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1	834.8	835.4	835.2
157.5°	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7	859.4	860.1	859.9
160°	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8	874.6	875.4	875.5
162.5°	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0	888.9	889.7	889.6
165°	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0	907.0	908.0	907.9
167.5°	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6	921.7	922.7	922.7
170°	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6	929.8	930.9	930.9
172.5°	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9	935.9	936.9	936.9
175°	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7	942.6	943.6	943.6
177.5°	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7	945.5	946.3	946.2
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1165.2	1164.8	1165.2	1163.5	1165.2	1164.8	1165.2	1170.2	1170.2	1170.7	1171.1
5°	1084.3	1083.7	1082.2	1077.5	1082.2	1083.7	1084.3	1085.8	1090.0	1097.4	1095.3
7.5°	1013.6	1012.9	1008.3	1008.4	1008.3	1012.9	1013.6	1017.7	1022.4	1026.9	1032.2
10°	971.7	972.2	966.0	962.3	966.0	972.2	971.7	975.4	982.2	985.8	989.5
12.5°	931.1	928.7	923.6	919.6	923.6	928.7	931.1	933.9	943.2	947.3	954.3
15°	877.5	872.2	859.7	860.7	859.7	872.2	877.5	875.4	884.8	890.0	892.1
17.5°	814.3	810.5	810.2	802.9	810.2	810.5	814.3	818.5	826.7	832.3	847.3
20°	777.5	774.9	775.9	768.6	775.9	774.9	777.5	785.8	791.1	798.4	810.5
22.5°	748.6	746.0	741.6	739.3	741.6	746.0	748.6	754.4	760.1	770.4	776.9
25°	706.3	702.1	697.9	700.5	697.9	702.1	706.3	709.4	719.9	724.6	734.0
27.5°	664.0	660.8	656.6	656.1	656.6	660.8	664.0	667.0	672.8	680.7	692.0
30°	637.2	634.0	631.9	629.3	631.9	634.0	637.2	639.8	645.5	653.9	662.3
32.5°	609.9	609.3	605.5	605.0	605.5	609.3	609.9	614.2	620.0	627.9	635.1
35°	574.3	571.2	570.1	570.7	570.1	571.2	574.3	576.4	581.7	589.0	595.8
37.5°	540.5	536.3	534.4	532.6	534.4	536.3	540.5	540.8	546.2	551.1	560.3
40°	516.2	512.0	511.0	509.9	511.0	512.0	516.2	515.7	521.5	525.1	533.5
42.5°	489.0	487.3	486.7	484.8	486.7	487.3	489.0	491.8	495.1	500.4	506.7
45°	451.8	451.3	448.2	449.2	448.2	451.3	451.8	453.4	459.2	462.8	468.6
47.5°	412.7	410.4	408.2	409.6	408.2	410.4	412.7	414.8	418.6	423.1	430.8
50°	385.9	384.8	380.1	381.1	380.1	384.8	385.9	388.0	390.6	396.3	403.1
52.5°	359.1	355.1	353.3	352.7	353.3	355.1	359.1	361.1	364.2	370.8	375.9
55°	314.7	309.9	307.8	306.8	307.8	309.9	314.7	318.3	322.5	329.8	335.1
57.5°	271.1	269.8	268.2	269.3	268.2	269.8	271.1	277.2	281.3	287.0	293.4
60°	245.5	245.5	245.5	245.0	245.5	245.5	245.5	250.8	254.4	260.2	267.0
62.5°	225.9	224.6	224.2	224.9	224.2	224.6	225.9	228.2	231.8	235.5	241.5
65°	195.8	195.3	193.2	192.7	193.2	195.3	195.8	197.4	200.5	203.1	207.3
67.5°	167.4	165.5	164.9	164.2	164.9	165.5	167.4	168.8	170.9	174.2	176.3
70°	146.1	145.0	141.9	142.4	141.9	145.0	146.1	148.7	150.8	155.0	157.1
72.5°	123.0	122.0	121.4	120.6	121.4	122.0	123.0	125.7	127.7	132.4	135.7
75°	97.4	96.9	96.3	98.4	96.3	96.9	97.4	97.9	98.4	100.0	101.6
77.5°	78.0	78.0	78.3	77.5	78.3	78.0	78.0	78.0	78.0	78.8	79.2
80°	65.4	65.4	64.9	64.9	64.9	65.4	65.4	65.4	65.4	65.4	64.9
82.5°	52.5	52.9	53.2	52.4	53.2	52.9	52.5	53.3	53.7	52.9	53.2
85°	34.6	34.0	35.1	34.6	35.1	34.0	34.6	34.6	33.5	34.6	34.0
87.5°	19.8	19.0	19.0	19.5	19.0	19.0	19.8	18.8	18.7	18.6	18.1
90°	21.3	21.6	21.9	22.3	21.9	21.6	21.3	20.9	20.5	19.8	19.1
92.5°	30.6	30.4	30.2	30.0	30.2	30.4	30.6	30.8	30.6	30.1	29.6
95°	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.9	57.6	56.9	56.2
97.5°	89.3	89.2	89.1	89.1	89.1	89.2	89.3	89.3	89.0	88.2	87.5
100°	111.8	112.2	112.5	112.8	112.5	112.2	111.8	111.5	111.1	110.6	110.1
102.5°	137.4	137.3	137.2	137.2	137.2	137.3	137.4	137.4	137.2	136.7	136.2
105°	175.7	176.0	176.3	176.7	176.3	176.0	175.7	175.3	175.2	175.2	175.2
107.5°	218.4	218.2	218.0	217.8	218.0	218.2	218.4	218.6	218.4	217.9	217.3
110°	246.7	246.3	246.0	245.7	246.0	246.3	246.7	247.0	246.8	246.2	245.5



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	275.6	275.5	275.4	275.4	275.4	275.5	275.6	275.6	275.3	274.5	273.7
115°	316.7	316.5	316.4	316.2	316.4	316.5	316.7	316.9	316.9	316.7	316.5
117.5°	359.0	358.5	358.1	357.6	358.1	358.5	359.0	359.5	359.7	359.7	359.8
120°	387.7	387.4	387.0	386.7	387.0	387.4	387.7	388.0	388.3	388.4	388.6
122.5°	416.0	415.5	415.1	414.6	415.1	415.5	416.0	416.5	416.9	417.3	417.8
125°	458.5	457.8	457.1	456.5	457.1	457.8	458.5	459.1	459.8	460.4	461.1
127.5°	500.5	499.7	499.0	498.2	499.0	499.7	500.5	501.2	502.1	503.0	503.9
130°	529.0	527.8	526.7	525.5	526.7	527.8	529.0	530.1	531.0	531.7	532.4
132.5°	556.7	555.8	554.9	554.0	554.9	555.8	556.7	557.6	558.4	559.2	560.0
135°	599.2	598.9	598.6	598.2	598.6	598.9	599.2	599.6	600.1	600.7	601.4
137.5°	639.2	638.5	637.9	637.3	637.9	638.5	639.2	639.8	640.5	641.1	641.8
140°	666.3	665.1	664.0	662.8	664.0	665.1	666.3	667.4	668.1	668.3	668.4
142.5°	691.6	690.7	689.8	688.9	689.8	690.7	691.6	692.5	693.0	693.2	693.4
145°	728.6	728.0	727.3	726.7	727.3	728.0	728.6	729.3	729.7	729.9	730.0
147.5°	763.2	762.2	761.2	760.2	761.2	762.2	763.2	764.2	764.7	764.7	764.7
150°	784.5	783.6	782.6	781.6	782.6	783.6	784.5	785.5	786.0	786.0	786.0
152.5°	804.9	804.1	803.2	802.4	803.2	804.1	804.9	805.8	806.1	805.8	805.6
155°	834.0	832.9	831.7	830.6	831.7	832.9	834.0	835.2	835.4	834.8	834.1
157.5°	859.0	858.1	857.2	856.2	857.2	858.1	859.0	859.9	860.1	859.4	858.7
160°	874.9	874.2	873.5	872.9	873.5	874.2	874.9	875.5	875.4	874.6	873.8
162.5°	888.5	887.5	886.4	885.3	886.4	887.5	888.5	889.6	889.7	888.9	888.0
165°	906.8	905.6	904.5	903.3	904.5	905.6	906.8	907.9	908.0	907.0	906.0
167.5°	921.7	920.6	919.6	918.6	919.6	920.6	921.7	922.7	922.7	921.7	920.6
170°	929.8	928.6	927.5	926.3	927.5	928.6	929.8	930.9	930.9	929.8	928.6
172.5°	935.7	934.6	933.4	932.3	933.4	934.6	935.7	936.9	936.9	935.9	934.9
175°	942.4	941.2	940.1	938.9	940.1	941.2	942.4	943.6	943.6	942.6	941.7
177.5°	945.3	944.3	943.4	942.5	943.4	944.3	945.3	946.2	946.3	945.5	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1167.3	1173.2	1179.0	1184.5	1192.9	1196.6	1202.1	1204.2	1210.4	1219.7	1227.2
5°	1096.3	1104.7	1115.7	1124.6	1138.7	1149.7	1161.8	1173.3	1186.9	1206.3	1223.5
7.5°	1036.1	1044.4	1057.6	1074.1	1089.7	1105.3	1121.8	1137.5	1156.9	1184.7	1212.2
10°	996.3	1006.3	1022.0	1039.8	1059.1	1074.3	1093.7	1113.6	1137.7	1169.6	1202.6
12.5°	962.0	969.4	987.6	1004.6	1026.5	1045.8	1064.8	1088.0	1115.5	1149.5	1189.2
15°	907.3	917.8	935.6	954.4	977.5	997.9	1022.5	1050.8	1077.5	1119.4	1167.5
17.5°	852.4	868.4	886.9	908.2	925.2	953.4	980.1	1009.1	1042.0	1086.4	1139.2
20°	817.3	829.8	847.1	878.0	900.5	922.0	946.6	982.7	1013.1	1063.3	1118.3
22.5°	787.5	796.7	816.1	841.6	867.8	892.7	917.7	952.1	989.6	1037.4	1096.9
25°	743.4	758.1	772.8	791.1	819.4	849.2	876.4	905.7	945.5	996.3	1060.7
27.5°	700.4	713.7	728.2	750.7	772.1	800.0	828.5	862.1	904.8	958.5	1023.9
30°	672.8	682.7	696.3	725.1	744.5	768.6	802.1	831.9	871.7	928.8	997.9
32.5°	644.3	657.2	672.0	694.1	718.1	740.9	771.5	803.9	844.5	900.7	971.5
35°	603.7	618.8	634.0	650.2	674.3	697.9	723.5	759.1	800.5	855.0	924.6
37.5°	566.3	578.5	590.9	611.0	633.8	656.2	680.2	715.3	754.2	813.0	876.8
40°	542.4	553.4	562.8	583.8	605.7	629.8	653.4	684.3	726.2	781.1	842.9
42.5°	516.4	526.6	539.4	556.5	580.2	600.5	624.1	653.3	692.7	748.5	802.7
45°	477.5	489.0	500.0	516.2	539.8	559.7	580.6	608.4	648.7	694.8	742.9
47.5°	437.0	448.5	461.0	476.7	497.3	517.5	538.4	563.0	599.8	645.0	677.5
50°	411.0	420.4	433.0	448.7	467.5	489.0	507.8	534.5	569.6	605.2	633.5
52.5°	384.2	392.8	407.0	423.6	441.1	459.7	479.8	502.7	534.4	567.9	590.4
55°	342.4	352.9	364.9	381.1	398.4	414.1	433.5	457.1	482.2	507.3	522.5
57.5°	303.3	312.0	322.2	338.9	353.9	372.7	390.0	408.4	431.6	450.6	460.5
60°	274.9	282.7	295.8	310.5	324.6	340.8	360.7	379.1	396.9	412.0	419.9
62.5°	248.1	257.2	268.6	282.0	297.4	312.8	330.2	345.5	361.2	374.3	379.7
65°	213.1	220.4	228.8	241.4	253.9	269.6	283.2	298.9	310.5	317.8	322.5
67.5°	181.3	186.1	192.5	200.8	213.2	226.9	240.1	252.4	262.0	267.0	271.2
70°	160.7	163.9	168.6	177.0	186.4	198.4	212.0	220.9	229.3	233.5	237.7
72.5°	140.2	144.2	148.5	155.2	162.9	171.6	181.5	192.5	197.1	202.1	204.6
75°	106.3	112.0	117.8	122.0	127.2	134.0	142.9	149.7	152.4	156.5	157.1
77.5°	80.2	81.5	85.7	90.9	95.3	100.2	105.9	111.9	113.2	115.4	116.8
80°	66.0	66.0	66.0	69.1	74.3	78.0	83.2	86.4	88.5	89.0	89.5
82.5°	53.0	53.0	52.6	53.2	55.1	57.1	61.9	65.4	67.1	66.8	65.7
85°	34.6	33.5	33.5	33.0	33.5	32.5	31.9	34.0	37.2	37.2	36.1
87.5°	17.9	17.4	17.4	16.5	15.7	14.8	13.2	13.3	13.0	14.3	13.6
90°	18.5	17.8	15.7	13.5	11.4	9.2	7.3	5.7	4.0	2.4	0.7
92.5°	29.0	28.5	27.3	26.1	24.8	23.6	22.4	21.3	20.2	19.1	18.0
95°	55.6	54.9	53.6	52.3	51.0	49.6	48.4	47.3	46.1	44.9	43.8
97.5°	86.7	86.0	85.0	84.0	83.1	82.1	81.2	80.4	79.5	78.6	77.8
100°	109.6	109.1	108.3	107.5	106.6	105.8	104.9	103.9	102.9	101.9	100.9
102.5°	135.7	135.2	134.1	133.1	132.0	130.9	130.0	129.4	128.9	128.3	127.7
105°	175.2	175.2	173.7	172.2	170.7	169.2	168.3	168.0	167.7	167.3	167.0
107.5°	216.8	216.3	215.7	215.1	214.5	213.9	213.5	213.3	213.1	212.9	212.7
110°	244.9	244.2	243.9	243.5	243.2	242.9	242.5	242.2	241.9	241.6	241.2



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.9	272.1	272.0	272.0	271.9	271.8	271.7	271.5	271.3	271.1	270.9
115°	316.4	316.2	316.5	316.9	317.2	317.5	317.4	316.9	316.4	315.9	315.5
117.5°	359.8	359.8	360.3	360.7	361.1	361.6	361.6	361.3	360.9	360.6	360.3
120°	388.8	388.9	389.8	390.6	391.4	392.2	392.2	391.2	390.2	389.2	388.2
122.5°	418.2	418.6	419.1	419.5	419.9	420.3	420.2	419.5	418.7	418.0	417.3
125°	461.8	462.4	462.7	463.1	463.4	463.7	463.7	463.2	462.7	462.2	461.7
127.5°	504.8	505.8	506.1	506.5	506.9	507.2	506.9	505.8	504.8	503.7	502.6
130°	533.0	533.7	534.2	534.7	535.2	535.7	535.2	533.9	532.6	531.3	530.0
132.5°	560.8	561.6	561.9	562.3	562.7	563.0	562.6	561.2	559.9	558.6	557.3
135°	602.0	602.7	602.9	603.0	603.2	603.4	602.9	602.0	601.0	600.0	599.0
137.5°	642.5	643.2	642.8	642.4	641.9	641.5	640.9	640.1	639.2	638.4	637.6
140°	668.6	668.8	668.6	668.4	668.3	668.1	667.6	666.8	666.0	665.1	664.3
142.5°	693.5	693.7	693.4	693.1	692.8	692.5	691.9	691.1	690.3	689.5	688.7
145°	730.2	730.4	729.9	729.4	728.9	728.4	728.0	727.6	727.3	727.0	726.7
147.5°	764.7	764.7	764.2	763.7	763.3	762.8	762.3	761.7	761.1	760.5	759.9
150°	786.0	786.0	785.7	785.4	785.0	784.7	784.4	784.1	783.7	783.4	783.1
152.5°	805.3	805.0	804.8	804.6	804.4	804.2	803.9	803.5	803.0	802.5	802.1
155°	833.5	832.8	832.6	832.5	832.3	832.1	832.1	832.1	832.1	832.1	832.1
157.5°	858.0	857.3	857.2	857.0	856.9	856.8	856.8	857.0	857.2	857.4	857.6
160°	873.0	872.1	872.1	872.1	872.1	872.1	872.3	872.6	873.0	873.3	873.6
162.5°	887.2	886.4	886.3	886.1	886.0	885.9	886.0	886.5	886.9	887.4	887.9
165°	905.0	904.0	904.0	904.0	904.0	904.0	904.3	904.8	905.3	905.8	906.3
167.5°	919.6	918.6	918.5	918.3	918.2	918.1	918.3	919.0	919.7	920.3	921.0
170°	927.5	926.3	926.3	926.3	926.3	926.3	926.6	927.3	928.0	928.6	929.3
172.5°	933.9	932.8	932.8	932.8	932.8	932.8	933.2	933.8	934.5	935.2	935.8
175°	940.7	939.7	939.7	939.7	939.7	939.7	940.0	940.7	941.3	942.0	942.6
177.5°	943.9	943.1	943.1	943.1	943.1	943.1	943.4	943.9	944.4	944.9	945.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1229.7	1234.3	1240.2	1249.0	1255.7	1261.5	1262.8	1264.5	1268.7	1275.8	1281.2
5°	1237.7	1249.7	1269.1	1287.9	1308.4	1325.1	1340.8	1351.8	1362.3	1384.3	1402.1
7.5°	1235.2	1262.0	1292.3	1326.2	1360.4	1393.6	1424.4	1451.9	1479.3	1511.4	1547.9
10°	1233.5	1264.9	1305.7	1349.2	1396.8	1443.4	1488.5	1523.5	1564.4	1601.0	1647.6
12.5°	1225.5	1270.8	1319.6	1375.2	1433.7	1487.4	1546.7	1595.2	1641.9	1694.8	1749.0
15°	1215.2	1270.1	1331.9	1405.7	1494.7	1559.7	1620.4	1704.7	1762.3	1819.9	1897.3
17.5°	1196.2	1263.3	1340.5	1436.4	1510.7	1597.9	1689.3	1755.9	1833.5	1914.6	1984.8
20°	1181.1	1259.1	1345.5	1439.8	1534.5	1629.3	1717.8	1797.3	1877.5	1971.2	2028.8
22.5°	1166.1	1243.2	1333.0	1433.1	1534.9	1634.7	1734.9	1828.3	1918.5	2013.1	2086.6
25°	1134.0	1225.6	1323.0	1425.1	1525.6	1635.6	1754.9	1859.1	1970.6	2068.0	2137.7
27.5°	1101.5	1185.5	1282.5	1386.0	1497.8	1627.7	1768.1	1886.6	1998.3	2068.0	2089.9
30°	1072.2	1161.2	1250.2	1355.5	1476.4	1621.4	1770.6	1906.2	1997.9	2028.2	2005.7
32.5°	1042.5	1123.1	1211.3	1319.0	1447.5	1605.9	1774.0	1894.5	1949.7	1926.5	1834.8
35°	990.0	1062.8	1148.1	1256.0	1403.6	1597.4	1760.2	1841.8	1828.2	1697.3	1524.6
37.5°	933.9	993.2	1072.2	1185.0	1358.2	1563.3	1700.7	1712.7	1594.9	1394.0	1194.4
40°	889.5	942.9	1024.1	1141.9	1323.0	1529.8	1640.8	1592.1	1409.4	1185.8	1019.4
42.5°	846.4	891.4	969.6	1096.6	1289.5	1484.2	1551.6	1445.5	1234.7	1023.3	871.9
45°	773.3	815.7	894.2	1024.6	1220.9	1396.8	1387.9	1203.6	992.7	822.5	696.8
47.5°	704.0	741.0	814.7	947.8	1140.4	1265.9	1182.7	986.6	807.6	671.1	581.5
50°	655.0	691.6	764.9	896.3	1075.9	1167.5	1048.7	859.7	695.8	582.7	511.5
52.5°	608.1	643.9	710.9	838.9	998.0	1052.8	925.1	749.9	613.3	515.7	454.5
55°	542.4	569.6	629.8	752.3	871.2	883.8	754.4	607.8	495.3	427.2	385.3
57.5°	475.5	498.9	558.4	656.0	739.4	732.9	610.3	483.4	407.6	357.1	326.7
60°	431.9	455.0	507.3	591.1	653.9	631.9	519.4	417.3	352.3	315.2	291.1
62.5°	391.3	409.3	458.3	519.5	564.7	539.8	444.0	359.5	308.0	276.6	257.6
65°	332.5	347.1	386.4	418.3	443.4	419.4	339.8	281.1	244.0	222.0	208.9
67.5°	276.5	285.9	310.7	322.2	339.9	313.5	255.5	216.2	195.1	176.5	167.4
70°	241.4	248.2	261.3	270.7	275.4	248.2	205.2	176.4	158.6	145.5	139.8
72.5°	206.2	212.1	214.8	222.5	220.1	194.6	165.0	142.1	129.3	120.4	113.0
75°	157.6	160.2	157.6	154.4	147.6	129.8	109.4	97.9	88.5	84.3	81.7
77.5°	114.9	114.0	110.5	105.5	93.9	82.7	71.7	67.9	63.8	61.6	60.6
80°	88.5	86.4	83.2	75.4	65.4	57.6	55.0	52.4	50.8	48.2	47.6
82.5°	65.9	64.6	59.4	52.8	45.8	42.1	39.9	39.0	37.4	36.0	35.9
85°	35.1	33.5	27.7	24.1	23.0	22.0	21.5	21.5	19.4	18.8	18.8
87.5°	11.8	9.6	9.5	8.6	9.0	8.6	9.4	9.0	9.0	9.6	8.9
90°	2.4	4.0	5.7	7.3	9.2	11.4	13.5	15.7	17.8	18.5	19.1
92.5°	19.1	20.2	21.3	22.4	23.6	24.8	26.1	27.3	28.5	29.0	29.6
95°	44.9	46.1	47.3	48.4	49.6	51.0	52.3	53.6	54.9	55.6	56.2
97.5°	78.6	79.5	80.4	81.2	82.1	83.1	84.0	85.0	86.0	86.7	87.5
100°	101.9	102.9	103.9	104.9	105.8	106.6	107.5	108.3	109.1	109.6	110.1
102.5°	128.3	128.9	129.4	130.0	130.9	132.0	133.1	134.1	135.2	135.7	136.2
105°	167.3	167.7	168.0	168.3	169.2	170.7	172.2	173.7	175.2	175.2	175.2
107.5°	212.9	213.1	213.3	213.5	213.9	214.5	215.1	215.7	216.3	216.8	217.3
110°	241.6	241.9	242.2	242.5	242.9	243.2	243.5	243.9	244.2	244.9	245.5





TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	271.1	271.3	271.5	271.7	271.8	271.9	272.0	272.0	272.1	272.9	273.7
115°	315.9	316.4	316.9	317.4	317.5	317.2	316.9	316.5	316.2	316.4	316.5
117.5°	360.6	360.9	361.3	361.6	361.6	361.1	360.7	360.3	359.8	359.8	359.8
120°	389.2	390.2	391.2	392.2	392.2	391.4	390.6	389.8	388.9	388.8	388.6
122.5°	418.0	418.7	419.5	420.2	420.3	419.9	419.5	419.1	418.6	418.2	417.8
125°	462.2	462.7	463.2	463.7	463.7	463.4	463.1	462.7	462.4	461.8	461.1
127.5°	503.7	504.8	505.8	506.9	507.2	506.9	506.5	506.1	505.8	504.8	503.9
130°	531.3	532.6	533.9	535.2	535.7	535.2	534.7	534.2	533.7	533.0	532.4
132.5°	558.6	559.9	561.2	562.6	563.0	562.7	562.3	561.9	561.6	560.8	560.0
135°	600.0	601.0	602.0	602.9	603.4	603.2	603.0	602.9	602.7	602.0	601.4
137.5°	638.4	639.2	640.1	640.9	641.5	641.9	642.4	642.8	643.2	642.5	641.8
140°	665.1	666.0	666.8	667.6	668.1	668.3	668.4	668.6	668.8	668.6	668.4
142.5°	689.5	690.3	691.1	691.9	692.5	692.8	693.1	693.4	693.7	693.5	693.4
145°	727.0	727.3	727.6	728.0	728.4	728.9	729.4	729.9	730.4	730.2	730.0
147.5°	760.5	761.1	761.7	762.3	762.8	763.3	763.7	764.2	764.7	764.7	764.7
150°	783.4	783.7	784.1	784.4	784.7	785.0	785.4	785.7	786.0	786.0	786.0
152.5°	802.5	803.0	803.5	803.9	804.2	804.4	804.6	804.8	805.0	805.3	805.6
155°	832.1	832.1	832.1	832.1	832.1	832.3	832.5	832.6	832.8	833.5	834.1
157.5°	857.4	857.2	857.0	856.8	856.8	856.9	857.0	857.2	857.3	858.0	858.7
160°	873.3	873.0	872.6	872.3	872.1	872.1	872.1	872.1	872.1	873.0	873.8
162.5°	887.4	886.9	886.5	886.0	885.9	886.0	886.1	886.3	886.4	887.2	888.0
165°	905.8	905.3	904.8	904.3	904.0	904.0	904.0	904.0	904.0	905.0	906.0
167.5°	920.3	919.7	919.0	918.3	918.1	918.2	918.3	918.5	918.6	919.6	920.6
170°	928.6	928.0	927.3	926.6	926.3	926.3	926.3	926.3	926.3	927.5	928.6
172.5°	935.2	934.5	933.8	933.2	932.8	932.8	932.8	932.8	932.8	933.9	934.9
175°	942.0	941.3	940.7	940.0	939.7	939.7	939.7	939.7	939.7	940.7	941.7
177.5°	944.9	944.4	943.9	943.4	943.1	943.1	943.1	943.1	943.1	943.9	944.7
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0	1223.0
2.5°	1290.0	1290.0	1291.7	1298.0	1298.8	1304.3	1302.6
5°	1417.8	1427.7	1431.4	1447.1	1456.5	1460.7	1452.3
7.5°	1574.0	1602.1	1615.4	1631.8	1646.4	1650.8	1639.3
10°	1687.9	1717.2	1741.9	1757.0	1771.2	1780.6	1792.6
12.5°	1798.1	1834.1	1857.5	1878.9	1893.5	1905.4	1907.4
15°	1917.8	1972.2	2013.6	2043.9	2059.1	2067.0	2063.8
17.5°	2038.5	2089.0	2118.4	2149.4	2170.4	2171.5	2172.1
20°	2106.8	2156.0	2190.0	2213.0	2236.6	2235.6	2240.8
22.5°	2152.4	2191.2	2217.2	2234.0	2242.1	2238.1	2239.1
25°	2173.8	2185.3	2180.6	2153.9	2147.1	2122.5	2126.7
27.5°	2063.6	2009.2	1952.8	1880.4	1823.2	1777.6	1779.9
30°	1914.1	1817.8	1707.8	1615.7	1533.0	1509.9	1460.7
32.5°	1705.1	1560.6	1431.8	1345.9	1274.9	1255.7	1212.8
35°	1350.8	1210.4	1078.0	998.4	967.0	923.0	922.5
37.5°	1049.9	926.4	856.3	796.6	765.3	738.7	736.1
40°	883.2	786.9	734.0	691.1	660.2	640.3	635.6
42.5°	766.8	688.9	639.4	612.8	589.0	578.7	571.1
45°	626.2	573.8	539.3	515.2	504.2	496.3	492.1
47.5°	523.8	488.7	465.1	449.1	440.2	431.9	434.1
50°	468.1	439.3	422.0	406.8	400.0	394.2	394.8
52.5°	423.2	397.4	383.4	372.5	364.0	359.9	357.9
55°	359.2	342.9	328.8	320.9	316.2	310.5	308.9
57.5°	306.4	293.8	282.3	273.4	272.2	266.7	267.4
60°	271.2	260.7	251.3	246.6	242.9	238.2	239.8
62.5°	242.3	233.5	224.9	221.0	217.4	213.9	214.7
65°	198.4	190.0	184.8	182.7	181.1	179.6	178.0
67.5°	158.1	153.0	149.7	145.2	142.0	141.5	139.9
70°	133.0	126.2	120.4	114.7	113.1	112.6	113.1
72.5°	106.6	102.3	100.7	97.9	97.6	96.2	97.2
75°	80.1	78.5	77.5	75.4	75.4	75.4	75.4
77.5°	59.1	58.1	57.5	57.1	56.5	55.8	55.7
80°	46.1	45.5	44.5	44.5	44.0	44.5	44.0
82.5°	34.8	34.7	33.6	33.6	33.1	32.8	33.1
85°	17.8	17.3	18.3	17.3	17.8	16.8	17.8
87.5°	9.0	9.1	8.8	8.9	8.5	9.4	8.6
90°	19.8	20.5	20.9	21.3	21.6	21.9	22.3
92.5°	30.1	30.6	30.8	30.6	30.4	30.2	30.0
95°	56.9	57.6	57.9	57.9	57.9	57.9	57.9
97.5°	88.2	89.0	89.3	89.3	89.2	89.1	89.1
100°	110.6	111.1	111.5	111.8	112.2	112.5	112.8
102.5°	136.7	137.2	137.4	137.4	137.3	137.2	137.2
105°	175.2	175.2	175.3	175.7	176.0	176.3	176.7
107.5°	217.9	218.4	218.6	218.4	218.2	218.0	217.8
110°	246.2	246.8	247.0	246.7	246.3	246.0	245.7



TEST NUMBER: P332435

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	274.5	275.3	275.6	275.6	275.5	275.4	275.4
115°	316.7	316.9	316.9	316.7	316.5	316.4	316.2
117.5°	359.7	359.7	359.5	359.0	358.5	358.1	357.6
120°	388.4	388.3	388.0	387.7	387.4	387.0	386.7
122.5°	417.3	416.9	416.5	416.0	415.5	415.1	414.6
125°	460.4	459.8	459.1	458.5	457.8	457.1	456.5
127.5°	503.0	502.1	501.2	500.5	499.7	499.0	498.2
130°	531.7	531.0	530.1	529.0	527.8	526.7	525.5
132.5°	559.2	558.4	557.6	556.7	555.8	554.9	554.0
135°	600.7	600.1	599.6	599.2	598.9	598.6	598.2
137.5°	641.1	640.5	639.8	639.2	638.5	637.9	637.3
140°	668.3	668.1	667.4	666.3	665.1	664.0	662.8
142.5°	693.2	693.0	692.5	691.6	690.7	689.8	688.9
145°	729.9	729.7	729.3	728.6	728.0	727.3	726.7
147.5°	764.7	764.7	764.2	763.2	762.2	761.2	760.2
150°	786.0	786.0	785.5	784.5	783.6	782.6	781.6
152.5°	805.8	806.1	805.8	804.9	804.1	803.2	802.4
155°	834.8	835.4	835.2	834.0	832.9	831.7	830.6
157.5°	859.4	860.1	859.9	859.0	858.1	857.2	856.2
160°	874.6	875.4	875.5	874.9	874.2	873.5	872.9
162.5°	888.9	889.7	889.6	888.5	887.5	886.4	885.3
165°	907.0	908.0	907.9	906.8	905.6	904.5	903.3
167.5°	921.7	922.7	922.7	921.7	920.6	919.6	918.6
170°	929.8	930.9	930.9	929.8	928.6	927.5	926.3
172.5°	935.9	936.9	936.9	935.7	934.6	933.4	932.3
175°	942.6	943.6	943.6	942.4	941.2	940.1	938.9
177.5°	945.5	946.3	946.2	945.3	944.3	943.4	942.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9

(END OF REPORT)