

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332436-927

Luminaire Tested: **S123RDIW-S775D755U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332436-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4705.4 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40	36
3	82	73	65	60	75	67	61	56	57	52	49	48	44	42	39	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21
7	59	47	39	33	54	44	37	32	37	32	28	32	28	24	26	23	21	18
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11009	11009	11009
5°	11051	10899	10962
10°	10989	10762	10726
15°	10871	10510	10399
20°	10709	10195	9958
25°	10542	9841	9526
30°	10320	9434	8918
35°	10093	9025	8360
40°	9884	8543	7669
45°	9608	8068	7046
50°	9306	7529	6348
55°	8997	6912	5697
60°	8714	6250	4982
65°	8344	5535	4266
70°	7884	4648	3446
75°	7207	3656	3244
80°	6428	3242	2982
85°	5434	2865	2655



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	2.0
10°-20°	267.2	5.7
20°-30°	384.8	8.2
30°-40°	433.4	9.2
40°-50°	414.6	8.8
50°-60°	339.6	7.2
60°-70°	229.1	4.9
70°-80°	115.3	2.4
80°-90°	32.7	0.7
90°-100°	28.5	0.6
100°-110°	136.0	2.9
110°-120°	326.6	6.9
120°-130°	415.9	8.8
130°-140°	444.3	9.4
140°-150°	415.5	8.8
150°-160°	335.2	7.1
160°-170°	216.3	4.6
170°-180°	74.5	1.6
0°-30°	748.0	15.9
0°-40°	1181.5	25.1
0°-60°	1935.6	41.1
0°-90°	2312.7	49.1
90°-120°	491.1	10.4
90°-150°	1766.8	37.5
90°-180°	2393.0	50.9
0°-180°	4705.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1023	1023	1023	1023	1023	
5°	1023	1018	1009	1016	1014	97
15°	976	966	943	939	933	275
25°	888	866	829	812	802	408
35°	768	737	687	652	636	481
45°	631	592	530	484	463	487
55°	479	437	368	322	304	430
65°	328	281	217	178	168	324
75°	173	133	88	80	78	185
85°	44	27	23	22	22	49
90°	1	7	14	16	18	4
95°	36	13	18	22	22	44
105°	174	177	128	30	26	184
115°	326	329	335	340	343	322
125°	459	464	466	468	469	410
135°	572	575	578	579	578	440
145°	660	664	665	666	666	413
155°	727	726	726	729	726	335
165°	767	765	764	768	765	216
175°	785	782	782	786	782	75
180°	785	785	785	785	785	



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1026.0	1025.5	1024.8	1024.3	1023.7	1022.5	1020.7	1019.0	1017.2	1015.4	1017.1
5°	1022.8	1021.8	1020.9	1020.0	1019.1	1017.5	1015.3	1013.0	1010.8	1008.7	1010.3
7.5°	1013.3	1012.3	1011.3	1010.3	1009.3	1007.3	1004.5	1001.6	998.8	995.9	996.8
10°	1005.4	1004.0	1002.7	1001.5	1000.1	997.8	994.5	991.3	987.9	984.6	984.8
12.5°	994.0	992.6	991.2	989.8	988.3	985.6	981.5	977.5	973.4	969.3	969.2
15°	975.5	973.4	971.4	969.4	967.3	963.8	958.6	953.5	948.2	943.1	942.2
17.5°	952.0	949.7	947.4	945.0	942.6	938.2	931.6	925.0	918.5	912.0	910.0
20°	934.9	931.8	928.9	926.0	923.1	918.1	911.0	904.0	897.1	890.0	887.6
22.5°	915.6	912.2	908.8	905.4	902.0	896.6	889.1	881.7	874.3	866.8	863.8
25°	887.6	883.0	878.3	873.7	869.1	862.5	854.1	845.6	837.1	828.6	824.7
27.5°	853.5	848.4	843.4	838.3	833.2	825.9	816.5	807.1	797.6	788.1	782.8
30°	830.3	824.7	819.3	813.7	808.2	800.3	790.0	779.6	769.3	759.0	752.7
32.5°	807.1	800.8	794.6	788.3	782.0	773.4	762.5	751.6	740.7	729.8	722.9
35°	768.1	761.4	754.8	748.2	741.6	732.5	721.1	709.6	698.2	686.8	678.9
37.5°	728.6	721.2	713.8	706.5	699.1	689.4	677.2	665.0	652.8	640.6	631.5
40°	703.4	695.3	687.1	679.1	671.0	660.4	647.3	634.2	621.1	608.0	598.4
42.5°	674.9	666.8	658.6	650.5	642.5	631.6	618.1	604.5	591.0	577.5	567.0
45°	631.2	623.0	614.7	606.3	598.0	586.8	572.6	558.4	544.2	530.0	519.5
47.5°	587.6	578.5	569.4	560.3	551.2	539.6	525.4	511.1	496.9	482.8	471.3
50°	555.7	547.1	538.4	529.7	521.1	509.3	494.4	479.4	464.5	449.6	438.2
52.5°	527.2	517.8	508.4	499.0	489.6	477.5	462.7	448.0	433.2	418.4	406.5
55°	479.4	470.4	461.4	452.3	443.3	430.9	415.3	399.7	384.0	368.3	357.6
57.5°	435.3	425.5	415.7	405.8	395.9	383.2	367.4	351.6	335.9	320.2	310.1
60°	404.8	394.7	384.5	374.4	364.2	351.5	336.2	320.9	305.6	290.3	280.4
62.5°	374.2	364.1	353.9	343.8	333.7	321.0	305.7	290.4	275.1	259.8	250.4
65°	327.6	317.5	307.4	297.2	287.1	274.8	260.5	246.1	231.7	217.3	208.3
67.5°	281.1	270.8	260.5	250.3	240.0	228.0	214.2	200.4	186.6	172.9	166.1
70°	250.5	240.6	230.6	220.6	210.7	199.2	186.3	173.5	160.6	147.7	141.2
72.5°	220.0	210.2	200.3	190.5	180.8	170.0	158.3	146.6	134.8	123.1	117.8
75°	173.3	164.5	155.7	146.8	138.0	128.5	118.4	108.2	98.1	87.9	86.1
77.5°	130.9	122.9	114.9	106.9	98.9	91.7	85.1	78.6	72.1	65.5	64.6
80°	103.7	96.1	88.6	81.0	73.4	67.7	63.8	60.0	56.2	52.3	51.7
82.5°	77.8	71.3	64.7	58.2	51.7	47.5	45.7	43.9	42.1	40.3	39.8
85°	44.0	39.9	35.9	31.8	27.7	25.4	24.9	24.3	23.8	23.2	22.9
87.5°	16.1	14.7	13.3	12.0	10.6	10.1	10.4	10.8	11.1	11.4	11.4
90°	0.6	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5
92.5°	10.9	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8
95°	35.6	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0
97.5°	71.5	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8
100°	98.5	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3
102.5°	129.3	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2
105°	173.7	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7
107.5°	220.5	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1
110°	251.8	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.7	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4
115°	325.8	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9
117.5°	368.7	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7
120°	395.2	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3
122.5°	422.3	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5
125°	459.4	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6
127.5°	495.3	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1
130°	517.6	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1
132.5°	539.1	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1
135°	571.9	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1
137.5°	599.8	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2
140°	618.5	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2
142.5°	635.7	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4
145°	659.9	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4
147.5°	682.6	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7
150°	696.6	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8
152.5°	709.2	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1
155°	726.9	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0
157.5°	740.7	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8
160°	749.1	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7
162.5°	757.0	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8
165°	766.6	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2
167.5°	774.0	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7
170°	778.2	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9
172.5°	781.0	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7
175°	784.7	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2
177.5°	785.5	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8	1022.8
2.5°	1018.7	1020.3	1021.9	1022.6	1022.3	1022.0	1021.7	1021.4
5°	1011.9	1013.6	1015.3	1015.9	1015.6	1015.2	1014.8	1014.5
7.5°	997.8	998.6	999.6	999.7	999.1	998.5	997.8	997.2
10°	985.0	985.2	985.3	985.0	984.0	983.1	982.2	981.3
12.5°	969.1	969.0	968.9	968.3	967.3	966.1	965.1	964.0
15°	941.3	940.3	939.4	938.3	937.1	935.7	934.5	933.2
17.5°	908.0	906.1	904.1	902.2	900.2	898.3	896.4	894.5
20°	885.3	882.8	880.4	878.1	875.9	873.7	871.5	869.3
22.5°	860.9	857.9	854.8	852.3	850.2	848.2	846.1	844.1
25°	820.9	817.1	813.2	810.2	808.2	806.1	804.1	802.1
27.5°	777.4	772.1	766.7	762.4	759.3	756.2	753.1	750.0
30°	746.5	740.1	733.9	729.3	726.4	723.4	720.4	717.5
32.5°	716.1	709.2	702.3	697.4	694.3	691.2	688.1	685.0
35°	671.0	663.1	655.1	649.5	646.2	642.9	639.5	636.2
37.5°	622.5	613.5	604.5	598.0	593.9	589.8	585.7	581.6
40°	588.8	579.2	569.7	562.8	558.5	554.3	550.0	545.8
42.5°	556.5	546.1	535.6	528.5	524.7	520.9	517.1	513.3
45°	509.1	498.5	488.0	480.5	476.1	471.7	467.3	462.9
47.5°	459.9	448.5	437.0	429.4	425.4	421.4	417.6	413.6
50°	426.7	415.3	403.9	396.0	391.8	387.5	383.3	379.1
52.5°	394.7	382.8	370.9	363.1	359.3	355.5	351.6	347.8
55°	346.9	336.2	325.5	318.3	314.7	310.9	307.3	303.6
57.5°	300.0	289.9	279.8	273.1	270.1	266.9	263.7	260.6
60°	270.4	260.5	250.5	244.0	240.8	237.7	234.6	231.4
62.5°	241.1	231.7	222.4	216.0	212.7	209.5	206.2	202.9
65°	199.2	190.2	181.2	175.6	173.6	171.6	169.6	167.5
67.5°	159.4	152.7	145.8	141.4	139.3	137.0	134.9	132.7
70°	134.8	128.3	121.8	117.6	115.6	113.5	111.5	109.5
72.5°	112.6	107.3	102.0	98.9	98.1	97.3	96.4	95.5
75°	84.2	82.4	80.6	79.5	79.1	78.7	78.3	78.0
77.5°	63.5	62.5	61.6	60.8	60.5	60.1	59.7	59.4
80°	51.2	50.6	50.1	49.6	49.2	48.9	48.5	48.1
82.5°	39.2	38.7	38.1	37.8	37.7	37.6	37.5	37.5
85°	22.5	22.1	21.8	21.5	21.5	21.5	21.5	21.5
87.5°	11.3	11.3	11.2	11.2	11.1	11.0	10.9	10.8
90°	15.1	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	16.6	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	19.9	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	20.8	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	21.3	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	31.9	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	81.8	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	200.3	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	254.4	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332436-927

CATALOG NUMBER: S123RDIW-S775D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.5	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	337.2	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	377.7	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	404.3	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.2	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	466.8	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	503.6	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	525.7	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	546.7	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	606.8	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	624.8	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	641.8	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.7	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.0	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.1	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	711.6	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	727.6	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	741.6	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	749.5	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	756.7	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	766.3	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	780.8	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	784.1	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	785.4	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)