

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332196-830

Luminaire Tested: **S123DIW-S1000D1030U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332196-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1030U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7771.6 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	44	42	40	35
3	81	72	64	58	75	66	60	55	56	51	47	47	44	41	39	36	34	30
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	32	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20	17
8	54	41	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.8
10°-20°	396.8	5.1
20°-30°	586.2	7.5
30°-40°	684.7	8.8
40°-50°	688.4	8.9
50°-60°	604.7	7.8
60°-70°	450.5	5.8
70°-80°	256.7	3.3
80°-90°	77.2	1.0
90°-100°	46.3	0.6
100°-110°	220.8	2.8
110°-120°	530.4	6.8
120°-130°	675.4	8.7
130°-140°	721.6	9.3
140°-150°	674.8	8.7
150°-160°	544.3	7.0
160°-170°	351.3	4.5
170°-180°	121.1	1.6
0°-30°	1123.5	14.5
0°-40°	1808.2	23.3
0°-60°	3101.3	39.9
0°-90°	3885.7	50.0
90°-120°	797.5	10.3
90°-150°	2869.2	36.9
90°-180°	3886.0	50.0
0°-180°	7771.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	11	23	26	28	6
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	529	535	543	553	557	522
125°	746	753	757	759	761	666
135°	929	934	938	941	938	715
145°	1072	1078	1080	1082	1082	671
155°	1180	1179	1180	1184	1179	544
165°	1245	1242	1241	1248	1242	352
175°	1274	1270	1270	1276	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	26.9	26.6	26.4	26.1	25.8	25.8	26.2	26.5	26.8	27.1	27.1
90°	0.9	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6
92.5°	17.6	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5
95°	57.8	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8
97.5°	116.0	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1
100°	159.9	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9
102.5°	210.0	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1
105°	282.1	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1
107.5°	358.3	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7
110°	409.0	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.4	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8
115°	529.2	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5
117.5°	598.7	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7
120°	641.9	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9
122.5°	685.8	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6
125°	746.0	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8
127.5°	804.3	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1
130°	840.7	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9
132.5°	875.5	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9
135°	928.7	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8
137.5°	974.1	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4
140°	1004.5	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8
142.5°	1032.5	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7
145°	1071.7	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6
147.5°	1108.6	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2
150°	1131.3	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4
152.5°	1151.8	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0
155°	1180.5	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6
157.5°	1202.9	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0
160°	1216.5	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9
162.5°	1229.4	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4
165°	1244.9	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8
167.5°	1257.0	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9
170°	1263.9	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7
172.5°	1268.4	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3
175°	1274.2	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0
177.5°	1275.7	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	27.0	27.0	26.9	26.9	27.0	27.1	27.1	27.2
90°	24.4	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	27.0	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	32.3	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	34.6	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	51.8	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	325.4	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	413.1	406.1	399.2	380.7	350.6	320.5	290.4	260.3



TEST NUMBER: P332196-830

CATALOG NUMBER: S123DIW-S1000D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	474.9	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	547.6	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	613.4	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	656.6	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	698.7	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.2	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	817.7	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	853.8	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	887.8	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	985.4	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1014.6	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1042.4	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.0	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1115.7	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1136.9	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1155.7	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1181.7	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1204.3	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1217.1	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1228.8	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1244.4	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1268.0	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1273.4	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1275.4	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)