

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332436

Luminaire Tested: **S123RDIW-S775D755U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332436
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5939.8 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49					49			
1	98	94	90	87	90	87	83	80	73	71	69	61	59	58	49	48	47					42				
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40					36				
3	82	73	65	60	75	67	61	56	57	52	49	48	44	42	39	37	35					31				
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30					27				
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26					23				
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23					21				
7	59	47	39	33	54	44	37	32	37	32	28	32	28	24	26	23	21					18				
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19					16				
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17					15				
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16					14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13897	13897	13897
5°	13950	13758	13837
10°	13871	13585	13539
15°	13722	13266	13127
20°	13518	12869	12569
25°	13307	12423	12025
30°	13027	11908	11257
35°	12741	11393	10553
40°	12476	10784	9681
45°	12129	10185	8894
50°	11747	9503	8013
55°	11357	8724	7191
60°	11001	7890	6288
65°	10534	6986	5387
70°	9951	5866	4349
75°	9100	4616	4092
80°	8114	4091	3763
85°	6854	3619	3359



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	2.0
10°-20°	337.3	5.7
20°-30°	485.7	8.2
30°-40°	547.1	9.2
40°-50°	523.4	8.8
50°-60°	428.6	7.2
60°-70°	289.2	4.9
70°-80°	145.5	2.4
80°-90°	41.3	0.7
90°-100°	36.0	0.6
100°-110°	171.6	2.9
110°-120°	412.3	6.9
120°-130°	525.0	8.8
130°-140°	560.9	9.4
140°-150°	524.5	8.8
150°-160°	423.1	7.1
160°-170°	273.1	4.6
170°-180°	94.1	1.6
0°-30°	944.3	15.9
0°-40°	1491.4	25.1
0°-60°	2443.4	41.1
0°-90°	2919.4	49.1
90°-120°	619.9	10.4
90°-150°	2230.2	37.5
90°-180°	3020.0	50.8
0°-180°	5939.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1291	1291	1291	1291	1291	
5°	1291	1285	1273	1282	1281	122
15°	1231	1219	1190	1185	1178	347
25°	1120	1093	1046	1025	1012	515
35°	970	930	867	823	803	607
45°	797	748	669	611	584	615
55°	605	552	465	406	383	542
65°	414	355	274	225	212	409
75°	219	168	111	101	98	233
85°	56	34	29	27	27	62
90°	1	8	18	21	22	5
95°	45	17	23	28	28	55
105°	219	223	161	38	32	232
115°	411	416	422	430	433	406
125°	580	586	589	590	592	518
135°	722	726	729	731	729	555
145°	833	838	840	841	841	521
155°	918	916	917	920	916	423
165°	968	966	965	970	965	273
175°	990	987	988	992	987	94
180°	990	990	990	990	990	



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1295.2	1294.5	1293.7	1293.0	1292.3	1290.8	1288.5	1286.3	1284.1	1281.8	1283.9
5°	1291.1	1289.9	1288.7	1287.6	1286.4	1284.4	1281.6	1278.8	1276.0	1273.3	1275.3
7.5°	1279.1	1277.9	1276.6	1275.3	1274.1	1271.6	1268.0	1264.4	1260.8	1257.1	1258.3
10°	1269.1	1267.4	1265.8	1264.2	1262.5	1259.6	1255.4	1251.3	1247.1	1242.9	1243.1
12.5°	1254.8	1253.0	1251.2	1249.4	1247.6	1244.1	1239.0	1233.9	1228.7	1223.6	1223.5
15°	1231.4	1228.8	1226.2	1223.7	1221.1	1216.6	1210.1	1203.6	1197.0	1190.5	1189.4
17.5°	1201.8	1198.9	1195.9	1192.9	1189.9	1184.3	1176.0	1167.7	1159.4	1151.2	1148.7
20°	1180.1	1176.3	1172.6	1168.9	1165.2	1158.9	1150.0	1141.2	1132.4	1123.5	1120.5
22.5°	1155.8	1151.5	1147.2	1142.9	1138.6	1131.8	1122.4	1113.0	1103.6	1094.2	1090.4
25°	1120.4	1114.6	1108.7	1102.9	1097.1	1088.8	1078.1	1067.4	1056.7	1046.0	1041.1
27.5°	1077.4	1071.0	1064.6	1058.2	1051.8	1042.6	1030.7	1018.8	1006.8	994.9	988.1
30°	1048.1	1041.1	1034.2	1027.2	1020.2	1010.2	997.2	984.1	971.1	958.1	950.2
32.5°	1018.8	1010.9	1003.0	995.1	987.2	976.3	962.5	948.8	935.0	921.2	912.6
35°	969.6	961.2	952.8	944.5	936.1	924.7	910.3	895.8	881.4	867.0	857.0
37.5°	919.8	910.4	901.1	891.8	882.5	870.2	854.8	839.4	824.0	808.6	797.2
40°	887.9	877.7	867.4	857.2	847.0	833.6	817.1	800.6	784.0	767.5	755.4
42.5°	851.9	841.7	831.4	821.2	811.0	797.3	780.2	763.1	746.1	729.0	715.8
45°	796.8	786.4	775.9	765.4	754.9	740.8	722.8	704.9	687.0	669.1	655.8
47.5°	741.8	730.3	718.8	707.3	695.8	681.1	663.2	645.2	627.3	609.4	595.0
50°	701.5	690.6	679.7	668.7	657.8	642.9	624.1	605.2	586.4	567.5	553.1
52.5°	665.5	653.7	641.8	629.9	618.1	602.8	584.1	565.5	546.8	528.1	513.2
55°	605.2	593.8	582.4	571.0	559.6	544.0	524.2	504.5	484.7	464.9	451.4
57.5°	549.5	537.1	524.7	512.2	499.8	483.7	463.8	443.9	424.0	404.2	391.4
60°	511.0	498.2	485.4	472.6	459.8	443.7	424.4	405.1	385.8	366.5	353.9
62.5°	472.4	459.6	446.8	434.0	421.3	405.2	385.9	366.6	347.3	327.9	316.1
65°	413.6	400.8	388.0	375.2	362.4	346.9	328.8	310.6	292.5	274.3	262.9
67.5°	354.8	341.8	328.9	315.9	303.0	287.8	270.4	253.0	235.6	218.2	209.7
70°	316.2	303.7	291.1	278.5	266.0	251.5	235.2	219.0	202.7	186.4	178.2
72.5°	277.7	265.3	252.9	240.5	228.2	214.6	199.8	185.0	170.2	155.4	148.7
75°	218.8	207.7	196.5	185.3	174.2	162.2	149.4	136.6	123.8	111.0	108.7
77.5°	165.2	155.1	145.0	134.9	124.8	115.7	107.4	99.2	91.0	82.7	81.5
80°	130.9	121.3	111.8	102.3	92.7	85.5	80.6	75.7	70.9	66.0	65.3
82.5°	98.2	90.0	81.7	73.5	65.3	60.0	57.7	55.4	53.2	50.9	50.2
85°	55.5	50.4	45.3	40.1	35.0	32.1	31.4	30.7	30.0	29.3	28.9
87.5°	20.3	18.5	16.8	15.1	13.4	12.7	13.1	13.6	14.0	14.4	14.4
90°	0.7	2.4	4.0	5.6	7.3	9.2	11.3	13.4	15.5	17.7	18.3
92.5°	13.7	13.2	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.8	19.9
95°	44.9	38.2	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.2	87.2	84.2	81.2	78.2	70.8	59.0	47.2	35.5	23.7	25.0
100°	124.4	127.6	130.9	134.2	137.4	126.3	100.8	75.3	49.8	24.3	25.6
102.5°	163.2	165.6	167.9	170.3	172.6	159.9	132.0	104.1	76.3	48.4	44.4
105°	219.3	221.1	222.9	224.7	226.5	220.0	205.3	190.6	175.9	161.2	132.2
107.5°	278.4	279.9	281.3	282.8	284.2	286.1	288.4	290.7	293.1	295.4	274.1
110°	317.9	319.2	320.5	321.8	323.1	324.7	326.5	328.3	330.1	331.9	326.5



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.6	356.7	357.9	359.1	360.3	361.8	363.6	365.4	367.2	369.0	369.1
115°	411.3	412.3	413.3	414.3	415.3	416.5	418.0	419.4	420.9	422.4	424.0
117.5°	465.4	466.6	467.8	469.0	470.2	471.2	471.9	472.7	473.4	474.2	475.5
120°	498.9	500.4	501.9	503.3	504.8	505.8	506.3	506.8	507.3	507.7	509.1
122.5°	533.1	534.3	535.5	536.7	537.9	538.8	539.4	540.1	540.7	541.3	542.2
125°	579.9	581.2	582.5	583.8	585.1	586.1	586.7	587.4	588.0	588.7	589.0
127.5°	625.2	626.5	627.8	629.1	630.4	631.5	632.3	633.0	633.8	634.6	635.1
130°	653.4	654.8	656.1	657.4	658.7	659.7	660.3	661.0	661.6	662.3	662.9
132.5°	680.5	681.8	683.1	684.4	685.8	686.7	687.2	687.7	688.2	688.8	689.4
135°	721.9	722.9	723.8	724.8	725.8	726.6	727.3	727.9	728.6	729.2	729.7
137.5°	757.2	758.4	759.7	760.9	762.2	763.0	763.3	763.7	764.1	764.4	765.2
140°	780.7	781.7	782.7	783.7	784.7	785.4	785.9	786.4	786.9	787.4	788.0
142.5°	802.5	803.5	804.5	805.5	806.5	807.2	807.7	808.2	808.7	809.2	809.7
145°	833.0	834.1	835.3	836.4	837.6	838.3	838.6	839.0	839.3	839.6	839.9
147.5°	861.7	862.4	863.2	863.9	864.7	865.2	865.6	865.9	866.2	866.5	866.9
150°	879.4	879.8	880.3	880.8	881.3	881.7	882.1	882.4	882.7	883.0	883.4
152.5°	895.2	895.5	895.7	895.9	896.2	896.4	896.6	896.8	897.0	897.2	897.7
155°	917.6	917.3	917.0	916.6	916.3	916.2	916.4	916.6	916.7	916.9	917.7
157.5°	935.0	935.0	934.9	934.9	934.9	934.8	934.6	934.4	934.3	934.1	935.1
160°	945.6	945.4	945.3	945.1	944.9	944.8	944.6	944.4	944.3	944.1	945.1
162.5°	955.6	955.2	954.7	954.3	953.9	953.6	953.4	953.3	953.1	952.9	954.1
165°	967.7	967.2	966.7	966.2	965.7	965.4	965.2	965.0	964.9	964.7	966.0
167.5°	977.1	976.4	975.8	975.1	974.5	974.1	974.1	974.1	974.1	974.1	975.4
170°	982.4	981.7	981.1	980.4	979.8	979.4	979.4	979.4	979.4	979.4	980.7
172.5°	985.9	985.1	984.3	983.6	982.8	982.4	982.6	982.7	982.8	983.0	984.3
175°	990.5	989.6	988.8	988.0	987.2	986.9	987.0	987.2	987.4	987.5	988.7
177.5°	991.6	991.0	990.3	989.7	989.0	988.8	988.9	989.0	989.2	989.3	990.3
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1	1291.1
2.5°	1285.9	1288.0	1290.0	1290.9	1290.5	1290.1	1289.7	1289.4
5°	1277.4	1279.5	1281.6	1282.4	1282.0	1281.5	1281.0	1280.6
7.5°	1259.5	1260.6	1261.8	1262.0	1261.2	1260.4	1259.6	1258.8
10°	1243.4	1243.6	1243.8	1243.4	1242.2	1241.0	1239.9	1238.7
12.5°	1223.3	1223.2	1223.1	1222.3	1221.0	1219.6	1218.3	1216.9
15°	1188.2	1187.0	1185.9	1184.5	1182.9	1181.2	1179.6	1178.0
17.5°	1146.2	1143.8	1141.3	1138.9	1136.4	1134.0	1131.6	1129.2
20°	1117.5	1114.4	1111.4	1108.5	1105.7	1102.9	1100.1	1097.3
22.5°	1086.7	1082.9	1079.1	1075.9	1073.3	1070.7	1068.1	1065.5
25°	1036.3	1031.4	1026.5	1022.8	1020.2	1017.6	1015.1	1012.5
27.5°	981.3	974.6	967.8	962.4	958.5	954.6	950.7	946.8
30°	942.3	934.3	926.4	920.6	916.9	913.2	909.4	905.7
32.5°	903.9	895.3	886.6	880.3	876.4	872.5	868.6	864.7
35°	847.0	837.0	827.0	819.9	815.7	811.5	807.3	803.1
37.5°	785.8	774.5	763.1	754.9	749.7	744.5	739.4	734.2
40°	743.3	731.2	719.1	710.4	705.0	699.7	694.3	689.0
42.5°	702.5	689.3	676.1	667.1	662.3	657.5	652.7	647.9
45°	642.6	629.3	616.0	606.6	601.0	595.4	589.9	584.3
47.5°	580.5	566.1	551.7	542.0	537.0	532.0	527.1	522.1
50°	538.7	524.2	509.8	499.9	494.6	489.2	483.9	478.5
52.5°	498.2	483.2	468.2	458.3	453.5	448.7	443.9	439.1
55°	437.9	424.4	410.9	401.8	397.2	392.5	387.9	383.2
57.5°	378.7	365.9	353.2	344.8	340.9	336.9	332.9	329.0
60°	341.3	328.8	316.2	308.0	304.0	300.0	296.1	292.1
62.5°	304.3	292.5	280.7	272.7	268.5	264.4	260.3	256.1
65°	251.5	240.1	228.7	221.7	219.2	216.6	214.1	211.5
67.5°	201.2	192.7	184.1	178.5	175.8	173.0	170.3	167.5
70°	170.1	161.9	153.8	148.5	145.9	143.3	140.8	138.2
72.5°	142.1	135.4	128.8	124.9	123.8	122.8	121.7	120.6
75°	106.3	104.0	101.7	100.3	99.8	99.4	98.9	98.4
77.5°	80.2	78.9	77.7	76.8	76.4	75.9	75.4	75.0
80°	64.6	63.9	63.2	62.6	62.1	61.7	61.2	60.7
82.5°	49.5	48.8	48.1	47.7	47.6	47.5	47.4	47.3
85°	28.4	27.9	27.5	27.2	27.2	27.2	27.2	27.2
87.5°	14.3	14.3	14.2	14.1	14.0	13.9	13.8	13.6
90°	19.0	19.6	20.3	20.8	21.1	21.4	21.7	22.1
92.5°	20.9	22.0	23.0	23.6	23.8	24.0	24.2	24.4
95°	25.1	26.2	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.3	27.6	28.9	29.7	29.8	30.0	30.2	30.3
100°	26.9	28.2	29.5	30.3	30.4	30.6	30.7	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.5
105°	103.3	74.3	45.4	31.1	31.4	31.7	32.1	32.4
107.5°	252.9	231.7	210.5	189.0	167.1	145.3	123.5	101.7
110°	321.1	315.7	310.3	295.9	272.5	249.1	225.7	202.4



TEST NUMBER: P332436

CATALOG NUMBER: S123RDIW-S775D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.2	369.3	369.4	366.9	362.0	357.1	352.1	347.2
115°	425.7	427.3	428.9	430.1	430.7	431.4	432.0	432.7
117.5°	476.8	478.1	479.4	480.1	480.3	480.4	480.5	480.7
120°	510.4	511.7	513.0	513.6	513.6	513.6	513.6	513.6
122.5°	543.1	544.0	545.0	545.5	545.6	545.7	545.9	546.0
125°	589.3	589.7	590.0	590.3	590.7	591.0	591.3	591.6
127.5°	635.7	636.2	636.7	636.8	636.5	636.1	635.8	635.5
130°	663.6	664.2	664.9	665.1	664.7	664.4	664.1	663.7
132.5°	690.1	690.7	691.4	691.5	691.0	690.6	690.1	689.6
135°	730.2	730.7	731.2	731.2	730.7	730.2	729.7	729.2
137.5°	766.0	766.8	767.6	767.8	767.5	767.1	766.8	766.5
140°	788.7	789.3	790.0	790.2	789.8	789.5	789.2	788.8
142.5°	810.2	810.7	811.2	811.3	810.8	810.4	809.9	809.4
145°	840.3	840.6	840.9	841.1	841.1	841.1	841.1	841.1
147.5°	867.2	867.5	867.9	867.6	866.9	866.1	865.4	864.6
150°	883.7	884.0	884.3	884.3	883.8	883.3	882.8	882.3
152.5°	898.3	898.9	899.5	899.4	898.7	897.9	897.2	896.4
155°	918.5	919.3	920.2	920.1	919.1	918.1	917.1	916.1
157.5°	936.1	937.0	938.0	937.9	936.6	935.3	934.1	932.8
160°	946.1	947.1	948.0	948.0	946.8	945.7	944.5	943.4
162.5°	955.2	956.3	957.4	957.4	956.4	955.4	954.4	953.4
165°	967.3	968.6	969.9	970.0	968.9	967.7	966.6	965.4
167.5°	976.7	978.1	979.4	979.4	978.1	976.7	975.4	974.1
170°	982.0	983.4	984.7	984.7	983.4	982.0	980.7	979.4
172.5°	985.6	986.9	988.2	988.1	986.7	985.3	983.8	982.4
175°	989.8	991.0	992.1	992.0	990.7	989.4	988.1	986.8
177.5°	991.4	992.4	993.5	993.3	992.0	990.7	989.4	988.1
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5

(END OF REPORT)