

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332209-935

Luminaire Tested: **S123DIW-S1000D1535U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332209-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8130.5 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14670	14670	14670
5°	14738	14536	14638
10°	14641	14410	14499
15°	14469	14247	14273
20°	14269	14014	14027
25°	14001	13737	13709
30°	13706	13430	13326
35°	13397	13104	12935
40°	13075	12745	12546
45°	12718	12415	12113
50°	12363	12010	11675
55°	11898	11590	11237
60°	11427	11102	10747
65°	11013	10565	10236
70°	10401	9958	9514
75°	9503	9162	8771
80°	8573	8207	8133
85°	7534	7237	6941



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.6
10°-20°	362.5	4.5
20°-30°	535.5	6.6
30°-40°	625.5	7.7
40°-50°	628.8	7.7
50°-60°	552.4	6.8
60°-70°	411.5	5.1
70°-80°	234.5	2.9
80°-90°	72.2	0.9
90°-100°	107.7	1.3
100°-110°	322.3	4.0
110°-120°	548.1	6.7
120°-130°	721.0	8.9
130°-140°	810.4	10.0
140°-150°	796.6	9.8
150°-160°	670.6	8.2
160°-170°	446.4	5.5
170°-180°	156.3	1.9
0°-30°	1026.3	12.6
0°-40°	1651.8	20.3
0°-60°	2833.0	34.8
0°-90°	3551.2	43.7
90°-120°	978.1	12.0
90°-150°	3306.0	40.7
90°-180°	4579.0	56.3
0°-180°	8130.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1363	1363	1363	1363	1363	
5°	1364	1358	1345	1356	1355	129
15°	1298	1293	1278	1287	1281	366
25°	1179	1171	1157	1158	1154	543
35°	1020	1012	997	990	984	638
45°	836	830	816	802	796	645
55°	634	632	618	605	599	568
65°	432	426	415	406	402	427
75°	228	224	220	215	211	244
85°	61	59	59	56	56	67
90°	1	14	31	36	39	8
95°	77	86	96	101	101	86
105°	292	295	306	307	309	313
115°	552	555	553	554	553	546
125°	808	811	809	804	798	720
135°	1048	1055	1054	1049	1046	807
145°	1271	1274	1278	1276	1271	794
155°	1455	1456	1457	1461	1453	670
165°	1585	1582	1581	1588	1580	447
175°	1649	1644	1644	1651	1642	157
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1367.5	1366.8	1365.9	1365.0	1364.3	1362.6	1360.4	1358.1	1355.8	1353.5	1355.6
5°	1364.0	1362.7	1361.4	1360.1	1358.8	1356.8	1353.9	1351.0	1348.2	1345.3	1347.9
7.5°	1350.7	1349.4	1348.1	1346.8	1345.5	1343.3	1340.4	1337.4	1334.5	1331.5	1333.8
10°	1339.5	1338.2	1336.8	1335.5	1334.2	1331.9	1328.5	1325.1	1321.7	1318.4	1320.7
12.5°	1324.4	1323.4	1322.2	1321.1	1320.1	1317.9	1314.7	1311.6	1308.4	1305.2	1306.9
15°	1298.4	1297.4	1296.3	1295.3	1294.3	1292.0	1288.7	1285.3	1281.9	1278.5	1280.6
17.5°	1268.2	1266.8	1265.5	1264.1	1262.7	1260.4	1257.0	1253.6	1250.3	1246.8	1248.3
20°	1245.7	1244.1	1242.6	1241.0	1239.4	1236.9	1233.6	1230.2	1226.8	1223.4	1224.4
22.5°	1220.4	1218.8	1217.3	1215.6	1214.1	1211.7	1208.2	1204.9	1201.5	1198.1	1198.9
25°	1178.9	1177.3	1175.8	1174.2	1172.6	1170.2	1166.7	1163.4	1160.0	1156.6	1156.8
27.5°	1134.6	1133.1	1131.5	1130.1	1128.5	1125.9	1122.3	1118.7	1115.0	1111.4	1111.6
30°	1102.7	1101.4	1100.1	1098.8	1097.5	1095.0	1091.4	1087.7	1084.1	1080.5	1080.5
32.5°	1070.8	1069.1	1067.4	1065.7	1063.9	1061.7	1058.9	1056.1	1053.3	1050.4	1049.0
35°	1019.5	1018.0	1016.4	1014.9	1013.2	1010.8	1007.4	1004.0	1000.7	997.2	995.7
37.5°	967.0	965.0	963.0	961.0	959.1	956.4	953.0	949.5	946.1	942.6	940.7
40°	930.5	928.8	927.3	925.7	924.2	921.6	917.9	914.3	910.7	907.0	904.9
42.5°	893.9	892.1	890.4	888.6	886.8	884.1	880.5	876.8	873.1	869.5	867.5
45°	835.5	834.5	833.4	832.4	831.4	829.1	825.8	822.3	819.0	815.6	812.5
47.5°	777.7	776.1	774.6	773.1	771.6	769.2	766.1	762.9	759.7	756.6	753.5
50°	738.3	736.9	735.6	734.3	733.1	730.7	727.3	723.9	720.6	717.2	714.3
52.5°	697.0	696.1	695.3	694.4	693.4	691.2	687.7	684.1	680.4	676.8	674.4
55°	634.0	633.7	633.4	633.2	632.9	631.1	627.8	624.3	621.0	617.6	614.7
57.5°	573.9	573.1	572.2	571.4	570.4	568.6	565.9	563.2	560.5	557.8	555.3
60°	530.8	530.5	530.3	530.0	529.8	528.1	525.0	521.9	518.8	515.7	513.2
62.5°	492.4	491.7	491.0	490.3	489.7	487.8	484.7	481.6	478.5	475.3	472.9
65°	432.4	431.1	429.8	428.5	427.2	425.2	422.7	420.1	417.4	414.8	412.8
67.5°	368.9	367.7	366.6	365.5	364.3	362.7	360.8	358.8	356.8	354.8	353.0
70°	330.5	328.9	327.4	325.8	324.3	322.6	321.1	319.5	318.0	316.4	314.6
72.5°	290.2	289.0	287.8	286.7	285.6	284.1	282.3	280.6	278.8	277.0	275.4
75°	228.5	227.5	226.4	225.4	224.4	223.4	222.7	221.9	221.1	220.3	219.0
77.5°	173.9	173.3	172.7	172.2	171.6	170.8	170.0	169.0	168.1	167.1	166.3
80°	138.3	137.5	136.7	136.0	135.2	134.5	134.0	133.5	132.9	132.4	132.2
82.5°	103.6	103.4	103.3	103.1	103.0	102.8	102.7	102.6	102.5	102.5	101.9
85°	61.0	60.4	59.9	59.4	58.9	58.6	58.6	58.6	58.6	58.6	58.0
87.5°	24.6	24.6	24.5	24.5	24.5	24.7	25.2	25.7	26.3	26.9	26.9
90°	1.3	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3
92.5°	31.4	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8
95°	76.6	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2
97.5°	136.0	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7
100°	176.6	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7
102.5°	223.3	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5
105°	292.1	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4
107.5°	372.1	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3
110°	422.0	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.9	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3
115°	551.8	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4
117.5°	630.3	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4
120°	679.1	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0
122.5°	730.0	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5
125°	807.5	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7
127.5°	879.3	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0
130°	927.0	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4
132.5°	974.8	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9
135°	1047.8	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1
137.5°	1115.3	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9
140°	1162.0	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1204.6	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1
145°	1271.1	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3
147.5°	1329.2	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6
150°	1369.8	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9
152.5°	1403.0	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7
155°	1455.4	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9
157.5°	1500.1	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8
160°	1528.2	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0
162.5°	1553.1	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0
165°	1585.3	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1
167.5°	1611.0	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6
170°	1625.5	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4
172.5°	1636.9	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6
175°	1648.9	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5
177.5°	1653.8	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9	1362.9
2.5°	1357.6	1359.8	1361.8	1362.8	1362.5	1362.4	1362.1	1361.9
5°	1350.5	1353.1	1355.7	1356.8	1356.2	1355.7	1355.2	1354.7
7.5°	1336.2	1338.5	1340.8	1341.9	1341.5	1341.3	1340.9	1340.6
10°	1323.0	1325.3	1327.7	1328.6	1328.1	1327.6	1327.1	1326.5
12.5°	1308.6	1310.4	1312.1	1312.8	1312.5	1312.2	1311.8	1311.6
15°	1282.6	1284.7	1286.9	1287.1	1285.6	1283.9	1282.4	1280.8
17.5°	1249.7	1251.2	1252.7	1253.1	1252.6	1252.0	1251.4	1250.9
20°	1225.5	1226.6	1227.6	1227.7	1226.9	1226.2	1225.4	1224.6
22.5°	1199.8	1200.6	1201.4	1201.4	1200.4	1199.4	1198.4	1197.4
25°	1157.1	1157.4	1157.7	1157.4	1156.6	1155.8	1155.0	1154.3
27.5°	1111.8	1112.0	1112.2	1111.8	1110.9	1109.8	1108.9	1107.8
30°	1080.5	1080.5	1080.5	1079.5	1077.7	1075.9	1074.1	1072.2
32.5°	1047.5	1046.1	1044.7	1043.4	1042.4	1041.4	1040.4	1039.4
35°	994.1	992.6	991.0	989.5	988.3	987.0	985.7	984.4
37.5°	938.9	937.0	935.1	933.8	933.0	932.1	931.3	930.5
40°	902.8	900.8	898.7	897.1	896.0	895.0	894.0	892.9
42.5°	865.3	863.2	861.2	859.6	858.6	857.6	856.5	855.5
45°	809.3	806.2	803.1	800.9	799.6	798.3	797.0	795.7
47.5°	750.4	747.3	744.2	742.2	741.0	739.9	738.7	737.5
50°	711.4	708.6	705.7	703.5	702.0	700.3	698.8	697.2
52.5°	671.9	669.5	667.1	665.0	663.5	661.9	660.4	658.8
55°	611.8	609.0	606.1	604.0	602.7	601.4	600.1	598.8
57.5°	552.7	550.2	547.6	545.5	544.1	542.5	541.1	539.5
60°	510.9	508.6	506.3	504.5	503.1	501.8	500.5	499.2
62.5°	470.6	468.3	465.9	464.3	463.4	462.5	461.7	460.8
65°	410.7	408.5	406.5	405.1	404.3	403.6	402.7	401.9
67.5°	351.2	349.4	347.6	346.1	345.0	343.9	342.8	341.7
70°	312.7	310.9	309.1	307.5	306.3	305.0	303.7	302.3
72.5°	273.8	272.2	270.5	269.4	268.7	268.0	267.4	266.7
75°	217.7	216.4	215.1	214.0	213.3	212.5	211.7	210.9
77.5°	165.3	164.5	163.6	163.2	163.2	163.2	163.2	163.2
80°	131.9	131.6	131.4	131.2	131.2	131.2	131.2	131.2
82.5°	101.5	101.0	100.6	100.2	100.0	99.8	99.6	99.4
85°	57.5	57.0	56.5	56.2	56.2	56.2	56.2	56.2
87.5°	26.9	26.9	26.9	27.0	27.1	27.2	27.4	27.5
90°	33.5	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	51.7	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	98.4	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	153.0	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	192.6	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	238.3	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	380.2	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	429.5	430.6	431.8	432.0	431.4	430.9	430.3	429.7



TEST NUMBER: P332209-935

CATALOG NUMBER: S123DIW-S1000D1535U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.7	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.8	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.7	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	806.6	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	881.5	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	931.2	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	979.6	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1052.0	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1122.7	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.2	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.9	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.9	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.1	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1459.1	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1502.0	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1528.4	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1553.3	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1584.8	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1635.3	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1647.2	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1652.4	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)