

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332209-830

Luminaire Tested: **S123DIW-S1000D1535U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332209-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8900.5 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80		64	64	64		50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65		57	55	53		44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54		50	47	45		39	37	36	31
3	80	71	63	57	73	65	58	53	54	49	45		44	41	38		35	32	30	26
4	73	62	55	49	67	57	50	45	48	43	39		39	35	32		31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33		35	31	28		28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29		32	28	24		25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25		29	25	22		23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23		26	22	19		21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20		24	20	17		19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18		22	18	16		18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16060	16060	16060
5°	16134	15913	16024
10°	16027	15774	15872
15°	15840	15597	15624
20°	15621	15341	15356
25°	15327	15037	15007
30°	15003	14701	14588
35°	14666	14345	14160
40°	14313	13952	13735
45°	13922	13592	13259
50°	13534	13147	12782
55°	13024	12688	12301
60°	12510	12152	11765
65°	12055	11566	11207
70°	11383	10902	10414
75°	10405	10031	9603
80°	9385	8988	8901
85°	8238	7929	7595



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.6
10°-20°	396.8	4.5
20°-30°	586.2	6.6
30°-40°	684.7	7.7
40°-50°	688.4	7.7
50°-60°	604.7	6.8
60°-70°	450.5	5.1
70°-80°	256.7	2.9
80°-90°	79.0	0.9
90°-100°	117.9	1.3
100°-110°	352.8	4.0
110°-120°	600.0	6.7
120°-130°	789.3	8.9
130°-140°	887.1	10.0
140°-150°	872.0	9.8
150°-160°	734.1	8.2
160°-170°	488.7	5.5
170°-180°	171.1	1.9
0°-30°	1123.5	12.6
0°-40°	1808.2	20.3
0°-60°	3101.3	34.8
0°-90°	3887.5	43.7
90°-120°	1070.7	12.0
90°-150°	3619.1	40.7
90°-180°	5013.0	56.3
0°-180°	8900.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1492	1492	1492	1492	1492	
5°	1493	1486	1473	1485	1483	141
15°	1421	1416	1400	1409	1402	401
25°	1290	1282	1266	1267	1264	594
35°	1116	1108	1092	1084	1078	698
45°	915	909	893	878	871	706
55°	694	692	676	662	656	621
65°	473	467	454	444	440	467
75°	250	245	241	235	231	267
85°	67	64	64	62	62	73
90°	1	16	34	40	43	9
95°	84	94	105	110	111	94
105°	320	323	336	336	338	343
115°	604	608	606	607	606	597
125°	884	888	886	880	874	788
135°	1147	1155	1154	1149	1146	884
145°	1392	1394	1398	1397	1392	869
155°	1593	1593	1595	1600	1590	733
165°	1735	1731	1731	1739	1730	489
175°	1805	1800	1799	1807	1798	171
180°	1809	1809	1809	1809	1809	



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1497.0	1496.2	1495.2	1494.3	1493.5	1491.7	1489.2	1486.7	1484.2	1481.7	1483.9
5°	1493.2	1491.8	1490.3	1488.9	1487.5	1485.3	1482.1	1478.9	1475.8	1472.7	1475.6
7.5°	1478.6	1477.2	1475.7	1474.3	1472.9	1470.6	1467.4	1464.1	1460.8	1457.5	1460.1
10°	1466.3	1464.9	1463.4	1462.0	1460.6	1458.0	1454.3	1450.6	1446.9	1443.2	1445.8
12.5°	1449.8	1448.7	1447.5	1446.2	1445.1	1442.7	1439.3	1435.8	1432.3	1428.8	1430.7
15°	1421.4	1420.2	1419.1	1418.0	1416.8	1414.4	1410.7	1407.0	1403.3	1399.6	1401.8
17.5°	1388.3	1386.8	1385.3	1383.8	1382.3	1379.8	1376.0	1372.3	1368.7	1364.9	1366.5
20°	1363.7	1362.0	1360.3	1358.5	1356.8	1354.1	1350.4	1346.7	1343.0	1339.3	1340.4
22.5°	1336.0	1334.3	1332.6	1330.8	1329.1	1326.4	1322.7	1319.0	1315.3	1311.5	1312.5
25°	1290.5	1288.8	1287.1	1285.4	1283.6	1281.0	1277.2	1273.6	1269.9	1266.1	1266.4
27.5°	1242.1	1240.4	1238.7	1237.1	1235.4	1232.6	1228.6	1224.6	1220.6	1216.6	1216.8
30°	1207.1	1205.7	1204.3	1202.9	1201.5	1198.7	1194.8	1190.7	1186.8	1182.8	1182.8
32.5°	1172.2	1170.4	1168.5	1166.6	1164.7	1162.2	1159.1	1156.1	1153.0	1149.9	1148.3
35°	1116.1	1114.4	1112.7	1111.0	1109.2	1106.5	1102.8	1099.1	1095.4	1091.7	1090.0
37.5°	1058.6	1056.4	1054.2	1052.1	1049.9	1047.0	1043.2	1039.4	1035.7	1031.9	1029.8
40°	1018.6	1016.8	1015.1	1013.4	1011.7	1008.9	1004.8	1000.9	996.9	992.9	990.6
42.5°	978.5	976.6	974.7	972.7	970.8	967.8	963.8	959.9	955.8	951.9	949.6
45°	914.6	913.5	912.4	911.3	910.1	907.7	904.0	900.2	896.5	892.9	889.5
47.5°	851.3	849.6	848.0	846.3	844.7	842.1	838.7	835.2	831.7	828.2	824.8
50°	808.2	806.7	805.3	803.9	802.5	799.9	796.2	792.5	788.8	785.1	781.9
52.5°	763.0	762.0	761.1	760.2	759.1	756.7	752.8	748.9	744.9	740.9	738.3
55°	694.0	693.7	693.4	693.1	692.9	690.9	687.2	683.4	679.8	676.1	672.9
57.5°	628.3	627.4	626.4	625.5	624.4	622.5	619.5	616.5	613.6	610.7	607.8
60°	581.1	580.8	580.5	580.2	579.9	578.2	574.7	571.3	567.9	564.5	561.8
62.5°	539.0	538.3	537.5	536.8	536.1	534.0	530.6	527.2	523.8	520.3	517.7
65°	473.3	471.9	470.5	469.1	467.7	465.5	462.7	459.9	456.9	454.1	451.9
67.5°	403.9	402.6	401.3	400.1	398.8	397.1	394.9	392.8	390.6	388.4	386.4
70°	361.7	360.1	358.4	356.7	355.0	353.2	351.5	349.8	348.1	346.4	344.4
72.5°	317.6	316.4	315.1	313.9	312.6	311.0	309.1	307.2	305.2	303.2	301.5
75°	250.2	249.0	247.9	246.8	245.6	244.6	243.7	242.9	242.0	241.2	239.8
77.5°	190.4	189.7	189.1	188.5	187.8	187.0	186.1	185.0	184.0	182.9	182.0
80°	151.4	150.5	149.7	148.8	148.0	147.2	146.7	146.1	145.5	145.0	144.7
82.5°	113.4	113.2	113.1	112.9	112.7	112.5	112.4	112.4	112.3	112.2	111.6
85°	66.7	66.2	65.6	65.0	64.5	64.2	64.2	64.2	64.2	64.2	63.5
87.5°	27.0	27.0	26.9	26.8	26.8	27.1	27.6	28.2	28.8	29.4	29.4
90°	1.4	4.6	7.7	10.9	14.0	17.7	21.8	25.9	30.0	34.1	35.3
92.5°	34.4	36.6	38.6	40.8	43.0	45.2	47.6	49.9	52.2	54.6	55.6
95°	83.9	86.1	88.3	90.5	92.7	95.1	97.6	100.1	102.6	105.2	106.4
97.5°	148.9	150.6	152.2	153.9	155.5	157.2	159.1	160.9	162.8	164.6	166.1
100°	193.3	195.2	197.1	199.0	200.9	202.6	204.2	205.8	207.4	209.0	209.9
102.5°	244.5	245.6	246.8	247.9	249.0	250.6	252.7	254.8	256.8	258.9	260.0
105°	319.8	320.5	321.0	321.7	322.3	324.0	326.9	329.7	332.6	335.5	335.5
107.5°	407.4	407.7	408.1	408.5	408.9	409.6	410.8	411.9	413.0	414.2	415.2
110°	461.9	462.6	463.2	463.8	464.5	465.1	465.7	466.4	466.9	467.6	468.9



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.8	519.2	519.5	519.9	520.3	520.6	520.7	520.8	520.9	521.0	522.5
115°	604.1	605.0	606.0	606.9	607.8	608.0	607.4	606.7	606.1	605.5	605.8
117.5°	689.9	690.5	691.2	691.8	692.4	692.3	691.5	690.7	689.8	689.1	689.0
120°	743.4	745.3	747.2	749.0	750.9	751.1	749.5	747.9	746.3	744.8	744.4
122.5°	799.1	800.4	801.8	803.2	804.6	804.9	804.1	803.2	802.5	801.6	800.8
125°	884.0	885.0	886.0	886.9	887.9	888.0	887.4	886.7	886.1	885.5	884.2
127.5°	962.5	964.5	966.6	968.6	970.6	971.3	970.5	969.9	969.2	968.5	966.7
130°	1014.8	1017.4	1019.8	1022.4	1024.9	1025.7	1024.7	1023.8	1022.8	1021.9	1020.7
132.5°	1067.1	1069.6	1072.1	1074.7	1077.2	1078.2	1077.4	1076.8	1076.0	1075.3	1073.8
135°	1147.0	1148.9	1150.8	1152.6	1154.6	1155.4	1155.1	1154.7	1154.4	1154.1	1152.8
137.5°	1220.9	1222.5	1224.1	1225.7	1227.2	1228.4	1229.3	1230.0	1230.9	1231.7	1230.4
140°	1272.1	1273.7	1275.3	1276.8	1278.4	1279.3	1279.7	1280.0	1280.3	1280.6	1280.3
142.5°	1318.7	1320.2	1321.8	1323.4	1325.0	1326.1	1326.6	1327.2	1327.8	1328.3	1328.0
145°	1391.5	1392.1	1392.7	1393.4	1394.0	1394.8	1395.7	1396.7	1397.6	1398.5	1398.3
147.5°	1455.1	1456.2	1457.4	1458.6	1459.7	1460.7	1461.6	1462.4	1463.3	1464.2	1464.2
150°	1499.5	1500.2	1500.7	1501.4	1502.0	1502.6	1503.3	1503.9	1504.5	1505.1	1505.1
152.5°	1535.9	1536.7	1537.7	1538.5	1539.4	1540.0	1540.4	1540.8	1541.2	1541.5	1542.1
155°	1593.3	1593.3	1593.3	1593.3	1593.3	1593.5	1593.7	1594.0	1594.4	1594.7	1596.0
157.5°	1642.2	1641.8	1641.4	1641.1	1640.7	1640.6	1640.9	1641.1	1641.3	1641.6	1642.9
160°	1672.9	1672.3	1671.6	1670.9	1670.4	1670.0	1670.0	1670.0	1670.0	1670.0	1671.6
162.5°	1700.2	1699.3	1698.4	1697.5	1696.7	1696.3	1696.6	1696.9	1697.0	1697.3	1698.9
165°	1735.4	1734.5	1733.5	1732.6	1731.6	1731.2	1731.2	1731.2	1731.2	1731.2	1733.1
167.5°	1763.6	1762.3	1761.0	1759.7	1758.5	1758.0	1758.2	1758.5	1758.8	1759.0	1761.0
170°	1779.4	1778.2	1777.0	1775.7	1774.4	1773.8	1773.8	1773.8	1773.8	1773.8	1776.0
172.5°	1792.0	1790.7	1789.4	1788.2	1787.0	1786.3	1786.3	1786.3	1786.3	1786.3	1788.3
175°	1805.1	1803.8	1802.5	1801.3	1800.0	1799.4	1799.4	1799.4	1799.4	1799.4	1801.3
177.5°	1810.4	1809.5	1808.5	1807.4	1806.4	1805.9	1805.9	1805.9	1805.9	1805.9	1807.4
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0	1492.0
2.5°	1486.2	1488.6	1490.8	1491.9	1491.6	1491.4	1491.1	1490.9
5°	1478.4	1481.2	1484.1	1485.3	1484.7	1484.1	1483.6	1483.0
7.5°	1462.7	1465.3	1467.8	1469.0	1468.6	1468.3	1467.9	1467.5
10°	1448.3	1450.9	1453.5	1454.4	1453.9	1453.3	1452.7	1452.2
12.5°	1432.6	1434.5	1436.3	1437.1	1436.8	1436.4	1436.1	1435.8
15°	1404.1	1406.4	1408.7	1409.0	1407.3	1405.5	1403.8	1402.1
17.5°	1368.1	1369.7	1371.3	1371.8	1371.2	1370.6	1369.9	1369.3
20°	1341.5	1342.7	1343.9	1344.0	1343.1	1342.3	1341.4	1340.6
22.5°	1313.4	1314.3	1315.2	1315.1	1314.1	1313.0	1311.9	1310.8
25°	1266.7	1267.1	1267.3	1267.1	1266.1	1265.3	1264.4	1263.6
27.5°	1217.1	1217.3	1217.6	1217.1	1216.1	1214.9	1213.9	1212.8
30°	1182.8	1182.8	1182.8	1181.8	1179.8	1177.8	1175.8	1173.7
32.5°	1146.7	1145.2	1143.6	1142.2	1141.1	1140.0	1139.0	1137.8
35°	1088.3	1086.6	1084.9	1083.3	1081.9	1080.4	1079.0	1077.6
37.5°	1027.8	1025.8	1023.7	1022.2	1021.3	1020.4	1019.5	1018.6
40°	988.4	986.1	983.8	982.0	980.9	979.8	978.6	977.5
42.5°	947.3	945.0	942.7	941.0	939.9	938.8	937.6	936.5
45°	886.0	882.6	879.2	876.8	875.3	873.9	872.5	871.0
47.5°	821.4	818.1	814.7	812.5	811.2	809.9	808.7	807.4
50°	778.8	775.7	772.5	770.2	768.5	766.7	765.0	763.3
52.5°	735.6	732.9	730.3	728.0	726.3	724.6	722.9	721.2
55°	669.8	666.7	663.5	661.2	659.8	658.4	657.0	655.5
57.5°	605.0	602.3	599.5	597.2	595.6	593.9	592.3	590.6
60°	559.3	556.8	554.2	552.2	550.7	549.3	547.9	546.5
62.5°	515.2	512.6	510.0	508.3	507.3	506.3	505.4	504.4
65°	449.6	447.2	445.0	443.5	442.6	441.8	440.8	440.0
67.5°	384.5	382.5	380.5	378.9	377.7	376.5	375.2	374.1
70°	342.3	340.4	338.4	336.7	335.3	333.8	332.4	330.9
72.5°	299.7	297.9	296.1	294.9	294.2	293.4	292.8	292.0
75°	238.4	236.9	235.4	234.3	233.5	232.6	231.8	230.9
77.5°	181.0	180.0	179.1	178.6	178.6	178.6	178.6	178.6
80°	144.4	144.1	143.8	143.6	143.6	143.6	143.6	143.6
82.5°	111.1	110.6	110.1	109.7	109.4	109.2	109.1	108.8
85°	63.0	62.4	61.8	61.5	61.5	61.5	61.5	61.5
87.5°	29.4	29.5	29.5	29.6	29.7	29.8	30.0	30.1
90°	36.7	37.9	39.2	40.2	40.7	41.4	42.0	42.6
92.5°	56.6	57.6	58.6	58.9	58.5	58.2	57.8	57.4
95°	107.7	109.0	110.2	110.8	110.8	110.8	110.8	110.8
97.5°	167.5	168.9	170.4	171.1	171.0	170.8	170.7	170.6
100°	210.8	211.8	212.7	213.5	214.1	214.8	215.4	216.0
102.5°	260.9	261.8	262.8	263.2	263.1	262.9	262.8	262.7
105°	335.5	335.5	335.5	335.7	336.4	337.1	337.6	338.3
107.5°	416.2	417.2	418.2	418.5	418.1	417.7	417.4	417.0
110°	470.1	471.4	472.7	473.0	472.3	471.7	471.1	470.4



TEST NUMBER: P332209-830

CATALOG NUMBER: S123DIW-S1000D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	524.1	525.6	527.1	527.8	527.7	527.5	527.4	527.3
115°	606.1	606.4	606.7	606.7	606.4	606.1	605.8	605.5
117.5°	688.9	688.9	688.8	688.3	687.4	686.5	685.7	684.8
120°	744.1	743.9	743.5	743.0	742.4	741.8	741.1	740.5
122.5°	799.9	799.2	798.3	797.5	796.6	795.7	794.8	793.9
125°	883.0	881.7	880.4	879.1	877.9	876.7	875.3	874.1
127.5°	965.0	963.2	961.4	959.8	958.4	956.9	955.5	953.9
130°	1019.4	1018.1	1016.9	1015.1	1013.0	1010.7	1008.5	1006.3
132.5°	1072.3	1070.8	1069.3	1067.7	1066.0	1064.3	1062.5	1060.8
135°	1151.6	1150.3	1149.1	1148.1	1147.5	1146.8	1146.2	1145.6
137.5°	1229.1	1227.8	1226.4	1225.1	1223.9	1222.8	1221.5	1220.3
140°	1280.0	1279.7	1279.3	1278.1	1275.8	1273.7	1271.4	1269.2
142.5°	1327.8	1327.4	1327.1	1326.1	1324.4	1322.7	1321.0	1319.3
145°	1397.9	1397.6	1397.3	1396.5	1395.2	1394.0	1392.7	1391.5
147.5°	1464.2	1464.2	1464.2	1463.3	1461.4	1459.5	1457.5	1455.7
150°	1505.1	1505.1	1505.1	1504.2	1502.3	1500.4	1498.5	1496.7
152.5°	1542.6	1543.0	1543.6	1543.0	1541.3	1539.7	1538.0	1536.4
155°	1597.2	1598.5	1599.8	1599.3	1597.0	1594.9	1592.6	1590.4
157.5°	1644.3	1645.6	1646.9	1646.7	1644.9	1643.1	1641.3	1639.6
160°	1673.2	1674.8	1676.3	1676.5	1675.3	1674.0	1672.7	1671.4
162.5°	1700.4	1702.0	1703.6	1703.5	1701.4	1699.4	1697.3	1695.4
165°	1734.9	1736.8	1738.7	1738.6	1736.4	1734.2	1731.9	1729.8
167.5°	1762.9	1764.9	1766.8	1766.8	1764.9	1762.9	1761.0	1759.0
170°	1778.2	1780.5	1782.6	1782.6	1780.5	1778.2	1776.0	1773.8
172.5°	1790.2	1792.2	1794.1	1794.0	1791.8	1789.6	1787.3	1785.2
175°	1803.2	1805.1	1806.9	1806.8	1804.6	1802.3	1800.2	1798.0
177.5°	1808.9	1810.4	1811.9	1811.8	1810.1	1808.3	1806.6	1804.8
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3

(END OF REPORT)