

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332233-935

Luminaire Tested: **S123DIW-S1165D1320U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332233-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1320U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8038.6 lumens  
Efficiency: N/A  
Efficacy: 105.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69		61	60	58		50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57		54	51	48		44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48		48	44	41		39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41		42	38	35		35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35		38	34	30		32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31		34	30	27		29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27		31	27	24		26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21		26	22	19		22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19		24	20	17		21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16942	16942	16942
5°	17022	16788	16904
10°	16909	16642	16746
15°	16711	16454	16485
20°	16479	16186	16200
25°	16170	15865	15833
30°	15830	15509	15392
35°	15473	15135	14939
40°	15100	14720	14491
45°	14690	14338	13988
50°	14277	13870	13485
55°	13741	13386	12979
60°	13199	12820	12411
65°	12720	12202	11826
70°	12013	11500	10990
75°	10975	10580	10131
80°	9899	9478	9397
85°	8682	8361	8028



TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.3	1.8
10°-20°	418.7	5.2
20°-30°	618.4	7.7
30°-40°	722.4	9.0
40°-50°	726.3	9.0
50°-60°	638.0	7.9
60°-70°	475.3	5.9
70°-80°	270.8	3.4
80°-90°	81.9	1.0
90°-100°	92.6	1.2
100°-110°	277.2	3.4
110°-120°	471.4	5.9
120°-130°	620.1	7.7
130°-140°	697.0	8.7
140°-150°	685.1	8.5
150°-160°	576.8	7.2
160°-170°	383.9	4.8
170°-180°	134.4	1.7
0°-30°	1185.3	14.7
0°-40°	1907.7	23.7
0°-60°	3272.0	40.7
0°-90°	4099.9	51.0
90°-120°	841.3	10.5
90°-150°	2843.5	35.4
90°-180°	3939.0	49.0
0°-180°	8038.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1574	1574	1574	1574	1574	
5°	1575	1568	1554	1566	1564	149
15°	1500	1494	1476	1486	1479	423
25°	1362	1353	1336	1337	1333	627
35°	1178	1169	1152	1144	1137	736
45°	965	959	942	926	919	745
55°	732	730	713	699	692	656
65°	499	492	479	469	464	493
75°	264	259	254	248	244	282
85°	70	68	68	65	65	77
90°	1	12	27	31	34	8
95°	66	74	83	87	87	74
105°	251	254	264	264	266	269
115°	475	478	476	477	476	469
125°	695	698	696	691	687	619
135°	901	907	907	902	900	694
145°	1093	1096	1099	1098	1093	683
155°	1252	1252	1253	1257	1250	576
165°	1364	1360	1360	1366	1359	384
175°	1418	1414	1414	1420	1413	135
180°	1422	1422	1422	1422	1422	



TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1579.4	1578.5	1577.5	1576.6	1575.5	1573.7	1571.2	1568.5	1565.8	1563.1	1565.6
5°	1575.4	1573.9	1572.4	1570.9	1569.3	1566.9	1563.7	1560.3	1557.0	1553.7	1556.7
7.5°	1560.0	1558.4	1556.9	1555.4	1553.9	1551.4	1548.0	1544.6	1541.2	1537.7	1540.4
10°	1547.0	1545.4	1543.9	1542.4	1540.9	1538.3	1534.3	1530.4	1526.5	1522.6	1525.3
12.5°	1529.7	1528.4	1527.1	1525.9	1524.6	1522.1	1518.5	1514.8	1511.1	1507.4	1509.4
15°	1499.6	1498.4	1497.2	1496.0	1494.8	1492.2	1488.3	1484.4	1480.5	1476.5	1478.9
17.5°	1464.6	1463.1	1461.5	1460.0	1458.4	1455.7	1451.7	1447.9	1443.9	1440.0	1441.7
20°	1438.6	1436.8	1435.0	1433.2	1431.5	1428.6	1424.7	1420.8	1416.9	1413.0	1414.2
22.5°	1409.5	1407.6	1405.8	1404.0	1402.2	1399.4	1395.4	1391.5	1387.7	1383.7	1384.7
25°	1361.5	1359.7	1357.9	1356.1	1354.4	1351.4	1347.6	1343.7	1339.7	1335.8	1336.1
27.5°	1310.4	1308.6	1306.9	1305.1	1303.4	1300.5	1296.2	1292.0	1287.8	1283.6	1283.8
30°	1273.6	1272.0	1270.6	1269.0	1267.6	1264.7	1260.5	1256.3	1252.1	1247.8	1247.8
32.5°	1236.7	1234.8	1232.8	1230.8	1228.8	1226.2	1223.0	1219.7	1216.4	1213.2	1211.5
35°	1177.5	1175.7	1173.9	1172.1	1170.3	1167.4	1163.5	1159.6	1155.6	1151.8	1150.0
37.5°	1116.8	1114.6	1112.2	1110.0	1107.7	1104.6	1100.6	1096.7	1092.7	1088.6	1086.5
40°	1074.6	1072.8	1071.0	1069.2	1067.4	1064.4	1060.1	1055.9	1051.7	1047.6	1045.2
42.5°	1032.3	1030.4	1028.3	1026.2	1024.2	1021.1	1016.8	1012.6	1008.4	1004.3	1001.9
45°	965.0	963.8	962.6	961.4	960.2	957.6	953.7	949.8	945.9	941.9	938.4
47.5°	898.1	896.4	894.7	892.9	891.1	888.5	884.8	881.1	877.4	873.7	870.2
50°	852.6	851.2	849.6	848.2	846.6	844.0	840.0	836.1	832.2	828.3	825.0
52.5°	805.0	804.0	803.0	801.9	800.9	798.3	794.2	790.1	785.9	781.7	778.9
55°	732.2	731.9	731.6	731.3	731.0	728.9	725.0	721.1	717.1	713.3	710.0
57.5°	662.9	661.9	660.8	659.9	658.8	656.8	653.6	650.5	647.4	644.2	641.3
60°	613.1	612.8	612.5	612.2	611.9	609.9	606.3	602.7	599.1	595.5	592.8
62.5°	568.7	567.9	567.1	566.4	565.6	563.4	559.7	556.1	552.6	549.0	546.2
65°	499.4	497.9	496.4	494.9	493.4	491.1	488.1	485.1	482.1	479.1	476.7
67.5°	426.0	424.7	423.4	422.1	420.8	419.0	416.6	414.4	412.1	409.8	407.7
70°	381.7	379.9	378.1	376.3	374.4	372.6	370.8	369.0	367.2	365.4	363.3
72.5°	335.1	333.8	332.4	331.1	329.8	328.1	326.1	324.0	322.0	319.9	318.1
75°	263.9	262.7	261.5	260.3	259.1	258.0	257.2	256.2	255.4	254.4	253.0
77.5°	200.9	200.2	199.5	198.9	198.2	197.3	196.2	195.2	194.1	193.0	192.0
80°	159.7	158.8	157.9	157.0	156.1	155.3	154.7	154.1	153.5	152.9	152.7
82.5°	119.7	119.4	119.2	119.1	118.9	118.7	118.6	118.6	118.4	118.3	117.8
85°	70.3	69.7	69.1	68.5	67.9	67.7	67.7	67.7	67.7	67.7	67.1
87.5°	28.4	28.2	27.9	27.7	27.5	27.6	28.0	28.4	28.8	29.2	29.1
90°	1.1	3.6	6.1	8.5	11.0	13.9	17.1	20.3	23.6	26.8	27.8
92.5°	27.0	28.7	30.4	32.1	33.8	35.6	37.4	39.2	41.1	42.9	43.7
95°	65.9	67.6	69.4	71.1	72.8	74.7	76.7	78.7	80.7	82.7	83.6
97.5°	117.0	118.3	119.6	120.9	122.2	123.6	125.0	126.4	127.9	129.3	130.4
100°	151.9	153.3	154.8	156.4	157.8	159.2	160.4	161.7	162.9	164.2	164.9
102.5°	192.1	193.0	193.9	194.8	195.6	196.9	198.5	200.2	201.8	203.5	204.2
105°	251.2	251.8	252.3	252.7	253.2	254.6	256.8	259.1	261.3	263.6	263.6
107.5°	320.0	320.4	320.6	321.0	321.2	321.8	322.7	323.6	324.5	325.4	326.2
110°	362.9	363.4	363.9	364.4	364.9	365.4	365.9	366.4	366.9	367.4	368.4



TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.6	407.9	408.2	408.5	408.8	409.0	409.1	409.1	409.3	409.4	410.6
115°	474.6	475.4	476.0	476.8	477.6	477.7	477.2	476.7	476.2	475.7	476.0
117.5°	542.1	542.5	543.0	543.5	544.1	544.0	543.3	542.7	542.0	541.4	541.3
120°	584.0	585.5	587.0	588.5	590.0	590.1	588.8	587.6	586.4	585.1	584.9
122.5°	627.8	628.9	630.0	631.1	632.1	632.4	631.7	631.1	630.4	629.8	629.1
125°	694.6	695.3	696.0	696.8	697.6	697.7	697.2	696.7	696.2	695.7	694.7
127.5°	756.2	757.9	759.4	761.0	762.6	763.1	762.6	762.0	761.5	761.0	759.5
130°	797.3	799.3	801.3	803.3	805.3	805.9	805.1	804.4	803.7	802.9	801.9
132.5°	838.4	840.4	842.4	844.4	846.4	847.1	846.5	846.0	845.4	844.9	843.7
135°	901.2	902.7	904.1	905.6	907.1	907.8	907.5	907.2	907.0	906.7	905.8
137.5°	959.2	960.4	961.7	962.9	964.2	965.2	965.8	966.5	967.1	967.8	966.6
140°	999.4	1000.7	1001.9	1003.2	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9
142.5°	1036.0	1037.3	1038.5	1039.8	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4
145°	1093.2	1093.7	1094.2	1094.8	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5
147.5°	1143.2	1144.2	1145.0	1146.0	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4
150°	1178.1	1178.6	1179.1	1179.6	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6
152.5°	1206.7	1207.4	1208.1	1208.8	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6
155°	1251.8	1251.8	1251.8	1251.8	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0
157.5°	1290.2	1290.0	1289.6	1289.3	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8
160°	1314.3	1313.9	1313.4	1312.9	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4
162.5°	1335.8	1335.1	1334.4	1333.7	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8
165°	1363.5	1362.7	1362.0	1361.2	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6
167.5°	1385.6	1384.6	1383.6	1382.6	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5
170°	1398.1	1397.1	1396.1	1395.2	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3
172.5°	1407.9	1407.0	1405.9	1405.0	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0
175°	1418.2	1417.2	1416.3	1415.2	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2
177.5°	1422.5	1421.7	1420.8	1420.0	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0	1574.0
2.5°	1568.0	1570.4	1572.8	1573.9	1573.6	1573.4	1573.1	1573.0
5°	1559.7	1562.7	1565.7	1566.9	1566.3	1565.7	1565.1	1564.5
7.5°	1543.2	1545.8	1548.6	1549.7	1549.4	1549.0	1548.7	1548.3
10°	1528.0	1530.7	1533.4	1534.5	1533.9	1533.3	1532.7	1532.1
12.5°	1511.4	1513.4	1515.4	1516.2	1515.8	1515.4	1515.1	1514.8
15°	1481.4	1483.8	1486.2	1486.5	1484.7	1482.9	1481.1	1479.3
17.5°	1443.4	1445.1	1446.7	1447.3	1446.7	1446.0	1445.3	1444.7
20°	1415.4	1416.6	1417.8	1417.9	1417.0	1416.1	1415.2	1414.3
22.5°	1385.7	1386.6	1387.6	1387.5	1386.4	1385.2	1384.1	1382.9
25°	1336.4	1336.7	1337.0	1336.7	1335.8	1334.9	1334.0	1333.1
27.5°	1284.1	1284.3	1284.5	1284.1	1283.0	1281.8	1280.7	1279.5
30°	1247.8	1247.8	1247.8	1246.8	1244.7	1242.6	1240.4	1238.4
32.5°	1209.8	1208.2	1206.4	1205.1	1203.9	1202.7	1201.6	1200.5
35°	1148.1	1146.3	1144.5	1142.9	1141.3	1139.9	1138.3	1136.9
37.5°	1084.3	1082.2	1080.0	1078.5	1077.5	1076.5	1075.6	1074.6
40°	1042.8	1040.3	1037.9	1036.1	1034.9	1033.7	1032.5	1031.3
42.5°	999.4	997.0	994.6	992.8	991.6	990.4	989.2	988.0
45°	934.8	931.2	927.6	925.0	923.5	922.0	920.5	918.9
47.5°	866.7	863.2	859.5	857.1	855.8	854.5	853.2	851.9
50°	821.7	818.4	815.0	812.5	810.7	808.9	807.1	805.3
52.5°	776.1	773.3	770.4	768.1	766.3	764.5	762.7	760.9
55°	706.6	703.4	700.0	697.6	696.1	694.6	693.1	691.6
57.5°	638.3	635.4	632.4	630.1	628.4	626.6	624.8	623.1
60°	590.1	587.4	584.7	582.6	581.1	579.5	578.1	576.5
62.5°	543.5	540.8	538.1	536.2	535.2	534.2	533.2	532.2
65°	474.3	471.9	469.5	467.9	466.9	466.1	465.1	464.3
67.5°	405.6	403.5	401.4	399.7	398.5	397.2	395.9	394.7
70°	361.2	359.1	357.0	355.2	353.7	352.1	350.7	349.2
72.5°	316.2	314.4	312.5	311.2	310.4	309.6	308.8	308.1
75°	251.4	249.9	248.4	247.2	246.3	245.4	244.5	243.6
77.5°	191.0	189.9	188.9	188.4	188.4	188.4	188.4	188.4
80°	152.3	152.1	151.7	151.6	151.6	151.6	151.6	151.6
82.5°	117.2	116.7	116.1	115.7	115.5	115.3	115.0	114.8
85°	66.5	65.9	65.3	65.0	65.0	65.0	65.0	65.0
87.5°	29.1	29.0	29.0	29.0	29.1	29.3	29.4	29.4
90°	28.8	29.8	30.7	31.5	32.0	32.5	33.0	33.5
92.5°	44.4	45.3	46.1	46.3	46.0	45.7	45.4	45.1
95°	84.6	85.6	86.6	87.1	87.1	87.1	87.1	87.1
97.5°	131.6	132.8	133.9	134.4	134.3	134.2	134.1	134.0
100°	165.7	166.3	167.1	167.7	168.2	168.8	169.3	169.7
102.5°	204.9	205.7	206.5	206.7	206.6	206.6	206.5	206.4
105°	263.6	263.6	263.6	263.8	264.3	264.8	265.3	265.8
107.5°	327.0	327.8	328.6	328.8	328.6	328.2	328.0	327.6
110°	369.4	370.4	371.3	371.6	371.1	370.7	370.1	369.6





TEST NUMBER: P332233-935

CATALOG NUMBER: S123DIW-S1165D1320U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	411.7	412.9	414.1	414.7	414.6	414.5	414.4	414.3
115°	476.2	476.5	476.7	476.7	476.5	476.2	476.0	475.7
117.5°	541.3	541.2	541.1	540.8	540.1	539.4	538.7	538.0
120°	584.6	584.4	584.2	583.8	583.3	582.8	582.3	581.8
122.5°	628.5	627.8	627.2	626.5	625.9	625.2	624.5	623.8
125°	693.7	692.8	691.7	690.8	689.7	688.7	687.8	686.7
127.5°	758.1	756.7	755.4	754.1	752.9	751.8	750.7	749.5
130°	800.9	800.0	798.9	797.5	795.8	794.1	792.4	790.7
132.5°	842.5	841.3	840.2	838.9	837.5	836.2	834.8	833.5
135°	904.7	903.8	902.8	902.1	901.6	901.0	900.5	900.1
137.5°	965.6	964.6	963.5	962.6	961.7	960.7	959.8	958.8
140°	1005.6	1005.4	1005.1	1004.2	1002.5	1000.7	998.9	997.2
142.5°	1043.2	1042.9	1042.7	1041.9	1040.5	1039.2	1037.8	1036.6
145°	1098.3	1098.1	1097.9	1097.3	1096.2	1095.2	1094.2	1093.2
147.5°	1150.4	1150.4	1150.4	1149.7	1148.2	1146.7	1145.2	1143.8
150°	1182.6	1182.6	1182.6	1181.8	1180.3	1178.9	1177.3	1175.9
152.5°	1211.9	1212.4	1212.7	1212.3	1211.0	1209.7	1208.4	1207.1
155°	1254.9	1255.9	1256.9	1256.5	1254.8	1253.1	1251.3	1249.6
157.5°	1291.8	1292.9	1294.0	1293.7	1292.4	1291.0	1289.6	1288.2
160°	1314.6	1315.9	1317.1	1317.2	1316.2	1315.3	1314.2	1313.2
162.5°	1336.0	1337.3	1338.5	1338.3	1336.8	1335.2	1333.6	1332.0
165°	1363.1	1364.6	1366.1	1366.0	1364.3	1362.5	1360.7	1359.0
167.5°	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0
170°	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6
172.5°	1406.5	1408.1	1409.6	1409.5	1407.8	1406.0	1404.3	1402.6
175°	1416.7	1418.2	1419.7	1419.5	1417.8	1416.1	1414.4	1412.6
177.5°	1421.3	1422.5	1423.7	1423.6	1422.1	1420.7	1419.4	1418.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6

(END OF REPORT)