

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332186-830

Luminaire Tested: **S123DIW-S1000D755U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332186-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6845.1 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	54	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14249	14249	14249	14249
5°	16993	14311	12682	14311
10°	21270	14238	11455	14238
15°	26088	14123	10664	14123
20°	31078	13945	10153	13945
25°	32999	13726	10041	13726
30°	28285	13569	10092	13569
35°	19671	13341	10198	13341
40°	14816	13078	10166	13078
45°	12301	12683	10036	12683
50°	11020	11879	9945	11879
55°	10303	11012	9822	11012
60°	9664	10107	9722	10107
65°	9085	9212	9411	9212
70°	8519	8195	8960	8195
75°	7627	7178	8218	7178
80°	6676	5883	7073	5883
85°	5224	4273	4755	4273



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.4	1.9
10°-20°	418.2	6.1
20°-30°	701.8	10.3
30°-40°	794.6	11.6
40°-50°	712.6	10.4
50°-60°	575.1	8.4
60°-70°	400.7	5.9
70°-80°	210.6	3.1
80°-90°	54.1	0.8
90°-100°	33.9	0.5
100°-110°	161.8	2.4
110°-120°	388.6	5.7
120°-130°	494.8	7.2
130°-140°	528.7	7.7
140°-150°	494.4	7.2
150°-160°	398.8	5.8
160°-170°	257.4	3.8
170°-180°	88.7	1.3
0°-30°	1250.4	18.3
0°-40°	2045.0	29.9
0°-60°	3332.7	48.7
0°-90°	3998.2	58.4
90°-120°	584.3	8.5
90°-150°	2102.1	30.7
90°-180°	2847.0	41.6
0°-180°	6845.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1573	1324	1174	1324	1573	163
15°	2341	1267	957	1267	2341	676
25°	2778	1156	845	1156	2778	1219
35°	1497	1015	776	1015	1497	973
45°	808	833	659	833	808	640
55°	549	587	523	587	549	493
65°	357	362	370	362	357	355
75°	183	173	198	173	183	196
85°	42	35	38	35	42	51
90°	21	1	21	1	21	12
95°	26	42	26	42	26	22
105°	30	207	30	207	30	70
115°	408	388	408	388	408	377
125°	558	547	558	547	558	498
135°	687	680	687	680	687	530
145°	793	785	793	785	793	495
155°	864	865	864	865	864	398
165°	910	912	910	912	910	257
175°	930	934	930	934	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1404.9	1403.9	1401.3	1403.4	1399.3	1393.6	1393.1	1388.0	1373.1	1372.1	1368.0
5°	1572.7	1567.5	1566.9	1566.3	1557.3	1545.1	1522.0	1520.1	1489.3	1473.9	1455.3
7.5°	1790.0	1792.7	1783.3	1775.1	1747.7	1729.6	1704.8	1673.1	1635.3	1596.9	1571.4
10°	1946.0	1967.2	1940.9	1922.9	1906.2	1874.8	1838.2	1792.7	1747.2	1693.9	1653.5
12.5°	2113.3	2123.6	2118.4	2101.5	2075.6	2027.7	1962.9	1912.8	1870.9	1782.2	1746.3
15°	2341.1	2380.2	2355.2	2297.4	2298.8	2253.2	2168.5	2075.6	2026.2	1948.5	1842.8
17.5°	2583.8	2588.7	2578.0	2529.9	2497.8	2435.2	2357.1	2267.9	2167.9	2074.0	1961.8
20°	2713.1	2709.2	2686.8	2661.7	2606.6	2557.9	2472.6	2373.1	2244.9	2152.5	2030.0
22.5°	2784.9	2778.5	2767.9	2746.9	2701.0	2648.7	2572.1	2463.4	2341.4	2214.1	2072.6
25°	2778.5	2786.8	2788.1	2782.4	2766.4	2734.9	2674.6	2588.0	2466.2	2302.6	2155.1
27.5°	2527.1	2538.9	2573.1	2603.6	2637.5	2672.2	2667.6	2624.6	2534.4	2393.1	2212.8
30°	2275.7	2250.0	2313.5	2393.7	2448.2	2544.4	2598.3	2601.5	2550.8	2429.6	2253.8
32.5°	1926.7	1954.9	1983.0	2081.7	2200.8	2308.9	2416.1	2502.5	2512.3	2431.7	2277.9
35°	1497.0	1532.3	1583.6	1634.9	1763.2	1873.5	2062.1	2226.3	2357.1	2374.5	2280.1
37.5°	1206.4	1223.8	1256.2	1307.7	1391.6	1522.4	1668.3	1875.8	2065.4	2206.4	2212.5
40°	1054.4	1059.6	1096.2	1135.3	1203.2	1311.0	1442.5	1625.9	1852.9	2049.9	2132.0
42.5°	940.6	951.8	967.3	1004.9	1059.0	1140.1	1262.3	1414.0	1622.1	1848.7	2009.3
45°	808.1	821.0	830.6	855.6	894.1	948.6	1034.0	1172.4	1330.9	1565.0	1781.1
47.5°	720.7	721.7	728.9	747.7	773.9	814.8	875.2	964.1	1109.6	1299.5	1521.4
50°	658.1	668.4	670.9	685.6	706.2	736.3	786.4	862.0	981.4	1148.1	1352.1
52.5°	614.0	617.0	624.2	634.9	652.8	676.3	719.6	778.9	872.5	1014.6	1202.2
55°	549.0	549.0	556.1	564.4	574.7	595.9	624.7	668.4	739.5	849.9	1005.0
57.5°	489.0	492.2	497.2	499.7	508.5	522.5	546.6	579.7	632.8	717.7	841.1
60°	448.9	454.8	454.1	459.2	466.9	477.9	498.3	525.3	572.8	640.7	744.7
62.5°	414.1	413.7	413.6	419.7	427.4	437.8	451.2	474.5	514.8	575.0	663.5
65°	356.7	355.3	359.9	363.6	366.3	373.9	384.2	404.7	431.7	476.5	545.2
67.5°	305.6	301.8	304.3	305.6	309.9	315.9	325.6	338.3	359.7	395.8	447.4
70°	270.7	267.5	266.8	268.1	271.9	276.4	283.5	295.7	315.6	344.4	382.3
72.5°	234.8	232.5	232.4	235.3	237.0	240.0	245.0	256.2	271.9	293.6	328.9
75°	183.4	183.4	183.4	184.1	186.0	188.6	192.4	198.2	210.4	225.7	249.5
77.5°	137.5	137.4	136.6	136.5	139.3	140.4	141.4	146.8	153.5	163.9	181.3
80°	107.7	104.5	105.8	107.7	109.1	109.7	111.6	112.9	118.7	124.4	136.6
82.5°	80.0	77.4	77.6	80.6	80.8	81.4	83.4	85.2	87.4	92.7	99.2
85°	42.3	42.3	43.0	43.0	43.6	43.0	44.9	45.5	45.5	48.7	52.6
87.5°	19.5	18.5	18.9	19.4	18.8	19.2	19.6	20.0	20.4	20.7	20.9
90°	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9	17.2	16.7	14.6
92.5°	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7	18.8	17.7	16.2
95°	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7	22.6	21.5	19.8
97.5°	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8	23.6	22.3	33.5
100°	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4	24.1	22.9	46.9
102.5°	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0	41.8	45.6	71.9
105°	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4	124.6	151.9	165.8
107.5°	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4	258.4	278.4	276.3
110°	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7	307.7	312.8	311.1



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0	347.9	347.8	346.1
115°	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2	399.6	398.1	396.7
117.5°	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4	448.2	447.0	446.2
120°	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1	479.8	478.5	478.2
122.5°	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9	511.0	510.2	509.6
125°	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4	555.2	554.9	554.2
127.5°	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2	598.6	598.1	597.4
130°	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5	624.8	624.2	623.6
132.5°	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4	649.8	649.2	648.7
135°	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3	686.7
137.5°	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0	721.2	720.5	720.2
140°	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4	742.7	742.2	741.7
142.5°	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6	763.2	762.7	762.2
145°	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0	791.6	791.4	791.1
147.5°	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4	817.1	816.7	816.4
150°	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9	832.6	832.3	832.0
152.5°	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7	846.1	845.6	845.5
155°	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7	865.0	864.2	864.0
157.5°	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3	881.4	880.4	880.6
160°	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7	890.8	889.9	890.0
162.5°	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3	899.3	898.1	898.3
165°	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7	910.5	909.3	909.5
167.5°	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1	918.1
170°	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1	923.1
172.5°	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0	927.7	926.5	926.3
175°	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9	931.9	930.8	930.7
177.5°	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4	933.4	932.5	932.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1364.9	1360.7	1356.7	1349.5	1343.3	1334.6	1332.0	1329.0	1319.7	1311.5	1305.3
5°	1448.2	1432.9	1410.4	1389.9	1373.2	1350.8	1337.9	1324.5	1305.2	1287.9	1273.8
7.5°	1535.5	1505.2	1470.4	1432.6	1397.5	1363.6	1336.2	1311.9	1285.0	1259.4	1239.5
10°	1604.8	1561.1	1512.4	1459.8	1414.9	1371.3	1334.7	1302.7	1268.0	1237.8	1212.9
12.5°	1683.8	1619.1	1551.9	1488.0	1434.9	1374.4	1330.1	1289.3	1250.1	1213.8	1185.7
15°	1777.3	1695.2	1615.7	1527.8	1447.0	1371.3	1318.7	1267.4	1221.8	1184.7	1148.8
17.5°	1862.5	1769.4	1664.6	1557.8	1460.3	1370.6	1296.9	1238.9	1181.9	1136.4	1100.6
20°	1910.7	1804.9	1686.2	1575.3	1467.5	1367.4	1286.7	1217.4	1155.7	1107.7	1067.2
22.5°	1952.3	1828.4	1705.7	1587.1	1467.0	1359.2	1267.6	1196.4	1129.6	1082.5	1039.5
25°	1995.4	1847.2	1724.1	1584.9	1450.9	1339.3	1236.6	1155.7	1089.1	1034.0	989.7
27.5°	2032.3	1846.0	1699.8	1550.1	1425.4	1313.5	1204.0	1117.3	1046.5	986.6	941.7
30°	2056.9	1848.5	1674.7	1526.5	1400.8	1285.3	1178.8	1091.7	1017.3	956.3	914.0
32.5°	2072.4	1846.9	1651.6	1493.6	1361.8	1259.7	1151.7	1061.4	985.0	925.0	884.2
35°	2081.3	1835.7	1611.8	1425.8	1298.8	1199.4	1109.0	1015.3	935.2	879.4	833.2
37.5°	2063.3	1811.9	1565.7	1360.4	1221.3	1123.4	1047.4	967.6	890.9	829.4	789.7
40°	2035.1	1796.6	1529.7	1314.2	1168.0	1073.7	1008.9	930.7	855.0	796.6	759.4
42.5°	1981.2	1765.2	1490.3	1262.9	1112.6	1018.2	958.7	893.2	821.6	766.9	729.6
45°	1849.7	1697.1	1431.0	1185.9	1030.7	933.2	880.6	833.2	768.4	715.1	683.1
47.5°	1667.4	1594.6	1345.3	1104.8	945.3	851.5	796.8	758.7	711.3	668.4	637.5
50°	1540.6	1510.5	1287.2	1049.3	888.3	796.6	744.0	709.4	675.4	632.4	604.2
52.5°	1394.4	1413.0	1219.6	991.8	830.4	740.2	690.7	663.2	632.3	597.0	572.4
55°	1188.5	1255.8	1102.6	895.4	744.0	658.1	611.2	586.8	568.9	542.6	521.4
57.5°	995.7	1081.4	976.1	796.0	659.2	585.0	540.2	513.6	502.1	488.3	471.6
60°	881.3	965.9	885.8	729.2	602.3	531.7	491.9	469.5	458.0	448.4	434.2
62.5°	779.2	864.9	797.5	661.6	546.3	480.9	446.3	424.3	415.4	410.4	398.3
65°	638.9	712.6	667.7	556.1	466.3	408.6	377.1	361.7	353.5	351.5	343.7
67.5°	519.9	576.1	543.4	461.3	390.6	340.7	314.1	301.0	294.5	293.9	288.1
70°	442.0	494.6	469.5	395.1	334.1	295.0	271.9	260.4	256.6	255.9	252.7
72.5°	381.4	418.0	398.1	336.1	289.0	253.4	236.6	224.5	220.1	221.0	218.9
75°	282.2	309.8	298.2	255.2	217.4	194.4	180.2	172.6	168.7	170.6	168.1
77.5°	203.0	220.6	210.1	180.4	157.0	140.3	130.0	125.2	121.8	121.6	120.5
80°	153.3	163.5	157.8	139.8	120.6	106.5	98.1	94.9	93.0	92.4	91.7
82.5°	109.1	117.9	111.1	98.8	85.7	77.2	72.5	68.2	66.8	67.2	66.5
85°	55.1	58.3	55.8	48.1	43.0	39.1	36.6	34.6	33.4	34.0	32.7
87.5°	21.5	21.6	19.7	17.2	15.9	14.1	13.8	12.4	11.8	12.1	11.9
90°	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7	2.3	3.8	5.3
92.5°	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9	12.4	12.1	11.6
95°	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3	36.0	29.7	23.4
97.5°	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0	82.2	79.4	76.5
100°	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3	120.3	123.4	126.5
102.5°	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8	156.1	158.3	160.5
105°	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7	208.4	210.1	211.8
107.5°	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4	263.8	265.1	266.6
110°	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6	300.9	302.1	303.3



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2	336.2	337.3	338.5
115°	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7	388.6	389.6	390.5
117.5°	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7	439.8	440.9	442.1
120°	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2	471.6	473.1	474.4
122.5°	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5	503.6	504.7	505.9
125°	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6	547.8	549.0	550.3
127.5°	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3	590.5	591.7	593.0
130°	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9	617.2	618.4	619.6
132.5°	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4	642.6	643.9	645.1
135°	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4	681.4	682.2	683.2
137.5°	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7	714.8	716.0	717.2
140°	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8	736.8	737.7	738.7
142.5°	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4	757.3	758.3	759.2
145°	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1	786.2	787.3	788.3
147.5°	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2	812.8	813.6	814.3
150°	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9	829.2	829.7	830.2
152.5°	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8	844.0	844.2	844.4
155°	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9	864.6	864.3	863.9
157.5°	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3	881.3	881.2	881.2
160°	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3	891.1	891.0	890.8
162.5°	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7	900.3	899.8	899.5
165°	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1	911.6	911.2	910.7
167.5°	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0	920.3	919.7	919.1
170°	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0	925.3	924.7	924.1
172.5°	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3	928.5	927.7	927.1
175°	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6	932.7	932.0	931.2
177.5°	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6	934.1	933.4	932.8
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1301.7	1298.2	1293.1	1285.3	1279.2	1269.4	1269.4	1271.0	1271.0	1270.5	1269.4
5°	1262.3	1252.6	1241.1	1227.7	1213.5	1199.4	1196.8	1191.8	1187.9	1185.2	1182.0
7.5°	1220.6	1203.5	1186.7	1167.8	1150.7	1136.4	1126.5	1118.3	1113.0	1107.4	1103.3
10°	1192.3	1171.2	1151.3	1131.4	1109.6	1092.3	1081.4	1073.7	1067.9	1062.8	1060.3
12.5°	1159.0	1134.7	1112.9	1093.9	1070.1	1052.3	1041.9	1038.3	1031.5	1020.7	1015.0
15°	1110.2	1087.8	1061.5	1032.6	1021.1	999.3	987.1	981.4	977.5	969.1	966.6
17.5°	1068.6	1039.2	1009.7	988.2	966.7	949.0	942.2	935.0	929.9	923.1	921.1
20°	1035.2	1008.9	981.9	958.8	936.4	917.2	911.4	906.3	901.2	898.0	895.4
22.5°	1001.4	975.1	952.7	931.1	907.2	894.6	888.3	882.7	879.1	876.9	874.3
25°	953.8	930.7	905.7	886.4	867.1	858.8	855.0	851.8	849.2	846.0	845.4
27.5°	911.2	886.0	865.7	847.8	834.0	827.0	823.3	821.7	822.3	823.4	824.2
30°	879.4	856.3	839.6	824.2	811.3	804.9	804.3	804.3	806.9	807.5	808.8
32.5°	850.1	831.1	814.5	799.6	789.9	785.4	787.9	787.9	789.9	791.6	793.9
35°	807.5	790.8	778.0	765.2	756.9	758.7	760.1	761.3	764.5	768.4	771.0
37.5°	766.9	752.3	739.0	729.0	725.2	728.6	731.7	734.4	738.1	741.0	743.7
40°	737.6	726.7	713.9	704.9	706.2	708.1	710.7	713.9	717.1	719.0	721.6
42.5°	710.4	699.0	689.3	681.8	683.6	686.1	687.6	689.3	693.0	696.4	698.0
45°	669.0	660.0	651.0	646.5	647.8	649.1	650.4	652.3	655.5	658.1	658.7
47.5°	622.4	616.1	610.1	605.8	607.8	607.3	609.0	613.0	614.1	615.6	619.2
50°	592.7	586.8	579.9	578.5	578.5	578.5	579.2	584.3	584.3	586.8	589.5
52.5°	559.8	556.1	551.6	549.3	548.3	548.3	550.9	553.6	554.6	558.2	560.7
55°	511.2	507.4	503.5	501.5	500.3	501.5	506.7	507.9	511.2	513.1	515.0
57.5°	460.5	457.6	454.5	453.5	453.2	454.9	457.7	461.6	462.3	468.3	471.2
60°	427.2	422.6	420.1	420.1	418.9	424.6	423.3	429.7	431.0	434.9	439.3
62.5°	392.8	386.7	385.7	385.7	387.6	389.2	391.0	393.8	397.2	402.0	405.5
65°	337.3	334.1	338.7	338.0	336.8	340.5	340.5	343.7	347.6	352.1	359.2
67.5°	284.9	283.2	283.6	283.6	285.6	287.8	289.5	292.4	297.0	301.7	306.3
70°	249.5	251.5	248.3	250.8	252.7	253.4	254.7	258.4	263.6	266.8	271.9
72.5°	215.1	215.0	215.4	216.4	218.3	219.5	220.7	225.2	230.7	233.5	237.6
75°	165.5	164.9	166.7	166.7	169.9	171.3	172.6	174.5	179.6	183.4	186.6
77.5°	120.8	121.6	121.2	123.4	122.5	122.7	126.8	128.7	129.2	136.8	138.5
80°	91.0	92.4	93.0	93.7	94.3	93.0	97.5	99.4	99.4	103.9	107.1
82.5°	65.4	66.2	67.9	68.5	68.6	69.9	70.3	71.7	73.2	75.2	79.4
85°	32.7	34.6	35.3	34.6	35.3	34.0	35.9	36.6	37.2	37.2	37.2
87.5°	11.6	12.5	12.3	13.3	13.2	14.1	14.2	13.3	13.5	15.1	13.2
90°	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9	18.5	19.1	19.6
92.5°	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7	20.7	21.7	22.2
95°	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7	24.7	25.8	26.4
97.5°	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8	26.0	27.2	28.0
100°	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4	26.6	27.8	28.6
102.5°	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0	34.2	30.3	28.6
105°	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4	70.0	42.8	29.3
107.5°	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4	218.4	198.4	178.1
110°	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7	297.6	292.5	278.9



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0	348.1	348.2	345.8
115°	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2	402.7	404.3	405.4
117.5°	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4	450.6	451.9	452.5
120°	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1	482.3	483.5	484.1
122.5°	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9	512.7	513.7	514.2
125°	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4	555.8	556.1	556.4
127.5°	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2	599.6	600.1	600.2
130°	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5	626.0	626.7	626.9
132.5°	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4	651.0	651.7	651.8
135°	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2	688.7	689.2	689.2
137.5°	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0	722.7	723.5	723.7
140°	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4	743.9	744.6	744.8
142.5°	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6	764.1	764.6	764.7
145°	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0	792.3	792.6	792.8
147.5°	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4	817.7	818.0	817.7
150°	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9	833.2	833.5	833.5
152.5°	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7	847.3	847.8	847.7
155°	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7	866.5	867.3	867.2
157.5°	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3	883.2	884.1	884.0
160°	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7	892.7	893.5	893.5
162.5°	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3	901.4	902.4	902.4
165°	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7	912.9	914.2	914.3
167.5°	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6	921.9	923.1	923.1
170°	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6	926.9	928.1	928.1
172.5°	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0	930.2	931.4	931.3
175°	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9	934.1	935.1	935.0
177.5°	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4	935.4	936.4	936.2
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1265.8	1265.4	1268.9	1266.4	1268.9	1265.4	1265.8	1269.4	1270.5	1271.0	1271.0
5°	1178.3	1180.2	1173.7	1173.7	1173.7	1180.2	1178.3	1182.0	1185.2	1187.9	1191.8
7.5°	1100.2	1097.4	1097.7	1094.2	1097.7	1097.4	1100.2	1103.3	1107.4	1113.0	1118.3
10°	1052.5	1048.7	1047.4	1048.0	1047.4	1048.7	1052.5	1060.3	1062.8	1067.9	1073.7
12.5°	1013.0	1012.3	1003.8	1003.9	1003.8	1012.3	1013.0	1015.0	1020.7	1031.5	1038.3
15°	966.6	954.4	953.1	957.0	953.1	954.4	966.6	966.6	969.1	977.5	981.4
17.5°	920.0	913.6	914.0	912.1	914.0	913.6	920.0	921.1	923.1	929.9	935.0
20°	895.4	891.6	890.9	886.4	890.9	891.6	895.4	895.4	898.0	901.2	906.3
22.5°	872.8	871.6	871.9	867.0	871.9	871.6	872.8	874.3	876.9	879.1	882.7
25°	844.7	847.9	845.4	845.4	845.4	847.9	844.7	845.4	846.0	849.2	851.8
27.5°	825.8	825.6	824.3	824.3	824.3	825.6	825.8	824.2	823.4	822.3	821.7
30°	811.3	810.7	812.0	812.0	812.0	810.7	811.3	808.8	807.5	806.9	804.3
32.5°	797.0	797.9	798.1	798.6	798.1	797.9	797.0	793.9	791.6	789.9	787.9
35°	774.8	775.4	777.4	776.1	777.4	775.4	774.8	771.0	768.4	764.5	761.3
37.5°	744.8	747.7	747.1	748.1	747.1	747.7	744.8	743.7	741.0	738.1	734.4
40°	722.2	724.2	723.5	723.5	723.5	724.2	722.2	721.6	719.0	717.1	713.9
42.5°	699.1	700.5	698.9	697.9	698.9	700.5	699.1	698.0	696.4	693.0	689.3
45°	661.3	660.0	661.9	659.3	661.9	660.0	661.3	658.7	658.1	655.5	652.3
47.5°	619.0	620.2	620.8	622.6	620.8	620.2	619.0	619.2	615.6	614.1	613.0
50°	590.7	594.6	594.6	593.9	594.6	594.6	590.7	589.5	586.8	584.3	584.3
52.5°	563.0	564.8	567.4	567.2	567.4	564.8	563.0	560.7	558.2	554.6	553.6
55°	520.2	521.4	522.7	523.4	522.7	521.4	520.2	515.0	513.1	511.2	507.9
57.5°	475.8	475.2	478.3	479.3	478.3	475.2	475.8	471.2	468.3	462.3	461.6
60°	444.5	444.5	449.6	451.6	449.6	444.5	444.5	439.3	434.9	431.0	429.7
62.5°	411.1	413.2	418.3	415.7	418.3	413.2	411.1	405.5	402.0	397.2	393.8
65°	362.4	367.5	366.8	369.5	366.8	367.5	362.4	359.2	352.1	347.6	343.7
67.5°	311.4	314.6	319.2	319.7	319.2	314.6	311.4	306.3	301.7	297.0	292.4
70°	277.1	280.3	282.9	284.7	282.9	280.3	277.1	271.9	266.8	263.6	258.4
72.5°	243.7	245.4	251.6	248.8	251.6	245.4	243.7	237.6	233.5	230.7	225.2
75°	191.1	195.6	199.4	197.6	199.4	195.6	191.1	186.6	183.4	179.6	174.5
77.5°	141.4	145.8	147.6	146.0	147.6	145.8	141.4	138.5	136.8	129.2	128.7
80°	111.6	110.9	114.8	114.1	114.8	110.9	111.6	107.1	103.9	99.4	99.4
82.5°	81.8	81.2	83.0	83.4	83.0	81.2	81.8	79.4	75.2	73.2	71.7
85°	39.8	41.7	39.1	38.5	39.1	41.7	39.8	37.2	37.2	37.2	36.6
87.5°	13.2	13.3	12.8	12.3	12.8	13.3	13.2	13.2	15.1	13.5	13.3
90°	19.9	20.2	20.5	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9
92.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7
95°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7
97.5°	28.1	28.3	28.5	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8
100°	28.7	28.8	28.9	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4
102.5°	28.8	29.1	29.4	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0
105°	29.6	29.9	30.3	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4
107.5°	157.5	137.0	116.4	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4
110°	256.8	234.8	212.7	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.2	336.6	331.9	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0
115°	406.0	406.6	407.2	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2
117.5°	452.7	452.8	452.9	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4
120°	484.1	484.1	484.1	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1
122.5°	514.3	514.3	514.5	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9
125°	556.8	557.0	557.3	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4
127.5°	599.9	599.6	599.3	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2
130°	626.5	626.2	625.9	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5
132.5°	651.3	650.9	650.4	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4
135°	688.7	688.2	687.8	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2
137.5°	723.4	723.0	722.7	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0
140°	744.4	744.1	743.9	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4
142.5°	764.2	763.8	763.4	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6
145°	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0
147.5°	817.1	816.3	815.7	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4
150°	833.0	832.5	832.1	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9
152.5°	847.1	846.3	845.6	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7
155°	866.3	865.3	864.4	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7
157.5°	882.8	881.6	880.4	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3
160°	892.4	891.4	890.2	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7
162.5°	901.4	900.5	899.6	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3
165°	913.2	912.1	911.1	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7
167.5°	921.9	920.6	919.4	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6
170°	926.9	925.6	924.4	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6
172.5°	930.0	928.7	927.3	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0
175°	933.8	932.6	931.3	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9
177.5°	935.0	933.8	932.6	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1269.4	1269.4	1279.2	1285.3	1293.1	1298.2	1301.7	1305.3	1311.5	1319.7	1329.0
5°	1196.8	1199.4	1213.5	1227.7	1241.1	1252.6	1262.3	1273.8	1287.9	1305.2	1324.5
7.5°	1126.5	1136.4	1150.7	1167.8	1186.7	1203.5	1220.6	1239.5	1259.4	1285.0	1311.9
10°	1081.4	1092.3	1109.6	1131.4	1151.3	1171.2	1192.3	1212.9	1237.8	1268.0	1302.7
12.5°	1041.9	1052.3	1070.1	1093.9	1112.9	1134.7	1159.0	1185.7	1213.8	1250.1	1289.3
15°	987.1	999.3	1021.1	1032.6	1061.5	1087.8	1110.2	1148.8	1184.7	1221.8	1267.4
17.5°	942.2	949.0	966.7	988.2	1009.7	1039.2	1068.6	1100.6	1136.4	1181.9	1238.9
20°	911.4	917.2	936.4	958.8	981.9	1008.9	1035.2	1067.2	1107.7	1155.7	1217.4
22.5°	888.3	894.6	907.2	931.1	952.7	975.1	1001.4	1039.5	1082.5	1129.6	1196.4
25°	855.0	858.8	867.1	886.4	905.7	930.7	953.8	989.7	1034.0	1089.1	1155.7
27.5°	823.3	827.0	834.0	847.8	865.7	886.0	911.2	941.7	986.6	1046.5	1117.3
30°	804.3	804.9	811.3	824.2	839.6	856.3	879.4	914.0	956.3	1017.3	1091.7
32.5°	787.9	785.4	789.9	799.6	814.5	831.1	850.1	884.2	925.0	985.0	1061.4
35°	760.1	758.7	756.9	765.2	778.0	790.8	807.5	833.2	879.4	935.2	1015.3
37.5°	731.7	728.6	725.2	729.0	739.0	752.3	766.9	789.7	829.4	890.9	967.6
40°	710.7	708.1	706.2	704.9	713.9	726.7	737.6	759.4	796.6	855.0	930.7
42.5°	687.6	686.1	683.6	681.8	689.3	699.0	710.4	729.6	766.9	821.6	893.2
45°	650.4	649.1	647.8	646.5	651.0	660.0	669.0	683.1	715.1	768.4	833.2
47.5°	609.0	607.3	607.8	605.8	610.1	616.1	622.4	637.5	668.4	711.3	758.7
50°	579.2	578.5	578.5	578.5	579.9	586.8	592.7	604.2	632.4	675.4	709.4
52.5°	550.9	548.3	548.3	549.3	551.6	556.1	559.8	572.4	597.0	632.3	663.2
55°	506.7	501.5	500.3	501.5	503.5	507.4	511.2	521.4	542.6	568.9	586.8
57.5°	457.7	454.9	453.2	453.5	454.5	457.6	460.5	471.6	488.3	502.1	513.6
60°	423.3	424.6	418.9	420.1	420.1	422.6	427.2	434.2	448.4	458.0	469.5
62.5°	391.0	389.2	387.6	385.7	385.7	386.7	392.8	398.3	410.4	415.4	424.3
65°	340.5	340.5	336.8	338.0	338.7	334.1	337.3	343.7	351.5	353.5	361.7
67.5°	289.5	287.8	285.6	283.6	283.6	283.2	284.9	288.1	293.9	294.5	301.0
70°	254.7	253.4	252.7	250.8	248.3	251.5	249.5	252.7	255.9	256.6	260.4
72.5°	220.7	219.5	218.3	216.4	215.4	215.0	215.1	218.9	221.0	220.1	224.5
75°	172.6	171.3	169.9	166.7	166.7	164.9	165.5	168.1	170.6	168.7	172.6
77.5°	126.8	122.7	122.5	123.4	121.2	121.6	120.8	120.5	121.6	121.8	125.2
80°	97.5	93.0	94.3	93.7	93.0	92.4	91.0	91.7	92.4	93.0	94.9
82.5°	70.3	69.9	68.6	68.5	67.9	66.2	65.4	66.5	67.2	66.8	68.2
85°	35.9	34.0	35.3	34.6	35.3	34.6	32.7	32.7	34.0	33.4	34.6
87.5°	14.2	14.1	13.2	13.3	12.3	12.5	11.6	11.9	12.1	11.8	12.4
90°	17.2	16.7	14.6	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7
92.5°	18.8	17.7	16.2	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9
95°	22.6	21.5	19.8	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3
97.5°	23.6	22.3	33.5	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0
100°	24.1	22.9	46.9	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3
102.5°	41.8	45.6	71.9	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8
105°	124.6	151.9	165.8	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7
107.5°	258.4	278.4	276.3	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4
110°	307.7	312.8	311.1	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.9	347.8	346.1	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2
115°	399.6	398.1	396.7	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7
117.5°	448.2	447.0	446.2	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7
120°	479.8	478.5	478.2	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2
122.5°	511.0	510.2	509.6	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5
125°	555.2	554.9	554.2	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6
127.5°	598.6	598.1	597.4	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3
130°	624.8	624.2	623.6	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9
132.5°	649.8	649.2	648.7	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4
135°	687.8	687.3	686.7	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4
137.5°	721.2	720.5	720.2	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7
140°	742.7	742.2	741.7	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8
142.5°	763.2	762.7	762.2	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4
145°	791.6	791.4	791.1	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1
147.5°	817.1	816.7	816.4	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2
150°	832.6	832.3	832.0	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9
152.5°	846.1	845.6	845.5	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8
155°	865.0	864.2	864.0	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9
157.5°	881.4	880.4	880.6	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3
160°	890.8	889.9	890.0	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3
162.5°	899.3	898.1	898.3	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7
165°	910.5	909.3	909.5	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1
167.5°	919.4	918.1	918.1	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0
170°	924.4	923.1	923.1	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0
172.5°	927.7	926.5	926.3	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3
175°	931.9	930.8	930.7	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6
177.5°	933.4	932.5	932.4	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1332.0	1334.6	1343.3	1349.5	1356.7	1360.7	1364.9	1368.0	1372.1	1373.1	1388.0
5°	1337.9	1350.8	1373.2	1389.9	1410.4	1432.9	1448.2	1455.3	1473.9	1489.3	1520.1
7.5°	1336.2	1363.6	1397.5	1432.6	1470.4	1505.2	1535.5	1571.4	1596.9	1635.3	1673.1
10°	1334.7	1371.3	1414.9	1459.8	1512.4	1561.1	1604.8	1653.5	1693.9	1747.2	1792.7
12.5°	1330.1	1374.4	1434.9	1488.0	1551.9	1619.1	1683.8	1746.3	1782.2	1870.9	1912.8
15°	1318.7	1371.3	1447.0	1527.8	1615.7	1695.2	1777.3	1842.8	1948.5	2026.2	2075.6
17.5°	1296.9	1370.6	1460.3	1557.8	1664.6	1769.4	1862.5	1961.8	2074.0	2167.9	2267.9
20°	1286.7	1367.4	1467.5	1575.3	1686.2	1804.9	1910.7	2030.0	2152.5	2244.9	2373.1
22.5°	1267.6	1359.2	1467.0	1587.1	1705.7	1828.4	1952.3	2072.6	2214.1	2341.4	2463.4
25°	1236.6	1339.3	1450.9	1584.9	1724.1	1847.2	1995.4	2155.1	2302.6	2466.2	2588.0
27.5°	1204.0	1313.5	1425.4	1550.1	1699.8	1846.0	2032.3	2212.8	2393.1	2534.4	2624.6
30°	1178.8	1285.3	1400.8	1526.5	1674.7	1848.5	2056.9	2253.8	2429.6	2550.8	2601.5
32.5°	1151.7	1259.7	1361.8	1493.6	1651.6	1846.9	2072.4	2277.9	2431.7	2512.3	2502.5
35°	1109.0	1199.4	1298.8	1425.8	1611.8	1835.7	2081.3	2280.1	2374.5	2357.1	2226.3
37.5°	1047.4	1123.4	1221.3	1360.4	1565.7	1811.9	2063.3	2212.5	2206.4	2065.4	1875.8
40°	1008.9	1073.7	1168.0	1314.2	1529.7	1796.6	2035.1	2132.0	2049.9	1852.9	1625.9
42.5°	958.7	1018.2	1112.6	1262.9	1490.3	1765.2	1981.2	2009.3	1848.7	1622.1	1414.0
45°	880.6	933.2	1030.7	1185.9	1431.0	1697.1	1849.7	1781.1	1565.0	1330.9	1172.4
47.5°	796.8	851.5	945.3	1104.8	1345.3	1594.6	1667.4	1521.4	1299.5	1109.6	964.1
50°	744.0	796.6	888.3	1049.3	1287.2	1510.5	1540.6	1352.1	1148.1	981.4	862.0
52.5°	690.7	740.2	830.4	991.8	1219.6	1413.0	1394.4	1202.2	1014.6	872.5	778.9
55°	611.2	658.1	744.0	895.4	1102.6	1255.8	1188.5	1005.0	849.9	739.5	668.4
57.5°	540.2	585.0	659.2	796.0	976.1	1081.4	995.7	841.1	717.7	632.8	579.7
60°	491.9	531.7	602.3	729.2	885.8	965.9	881.3	744.7	640.7	572.8	525.3
62.5°	446.3	480.9	546.3	661.6	797.5	864.9	779.2	663.5	575.0	514.8	474.5
65°	377.1	408.6	466.3	556.1	667.7	712.6	638.9	545.2	476.5	431.7	404.7
67.5°	314.1	340.7	390.6	461.3	543.4	576.1	519.9	447.4	395.8	359.7	338.3
70°	271.9	295.0	334.1	395.1	469.5	494.6	442.0	382.3	344.4	315.6	295.7
72.5°	236.6	253.4	289.0	336.1	398.1	418.0	381.4	328.9	293.6	271.9	256.2
75°	180.2	194.4	217.4	255.2	298.2	309.8	282.2	249.5	225.7	210.4	198.2
77.5°	130.0	140.3	157.0	180.4	210.1	220.6	203.0	181.3	163.9	153.5	146.8
80°	98.1	106.5	120.6	139.8	157.8	163.5	153.3	136.6	124.4	118.7	112.9
82.5°	72.5	77.2	85.7	98.8	111.1	117.9	109.1	99.2	92.7	87.4	85.2
85°	36.6	39.1	43.0	48.1	55.8	58.3	55.1	52.6	48.7	45.5	45.5
87.5°	13.8	14.1	15.9	17.2	19.7	21.6	21.5	20.9	20.7	20.4	20.0
90°	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9
92.5°	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7
95°	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7
97.5°	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8
100°	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4
102.5°	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0
105°	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4
107.5°	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4
110°	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0
115°	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2
117.5°	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4
120°	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1
122.5°	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9
125°	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4
127.5°	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2
130°	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5
132.5°	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4
135°	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2
137.5°	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0
140°	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4
142.5°	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6
145°	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0
147.5°	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4
150°	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9
152.5°	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7
155°	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7
157.5°	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3
160°	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7
162.5°	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3
165°	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7
167.5°	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6
170°	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6
172.5°	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0
175°	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9
177.5°	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8	1323.8
2.5°	1393.1	1393.6	1399.3	1403.4	1401.3	1403.9	1404.9
5°	1522.0	1545.1	1557.3	1566.3	1566.9	1567.5	1572.7
7.5°	1704.8	1729.6	1747.7	1775.1	1783.3	1792.7	1790.0
10°	1838.2	1874.8	1906.2	1922.9	1940.9	1967.2	1946.0
12.5°	1962.9	2027.7	2075.6	2101.5	2118.4	2123.6	2113.3
15°	2168.5	2253.2	2298.8	2297.4	2355.2	2380.2	2341.1
17.5°	2357.1	2435.2	2497.8	2529.9	2578.0	2588.7	2583.8
20°	2472.6	2557.9	2606.6	2661.7	2686.8	2709.2	2713.1
22.5°	2572.1	2648.7	2701.0	2746.9	2767.9	2778.5	2784.9
25°	2674.6	2734.9	2766.4	2782.4	2788.1	2786.8	2778.5
27.5°	2667.6	2672.2	2637.5	2603.6	2573.1	2538.9	2527.1
30°	2598.3	2544.4	2448.2	2393.7	2313.5	2250.0	2275.7
32.5°	2416.1	2308.9	2200.8	2081.7	1983.0	1954.9	1926.7
35°	2062.1	1873.5	1763.2	1634.9	1583.6	1532.3	1497.0
37.5°	1668.3	1522.4	1391.6	1307.7	1256.2	1223.8	1206.4
40°	1442.5	1311.0	1203.2	1135.3	1096.2	1059.6	1054.4
42.5°	1262.3	1140.1	1059.0	1004.9	967.3	951.8	940.6
45°	1034.0	948.6	894.1	855.6	830.6	821.0	808.1
47.5°	875.2	814.8	773.9	747.7	728.9	721.7	720.7
50°	786.4	736.3	706.2	685.6	670.9	668.4	658.1
52.5°	719.6	676.3	652.8	634.9	624.2	617.0	614.0
55°	624.7	595.9	574.7	564.4	556.1	549.0	549.0
57.5°	546.6	522.5	508.5	499.7	497.2	492.2	489.0
60°	498.3	477.9	466.9	459.2	454.1	454.8	448.9
62.5°	451.2	437.8	427.4	419.7	413.6	413.7	414.1
65°	384.2	373.9	366.3	363.6	359.9	355.3	356.7
67.5°	325.6	315.9	309.9	305.6	304.3	301.8	305.6
70°	283.5	276.4	271.9	268.1	266.8	267.5	270.7
72.5°	245.0	240.0	237.0	235.3	232.4	232.5	234.8
75°	192.4	188.6	186.0	184.1	183.4	183.4	183.4
77.5°	141.4	140.4	139.3	136.5	136.6	137.4	137.5
80°	111.6	109.7	109.1	107.7	105.8	104.5	107.7
82.5°	83.4	81.4	80.8	80.6	77.6	77.4	80.0
85°	44.9	43.0	43.6	43.0	43.0	42.3	42.3
87.5°	19.6	19.2	18.8	19.4	18.9	18.5	19.5
90°	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332186-830

CATALOG NUMBER: S123DIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)