

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332235-935

Luminaire Tested: **S123DIW-S1165D1535U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332235-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8799.6 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332235-935
CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41		
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	35	35	35		
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30		
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	26	26	26	26	26	26	26		
5	68	57	49	43	63	53	46	41	45	40	35	38	34	30	31	28	26	22	22	22	22	22	22	22		
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20		
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17	17	17	17	17	17	17		
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16	16	16	16	16	16	16		
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	14	14	14	14		
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	13	13	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	1.6
10°-20°	441.2	5.0
20°-30°	740.4	8.4
30°-40°	838.4	9.5
40°-50°	751.8	8.5
50°-60°	606.7	6.9
60°-70°	422.8	4.8
70°-80°	222.2	2.5
80°-90°	59.2	0.7
90°-100°	107.7	1.2
100°-110°	322.3	3.7
110°-120°	548.1	6.2
120°-130°	721.0	8.2
130°-140°	810.4	9.2
140°-150°	796.6	9.1
150°-160°	670.6	7.6
160°-170°	446.4	5.1
170°-180°	156.3	1.8
0°-30°	1319.2	15.0
0°-40°	2157.5	24.5
0°-60°	3516.1	40.0
0°-90°	4220.3	48.0
90°-120°	978.1	11.1
90°-150°	3306.0	37.6
90°-180°	4579.0	52.0
0°-180°	8799.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	54
90°	39	1	39	1	39	21
95°	101	77	101	77	101	104
105°	309	292	309	292	309	328
115°	553	552	553	552	553	548
125°	798	808	798	808	798	714
135°	1046	1048	1046	1048	1046	805
145°	1271	1271	1271	1271	1271	793
155°	1453	1455	1453	1455	1453	669
165°	1580	1585	1580	1585	1580	446
175°	1642	1649	1642	1649	1642	156
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	24.0	22.8	23.2	23.7	23.0	23.4	23.7	24.0	24.4	24.6	24.5
90°	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5	32.3	31.2	27.4
92.5°	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7	50.8	49.9	47.7
95°	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4	97.2	96.1	93.8
97.5°	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0	151.7	150.3	148.7
100°	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6	191.7	190.9	189.4
102.5°	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3	237.5	236.5	234.6
105°	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4	306.4	306.4	303.8
107.5°	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2	379.3	378.3	377.3
110°	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5	428.3	427.1	426.5



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7	477.3	476.0	475.9
115°	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1	553.7
117.5°	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3	629.4	629.5	630.2
120°	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8	680.0	680.4	681.7
122.5°	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7	731.5	732.3	733.1
125°	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6	807.7	808.9	809.4
127.5°	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5	883.0	884.7	885.4
130°	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2	932.4	933.5	934.4
132.5°	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6	980.9	982.3	982.9
135°	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0	1053.1	1054.3	1054.6
137.5°	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7	1123.9	1125.2	1124.4
140°	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9	1213.1	1213.4	1212.9
145°	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9	1277.3	1277.6	1276.7
147.5°	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9	1374.9	1374.9	1374.3
152.5°	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1	1408.7	1408.2	1407.8
155°	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1	1457.9	1456.7	1456.5
157.5°	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0	1500.8	1499.6	1499.3
160°	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4	1527.0	1525.5	1525.5
162.5°	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3	1552.0	1550.5	1550.2
165°	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8	1583.1	1581.4	1581.4
167.5°	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8	1606.6
170°	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3	1620.3
172.5°	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3	1633.6	1631.8	1631.8
175°	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2	1645.5	1643.7	1643.7
177.5°	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4	1651.1	1649.7	1649.7
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	24.8	24.5	22.2	19.4	17.7	15.5	14.9	13.3	12.7	13.3	13.3
90°	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3	4.2	7.1	10.0
92.5°	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4	33.4	35.3	37.3
95°	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6	78.6	80.7	82.7
97.5°	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0	137.6	139.1	140.6
100°	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6	178.3	180.0	181.8
102.5°	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3	224.4	225.4	226.4
105°	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1	292.7	293.3	293.9
107.5°	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1	372.5	372.8	373.2
110°	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0	422.6	423.1	423.7



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9	474.2	474.6	474.9
115°	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8	552.7	553.5	554.4
117.5°	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3	630.8	631.4	632.0
120°	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1	680.8	682.5	684.2
122.5°	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0	731.2	732.5	733.7
125°	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5	808.4	809.3	810.2
127.5°	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3	881.1	883.0	884.8
130°	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0	929.4	931.6	933.9
132.5°	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8	977.1	979.4	981.7
135°	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8	1049.5	1051.2	1052.9
137.5°	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3	1116.7	1118.2	1119.6
140°	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0	1163.5	1164.9	1166.3
142.5°	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6	1206.0	1207.5	1208.9
145°	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1	1271.7	1272.2	1272.8
147.5°	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2	1330.2	1331.3	1332.4
150°	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8	1370.4	1370.9	1371.5
152.5°	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0	1403.8	1404.6	1405.4
155°	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1	1499.8	1499.4	1499.1
160°	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2	1527.6	1527.0	1526.4
162.5°	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1	1552.3	1551.4	1550.7
165°	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3	1584.4	1583.6	1582.7
167.5°	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0	1609.8	1608.7	1607.5
170°	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5	1624.4	1623.2	1622.0
172.5°	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9	1635.8	1634.6	1633.5
175°	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9	1647.8	1646.6	1645.5
177.5°	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8	1652.9	1652.0	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	13.4	14.6	14.8	16.1	16.3	17.6	17.8	17.0	17.2	19.0	17.0
90°	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5	34.6	35.8	36.7
92.5°	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7	52.6	53.6	53.8
95°	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4	99.5	100.7	101.3
97.5°	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0	154.3	155.7	156.3
100°	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6	193.5	194.3	195.0
102.5°	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3	239.2	240.0	240.4
105°	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4	306.4	306.4	306.7
107.5°	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2	381.1	382.0	382.3
110°	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5	430.6	431.8	432.0



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7	480.1	481.5	482.2
115°	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7	554.0	554.2	554.2
117.5°	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3	629.3	629.2	628.8
120°	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8	679.5	679.2	678.7
122.5°	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7	730.0	729.3	728.5
125°	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6	805.4	804.3	803.1
127.5°	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5	879.9	878.2	876.8
130°	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2	930.1	928.9	927.3
132.5°	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6	978.2	976.8	975.3
135°	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0	1050.8	1049.6	1048.8
137.5°	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7	1121.5	1120.3	1119.1
140°	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.5
142.5°	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9	1212.5	1212.3	1211.3
145°	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9	1276.7	1276.4	1275.7
147.5°	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9	1374.9	1374.9	1374.1
152.5°	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1	1409.5	1410.1	1409.5
155°	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1	1460.2	1461.4	1460.9
157.5°	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0	1503.2	1504.4	1504.3
160°	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4	1529.9	1531.3	1531.5
162.5°	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3	1554.8	1556.3	1556.1
165°	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8	1586.6	1588.3	1588.2
167.5°	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9
170°	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4
172.5°	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3	1637.1	1638.9	1638.8
175°	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2	1648.9	1650.6	1650.5
177.5°	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4	1653.8	1655.2	1655.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	17.2	17.3	16.9	16.4	16.9	17.3	17.2	17.0	19.0	17.2	17.0
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5
92.5°	53.5	53.1	52.8	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7
95°	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4
97.5°	156.2	156.0	155.9	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0
100°	195.6	196.2	196.7	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6
102.5°	240.3	240.1	240.0	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3
105°	307.3	307.9	308.4	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4
107.5°	381.9	381.6	381.3	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2
110°	431.4	430.9	430.3	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.1	481.9	481.8	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7
115°	554.0	553.7	553.4	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7
117.5°	627.9	627.2	626.4	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3
120°	678.2	677.6	677.0	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8
122.5°	727.7	726.9	726.1	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7
125°	801.9	800.8	799.6	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6
127.5°	875.5	874.1	872.8	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5
130°	925.3	923.3	921.3	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2
132.5°	973.8	972.2	970.6	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6
135°	1048.2	1047.6	1047.1	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0
137.5°	1118.0	1117.0	1115.9	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7
140°	1165.4	1163.5	1161.4	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2
142.5°	1209.8	1208.2	1206.7	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9
145°	1274.5	1273.4	1272.2	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9
147.5°	1335.0	1333.3	1331.5	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6
150°	1372.3	1370.6	1368.9	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9
152.5°	1408.0	1406.5	1405.0	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1
155°	1458.9	1456.9	1454.8	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1
157.5°	1502.6	1501.0	1499.3	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0
160°	1530.3	1529.1	1528.0	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4
162.5°	1554.2	1552.4	1550.5	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3
165°	1586.1	1584.2	1582.1	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8
167.5°	1612.2	1610.4	1608.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4
170°	1626.4	1624.4	1622.4	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4
172.5°	1636.8	1634.8	1632.7	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3
175°	1648.5	1646.4	1644.4	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2
177.5°	1653.5	1651.8	1650.3	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	17.8	17.6	16.3	16.1	14.8	14.6	13.4	13.3	13.3	12.7	13.3
90°	32.3	31.2	27.4	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3
92.5°	50.8	49.9	47.7	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4
95°	97.2	96.1	93.8	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6
97.5°	151.7	150.3	148.7	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0
100°	191.7	190.9	189.4	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6
102.5°	237.5	236.5	234.6	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3
105°	306.4	306.4	303.8	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1
107.5°	379.3	378.3	377.3	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1
110°	428.3	427.1	426.5	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	477.3	476.0	475.9	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9
115°	553.4	553.1	553.7	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8
117.5°	629.4	629.5	630.2	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3
120°	680.0	680.4	681.7	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1
122.5°	731.5	732.3	733.1	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0
125°	807.7	808.9	809.4	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5
127.5°	883.0	884.7	885.4	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3
130°	932.4	933.5	934.4	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0
132.5°	980.9	982.3	982.9	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8
135°	1053.1	1054.3	1054.6	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8
137.5°	1123.9	1125.2	1124.4	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3
140°	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0
142.5°	1213.1	1213.4	1212.9	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6
145°	1277.3	1277.6	1276.7	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1
147.5°	1337.6	1337.6	1336.7	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2
150°	1374.9	1374.9	1374.3	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8
152.5°	1408.7	1408.2	1407.8	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0
155°	1457.9	1456.7	1456.5	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1500.8	1499.6	1499.3	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1
160°	1527.0	1525.5	1525.5	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2
162.5°	1552.0	1550.5	1550.2	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1
165°	1583.1	1581.4	1581.4	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3
167.5°	1608.6	1606.8	1606.6	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0
170°	1622.4	1620.3	1620.3	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5
172.5°	1633.6	1631.8	1631.8	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9
175°	1645.5	1643.7	1643.7	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9
177.5°	1651.1	1649.7	1649.7	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.9	15.5	17.7	19.4	22.2	24.5	24.8	24.5	24.6	24.4	24.0
90°	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5
92.5°	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7
95°	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4
97.5°	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0
100°	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6
102.5°	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3
105°	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4
107.5°	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2
110°	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7
115°	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7
117.5°	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3
120°	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8
122.5°	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7
125°	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6
127.5°	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5
130°	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2
132.5°	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6
135°	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0
137.5°	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7
140°	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2
142.5°	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9
145°	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9
147.5°	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6
150°	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9
152.5°	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1
155°	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1
157.5°	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0
160°	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4
162.5°	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3
165°	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8
167.5°	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4
170°	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4
172.5°	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3
175°	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2
177.5°	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	23.7	23.4	23.0	23.7	23.2	22.8	24.0
90°	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	430.6	431.8	432.0	431.4	430.9	430.3	429.7



TEST NUMBER: P332235-935

CATALOG NUMBER: S123DIW-S1165D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)