

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332226-830

Luminaire Tested: **S123DIW-S1165D1030U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332226-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1030U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8373.0 lumens  
Efficiency: N/A  
Efficacy: 124.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.3	1.9
10°-20°	458.3	5.5
20°-30°	677.0	8.1
30°-40°	790.8	9.4
40°-50°	795.1	9.5
50°-60°	698.4	8.3
60°-70°	520.3	6.2
70°-80°	296.4	3.5
80°-90°	88.7	1.1
90°-100°	46.3	0.6
100°-110°	220.8	2.6
110°-120°	530.4	6.3
120°-130°	675.4	8.1
130°-140°	721.6	8.6
140°-150°	674.8	8.1
150°-160°	544.3	6.5
160°-170°	351.3	4.2
170°-180°	121.1	1.4
0°-30°	1297.6	15.5
0°-40°	2088.4	24.9
0°-60°	3581.8	42.8
0°-90°	4487.2	53.6
90°-120°	797.5	9.5
90°-150°	2869.2	34.3
90°-180°	3886.0	46.4
0°-180°	8373.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	11	23	26	28	7
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	529	535	543	553	557	522
125°	746	753	757	759	761	666
135°	929	934	938	941	938	715
145°	1072	1078	1080	1082	1082	671
155°	1180	1179	1180	1184	1179	544
165°	1245	1242	1241	1248	1242	352
175°	1274	1270	1270	1276	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.0	30.6	30.3	29.9	29.5	29.5	29.8	30.1	30.3	30.6	30.5
90°	0.9	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6
92.5°	17.6	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5
95°	57.8	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8
97.5°	116.0	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1
100°	159.9	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9
102.5°	210.0	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1
105°	282.1	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1
107.5°	358.3	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7
110°	409.0	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0



TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.4	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8
115°	529.2	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5
117.5°	598.7	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7
120°	641.9	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9
122.5°	685.8	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6
125°	746.0	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8
127.5°	804.3	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1
130°	840.7	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9
132.5°	875.5	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9
135°	928.7	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8
137.5°	974.1	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4
140°	1004.5	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8
142.5°	1032.5	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7
145°	1071.7	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6
147.5°	1108.6	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2
150°	1131.3	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4
152.5°	1151.8	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0
155°	1180.5	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6
157.5°	1202.9	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0
160°	1216.5	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9
162.5°	1229.4	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4
165°	1244.9	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8
167.5°	1257.0	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9
170°	1263.9	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7
172.5°	1268.4	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3
175°	1274.2	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0
177.5°	1275.7	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	30.4	30.3	30.3	30.3	30.3	30.4	30.4	30.5
90°	24.4	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	27.0	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	32.3	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	34.6	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	51.8	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	325.4	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	413.1	406.1	399.2	380.7	350.6	320.5	290.4	260.3





TEST NUMBER: P332226-830

CATALOG NUMBER: S123DIW-S1165D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	474.9	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	547.6	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	613.4	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	656.6	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	698.7	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.2	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	817.7	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	853.8	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	887.8	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	985.4	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1014.6	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1042.4	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.0	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1115.7	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1136.9	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1155.7	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1181.7	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1204.3	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1217.1	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1228.8	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1244.4	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1268.0	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1273.4	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1275.4	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)