

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332216-935

Luminaire Tested: **S123DIW-S1165D755U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332216-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D755U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 755 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6818.4 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	59	57	53
2	92	85	79	73	86	80	74	70	70	66	62	61	58	55	53	51	49	45
3	84	75	67	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	42	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	35	38	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.6	2.0
10°-20°	441.2	6.5
20°-30°	740.4	10.9
30°-40°	838.4	12.3
40°-50°	751.8	11.0
50°-60°	606.7	8.9
60°-70°	422.8	6.2
70°-80°	222.2	3.3
80°-90°	56.7	0.8
90°-100°	31.0	0.5
100°-110°	147.8	2.2
110°-120°	355.0	5.2
120°-130°	452.0	6.6
130°-140°	482.9	7.1
140°-150°	451.6	6.6
150°-160°	364.3	5.3
160°-170°	235.1	3.4
170°-180°	81.0	1.2
0°-30°	1319.2	19.3
0°-40°	2157.5	31.6
0°-60°	3516.1	51.6
0°-90°	4217.8	61.9
90°-120°	533.7	7.8
90°-150°	1920.2	28.2
90°-180°	2601.0	38.1
0°-180°	6818.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	53
90°	19	1	19	1	19	11
95°	24	39	24	39	24	20
105°	28	189	28	189	28	64
115°	373	354	373	354	373	344
125°	509	499	509	499	509	455
135°	628	622	628	622	628	484
145°	724	717	724	717	724	452
155°	789	790	789	790	789	364
165°	831	833	831	833	831	235
175°	850	853	850	853	850	81
180°	853	853	853	853	853	



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	20.1	18.9	19.4	19.9	19.3	19.7	20.1	20.6	21.0	21.4	21.6
90°	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4	15.8	15.2	13.3
92.5°	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0	17.1	16.2	14.8
95°	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6	20.7	19.6	18.1
97.5°	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6	21.5	20.4	30.6
100°	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2	22.0	20.9	42.9
102.5°	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7	38.2	41.7	65.7
105°	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9	113.8	138.8	151.4
107.5°	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7	236.0	254.3	252.4
110°	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5	281.1	285.8	284.2



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9	317.8	317.7	316.2
115°	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5	365.1	363.7	362.4
117.5°	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5	409.4	408.3	407.6
120°	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5	438.3	437.1	436.8
122.5°	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6	466.8	466.1	465.5
125°	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4	507.1	506.9	506.3
127.5°	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3	546.8	546.4	545.7
130°	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4	570.8	570.2	569.6
132.5°	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2	593.6	593.1	592.5
135°	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7	628.3	627.8	627.3
137.5°	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5	658.8	658.1	657.9
140°	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1	678.5	678.0	677.5
142.5°	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6	697.2	696.7	696.3
145°	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5	723.2	722.9	722.6
147.5°	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7	746.4	746.1	745.8
150°	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9	760.6	760.3	760.0
152.5°	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4	772.9	772.5	772.3
155°	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8	790.1	789.5	789.3
157.5°	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0	805.1	804.3	804.4
160°	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6	813.7	812.9	813.0
162.5°	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4	821.5	820.4	820.6
165°	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8	831.7	830.6	830.8
167.5°	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9	839.8	838.7	838.7
170°	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5	844.4	843.3	843.3
172.5°	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6	847.5	846.4	846.2
175°	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2	851.3	850.2	850.2
177.5°	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6	852.6	851.8	851.7
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	22.3	22.5	20.5	18.0	16.7	14.7	14.5	13.1	12.3	12.6	12.3
90°	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6	2.1	3.4	4.8
92.5°	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8	11.4	11.0	10.6
95°	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7	32.9	27.1	21.4
97.5°	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7	75.1	72.5	69.9
100°	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1	109.9	112.7	115.5
102.5°	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5	142.6	144.6	146.6
105°	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8	190.4	191.9	193.5
107.5°	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7	241.0	242.2	243.5
110°	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7	274.8	276.0	277.1





TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2	307.1	308.2	309.2
115°	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1	355.0	355.9	356.7
117.5°	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7	401.7	402.8	403.8
120°	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6	430.8	432.1	433.3
122.5°	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0	460.0	461.1	462.1
125°	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3	500.4	501.5	502.7
127.5°	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3	539.4	540.5	541.7
130°	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6	563.8	564.9	566.0
132.5°	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9	587.0	588.1	589.3
135°	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6	622.4	623.2	624.1
137.5°	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9	653.0	654.1	655.1
140°	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2	673.0	673.9	674.8
142.5°	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0	691.8	692.7	693.5
145°	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2	718.2	719.2	720.1
147.5°	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9	742.5	743.2	743.8
150°	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2	757.5	757.9	758.4
152.5°	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8	771.0	771.2	771.4
155°	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1	789.8	789.5	789.2
157.5°	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0	805.0	804.9	804.9
160°	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2	814.0	813.9	813.7
162.5°	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8	822.4	822.0	821.7
165°	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2	832.8	832.3	831.9
167.5°	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3	840.7	840.2	839.6
170°	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8	845.2	844.7	844.1
172.5°	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9	848.2	847.5	846.9
175°	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8	852.0	851.4	850.7
177.5°	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8	853.3	852.6	852.1
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	12.1	12.9	12.7	13.7	13.5	14.4	14.6	13.5	13.7	15.4	13.3
90°	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4	16.9	17.5	17.9
92.5°	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0	18.9	19.8	20.3
95°	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6	22.6	23.6	24.1
97.5°	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6	23.8	24.9	25.6
100°	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2	24.3	25.4	26.1
102.5°	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7	31.3	27.7	26.1
105°	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9	64.0	39.1	26.8
107.5°	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7	199.5	181.2	162.7
110°	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5	271.8	267.2	254.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9	318.0	318.1	315.9
115°	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5	367.9	369.3	370.3
117.5°	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5	411.6	412.8	413.4
120°	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5	440.6	441.7	442.2
122.5°	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6	468.4	469.2	469.7
125°	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4	507.7	508.0	508.2
127.5°	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3	547.8	548.2	548.3
130°	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4	571.9	572.5	572.7
132.5°	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2	594.7	595.3	595.4
135°	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7	629.1	629.6	629.6
137.5°	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5	660.2	660.9	661.1
140°	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1	679.6	680.2	680.4
142.5°	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6	698.0	698.4	698.5
145°	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5	723.8	724.0	724.2
147.5°	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7	746.9	747.3	747.0
150°	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9	761.1	761.4	761.4
152.5°	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4	774.0	774.5	774.4
155°	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8	791.5	792.3	792.2
157.5°	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0	806.8	807.6	807.5
160°	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6	815.5	816.2	816.2
162.5°	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4	823.4	824.3	824.3
165°	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8	834.0	835.1	835.2
167.5°	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9	842.1	843.3	843.3
170°	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5	846.7	847.8	847.8
172.5°	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6	849.7	850.8	850.8
175°	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2	853.3	854.2	854.1
177.5°	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6	854.5	855.4	855.2
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	13.3	13.4	12.9	12.5	12.9	13.4	13.3	13.3	15.4	13.7	13.5
90°	18.2	18.4	18.7	19.0	18.7	18.4	18.2	17.9	17.5	16.9	16.4
92.5°	20.5	20.7	20.8	21.0	20.8	20.7	20.5	20.3	19.8	18.9	18.0
95°	24.1	24.1	24.1	24.1	24.1	24.1	24.1	24.1	23.6	22.6	21.6
97.5°	25.7	25.8	26.0	26.1	26.0	25.8	25.7	25.6	24.9	23.8	22.6
100°	26.2	26.3	26.4	26.6	26.4	26.3	26.2	26.1	25.4	24.3	23.2
102.5°	26.3	26.6	26.9	27.1	26.9	26.6	26.3	26.1	27.7	31.3	34.7
105°	27.0	27.3	27.6	27.9	27.6	27.3	27.0	26.8	39.1	64.0	88.9
107.5°	143.9	125.1	106.3	87.6	106.3	125.1	143.9	162.7	181.2	199.5	217.7
110°	234.6	214.5	194.3	174.3	194.3	214.5	234.6	254.8	267.2	271.8	276.5



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	311.7	307.5	303.2	298.9	303.2	307.5	311.7	315.9	318.1	318.0	317.9
115°	370.8	371.4	372.0	372.6	372.0	371.4	370.8	370.3	369.3	367.9	366.5
117.5°	413.5	413.6	413.7	413.9	413.7	413.6	413.5	413.4	412.8	411.6	410.5
120°	442.2	442.2	442.2	442.2	442.2	442.2	442.2	442.2	441.7	440.6	439.5
122.5°	469.8	469.8	470.0	470.1	470.0	469.8	469.8	469.7	469.2	468.4	467.6
125°	508.6	508.9	509.1	509.4	509.1	508.9	508.6	508.2	508.0	507.7	507.4
127.5°	548.0	547.7	547.4	547.2	547.4	547.7	548.0	548.3	548.2	547.8	547.3
130°	572.3	572.0	571.8	571.4	571.8	572.0	572.3	572.7	572.5	571.9	571.4
132.5°	595.0	594.6	594.2	593.7	594.2	594.6	595.0	595.4	595.3	594.7	594.2
135°	629.1	628.7	628.3	627.8	628.3	628.7	629.1	629.6	629.6	629.1	628.7
137.5°	660.8	660.5	660.2	660.0	660.2	660.5	660.8	661.1	660.9	660.2	659.5
140°	680.0	679.8	679.5	679.2	679.5	679.8	680.0	680.4	680.2	679.6	679.1
142.5°	698.1	697.8	697.3	696.9	697.3	697.8	698.1	698.5	698.4	698.0	697.6
145°	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.2	724.0	723.8	723.5
147.5°	746.4	745.7	745.1	744.4	745.1	745.7	746.4	747.0	747.3	746.9	746.7
150°	761.0	760.5	760.1	759.7	760.1	760.5	761.0	761.4	761.4	761.1	760.9
152.5°	773.8	773.1	772.5	771.8	772.5	773.1	773.8	774.4	774.5	774.0	773.4
155°	791.3	790.5	789.6	788.8	789.6	790.5	791.3	792.2	792.3	791.5	790.8
157.5°	806.4	805.3	804.3	803.1	804.3	805.3	806.4	807.5	807.6	806.8	806.0
160°	815.2	814.2	813.2	812.3	813.2	814.2	815.2	816.2	816.2	815.5	814.6
162.5°	823.5	822.6	821.7	820.9	821.7	822.6	823.5	824.3	824.3	823.4	822.4
165°	834.2	833.2	832.2	831.2	832.2	833.2	834.2	835.2	835.1	834.0	832.8
167.5°	842.1	840.9	839.8	838.7	839.8	840.9	842.1	843.3	843.3	842.1	840.9
170°	846.7	845.5	844.4	843.3	844.4	845.5	846.7	847.8	847.8	846.7	845.5
172.5°	849.5	848.3	847.1	845.8	847.1	848.3	849.5	850.8	850.8	849.7	848.6
175°	853.0	851.9	850.8	849.6	850.8	851.9	853.0	854.1	854.2	853.3	852.2
177.5°	854.1	853.0	851.9	850.8	851.9	853.0	854.1	855.2	855.4	854.5	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	14.6	14.4	13.5	13.7	12.7	12.9	12.1	12.3	12.6	12.3	13.1
90°	15.8	15.2	13.3	11.5	9.7	7.9	6.3	4.8	3.4	2.1	0.6
92.5°	17.1	16.2	14.8	13.4	12.1	10.7	10.2	10.6	11.0	11.4	11.8
95°	20.7	19.6	18.1	16.5	15.0	13.4	15.6	21.4	27.1	32.9	38.7
97.5°	21.5	20.4	30.6	40.6	50.8	61.0	67.3	69.9	72.5	75.1	77.7
100°	22.0	20.9	42.9	64.8	86.8	108.7	118.3	115.5	112.7	109.9	107.1
102.5°	38.2	41.7	65.7	89.6	113.7	137.7	148.6	146.6	144.6	142.6	140.5
105°	113.8	138.8	151.4	164.1	176.8	189.4	195.0	193.5	191.9	190.4	188.8
107.5°	236.0	254.3	252.4	250.3	248.3	246.3	244.7	243.5	242.2	241.0	239.7
110°	281.1	285.8	284.2	282.7	281.1	279.6	278.2	277.1	276.0	274.8	273.7



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	317.8	317.7	316.2	314.6	313.1	311.5	310.2	309.2	308.2	307.1	306.2
115°	365.1	363.7	362.4	361.1	359.9	358.6	357.6	356.7	355.9	355.0	354.1
117.5°	409.4	408.3	407.6	407.0	406.3	405.7	404.8	403.8	402.8	401.7	400.7
120°	438.3	437.1	436.8	436.4	435.9	435.5	434.6	433.3	432.1	430.8	429.6
122.5°	466.8	466.1	465.5	465.0	464.4	463.9	463.1	462.1	461.1	460.0	459.0
125°	507.1	506.9	506.3	505.8	505.1	504.6	503.8	502.7	501.5	500.4	499.3
127.5°	546.8	546.4	545.7	545.0	544.4	543.7	542.8	541.7	540.5	539.4	538.3
130°	570.8	570.2	569.6	569.1	568.5	568.0	567.1	566.0	564.9	563.8	562.6
132.5°	593.6	593.1	592.5	592.1	591.7	591.2	590.5	589.3	588.1	587.0	585.9
135°	628.3	627.8	627.3	626.7	626.2	625.6	624.9	624.1	623.2	622.4	621.6
137.5°	658.8	658.1	657.9	657.5	657.2	656.9	656.3	655.1	654.1	653.0	651.9
140°	678.5	678.0	677.5	677.1	676.7	676.2	675.6	674.8	673.9	673.0	672.2
142.5°	697.2	696.7	696.3	695.9	695.4	695.0	694.4	693.5	692.7	691.8	691.0
145°	723.2	722.9	722.6	722.4	722.0	721.8	721.2	720.1	719.2	718.2	717.2
147.5°	746.4	746.1	745.8	745.5	745.3	744.9	744.5	743.8	743.2	742.5	741.9
150°	760.6	760.3	760.0	759.7	759.5	759.1	758.8	758.4	757.9	757.5	757.2
152.5°	772.9	772.5	772.3	772.1	772.0	771.8	771.6	771.4	771.2	771.0	770.8
155°	790.1	789.5	789.3	789.2	789.0	788.8	788.9	789.2	789.5	789.8	790.1
157.5°	805.1	804.3	804.4	804.5	804.7	804.9	804.9	804.9	804.9	805.0	805.0
160°	813.7	812.9	813.0	813.1	813.3	813.5	813.6	813.7	813.9	814.0	814.2
162.5°	821.5	820.4	820.6	820.8	820.9	821.0	821.3	821.7	822.0	822.4	822.8
165°	831.7	830.6	830.8	830.9	831.0	831.2	831.5	831.9	832.3	832.8	833.2
167.5°	839.8	838.7	838.7	838.7	838.7	838.7	839.0	839.6	840.2	840.7	841.3
170°	844.4	843.3	843.3	843.3	843.3	843.3	843.6	844.1	844.7	845.2	845.8
172.5°	847.5	846.4	846.2	846.1	846.0	845.8	846.2	846.9	847.5	848.2	848.9
175°	851.3	850.2	850.2	850.0	849.8	849.7	850.0	850.7	851.4	852.0	852.8
177.5°	852.6	851.8	851.7	851.5	851.4	851.4	851.5	852.1	852.6	853.3	853.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.5	14.7	16.7	18.0	20.5	22.5	22.3	21.6	21.4	21.0	20.6
90°	2.1	3.4	4.8	6.3	7.9	9.7	11.5	13.3	15.2	15.8	16.4
92.5°	11.4	11.0	10.6	10.2	10.7	12.1	13.4	14.8	16.2	17.1	18.0
95°	32.9	27.1	21.4	15.6	13.4	15.0	16.5	18.1	19.6	20.7	21.6
97.5°	75.1	72.5	69.9	67.3	61.0	50.8	40.6	30.6	20.4	21.5	22.6
100°	109.9	112.7	115.5	118.3	108.7	86.8	64.8	42.9	20.9	22.0	23.2
102.5°	142.6	144.6	146.6	148.6	137.7	113.7	89.6	65.7	41.7	38.2	34.7
105°	190.4	191.9	193.5	195.0	189.4	176.8	164.1	151.4	138.8	113.8	88.9
107.5°	241.0	242.2	243.5	244.7	246.3	248.3	250.3	252.4	254.3	236.0	217.7
110°	274.8	276.0	277.1	278.2	279.6	281.1	282.7	284.2	285.8	281.1	276.5





TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	307.1	308.2	309.2	310.2	311.5	313.1	314.6	316.2	317.7	317.8	317.9
115°	355.0	355.9	356.7	357.6	358.6	359.9	361.1	362.4	363.7	365.1	366.5
117.5°	401.7	402.8	403.8	404.8	405.7	406.3	407.0	407.6	408.3	409.4	410.5
120°	430.8	432.1	433.3	434.6	435.5	435.9	436.4	436.8	437.1	438.3	439.5
122.5°	460.0	461.1	462.1	463.1	463.9	464.4	465.0	465.5	466.1	466.8	467.6
125°	500.4	501.5	502.7	503.8	504.6	505.1	505.8	506.3	506.9	507.1	507.4
127.5°	539.4	540.5	541.7	542.8	543.7	544.4	545.0	545.7	546.4	546.8	547.3
130°	563.8	564.9	566.0	567.1	568.0	568.5	569.1	569.6	570.2	570.8	571.4
132.5°	587.0	588.1	589.3	590.5	591.2	591.7	592.1	592.5	593.1	593.6	594.2
135°	622.4	623.2	624.1	624.9	625.6	626.2	626.7	627.3	627.8	628.3	628.7
137.5°	653.0	654.1	655.1	656.3	656.9	657.2	657.5	657.9	658.1	658.8	659.5
140°	673.0	673.9	674.8	675.6	676.2	676.7	677.1	677.5	678.0	678.5	679.1
142.5°	691.8	692.7	693.5	694.4	695.0	695.4	695.9	696.3	696.7	697.2	697.6
145°	718.2	719.2	720.1	721.2	721.8	722.0	722.4	722.6	722.9	723.2	723.5
147.5°	742.5	743.2	743.8	744.5	744.9	745.3	745.5	745.8	746.1	746.4	746.7
150°	757.5	757.9	758.4	758.8	759.1	759.5	759.7	760.0	760.3	760.6	760.9
152.5°	771.0	771.2	771.4	771.6	771.8	772.0	772.1	772.3	772.5	772.9	773.4
155°	789.8	789.5	789.2	788.9	788.8	789.0	789.2	789.3	789.5	790.1	790.8
157.5°	805.0	804.9	804.9	804.9	804.9	804.7	804.5	804.4	804.3	805.1	806.0
160°	814.0	813.9	813.7	813.6	813.5	813.3	813.1	813.0	812.9	813.7	814.6
162.5°	822.4	822.0	821.7	821.3	821.0	820.9	820.8	820.6	820.4	821.5	822.4
165°	832.8	832.3	831.9	831.5	831.2	831.0	830.9	830.8	830.6	831.7	832.8
167.5°	840.7	840.2	839.6	839.0	838.7	838.7	838.7	838.7	838.7	839.8	840.9
170°	845.2	844.7	844.1	843.6	843.3	843.3	843.3	843.3	843.3	844.4	845.5
172.5°	848.2	847.5	846.9	846.2	845.8	846.0	846.1	846.2	846.4	847.5	848.6
175°	852.0	851.4	850.7	850.0	849.7	849.8	850.0	850.2	850.2	851.3	852.2
177.5°	853.3	852.6	852.1	851.5	851.4	851.4	851.5	851.7	851.8	852.6	853.6
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8	852.8



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	20.1	19.7	19.3	19.9	19.4	18.9	20.1
90°	16.9	17.5	17.9	18.2	18.4	18.7	19.0
92.5°	18.9	19.8	20.3	20.5	20.7	20.8	21.0
95°	22.6	23.6	24.1	24.1	24.1	24.1	24.1
97.5°	23.8	24.9	25.6	25.7	25.8	26.0	26.1
100°	24.3	25.4	26.1	26.2	26.3	26.4	26.6
102.5°	31.3	27.7	26.1	26.3	26.6	26.9	27.1
105°	64.0	39.1	26.8	27.0	27.3	27.6	27.9
107.5°	199.5	181.2	162.7	143.9	125.1	106.3	87.6
110°	271.8	267.2	254.8	234.6	214.5	194.3	174.3



TEST NUMBER: P332216-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	318.0	318.1	315.9	311.7	307.5	303.2	298.9
115°	367.9	369.3	370.3	370.8	371.4	372.0	372.6
117.5°	411.6	412.8	413.4	413.5	413.6	413.7	413.9
120°	440.6	441.7	442.2	442.2	442.2	442.2	442.2
122.5°	468.4	469.2	469.7	469.8	469.8	470.0	470.1
125°	507.7	508.0	508.2	508.6	508.9	509.1	509.4
127.5°	547.8	548.2	548.3	548.0	547.7	547.4	547.2
130°	571.9	572.5	572.7	572.3	572.0	571.8	571.4
132.5°	594.7	595.3	595.4	595.0	594.6	594.2	593.7
135°	629.1	629.6	629.6	629.1	628.7	628.3	627.8
137.5°	660.2	660.9	661.1	660.8	660.5	660.2	660.0
140°	679.6	680.2	680.4	680.0	679.8	679.5	679.2
142.5°	698.0	698.4	698.5	698.1	697.8	697.3	696.9
145°	723.8	724.0	724.2	724.2	724.2	724.2	724.2
147.5°	746.9	747.3	747.0	746.4	745.7	745.1	744.4
150°	761.1	761.4	761.4	761.0	760.5	760.1	759.7
152.5°	774.0	774.5	774.4	773.8	773.1	772.5	771.8
155°	791.5	792.3	792.2	791.3	790.5	789.6	788.8
157.5°	806.8	807.6	807.5	806.4	805.3	804.3	803.1
160°	815.5	816.2	816.2	815.2	814.2	813.2	812.3
162.5°	823.4	824.3	824.3	823.5	822.6	821.7	820.9
165°	834.0	835.1	835.2	834.2	833.2	832.2	831.2
167.5°	842.1	843.3	843.3	842.1	840.9	839.8	838.7
170°	846.7	847.8	847.8	846.7	845.5	844.4	843.3
172.5°	849.7	850.8	850.8	849.5	848.3	847.1	845.8
175°	853.3	854.2	854.1	853.0	851.9	850.8	849.6
177.5°	854.5	855.4	855.2	854.1	853.0	851.9	850.8
180°	852.8	852.8	852.8	852.8	852.8	852.8	852.8

(END OF REPORT)