

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332239-830

Luminaire Tested: **S123DIW-S1165D1535U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332239-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9502.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45				40	
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	42	40	38				33	
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32				28	
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24				21	
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21				18	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19				16	
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17				15	
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15				13	
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18547	18547	18547
5°	18634	18377	18506
10°	18510	18218	18332
15°	18293	18013	18046
20°	18040	17718	17734
25°	17701	17368	17332
30°	17329	16978	16850
35°	16938	16567	16353
40°	16530	16114	15864
45°	16081	15696	15314
50°	15630	15183	14763
55°	15041	14653	14208
60°	14449	14034	13586
65°	13924	13359	12944
70°	13149	12589	12032
75°	12015	11582	11088
80°	10835	10377	10290
85°	9510	9152	8793



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	1.7
10°-20°	458.3	4.8
20°-30°	677.0	7.1
30°-40°	790.8	8.3
40°-50°	795.1	8.4
50°-60°	698.4	7.3
60°-70°	520.3	5.5
70°-80°	296.4	3.1
80°-90°	90.4	1.0
90°-100°	117.9	1.2
100°-110°	352.8	3.7
110°-120°	600.0	6.3
120°-130°	789.3	8.3
130°-140°	887.1	9.3
140°-150°	872.0	9.2
150°-160°	734.1	7.7
160°-170°	488.7	5.1
170°-180°	171.1	1.8
0°-30°	1297.6	13.7
0°-40°	2088.4	22.0
0°-60°	3581.8	37.7
0°-90°	4489.0	47.2
90°-120°	1070.7	11.3
90°-150°	3619.1	38.1
90°-180°	5013.0	52.8
0°-180°	9502.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1723	1723	1723	1723	1723	
5°	1725	1717	1701	1715	1713	163
15°	1642	1635	1616	1627	1619	463
25°	1490	1481	1462	1464	1459	686
35°	1289	1280	1261	1252	1244	806
45°	1056	1050	1031	1014	1006	815
55°	802	799	781	765	757	718
65°	547	539	524	513	508	539
75°	289	283	278	271	267	309
85°	77	74	74	71	71	85
90°	1	16	34	40	43	9
95°	84	94	105	110	111	94
105°	320	323	336	336	338	343
115°	604	608	606	607	606	597
125°	884	888	886	880	874	788
135°	1147	1155	1154	1149	1146	884
145°	1392	1394	1398	1397	1392	869
155°	1593	1593	1595	1600	1590	733
165°	1735	1731	1731	1739	1730	489
175°	1805	1800	1799	1807	1798	171
180°	1809	1809	1809	1809	1809	



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1729.0	1728.0	1726.9	1725.9	1724.8	1722.8	1720.0	1717.0	1714.1	1711.2	1713.8
5°	1724.6	1723.0	1721.3	1719.7	1718.0	1715.3	1711.8	1708.1	1704.5	1700.8	1704.1
7.5°	1707.7	1706.0	1704.4	1702.7	1701.1	1698.4	1694.6	1690.9	1687.2	1683.4	1686.3
10°	1693.5	1691.8	1690.2	1688.5	1686.9	1683.9	1679.6	1675.4	1671.0	1666.8	1669.7
12.5°	1674.5	1673.1	1671.7	1670.4	1669.0	1666.2	1662.3	1658.2	1654.2	1650.2	1652.4
15°	1641.6	1640.3	1639.0	1637.7	1636.3	1633.5	1629.3	1624.9	1620.7	1616.4	1619.0
17.5°	1603.4	1601.7	1600.0	1598.3	1596.5	1593.6	1589.2	1585.0	1580.6	1576.4	1578.3
20°	1574.9	1572.9	1570.9	1569.0	1567.1	1563.9	1559.6	1555.4	1551.0	1546.8	1548.1
22.5°	1542.9	1541.0	1539.0	1537.0	1535.0	1531.9	1527.6	1523.3	1519.1	1514.8	1515.8
25°	1490.4	1488.5	1486.5	1484.5	1482.6	1479.4	1475.2	1470.9	1466.6	1462.4	1462.6
27.5°	1434.5	1432.6	1430.7	1428.7	1426.8	1423.6	1419.0	1414.4	1409.8	1405.1	1405.4
30°	1394.2	1392.5	1390.9	1389.2	1387.6	1384.5	1379.9	1375.3	1370.6	1366.0	1366.0
32.5°	1353.9	1351.7	1349.5	1347.4	1345.2	1342.3	1338.8	1335.2	1331.6	1328.1	1326.3
35°	1289.0	1287.0	1285.1	1283.1	1281.1	1278.0	1273.7	1269.4	1265.1	1260.8	1258.9
37.5°	1222.6	1220.1	1217.6	1215.1	1212.6	1209.2	1204.9	1200.5	1196.2	1191.8	1189.4
40°	1176.4	1174.4	1172.4	1170.4	1168.5	1165.2	1160.6	1155.9	1151.3	1146.8	1144.2
42.5°	1130.1	1127.9	1125.7	1123.4	1121.2	1117.8	1113.1	1108.5	1103.9	1099.4	1096.7
45°	1056.4	1055.1	1053.8	1052.4	1051.1	1048.3	1044.1	1039.7	1035.5	1031.1	1027.3
47.5°	983.2	981.3	979.4	977.4	975.5	972.6	968.6	964.5	960.5	956.5	952.6
50°	933.4	931.8	930.1	928.5	926.8	923.9	919.5	915.3	911.0	906.7	903.1
52.5°	881.3	880.1	879.0	877.9	876.8	873.9	869.4	864.9	860.4	855.7	852.6
55°	801.5	801.3	800.9	800.6	800.2	798.0	793.6	789.4	785.0	780.8	777.2
57.5°	725.7	724.5	723.4	722.4	721.2	719.0	715.5	712.1	708.7	705.2	702.0
60°	671.2	670.8	670.5	670.1	669.9	667.7	663.7	659.8	655.8	651.9	648.9
62.5°	622.5	621.7	620.9	620.0	619.2	616.7	612.7	608.8	604.9	601.0	597.9
65°	546.7	545.1	543.4	541.8	540.1	537.6	534.3	531.0	527.7	524.5	521.9
67.5°	466.4	465.0	463.5	462.0	460.6	458.6	456.1	453.6	451.1	448.7	446.3
70°	417.8	415.8	413.9	411.9	409.9	407.9	406.0	404.0	402.0	400.0	397.8
72.5°	366.8	365.4	363.9	362.5	361.1	359.2	356.9	354.7	352.5	350.2	348.2
75°	288.9	287.6	286.3	284.9	283.6	282.5	281.5	280.5	279.6	278.5	276.9
77.5°	219.9	219.1	218.4	217.7	217.0	216.0	214.8	213.7	212.4	211.3	210.2
80°	174.8	173.8	172.9	171.8	170.9	170.0	169.4	168.7	168.1	167.4	167.1
82.5°	131.0	130.7	130.5	130.4	130.2	130.0	129.9	129.8	129.6	129.5	128.9
85°	77.0	76.3	75.7	75.0	74.4	74.1	74.1	74.1	74.1	74.1	73.4
87.5°	31.1	30.9	30.8	30.6	30.4	30.6	31.2	31.8	32.3	32.9	32.9
90°	1.4	4.6	7.7	10.9	14.0	17.7	21.8	25.9	30.0	34.1	35.3
92.5°	34.4	36.6	38.6	40.8	43.0	45.2	47.6	49.9	52.2	54.6	55.6
95°	83.9	86.1	88.3	90.5	92.7	95.1	97.6	100.1	102.6	105.2	106.4
97.5°	148.9	150.6	152.2	153.9	155.5	157.2	159.1	160.9	162.8	164.6	166.1
100°	193.3	195.2	197.1	199.0	200.9	202.6	204.2	205.8	207.4	209.0	209.9
102.5°	244.5	245.6	246.8	247.9	249.0	250.6	252.7	254.8	256.8	258.9	260.0
105°	319.8	320.5	321.0	321.7	322.3	324.0	326.9	329.7	332.6	335.5	335.5
107.5°	407.4	407.7	408.1	408.5	408.9	409.6	410.8	411.9	413.0	414.2	415.2
110°	461.9	462.6	463.2	463.8	464.5	465.1	465.7	466.4	466.9	467.6	468.9



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.8	519.2	519.5	519.9	520.3	520.6	520.7	520.8	520.9	521.0	522.5
115°	604.1	605.0	606.0	606.9	607.8	608.0	607.4	606.7	606.1	605.5	605.8
117.5°	689.9	690.5	691.2	691.8	692.4	692.3	691.5	690.7	689.8	689.1	689.0
120°	743.4	745.3	747.2	749.0	750.9	751.1	749.5	747.9	746.3	744.8	744.4
122.5°	799.1	800.4	801.8	803.2	804.6	804.9	804.1	803.2	802.5	801.6	800.8
125°	884.0	885.0	886.0	886.9	887.9	888.0	887.4	886.7	886.1	885.5	884.2
127.5°	962.5	964.5	966.6	968.6	970.6	971.3	970.5	969.9	969.2	968.5	966.7
130°	1014.8	1017.4	1019.8	1022.4	1024.9	1025.7	1024.7	1023.8	1022.8	1021.9	1020.7
132.5°	1067.1	1069.6	1072.1	1074.7	1077.2	1078.2	1077.4	1076.8	1076.0	1075.3	1073.8
135°	1147.0	1148.9	1150.8	1152.6	1154.6	1155.4	1155.1	1154.7	1154.4	1154.1	1152.8
137.5°	1220.9	1222.5	1224.1	1225.7	1227.2	1228.4	1229.3	1230.0	1230.9	1231.7	1230.4
140°	1272.1	1273.7	1275.3	1276.8	1278.4	1279.3	1279.7	1280.0	1280.3	1280.6	1280.3
142.5°	1318.7	1320.2	1321.8	1323.4	1325.0	1326.1	1326.6	1327.2	1327.8	1328.3	1328.0
145°	1391.5	1392.1	1392.7	1393.4	1394.0	1394.8	1395.7	1396.7	1397.6	1398.5	1398.3
147.5°	1455.1	1456.2	1457.4	1458.6	1459.7	1460.7	1461.6	1462.4	1463.3	1464.2	1464.2
150°	1499.5	1500.2	1500.7	1501.4	1502.0	1502.6	1503.3	1503.9	1504.5	1505.1	1505.1
152.5°	1535.9	1536.7	1537.7	1538.5	1539.4	1540.0	1540.4	1540.8	1541.2	1541.5	1542.1
155°	1593.3	1593.3	1593.3	1593.3	1593.3	1593.5	1593.7	1594.0	1594.4	1594.7	1596.0
157.5°	1642.2	1641.8	1641.4	1641.1	1640.7	1640.6	1640.9	1641.1	1641.3	1641.6	1642.9
160°	1672.9	1672.3	1671.6	1670.9	1670.4	1670.0	1670.0	1670.0	1670.0	1670.0	1671.6
162.5°	1700.2	1699.3	1698.4	1697.5	1696.7	1696.3	1696.6	1696.9	1697.0	1697.3	1698.9
165°	1735.4	1734.5	1733.5	1732.6	1731.6	1731.2	1731.2	1731.2	1731.2	1731.2	1733.1
167.5°	1763.6	1762.3	1761.0	1759.7	1758.5	1758.0	1758.2	1758.5	1758.8	1759.0	1761.0
170°	1779.4	1778.2	1777.0	1775.7	1774.4	1773.8	1773.8	1773.8	1773.8	1773.8	1776.0
172.5°	1792.0	1790.7	1789.4	1788.2	1787.0	1786.3	1786.3	1786.3	1786.3	1786.3	1788.3
175°	1805.1	1803.8	1802.5	1801.3	1800.0	1799.4	1799.4	1799.4	1799.4	1799.4	1801.3
177.5°	1810.4	1809.5	1808.5	1807.4	1806.4	1805.9	1805.9	1805.9	1805.9	1805.9	1807.4
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1	1723.1
2.5°	1716.5	1719.1	1721.7	1723.0	1722.7	1722.4	1722.1	1721.9
5°	1707.4	1710.7	1714.0	1715.3	1714.7	1714.0	1713.4	1712.7
7.5°	1689.3	1692.2	1695.3	1696.5	1696.1	1695.7	1695.4	1695.0
10°	1672.7	1675.7	1678.7	1679.8	1679.1	1678.5	1677.8	1677.2
12.5°	1654.5	1656.7	1658.9	1659.8	1659.3	1659.0	1658.6	1658.2
15°	1621.6	1624.3	1626.9	1627.3	1625.3	1623.3	1621.4	1619.4
17.5°	1580.1	1582.0	1583.8	1584.3	1583.7	1582.9	1582.2	1581.5
20°	1549.4	1550.8	1552.1	1552.2	1551.2	1550.2	1549.3	1548.2
22.5°	1516.9	1518.0	1519.0	1518.9	1517.7	1516.4	1515.1	1513.9
25°	1463.0	1463.3	1463.7	1463.3	1462.4	1461.3	1460.4	1459.3
27.5°	1405.7	1405.9	1406.2	1405.7	1404.5	1403.2	1401.9	1400.7
30°	1366.0	1366.0	1366.0	1364.9	1362.5	1360.3	1357.9	1355.7
32.5°	1324.4	1322.6	1320.7	1319.2	1318.0	1316.6	1315.4	1314.2
35°	1256.9	1254.9	1252.9	1251.1	1249.4	1247.8	1246.1	1244.5
37.5°	1187.0	1184.7	1182.3	1180.6	1179.5	1178.5	1177.4	1176.4
40°	1141.5	1138.9	1136.2	1134.3	1132.9	1131.6	1130.3	1129.0
42.5°	1094.1	1091.5	1088.8	1086.8	1085.5	1084.2	1082.9	1081.6
45°	1023.3	1019.4	1015.4	1012.6	1011.0	1009.3	1007.7	1006.0
47.5°	948.8	944.9	940.9	938.3	936.9	935.4	934.0	932.6
50°	899.5	895.9	892.2	889.5	887.5	885.5	883.5	881.6
52.5°	849.6	846.5	843.4	840.8	838.9	836.9	834.9	832.9
55°	773.5	770.0	766.3	763.6	762.0	760.3	758.7	757.1
57.5°	698.8	695.6	692.3	689.8	687.9	686.0	684.0	682.1
60°	646.0	643.0	640.1	637.7	636.1	634.4	632.8	631.1
62.5°	595.0	592.0	589.1	587.0	585.9	584.8	583.7	582.6
65°	519.2	516.6	514.0	512.2	511.1	510.2	509.2	508.2
67.5°	444.0	441.7	439.4	437.5	436.2	434.8	433.4	432.1
70°	395.4	393.1	390.8	388.8	387.2	385.5	383.9	382.3
72.5°	346.2	344.1	342.0	340.6	339.8	338.9	338.1	337.2
75°	275.2	273.6	271.9	270.6	269.7	268.6	267.7	266.6
77.5°	209.1	207.9	206.8	206.2	206.2	206.2	206.2	206.2
80°	166.7	166.5	166.1	166.0	166.0	166.0	166.0	166.0
82.5°	128.3	127.7	127.1	126.7	126.4	126.2	125.9	125.6
85°	72.8	72.1	71.4	71.2	71.2	71.2	71.2	71.2
87.5°	32.9	32.9	32.9	32.9	33.1	33.2	33.3	33.5
90°	36.7	37.9	39.2	40.2	40.7	41.4	42.0	42.6
92.5°	56.6	57.6	58.6	58.9	58.5	58.2	57.8	57.4
95°	107.7	109.0	110.2	110.8	110.8	110.8	110.8	110.8
97.5°	167.5	168.9	170.4	171.1	171.0	170.8	170.7	170.6
100°	210.8	211.8	212.7	213.5	214.1	214.8	215.4	216.0
102.5°	260.9	261.8	262.8	263.2	263.1	262.9	262.8	262.7
105°	335.5	335.5	335.5	335.7	336.4	337.1	337.6	338.3
107.5°	416.2	417.2	418.2	418.5	418.1	417.7	417.4	417.0
110°	470.1	471.4	472.7	473.0	472.3	471.7	471.1	470.4



TEST NUMBER: P332239-830

CATALOG NUMBER: S123DIW-S1165D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	524.1	525.6	527.1	527.8	527.7	527.5	527.4	527.3
115°	606.1	606.4	606.7	606.7	606.4	606.1	605.8	605.5
117.5°	688.9	688.9	688.8	688.3	687.4	686.5	685.7	684.8
120°	744.1	743.9	743.5	743.0	742.4	741.8	741.1	740.5
122.5°	799.9	799.2	798.3	797.5	796.6	795.7	794.8	793.9
125°	883.0	881.7	880.4	879.1	877.9	876.7	875.3	874.1
127.5°	965.0	963.2	961.4	959.8	958.4	956.9	955.5	953.9
130°	1019.4	1018.1	1016.9	1015.1	1013.0	1010.7	1008.5	1006.3
132.5°	1072.3	1070.8	1069.3	1067.7	1066.0	1064.3	1062.5	1060.8
135°	1151.6	1150.3	1149.1	1148.1	1147.5	1146.8	1146.2	1145.6
137.5°	1229.1	1227.8	1226.4	1225.1	1223.9	1222.8	1221.5	1220.3
140°	1280.0	1279.7	1279.3	1278.1	1275.8	1273.7	1271.4	1269.2
142.5°	1327.8	1327.4	1327.1	1326.1	1324.4	1322.7	1321.0	1319.3
145°	1397.9	1397.6	1397.3	1396.5	1395.2	1394.0	1392.7	1391.5
147.5°	1464.2	1464.2	1464.2	1463.3	1461.4	1459.5	1457.5	1455.7
150°	1505.1	1505.1	1505.1	1504.2	1502.3	1500.4	1498.5	1496.7
152.5°	1542.6	1543.0	1543.6	1543.0	1541.3	1539.7	1538.0	1536.4
155°	1597.2	1598.5	1599.8	1599.3	1597.0	1594.9	1592.6	1590.4
157.5°	1644.3	1645.6	1646.9	1646.7	1644.9	1643.1	1641.3	1639.6
160°	1673.2	1674.8	1676.3	1676.5	1675.3	1674.0	1672.7	1671.4
162.5°	1700.4	1702.0	1703.6	1703.5	1701.4	1699.4	1697.3	1695.4
165°	1734.9	1736.8	1738.7	1738.6	1736.4	1734.2	1731.9	1729.8
167.5°	1762.9	1764.9	1766.8	1766.8	1764.9	1762.9	1761.0	1759.0
170°	1778.2	1780.5	1782.6	1782.6	1780.5	1778.2	1776.0	1773.8
172.5°	1790.2	1792.2	1794.1	1794.0	1791.8	1789.6	1787.3	1785.2
175°	1803.2	1805.1	1806.9	1806.8	1804.6	1802.3	1800.2	1798.0
177.5°	1808.9	1810.4	1811.9	1811.8	1810.1	1808.3	1806.6	1804.8
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3

(END OF REPORT)