

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332217-935

Luminaire Tested: **S123DIW-S1165D755U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332217-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D755U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6471.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	97	93	90	95	92	88	85	81	79	76	71	70	68	63	61	60	56
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51	47
3	85	75	68	62	80	71	65	59	63	58	54	56	52	49	49	46	44	40
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	44	41	38	35
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	27
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15033	15033	15033	15033
5°	17928	15098	13380	15098
10°	22440	15021	12085	15021
15°	27524	14900	11251	14900
20°	32787	14712	10711	14712
25°	34815	14481	10592	14481
30°	29840	14315	10648	14315
35°	20752	14076	10759	14076
40°	15632	13797	10725	13797
45°	12979	13381	10589	13381
50°	11627	12532	10493	12532
55°	10869	11618	10363	11618
60°	10196	10663	10256	10663
65°	9584	9722	9928	9722
70°	8988	8645	9454	8645
75°	8052	7569	8667	7569
80°	7048	6205	7469	6205
85°	5521	4508	5014	4508



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.6	2.1
10°-20°	441.2	6.8
20°-30°	740.4	11.4
30°-40°	838.4	13.0
40°-50°	751.8	11.6
50°-60°	606.7	9.4
60°-70°	422.8	6.5
70°-80°	222.2	3.4
80°-90°	56.8	0.9
90°-100°	53.0	0.8
100°-110°	158.6	2.5
110°-120°	269.8	4.2
120°-130°	354.9	5.5
130°-140°	398.9	6.2
140°-150°	392.1	6.1
150°-160°	330.1	5.1
160°-170°	219.7	3.4
170°-180°	76.9	1.2
0°-30°	1319.2	20.4
0°-40°	2157.5	33.3
0°-60°	3516.1	54.3
0°-90°	4217.8	65.2
90°-120°	481.4	7.4
90°-150°	1627.3	25.1
90°-180°	2254.0	34.8
0°-180°	6471.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1397	1397	1397	1397	1397	
5°	1659	1397	1238	1397	1659	172
15°	2470	1337	1010	1337	2470	713
25°	2931	1219	892	1219	2931	1286
35°	1579	1071	819	1071	1579	1026
45°	853	879	696	879	853	675
55°	579	619	552	619	579	520
65°	376	382	390	382	376	375
75°	194	182	208	182	194	207
85°	45	36	41	36	45	53
90°	19	1	19	1	19	12
95°	50	38	50	38	50	51
105°	152	144	152	144	152	161
115°	272	272	272	272	272	270
125°	393	398	393	398	393	351
135°	515	516	515	516	515	396
145°	626	626	626	626	626	391
155°	715	716	715	716	715	329
165°	778	780	778	780	778	219
175°	808	812	808	812	808	77
180°	814	814	814	814	814	



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1482.2	1481.1	1478.4	1480.6	1476.3	1470.2	1469.7	1464.3	1448.6	1447.5	1443.2
5°	1659.2	1653.8	1653.1	1652.4	1643.0	1630.1	1605.8	1603.7	1571.2	1555.0	1535.4
7.5°	1888.4	1891.3	1881.5	1872.8	1843.8	1824.7	1798.6	1765.2	1725.3	1684.8	1657.9
10°	2053.1	2075.4	2047.6	2028.7	2011.1	1977.9	1939.4	1891.3	1843.2	1787.1	1744.5
12.5°	2229.6	2240.5	2234.9	2217.1	2189.7	2139.2	2070.9	2018.0	1973.8	1880.3	1842.5
15°	2469.9	2511.2	2484.8	2423.9	2425.2	2377.1	2287.8	2189.7	2137.6	2055.7	1944.1
17.5°	2725.9	2731.1	2719.8	2669.1	2635.3	2569.2	2486.8	2392.7	2287.2	2188.1	2069.7
20°	2862.3	2858.3	2834.6	2808.2	2750.0	2698.6	2608.6	2503.7	2368.4	2271.0	2141.7
22.5°	2938.2	2931.4	2920.2	2898.0	2849.7	2794.4	2713.6	2599.0	2470.1	2335.9	2186.6
25°	2931.4	2940.1	2941.5	2935.4	2918.5	2885.4	2821.8	2730.4	2601.9	2429.3	2273.6
27.5°	2666.1	2678.6	2714.7	2746.8	2782.7	2819.2	2814.3	2769.0	2673.8	2524.8	2334.5
30°	2400.8	2373.8	2440.8	2525.4	2582.9	2684.3	2741.3	2744.6	2691.1	2563.3	2377.8
32.5°	2032.7	2062.5	2092.1	2196.2	2321.9	2435.9	2549.1	2640.2	2650.6	2565.4	2403.3
35°	1579.3	1616.6	1670.7	1724.8	1860.2	1976.6	2175.5	2348.7	2486.8	2505.1	2405.5
37.5°	1272.7	1291.1	1325.3	1379.6	1468.1	1606.2	1760.1	1979.0	2179.0	2327.8	2334.3
40°	1112.5	1117.8	1156.4	1197.7	1269.5	1383.1	1521.8	1715.4	1954.9	2162.7	2249.3
42.5°	992.3	1004.2	1020.5	1060.2	1117.3	1202.9	1331.9	1491.8	1711.3	1950.4	2119.9
45°	852.6	866.2	876.3	902.7	943.3	1000.8	1090.8	1237.0	1404.1	1651.1	1879.1
47.5°	760.3	761.4	769.0	788.8	816.5	859.6	923.3	1017.2	1170.6	1371.0	1605.1
50°	694.3	705.1	707.8	723.3	745.0	776.8	829.6	909.5	1035.4	1211.3	1426.4
52.5°	647.7	651.0	658.6	669.8	688.7	713.5	759.2	821.7	920.6	1070.5	1268.3
55°	579.2	579.2	586.7	595.5	606.3	628.6	659.1	705.1	780.2	896.6	1060.3
57.5°	515.9	519.3	524.5	527.3	536.5	551.2	576.7	611.6	667.6	757.2	887.4
60°	473.6	479.7	479.1	484.5	492.7	504.1	525.8	554.2	604.2	676.0	785.7
62.5°	436.9	436.4	436.4	442.8	450.9	461.9	476.0	500.6	543.1	606.7	700.1
65°	376.3	374.9	379.6	383.7	386.4	394.5	405.4	427.0	455.4	502.7	575.1
67.5°	322.4	318.5	321.0	322.4	327.0	333.3	343.5	356.9	379.4	417.5	472.1
70°	285.6	282.1	281.5	282.8	286.9	291.6	299.1	311.9	332.9	363.3	403.3
72.5°	247.6	245.4	245.2	248.2	250.1	253.2	258.5	270.3	286.9	309.8	347.0
75°	193.6	193.6	193.6	194.2	196.2	199.0	203.0	209.1	222.0	238.2	263.2
77.5°	145.1	144.9	144.1	144.0	147.0	148.2	149.1	154.8	162.0	173.0	191.2
80°	113.7	110.3	111.7	113.7	115.0	115.7	117.8	119.1	125.2	131.3	144.1
82.5°	84.5	81.6	81.9	85.0	85.2	85.9	88.0	89.9	92.1	97.7	104.6
85°	44.7	44.7	45.4	45.4	46.0	45.4	47.4	48.0	48.0	51.4	55.4
87.5°	20.1	18.9	19.5	19.9	19.3	19.8	20.1	20.6	21.0	21.4	21.6
90°	19.2	18.9	18.6	18.3	18.0	17.7	17.0	16.4	15.9	15.3	13.5
92.5°	25.8	26.0	26.2	26.3	26.5	26.3	25.9	25.5	25.0	24.5	23.5
95°	49.9	49.9	49.9	49.9	49.9	49.6	49.0	48.4	47.9	47.3	46.1
97.5°	76.7	76.7	76.8	76.9	76.9	76.6	75.9	75.3	74.6	74.0	73.2
100°	97.1	96.9	96.6	96.3	96.0	95.7	95.2	94.8	94.4	93.9	93.2
102.5°	118.1	118.1	118.2	118.3	118.3	118.1	117.7	117.3	116.8	116.4	115.5
105°	152.1	151.8	151.5	151.3	150.9	150.8	150.8	150.8	150.8	150.8	149.6
107.5°	187.5	187.7	187.9	188.0	188.2	188.0	187.6	187.1	186.7	186.2	185.7
110°	211.5	211.8	212.1	212.4	212.7	212.5	212.0	211.4	210.9	210.3	210.0



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	237.1	237.1	237.2	237.3	237.3	237.0	236.3	235.7	235.0	234.3	234.2
115°	272.2	272.4	272.5	272.7	272.9	272.9	272.7	272.5	272.4	272.2	272.5
117.5°	307.9	308.3	308.7	309.1	309.5	309.7	309.7	309.8	309.8	309.8	310.2
120°	332.9	333.2	333.6	333.8	334.1	334.3	334.4	334.6	334.8	334.8	335.6
122.5°	357.0	357.4	357.7	358.2	358.6	359.0	359.3	359.7	360.1	360.4	360.8
125°	393.0	393.6	394.2	394.8	395.3	395.9	396.4	397.0	397.6	398.1	398.4
127.5°	429.0	429.6	430.2	430.9	431.5	432.3	433.1	433.9	434.6	435.5	435.8
130°	452.5	453.5	454.4	455.5	456.4	457.2	457.8	458.4	458.9	459.5	459.9
132.5°	477.0	477.8	478.5	479.3	480.1	480.8	481.5	482.2	482.8	483.5	483.8
135°	515.1	515.4	515.7	515.9	516.3	516.7	517.2	517.8	518.3	518.9	519.1
137.5°	548.7	549.2	549.7	550.4	550.9	551.5	552.0	552.6	553.2	553.8	553.5
140°	570.7	571.7	572.7	573.7	574.6	575.2	575.4	575.5	575.7	575.8	575.7
142.5°	593.1	593.9	594.7	595.5	596.2	596.7	596.8	597.0	597.1	597.3	597.0
145°	625.7	626.2	626.8	627.3	627.9	628.3	628.4	628.5	628.7	628.9	628.4
147.5°	654.5	655.4	656.3	657.1	658.0	658.4	658.4	658.4	658.4	658.4	658.0
150°	673.0	673.8	674.7	675.5	676.3	676.7	676.7	676.7	676.7	676.7	676.5
152.5°	690.9	691.6	692.3	693.0	693.8	694.1	693.8	693.6	693.4	693.1	692.9
155°	715.1	716.1	717.1	718.1	719.1	719.3	718.8	718.2	717.6	717.0	716.9
157.5°	737.2	738.0	738.8	739.6	740.4	740.5	739.9	739.3	738.7	738.1	738.0
160°	751.6	752.1	752.7	753.3	753.8	753.7	753.0	752.3	751.7	750.9	750.9
162.5°	762.2	763.2	764.1	765.0	765.9	766.0	765.3	764.6	763.9	763.2	763.1
165°	777.7	778.8	779.7	780.8	781.7	781.8	780.9	780.1	779.2	778.3	778.3
167.5°	790.9	791.8	792.6	793.6	794.4	794.4	793.6	792.6	791.8	790.9	790.8
170°	797.5	798.6	799.5	800.6	801.5	801.5	800.6	799.5	798.6	797.5	797.5
172.5°	802.7	803.7	804.7	805.6	806.7	806.7	805.8	804.9	804.1	803.1	803.1
175°	808.4	809.4	810.4	811.4	812.4	812.4	811.6	810.8	809.9	809.1	809.1
177.5°	811.5	812.3	813.0	813.9	814.7	814.8	814.1	813.4	812.7	812.0	812.0
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1439.9	1435.6	1431.3	1423.7	1417.2	1408.0	1405.3	1402.1	1392.3	1383.7	1377.2
5°	1527.9	1511.7	1488.0	1466.4	1448.8	1425.1	1411.5	1397.3	1377.0	1358.7	1343.8
7.5°	1620.0	1588.0	1551.2	1511.4	1474.4	1438.6	1409.8	1384.1	1355.6	1328.7	1307.8
10°	1693.1	1647.0	1595.6	1540.2	1492.7	1446.7	1408.2	1374.3	1337.8	1306.0	1279.6
12.5°	1776.4	1708.2	1637.3	1569.9	1513.9	1450.0	1403.3	1360.3	1318.9	1280.6	1250.9
15°	1875.1	1788.5	1704.5	1611.9	1526.6	1446.7	1391.3	1337.1	1289.1	1249.8	1211.9
17.5°	1965.0	1866.8	1756.3	1643.5	1540.7	1446.0	1368.2	1307.1	1247.0	1198.9	1161.1
20°	2015.9	1904.2	1779.0	1661.9	1548.3	1442.7	1357.5	1284.4	1219.3	1168.6	1126.0
22.5°	2059.7	1929.1	1799.6	1674.4	1547.7	1434.0	1337.4	1262.1	1191.8	1142.1	1096.7
25°	2105.1	1948.9	1818.9	1672.1	1530.7	1412.9	1304.7	1219.3	1149.0	1090.8	1044.1
27.5°	2144.1	1947.5	1793.3	1635.4	1503.8	1385.9	1270.2	1178.8	1104.1	1040.9	993.5
30°	2170.1	1950.2	1766.8	1610.5	1477.9	1356.1	1243.7	1151.7	1073.2	1008.9	964.2
32.5°	2186.3	1948.5	1742.4	1575.9	1436.8	1329.0	1215.0	1119.7	1039.1	975.9	932.9
35°	2195.8	1936.6	1700.5	1504.3	1370.3	1265.4	1170.0	1071.2	986.6	927.7	879.0
37.5°	2176.9	1911.6	1651.7	1435.2	1288.6	1185.3	1105.0	1020.8	939.9	875.1	833.1
40°	2147.1	1895.4	1613.9	1386.6	1232.3	1132.7	1064.5	981.9	902.0	840.4	801.2
42.5°	2090.2	1862.3	1572.2	1332.4	1173.8	1074.3	1011.3	942.4	866.9	809.0	769.8
45°	1951.5	1790.4	1509.7	1251.2	1087.4	984.6	929.1	879.0	810.6	754.5	720.7
47.5°	1759.1	1682.4	1419.3	1165.5	997.3	898.4	840.7	800.4	750.4	705.1	672.6
50°	1625.4	1593.5	1358.1	1107.1	937.2	840.4	785.0	748.4	712.6	667.2	637.4
52.5°	1471.1	1490.7	1286.7	1046.4	876.1	780.9	728.7	699.6	667.1	629.8	603.9
55°	1253.9	1324.9	1163.2	944.6	785.0	694.3	644.9	619.1	600.2	572.5	550.2
57.5°	1050.5	1140.9	1029.8	839.7	695.5	617.3	569.9	541.9	529.7	515.2	497.7
60°	929.8	1019.1	934.5	769.4	635.4	560.9	519.0	495.3	483.1	473.0	458.1
62.5°	822.0	912.4	841.4	697.9	576.4	507.4	470.8	447.7	438.2	432.9	420.3
65°	674.0	751.8	704.4	586.7	492.0	431.0	397.9	381.7	372.8	370.8	362.7
67.5°	548.5	607.8	573.3	486.6	412.1	359.5	331.3	317.5	310.7	310.0	303.9
70°	466.2	521.7	495.3	416.8	352.6	311.3	286.9	274.7	270.7	270.0	266.7
72.5°	402.3	441.1	420.1	354.6	304.9	267.4	249.5	236.9	232.2	233.2	230.9
75°	297.7	326.8	314.7	269.3	229.4	205.0	190.1	182.0	178.0	180.0	177.3
77.5°	214.2	232.6	221.7	190.3	165.7	148.1	137.1	132.1	128.5	128.3	127.1
80°	161.7	172.5	166.4	147.5	127.3	112.4	103.5	100.1	98.2	97.5	96.8
82.5°	115.2	124.4	117.2	104.2	90.4	81.5	76.5	72.0	70.5	70.9	70.3
85°	58.2	61.6	58.9	50.7	45.4	41.2	38.6	36.5	35.2	35.9	34.5
87.5°	22.4	22.6	20.6	18.1	16.7	14.8	14.5	13.1	12.3	12.6	12.3
90°	11.6	9.8	7.9	6.3	4.9	3.4	2.1	0.6	2.1	3.4	4.9
92.5°	22.5	21.4	20.3	19.3	18.3	17.4	16.4	15.5	16.4	17.4	18.3
95°	45.0	43.9	42.7	41.7	40.7	39.7	38.7	37.7	38.7	39.7	40.7
97.5°	72.3	71.5	70.7	69.9	69.2	68.4	67.7	67.0	67.7	68.4	69.2
100°	92.6	91.8	91.1	90.3	89.5	88.6	87.7	86.9	87.7	88.6	89.5
102.5°	114.6	113.7	112.7	111.9	111.4	111.0	110.5	109.9	110.5	111.0	111.4
105°	148.3	147.0	145.7	144.9	144.6	144.4	144.0	143.8	144.0	144.4	144.6
107.5°	185.2	184.7	184.2	183.8	183.7	183.5	183.3	183.1	183.3	183.5	183.7
110°	209.7	209.4	209.1	208.8	208.5	208.3	208.0	207.7	208.0	208.3	208.5



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	234.2	234.1	234.0	233.9	233.8	233.6	233.4	233.2	233.4	233.6	233.8
115°	272.9	273.1	273.4	273.3	272.9	272.4	272.0	271.6	272.0	272.4	272.9
117.5°	310.6	310.9	311.3	311.3	311.1	310.7	310.5	310.2	310.5	310.7	311.1
120°	336.3	337.0	337.7	337.7	336.8	336.0	335.1	334.2	335.1	336.0	336.8
122.5°	361.2	361.5	361.9	361.8	361.2	360.5	359.9	359.3	359.9	360.5	361.2
125°	398.7	399.0	399.2	399.2	398.8	398.4	398.0	397.5	398.0	398.4	398.8
127.5°	436.1	436.4	436.7	436.4	435.5	434.6	433.7	432.7	433.7	434.6	435.5
130°	460.4	460.8	461.2	460.8	459.7	458.6	457.4	456.3	457.4	458.6	459.7
132.5°	484.1	484.5	484.7	484.4	483.2	482.1	481.0	479.8	481.0	482.1	483.2
135°	519.2	519.4	519.5	519.1	518.3	517.5	516.6	515.7	516.6	517.5	518.3
137.5°	553.1	552.7	552.3	551.8	551.1	550.4	549.7	549.0	549.7	550.4	551.1
140°	575.5	575.4	575.2	574.8	574.1	573.4	572.7	572.0	572.7	573.4	574.1
142.5°	596.8	596.5	596.2	595.7	595.0	594.3	593.7	593.0	593.7	594.3	595.0
145°	628.0	627.6	627.2	626.8	626.5	626.2	625.9	625.7	625.9	626.2	626.5
147.5°	657.5	657.2	656.8	656.3	655.8	655.3	654.8	654.3	654.8	655.3	655.8
150°	676.2	675.9	675.6	675.4	675.1	674.8	674.5	674.2	674.5	674.8	675.1
152.5°	692.8	692.6	692.4	692.2	691.8	691.4	691.0	690.6	691.0	691.4	691.8
155°	716.8	716.6	716.4	716.4	716.4	716.4	716.4	716.4	716.4	716.4	716.4
157.5°	737.9	737.8	737.7	737.7	737.9	738.0	738.2	738.4	738.2	738.0	737.9
160°	750.9	750.9	750.9	751.1	751.3	751.7	751.9	752.2	751.9	751.7	751.3
162.5°	762.9	762.8	762.8	762.8	763.3	763.6	764.1	764.5	764.1	763.6	763.3
165°	778.3	778.3	778.3	778.6	779.0	779.5	779.9	780.3	779.9	779.5	779.0
167.5°	790.7	790.6	790.5	790.7	791.3	791.9	792.4	793.0	792.4	791.9	791.3
170°	797.5	797.5	797.5	797.8	798.4	799.0	799.5	800.1	799.5	799.0	798.4
172.5°	803.1	803.1	803.1	803.5	804.0	804.6	805.2	805.7	805.2	804.6	804.0
175°	809.1	809.1	809.1	809.3	809.9	810.5	811.1	811.6	811.1	810.5	809.9
177.5°	812.0	812.0	812.0	812.3	812.7	813.1	813.6	814.1	813.6	813.1	812.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1373.4	1369.6	1364.2	1356.1	1349.5	1339.3	1339.3	1340.9	1340.9	1340.4	1339.3
5°	1331.7	1321.5	1309.4	1295.2	1280.3	1265.4	1262.7	1257.2	1253.2	1250.5	1247.2
7.5°	1287.7	1269.7	1252.0	1232.1	1213.9	1198.9	1188.5	1179.8	1174.3	1168.4	1164.0
10°	1257.9	1235.6	1214.6	1193.7	1170.6	1152.4	1140.9	1132.7	1126.7	1121.3	1118.5
12.5°	1222.8	1197.2	1174.1	1154.2	1128.9	1110.2	1099.2	1095.4	1088.2	1076.9	1070.9
15°	1171.3	1147.6	1119.9	1089.4	1077.3	1054.3	1041.4	1035.4	1031.2	1022.4	1019.8
17.5°	1127.3	1096.3	1065.2	1042.5	1019.9	1001.2	994.0	986.4	981.0	973.9	971.7
20°	1092.2	1064.5	1036.0	1011.7	987.9	967.7	961.6	956.1	950.7	947.4	944.6
22.5°	1056.4	1028.7	1005.1	982.4	957.1	943.8	937.2	931.3	927.5	925.1	922.5
25°	1006.3	981.9	955.5	935.1	914.9	906.0	902.0	898.6	896.0	892.5	891.8
27.5°	961.3	934.8	913.3	894.4	879.9	872.5	868.6	866.9	867.5	868.7	869.5
30°	927.7	903.4	885.8	869.5	856.0	849.2	848.5	848.5	851.3	852.0	853.3
32.5°	896.9	876.8	859.3	843.5	833.3	828.6	831.2	831.2	833.4	835.2	837.6
35°	852.0	834.3	820.8	807.3	798.5	800.5	801.8	803.2	806.6	810.6	813.4
37.5°	809.0	793.8	779.6	769.1	765.1	768.7	772.0	774.8	778.7	781.9	784.5
40°	778.2	766.6	753.1	743.6	745.0	747.1	749.8	753.1	756.6	758.5	761.3
42.5°	749.5	737.4	727.2	719.3	721.2	723.8	725.4	727.2	731.1	734.8	736.3
45°	705.8	696.3	686.8	682.1	683.5	684.8	686.1	688.2	691.6	694.3	694.9
47.5°	656.7	650.1	643.7	639.0	641.2	640.7	642.5	646.8	647.8	649.5	653.2
50°	625.3	619.1	611.7	610.4	610.4	610.4	611.1	616.5	616.5	619.1	621.9
52.5°	590.6	586.7	581.9	579.5	578.4	578.4	581.3	584.0	585.0	588.8	591.6
55°	539.3	535.3	531.2	529.2	527.8	529.2	534.6	535.9	539.3	541.3	543.4
57.5°	485.9	482.8	479.5	478.4	478.1	479.9	482.8	486.9	487.8	494.0	497.1
60°	450.6	445.9	443.2	443.2	441.9	448.0	446.6	453.4	454.7	458.8	463.6
62.5°	414.4	408.0	407.0	407.0	408.9	410.6	412.5	415.5	419.0	424.1	427.8
65°	355.9	352.6	357.3	356.6	355.2	359.3	359.3	362.7	366.8	371.5	378.9
67.5°	300.6	298.9	299.2	299.2	301.3	303.6	305.5	308.4	313.3	318.3	323.2
70°	263.2	265.3	261.9	264.6	266.7	267.3	268.6	272.7	278.1	281.5	286.9
72.5°	227.0	226.8	227.2	228.3	230.3	231.5	232.9	237.5	243.5	246.3	250.6
75°	174.6	173.9	175.9	175.9	179.3	180.6	182.0	184.1	189.5	193.6	196.9
77.5°	127.5	128.3	127.9	130.2	129.2	129.5	133.7	135.8	136.3	144.3	146.0
80°	96.1	97.5	98.2	98.8	99.4	98.2	102.9	104.9	104.9	109.6	113.0
82.5°	69.1	69.8	71.6	72.2	72.4	73.8	74.1	75.7	77.3	79.3	83.8
85°	34.5	36.5	37.2	36.5	37.2	35.9	37.9	38.6	39.3	39.3	39.3
87.5°	12.1	13.0	12.8	13.7	13.5	14.5	14.6	13.6	13.7	15.4	13.3
90°	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.4	17.0	17.7	18.0
92.5°	19.3	20.3	21.4	22.5	23.5	24.5	25.0	25.5	25.9	26.3	26.5
95°	41.7	42.7	43.9	45.0	46.1	47.3	47.9	48.4	49.0	49.6	49.9
97.5°	69.9	70.7	71.5	72.3	73.2	74.0	74.6	75.3	75.9	76.6	76.9
100°	90.3	91.1	91.8	92.6	93.2	93.9	94.4	94.8	95.2	95.7	96.0
102.5°	111.9	112.7	113.7	114.6	115.5	116.4	116.8	117.3	117.7	118.1	118.3
105°	144.9	145.7	147.0	148.3	149.6	150.8	150.8	150.8	150.8	150.8	150.9
107.5°	183.8	184.2	184.7	185.2	185.7	186.2	186.7	187.1	187.6	188.0	188.2
110°	208.8	209.1	209.4	209.7	210.0	210.3	210.9	211.4	212.0	212.5	212.7



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	233.9	234.0	234.1	234.2	234.2	234.3	235.0	235.7	236.3	237.0	237.3
115°	273.3	273.4	273.1	272.9	272.5	272.2	272.4	272.5	272.7	272.9	272.9
117.5°	311.3	311.3	310.9	310.6	310.2	309.8	309.8	309.8	309.7	309.7	309.5
120°	337.7	337.7	337.0	336.3	335.6	334.8	334.8	334.6	334.4	334.3	334.1
122.5°	361.8	361.9	361.5	361.2	360.8	360.4	360.1	359.7	359.3	359.0	358.6
125°	399.2	399.2	399.0	398.7	398.4	398.1	397.6	397.0	396.4	395.9	395.3
127.5°	436.4	436.7	436.4	436.1	435.8	435.5	434.6	433.9	433.1	432.3	431.5
130°	460.8	461.2	460.8	460.4	459.9	459.5	458.9	458.4	457.8	457.2	456.4
132.5°	484.4	484.7	484.5	484.1	483.8	483.5	482.8	482.2	481.5	480.8	480.1
135°	519.1	519.5	519.4	519.2	519.1	518.9	518.3	517.8	517.2	516.7	516.3
137.5°	551.8	552.3	552.7	553.1	553.5	553.8	553.2	552.6	552.0	551.5	550.9
140°	574.8	575.2	575.4	575.5	575.7	575.8	575.7	575.5	575.4	575.2	574.6
142.5°	595.7	596.2	596.5	596.8	597.0	597.3	597.1	597.0	596.8	596.7	596.2
145°	626.8	627.2	627.6	628.0	628.4	628.9	628.7	628.5	628.4	628.3	627.9
147.5°	656.3	656.8	657.2	657.5	658.0	658.4	658.4	658.4	658.4	658.4	658.0
150°	675.4	675.6	675.9	676.2	676.5	676.7	676.7	676.7	676.7	676.7	676.3
152.5°	692.2	692.4	692.6	692.8	692.9	693.1	693.4	693.6	693.8	694.1	693.8
155°	716.4	716.4	716.6	716.8	716.9	717.0	717.6	718.2	718.8	719.3	719.1
157.5°	737.7	737.7	737.8	737.9	738.0	738.1	738.7	739.3	739.9	740.5	740.4
160°	751.1	750.9	750.9	750.9	750.9	750.9	751.7	752.3	753.0	753.7	753.8
162.5°	762.8	762.8	762.8	762.9	763.1	763.2	763.9	764.6	765.3	766.0	765.9
165°	778.6	778.3	778.3	778.3	778.3	778.3	779.2	780.1	780.9	781.8	781.7
167.5°	790.7	790.5	790.6	790.7	790.8	790.9	791.8	792.6	793.6	794.4	794.4
170°	797.8	797.5	797.5	797.5	797.5	797.5	798.6	799.5	800.6	801.5	801.5
172.5°	803.5	803.1	803.1	803.1	803.1	803.1	804.1	804.9	805.8	806.7	806.7
175°	809.3	809.1	809.1	809.1	809.1	809.1	809.9	810.8	811.6	812.4	812.4
177.5°	812.3	812.0	812.0	812.0	812.0	812.0	812.7	813.4	814.1	814.8	814.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1335.5	1335.0	1338.8	1336.0	1338.8	1335.0	1335.5	1339.3	1340.4	1340.9	1340.9
5°	1243.0	1245.1	1238.3	1238.3	1238.3	1245.1	1243.0	1247.2	1250.5	1253.2	1257.2
7.5°	1160.8	1157.8	1158.0	1154.4	1158.0	1157.8	1160.8	1164.0	1168.4	1174.3	1179.8
10°	1110.4	1106.4	1105.0	1105.7	1105.0	1106.4	1110.4	1118.5	1121.3	1126.7	1132.7
12.5°	1068.8	1067.9	1059.0	1059.1	1059.0	1067.9	1068.8	1070.9	1076.9	1088.2	1095.4
15°	1019.8	1006.9	1005.6	1009.6	1005.6	1006.9	1019.8	1019.8	1022.4	1031.2	1035.4
17.5°	970.6	963.9	964.2	962.3	964.2	963.9	970.6	971.7	973.9	981.0	986.4
20°	944.6	940.6	939.9	935.1	939.9	940.6	944.6	944.6	947.4	950.7	956.1
22.5°	920.8	919.5	919.9	914.6	919.9	919.5	920.8	922.5	925.1	927.5	931.3
25°	891.2	894.6	891.8	891.8	891.8	894.6	891.2	891.8	892.5	896.0	898.6
27.5°	871.2	871.0	869.7	869.7	869.7	871.0	871.2	869.5	868.7	867.5	866.9
30°	856.0	855.3	856.7	856.7	856.7	855.3	856.0	853.3	852.0	851.3	848.5
32.5°	840.9	841.8	842.1	842.6	842.1	841.8	840.9	837.6	835.2	833.4	831.2
35°	817.4	818.1	820.1	818.8	820.1	818.1	817.4	813.4	810.6	806.6	803.2
37.5°	785.7	788.8	788.2	789.3	788.2	788.8	785.7	784.5	781.9	778.7	774.8
40°	761.9	764.0	763.3	763.3	763.3	764.0	761.9	761.3	758.5	756.6	753.1
42.5°	737.6	739.1	737.3	736.2	737.3	739.1	737.6	736.3	734.8	731.1	727.2
45°	697.7	696.3	698.4	695.6	698.4	696.3	697.7	694.9	694.3	691.6	688.2
47.5°	653.0	654.4	654.9	656.9	654.9	654.4	653.0	653.2	649.5	647.8	646.8
50°	623.2	627.2	627.2	626.6	627.2	627.2	623.2	621.9	619.1	616.5	616.5
52.5°	594.0	595.9	598.6	598.5	598.6	595.9	594.0	591.6	588.8	585.0	584.0
55°	548.8	550.2	551.5	552.2	551.5	550.2	548.8	543.4	541.3	539.3	535.9
57.5°	502.0	501.4	504.6	505.6	504.6	501.4	502.0	497.1	494.0	487.8	486.9
60°	468.9	468.9	474.3	476.4	474.3	468.9	468.9	463.6	458.8	454.7	453.4
62.5°	433.8	435.9	441.3	438.5	441.3	435.9	433.8	427.8	424.1	419.0	415.5
65°	382.3	387.7	387.0	389.8	387.0	387.7	382.3	378.9	371.5	366.8	362.7
67.5°	328.6	332.0	336.8	337.3	336.8	332.0	328.6	323.2	318.3	313.3	308.4
70°	292.3	295.7	298.4	300.4	298.4	295.7	292.3	286.9	281.5	278.1	272.7
72.5°	257.2	258.9	265.4	262.5	265.4	258.9	257.2	250.6	246.3	243.5	237.5
75°	201.6	206.4	210.4	208.4	210.4	206.4	201.6	196.9	193.6	189.5	184.1
77.5°	149.1	153.9	155.8	154.0	155.8	153.9	149.1	146.0	144.3	136.3	135.8
80°	117.8	117.1	121.1	120.5	121.1	117.1	117.8	113.0	109.6	104.9	104.9
82.5°	86.4	85.7	87.6	88.0	87.6	85.7	86.4	83.8	79.3	77.3	75.7
85°	41.9	44.0	41.2	40.6	41.2	44.0	41.9	39.3	39.3	39.3	38.6
87.5°	13.4	13.4	13.0	12.5	13.0	13.4	13.4	13.3	15.4	13.7	13.6
90°	18.3	18.6	18.9	19.2	18.9	18.6	18.3	18.0	17.7	17.0	16.4
92.5°	26.3	26.2	26.0	25.8	26.0	26.2	26.3	26.5	26.3	25.9	25.5
95°	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.9	49.6	49.0	48.4
97.5°	76.9	76.8	76.7	76.7	76.7	76.8	76.9	76.9	76.6	75.9	75.3
100°	96.3	96.6	96.9	97.1	96.9	96.6	96.3	96.0	95.7	95.2	94.8
102.5°	118.3	118.2	118.1	118.1	118.1	118.2	118.3	118.3	118.1	117.7	117.3
105°	151.3	151.5	151.8	152.1	151.8	151.5	151.3	150.9	150.8	150.8	150.8
107.5°	188.0	187.9	187.7	187.5	187.7	187.9	188.0	188.2	188.0	187.6	187.1
110°	212.4	212.1	211.8	211.5	211.8	212.1	212.4	212.7	212.5	212.0	211.4



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	237.3	237.2	237.1	237.1	237.1	237.2	237.3	237.3	237.0	236.3	235.7
115°	272.7	272.5	272.4	272.2	272.4	272.5	272.7	272.9	272.9	272.7	272.5
117.5°	309.1	308.7	308.3	307.9	308.3	308.7	309.1	309.5	309.7	309.7	309.8
120°	333.8	333.6	333.2	332.9	333.2	333.6	333.8	334.1	334.3	334.4	334.6
122.5°	358.2	357.7	357.4	357.0	357.4	357.7	358.2	358.6	359.0	359.3	359.7
125°	394.8	394.2	393.6	393.0	393.6	394.2	394.8	395.3	395.9	396.4	397.0
127.5°	430.9	430.2	429.6	429.0	429.6	430.2	430.9	431.5	432.3	433.1	433.9
130°	455.5	454.4	453.5	452.5	453.5	454.4	455.5	456.4	457.2	457.8	458.4
132.5°	479.3	478.5	477.8	477.0	477.8	478.5	479.3	480.1	480.8	481.5	482.2
135°	515.9	515.7	515.4	515.1	515.4	515.7	515.9	516.3	516.7	517.2	517.8
137.5°	550.4	549.7	549.2	548.7	549.2	549.7	550.4	550.9	551.5	552.0	552.6
140°	573.7	572.7	571.7	570.7	571.7	572.7	573.7	574.6	575.2	575.4	575.5
142.5°	595.5	594.7	593.9	593.1	593.9	594.7	595.5	596.2	596.7	596.8	597.0
145°	627.3	626.8	626.2	625.7	626.2	626.8	627.3	627.9	628.3	628.4	628.5
147.5°	657.1	656.3	655.4	654.5	655.4	656.3	657.1	658.0	658.4	658.4	658.4
150°	675.5	674.7	673.8	673.0	673.8	674.7	675.5	676.3	676.7	676.7	676.7
152.5°	693.0	692.3	691.6	690.9	691.6	692.3	693.0	693.8	694.1	693.8	693.6
155°	718.1	717.1	716.1	715.1	716.1	717.1	718.1	719.1	719.3	718.8	718.2
157.5°	739.6	738.8	738.0	737.2	738.0	738.8	739.6	740.4	740.5	739.9	739.3
160°	753.3	752.7	752.1	751.6	752.1	752.7	753.3	753.8	753.7	753.0	752.3
162.5°	765.0	764.1	763.2	762.2	763.2	764.1	765.0	765.9	766.0	765.3	764.6
165°	780.8	779.7	778.8	777.7	778.8	779.7	780.8	781.7	781.8	780.9	780.1
167.5°	793.6	792.6	791.8	790.9	791.8	792.6	793.6	794.4	794.4	793.6	792.6
170°	800.6	799.5	798.6	797.5	798.6	799.5	800.6	801.5	801.5	800.6	799.5
172.5°	805.6	804.7	803.7	802.7	803.7	804.7	805.6	806.7	806.7	805.8	804.9
175°	811.4	810.4	809.4	808.4	809.4	810.4	811.4	812.4	812.4	811.6	810.8
177.5°	813.9	813.0	812.3	811.5	812.3	813.0	813.9	814.7	814.8	814.1	813.4
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1339.3	1339.3	1349.5	1356.1	1364.2	1369.6	1373.4	1377.2	1383.7	1392.3	1402.1
5°	1262.7	1265.4	1280.3	1295.2	1309.4	1321.5	1331.7	1343.8	1358.7	1377.0	1397.3
7.5°	1188.5	1198.9	1213.9	1232.1	1252.0	1269.7	1287.7	1307.8	1328.7	1355.6	1384.1
10°	1140.9	1152.4	1170.6	1193.7	1214.6	1235.6	1257.9	1279.6	1306.0	1337.8	1374.3
12.5°	1099.2	1110.2	1128.9	1154.2	1174.1	1197.2	1222.8	1250.9	1280.6	1318.9	1360.3
15°	1041.4	1054.3	1077.3	1089.4	1119.9	1147.6	1171.3	1211.9	1249.8	1289.1	1337.1
17.5°	994.0	1001.2	1019.9	1042.5	1065.2	1096.3	1127.3	1161.1	1198.9	1247.0	1307.1
20°	961.6	967.7	987.9	1011.7	1036.0	1064.5	1092.2	1126.0	1168.6	1219.3	1284.4
22.5°	937.2	943.8	957.1	982.4	1005.1	1028.7	1056.4	1096.7	1142.1	1191.8	1262.1
25°	902.0	906.0	914.9	935.1	955.5	981.9	1006.3	1044.1	1090.8	1149.0	1219.3
27.5°	868.6	872.5	879.9	894.4	913.3	934.8	961.3	993.5	1040.9	1104.1	1178.8
30°	848.5	849.2	856.0	869.5	885.8	903.4	927.7	964.2	1008.9	1073.2	1151.7
32.5°	831.2	828.6	833.3	843.5	859.3	876.8	896.9	932.9	975.9	1039.1	1119.7
35°	801.8	800.5	798.5	807.3	820.8	834.3	852.0	879.0	927.7	986.6	1071.2
37.5°	772.0	768.7	765.1	769.1	779.6	793.8	809.0	833.1	875.1	939.9	1020.8
40°	749.8	747.1	745.0	743.6	753.1	766.6	778.2	801.2	840.4	902.0	981.9
42.5°	725.4	723.8	721.2	719.3	727.2	737.4	749.5	769.8	809.0	866.9	942.4
45°	686.1	684.8	683.5	682.1	686.8	696.3	705.8	720.7	754.5	810.6	879.0
47.5°	642.5	640.7	641.2	639.0	643.7	650.1	656.7	672.6	705.1	750.4	800.4
50°	611.1	610.4	610.4	610.4	611.7	619.1	625.3	637.4	667.2	712.6	748.4
52.5°	581.3	578.4	578.4	579.5	581.9	586.7	590.6	603.9	629.8	667.1	699.6
55°	534.6	529.2	527.8	529.2	531.2	535.3	539.3	550.2	572.5	600.2	619.1
57.5°	482.8	479.9	478.1	478.4	479.5	482.8	485.9	497.7	515.2	529.7	541.9
60°	446.6	448.0	441.9	443.2	443.2	445.9	450.6	458.1	473.0	483.1	495.3
62.5°	412.5	410.6	408.9	407.0	407.0	408.0	414.4	420.3	432.9	438.2	447.7
65°	359.3	359.3	355.2	356.6	357.3	352.6	355.9	362.7	370.8	372.8	381.7
67.5°	305.5	303.6	301.3	299.2	299.2	298.9	300.6	303.9	310.0	310.7	317.5
70°	268.6	267.3	266.7	264.6	261.9	265.3	263.2	266.7	270.0	270.7	274.7
72.5°	232.9	231.5	230.3	228.3	227.2	226.8	227.0	230.9	233.2	232.2	236.9
75°	182.0	180.6	179.3	175.9	175.9	173.9	174.6	177.3	180.0	178.0	182.0
77.5°	133.7	129.5	129.2	130.2	127.9	128.3	127.5	127.1	128.3	128.5	132.1
80°	102.9	98.2	99.4	98.8	98.2	97.5	96.1	96.8	97.5	98.2	100.1
82.5°	74.1	73.8	72.4	72.2	71.6	69.8	69.1	70.3	70.9	70.5	72.0
85°	37.9	35.9	37.2	36.5	37.2	36.5	34.5	34.5	35.9	35.2	36.5
87.5°	14.6	14.5	13.5	13.7	12.8	13.0	12.1	12.3	12.6	12.3	13.1
90°	15.9	15.3	13.5	11.6	9.8	7.9	6.3	4.9	3.4	2.1	0.6
92.5°	25.0	24.5	23.5	22.5	21.4	20.3	19.3	18.3	17.4	16.4	15.5
95°	47.9	47.3	46.1	45.0	43.9	42.7	41.7	40.7	39.7	38.7	37.7
97.5°	74.6	74.0	73.2	72.3	71.5	70.7	69.9	69.2	68.4	67.7	67.0
100°	94.4	93.9	93.2	92.6	91.8	91.1	90.3	89.5	88.6	87.7	86.9
102.5°	116.8	116.4	115.5	114.6	113.7	112.7	111.9	111.4	111.0	110.5	109.9
105°	150.8	150.8	149.6	148.3	147.0	145.7	144.9	144.6	144.4	144.0	143.8
107.5°	186.7	186.2	185.7	185.2	184.7	184.2	183.8	183.7	183.5	183.3	183.1
110°	210.9	210.3	210.0	209.7	209.4	209.1	208.8	208.5	208.3	208.0	207.7



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	235.0	234.3	234.2	234.2	234.1	234.0	233.9	233.8	233.6	233.4	233.2
115°	272.4	272.2	272.5	272.9	273.1	273.4	273.3	272.9	272.4	272.0	271.6
117.5°	309.8	309.8	310.2	310.6	310.9	311.3	311.3	311.1	310.7	310.5	310.2
120°	334.8	334.8	335.6	336.3	337.0	337.7	337.7	336.8	336.0	335.1	334.2
122.5°	360.1	360.4	360.8	361.2	361.5	361.9	361.8	361.2	360.5	359.9	359.3
125°	397.6	398.1	398.4	398.7	399.0	399.2	399.2	398.8	398.4	398.0	397.5
127.5°	434.6	435.5	435.8	436.1	436.4	436.7	436.4	435.5	434.6	433.7	432.7
130°	458.9	459.5	459.9	460.4	460.8	461.2	460.8	459.7	458.6	457.4	456.3
132.5°	482.8	483.5	483.8	484.1	484.5	484.7	484.4	483.2	482.1	481.0	479.8
135°	518.3	518.9	519.1	519.2	519.4	519.5	519.1	518.3	517.5	516.6	515.7
137.5°	553.2	553.8	553.5	553.1	552.7	552.3	551.8	551.1	550.4	549.7	549.0
140°	575.7	575.8	575.7	575.5	575.4	575.2	574.8	574.1	573.4	572.7	572.0
142.5°	597.1	597.3	597.0	596.8	596.5	596.2	595.7	595.0	594.3	593.7	593.0
145°	628.7	628.9	628.4	628.0	627.6	627.2	626.8	626.5	626.2	625.9	625.7
147.5°	658.4	658.4	658.0	657.5	657.2	656.8	656.3	655.8	655.3	654.8	654.3
150°	676.7	676.7	676.5	676.2	675.9	675.6	675.4	675.1	674.8	674.5	674.2
152.5°	693.4	693.1	692.9	692.8	692.6	692.4	692.2	691.8	691.4	691.0	690.6
155°	717.6	717.0	716.9	716.8	716.6	716.4	716.4	716.4	716.4	716.4	716.4
157.5°	738.7	738.1	738.0	737.9	737.8	737.7	737.7	737.9	738.0	738.2	738.4
160°	751.7	750.9	750.9	750.9	750.9	750.9	751.1	751.3	751.7	751.9	752.2
162.5°	763.9	763.2	763.1	762.9	762.8	762.8	762.8	763.3	763.6	764.1	764.5
165°	779.2	778.3	778.3	778.3	778.3	778.3	778.6	779.0	779.5	779.9	780.3
167.5°	791.8	790.9	790.8	790.7	790.6	790.5	790.7	791.3	791.9	792.4	793.0
170°	798.6	797.5	797.5	797.5	797.5	797.5	797.8	798.4	799.0	799.5	800.1
172.5°	804.1	803.1	803.1	803.1	803.1	803.1	803.5	804.0	804.6	805.2	805.7
175°	809.9	809.1	809.1	809.1	809.1	809.1	809.3	809.9	810.5	811.1	811.6
177.5°	812.7	812.0	812.0	812.0	812.0	812.0	812.3	812.7	813.1	813.6	814.1
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1405.3	1408.0	1417.2	1423.7	1431.3	1435.6	1439.9	1443.2	1447.5	1448.6	1464.3
5°	1411.5	1425.1	1448.8	1466.4	1488.0	1511.7	1527.9	1535.4	1555.0	1571.2	1603.7
7.5°	1409.8	1438.6	1474.4	1511.4	1551.2	1588.0	1620.0	1657.9	1684.8	1725.3	1765.2
10°	1408.2	1446.7	1492.7	1540.2	1595.6	1647.0	1693.1	1744.5	1787.1	1843.2	1891.3
12.5°	1403.3	1450.0	1513.9	1569.9	1637.3	1708.2	1776.4	1842.5	1880.3	1973.8	2018.0
15°	1391.3	1446.7	1526.6	1611.9	1704.5	1788.5	1875.1	1944.1	2055.7	2137.6	2189.7
17.5°	1368.2	1446.0	1540.7	1643.5	1756.3	1866.8	1965.0	2069.7	2188.1	2287.2	2392.7
20°	1357.5	1442.7	1548.3	1661.9	1779.0	1904.2	2015.9	2141.7	2271.0	2368.4	2503.7
22.5°	1337.4	1434.0	1547.7	1674.4	1799.6	1929.1	2059.7	2186.6	2335.9	2470.1	2599.0
25°	1304.7	1412.9	1530.7	1672.1	1818.9	1948.9	2105.1	2273.6	2429.3	2601.9	2730.4
27.5°	1270.2	1385.9	1503.8	1635.4	1793.3	1947.5	2144.1	2334.5	2524.8	2673.8	2769.0
30°	1243.7	1356.1	1477.9	1610.5	1766.8	1950.2	2170.1	2377.8	2563.3	2691.1	2744.6
32.5°	1215.0	1329.0	1436.8	1575.9	1742.4	1948.5	2186.3	2403.3	2565.4	2650.6	2640.2
35°	1170.0	1265.4	1370.3	1504.3	1700.5	1936.6	2195.8	2405.5	2505.1	2486.8	2348.7
37.5°	1105.0	1185.3	1288.6	1435.2	1651.7	1911.6	2176.9	2334.3	2327.8	2179.0	1979.0
40°	1064.5	1132.7	1232.3	1386.6	1613.9	1895.4	2147.1	2249.3	2162.7	1954.9	1715.4
42.5°	1011.3	1074.3	1173.8	1332.4	1572.2	1862.3	2090.2	2119.9	1950.4	1711.3	1491.8
45°	929.1	984.6	1087.4	1251.2	1509.7	1790.4	1951.5	1879.1	1651.1	1404.1	1237.0
47.5°	840.7	898.4	997.3	1165.5	1419.3	1682.4	1759.1	1605.1	1371.0	1170.6	1017.2
50°	785.0	840.4	937.2	1107.1	1358.1	1593.5	1625.4	1426.4	1211.3	1035.4	909.5
52.5°	728.7	780.9	876.1	1046.4	1286.7	1490.7	1471.1	1268.3	1070.5	920.6	821.7
55°	644.9	694.3	785.0	944.6	1163.2	1324.9	1253.9	1060.3	896.6	780.2	705.1
57.5°	569.9	617.3	695.5	839.7	1029.8	1140.9	1050.5	887.4	757.2	667.6	611.6
60°	519.0	560.9	635.4	769.4	934.5	1019.1	929.8	785.7	676.0	604.2	554.2
62.5°	470.8	507.4	576.4	697.9	841.4	912.4	822.0	700.1	606.7	543.1	500.6
65°	397.9	431.0	492.0	586.7	704.4	751.8	674.0	575.1	502.7	455.4	427.0
67.5°	331.3	359.5	412.1	486.6	573.3	607.8	548.5	472.1	417.5	379.4	356.9
70°	286.9	311.3	352.6	416.8	495.3	521.7	466.2	403.3	363.3	332.9	311.9
72.5°	249.5	267.4	304.9	354.6	420.1	441.1	402.3	347.0	309.8	286.9	270.3
75°	190.1	205.0	229.4	269.3	314.7	326.8	297.7	263.2	238.2	222.0	209.1
77.5°	137.1	148.1	165.7	190.3	221.7	232.6	214.2	191.2	173.0	162.0	154.8
80°	103.5	112.4	127.3	147.5	166.4	172.5	161.7	144.1	131.3	125.2	119.1
82.5°	76.5	81.5	90.4	104.2	117.2	124.4	115.2	104.6	97.7	92.1	89.9
85°	38.6	41.2	45.4	50.7	58.9	61.6	58.2	55.4	51.4	48.0	48.0
87.5°	14.5	14.8	16.7	18.1	20.6	22.6	22.4	21.6	21.4	21.0	20.6
90°	2.1	3.4	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9	16.4
92.5°	16.4	17.4	18.3	19.3	20.3	21.4	22.5	23.5	24.5	25.0	25.5
95°	38.7	39.7	40.7	41.7	42.7	43.9	45.0	46.1	47.3	47.9	48.4
97.5°	67.7	68.4	69.2	69.9	70.7	71.5	72.3	73.2	74.0	74.6	75.3
100°	87.7	88.6	89.5	90.3	91.1	91.8	92.6	93.2	93.9	94.4	94.8
102.5°	110.5	111.0	111.4	111.9	112.7	113.7	114.6	115.5	116.4	116.8	117.3
105°	144.0	144.4	144.6	144.9	145.7	147.0	148.3	149.6	150.8	150.8	150.8
107.5°	183.3	183.5	183.7	183.8	184.2	184.7	185.2	185.7	186.2	186.7	187.1
110°	208.0	208.3	208.5	208.8	209.1	209.4	209.7	210.0	210.3	210.9	211.4



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	233.4	233.6	233.8	233.9	234.0	234.1	234.2	234.2	234.3	235.0	235.7
115°	272.0	272.4	272.9	273.3	273.4	273.1	272.9	272.5	272.2	272.4	272.5
117.5°	310.5	310.7	311.1	311.3	311.3	310.9	310.6	310.2	309.8	309.8	309.8
120°	335.1	336.0	336.8	337.7	337.7	337.0	336.3	335.6	334.8	334.8	334.6
122.5°	359.9	360.5	361.2	361.8	361.9	361.5	361.2	360.8	360.4	360.1	359.7
125°	398.0	398.4	398.8	399.2	399.2	399.0	398.7	398.4	398.1	397.6	397.0
127.5°	433.7	434.6	435.5	436.4	436.7	436.4	436.1	435.8	435.5	434.6	433.9
130°	457.4	458.6	459.7	460.8	461.2	460.8	460.4	459.9	459.5	458.9	458.4
132.5°	481.0	482.1	483.2	484.4	484.7	484.5	484.1	483.8	483.5	482.8	482.2
135°	516.6	517.5	518.3	519.1	519.5	519.4	519.2	519.1	518.9	518.3	517.8
137.5°	549.7	550.4	551.1	551.8	552.3	552.7	553.1	553.5	553.8	553.2	552.6
140°	572.7	573.4	574.1	574.8	575.2	575.4	575.5	575.7	575.8	575.7	575.5
142.5°	593.7	594.3	595.0	595.7	596.2	596.5	596.8	597.0	597.3	597.1	597.0
145°	625.9	626.2	626.5	626.8	627.2	627.6	628.0	628.4	628.9	628.7	628.5
147.5°	654.8	655.3	655.8	656.3	656.8	657.2	657.5	658.0	658.4	658.4	658.4
150°	674.5	674.8	675.1	675.4	675.6	675.9	676.2	676.5	676.7	676.7	676.7
152.5°	691.0	691.4	691.8	692.2	692.4	692.6	692.8	692.9	693.1	693.4	693.6
155°	716.4	716.4	716.4	716.4	716.4	716.6	716.8	716.9	717.0	717.6	718.2
157.5°	738.2	738.0	737.9	737.7	737.7	737.8	737.9	738.0	738.1	738.7	739.3
160°	751.9	751.7	751.3	751.1	750.9	750.9	750.9	750.9	750.9	751.7	752.3
162.5°	764.1	763.6	763.3	762.8	762.8	762.8	762.9	763.1	763.2	763.9	764.6
165°	779.9	779.5	779.0	778.6	778.3	778.3	778.3	778.3	778.3	779.2	780.1
167.5°	792.4	791.9	791.3	790.7	790.5	790.6	790.7	790.8	790.9	791.8	792.6
170°	799.5	799.0	798.4	797.8	797.5	797.5	797.5	797.5	797.5	798.6	799.5
172.5°	805.2	804.6	804.0	803.5	803.1	803.1	803.1	803.1	803.1	804.1	804.9
175°	811.1	810.5	809.9	809.3	809.1	809.1	809.1	809.1	809.1	809.9	810.8
177.5°	813.6	813.1	812.7	812.3	812.0	812.0	812.0	812.0	812.0	812.7	813.4
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1469.7	1470.2	1476.3	1480.6	1478.4	1481.1	1482.2
5°	1605.8	1630.1	1643.0	1652.4	1653.1	1653.8	1659.2
7.5°	1798.6	1824.7	1843.8	1872.8	1881.5	1891.3	1888.4
10°	1939.4	1977.9	2011.1	2028.7	2047.6	2075.4	2053.1
12.5°	2070.9	2139.2	2189.7	2217.1	2234.9	2240.5	2229.6
15°	2287.8	2377.1	2425.2	2423.9	2484.8	2511.2	2469.9
17.5°	2486.8	2569.2	2635.3	2669.1	2719.8	2731.1	2725.9
20°	2608.6	2698.6	2750.0	2808.2	2834.6	2858.3	2862.3
22.5°	2713.6	2794.4	2849.7	2898.0	2920.2	2931.4	2938.2
25°	2821.8	2885.4	2918.5	2935.4	2941.5	2940.1	2931.4
27.5°	2814.3	2819.2	2782.7	2746.8	2714.7	2678.6	2666.1
30°	2741.3	2684.3	2582.9	2525.4	2440.8	2373.8	2400.8
32.5°	2549.1	2435.9	2321.9	2196.2	2092.1	2062.5	2032.7
35°	2175.5	1976.6	1860.2	1724.8	1670.7	1616.6	1579.3
37.5°	1760.1	1606.2	1468.1	1379.6	1325.3	1291.1	1272.7
40°	1521.8	1383.1	1269.5	1197.7	1156.4	1117.8	1112.5
42.5°	1331.9	1202.9	1117.3	1060.2	1020.5	1004.2	992.3
45°	1090.8	1000.8	943.3	902.7	876.3	866.2	852.6
47.5°	923.3	859.6	816.5	788.8	769.0	761.4	760.3
50°	829.6	776.8	745.0	723.3	707.8	705.1	694.3
52.5°	759.2	713.5	688.7	669.8	658.6	651.0	647.7
55°	659.1	628.6	606.3	595.5	586.7	579.2	579.2
57.5°	576.7	551.2	536.5	527.3	524.5	519.3	515.9
60°	525.8	504.1	492.7	484.5	479.1	479.7	473.6
62.5°	476.0	461.9	450.9	442.8	436.4	436.4	436.9
65°	405.4	394.5	386.4	383.7	379.6	374.9	376.3
67.5°	343.5	333.3	327.0	322.4	321.0	318.5	322.4
70°	299.1	291.6	286.9	282.8	281.5	282.1	285.6
72.5°	258.5	253.2	250.1	248.2	245.2	245.4	247.6
75°	203.0	199.0	196.2	194.2	193.6	193.6	193.6
77.5°	149.1	148.2	147.0	144.0	144.1	144.9	145.1
80°	117.8	115.7	115.0	113.7	111.7	110.3	113.7
82.5°	88.0	85.9	85.2	85.0	81.9	81.6	84.5
85°	47.4	45.4	46.0	45.4	45.4	44.7	44.7
87.5°	20.1	19.8	19.3	19.9	19.5	18.9	20.1
90°	17.0	17.7	18.0	18.3	18.6	18.9	19.2
92.5°	25.9	26.3	26.5	26.3	26.2	26.0	25.8
95°	49.0	49.6	49.9	49.9	49.9	49.9	49.9
97.5°	75.9	76.6	76.9	76.9	76.8	76.7	76.7
100°	95.2	95.7	96.0	96.3	96.6	96.9	97.1
102.5°	117.7	118.1	118.3	118.3	118.2	118.1	118.1
105°	150.8	150.8	150.9	151.3	151.5	151.8	152.1
107.5°	187.6	188.0	188.2	188.0	187.9	187.7	187.5
110°	212.0	212.5	212.7	212.4	212.1	211.8	211.5



TEST NUMBER: P332217-935

CATALOG NUMBER: S123DIW-S1165D755U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	236.3	237.0	237.3	237.3	237.2	237.1	237.1
115°	272.7	272.9	272.9	272.7	272.5	272.4	272.2
117.5°	309.7	309.7	309.5	309.1	308.7	308.3	307.9
120°	334.4	334.3	334.1	333.8	333.6	333.2	332.9
122.5°	359.3	359.0	358.6	358.2	357.7	357.4	357.0
125°	396.4	395.9	395.3	394.8	394.2	393.6	393.0
127.5°	433.1	432.3	431.5	430.9	430.2	429.6	429.0
130°	457.8	457.2	456.4	455.5	454.4	453.5	452.5
132.5°	481.5	480.8	480.1	479.3	478.5	477.8	477.0
135°	517.2	516.7	516.3	515.9	515.7	515.4	515.1
137.5°	552.0	551.5	550.9	550.4	549.7	549.2	548.7
140°	575.4	575.2	574.6	573.7	572.7	571.7	570.7
142.5°	596.8	596.7	596.2	595.5	594.7	593.9	593.1
145°	628.4	628.3	627.9	627.3	626.8	626.2	625.7
147.5°	658.4	658.4	658.0	657.1	656.3	655.4	654.5
150°	676.7	676.7	676.3	675.5	674.7	673.8	673.0
152.5°	693.8	694.1	693.8	693.0	692.3	691.6	690.9
155°	718.8	719.3	719.1	718.1	717.1	716.1	715.1
157.5°	739.9	740.5	740.4	739.6	738.8	738.0	737.2
160°	753.0	753.7	753.8	753.3	752.7	752.1	751.6
162.5°	765.3	766.0	765.9	765.0	764.1	763.2	762.2
165°	780.9	781.8	781.7	780.8	779.7	778.8	777.7
167.5°	793.6	794.4	794.4	793.6	792.6	791.8	790.9
170°	800.6	801.5	801.5	800.6	799.5	798.6	797.5
172.5°	805.8	806.7	806.7	805.6	804.7	803.7	802.7
175°	811.6	812.4	812.4	811.4	810.4	809.4	808.4
177.5°	814.1	814.8	814.7	813.9	813.0	812.3	811.5
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6

(END OF REPORT)