

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332115-935

Luminaire Tested: **S123DIW-S340D1535U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332115-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U935-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5833.7 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	20	18	13
4	69	59	52	46	61	53	47	42	41	36	33	29	26	24	19	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	33	28	24	24	21	18	15	14	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4456	4456	4456	4456
5°	5314	4475	3965	4475
10°	6652	4453	3583	4453
15°	8158	4416	3335	4416
20°	9718	4361	3175	4361
25°	10320	4292	3139	4292
30°	8846	4243	3156	4243
35°	6151	4172	3189	4172
40°	4634	4089	3180	4089
45°	3847	3965	3139	3965
50°	3446	3716	3110	3716
55°	3222	3445	3072	3445
60°	3023	3160	3040	3160
65°	2840	2881	2942	2881
70°	2662	2565	2801	2565
75°	2383	2246	2570	2246
80°	2089	1841	2213	1841
85°	1643	1334	1494	1334



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.8	0.7
10°-20°	130.8	2.2
20°-30°	219.5	3.8
30°-40°	248.5	4.3
40°-50°	222.9	3.8
50°-60°	179.8	3.1
60°-70°	125.3	2.1
70°-80°	65.9	1.1
80°-90°	21.0	0.4
90°-100°	107.7	1.8
100°-110°	322.3	5.5
110°-120°	548.1	9.4
120°-130°	721.0	12.4
130°-140°	810.4	13.9
140°-150°	796.6	13.7
150°-160°	670.6	11.5
160°-170°	446.4	7.7
170°-180°	156.3	2.7
0°-30°	391.0	6.7
0°-40°	639.5	11.0
0°-60°	1042.2	17.9
0°-90°	1254.4	21.5
90°-120°	978.1	16.8
90°-150°	3306.0	56.7
90°-180°	4579.0	78.5
0°-180°	5833.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	414	414	414	414	414	
5°	492	414	367	414	492	51
15°	732	396	299	396	732	211
25°	869	361	264	361	869	381
35°	468	318	243	318	468	304
45°	253	260	206	260	253	200
55°	172	184	164	184	172	154
65°	112	113	116	113	112	111
75°	57	54	62	54	57	61
85°	13	11	12	11	13	17
90°	39	1	39	1	39	20
95°	101	77	101	77	101	104
105°	309	292	309	292	309	328
115°	553	552	553	552	553	548
125°	798	808	798	808	798	714
135°	1046	1048	1046	1048	1046	805
145°	1271	1271	1271	1271	1271	793
155°	1453	1455	1453	1455	1453	669
165°	1580	1585	1580	1585	1580	446
175°	1642	1649	1642	1649	1642	156
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	439.4	439.0	438.2	438.9	437.6	435.8	435.7	434.0	429.4	429.1	427.8
5°	491.8	490.3	490.0	489.8	487.0	483.2	476.0	475.4	465.7	461.0	455.1
7.5°	559.8	560.6	557.7	555.2	546.6	540.9	533.1	523.2	511.4	499.4	491.5
10°	608.6	615.2	607.0	601.3	596.2	586.3	574.9	560.6	546.4	529.8	517.1
12.5°	660.9	664.1	662.5	657.2	649.1	634.1	613.9	598.1	585.0	557.3	546.1
15°	732.1	744.3	736.5	718.5	718.8	704.6	678.2	649.1	633.6	609.3	576.3
17.5°	808.0	809.5	806.2	791.2	781.2	761.6	737.1	709.3	678.0	648.6	613.5
20°	848.4	847.2	840.2	832.4	815.2	800.0	773.3	742.2	702.1	673.1	634.8
22.5°	870.9	868.9	865.6	859.0	844.7	828.4	804.3	770.4	732.2	692.4	648.2
25°	868.9	871.5	871.9	870.1	865.1	855.3	836.5	809.3	771.3	720.1	674.0
27.5°	790.3	794.0	804.7	814.2	824.8	835.7	834.2	820.8	792.6	748.4	692.0
30°	711.7	703.6	723.5	748.6	765.6	795.7	812.5	813.6	797.7	759.8	704.8
32.5°	602.5	611.4	620.2	651.0	688.3	722.0	755.6	782.6	785.7	760.4	712.4
35°	468.1	479.2	495.2	511.3	551.4	585.9	644.9	696.2	737.1	742.5	713.1
37.5°	377.3	382.7	392.9	409.0	435.1	476.1	521.7	586.6	645.9	690.0	691.9
40°	329.8	331.4	342.8	355.0	376.3	410.0	451.1	508.5	579.5	641.1	666.8
42.5°	294.1	297.6	302.6	314.3	331.2	356.5	394.8	442.2	507.3	578.2	628.4
45°	252.7	256.8	259.8	267.6	279.7	296.7	323.3	366.7	416.2	489.4	557.0
47.5°	225.4	225.7	227.9	233.8	242.0	254.9	273.7	301.5	347.0	406.4	475.8
50°	205.8	209.0	209.8	214.4	220.8	230.2	245.9	269.6	306.9	359.0	422.8
52.5°	192.0	193.0	195.2	198.5	204.1	211.5	225.1	243.6	272.9	317.4	376.0
55°	171.7	171.7	173.9	176.5	179.7	186.3	195.4	209.0	231.3	265.8	314.4
57.5°	152.9	153.9	155.5	156.3	159.0	163.4	170.9	181.3	197.9	224.5	263.0
60°	140.4	142.2	142.0	143.6	146.0	149.5	155.8	164.3	179.1	200.4	232.9
62.5°	129.5	129.4	129.3	131.3	133.6	136.9	141.1	148.4	161.0	179.9	207.5
65°	111.5	111.2	112.5	113.7	114.5	116.9	120.1	126.6	135.0	149.0	170.5
67.5°	95.6	94.4	95.1	95.6	96.9	98.8	101.9	105.8	112.4	123.7	139.9
70°	84.6	83.6	83.4	83.9	85.1	86.4	88.7	92.5	98.7	107.7	119.5
72.5°	73.4	72.8	72.7	73.6	74.1	75.1	76.6	80.1	85.1	91.9	102.9
75°	57.3	57.3	57.3	57.6	58.2	59.0	60.2	62.0	65.8	70.6	78.0
77.5°	43.0	43.0	42.7	42.7	43.6	43.9	44.2	45.9	48.0	51.2	56.7
80°	33.7	32.7	33.1	33.7	34.1	34.3	34.9	35.3	37.1	38.9	42.7
82.5°	25.1	24.2	24.3	25.2	25.3	25.5	26.1	26.6	27.3	28.9	31.0
85°	13.3	13.3	13.4	13.4	13.6	13.4	14.0	14.2	14.2	15.2	16.4
87.5°	12.6	12.1	12.2	12.2	12.0	12.0	11.9	11.8	11.8	11.7	11.1
90°	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5	32.3	31.2	27.4
92.5°	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7	50.8	49.9	47.7
95°	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4	97.2	96.1	93.8
97.5°	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0	151.7	150.3	148.7
100°	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6	191.7	190.9	189.4
102.5°	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3	237.5	236.5	234.6
105°	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4	306.4	306.4	303.8
107.5°	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2	379.3	378.3	377.3
110°	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5	428.3	427.1	426.5



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7	477.3	476.0	475.9
115°	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1	553.7
117.5°	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3	629.4	629.5	630.2
120°	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8	680.0	680.4	681.7
122.5°	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7	731.5	732.3	733.1
125°	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6	807.7	808.9	809.4
127.5°	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5	883.0	884.7	885.4
130°	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2	932.4	933.5	934.4
132.5°	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6	980.9	982.3	982.9
135°	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0	1053.1	1054.3	1054.6
137.5°	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7	1123.9	1125.2	1124.4
140°	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9	1213.1	1213.4	1212.9
145°	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9	1277.3	1277.6	1276.7
147.5°	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9	1374.9	1374.9	1374.3
152.5°	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1	1408.7	1408.2	1407.8
155°	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1	1457.9	1456.7	1456.5
157.5°	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0	1500.8	1499.6	1499.3
160°	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4	1527.0	1525.5	1525.5
162.5°	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3	1552.0	1550.5	1550.2
165°	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8	1583.1	1581.4	1581.4
167.5°	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8	1606.6
170°	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3	1620.3
172.5°	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3	1633.6	1631.8	1631.8
175°	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2	1645.5	1643.7	1643.7
177.5°	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4	1651.1	1649.7	1649.7
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	426.8	425.6	424.3	422.1	420.1	417.4	416.6	415.6	412.7	410.2	408.2
5°	452.9	448.1	441.1	434.6	429.5	422.4	418.4	414.2	408.2	402.8	398.4
7.5°	480.2	470.7	459.8	448.1	437.0	426.5	417.9	410.3	401.8	393.9	387.6
10°	501.9	488.2	472.9	456.5	442.5	428.9	417.4	407.4	396.6	387.1	379.3
12.5°	526.6	506.4	485.3	465.4	448.8	429.8	415.9	403.2	390.9	379.6	370.8
15°	555.8	530.1	505.2	477.8	452.5	428.9	412.4	396.3	382.1	370.5	359.2
17.5°	582.5	553.4	520.6	487.2	456.7	428.6	405.6	387.4	369.6	355.4	344.2
20°	597.5	564.5	527.4	492.7	458.9	427.7	402.3	380.7	361.4	346.4	333.8
22.5°	610.5	571.8	533.4	496.3	458.7	425.1	396.4	374.1	353.3	338.5	325.1
25°	624.1	577.6	539.2	495.7	453.7	418.8	386.8	361.4	340.6	323.3	309.5
27.5°	635.6	577.3	531.6	484.7	445.7	410.8	376.5	349.4	327.3	308.5	294.5
30°	643.3	578.1	523.7	477.4	438.1	402.0	368.7	341.4	318.1	299.1	285.9
32.5°	648.1	577.6	516.5	467.1	425.9	393.9	360.2	331.9	308.0	289.3	276.6
35°	650.9	574.0	504.0	445.9	406.2	375.1	346.8	317.5	292.5	275.0	260.5
37.5°	645.2	566.6	489.7	425.4	381.9	351.4	327.5	302.6	278.6	259.4	246.9
40°	636.5	561.8	478.4	411.0	365.2	335.8	315.6	291.0	267.3	249.1	237.5
42.5°	619.6	552.1	466.1	394.9	347.9	318.5	299.8	279.3	256.9	239.8	228.2
45°	578.5	530.7	447.5	370.9	322.4	291.9	275.4	260.5	240.3	223.7	213.6
47.5°	521.4	498.7	420.7	345.5	295.6	266.3	249.2	237.3	222.5	209.0	199.4
50°	481.8	472.3	402.6	328.1	277.8	249.1	232.6	221.9	211.2	197.8	189.0
52.5°	436.1	441.9	381.4	310.2	259.7	231.4	216.0	207.4	197.8	186.7	179.0
55°	371.7	392.7	344.8	280.0	232.6	205.8	191.1	183.6	177.9	169.7	163.1
57.5°	311.4	338.2	305.2	248.9	206.1	183.0	168.9	160.7	157.0	152.7	147.5
60°	275.6	302.0	277.0	228.1	188.4	166.3	153.9	146.8	143.2	140.2	135.8
62.5°	243.7	270.4	249.4	206.9	170.8	150.4	139.6	132.7	129.9	128.4	124.6
65°	199.8	222.8	208.8	173.9	145.9	127.8	118.0	113.1	110.6	109.9	107.5
67.5°	162.6	180.1	170.0	144.2	122.2	106.6	98.2	94.1	92.1	91.9	90.1
70°	138.2	154.6	146.8	123.6	104.5	92.3	85.1	81.5	80.2	80.1	79.0
72.5°	119.2	130.7	124.5	105.1	90.4	79.3	74.0	70.2	68.9	69.1	68.4
75°	88.3	96.9	93.2	79.8	68.0	60.8	56.4	54.0	52.8	53.4	52.5
77.5°	63.5	69.0	65.7	56.4	49.1	43.9	40.6	39.2	38.1	38.1	37.7
80°	48.0	51.1	49.3	43.7	37.7	33.3	30.7	29.7	29.1	28.8	28.7
82.5°	34.2	36.9	34.7	30.9	26.8	24.1	22.6	21.4	20.9	21.0	20.8
85°	17.2	18.3	17.5	15.1	13.4	12.2	11.5	10.8	10.4	10.6	10.2
87.5°	10.7	10.1	8.9	7.6	6.6	5.6	5.0	4.1	4.4	4.9	5.3
90°	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3	4.2	7.1	10.0
92.5°	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4	33.4	35.3	37.3
95°	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6	78.6	80.7	82.7
97.5°	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0	137.6	139.1	140.6
100°	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6	178.3	180.0	181.8
102.5°	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3	224.4	225.4	226.4
105°	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1	292.7	293.3	293.9
107.5°	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1	372.5	372.8	373.2
110°	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0	422.6	423.1	423.7



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9	474.2	474.6	474.9
115°	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8	552.7	553.5	554.4
117.5°	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3	630.8	631.4	632.0
120°	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1	680.8	682.5	684.2
122.5°	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0	731.2	732.5	733.7
125°	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5	808.4	809.3	810.2
127.5°	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3	881.1	883.0	884.8
130°	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0	929.4	931.6	933.9
132.5°	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8	977.1	979.4	981.7
135°	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8	1049.5	1051.2	1052.9
137.5°	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3	1116.7	1118.2	1119.6
140°	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0	1163.5	1164.9	1166.3
142.5°	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6	1206.0	1207.5	1208.9
145°	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1	1271.7	1272.2	1272.8
147.5°	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2	1330.2	1331.3	1332.4
150°	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8	1370.4	1370.9	1371.5
152.5°	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0	1403.8	1404.6	1405.4
155°	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1	1499.8	1499.4	1499.1
160°	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2	1527.6	1527.0	1526.4
162.5°	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1	1552.3	1551.4	1550.7
165°	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3	1584.4	1583.6	1582.7
167.5°	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0	1609.8	1608.7	1607.5
170°	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5	1624.4	1623.2	1622.0
172.5°	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9	1635.8	1634.6	1633.5
175°	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9	1647.8	1646.6	1645.5
177.5°	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8	1652.9	1652.0	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	407.1	406.0	404.4	402.0	400.0	397.0	397.0	397.4	397.4	397.4	397.0
5°	394.8	391.8	388.1	383.9	379.5	375.1	374.3	372.6	371.5	370.7	369.7
7.5°	381.7	376.3	371.1	365.2	359.8	355.4	352.3	349.7	348.1	346.3	345.0
10°	372.9	366.3	360.1	353.9	347.0	341.6	338.2	335.8	334.0	332.3	331.6
12.5°	362.5	354.9	348.0	342.1	334.7	329.1	325.8	324.7	322.6	319.2	317.5
15°	347.2	340.2	332.0	323.0	319.3	312.5	308.7	306.9	305.7	303.1	302.3
17.5°	334.2	325.0	315.7	309.0	302.3	296.8	294.6	292.4	290.8	288.7	288.0
20°	323.7	315.6	307.1	299.9	292.8	286.8	285.0	283.4	281.8	280.9	280.0
22.5°	313.1	305.0	297.9	291.2	283.7	279.7	277.8	276.0	274.9	274.2	273.5
25°	298.3	291.0	283.2	277.2	271.2	268.5	267.3	266.4	265.5	264.6	264.3
27.5°	285.0	277.1	270.8	265.1	260.8	258.6	257.4	257.0	257.2	257.5	257.8
30°	275.0	267.8	262.6	257.8	253.7	251.8	251.5	251.5	252.4	252.5	253.0
32.5°	265.9	259.9	254.7	250.0	247.0	245.6	246.4	246.4	247.0	247.5	248.3
35°	252.5	247.3	243.3	239.3	236.7	237.3	237.7	238.1	239.1	240.3	241.1
37.5°	239.8	235.3	231.1	228.0	226.8	227.8	228.9	229.6	230.8	231.8	232.6
40°	230.7	227.2	223.3	220.4	220.8	221.4	222.2	223.3	224.3	224.9	225.7
42.5°	222.1	218.6	215.5	213.2	213.8	214.6	215.0	215.5	216.7	217.8	218.3
45°	209.2	206.4	203.6	202.2	202.6	203.0	203.4	204.0	205.0	205.8	206.0
47.5°	194.7	192.7	190.8	189.4	190.1	189.9	190.5	191.7	192.0	192.5	193.6
50°	185.4	183.6	181.3	180.9	180.9	180.9	181.2	182.7	182.7	183.6	184.3
52.5°	175.0	173.9	172.5	171.8	171.4	171.4	172.3	173.1	173.4	174.5	175.4
55°	159.9	158.7	157.5	156.9	156.4	156.9	158.4	158.9	159.9	160.5	161.1
57.5°	144.0	143.1	142.2	141.8	141.7	142.2	143.1	144.3	144.6	146.5	147.3
60°	133.6	132.2	131.4	131.4	131.0	132.8	132.4	134.4	134.8	136.0	137.4
62.5°	122.9	121.0	120.6	120.6	121.2	121.7	122.3	123.1	124.2	125.7	126.8
65°	105.5	104.5	105.9	105.7	105.3	106.5	106.5	107.5	108.7	110.1	112.4
67.5°	89.1	88.6	88.7	88.7	89.3	90.0	90.6	91.4	92.9	94.4	95.8
70°	78.0	78.6	77.7	78.4	79.0	79.2	79.6	80.8	82.4	83.4	85.1
72.5°	67.2	67.2	67.3	67.7	68.3	68.6	69.1	70.4	72.2	73.0	74.3
75°	51.7	51.6	52.2	52.2	53.1	53.6	54.0	54.6	56.1	57.3	58.4
77.5°	37.8	38.1	37.9	38.6	38.3	38.4	39.6	40.2	40.4	42.8	43.3
80°	28.5	28.8	29.1	29.3	29.4	29.1	30.5	31.1	31.1	32.5	33.5
82.5°	20.5	20.7	21.2	21.4	21.4	21.9	22.0	22.4	22.9	23.5	24.8
85°	10.2	10.8	11.0	10.8	11.0	10.6	11.2	11.5	11.6	11.6	11.6
87.5°	5.8	6.6	7.2	8.1	8.7	9.6	9.8	9.7	10.0	10.7	10.2
90°	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5	34.6	35.8	36.7
92.5°	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7	52.6	53.6	53.8
95°	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4	99.5	100.7	101.3
97.5°	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0	154.3	155.7	156.3
100°	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6	193.5	194.3	195.0
102.5°	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3	239.2	240.0	240.4
105°	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4	306.4	306.4	306.7
107.5°	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2	381.1	382.0	382.3
110°	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5	430.6	431.8	432.0



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7	480.1	481.5	482.2
115°	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7	554.0	554.2	554.2
117.5°	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3	629.3	629.2	628.8
120°	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8	679.5	679.2	678.7
122.5°	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7	730.0	729.3	728.5
125°	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6	805.4	804.3	803.1
127.5°	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5	879.9	878.2	876.8
130°	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2	930.1	928.9	927.3
132.5°	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6	978.2	976.8	975.3
135°	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0	1050.8	1049.6	1048.8
137.5°	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7	1121.5	1120.3	1119.1
140°	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.5
142.5°	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9	1212.5	1212.3	1211.3
145°	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9	1276.7	1276.4	1275.7
147.5°	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9	1374.9	1374.9	1374.1
152.5°	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1	1409.5	1410.1	1409.5
155°	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1	1460.2	1461.4	1460.9
157.5°	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0	1503.2	1504.4	1504.3
160°	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4	1529.9	1531.3	1531.5
162.5°	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3	1554.8	1556.3	1556.1
165°	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8	1586.6	1588.3	1588.2
167.5°	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9
170°	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4
172.5°	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3	1637.1	1638.9	1638.8
175°	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2	1648.9	1650.6	1650.5
177.5°	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4	1653.8	1655.2	1655.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	395.9	395.7	396.8	396.1	396.8	395.7	395.9	397.0	397.4	397.4	397.4
5°	368.5	369.1	367.0	367.0	367.0	369.1	368.5	369.7	370.7	371.5	372.6
7.5°	344.1	343.2	343.3	342.2	343.3	343.2	344.1	345.0	346.3	348.1	349.7
10°	329.2	328.0	327.5	327.8	327.5	328.0	329.2	331.6	332.3	334.0	335.8
12.5°	316.8	316.6	313.9	313.9	313.9	316.6	316.8	317.5	319.2	322.6	324.7
15°	302.3	298.5	298.1	299.3	298.1	298.5	302.3	302.3	303.1	305.7	306.9
17.5°	287.7	285.7	285.9	285.2	285.9	285.7	287.7	288.0	288.7	290.8	292.4
20°	280.0	278.8	278.6	277.2	278.6	278.8	280.0	280.0	280.9	281.8	283.4
22.5°	272.9	272.6	272.7	271.1	272.7	272.6	272.9	273.5	274.2	274.9	276.0
25°	264.2	265.2	264.3	264.3	264.3	265.2	264.2	264.3	264.6	265.5	266.4
27.5°	258.2	258.2	257.8	257.8	257.8	258.2	258.2	257.8	257.5	257.2	257.0
30°	253.7	253.6	253.9	253.9	253.9	253.6	253.7	253.0	252.5	252.4	251.5
32.5°	249.3	249.5	249.6	249.8	249.6	249.5	249.3	248.3	247.5	247.0	246.4
35°	242.3	242.5	243.1	242.7	243.1	242.5	242.3	241.1	240.3	239.1	238.1
37.5°	232.9	233.8	233.7	233.9	233.7	233.8	232.9	232.6	231.8	230.8	229.6
40°	225.8	226.4	226.3	226.3	226.3	226.4	225.8	225.7	224.9	224.3	223.3
42.5°	218.6	219.0	218.5	218.3	218.5	219.0	218.6	218.3	217.8	216.7	215.5
45°	206.8	206.4	207.0	206.2	207.0	206.4	206.8	206.0	205.8	205.0	204.0
47.5°	193.6	194.0	194.2	194.8	194.2	194.0	193.6	193.6	192.5	192.0	191.7
50°	184.8	186.0	186.0	185.7	186.0	186.0	184.8	184.3	183.6	182.7	182.7
52.5°	176.1	176.6	177.5	177.4	177.5	176.6	176.1	175.4	174.5	173.4	173.1
55°	162.6	163.1	163.5	163.7	163.5	163.1	162.6	161.1	160.5	159.9	158.9
57.5°	148.8	148.6	149.6	149.9	149.6	148.6	148.8	147.3	146.5	144.6	144.3
60°	139.0	139.0	140.6	141.2	140.6	139.0	139.0	137.4	136.0	134.8	134.4
62.5°	128.5	129.2	130.8	130.0	130.8	129.2	128.5	126.8	125.7	124.2	123.1
65°	113.3	114.9	114.8	115.5	114.8	114.9	113.3	112.4	110.1	108.7	107.5
67.5°	97.4	98.4	99.9	100.0	99.9	98.4	97.4	95.8	94.4	92.9	91.4
70°	86.6	87.6	88.4	89.0	88.4	87.6	86.6	85.1	83.4	82.4	80.8
72.5°	76.2	76.7	78.7	77.8	78.7	76.7	76.2	74.3	73.0	72.2	70.4
75°	59.8	61.2	62.4	61.8	62.4	61.2	59.8	58.4	57.3	56.1	54.6
77.5°	44.2	45.6	46.1	45.6	46.1	45.6	44.2	43.3	42.8	40.4	40.2
80°	34.9	34.7	35.9	35.7	35.9	34.7	34.9	33.5	32.5	31.1	31.1
82.5°	25.6	25.4	25.9	26.1	25.9	25.4	25.6	24.8	23.5	22.9	22.4
85°	12.4	13.0	12.2	12.1	12.2	13.0	12.4	11.6	11.6	11.6	11.5
87.5°	10.3	10.4	10.4	10.3	10.4	10.4	10.3	10.2	10.7	10.0	9.7
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5
92.5°	53.5	53.1	52.8	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7
95°	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4
97.5°	156.2	156.0	155.9	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0
100°	195.6	196.2	196.7	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6
102.5°	240.3	240.1	240.0	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3
105°	307.3	307.9	308.4	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4
107.5°	381.9	381.6	381.3	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2
110°	431.4	430.9	430.3	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.1	481.9	481.8	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7
115°	554.0	553.7	553.4	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7
117.5°	627.9	627.2	626.4	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3
120°	678.2	677.6	677.0	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8
122.5°	727.7	726.9	726.1	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7
125°	801.9	800.8	799.6	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6
127.5°	875.5	874.1	872.8	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5
130°	925.3	923.3	921.3	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2
132.5°	973.8	972.2	970.6	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6
135°	1048.2	1047.6	1047.1	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0
137.5°	1118.0	1117.0	1115.9	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7
140°	1165.4	1163.5	1161.4	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2
142.5°	1209.8	1208.2	1206.7	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9
145°	1274.5	1273.4	1272.2	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9
147.5°	1335.0	1333.3	1331.5	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6
150°	1372.3	1370.6	1368.9	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9
152.5°	1408.0	1406.5	1405.0	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1
155°	1458.9	1456.9	1454.8	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1
157.5°	1502.6	1501.0	1499.3	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0
160°	1530.3	1529.1	1528.0	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4
162.5°	1554.2	1552.4	1550.5	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3
165°	1586.1	1584.2	1582.1	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8
167.5°	1612.2	1610.4	1608.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4
170°	1626.4	1624.4	1622.4	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4
172.5°	1636.8	1634.8	1632.7	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3
175°	1648.5	1646.4	1644.4	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2
177.5°	1653.5	1651.8	1650.3	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	397.0	397.0	400.0	402.0	404.4	406.0	407.1	408.2	410.2	412.7	415.6
5°	374.3	375.1	379.5	383.9	388.1	391.8	394.8	398.4	402.8	408.2	414.2
7.5°	352.3	355.4	359.8	365.2	371.1	376.3	381.7	387.6	393.9	401.8	410.3
10°	338.2	341.6	347.0	353.9	360.1	366.3	372.9	379.3	387.1	396.6	407.4
12.5°	325.8	329.1	334.7	342.1	348.0	354.9	362.5	370.8	379.6	390.9	403.2
15°	308.7	312.5	319.3	323.0	332.0	340.2	347.2	359.2	370.5	382.1	396.3
17.5°	294.6	296.8	302.3	309.0	315.7	325.0	334.2	344.2	355.4	369.6	387.4
20°	285.0	286.8	292.8	299.9	307.1	315.6	323.7	333.8	346.4	361.4	380.7
22.5°	277.8	279.7	283.7	291.2	297.9	305.0	313.1	325.1	338.5	353.3	374.1
25°	267.3	268.5	271.2	277.2	283.2	291.0	298.3	309.5	323.3	340.6	361.4
27.5°	257.4	258.6	260.8	265.1	270.8	277.1	285.0	294.5	308.5	327.3	349.4
30°	251.5	251.8	253.7	257.8	262.6	267.8	275.0	285.9	299.1	318.1	341.4
32.5°	246.4	245.6	247.0	250.0	254.7	259.9	265.9	276.6	289.3	308.0	331.9
35°	237.7	237.3	236.7	239.3	243.3	247.3	252.5	260.5	275.0	292.5	317.5
37.5°	228.9	227.8	226.8	228.0	231.1	235.3	239.8	246.9	259.4	278.6	302.6
40°	222.2	221.4	220.8	220.4	223.3	227.2	230.7	237.5	249.1	267.3	291.0
42.5°	215.0	214.6	213.8	213.2	215.5	218.6	222.1	228.2	239.8	256.9	279.3
45°	203.4	203.0	202.6	202.2	203.6	206.4	209.2	213.6	223.7	240.3	260.5
47.5°	190.5	189.9	190.1	189.4	190.8	192.7	194.7	199.4	209.0	222.5	237.3
50°	181.2	180.9	180.9	180.9	181.3	183.6	185.4	189.0	197.8	211.2	221.9
52.5°	172.3	171.4	171.4	171.8	172.5	173.9	175.0	179.0	186.7	197.8	207.4
55°	158.4	156.9	156.4	156.9	157.5	158.7	159.9	163.1	169.7	177.9	183.6
57.5°	143.1	142.2	141.7	141.8	142.2	143.1	144.0	147.5	152.7	157.0	160.7
60°	132.4	132.8	131.0	131.4	131.4	132.2	133.6	135.8	140.2	143.2	146.8
62.5°	122.3	121.7	121.2	120.6	120.6	121.0	122.9	124.6	128.4	129.9	132.7
65°	106.5	106.5	105.3	105.7	105.9	104.5	105.5	107.5	109.9	110.6	113.1
67.5°	90.6	90.0	89.3	88.7	88.7	88.6	89.1	90.1	91.9	92.1	94.1
70°	79.6	79.2	79.0	78.4	77.7	78.6	78.0	79.0	80.1	80.2	81.5
72.5°	69.1	68.6	68.3	67.7	67.3	67.2	67.2	68.4	69.1	68.9	70.2
75°	54.0	53.6	53.1	52.2	52.2	51.6	51.7	52.5	53.4	52.8	54.0
77.5°	39.6	38.4	38.3	38.6	37.9	38.1	37.8	37.7	38.1	38.1	39.2
80°	30.5	29.1	29.4	29.3	29.1	28.8	28.5	28.7	28.8	29.1	29.7
82.5°	22.0	21.9	21.4	21.4	21.2	20.7	20.5	20.8	21.0	20.9	21.4
85°	11.2	10.6	11.0	10.8	11.0	10.8	10.2	10.2	10.6	10.4	10.8
87.5°	9.8	9.6	8.7	8.1	7.2	6.6	5.8	5.3	4.9	4.4	4.1
90°	32.3	31.2	27.4	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3
92.5°	50.8	49.9	47.7	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4
95°	97.2	96.1	93.8	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6
97.5°	151.7	150.3	148.7	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0
100°	191.7	190.9	189.4	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6
102.5°	237.5	236.5	234.6	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3
105°	306.4	306.4	303.8	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1
107.5°	379.3	378.3	377.3	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1
110°	428.3	427.1	426.5	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	477.3	476.0	475.9	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9
115°	553.4	553.1	553.7	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8
117.5°	629.4	629.5	630.2	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3
120°	680.0	680.4	681.7	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1
122.5°	731.5	732.3	733.1	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0
125°	807.7	808.9	809.4	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5
127.5°	883.0	884.7	885.4	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3
130°	932.4	933.5	934.4	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0
132.5°	980.9	982.3	982.9	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8
135°	1053.1	1054.3	1054.6	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8
137.5°	1123.9	1125.2	1124.4	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3
140°	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0
142.5°	1213.1	1213.4	1212.9	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6
145°	1277.3	1277.6	1276.7	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1
147.5°	1337.6	1337.6	1336.7	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2
150°	1374.9	1374.9	1374.3	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8
152.5°	1408.7	1408.2	1407.8	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0
155°	1457.9	1456.7	1456.5	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1500.8	1499.6	1499.3	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1
160°	1527.0	1525.5	1525.5	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2
162.5°	1552.0	1550.5	1550.2	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1
165°	1583.1	1581.4	1581.4	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3
167.5°	1608.6	1606.8	1606.6	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0
170°	1622.4	1620.3	1620.3	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5
172.5°	1633.6	1631.8	1631.8	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9
175°	1645.5	1643.7	1643.7	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9
177.5°	1651.1	1649.7	1649.7	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	416.6	417.4	420.1	422.1	424.3	425.6	426.8	427.8	429.1	429.4	434.0
5°	418.4	422.4	429.5	434.6	441.1	448.1	452.9	455.1	461.0	465.7	475.4
7.5°	417.9	426.5	437.0	448.1	459.8	470.7	480.2	491.5	499.4	511.4	523.2
10°	417.4	428.9	442.5	456.5	472.9	488.2	501.9	517.1	529.8	546.4	560.6
12.5°	415.9	429.8	448.8	465.4	485.3	506.4	526.6	546.1	557.3	585.0	598.1
15°	412.4	428.9	452.5	477.8	505.2	530.1	555.8	576.3	609.3	633.6	649.1
17.5°	405.6	428.6	456.7	487.2	520.6	553.4	582.5	613.5	648.6	678.0	709.3
20°	402.3	427.7	458.9	492.7	527.4	564.5	597.5	634.8	673.1	702.1	742.2
22.5°	396.4	425.1	458.7	496.3	533.4	571.8	610.5	648.2	692.4	732.2	770.4
25°	386.8	418.8	453.7	495.7	539.2	577.6	624.1	674.0	720.1	771.3	809.3
27.5°	376.5	410.8	445.7	484.7	531.6	577.3	635.6	692.0	748.4	792.6	820.8
30°	368.7	402.0	438.1	477.4	523.7	578.1	643.3	704.8	759.8	797.7	813.6
32.5°	360.2	393.9	425.9	467.1	516.5	577.6	648.1	712.4	760.4	785.7	782.6
35°	346.8	375.1	406.2	445.9	504.0	574.0	650.9	713.1	742.5	737.1	696.2
37.5°	327.5	351.4	381.9	425.4	489.7	566.6	645.2	691.9	690.0	645.9	586.6
40°	315.6	335.8	365.2	411.0	478.4	561.8	636.5	666.8	641.1	579.5	508.5
42.5°	299.8	318.5	347.9	394.9	466.1	552.1	619.6	628.4	578.2	507.3	442.2
45°	275.4	291.9	322.4	370.9	447.5	530.7	578.5	557.0	489.4	416.2	366.7
47.5°	249.2	266.3	295.6	345.5	420.7	498.7	521.4	475.8	406.4	347.0	301.5
50°	232.6	249.1	277.8	328.1	402.6	472.3	481.8	422.8	359.0	306.9	269.6
52.5°	216.0	231.4	259.7	310.2	381.4	441.9	436.1	376.0	317.4	272.9	243.6
55°	191.1	205.8	232.6	280.0	344.8	392.7	371.7	314.4	265.8	231.3	209.0
57.5°	168.9	183.0	206.1	248.9	305.2	338.2	311.4	263.0	224.5	197.9	181.3
60°	153.9	166.3	188.4	228.1	277.0	302.0	275.6	232.9	200.4	179.1	164.3
62.5°	139.6	150.4	170.8	206.9	249.4	270.4	243.7	207.5	179.9	161.0	148.4
65°	118.0	127.8	145.9	173.9	208.8	222.8	199.8	170.5	149.0	135.0	126.6
67.5°	98.2	106.6	122.2	144.2	170.0	180.1	162.6	139.9	123.7	112.4	105.8
70°	85.1	92.3	104.5	123.6	146.8	154.6	138.2	119.5	107.7	98.7	92.5
72.5°	74.0	79.3	90.4	105.1	124.5	130.7	119.2	102.9	91.9	85.1	80.1
75°	56.4	60.8	68.0	79.8	93.2	96.9	88.3	78.0	70.6	65.8	62.0
77.5°	40.6	43.9	49.1	56.4	65.7	69.0	63.5	56.7	51.2	48.0	45.9
80°	30.7	33.3	37.7	43.7	49.3	51.1	48.0	42.7	38.9	37.1	35.3
82.5°	22.6	24.1	26.8	30.9	34.7	36.9	34.2	31.0	28.9	27.3	26.6
85°	11.5	12.2	13.4	15.1	17.5	18.3	17.2	16.4	15.2	14.2	14.2
87.5°	5.0	5.6	6.6	7.6	8.9	10.1	10.7	11.1	11.7	11.8	11.8
90°	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5
92.5°	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7
95°	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4
97.5°	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0
100°	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6
102.5°	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3
105°	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4
107.5°	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2
110°	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7
115°	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7
117.5°	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3
120°	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8
122.5°	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7
125°	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6
127.5°	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5
130°	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2
132.5°	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6
135°	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0
137.5°	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7
140°	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2
142.5°	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9
145°	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9
147.5°	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6
150°	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9
152.5°	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1
155°	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1
157.5°	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0
160°	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4
162.5°	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3
165°	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8
167.5°	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4
170°	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4
172.5°	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3
175°	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2
177.5°	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	414.0	414.0	414.0	414.0	414.0	414.0	414.0
2.5°	435.7	435.8	437.6	438.9	438.2	439.0	439.4
5°	476.0	483.2	487.0	489.8	490.0	490.3	491.8
7.5°	533.1	540.9	546.6	555.2	557.7	560.6	559.8
10°	574.9	586.3	596.2	601.3	607.0	615.2	608.6
12.5°	613.9	634.1	649.1	657.2	662.5	664.1	660.9
15°	678.2	704.6	718.8	718.5	736.5	744.3	732.1
17.5°	737.1	761.6	781.2	791.2	806.2	809.5	808.0
20°	773.3	800.0	815.2	832.4	840.2	847.2	848.4
22.5°	804.3	828.4	844.7	859.0	865.6	868.9	870.9
25°	836.5	855.3	865.1	870.1	871.9	871.5	868.9
27.5°	834.2	835.7	824.8	814.2	804.7	794.0	790.3
30°	812.5	795.7	765.6	748.6	723.5	703.6	711.7
32.5°	755.6	722.0	688.3	651.0	620.2	611.4	602.5
35°	644.9	585.9	551.4	511.3	495.2	479.2	468.1
37.5°	521.7	476.1	435.1	409.0	392.9	382.7	377.3
40°	451.1	410.0	376.3	355.0	342.8	331.4	329.8
42.5°	394.8	356.5	331.2	314.3	302.6	297.6	294.1
45°	323.3	296.7	279.7	267.6	259.8	256.8	252.7
47.5°	273.7	254.9	242.0	233.8	227.9	225.7	225.4
50°	245.9	230.2	220.8	214.4	209.8	209.0	205.8
52.5°	225.1	211.5	204.1	198.5	195.2	193.0	192.0
55°	195.4	186.3	179.7	176.5	173.9	171.7	171.7
57.5°	170.9	163.4	159.0	156.3	155.5	153.9	152.9
60°	155.8	149.5	146.0	143.6	142.0	142.2	140.4
62.5°	141.1	136.9	133.6	131.3	129.3	129.4	129.5
65°	120.1	116.9	114.5	113.7	112.5	111.2	111.5
67.5°	101.9	98.8	96.9	95.6	95.1	94.4	95.6
70°	88.7	86.4	85.1	83.9	83.4	83.6	84.6
72.5°	76.6	75.1	74.1	73.6	72.7	72.8	73.4
75°	60.2	59.0	58.2	57.6	57.3	57.3	57.3
77.5°	44.2	43.9	43.6	42.7	42.7	43.0	43.0
80°	34.9	34.3	34.1	33.7	33.1	32.7	33.7
82.5°	26.1	25.5	25.3	25.2	24.3	24.2	25.1
85°	14.0	13.4	13.6	13.4	13.4	13.3	13.3
87.5°	11.9	12.0	12.0	12.2	12.2	12.1	12.6
90°	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	430.6	431.8	432.0	431.4	430.9	430.3	429.7



TEST NUMBER: P332115-935

CATALOG NUMBER: S123DIW-S340D1535U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)