

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332094-830

Luminaire Tested: **S123DIW-S340D460U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332094-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D460U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3068.8 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35	30				
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26				
4	73	62	54	48	66	57	50	45	48	43	39	39	35	32	31	28	26	22				
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17				
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.6
10°-20°	135.9	4.4
20°-30°	200.7	6.5
30°-40°	234.4	7.6
40°-50°	235.7	7.7
50°-60°	207.0	6.7
60°-70°	154.2	5.0
70°-80°	87.9	2.9
80°-90°	26.8	0.9
90°-100°	20.7	0.7
100°-110°	98.8	3.2
110°-120°	237.2	7.7
120°-130°	302.1	9.8
130°-140°	322.8	10.5
140°-150°	301.8	9.8
150°-160°	243.5	7.9
160°-170°	157.1	5.1
170°-180°	54.2	1.8
0°-30°	384.6	12.5
0°-40°	619.1	20.2
0°-60°	1061.7	34.6
0°-90°	1330.7	43.4
90°-120°	356.7	11.6
90°-150°	1283.4	41.8
90°-180°	1738.0	56.6
0°-180°	3068.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	0	5	10	12	13	2
95°	26	10	13	16	16	32
105°	126	128	93	22	19	134
115°	237	239	243	247	249	234
125°	334	337	339	340	340	298
135°	415	418	420	421	420	320
145°	479	482	483	484	484	300
155°	528	527	528	529	527	243
165°	557	556	555	558	556	157
175°	570	568	568	571	568	54
180°	570	570	570	570	570	



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.1	9.1	9.0	9.0	9.1	9.2	9.4	9.6	9.8	9.8
90°	0.4	1.3	2.3	3.2	4.1	5.3	6.5	7.7	9.0	10.2	10.6
92.5°	7.9	7.6	7.4	7.1	6.8	7.2	8.1	9.0	9.9	10.8	11.4
95°	25.8	22.0	18.1	14.2	10.4	9.0	10.0	11.0	12.1	13.1	13.8
97.5°	51.9	50.1	48.4	46.8	45.0	40.7	33.9	27.1	20.5	13.7	14.4
100°	71.5	73.4	75.3	77.2	79.1	72.7	58.1	43.4	28.7	13.9	14.7
102.5°	93.9	95.3	96.6	98.0	99.3	92.0	76.0	59.9	43.9	27.9	25.5
105°	126.2	127.2	128.3	129.3	130.4	126.6	118.1	109.7	101.2	92.7	76.1
107.5°	160.2	161.1	161.9	162.7	163.5	164.7	166.0	167.3	168.6	169.9	157.8
110°	182.9	183.7	184.5	185.2	186.0	186.8	187.8	188.9	189.9	191.0	187.8



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.6	205.3	205.9	206.6	207.4	208.2	209.2	210.3	211.3	212.4	212.4
115°	236.7	237.2	237.8	238.4	238.9	239.7	240.5	241.4	242.2	243.1	244.0
117.5°	267.8	268.5	269.2	269.8	270.6	271.2	271.5	272.0	272.5	272.9	273.6
120°	287.1	287.9	288.8	289.6	290.5	291.1	291.3	291.6	291.9	292.2	292.9
122.5°	306.8	307.5	308.1	308.9	309.5	310.1	310.5	310.8	311.1	311.5	312.0
125°	333.7	334.4	335.2	335.9	336.7	337.2	337.6	338.0	338.4	338.7	338.9
127.5°	359.8	360.5	361.3	362.0	362.8	363.4	363.8	364.3	364.8	365.2	365.5
130°	376.1	376.8	377.6	378.3	379.1	379.7	380.0	380.4	380.8	381.1	381.4
132.5°	391.6	392.4	393.1	393.9	394.6	395.1	395.5	395.8	396.1	396.3	396.7
135°	415.4	415.9	416.5	417.1	417.6	418.1	418.5	418.9	419.2	419.6	419.9
137.5°	435.7	436.5	437.2	437.9	438.6	439.0	439.3	439.5	439.7	439.9	440.4
140°	449.3	449.9	450.4	451.0	451.6	451.9	452.2	452.5	452.8	453.1	453.5
142.5°	461.8	462.4	463.0	463.5	464.1	464.5	464.8	465.1	465.3	465.6	465.9
145°	479.4	480.0	480.7	481.4	482.0	482.4	482.6	482.8	483.0	483.1	483.3
147.5°	495.9	496.3	496.7	497.2	497.6	497.9	498.1	498.3	498.5	498.7	498.9
150°	506.1	506.3	506.6	506.9	507.2	507.4	507.6	507.7	507.9	508.1	508.3
152.5°	515.2	515.3	515.5	515.6	515.8	515.9	515.9	516.0	516.1	516.3	516.6
155°	528.0	527.8	527.6	527.5	527.4	527.3	527.4	527.4	527.5	527.6	528.1
157.5°	538.1	538.0	538.0	538.0	538.0	537.9	537.8	537.7	537.6	537.5	538.1
160°	544.1	544.0	543.9	543.8	543.8	543.7	543.6	543.5	543.4	543.3	543.8
162.5°	549.9	549.7	549.4	549.2	548.9	548.7	548.7	548.6	548.5	548.4	549.0
165°	556.9	556.6	556.3	556.0	555.7	555.5	555.4	555.3	555.3	555.2	555.9
167.5°	562.3	561.9	561.6	561.2	560.8	560.6	560.6	560.6	560.6	560.6	561.4
170°	565.3	565.0	564.6	564.2	563.8	563.6	563.6	563.6	563.6	563.6	564.4
172.5°	567.3	566.9	566.5	566.0	565.5	565.3	565.4	565.5	565.6	565.6	566.4
175°	570.0	569.5	569.0	568.5	568.1	567.9	568.0	568.1	568.2	568.3	568.9
177.5°	570.6	570.2	569.9	569.5	569.1	569.0	569.1	569.1	569.2	569.3	569.9
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	9.8	9.7	9.7	9.8	9.8	9.8	9.9	9.9
90°	10.9	11.3	11.7	12.0	12.2	12.3	12.5	12.7
92.5°	12.1	12.6	13.3	13.6	13.8	13.9	13.9	14.0
95°	14.4	15.1	15.7	16.1	16.1	16.1	16.1	16.1
97.5°	15.2	15.9	16.7	17.1	17.2	17.2	17.3	17.4
100°	15.5	16.2	17.0	17.4	17.5	17.6	17.7	17.8
102.5°	23.2	20.8	18.6	17.4	17.6	17.8	17.9	18.1
105°	59.4	42.8	26.1	17.9	18.1	18.3	18.5	18.7
107.5°	145.5	133.4	121.1	108.8	96.1	83.6	71.1	58.5
110°	184.7	181.6	178.5	170.3	156.8	143.4	129.9	116.5



TEST NUMBER: P332094-830

CATALOG NUMBER: S123DIW-S340D460U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	212.4	212.4	212.5	211.1	208.3	205.5	202.6	199.8
115°	245.0	245.9	246.9	247.5	247.9	248.3	248.6	249.0
117.5°	274.4	275.1	275.9	276.3	276.4	276.4	276.5	276.6
120°	293.7	294.5	295.2	295.6	295.6	295.6	295.6	295.6
122.5°	312.5	313.1	313.6	313.9	314.0	314.1	314.1	314.2
125°	339.1	339.3	339.5	339.7	339.9	340.1	340.3	340.4
127.5°	365.8	366.1	366.4	366.5	366.3	366.1	365.9	365.7
130°	381.8	382.2	382.6	382.7	382.5	382.3	382.1	381.9
132.5°	397.1	397.5	397.8	397.9	397.7	397.4	397.1	396.9
135°	420.2	420.5	420.8	420.8	420.5	420.2	419.9	419.6
137.5°	440.8	441.2	441.7	441.9	441.7	441.5	441.3	441.1
140°	453.8	454.2	454.6	454.7	454.5	454.3	454.1	453.9
142.5°	466.3	466.6	466.8	466.8	466.6	466.4	466.1	465.8
145°	483.5	483.7	483.9	484.0	484.0	484.0	484.0	484.0
147.5°	499.1	499.3	499.5	499.3	498.9	498.4	498.0	497.6
150°	508.5	508.7	508.9	508.9	508.6	508.3	508.0	507.7
152.5°	517.0	517.3	517.6	517.6	517.2	516.7	516.3	515.9
155°	528.6	529.0	529.5	529.4	528.9	528.3	527.7	527.3
157.5°	538.7	539.2	539.8	539.7	538.9	538.3	537.5	536.8
160°	544.4	545.0	545.5	545.5	544.9	544.2	543.6	542.9
162.5°	549.7	550.4	550.9	551.0	550.4	549.8	549.2	548.7
165°	556.7	557.4	558.2	558.2	557.5	556.9	556.3	555.6
167.5°	562.1	562.8	563.5	563.5	562.8	562.1	561.4	560.6
170°	565.1	565.9	566.7	566.7	565.9	565.1	564.4	563.6
172.5°	567.1	567.9	568.6	568.6	567.8	566.9	566.2	565.3
175°	569.6	570.2	570.9	570.9	570.1	569.4	568.6	567.9
177.5°	570.5	571.1	571.7	571.7	570.9	570.1	569.4	568.6
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0

(END OF REPORT)