

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332136-935

Luminaire Tested: **S123DIW-S560D1030U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332136-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1030U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5548.9 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36	30
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31	25
3	78	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	53	48	65	56	49	44	45	40	36	36	32	29	27	24	22	18
5	66	54	46	41	59	50	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.3
10°-20°	204.0	3.7
20°-30°	301.4	5.4
30°-40°	352.0	6.3
40°-50°	353.9	6.4
50°-60°	310.9	5.6
60°-70°	231.6	4.2
70°-80°	132.0	2.4
80°-90°	41.1	0.7
90°-100°	42.3	0.8
100°-110°	201.7	3.6
110°-120°	484.5	8.7
120°-130°	616.9	11.1
130°-140°	659.2	11.9
140°-150°	616.4	11.1
150°-160°	497.2	9.0
160°-170°	320.9	5.8
170°-180°	110.6	2.0
0°-30°	577.6	10.4
0°-40°	929.7	16.8
0°-60°	1594.5	28.7
0°-90°	1999.2	36.0
90°-120°	728.5	13.1
90°-150°	2621.0	47.2
90°-180°	3550.0	64.0
0°-180°	5548.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	10	21	24	26	4
95°	53	20	27	33	33	65
105°	258	262	189	45	38	273
115°	484	489	496	505	508	477
125°	682	688	692	694	695	608
135°	848	853	857	859	857	653
145°	979	985	987	988	988	613
155°	1078	1077	1078	1081	1077	497
165°	1137	1135	1134	1140	1135	321
175°	1164	1160	1160	1166	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.9	13.9	13.9	14.0	14.2	14.6	15.0	15.4	15.8	15.8
90°	0.9	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5
92.5°	16.1	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3
95°	52.8	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2
97.5°	106.0	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4
100°	146.1	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0
102.5°	191.8	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2
105°	257.7	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4
107.5°	327.3	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2
110°	373.6	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.8	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7
115°	483.5	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3
117.5°	546.9	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8
120°	586.3	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2
122.5°	626.5	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2
125°	681.5	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2
127.5°	734.7	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4
130°	767.9	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1
132.5°	799.8	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2
135°	848.3	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6
137.5°	889.8	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2
140°	917.6	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1
142.5°	943.1	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6
145°	979.0	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1
147.5°	1012.7	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7
150°	1033.5	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1
152.5°	1052.1	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1
155°	1078.4	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5
157.5°	1098.8	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9
160°	1111.3	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7
162.5°	1123.0	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2
165°	1137.2	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3
167.5°	1148.2	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3
170°	1154.5	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5
172.5°	1158.6	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8
175°	1164.0	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9
177.5°	1165.4	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	15.8	15.8	15.9	15.9	16.0	16.1	16.2	16.3
90°	22.3	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	24.6	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	29.5	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	30.9	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	31.6	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	47.4	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	121.4	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	297.2	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	377.4	371.0	364.6	347.8	320.3	292.7	265.3	237.8



TEST NUMBER: P332136-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	433.9	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	500.2	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	560.3	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	599.8	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	638.3	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	692.6	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.0	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	779.9	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.0	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	900.2	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	926.9	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.2	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.5	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.2	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.5	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1055.8	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1079.4	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1100.1	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1111.8	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1122.5	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1136.8	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1158.3	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1163.2	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1165.1	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)