

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332100-830

Luminaire Tested: **S123DIW-S340D755U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332100-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4178.6 lumens
Efficiency: N/A
Efficacy: 137.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5498	5498	5498
5°	5524	5448	5486
10°	5487	5400	5434
15°	5422	5340	5349
20°	5347	5252	5257
25°	5247	5149	5138
30°	5137	5033	4994
35°	5021	4911	4847
40°	4900	4776	4703
45°	4766	4654	4539
50°	4632	4501	4376
55°	4459	4344	4211
60°	4284	4159	4028
65°	4126	3958	3836
70°	3899	3733	3566
75°	3564	3435	3290
80°	3211	3081	3050
85°	2816	2717	2606



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.2
10°-20°	135.9	3.3
20°-30°	200.7	4.8
30°-40°	234.4	5.6
40°-50°	235.7	5.6
50°-60°	207.0	5.0
60°-70°	154.2	3.7
70°-80°	87.9	2.1
80°-90°	27.8	0.7
90°-100°	33.9	0.8
100°-110°	161.8	3.9
110°-120°	388.6	9.3
120°-130°	494.8	11.8
130°-140°	528.7	12.7
140°-150°	494.4	11.8
150°-160°	398.8	9.5
160°-170°	257.4	6.2
170°-180°	88.7	2.1
0°-30°	384.6	9.2
0°-40°	619.1	14.8
0°-60°	1061.7	25.4
0°-90°	1331.7	31.9
90°-120°	584.3	14.0
90°-150°	2102.1	50.3
90°-180°	2847.0	68.1
0°-180°	4178.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	511	511	511	511	511	
5°	511	509	504	508	508	48
15°	487	485	479	482	480	137
25°	442	439	434	434	433	203
35°	382	379	374	371	369	239
45°	313	311	306	301	298	242
55°	238	237	232	227	224	213
65°	162	160	155	152	151	160
75°	86	84	83	80	79	92
85°	23	22	22	21	21	25
90°	1	8	17	19	21	3
95°	42	16	22	26	26	52
105°	207	210	152	36	30	219
115°	388	392	398	405	408	383
125°	547	552	555	556	558	488
135°	680	684	687	689	687	524
145°	785	790	791	793	793	491
155°	865	864	864	867	864	398
165°	912	910	909	914	910	258
175°	934	930	931	935	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	512.6	512.2	511.9	511.6	511.2	510.7	509.8	509.0	508.1	507.3	508.0
5°	511.2	510.7	510.2	509.7	509.3	508.5	507.4	506.3	505.2	504.2	505.1
7.5°	506.2	505.7	505.2	504.7	504.3	503.4	502.4	501.2	500.1	499.0	499.8
10°	502.0	501.5	501.0	500.5	500.0	499.2	497.9	496.6	495.3	494.1	494.9
12.5°	496.3	496.0	495.5	495.1	494.7	493.9	492.8	491.5	490.3	489.2	489.8
15°	486.6	486.3	485.8	485.4	485.0	484.2	483.0	481.6	480.4	479.2	479.9
17.5°	475.2	474.8	474.3	473.7	473.3	472.4	471.1	469.9	468.5	467.3	467.8
20°	466.8	466.3	465.7	465.1	464.5	463.5	462.3	461.0	459.8	458.5	458.9
22.5°	457.3	456.8	456.2	455.6	455.1	454.1	452.8	451.6	450.3	449.0	449.3
25°	441.8	441.2	440.6	440.1	439.5	438.6	437.2	436.0	434.7	433.5	433.6
27.5°	425.2	424.6	424.0	423.5	422.9	422.0	420.7	419.2	417.9	416.5	416.6
30°	413.3	412.7	412.3	411.8	411.3	410.4	409.1	407.6	406.3	404.9	404.9
32.5°	401.3	400.7	400.0	399.4	398.8	397.8	396.8	395.8	394.7	393.7	393.1
35°	382.1	381.5	380.9	380.3	379.8	378.8	377.6	376.3	375.0	373.7	373.2
37.5°	362.4	361.7	360.9	360.1	359.5	358.4	357.1	355.8	354.6	353.3	352.6
40°	348.7	348.1	347.5	346.9	346.4	345.3	344.0	342.6	341.3	339.9	339.1
42.5°	335.0	334.3	333.7	333.0	332.3	331.3	330.0	328.6	327.3	325.8	325.1
45°	313.1	312.7	312.4	312.0	311.6	310.8	309.4	308.2	306.9	305.7	304.5
47.5°	291.4	290.9	290.3	289.7	289.2	288.3	287.1	285.9	284.7	283.5	282.4
50°	276.6	276.2	275.7	275.2	274.8	273.8	272.6	271.4	270.0	268.8	267.7
52.5°	261.2	260.9	260.5	260.2	259.9	259.0	257.7	256.4	255.1	253.6	252.8
55°	237.6	237.5	237.4	237.3	237.2	236.5	235.3	233.9	232.7	231.5	230.4
57.5°	215.1	214.8	214.4	214.1	213.8	213.1	212.1	211.0	210.1	209.1	208.1
60°	199.0	198.9	198.8	198.7	198.6	197.9	196.7	195.6	194.4	193.2	192.4
62.5°	184.5	184.3	184.1	183.8	183.5	182.9	181.6	180.5	179.3	178.1	177.3
65°	162.0	161.6	161.1	160.6	160.1	159.4	158.4	157.4	156.5	155.4	154.7
67.5°	138.3	137.8	137.4	137.0	136.6	135.9	135.3	134.5	133.7	133.0	132.3
70°	123.9	123.3	122.7	122.1	121.5	120.9	120.4	119.7	119.1	118.6	117.9
72.5°	108.8	108.3	107.9	107.4	107.0	106.5	105.8	105.2	104.5	103.9	103.2
75°	85.7	85.2	84.8	84.5	84.1	83.7	83.4	83.1	82.8	82.6	82.1
77.5°	65.1	64.9	64.8	64.6	64.3	64.0	63.7	63.3	63.0	62.6	62.3
80°	51.8	51.6	51.3	51.0	50.6	50.4	50.2	50.0	49.9	49.7	49.5
82.5°	38.8	38.7	38.7	38.6	38.5	38.5	38.5	38.5	38.5	38.4	38.2
85°	22.8	22.6	22.4	22.2	22.1	22.0	22.0	22.0	22.0	22.0	21.8
87.5°	9.2	9.3	9.4	9.5	9.6	9.8	10.1	10.4	10.7	11.0	11.1
90°	0.7	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2
92.5°	12.9	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8
95°	42.3	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6
97.5°	85.0	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6
100°	117.3	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1
102.5°	153.8	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8
105°	206.7	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6
107.5°	262.4	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4
110°	299.6	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	335.2	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9
115°	387.7	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6
117.5°	438.7	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2
120°	470.2	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8
122.5°	502.5	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0
125°	546.6	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2
127.5°	589.3	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6
130°	615.9	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8
132.5°	641.4	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8
135°	680.4	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8
137.5°	713.7	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2
140°	735.8	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7
142.5°	756.4	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2
145°	785.1	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6
147.5°	812.2	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1
150°	828.9	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6
152.5°	843.8	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1
155°	864.9	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0
157.5°	881.3	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4
160°	891.3	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8
162.5°	900.7	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3
165°	912.1	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5
167.5°	921.0	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4
170°	926.0	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4
172.5°	929.3	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7
175°	933.6	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9
177.5°	934.6	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	510.8	510.8	510.8	510.8	510.8	510.8	510.8	510.8
2.5°	508.8	509.6	510.4	510.8	510.7	510.6	510.5	510.4
5°	506.1	507.1	508.1	508.5	508.3	508.1	507.8	507.7
7.5°	500.8	501.6	502.5	502.8	502.8	502.7	502.6	502.4
10°	495.9	496.7	497.6	497.9	497.8	497.6	497.4	497.2
12.5°	490.4	491.1	491.7	492.0	491.9	491.7	491.6	491.5
15°	480.7	481.5	482.3	482.4	481.7	481.2	480.6	480.0
17.5°	468.3	468.9	469.5	469.7	469.4	469.2	469.0	468.8
20°	459.3	459.7	460.1	460.1	459.8	459.5	459.2	458.9
22.5°	449.6	450.0	450.3	450.3	449.9	449.5	449.1	448.7
25°	433.7	433.8	433.9	433.8	433.5	433.2	432.9	432.6
27.5°	416.7	416.8	416.8	416.7	416.3	415.9	415.6	415.2
30°	404.9	404.9	404.9	404.5	403.9	403.2	402.6	401.8
32.5°	392.6	392.0	391.5	391.1	390.7	390.3	389.9	389.6
35°	372.6	372.0	371.4	370.9	370.4	369.9	369.4	368.9
37.5°	351.9	351.2	350.4	350.0	349.7	349.3	349.0	348.7
40°	338.4	337.6	336.8	336.2	335.8	335.5	335.1	334.7
42.5°	324.3	323.5	322.7	322.2	321.8	321.4	321.0	320.6
45°	303.3	302.2	301.0	300.2	299.6	299.2	298.7	298.2
47.5°	281.3	280.1	278.9	278.1	277.7	277.3	276.8	276.4
50°	266.6	265.5	264.5	263.6	263.1	262.5	261.9	261.3
52.5°	251.8	250.9	250.0	249.2	248.6	248.1	247.5	246.9
55°	229.3	228.2	227.2	226.4	225.9	225.4	224.9	224.4
57.5°	207.2	206.1	205.2	204.4	203.9	203.3	202.7	202.2
60°	191.5	190.6	189.7	189.1	188.5	188.0	187.6	187.1
62.5°	176.3	175.5	174.7	174.0	173.7	173.3	173.1	172.7
65°	153.9	153.2	152.3	151.8	151.6	151.2	150.9	150.6
67.5°	131.6	130.9	130.3	129.7	129.3	128.8	128.5	128.1
70°	117.3	116.5	115.8	115.3	114.8	114.3	113.8	113.3
72.5°	102.6	102.0	101.4	100.9	100.8	100.5	100.2	99.9
75°	81.6	81.1	80.6	80.2	79.9	79.6	79.4	79.1
77.5°	61.9	61.6	61.3	61.2	61.2	61.2	61.2	61.2
80°	49.4	49.3	49.2	49.2	49.2	49.2	49.2	49.2
82.5°	38.1	37.9	37.7	37.5	37.5	37.4	37.3	37.2
85°	21.6	21.4	21.2	21.1	21.1	21.1	21.1	21.1
87.5°	11.1	11.2	11.2	11.3	11.3	11.4	11.5	11.5
90°	17.9	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	19.7	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	23.7	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	24.8	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	25.4	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	38.0	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	97.4	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	238.4	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	302.7	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332100-830

CATALOG NUMBER: S123DIW-S340D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	348.0	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	401.2	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	449.4	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	481.1	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	511.9	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.4	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.2	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	625.5	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	650.4	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.0	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.4	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	763.6	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.0	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.4	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	832.9	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	846.7	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	865.7	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	882.3	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	891.7	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	900.3	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	911.7	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	929.0	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	932.9	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	934.4	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)