

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332137-935

Luminaire Tested: **S123DIW-S560D1030U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332137-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1030U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5075.8 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	14
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.4
10°-20°	204.0	4.0
20°-30°	301.4	5.9
30°-40°	352.0	6.9
40°-50°	353.9	7.0
50°-60°	310.9	6.1
60°-70°	231.6	4.6
70°-80°	132.0	2.6
80°-90°	41.2	0.8
90°-100°	72.4	1.4
100°-110°	216.5	4.3
110°-120°	368.3	7.3
120°-130°	484.4	9.5
130°-140°	544.4	10.7
140°-150°	535.2	10.5
150°-160°	450.5	8.9
160°-170°	299.9	5.9
170°-180°	105.0	2.1
0°-30°	577.6	11.4
0°-40°	929.7	18.3
0°-60°	1594.5	31.4
0°-90°	1999.2	39.4
90°-120°	657.1	12.9
90°-150°	2221.1	43.8
90°-180°	3077.0	60.6
0°-180°	5075.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	10	21	24	26	5
95°	52	58	65	68	68	58
105°	196	198	206	206	208	210
115°	371	373	372	372	372	367
125°	543	545	544	540	536	484
135°	704	709	708	705	703	542
145°	854	856	858	857	854	533
155°	978	978	979	982	976	450
165°	1065	1063	1062	1067	1062	300
175°	1108	1104	1104	1109	1104	105
180°	1110	1110	1110	1110	1110	



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.9	13.9	14.0	14.0	14.2	14.6	15.0	15.4	15.8	15.8
90°	0.9	2.8	4.7	6.7	8.6	10.8	13.3	15.9	18.4	20.9	21.7
92.5°	21.1	22.4	23.8	25.1	26.3	27.7	29.2	30.7	32.0	33.5	34.1
95°	51.5	52.8	54.2	55.5	56.9	58.4	59.9	61.5	63.0	64.6	65.3
97.5°	91.4	92.4	93.4	94.5	95.5	96.5	97.6	98.8	99.9	101.0	101.9
100°	118.6	119.8	121.0	122.1	123.3	124.3	125.4	126.3	127.3	128.2	128.8
102.5°	150.1	150.8	151.4	152.1	152.8	153.8	155.1	156.4	157.6	158.9	159.5
105°	196.3	196.7	197.1	197.4	197.9	198.9	200.6	202.3	204.1	205.9	205.9
107.5°	250.0	250.2	250.5	250.7	250.9	251.4	252.1	252.8	253.5	254.2	254.8
110°	283.5	283.9	284.3	284.6	285.1	285.4	285.9	286.2	286.6	287.0	287.7



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	318.4	318.7	318.8	319.1	319.3	319.4	319.5	319.6	319.7	319.8	320.7
115°	370.7	371.3	371.9	372.5	373.1	373.2	372.7	372.4	372.0	371.6	371.8
117.5°	423.4	423.8	424.2	424.6	425.0	424.9	424.4	423.9	423.4	422.9	422.8
120°	456.2	457.4	458.6	459.7	460.9	461.0	459.9	459.0	458.1	457.1	456.8
122.5°	490.4	491.3	492.1	492.9	493.8	494.0	493.5	493.0	492.5	492.0	491.5
125°	542.6	543.1	543.7	544.3	544.9	545.0	544.6	544.2	543.8	543.5	542.7
127.5°	590.7	591.9	593.2	594.4	595.6	596.1	595.6	595.2	594.8	594.3	593.3
130°	622.8	624.4	625.9	627.5	629.0	629.5	629.0	628.4	627.8	627.2	626.4
132.5°	654.9	656.4	658.0	659.6	661.2	661.7	661.2	660.8	660.4	660.0	659.0
135°	704.0	705.1	706.3	707.4	708.6	709.0	708.9	708.7	708.5	708.3	707.5
137.5°	749.3	750.3	751.2	752.2	753.2	753.9	754.4	754.9	755.4	756.0	755.1
140°	780.7	781.7	782.6	783.6	784.5	785.1	785.3	785.6	785.7	785.9	785.7
142.5°	809.3	810.3	811.2	812.2	813.2	813.8	814.2	814.5	814.9	815.3	815.0
145°	853.9	854.4	854.7	855.1	855.5	856.0	856.6	857.2	857.7	858.3	858.2
147.5°	893.0	893.7	894.4	895.2	895.9	896.5	897.0	897.6	898.1	898.6	898.6
150°	920.2	920.7	921.0	921.4	921.8	922.2	922.6	923.0	923.3	923.8	923.8
152.5°	942.6	943.1	943.7	944.3	944.8	945.1	945.4	945.6	945.9	946.1	946.4
155°	977.8	977.8	977.8	977.8	977.8	977.9	978.1	978.4	978.5	978.7	979.5
157.5°	1007.9	1007.6	1007.4	1007.1	1006.9	1006.9	1007.0	1007.2	1007.4	1007.5	1008.3
160°	1026.7	1026.3	1025.9	1025.5	1025.1	1024.9	1024.9	1024.9	1024.9	1024.9	1025.9
162.5°	1043.4	1042.9	1042.3	1041.8	1041.3	1041.0	1041.2	1041.4	1041.6	1041.7	1042.7
165°	1065.1	1064.5	1063.9	1063.3	1062.7	1062.5	1062.5	1062.5	1062.5	1062.5	1063.6
167.5°	1082.4	1081.6	1080.8	1080.0	1079.3	1078.9	1079.1	1079.3	1079.4	1079.5	1080.7
170°	1092.1	1091.3	1090.5	1089.8	1089.0	1088.6	1088.6	1088.6	1088.6	1088.6	1089.9
172.5°	1099.8	1099.0	1098.2	1097.4	1096.7	1096.3	1096.3	1096.3	1096.3	1096.3	1097.5
175°	1107.8	1107.1	1106.3	1105.5	1104.7	1104.3	1104.3	1104.3	1104.3	1104.3	1105.5
177.5°	1111.1	1110.5	1109.9	1109.2	1108.6	1108.4	1108.4	1108.4	1108.4	1108.4	1109.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	15.8	15.9	15.9	16.0	16.1	16.2	16.3	16.3
90°	22.5	23.2	24.0	24.6	25.0	25.4	25.7	26.2
92.5°	34.7	35.4	36.0	36.2	35.9	35.7	35.5	35.2
95°	66.1	66.9	67.7	68.0	68.0	68.0	68.0	68.0
97.5°	102.8	103.7	104.6	105.0	104.9	104.9	104.8	104.7
100°	129.4	130.0	130.5	131.0	131.4	131.8	132.2	132.6
102.5°	160.1	160.7	161.3	161.5	161.4	161.4	161.3	161.2
105°	205.9	205.9	205.9	206.0	206.5	206.8	207.2	207.6
107.5°	255.5	256.1	256.7	256.8	256.7	256.4	256.1	255.9
110°	288.5	289.3	290.1	290.2	289.9	289.5	289.1	288.7



TEST NUMBER: P332137-935

CATALOG NUMBER: S123DIW-S560D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	321.7	322.5	323.5	323.9	323.8	323.7	323.7	323.6
115°	372.0	372.2	372.4	372.4	372.2	372.0	371.8	371.6
117.5°	422.8	422.8	422.8	422.4	421.9	421.4	420.8	420.3
120°	456.7	456.5	456.3	456.0	455.6	455.2	454.9	454.4
122.5°	490.9	490.4	490.0	489.4	488.9	488.4	487.8	487.2
125°	541.9	541.1	540.4	539.6	538.8	538.0	537.3	536.5
127.5°	592.2	591.2	590.0	589.0	588.1	587.3	586.3	585.5
130°	625.6	624.8	624.1	623.0	621.6	620.3	619.0	617.6
132.5°	658.1	657.2	656.3	655.3	654.2	653.2	652.1	651.1
135°	706.7	705.9	705.2	704.6	704.2	703.9	703.4	703.1
137.5°	754.3	753.5	752.7	751.9	751.1	750.4	749.7	749.0
140°	785.6	785.3	785.1	784.4	783.0	781.7	780.3	778.9
142.5°	814.9	814.7	814.5	813.8	812.8	811.8	810.7	809.7
145°	858.0	857.7	857.6	857.0	856.3	855.5	854.7	853.9
147.5°	898.6	898.6	898.6	898.0	896.9	895.7	894.6	893.4
150°	923.8	923.8	923.8	923.2	922.0	920.8	919.7	918.5
152.5°	946.7	947.0	947.4	947.0	946.0	944.9	943.9	943.0
155°	980.2	981.0	981.8	981.5	980.2	978.8	977.5	976.1
157.5°	1009.1	1010.0	1010.7	1010.6	1009.5	1008.5	1007.4	1006.3
160°	1026.9	1027.9	1028.8	1028.9	1028.1	1027.3	1026.6	1025.8
162.5°	1043.6	1044.6	1045.6	1045.4	1044.2	1042.9	1041.7	1040.4
165°	1064.8	1065.9	1067.1	1067.0	1065.7	1064.3	1062.9	1061.6
167.5°	1081.9	1083.1	1084.3	1084.3	1083.1	1081.9	1080.7	1079.5
170°	1091.3	1092.7	1094.1	1094.1	1092.7	1091.3	1089.9	1088.6
172.5°	1098.7	1099.9	1101.1	1101.0	1099.7	1098.3	1096.9	1095.6
175°	1106.6	1107.8	1109.0	1108.9	1107.5	1106.1	1104.8	1103.5
177.5°	1110.2	1111.1	1112.1	1112.0	1110.9	1109.8	1108.7	1107.7
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4

(END OF REPORT)