

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332142-830

Luminaire Tested: **S123DIW-S560D1320U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332142-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S560D1320U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7164.2 lumens  
Efficiency: N/A  
Efficacy: 133.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38	31
1	93	89	85	82	84	80	77	74	63	61	59	48	47	45	34	33	32	26
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27	21
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	40	58	48	42	37	39	34	30	30	26	23	21	19	17	13
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15	12
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13	10
8	51	39	32	26	46	35	29	24	29	24	20	22	19	16	16	14	12	9
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	1.1
10°-20°	223.3	3.1
20°-30°	329.9	4.6
30°-40°	385.4	5.4
40°-50°	387.4	5.4
50°-60°	340.3	4.8
60°-70°	253.5	3.5
70°-80°	144.5	2.0
80°-90°	46.0	0.6
90°-100°	59.3	0.8
100°-110°	282.7	3.9
110°-120°	679.0	9.5
120°-130°	864.6	12.1
130°-140°	923.8	12.9
140°-150°	863.8	12.1
150°-160°	696.8	9.7
160°-170°	449.7	6.3
170°-180°	155.0	2.2
0°-30°	632.3	8.8
0°-40°	1017.7	14.2
0°-60°	1745.5	24.4
0°-90°	2189.5	30.6
90°-120°	1020.9	14.3
90°-150°	3673.1	51.3
90°-180°	4975.0	69.4
0°-180°	7164.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	14	29	34	36	6
95°	74	28	38	46	46	91
105°	361	368	265	63	53	383
115°	678	685	696	707	713	669
125°	955	964	970	972	974	853
135°	1189	1196	1201	1204	1201	915
145°	1372	1380	1383	1385	1385	858
155°	1511	1509	1510	1515	1509	696
165°	1594	1590	1589	1598	1590	450
175°	1631	1626	1626	1634	1625	155
180°	1631	1631	1631	1631	1631	



TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.3	15.5	15.6	15.7	15.8	16.2	16.8	17.3	17.9	18.6	18.6
90°	1.2	3.9	6.6	9.3	12.0	15.1	18.6	22.1	25.5	29.1	30.2
92.5°	22.5	21.8	21.0	20.3	19.5	20.5	23.1	25.7	28.4	31.0	32.7
95°	73.9	62.9	51.8	40.8	29.8	25.7	28.7	31.7	34.6	37.6	39.5
97.5°	148.5	143.6	138.6	133.7	128.8	116.6	97.2	77.9	58.4	39.0	41.2
100°	204.8	210.2	215.6	220.9	226.4	208.0	166.1	124.0	82.0	40.0	42.1
102.5°	268.8	272.7	276.5	280.4	284.4	263.3	217.4	171.5	125.6	79.7	73.0
105°	361.2	364.1	367.1	370.0	373.0	362.4	338.1	313.9	289.6	265.4	217.7
107.5°	458.6	461.0	463.4	465.7	468.1	471.2	475.0	478.8	482.7	486.4	451.5
110°	523.6	525.8	527.8	530.0	532.2	534.7	537.7	540.6	543.7	546.6	537.7



TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	585.6	587.6	589.5	591.4	593.3	595.8	598.8	601.7	604.7	607.7	607.8
115°	677.5	679.1	680.7	682.3	683.9	686.0	688.3	690.8	693.2	695.7	698.3
117.5°	766.5	768.5	770.4	772.4	774.4	776.0	777.2	778.5	779.8	781.0	783.2
120°	821.7	824.2	826.5	829.0	831.4	833.0	833.8	834.6	835.5	836.2	838.4
122.5°	878.0	880.0	881.9	883.9	885.9	887.4	888.4	889.5	890.5	891.6	893.1
125°	955.0	957.2	959.3	961.5	963.7	965.3	966.3	967.4	968.5	969.6	970.1
127.5°	1029.6	1031.8	1034.0	1036.1	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0
130°	1076.2	1078.4	1080.5	1082.7	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8
132.5°	1120.8	1122.9	1125.1	1127.3	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5
135°	1188.9	1190.5	1192.1	1193.7	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8
137.5°	1247.1	1249.2	1251.2	1253.2	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3
140°	1285.9	1287.5	1289.1	1290.7	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9
142.5°	1321.7	1323.3	1325.0	1326.6	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5
145°	1372.0	1373.9	1375.7	1377.6	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4
147.5°	1419.2	1420.4	1421.6	1422.9	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8
150°	1448.3	1449.1	1449.9	1450.7	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9
152.5°	1474.4	1474.8	1475.2	1475.6	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6
155°	1511.3	1510.8	1510.2	1509.7	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5
157.5°	1539.9	1539.8	1539.8	1539.7	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0
160°	1557.4	1557.1	1556.8	1556.5	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5
162.5°	1573.9	1573.1	1572.4	1571.7	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3
165°	1593.7	1592.9	1592.0	1591.3	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0
167.5°	1609.2	1608.2	1607.0	1606.0	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6
170°	1618.0	1616.8	1615.8	1614.8	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2
172.5°	1623.8	1622.5	1621.2	1619.9	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1
175°	1631.3	1629.9	1628.6	1627.2	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3
177.5°	1633.2	1632.1	1631.1	1630.0	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	18.7	18.8	18.9	18.9	19.0	19.2	19.3	19.4
90°	31.2	32.3	33.4	34.2	34.8	35.3	35.8	36.4
92.5°	34.5	36.2	37.9	38.9	39.3	39.6	39.9	40.2
95°	41.4	43.3	45.1	46.1	46.1	46.1	46.1	46.1
97.5°	43.4	45.5	47.6	48.8	49.1	49.4	49.7	50.0
100°	44.3	46.5	48.6	49.9	50.0	50.3	50.6	50.9
102.5°	66.4	59.7	53.1	50.0	50.4	50.9	51.4	51.8
105°	170.0	122.4	74.7	51.2	51.7	52.2	52.8	53.3
107.5°	416.6	381.6	346.7	311.2	275.3	239.3	203.4	167.5
110°	528.8	519.9	511.0	487.3	448.8	410.3	371.8	333.3





TEST NUMBER: P332142-830

CATALOG NUMBER: S123DIW-S560D1320U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	608.0	608.1	608.3	604.4	596.2	588.1	579.9	571.8
115°	701.1	703.7	706.4	708.3	709.4	710.5	711.5	712.7
117.5°	785.3	787.4	789.6	790.8	791.0	791.2	791.5	791.6
120°	840.6	842.7	844.9	845.9	845.9	845.9	845.9	845.9
122.5°	894.6	896.1	897.6	898.4	898.6	898.8	899.1	899.3
125°	970.6	971.2	971.7	972.2	972.8	973.4	973.8	974.4
127.5°	1046.9	1047.7	1048.7	1048.8	1048.3	1047.7	1047.2	1046.6
130°	1092.9	1094.0	1095.0	1095.3	1094.8	1094.3	1093.7	1093.2
132.5°	1136.5	1137.6	1138.7	1138.9	1138.1	1137.4	1136.6	1135.9
135°	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1
137.5°	1261.6	1262.8	1264.1	1264.5	1263.9	1263.5	1262.9	1262.3
140°	1298.9	1300.0	1301.1	1301.4	1300.8	1300.2	1299.8	1299.2
142.5°	1334.4	1335.2	1336.1	1336.1	1335.4	1334.6	1333.9	1333.1
145°	1383.9	1384.4	1385.0	1385.3	1385.3	1385.3	1385.3	1385.3
147.5°	1428.2	1428.8	1429.4	1429.0	1427.8	1426.5	1425.3	1424.0
150°	1455.4	1455.9	1456.5	1456.3	1455.6	1454.7	1454.0	1453.1
152.5°	1479.5	1480.5	1481.5	1481.4	1480.1	1478.8	1477.6	1476.4
155°	1512.8	1514.1	1515.5	1515.3	1513.7	1512.1	1510.5	1508.9
157.5°	1541.7	1543.3	1544.9	1544.6	1542.6	1540.5	1538.3	1536.3
160°	1558.1	1559.8	1561.4	1561.2	1559.3	1557.5	1555.6	1553.7
162.5°	1573.1	1575.0	1576.8	1576.9	1575.2	1573.6	1571.9	1570.2
165°	1593.2	1595.3	1597.5	1597.6	1595.7	1593.8	1592.0	1590.1
167.5°	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4
170°	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1
172.5°	1623.2	1625.4	1627.6	1627.4	1625.0	1622.7	1620.3	1618.0
175°	1630.2	1632.1	1634.0	1633.8	1631.7	1629.6	1627.4	1625.2
177.5°	1632.8	1634.6	1636.3	1636.1	1633.9	1631.7	1629.6	1627.4
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3

(END OF REPORT)