

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332143-935

Luminaire Tested: **S123DIW-S560D1320U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332143-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1320U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5938.8 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	78	72	67	77	71	66	61	57	53	50	44	41	39	32	30	29	24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20
4	71	61	53	47	64	55	48	43	44	40	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15
6	60	48	40	35	54	44	37	32	36	31	27	28	24	21	21	18	16	13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	13	15	12	11	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.2
10°-20°	204.0	3.4
20°-30°	301.4	5.1
30°-40°	352.0	5.9
40°-50°	353.9	6.0
50°-60°	310.9	5.2
60°-70°	231.6	3.9
70°-80°	132.0	2.2
80°-90°	42.1	0.7
90°-100°	92.6	1.6
100°-110°	277.2	4.7
110°-120°	471.4	7.9
120°-130°	620.1	10.4
130°-140°	697.0	11.7
140°-150°	685.1	11.5
150°-160°	576.8	9.7
160°-170°	383.9	6.5
170°-180°	134.4	2.3
0°-30°	577.6	9.7
0°-40°	929.7	15.7
0°-60°	1594.5	26.8
0°-90°	2000.1	33.7
90°-120°	841.3	14.2
90°-150°	2843.5	47.9
90°-180°	3939.0	66.3
0°-180°	5938.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	12	27	31	34	6
95°	66	74	83	87	87	74
105°	251	254	264	264	266	269
115°	475	478	476	477	476	469
125°	695	698	696	691	687	619
135°	901	907	907	902	900	694
145°	1093	1096	1099	1098	1093	683
155°	1252	1252	1253	1257	1250	576
165°	1364	1360	1360	1366	1359	384
175°	1418	1414	1414	1420	1413	135
180°	1422	1422	1422	1422	1422	



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	14.1	14.2	14.4	14.6	14.9	15.4	15.9	16.4	17.0	17.0
90°	1.1	3.6	6.1	8.5	11.0	13.9	17.1	20.3	23.6	26.8	27.8
92.5°	27.0	28.7	30.4	32.1	33.8	35.6	37.4	39.2	41.1	42.9	43.7
95°	65.9	67.6	69.4	71.1	72.8	74.7	76.7	78.7	80.7	82.7	83.6
97.5°	117.0	118.3	119.6	120.9	122.2	123.6	125.0	126.4	127.9	129.3	130.4
100°	151.9	153.3	154.8	156.4	157.8	159.2	160.4	161.7	162.9	164.2	164.9
102.5°	192.1	193.0	193.9	194.8	195.6	196.9	198.5	200.2	201.8	203.5	204.2
105°	251.2	251.8	252.3	252.7	253.2	254.6	256.8	259.1	261.3	263.6	263.6
107.5°	320.0	320.4	320.6	321.0	321.2	321.8	322.7	323.6	324.5	325.4	326.2
110°	362.9	363.4	363.9	364.4	364.9	365.4	365.9	366.4	366.9	367.4	368.4



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.6	407.9	408.2	408.5	408.8	409.0	409.1	409.1	409.3	409.4	410.6
115°	474.6	475.4	476.0	476.8	477.6	477.7	477.2	476.7	476.2	475.7	476.0
117.5°	542.1	542.5	543.0	543.5	544.1	544.0	543.3	542.7	542.0	541.4	541.3
120°	584.0	585.5	587.0	588.5	590.0	590.1	588.8	587.6	586.4	585.1	584.9
122.5°	627.8	628.9	630.0	631.1	632.1	632.4	631.7	631.1	630.4	629.8	629.1
125°	694.6	695.3	696.0	696.8	697.6	697.7	697.2	696.7	696.2	695.7	694.7
127.5°	756.2	757.9	759.4	761.0	762.6	763.1	762.6	762.0	761.5	761.0	759.5
130°	797.3	799.3	801.3	803.3	805.3	805.9	805.1	804.4	803.7	802.9	801.9
132.5°	838.4	840.4	842.4	844.4	846.4	847.1	846.5	846.0	845.4	844.9	843.7
135°	901.2	902.7	904.1	905.6	907.1	907.8	907.5	907.2	907.0	906.7	905.8
137.5°	959.2	960.4	961.7	962.9	964.2	965.2	965.8	966.5	967.1	967.8	966.6
140°	999.4	1000.7	1001.9	1003.2	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9
142.5°	1036.0	1037.3	1038.5	1039.8	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4
145°	1093.2	1093.7	1094.2	1094.8	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5
147.5°	1143.2	1144.2	1145.0	1146.0	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4
150°	1178.1	1178.6	1179.1	1179.6	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6
152.5°	1206.7	1207.4	1208.1	1208.8	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6
155°	1251.8	1251.8	1251.8	1251.8	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0
157.5°	1290.2	1290.0	1289.6	1289.3	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8
160°	1314.3	1313.9	1313.4	1312.9	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4
162.5°	1335.8	1335.1	1334.4	1333.7	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8
165°	1363.5	1362.7	1362.0	1361.2	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6
167.5°	1385.6	1384.6	1383.6	1382.6	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5
170°	1398.1	1397.1	1396.1	1395.2	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3
172.5°	1407.9	1407.0	1405.9	1405.0	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0
175°	1418.2	1417.2	1416.3	1415.2	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2
177.5°	1422.5	1421.7	1420.8	1420.0	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	17.1	17.2	17.3	17.4	17.5	17.6	17.7	17.8
90°	28.8	29.8	30.7	31.5	32.0	32.5	33.0	33.5
92.5°	44.4	45.3	46.1	46.3	46.0	45.7	45.4	45.1
95°	84.6	85.6	86.6	87.1	87.1	87.1	87.1	87.1
97.5°	131.6	132.8	133.9	134.4	134.3	134.2	134.1	134.0
100°	165.7	166.3	167.1	167.7	168.2	168.8	169.3	169.7
102.5°	204.9	205.7	206.5	206.7	206.6	206.6	206.5	206.4
105°	263.6	263.6	263.6	263.8	264.3	264.8	265.3	265.8
107.5°	327.0	327.8	328.6	328.8	328.6	328.2	328.0	327.6
110°	369.4	370.4	371.3	371.6	371.1	370.7	370.1	369.6



TEST NUMBER: P332143-935

CATALOG NUMBER: S123DIW-S560D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	411.7	412.9	414.1	414.7	414.6	414.5	414.4	414.3
115°	476.2	476.5	476.7	476.7	476.5	476.2	476.0	475.7
117.5°	541.3	541.2	541.1	540.8	540.1	539.4	538.7	538.0
120°	584.6	584.4	584.2	583.8	583.3	582.8	582.3	581.8
122.5°	628.5	627.8	627.2	626.5	625.9	625.2	624.5	623.8
125°	693.7	692.8	691.7	690.8	689.7	688.7	687.8	686.7
127.5°	758.1	756.7	755.4	754.1	752.9	751.8	750.7	749.5
130°	800.9	800.0	798.9	797.5	795.8	794.1	792.4	790.7
132.5°	842.5	841.3	840.2	838.9	837.5	836.2	834.8	833.5
135°	904.7	903.8	902.8	902.1	901.6	901.0	900.5	900.1
137.5°	965.6	964.6	963.5	962.6	961.7	960.7	959.8	958.8
140°	1005.6	1005.4	1005.1	1004.2	1002.5	1000.7	998.9	997.2
142.5°	1043.2	1042.9	1042.7	1041.9	1040.5	1039.2	1037.8	1036.6
145°	1098.3	1098.1	1097.9	1097.3	1096.2	1095.2	1094.2	1093.2
147.5°	1150.4	1150.4	1150.4	1149.7	1148.2	1146.7	1145.2	1143.8
150°	1182.6	1182.6	1182.6	1181.8	1180.3	1178.9	1177.3	1175.9
152.5°	1211.9	1212.4	1212.7	1212.3	1211.0	1209.7	1208.4	1207.1
155°	1254.9	1255.9	1256.9	1256.5	1254.8	1253.1	1251.3	1249.6
157.5°	1291.8	1292.9	1294.0	1293.7	1292.4	1291.0	1289.6	1288.2
160°	1314.6	1315.9	1317.1	1317.2	1316.2	1315.3	1314.2	1313.2
162.5°	1336.0	1337.3	1338.5	1338.3	1336.8	1335.2	1333.6	1332.0
165°	1363.1	1364.6	1366.1	1366.0	1364.3	1362.5	1360.7	1359.0
167.5°	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0
170°	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6
172.5°	1406.5	1408.1	1409.6	1409.5	1407.8	1406.0	1404.3	1402.6
175°	1416.7	1418.2	1419.7	1419.5	1417.8	1416.1	1414.4	1412.6
177.5°	1421.3	1422.5	1423.7	1423.6	1422.1	1420.7	1419.4	1418.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6

(END OF REPORT)