

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332149-830

Luminaire Tested: **S123DIW-S560D1535U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332149-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1535U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7203.3 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	34	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	30	28	27
3	77	68	61	56	69	62	55	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	34	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	25	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.1
10°-20°	223.3	3.1
20°-30°	329.9	4.6
30°-40°	385.4	5.3
40°-50°	387.4	5.4
50°-60°	340.3	4.7
60°-70°	253.5	3.5
70°-80°	144.5	2.0
80°-90°	46.8	0.6
90°-100°	117.9	1.6
100°-110°	352.8	4.9
110°-120°	600.0	8.3
120°-130°	789.3	11.0
130°-140°	887.1	12.3
140°-150°	872.0	12.1
150°-160°	734.1	10.2
160°-170°	488.7	6.8
170°-180°	171.1	2.4
0°-30°	632.3	8.8
0°-40°	1017.7	14.1
0°-60°	1745.5	24.2
0°-90°	2190.3	30.4
90°-120°	1070.7	14.9
90°-150°	3619.1	50.2
90°-180°	5013.0	69.6
0°-180°	7203.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	16	34	40	43	7
95°	84	94	105	110	111	94
105°	320	323	336	336	338	343
115°	604	608	606	607	606	597
125°	884	888	886	880	874	788
135°	1147	1155	1154	1149	1146	884
145°	1392	1394	1398	1397	1392	869
155°	1593	1593	1595	1600	1590	733
165°	1735	1731	1731	1739	1730	489
175°	1805	1800	1799	1807	1798	171
180°	1809	1809	1809	1809	1809	



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.3	15.6	15.8	16.0	16.3	16.8	17.4	18.1	18.9	19.5	19.7
90°	1.4	4.6	7.7	10.9	14.0	17.7	21.8	25.9	30.0	34.1	35.3
92.5°	34.4	36.6	38.6	40.8	43.0	45.2	47.6	49.9	52.2	54.6	55.6
95°	83.9	86.1	88.3	90.5	92.7	95.1	97.6	100.1	102.6	105.2	106.4
97.5°	148.9	150.6	152.2	153.9	155.5	157.2	159.1	160.9	162.8	164.6	166.1
100°	193.3	195.2	197.1	199.0	200.9	202.6	204.2	205.8	207.4	209.0	209.9
102.5°	244.5	245.6	246.8	247.9	249.0	250.6	252.7	254.8	256.8	258.9	260.0
105°	319.8	320.5	321.0	321.7	322.3	324.0	326.9	329.7	332.6	335.5	335.5
107.5°	407.4	407.7	408.1	408.5	408.9	409.6	410.8	411.9	413.0	414.2	415.2
110°	461.9	462.6	463.2	463.8	464.5	465.1	465.7	466.4	466.9	467.6	468.9



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	518.8	519.2	519.5	519.9	520.3	520.6	520.7	520.8	520.9	521.0	522.5
115°	604.1	605.0	606.0	606.9	607.8	608.0	607.4	606.7	606.1	605.5	605.8
117.5°	689.9	690.5	691.2	691.8	692.4	692.3	691.5	690.7	689.8	689.1	689.0
120°	743.4	745.3	747.2	749.0	750.9	751.1	749.5	747.9	746.3	744.8	744.4
122.5°	799.1	800.4	801.8	803.2	804.6	804.9	804.1	803.2	802.5	801.6	800.8
125°	884.0	885.0	886.0	886.9	887.9	888.0	887.4	886.7	886.1	885.5	884.2
127.5°	962.5	964.5	966.6	968.6	970.6	971.3	970.5	969.9	969.2	968.5	966.7
130°	1014.8	1017.4	1019.8	1022.4	1024.9	1025.7	1024.7	1023.8	1022.8	1021.9	1020.7
132.5°	1067.1	1069.6	1072.1	1074.7	1077.2	1078.2	1077.4	1076.8	1076.0	1075.3	1073.8
135°	1147.0	1148.9	1150.8	1152.6	1154.6	1155.4	1155.1	1154.7	1154.4	1154.1	1152.8
137.5°	1220.9	1222.5	1224.1	1225.7	1227.2	1228.4	1229.3	1230.0	1230.9	1231.7	1230.4
140°	1272.1	1273.7	1275.3	1276.8	1278.4	1279.3	1279.7	1280.0	1280.3	1280.6	1280.3
142.5°	1318.7	1320.2	1321.8	1323.4	1325.0	1326.1	1326.6	1327.2	1327.8	1328.3	1328.0
145°	1391.5	1392.1	1392.7	1393.4	1394.0	1394.8	1395.7	1396.7	1397.6	1398.5	1398.3
147.5°	1455.1	1456.2	1457.4	1458.6	1459.7	1460.7	1461.6	1462.4	1463.3	1464.2	1464.2
150°	1499.5	1500.2	1500.7	1501.4	1502.0	1502.6	1503.3	1503.9	1504.5	1505.1	1505.1
152.5°	1535.9	1536.7	1537.7	1538.5	1539.4	1540.0	1540.4	1540.8	1541.2	1541.5	1542.1
155°	1593.3	1593.3	1593.3	1593.3	1593.3	1593.5	1593.7	1594.0	1594.4	1594.7	1596.0
157.5°	1642.2	1641.8	1641.4	1641.1	1640.7	1640.6	1640.9	1641.1	1641.3	1641.6	1642.9
160°	1672.9	1672.3	1671.6	1670.9	1670.4	1670.0	1670.0	1670.0	1670.0	1670.0	1671.6
162.5°	1700.2	1699.3	1698.4	1697.5	1696.7	1696.3	1696.6	1696.9	1697.0	1697.3	1698.9
165°	1735.4	1734.5	1733.5	1732.6	1731.6	1731.2	1731.2	1731.2	1731.2	1731.2	1733.1
167.5°	1763.6	1762.3	1761.0	1759.7	1758.5	1758.0	1758.2	1758.5	1758.8	1759.0	1761.0
170°	1779.4	1778.2	1777.0	1775.7	1774.4	1773.8	1773.8	1773.8	1773.8	1773.8	1776.0
172.5°	1792.0	1790.7	1789.4	1788.2	1787.0	1786.3	1786.3	1786.3	1786.3	1786.3	1788.3
175°	1805.1	1803.8	1802.5	1801.3	1800.0	1799.4	1799.4	1799.4	1799.4	1799.4	1801.3
177.5°	1810.4	1809.5	1808.5	1807.4	1806.4	1805.9	1805.9	1805.9	1805.9	1805.9	1807.4
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	19.8	19.9	20.0	20.2	20.3	20.4	20.5	20.6
90°	36.7	37.9	39.2	40.2	40.7	41.4	42.0	42.6
92.5°	56.6	57.6	58.6	58.9	58.5	58.2	57.8	57.4
95°	107.7	109.0	110.2	110.8	110.8	110.8	110.8	110.8
97.5°	167.5	168.9	170.4	171.1	171.0	170.8	170.7	170.6
100°	210.8	211.8	212.7	213.5	214.1	214.8	215.4	216.0
102.5°	260.9	261.8	262.8	263.2	263.1	262.9	262.8	262.7
105°	335.5	335.5	335.5	335.7	336.4	337.1	337.6	338.3
107.5°	416.2	417.2	418.2	418.5	418.1	417.7	417.4	417.0
110°	470.1	471.4	472.7	473.0	472.3	471.7	471.1	470.4



TEST NUMBER: P332149-830

CATALOG NUMBER: S123DIW-S560D1535U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	524.1	525.6	527.1	527.8	527.7	527.5	527.4	527.3
115°	606.1	606.4	606.7	606.7	606.4	606.1	605.8	605.5
117.5°	688.9	688.9	688.8	688.3	687.4	686.5	685.7	684.8
120°	744.1	743.9	743.5	743.0	742.4	741.8	741.1	740.5
122.5°	799.9	799.2	798.3	797.5	796.6	795.7	794.8	793.9
125°	883.0	881.7	880.4	879.1	877.9	876.7	875.3	874.1
127.5°	965.0	963.2	961.4	959.8	958.4	956.9	955.5	953.9
130°	1019.4	1018.1	1016.9	1015.1	1013.0	1010.7	1008.5	1006.3
132.5°	1072.3	1070.8	1069.3	1067.7	1066.0	1064.3	1062.5	1060.8
135°	1151.6	1150.3	1149.1	1148.1	1147.5	1146.8	1146.2	1145.6
137.5°	1229.1	1227.8	1226.4	1225.1	1223.9	1222.8	1221.5	1220.3
140°	1280.0	1279.7	1279.3	1278.1	1275.8	1273.7	1271.4	1269.2
142.5°	1327.8	1327.4	1327.1	1326.1	1324.4	1322.7	1321.0	1319.3
145°	1397.9	1397.6	1397.3	1396.5	1395.2	1394.0	1392.7	1391.5
147.5°	1464.2	1464.2	1464.2	1463.3	1461.4	1459.5	1457.5	1455.7
150°	1505.1	1505.1	1505.1	1504.2	1502.3	1500.4	1498.5	1496.7
152.5°	1542.6	1543.0	1543.6	1543.0	1541.3	1539.7	1538.0	1536.4
155°	1597.2	1598.5	1599.8	1599.3	1597.0	1594.9	1592.6	1590.4
157.5°	1644.3	1645.6	1646.9	1646.7	1644.9	1643.1	1641.3	1639.6
160°	1673.2	1674.8	1676.3	1676.5	1675.3	1674.0	1672.7	1671.4
162.5°	1700.4	1702.0	1703.6	1703.5	1701.4	1699.4	1697.3	1695.4
165°	1734.9	1736.8	1738.7	1738.6	1736.4	1734.2	1731.9	1729.8
167.5°	1762.9	1764.9	1766.8	1766.8	1764.9	1762.9	1761.0	1759.0
170°	1778.2	1780.5	1782.6	1782.6	1780.5	1778.2	1776.0	1773.8
172.5°	1790.2	1792.2	1794.1	1794.0	1791.8	1789.6	1787.3	1785.2
175°	1803.2	1805.1	1806.9	1806.8	1804.6	1802.3	1800.2	1798.0
177.5°	1808.9	1810.4	1811.9	1811.8	1810.1	1808.3	1806.6	1804.8
180°	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3	1809.3

(END OF REPORT)