

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332125-830

Luminaire Tested: **S123DIW-S560D460U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332125-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D460U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3693.1 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.1
10°-20°	223.3	6.0
20°-30°	329.9	8.9
30°-40°	385.4	10.4
40°-50°	387.4	10.5
50°-60°	340.3	9.2
60°-70°	253.5	6.9
70°-80°	144.5	3.9
80°-90°	43.1	1.2
90°-100°	35.4	1.0
100°-110°	106.0	2.9
110°-120°	180.3	4.9
120°-130°	237.2	6.4
130°-140°	266.6	7.2
140°-150°	262.1	7.1
150°-160°	220.6	6.0
160°-170°	146.9	4.0
170°-180°	51.4	1.4
0°-30°	632.3	17.1
0°-40°	1017.7	27.6
0°-60°	1745.5	47.3
0°-90°	2186.6	59.2
90°-120°	321.8	8.7
90°-150°	1087.6	29.5
90°-180°	1507.0	40.8
0°-180°	3693.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	0	5	10	12	13	4
95°	25	28	32	33	33	28
105°	96	97	101	101	102	103
115°	182	183	182	182	182	180
125°	266	267	266	264	263	237
135°	345	347	347	345	344	266
145°	418	419	420	420	418	261
155°	479	479	479	481	478	220
165°	522	520	520	522	520	147
175°	542	541	541	543	540	52
180°	544	544	544	544	544	



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.1	14.9	14.7	14.5	14.3	14.3	14.4	14.5	14.6	14.8	14.7
90°	0.5	1.4	2.4	3.3	4.2	5.3	6.5	7.8	9.0	10.3	10.7
92.5°	10.4	11.0	11.6	12.3	12.9	13.6	14.3	15.0	15.7	16.4	16.7
95°	25.2	25.8	26.5	27.2	27.9	28.6	29.3	30.1	30.8	31.6	32.0
97.5°	44.8	45.2	45.7	46.3	46.8	47.2	47.8	48.4	48.9	49.5	49.9
100°	58.1	58.6	59.2	59.8	60.3	60.9	61.4	61.8	62.3	62.8	63.1
102.5°	73.4	73.8	74.2	74.5	74.8	75.3	76.0	76.5	77.2	77.9	78.1
105°	96.1	96.3	96.5	96.7	96.9	97.4	98.2	99.1	99.9	100.8	100.8
107.5°	122.4	122.5	122.6	122.7	122.9	123.1	123.5	123.8	124.1	124.5	124.8
110°	138.8	139.0	139.2	139.4	139.6	139.8	140.0	140.2	140.3	140.5	140.9



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.0	156.2	156.3	156.4	156.5	156.5	156.6	156.6	156.6	157.0
115°	181.5	181.8	182.1	182.4	182.7	182.8	182.6	182.4	182.2	182.0	182.1
117.5°	207.4	207.5	207.7	207.9	208.1	208.0	207.8	207.5	207.4	207.1	207.1
120°	223.4	223.9	224.5	225.1	225.6	225.7	225.3	224.8	224.3	223.9	223.8
122.5°	240.2	240.5	241.0	241.4	241.8	241.9	241.7	241.4	241.2	240.9	240.6
125°	265.7	266.0	266.3	266.6	266.8	266.8	266.6	266.5	266.3	266.1	265.7
127.5°	289.3	289.8	290.5	291.1	291.7	291.9	291.7	291.4	291.2	291.1	290.5
130°	305.0	305.8	306.5	307.3	308.0	308.2	307.9	307.6	307.4	307.1	306.7
132.5°	320.7	321.4	322.3	323.0	323.8	324.0	323.8	323.6	323.4	323.2	322.7
135°	344.7	345.3	345.8	346.4	346.9	347.2	347.1	347.0	346.9	346.9	346.5
137.5°	366.9	367.4	367.9	368.3	368.8	369.2	369.4	369.7	369.9	370.1	369.8
140°	382.3	382.8	383.2	383.7	384.2	384.5	384.6	384.7	384.7	384.8	384.7
142.5°	396.3	396.8	397.3	397.8	398.2	398.5	398.7	398.9	399.1	399.2	399.1
145°	418.2	418.4	418.6	418.8	419.0	419.1	419.4	419.7	420.0	420.3	420.2
147.5°	437.3	437.6	438.0	438.3	438.7	438.9	439.2	439.5	439.8	440.1	440.1
150°	450.6	450.8	451.0	451.2	451.4	451.6	451.8	451.9	452.1	452.3	452.3
152.5°	461.6	461.8	462.1	462.3	462.6	462.8	462.9	463.1	463.2	463.3	463.4
155°	478.8	478.8	478.8	478.8	478.8	478.9	479.0	479.1	479.2	479.3	479.7
157.5°	493.5	493.4	493.3	493.1	493.0	493.0	493.1	493.2	493.2	493.3	493.7
160°	502.8	502.6	502.4	502.2	502.0	501.9	501.9	501.9	501.9	501.9	502.4
162.5°	511.0	510.7	510.4	510.1	509.9	509.8	509.8	509.9	510.0	510.1	510.6
165°	521.5	521.2	520.9	520.7	520.4	520.3	520.3	520.3	520.3	520.3	520.8
167.5°	530.0	529.6	529.2	528.9	528.5	528.3	528.4	528.5	528.6	528.6	529.2
170°	534.8	534.4	534.0	533.7	533.3	533.1	533.1	533.1	533.1	533.1	533.8
172.5°	538.6	538.2	537.8	537.4	537.0	536.8	536.8	536.8	536.8	536.8	537.4
175°	542.4	542.1	541.7	541.3	540.9	540.7	540.7	540.7	540.7	540.7	541.3
177.5°	544.1	543.8	543.5	543.2	542.9	542.7	542.7	542.7	542.7	542.7	543.2
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	14.6	14.6	14.5	14.5	14.6	14.6	14.6	14.7
90°	11.0	11.4	11.8	12.1	12.3	12.4	12.6	12.8
92.5°	17.0	17.3	17.6	17.7	17.6	17.4	17.3	17.2
95°	32.3	32.7	33.1	33.3	33.3	33.3	33.3	33.3
97.5°	50.3	50.8	51.2	51.4	51.4	51.4	51.3	51.3
100°	63.3	63.6	63.9	64.2	64.4	64.6	64.8	64.9
102.5°	78.4	78.7	79.0	79.1	79.1	79.0	79.0	78.9
105°	100.8	100.8	100.8	100.9	101.1	101.3	101.5	101.7
107.5°	125.1	125.4	125.6	125.7	125.6	125.5	125.5	125.4
110°	141.3	141.7	142.0	142.1	141.9	141.8	141.6	141.4



TEST NUMBER: P332125-830

CATALOG NUMBER: S123DIW-S560D460U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	158.0	158.4	158.6	158.5	158.5	158.5	158.4
115°	182.2	182.3	182.4	182.4	182.3	182.2	182.1	182.0
117.5°	207.1	207.0	207.0	206.9	206.6	206.3	206.0	205.8
120°	223.7	223.6	223.5	223.3	223.1	222.9	222.7	222.5
122.5°	240.4	240.2	239.9	239.7	239.4	239.1	238.8	238.6
125°	265.3	264.9	264.6	264.2	263.8	263.4	263.1	262.7
127.5°	290.0	289.5	288.9	288.4	288.0	287.6	287.1	286.7
130°	306.3	305.9	305.6	305.1	304.4	303.8	303.1	302.4
132.5°	322.3	321.8	321.3	320.8	320.4	319.8	319.3	318.8
135°	346.1	345.7	345.3	345.1	344.9	344.7	344.5	344.3
137.5°	369.4	369.0	368.5	368.2	367.8	367.5	367.1	366.7
140°	384.7	384.6	384.5	384.1	383.4	382.8	382.1	381.4
142.5°	399.0	398.9	398.8	398.5	398.0	397.5	397.0	396.4
145°	420.1	420.0	419.9	419.7	419.3	419.0	418.6	418.2
147.5°	440.1	440.1	440.1	439.8	439.2	438.6	438.0	437.4
150°	452.3	452.3	452.3	452.0	451.5	450.9	450.3	449.8
152.5°	463.5	463.7	463.9	463.7	463.3	462.7	462.2	461.8
155°	480.0	480.4	480.8	480.6	479.9	479.3	478.6	478.0
157.5°	494.2	494.6	494.9	494.8	494.4	493.8	493.2	492.8
160°	502.8	503.3	503.8	503.8	503.4	503.0	502.7	502.3
162.5°	511.0	511.5	512.0	511.9	511.3	510.7	510.1	509.4
165°	521.4	522.0	522.5	522.5	521.8	521.1	520.5	519.8
167.5°	529.8	530.4	530.9	530.9	530.4	529.8	529.2	528.6
170°	534.4	535.1	535.7	535.7	535.1	534.4	533.8	533.1
172.5°	538.0	538.6	539.1	539.1	538.5	537.8	537.2	536.5
175°	541.9	542.4	543.0	543.0	542.3	541.7	541.0	540.4
177.5°	543.7	544.1	544.5	544.5	543.9	543.5	542.9	542.3
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8

(END OF REPORT)