

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332131-935

Luminaire Tested: **S123DIW-S560D755U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332131-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4252.4 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332131-935
CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82		67	67	67		53	53	53	47
1	97	93	89	85	89	85	82	79	71	69	67		59	57	56		47	46	45	39
2	88	81	75	70	81	75	69	65	63	59	55		52	49	46		41	39	38	33
3	81	71	64	58	74	66	59	54	55	50	46		46	42	39		37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40		41	37	34		33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34		36	32	29		29	26	24	21
6	62	50	42	36	57	46	39	34	39	34	30		33	29	25		27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26		30	26	22		24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23		27	23	20		22	19	17	14
9	50	37	30	25	46	35	28	24	30	24	21		25	21	18		21	18	15	13
10	46	34	27	22	43	32	25	21	27	22	19		23	19	16		19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8257	8257	8257
5°	8295	8182	8238
10°	8240	8110	8160
15°	8143	8018	8033
20°	8031	7887	7895
25°	7880	7732	7715
30°	7713	7558	7501
35°	7540	7376	7281
40°	7359	7173	7062
45°	7159	6987	6817
50°	6958	6759	6571
55°	6696	6523	6324
60°	6433	6247	6047
65°	6199	5947	5761
70°	5854	5605	5353
75°	5348	5157	4937
80°	4823	4624	4581
85°	4236	4076	3915



TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	1.7
10°-20°	204.0	4.8
20°-30°	301.4	7.1
30°-40°	352.0	8.3
40°-50°	353.9	8.3
50°-60°	310.9	7.3
60°-70°	231.6	5.4
70°-80°	132.0	3.1
80°-90°	40.3	0.9
90°-100°	53.0	1.2
100°-110°	158.6	3.7
110°-120°	269.8	6.3
120°-130°	354.9	8.3
130°-140°	398.9	9.4
140°-150°	392.1	9.2
150°-160°	330.1	7.8
160°-170°	219.7	5.2
170°-180°	76.9	1.8
0°-30°	577.6	13.6
0°-40°	929.7	21.9
0°-60°	1594.5	37.5
0°-90°	1998.3	47.0
90°-120°	481.4	11.3
90°-150°	1627.3	38.3
90°-180°	2254.0	53.0
0°-180°	4252.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	767	767	767	767	767	
5°	768	764	757	763	762	73
15°	731	728	720	724	721	206
25°	664	659	651	651	650	305
35°	574	570	561	557	554	359
45°	470	467	459	451	448	363
55°	357	356	348	340	337	319
65°	243	240	234	228	226	240
75°	129	126	124	121	119	138
85°	34	33	33	32	32	38
90°	1	7	15	18	19	4
95°	38	42	47	50	50	42
105°	144	145	151	151	152	154
115°	272	273	272	273	272	269
125°	398	399	398	396	393	354
135°	516	519	519	516	515	397
145°	626	627	629	628	626	391
155°	716	716	717	719	715	330
165°	780	778	778	782	778	220
175°	812	809	809	812	808	77
180°	814	814	814	814	814	



TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	769.6	769.2	768.8	768.3	767.8	766.9	765.6	764.3	763.1	761.8	762.9
5°	767.7	767.0	766.2	765.5	764.7	763.6	762.0	760.3	758.8	757.2	758.6
7.5°	760.2	759.5	758.7	758.0	757.2	756.0	754.4	752.7	751.1	749.4	750.7
10°	753.9	753.1	752.4	751.7	751.0	749.6	747.7	745.8	743.9	742.0	743.3
12.5°	745.5	744.8	744.2	743.6	743.0	741.8	739.9	738.1	736.4	734.6	735.6
15°	730.7	730.2	729.6	729.0	728.4	727.2	725.3	723.4	721.4	719.5	720.7
17.5°	713.8	713.0	712.2	711.4	710.7	709.4	707.5	705.6	703.7	701.7	702.6
20°	701.1	700.3	699.3	698.4	697.6	696.2	694.3	692.4	690.4	688.5	689.1
22.5°	686.8	686.0	685.1	684.2	683.3	681.9	680.0	678.1	676.2	674.3	674.8
25°	663.5	662.6	661.8	660.9	660.0	658.6	656.7	654.8	652.9	651.0	651.1
27.5°	638.6	637.7	636.9	636.0	635.2	633.7	631.6	629.6	627.6	625.5	625.6
30°	620.6	619.9	619.1	618.5	617.7	616.3	614.2	612.2	610.2	608.1	608.1
32.5°	602.7	601.8	600.7	599.8	598.8	597.5	596.0	594.3	592.8	591.2	590.4
35°	573.8	572.9	572.0	571.2	570.3	568.9	567.0	565.1	563.2	561.3	560.4
37.5°	544.2	543.1	542.0	540.9	539.8	538.3	536.3	534.4	532.4	530.5	529.5
40°	523.7	522.8	521.9	521.1	520.1	518.7	516.6	514.6	512.6	510.5	509.3
42.5°	503.1	502.1	501.1	500.1	499.1	497.6	495.5	493.5	491.5	489.4	488.2
45°	470.3	469.7	469.1	468.5	467.9	466.7	464.8	462.9	461.0	459.0	457.3
47.5°	437.6	436.8	436.0	435.1	434.3	432.9	431.2	429.4	427.6	425.8	424.0
50°	415.5	414.7	414.1	413.3	412.6	411.3	409.3	407.4	405.5	403.6	402.0
52.5°	392.3	391.8	391.3	390.8	390.3	389.0	387.0	385.0	383.0	381.0	379.6
55°	356.8	356.6	356.5	356.4	356.2	355.2	353.3	351.4	349.5	347.6	345.9
57.5°	323.0	322.5	322.0	321.6	321.1	320.0	318.5	317.0	315.5	313.9	312.5
60°	298.8	298.6	298.5	298.3	298.2	297.2	295.5	293.7	292.0	290.2	288.9
62.5°	277.2	276.7	276.4	276.0	275.6	274.6	272.8	271.0	269.2	267.5	266.2
65°	243.4	242.6	241.9	241.2	240.5	239.4	237.9	236.4	235.0	233.5	232.3
67.5°	207.6	207.0	206.3	205.7	205.0	204.1	203.0	201.9	200.8	199.8	198.7
70°	186.0	185.1	184.3	183.4	182.4	181.6	180.7	179.9	178.9	178.1	177.0
72.5°	163.3	162.6	162.0	161.4	160.7	159.9	158.9	157.9	156.9	155.9	155.0
75°	128.6	128.0	127.4	126.8	126.3	125.8	125.3	124.8	124.4	124.0	123.3
77.5°	97.9	97.6	97.2	96.9	96.6	96.2	95.7	95.1	94.5	94.0	93.6
80°	77.8	77.4	77.0	76.5	76.0	75.7	75.4	75.1	74.8	74.6	74.4
82.5°	58.3	58.2	58.1	58.0	57.9	57.9	57.9	57.8	57.7	57.7	57.3
85°	34.3	34.0	33.8	33.4	33.1	33.0	33.0	33.0	33.0	33.0	32.7
87.5°	13.9	13.8	13.7	13.6	13.6	13.7	13.9	14.2	14.5	14.6	14.6
90°	0.6	2.1	3.4	4.9	6.3	7.9	9.8	11.6	13.5	15.3	15.9
92.5°	15.5	16.4	17.4	18.3	19.3	20.3	21.4	22.5	23.5	24.5	25.0
95°	37.7	38.7	39.7	40.7	41.7	42.7	43.9	45.0	46.1	47.3	47.9
97.5°	67.0	67.7	68.4	69.2	69.9	70.7	71.5	72.3	73.2	74.0	74.6
100°	86.9	87.7	88.6	89.5	90.3	91.1	91.8	92.6	93.2	93.9	94.4
102.5°	109.9	110.5	111.0	111.4	111.9	112.7	113.7	114.6	115.5	116.4	116.8
105°	143.8	144.0	144.4	144.6	144.9	145.7	147.0	148.3	149.6	150.8	150.8
107.5°	183.1	183.3	183.5	183.7	183.8	184.2	184.7	185.2	185.7	186.2	186.7
110°	207.7	208.0	208.3	208.5	208.8	209.1	209.4	209.7	210.0	210.3	210.9



TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	233.2	233.4	233.6	233.8	233.9	234.0	234.1	234.2	234.2	234.3	235.0
115°	271.6	272.0	272.4	272.9	273.3	273.4	273.1	272.9	272.5	272.2	272.4
117.5°	310.2	310.5	310.7	311.1	311.3	311.3	310.9	310.6	310.2	309.8	309.8
120°	334.2	335.1	336.0	336.8	337.7	337.7	337.0	336.3	335.6	334.8	334.8
122.5°	359.3	359.9	360.5	361.2	361.8	361.9	361.5	361.2	360.8	360.4	360.1
125°	397.5	398.0	398.4	398.8	399.2	399.2	399.0	398.7	398.4	398.1	397.6
127.5°	432.7	433.7	434.6	435.5	436.4	436.7	436.4	436.1	435.8	435.5	434.6
130°	456.3	457.4	458.6	459.7	460.8	461.2	460.8	460.4	459.9	459.5	458.9
132.5°	479.8	481.0	482.1	483.2	484.4	484.7	484.5	484.1	483.8	483.5	482.8
135°	515.7	516.6	517.5	518.3	519.1	519.5	519.4	519.2	519.1	518.9	518.3
137.5°	549.0	549.7	550.4	551.1	551.8	552.3	552.7	553.1	553.5	553.8	553.2
140°	572.0	572.7	573.4	574.1	574.8	575.2	575.4	575.5	575.7	575.8	575.7
142.5°	593.0	593.7	594.3	595.0	595.7	596.2	596.5	596.8	597.0	597.3	597.1
145°	625.7	625.9	626.2	626.5	626.8	627.2	627.6	628.0	628.4	628.9	628.7
147.5°	654.3	654.8	655.3	655.8	656.3	656.8	657.2	657.5	658.0	658.4	658.4
150°	674.2	674.5	674.8	675.1	675.4	675.6	675.9	676.2	676.5	676.7	676.7
152.5°	690.6	691.0	691.4	691.8	692.2	692.4	692.6	692.8	692.9	693.1	693.4
155°	716.4	716.4	716.4	716.4	716.4	716.4	716.6	716.8	716.9	717.0	717.6
157.5°	738.4	738.2	738.0	737.9	737.7	737.7	737.8	737.9	738.0	738.1	738.7
160°	752.2	751.9	751.7	751.3	751.1	750.9	750.9	750.9	750.9	750.9	751.7
162.5°	764.5	764.1	763.6	763.3	762.8	762.8	762.8	762.9	763.1	763.2	763.9
165°	780.3	779.9	779.5	779.0	778.6	778.3	778.3	778.3	778.3	778.3	779.2
167.5°	793.0	792.4	791.9	791.3	790.7	790.5	790.6	790.7	790.8	790.9	791.8
170°	800.1	799.5	799.0	798.4	797.8	797.5	797.5	797.5	797.5	797.5	798.6
172.5°	805.7	805.2	804.6	804.0	803.5	803.1	803.1	803.1	803.1	803.1	804.1
175°	811.6	811.1	810.5	809.9	809.3	809.1	809.1	809.1	809.1	809.1	809.9
177.5°	814.1	813.6	813.1	812.7	812.3	812.0	812.0	812.0	812.0	812.0	812.7
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6



TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	767.1	767.1	767.1	767.1	767.1	767.1	767.1	767.1
2.5°	764.1	765.3	766.5	767.0	766.9	766.7	766.6	766.5
5°	760.1	761.6	763.0	763.6	763.3	763.0	762.8	762.4
7.5°	752.0	753.3	754.7	755.2	755.0	754.8	754.7	754.5
10°	744.6	746.0	747.3	747.8	747.5	747.2	746.9	746.6
12.5°	736.5	737.5	738.5	738.8	738.7	738.5	738.3	738.1
15°	721.9	723.1	724.3	724.4	723.5	722.6	721.8	720.9
17.5°	703.4	704.2	705.1	705.2	705.0	704.6	704.3	704.0
20°	689.7	690.3	690.9	691.0	690.5	690.1	689.7	689.2
22.5°	675.3	675.7	676.2	676.1	675.6	675.0	674.5	673.9
25°	651.3	651.4	651.5	651.4	651.0	650.6	650.1	649.6
27.5°	625.8	625.9	625.9	625.8	625.2	624.7	624.1	623.5
30°	608.1	608.1	608.1	607.6	606.6	605.5	604.5	603.5
32.5°	589.6	588.8	587.9	587.2	586.7	586.2	585.6	585.0
35°	559.5	558.6	557.8	557.0	556.2	555.5	554.7	554.1
37.5°	528.4	527.4	526.3	525.6	525.1	524.6	524.2	523.7
40°	508.2	507.0	505.8	504.9	504.3	503.8	503.2	502.6
42.5°	487.1	485.9	484.7	483.8	483.2	482.7	482.1	481.5
45°	455.6	453.7	452.0	450.7	450.0	449.3	448.6	447.8
47.5°	422.3	420.6	418.9	417.7	417.1	416.4	415.8	415.1
50°	400.5	398.8	397.2	396.0	395.0	394.2	393.3	392.4
52.5°	378.2	376.9	375.5	374.3	373.4	372.6	371.7	370.8
55°	344.3	342.8	341.1	339.9	339.2	338.5	337.8	337.0
57.5°	311.1	309.6	308.2	307.0	306.2	305.4	304.5	303.7
60°	287.6	286.3	284.9	283.9	283.2	282.4	281.7	280.9
62.5°	264.8	263.6	262.3	261.3	260.8	260.4	259.8	259.3
65°	231.1	230.0	228.8	228.0	227.6	227.1	226.7	226.2
67.5°	197.7	196.7	195.6	194.8	194.2	193.6	193.0	192.3
70°	176.0	175.0	174.0	173.1	172.4	171.6	170.9	170.1
72.5°	154.1	153.2	152.3	151.6	151.3	150.8	150.5	150.1
75°	122.5	121.8	121.1	120.5	120.0	119.6	119.2	118.7
77.5°	93.1	92.6	92.0	91.8	91.8	91.8	91.8	91.8
80°	74.2	74.0	74.0	73.9	73.9	73.9	73.9	73.9
82.5°	57.1	56.8	56.6	56.4	56.3	56.1	56.1	56.0
85°	32.4	32.1	31.8	31.7	31.7	31.7	31.7	31.7
87.5°	14.6	14.6	14.6	14.7	14.7	14.8	14.9	14.9
90°	16.4	17.0	17.7	18.0	18.3	18.6	18.9	19.2
92.5°	25.5	25.9	26.3	26.5	26.3	26.2	26.0	25.8
95°	48.4	49.0	49.6	49.9	49.9	49.9	49.9	49.9
97.5°	75.3	75.9	76.6	76.9	76.9	76.8	76.7	76.7
100°	94.8	95.2	95.7	96.0	96.3	96.6	96.9	97.1
102.5°	117.3	117.7	118.1	118.3	118.3	118.2	118.1	118.1
105°	150.8	150.8	150.8	150.9	151.3	151.5	151.8	152.1
107.5°	187.1	187.6	188.0	188.2	188.0	187.9	187.7	187.5
110°	211.4	212.0	212.5	212.7	212.4	212.1	211.8	211.5



TEST NUMBER: P332131-935

CATALOG NUMBER: S123DIW-S560D755U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	235.7	236.3	237.0	237.3	237.3	237.2	237.1	237.1
115°	272.5	272.7	272.9	272.9	272.7	272.5	272.4	272.2
117.5°	309.8	309.7	309.7	309.5	309.1	308.7	308.3	307.9
120°	334.6	334.4	334.3	334.1	333.8	333.6	333.2	332.9
122.5°	359.7	359.3	359.0	358.6	358.2	357.7	357.4	357.0
125°	397.0	396.4	395.9	395.3	394.8	394.2	393.6	393.0
127.5°	433.9	433.1	432.3	431.5	430.9	430.2	429.6	429.0
130°	458.4	457.8	457.2	456.4	455.5	454.4	453.5	452.5
132.5°	482.2	481.5	480.8	480.1	479.3	478.5	477.8	477.0
135°	517.8	517.2	516.7	516.3	515.9	515.7	515.4	515.1
137.5°	552.6	552.0	551.5	550.9	550.4	549.7	549.2	548.7
140°	575.5	575.4	575.2	574.6	573.7	572.7	571.7	570.7
142.5°	597.0	596.8	596.7	596.2	595.5	594.7	593.9	593.1
145°	628.5	628.4	628.3	627.9	627.3	626.8	626.2	625.7
147.5°	658.4	658.4	658.4	658.0	657.1	656.3	655.4	654.5
150°	676.7	676.7	676.7	676.3	675.5	674.7	673.8	673.0
152.5°	693.6	693.8	694.1	693.8	693.0	692.3	691.6	690.9
155°	718.2	718.8	719.3	719.1	718.1	717.1	716.1	715.1
157.5°	739.3	739.9	740.5	740.4	739.6	738.8	738.0	737.2
160°	752.3	753.0	753.7	753.8	753.3	752.7	752.1	751.6
162.5°	764.6	765.3	766.0	765.9	765.0	764.1	763.2	762.2
165°	780.1	780.9	781.8	781.7	780.8	779.7	778.8	777.7
167.5°	792.6	793.6	794.4	794.4	793.6	792.6	791.8	790.9
170°	799.5	800.6	801.5	801.5	800.6	799.5	798.6	797.5
172.5°	804.9	805.8	806.7	806.7	805.6	804.7	803.7	802.7
175°	810.8	811.6	812.4	812.4	811.4	810.4	809.4	808.4
177.5°	813.4	814.1	814.8	814.7	813.9	813.0	812.3	811.5
180°	813.6	813.6	813.6	813.6	813.6	813.6	813.6	813.6

(END OF REPORT)