

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332166-935

Luminaire Tested: **S123DIW-S775D1030U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332166-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1030U935-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6281.2 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26
4	73	62	54	48	67	57	50	45	48	43	39	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11286	11286	11286
5°	11339	11182	11261
10°	11262	11086	11154
15°	11131	10961	10981
20°	10977	10781	10791
25°	10772	10568	10546
30°	10544	10331	10253
35°	10307	10081	9950
40°	10058	9805	9653
45°	9785	9552	9319
50°	9512	9239	8982
55°	9154	8916	8646
60°	8792	8540	8269
65°	8474	8130	7875
70°	8003	7660	7320
75°	7311	7049	6750
80°	6595	6316	6261
85°	5780	5570	5348



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	1.6
10°-20°	278.9	4.4
20°-30°	411.9	6.6
30°-40°	481.2	7.7
40°-50°	483.8	7.7
50°-60°	425.0	6.8
60°-70°	316.6	5.0
70°-80°	180.4	2.9
80°-90°	55.0	0.9
90°-100°	42.3	0.7
100°-110°	201.7	3.2
110°-120°	484.5	7.7
120°-130°	616.9	9.8
130°-140°	659.2	10.5
140°-150°	616.4	9.8
150°-160°	497.2	7.9
160°-170°	320.9	5.1
170°-180°	110.6	1.8
0°-30°	789.6	12.6
0°-40°	1270.8	20.2
0°-60°	2179.5	34.7
0°-90°	2731.5	43.5
90°-120°	728.5	11.6
90°-150°	2621.0	41.7
90°-180°	3550.0	56.5
0°-180°	6281.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1048	1048	1048	1048	1048	
5°	1049	1045	1035	1043	1042	99
15°	999	995	984	990	985	281
25°	907	901	890	890	888	418
35°	784	779	767	762	757	490
45°	643	639	628	617	612	496
55°	488	486	475	466	461	437
65°	333	328	319	312	309	328
75°	176	172	170	165	162	188
85°	47	45	45	43	43	51
90°	1	10	21	24	26	5
95°	53	20	27	33	33	65
105°	258	262	189	45	38	273
115°	484	489	496	505	508	477
125°	682	688	692	694	695	608
135°	848	853	857	859	857	653
145°	979	985	987	988	988	613
155°	1078	1077	1078	1081	1077	497
165°	1137	1135	1134	1140	1135	321
175°	1164	1160	1160	1166	1160	111
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1052.1	1051.5	1050.9	1050.2	1049.6	1048.4	1046.5	1044.8	1043.0	1041.3	1042.8
5°	1049.4	1048.4	1047.4	1046.4	1045.3	1043.8	1041.6	1039.4	1037.2	1034.9	1037.0
7.5°	1039.1	1038.1	1037.1	1036.1	1035.1	1033.5	1031.1	1028.9	1026.6	1024.3	1026.1
10°	1030.4	1029.4	1028.5	1027.4	1026.5	1024.7	1022.0	1019.4	1016.8	1014.3	1016.1
12.5°	1018.9	1018.0	1017.3	1016.4	1015.5	1013.9	1011.5	1009.0	1006.6	1004.1	1005.5
15°	998.9	998.1	997.3	996.5	995.7	994.0	991.4	988.8	986.2	983.6	985.2
17.5°	975.6	974.6	973.5	972.5	971.5	969.7	967.1	964.4	961.8	959.2	960.4
20°	958.3	957.1	956.0	954.8	953.6	951.6	949.0	946.4	943.8	941.2	942.0
22.5°	938.8	937.6	936.4	935.2	934.0	932.1	929.5	927.0	924.4	921.7	922.4
25°	907.0	905.8	904.6	903.4	902.2	900.3	897.6	895.0	892.4	889.8	890.0
27.5°	872.9	871.7	870.6	869.4	868.2	866.3	863.4	860.7	857.8	855.0	855.1
30°	848.3	847.3	846.4	845.3	844.3	842.4	839.6	836.8	834.1	831.2	831.2
32.5°	823.8	822.5	821.1	819.8	818.6	816.8	814.6	812.4	810.3	808.1	807.0
35°	784.4	783.2	782.0	780.8	779.5	777.7	775.0	772.4	769.8	767.2	766.0
37.5°	743.9	742.4	740.9	739.3	737.9	735.8	733.1	730.5	727.8	725.2	723.8
40°	715.8	714.6	713.4	712.2	711.0	709.0	706.2	703.4	700.6	697.8	696.2
42.5°	687.7	686.3	684.9	683.6	682.3	680.2	677.3	674.5	671.8	668.9	667.4
45°	642.8	642.0	641.2	640.4	639.6	637.9	635.2	632.7	630.1	627.5	625.1
47.5°	598.2	597.1	595.9	594.8	593.6	591.8	589.4	586.9	584.4	582.0	579.6
50°	568.0	567.0	565.9	565.0	564.0	562.1	559.6	557.0	554.3	551.7	549.6
52.5°	536.2	535.5	534.9	534.2	533.5	531.8	529.0	526.2	523.5	520.7	518.8
55°	487.8	487.5	487.3	487.2	486.9	485.5	482.9	480.4	477.7	475.1	472.9
57.5°	441.6	440.9	440.2	439.5	438.9	437.5	435.4	433.3	431.2	429.1	427.1
60°	408.4	408.2	408.0	407.8	407.6	406.3	403.9	401.5	399.1	396.7	394.9
62.5°	378.8	378.3	377.8	377.3	376.8	375.3	372.9	370.5	368.1	365.7	363.9
65°	332.7	331.7	330.6	329.7	328.6	327.2	325.1	323.1	321.2	319.2	317.5
67.5°	283.8	282.9	282.1	281.1	280.3	279.1	277.6	276.0	274.5	273.0	271.6
70°	254.3	253.0	251.8	250.6	249.4	248.2	247.0	245.8	244.6	243.4	242.0
72.5°	223.3	222.3	221.4	220.6	219.7	218.6	217.2	215.9	214.5	213.1	211.9
75°	175.8	175.0	174.2	173.4	172.6	171.9	171.3	170.7	170.0	169.5	168.5
77.5°	133.8	133.4	132.9	132.5	132.0	131.5	130.7	130.0	129.3	128.5	127.9
80°	106.4	105.8	105.2	104.6	104.0	103.5	103.1	102.7	102.3	101.9	101.7
82.5°	79.7	79.6	79.5	79.3	79.2	79.1	79.0	79.0	78.9	78.8	78.4
85°	46.8	46.5	46.1	45.7	45.3	45.1	45.1	45.1	45.1	45.1	44.7
87.5°	18.9	18.9	18.8	18.6	18.5	18.7	19.0	19.4	19.7	20.0	20.0
90°	0.9	2.8	4.7	6.6	8.5	10.8	13.3	15.8	18.3	20.8	21.5
92.5°	16.1	15.6	15.0	14.5	13.9	14.6	16.5	18.3	20.2	22.1	23.3
95°	52.8	44.9	37.0	29.1	21.3	18.3	20.5	22.6	24.7	26.8	28.2
97.5°	106.0	102.5	98.9	95.4	91.9	83.2	69.4	55.5	41.7	27.8	29.4
100°	146.1	150.0	153.9	157.6	161.5	148.4	118.5	88.5	58.5	28.5	30.0
102.5°	191.8	194.6	197.3	200.1	202.9	187.9	155.2	122.4	89.6	56.9	52.2
105°	257.7	259.8	261.9	264.1	266.1	258.6	241.3	223.9	206.7	189.4	155.4
107.5°	327.3	328.9	330.6	332.3	334.0	336.2	339.0	341.6	344.4	347.2	322.2
110°	373.6	375.1	376.7	378.2	379.7	381.6	383.7	385.8	387.9	390.0	383.7



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	417.8	419.2	420.6	422.1	423.4	425.2	427.2	429.4	431.5	433.6	433.7
115°	483.5	484.6	485.7	486.9	488.0	489.5	491.2	492.9	494.6	496.4	498.3
117.5°	546.9	548.3	549.7	551.1	552.6	553.7	554.7	555.5	556.4	557.2	558.8
120°	586.3	588.1	589.8	591.5	593.2	594.4	595.0	595.6	596.2	596.7	598.2
122.5°	626.5	627.8	629.3	630.7	632.1	633.2	634.0	634.6	635.4	636.1	637.2
125°	681.5	683.0	684.5	686.0	687.6	688.8	689.5	690.3	691.0	691.8	692.2
127.5°	734.7	736.2	737.8	739.3	740.9	742.1	743.0	744.0	744.9	745.8	746.4
130°	767.9	769.5	771.0	772.6	774.1	775.2	776.0	776.8	777.6	778.3	779.1
132.5°	799.8	801.3	802.8	804.3	805.9	807.0	807.6	808.2	808.8	809.4	810.2
135°	848.3	849.5	850.7	851.8	853.0	853.9	854.7	855.5	856.3	857.0	857.6
137.5°	889.8	891.3	892.8	894.2	895.7	896.6	897.1	897.5	897.9	898.4	899.2
140°	917.6	918.7	919.9	921.0	922.1	923.0	923.6	924.2	924.7	925.3	926.1
142.5°	943.1	944.3	945.5	946.6	947.8	948.6	949.2	949.8	950.4	950.9	951.6
145°	979.0	980.2	981.6	983.0	984.3	985.2	985.6	985.9	986.4	986.7	987.1
147.5°	1012.7	1013.6	1014.4	1015.3	1016.2	1016.8	1017.2	1017.6	1018.0	1018.4	1018.7
150°	1033.5	1034.0	1034.6	1035.2	1035.7	1036.2	1036.6	1037.0	1037.3	1037.8	1038.1
152.5°	1052.1	1052.4	1052.7	1052.9	1053.2	1053.4	1053.7	1053.9	1054.1	1054.4	1055.1
155°	1078.4	1078.0	1077.6	1077.3	1076.9	1076.8	1076.9	1077.1	1077.4	1077.5	1078.5
157.5°	1098.8	1098.8	1098.7	1098.7	1098.6	1098.5	1098.4	1098.1	1097.9	1097.8	1098.9
160°	1111.3	1111.0	1110.9	1110.7	1110.5	1110.3	1110.1	1109.9	1109.7	1109.6	1110.7
162.5°	1123.0	1122.5	1122.1	1121.5	1121.0	1120.7	1120.5	1120.3	1120.1	1119.9	1121.2
165°	1137.2	1136.6	1136.1	1135.5	1134.9	1134.5	1134.3	1134.1	1133.9	1133.8	1135.3
167.5°	1148.2	1147.5	1146.8	1146.0	1145.2	1144.8	1144.8	1144.8	1144.8	1144.8	1146.3
170°	1154.5	1153.7	1153.0	1152.2	1151.4	1151.1	1151.1	1151.1	1151.1	1151.1	1152.5
172.5°	1158.6	1157.7	1156.8	1155.9	1154.9	1154.6	1154.7	1154.9	1155.0	1155.2	1156.8
175°	1164.0	1163.0	1162.1	1161.1	1160.2	1159.8	1159.9	1160.2	1160.4	1160.5	1161.9
177.5°	1165.4	1164.6	1163.9	1163.1	1162.4	1162.0	1162.2	1162.4	1162.4	1162.6	1163.9
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5	1048.5
2.5°	1044.5	1046.1	1047.7	1048.4	1048.3	1048.1	1047.9	1047.8
5°	1039.0	1040.9	1043.0	1043.8	1043.4	1043.0	1042.6	1042.2
7.5°	1027.9	1029.8	1031.6	1032.3	1032.1	1031.8	1031.6	1031.4
10°	1017.9	1019.6	1021.4	1022.2	1021.7	1021.3	1021.0	1020.5
12.5°	1006.8	1008.1	1009.4	1010.0	1009.7	1009.4	1009.3	1009.0
15°	986.8	988.3	990.0	990.2	988.9	987.7	986.6	985.4
17.5°	961.5	962.6	963.7	964.1	963.6	963.2	962.8	962.3
20°	942.8	943.6	944.4	944.5	943.9	943.3	942.7	942.1
22.5°	923.0	923.7	924.3	924.2	923.5	922.7	922.0	921.2
25°	890.2	890.4	890.6	890.4	889.8	889.2	888.6	888.0
27.5°	855.3	855.5	855.7	855.3	854.6	853.9	853.1	852.3
30°	831.2	831.2	831.2	830.5	829.1	827.7	826.3	824.9
32.5°	805.9	804.8	803.7	802.7	801.9	801.2	800.4	799.7
35°	764.8	763.6	762.4	761.3	760.3	759.3	758.3	757.2
37.5°	722.3	720.8	719.5	718.4	717.7	717.1	716.4	715.8
40°	694.6	693.0	691.4	690.2	689.4	688.5	687.8	687.0
42.5°	665.7	664.1	662.5	661.3	660.6	659.7	658.9	658.1
45°	622.7	620.3	617.9	616.1	615.2	614.2	613.1	612.2
47.5°	577.3	575.0	572.6	570.9	570.1	569.2	568.3	567.4
50°	547.3	545.1	542.9	541.2	540.0	538.8	537.6	536.4
52.5°	516.9	515.1	513.2	511.7	510.5	509.3	508.1	506.9
55°	470.7	468.5	466.3	464.7	463.6	462.7	461.7	460.7
57.5°	425.2	423.3	421.3	419.7	418.5	417.4	416.2	415.1
60°	393.0	391.2	389.4	388.1	387.0	386.1	385.0	384.1
62.5°	362.1	360.2	358.4	357.2	356.5	355.9	355.2	354.5
65°	315.9	314.4	312.7	311.6	311.0	310.4	309.8	309.2
67.5°	270.2	268.8	267.3	266.2	265.4	264.6	263.7	262.9
70°	240.6	239.2	237.8	236.6	235.6	234.6	233.6	232.6
72.5°	210.6	209.4	208.2	207.2	206.7	206.2	205.7	205.2
75°	167.5	166.5	165.5	164.7	164.1	163.5	162.9	162.3
77.5°	127.2	126.5	125.8	125.5	125.5	125.5	125.5	125.5
80°	101.5	101.3	101.1	101.0	101.0	101.0	101.0	101.0
82.5°	78.1	77.7	77.3	77.1	77.0	76.8	76.6	76.5
85°	44.3	43.9	43.5	43.3	43.3	43.3	43.3	43.3
87.5°	20.0	20.0	20.0	20.1	20.1	20.1	20.2	20.3
90°	22.3	23.1	23.8	24.4	24.8	25.1	25.6	25.9
92.5°	24.6	25.8	27.0	27.8	28.0	28.2	28.5	28.7
95°	29.5	30.8	32.2	32.9	32.9	32.9	32.9	32.9
97.5°	30.9	32.5	34.0	34.9	35.0	35.2	35.5	35.6
100°	31.6	33.1	34.7	35.6	35.7	35.9	36.2	36.3
102.5°	47.4	42.6	37.8	35.6	36.0	36.3	36.7	37.0
105°	121.4	87.3	53.3	36.5	36.9	37.3	37.6	38.1
107.5°	297.2	272.3	247.4	222.1	196.4	170.8	145.2	119.5
110°	377.4	371.0	364.6	347.8	320.3	292.7	265.3	237.8



TEST NUMBER: P332166-935

CATALOG NUMBER: S123DIW-S775D1030U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	433.9	433.9	434.0	431.2	425.4	419.7	413.8	408.0
115°	500.2	502.1	504.1	505.4	506.2	507.0	507.7	508.5
117.5°	560.3	561.9	563.4	564.3	564.4	564.6	564.7	564.9
120°	599.8	601.3	602.9	603.6	603.6	603.6	603.6	603.6
122.5°	638.3	639.4	640.4	641.1	641.2	641.4	641.5	641.7
125°	692.6	693.0	693.4	693.8	694.1	694.5	694.9	695.3
127.5°	747.0	747.6	748.3	748.4	748.0	747.6	747.3	746.8
130°	779.9	780.6	781.4	781.6	781.2	780.8	780.4	780.1
132.5°	811.0	811.8	812.5	812.6	812.1	811.6	811.1	810.5
135°	858.2	858.8	859.3	859.3	858.8	858.2	857.6	857.0
137.5°	900.2	901.1	902.1	902.3	901.9	901.6	901.1	900.8
140°	926.9	927.6	928.4	928.6	928.2	927.8	927.5	927.0
142.5°	952.2	952.8	953.4	953.4	952.9	952.4	951.8	951.2
145°	987.5	987.9	988.3	988.4	988.4	988.4	988.4	988.4
147.5°	1019.2	1019.5	1019.9	1019.7	1018.8	1017.9	1017.0	1016.2
150°	1038.5	1038.9	1039.3	1039.2	1038.6	1038.0	1037.5	1036.9
152.5°	1055.8	1056.4	1057.1	1057.0	1056.1	1055.2	1054.4	1053.5
155°	1079.4	1080.4	1081.4	1081.2	1080.1	1079.0	1077.8	1076.7
157.5°	1100.1	1101.2	1102.3	1102.2	1100.7	1099.2	1097.7	1096.2
160°	1111.8	1113.0	1114.1	1114.0	1112.7	1111.4	1110.0	1108.6
162.5°	1122.5	1123.9	1125.2	1125.2	1124.0	1122.8	1121.6	1120.4
165°	1136.8	1138.3	1139.9	1140.0	1138.7	1137.3	1135.9	1134.6
167.5°	1147.9	1149.4	1151.0	1151.0	1149.4	1147.9	1146.3	1144.8
170°	1154.1	1155.6	1157.2	1157.2	1155.6	1154.1	1152.5	1151.1
172.5°	1158.3	1159.8	1161.3	1161.2	1159.6	1157.9	1156.2	1154.5
175°	1163.2	1164.6	1166.0	1165.9	1164.3	1162.8	1161.2	1159.7
177.5°	1165.1	1166.3	1167.5	1167.4	1165.9	1164.3	1162.8	1161.2
180°	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0	1164.0

(END OF REPORT)