

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332131-830

Luminaire Tested: **S123DIW-S560D755U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332131-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D755U830-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4655.1 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33
3	81	71	64	58	74	66	59	54	55	50	46	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	14
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	25	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9038	9038	9038
5°	9081	8956	9018
10°	9021	8878	8933
15°	8914	8778	8795
20°	8791	8635	8643
25°	8626	8464	8445
30°	8444	8274	8211
35°	8253	8073	7970
40°	8056	7852	7731
45°	7837	7649	7462
50°	7618	7400	7194
55°	7330	7141	6923
60°	7042	6837	6622
65°	6788	6510	6306
70°	6408	6134	5860
75°	5856	5644	5407
80°	5281	5058	5015
85°	4631	4458	4286



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.7
10°-20°	223.3	4.8
20°-30°	329.9	7.1
30°-40°	385.4	8.3
40°-50°	387.4	8.3
50°-60°	340.3	7.3
60°-70°	253.5	5.4
70°-80°	144.5	3.1
80°-90°	44.1	0.9
90°-100°	58.0	1.2
100°-110°	173.6	3.7
110°-120°	295.3	6.3
120°-130°	388.5	8.3
130°-140°	436.7	9.4
140°-150°	429.2	9.2
150°-160°	361.3	7.8
160°-170°	240.5	5.2
170°-180°	84.2	1.8
0°-30°	632.3	13.6
0°-40°	1017.7	21.9
0°-60°	1745.5	37.5
0°-90°	2187.6	47.0
90°-120°	527.0	11.3
90°-150°	1781.4	38.3
90°-180°	2468.0	53.0
0°-180°	4655.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	840	840	840	840	840	
5°	840	837	829	836	835	80
15°	800	797	788	793	789	225
25°	726	722	713	713	711	334
35°	628	624	614	610	606	393
45°	515	512	502	494	490	397
55°	391	389	380	373	369	350
65°	266	263	256	250	248	263
75°	141	138	136	132	130	151
85°	38	36	36	35	35	41
90°	1	8	17	20	21	5
95°	41	46	52	54	55	46
105°	157	159	165	165	166	169
115°	297	299	298	299	298	294
125°	435	437	436	433	430	388
135°	565	568	568	565	564	435
145°	685	686	688	688	685	428
155°	784	784	785	787	783	361
165°	854	852	852	856	851	241
175°	888	886	886	889	885	84
180°	891	891	891	891	891	



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	842.5	842.1	841.6	841.0	840.6	839.5	838.1	836.7	835.4	834.0	835.2
5°	840.4	839.6	838.8	838.0	837.2	835.9	834.2	832.4	830.7	828.9	830.5
7.5°	832.2	831.4	830.6	829.8	829.0	827.6	825.9	824.0	822.2	820.4	821.8
10°	825.3	824.4	823.7	822.8	822.1	820.6	818.5	816.4	814.4	812.3	813.7
12.5°	816.1	815.3	814.6	814.0	813.3	812.0	810.0	808.0	806.2	804.2	805.2
15°	799.9	799.4	798.7	798.1	797.4	796.1	794.0	791.9	789.8	787.7	789.0
17.5°	781.4	780.5	779.7	778.8	778.0	776.6	774.5	772.4	770.3	768.2	769.1
20°	767.5	766.6	765.5	764.6	763.6	762.1	760.1	758.0	755.8	753.8	754.4
22.5°	751.9	750.9	750.0	749.0	748.0	746.5	744.4	742.3	740.3	738.2	738.7
25°	726.3	725.4	724.4	723.5	722.5	721.0	718.9	716.8	714.7	712.7	712.8
27.5°	699.1	698.1	697.2	696.3	695.3	693.7	691.4	689.3	687.0	684.8	684.9
30°	679.4	678.6	677.8	677.0	676.2	674.7	672.4	670.1	668.0	665.7	665.7
32.5°	659.8	658.7	657.6	656.6	655.5	654.1	652.4	650.6	648.9	647.2	646.3
35°	628.1	627.2	626.2	625.3	624.3	622.7	620.7	618.6	616.5	614.4	613.5
37.5°	595.8	594.6	593.3	592.1	590.9	589.3	587.1	585.0	582.9	580.8	579.7
40°	573.3	572.3	571.4	570.4	569.4	567.8	565.5	563.4	561.1	558.8	557.5
42.5°	550.7	549.7	548.6	547.4	546.4	544.7	542.4	540.3	538.0	535.7	534.4
45°	514.8	514.2	513.5	512.8	512.2	510.9	508.8	506.7	504.6	502.5	500.6
47.5°	479.1	478.2	477.3	476.4	475.4	473.9	472.0	470.0	468.1	466.1	464.2
50°	454.9	454.0	453.3	452.4	451.7	450.3	448.1	446.0	443.9	441.9	440.1
52.5°	429.4	428.9	428.4	427.8	427.3	425.8	423.7	421.5	419.2	417.1	415.6
55°	390.6	390.4	390.3	390.1	389.9	388.8	386.7	384.7	382.6	380.5	378.7
57.5°	353.6	353.1	352.5	352.0	351.5	350.3	348.6	347.0	345.3	343.7	342.1
60°	327.1	326.9	326.8	326.6	326.4	325.4	323.5	321.5	319.6	317.6	316.2
62.5°	303.4	302.9	302.6	302.2	301.7	300.6	298.6	296.7	294.7	292.8	291.4
65°	266.5	265.6	264.9	264.0	263.3	262.0	260.4	258.8	257.2	255.6	254.3
67.5°	227.2	226.6	225.8	225.2	224.4	223.5	222.3	221.0	219.8	218.7	217.5
70°	203.6	202.6	201.7	200.8	199.7	198.8	197.8	196.9	195.9	194.9	193.8
72.5°	178.8	178.0	177.4	176.6	176.0	175.0	174.0	172.9	171.7	170.7	169.7
75°	140.8	140.2	139.5	138.8	138.3	137.7	137.1	136.7	136.2	135.7	135.0
77.5°	107.2	106.8	106.4	106.1	105.8	105.3	104.7	104.2	103.5	102.9	102.5
80°	85.2	84.7	84.3	83.8	83.2	82.8	82.6	82.2	81.9	81.6	81.4
82.5°	63.8	63.7	63.6	63.5	63.4	63.3	63.3	63.2	63.2	63.2	62.8
85°	37.5	37.2	36.9	36.6	36.3	36.1	36.1	36.1	36.1	36.1	35.8
87.5°	15.2	15.1	15.0	14.9	14.9	15.0	15.3	15.6	15.8	16.0	16.0
90°	0.7	2.3	3.8	5.4	6.9	8.7	10.7	12.7	14.8	16.8	17.4
92.5°	17.0	18.0	19.0	20.1	21.1	22.2	23.4	24.6	25.7	26.9	27.3
95°	41.3	42.3	43.5	44.6	45.6	46.8	48.1	49.3	50.5	51.7	52.4
97.5°	73.3	74.1	74.9	75.8	76.5	77.4	78.3	79.2	80.1	81.1	81.7
100°	95.1	96.0	97.0	97.9	98.9	99.7	100.5	101.3	102.1	102.8	103.3
102.5°	120.4	120.9	121.5	122.0	122.5	123.4	124.4	125.5	126.4	127.4	127.9
105°	157.4	157.7	158.1	158.3	158.6	159.5	160.9	162.3	163.7	165.1	165.1
107.5°	200.5	200.7	200.9	201.0	201.2	201.6	202.2	202.7	203.3	203.9	204.3
110°	227.3	227.7	228.0	228.3	228.6	228.9	229.2	229.5	229.9	230.2	230.8



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	255.3	255.5	255.7	255.9	256.1	256.2	256.3	256.4	256.4	256.5	257.2
115°	297.4	297.7	298.2	298.7	299.2	299.3	299.0	298.7	298.3	298.0	298.2
117.5°	339.6	339.9	340.2	340.5	340.8	340.8	340.4	340.0	339.6	339.1	339.1
120°	365.9	366.8	367.8	368.7	369.7	369.7	368.9	368.2	367.4	366.6	366.5
122.5°	393.3	394.0	394.6	395.4	396.1	396.2	395.8	395.4	395.0	394.5	394.2
125°	435.2	435.6	436.1	436.6	437.1	437.1	436.8	436.5	436.1	435.8	435.3
127.5°	473.7	474.8	475.8	476.7	477.8	478.1	477.8	477.4	477.0	476.7	475.8
130°	499.5	500.8	502.0	503.2	504.4	504.9	504.4	504.0	503.5	503.0	502.4
132.5°	525.3	526.5	527.7	529.0	530.3	530.7	530.4	530.0	529.6	529.3	528.6
135°	564.6	565.5	566.5	567.4	568.3	568.7	568.5	568.4	568.3	568.1	567.4
137.5°	601.0	601.7	602.5	603.3	604.1	604.6	605.0	605.5	605.9	606.2	605.6
140°	626.1	626.9	627.7	628.5	629.2	629.7	629.9	630.0	630.2	630.4	630.2
142.5°	649.1	649.9	650.6	651.4	652.1	652.7	653.0	653.3	653.6	653.8	653.7
145°	684.9	685.2	685.5	685.8	686.2	686.5	687.0	687.5	688.0	688.4	688.2
147.5°	716.2	716.8	717.4	717.9	718.5	719.0	719.4	719.8	720.3	720.8	720.8
150°	738.1	738.4	738.7	739.0	739.3	739.6	739.9	740.3	740.6	740.8	740.8
152.5°	756.0	756.4	756.9	757.3	757.7	758.0	758.2	758.4	758.6	758.7	759.0
155°	784.3	784.3	784.3	784.3	784.3	784.3	784.5	784.7	784.8	784.9	785.6
157.5°	808.3	808.1	807.9	807.8	807.6	807.6	807.7	807.8	807.9	808.0	808.7
160°	823.4	823.1	822.8	822.5	822.2	822.0	822.0	822.0	822.0	822.0	822.8
162.5°	836.9	836.4	835.9	835.6	835.1	835.0	835.1	835.2	835.4	835.5	836.2
165°	854.2	853.8	853.3	852.8	852.3	852.1	852.1	852.1	852.1	852.1	853.0
167.5°	868.1	867.4	866.9	866.2	865.5	865.3	865.4	865.5	865.7	865.8	866.8
170°	875.9	875.2	874.7	874.0	873.4	873.1	873.1	873.1	873.1	873.1	874.2
172.5°	882.0	881.5	880.8	880.1	879.6	879.2	879.2	879.2	879.2	879.2	880.2
175°	888.4	887.9	887.2	886.6	886.0	885.7	885.7	885.7	885.7	885.7	886.6
177.5°	891.2	890.6	890.1	889.7	889.2	888.9	888.9	888.9	888.9	888.9	889.7
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	839.7	839.7	839.7	839.7	839.7	839.7	839.7	839.7
2.5°	836.5	837.7	839.1	839.6	839.5	839.3	839.2	839.1
5°	832.1	833.7	835.3	835.9	835.6	835.3	835.0	834.6
7.5°	823.2	824.6	826.1	826.7	826.5	826.3	826.1	826.0
10°	815.1	816.6	818.0	818.6	818.3	817.9	817.7	817.3
12.5°	806.3	807.4	808.4	808.8	808.6	808.4	808.2	808.0
15°	790.3	791.5	792.9	793.0	792.0	791.1	790.1	789.2
17.5°	770.1	770.9	771.8	772.0	771.8	771.4	771.0	770.6
20°	755.1	755.7	756.3	756.4	755.9	755.4	755.0	754.5
22.5°	739.2	739.7	740.3	740.2	739.6	739.0	738.4	737.7
25°	712.9	713.1	713.2	713.1	712.7	712.2	711.6	711.1
27.5°	685.0	685.1	685.2	685.0	684.4	683.8	683.2	682.6
30°	665.7	665.7	665.7	665.2	664.0	662.9	661.8	660.6
32.5°	645.5	644.5	643.6	642.8	642.2	641.7	641.0	640.5
35°	612.5	611.5	610.6	609.7	608.9	608.1	607.3	606.5
37.5°	578.4	577.3	576.2	575.3	574.9	574.3	573.8	573.3
40°	556.3	555.0	553.7	552.7	552.0	551.5	550.8	550.2
42.5°	533.2	531.9	530.6	529.6	529.0	528.4	527.7	527.1
45°	498.7	496.7	494.8	493.4	492.7	491.8	491.1	490.2
47.5°	462.3	460.4	458.5	457.2	456.6	455.8	455.2	454.4
50°	438.4	436.6	434.8	433.5	432.4	431.5	430.6	429.6
52.5°	414.1	412.6	411.0	409.7	408.8	407.8	406.9	406.0
55°	376.9	375.2	373.4	372.1	371.4	370.5	369.8	368.9
57.5°	340.5	338.9	337.4	336.1	335.2	334.3	333.4	332.4
60°	314.8	313.4	311.9	310.8	310.0	309.2	308.4	307.6
62.5°	289.9	288.5	287.1	286.1	285.5	285.0	284.5	283.9
65°	253.0	251.8	250.4	249.6	249.1	248.6	248.2	247.6
67.5°	216.4	215.3	214.1	213.2	212.5	211.9	211.2	210.6
70°	192.7	191.6	190.5	189.5	188.7	187.8	187.1	186.2
72.5°	168.7	167.7	166.7	166.0	165.6	165.1	164.8	164.3
75°	134.1	133.4	132.5	131.9	131.4	130.9	130.4	130.0
77.5°	101.9	101.3	100.8	100.5	100.5	100.5	100.5	100.5
80°	81.2	81.1	81.0	80.9	80.9	80.9	80.9	80.9
82.5°	62.5	62.2	61.9	61.7	61.6	61.5	61.4	61.3
85°	35.4	35.2	34.8	34.7	34.7	34.7	34.7	34.7
87.5°	16.0	16.0	16.0	16.1	16.1	16.2	16.3	16.3
90°	18.0	18.7	19.3	19.7	20.1	20.4	20.6	21.0
92.5°	27.9	28.4	28.8	29.0	28.8	28.7	28.5	28.3
95°	53.0	53.6	54.3	54.6	54.6	54.6	54.6	54.6
97.5°	82.5	83.1	83.9	84.2	84.2	84.1	84.0	84.0
100°	103.8	104.2	104.7	105.1	105.4	105.8	106.0	106.3
102.5°	128.4	128.8	129.3	129.5	129.5	129.4	129.3	129.3
105°	165.1	165.1	165.1	165.2	165.6	165.9	166.2	166.5
107.5°	204.8	205.4	205.9	206.0	205.9	205.7	205.5	205.3
110°	231.4	232.1	232.6	232.8	232.5	232.1	231.9	231.6



TEST NUMBER: P332131-830

CATALOG NUMBER: S123DIW-S560D755U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	258.0	258.7	259.5	259.8	259.8	259.7	259.6	259.6
115°	298.3	298.5	298.7	298.7	298.5	298.3	298.2	298.0
117.5°	339.1	339.0	339.0	338.8	338.4	337.9	337.5	337.1
120°	366.3	366.1	366.0	365.7	365.4	365.1	364.8	364.5
122.5°	393.8	393.3	392.9	392.6	392.1	391.6	391.2	390.8
125°	434.6	433.9	433.4	432.7	432.2	431.5	430.8	430.3
127.5°	474.9	474.1	473.3	472.4	471.7	471.0	470.3	469.6
130°	501.8	501.1	500.5	499.6	498.6	497.5	496.4	495.3
132.5°	527.8	527.1	526.3	525.6	524.7	523.9	523.0	522.2
135°	566.8	566.2	565.6	565.1	564.8	564.5	564.2	563.8
137.5°	604.9	604.3	603.7	603.0	602.5	601.8	601.2	600.7
140°	630.0	629.9	629.7	629.1	628.0	626.9	625.8	624.7
142.5°	653.6	653.4	653.2	652.7	651.9	651.0	650.2	649.3
145°	688.1	688.0	687.8	687.4	686.7	686.2	685.5	684.9
147.5°	720.8	720.8	720.8	720.3	719.3	718.4	717.5	716.5
150°	740.8	740.8	740.8	740.4	739.4	738.6	737.6	736.7
152.5°	759.3	759.5	759.8	759.5	758.7	757.9	757.1	756.3
155°	786.2	786.8	787.4	787.2	786.1	785.0	783.9	782.9
157.5°	809.4	810.0	810.7	810.5	809.6	808.8	807.9	807.0
160°	823.6	824.3	825.1	825.2	824.6	824.0	823.3	822.7
162.5°	837.0	837.8	838.6	838.5	837.4	836.5	835.5	834.4
165°	853.9	854.9	855.8	855.7	854.7	853.6	852.5	851.4
167.5°	867.7	868.7	869.7	869.7	868.7	867.7	866.8	865.8
170°	875.2	876.4	877.4	877.4	876.4	875.2	874.2	873.1
172.5°	881.2	882.1	883.1	883.1	881.9	880.9	879.8	878.7
175°	887.6	888.4	889.4	889.4	888.3	887.1	886.1	885.0
177.5°	890.4	891.2	891.9	891.8	891.0	890.0	889.2	888.3
180°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6

(END OF REPORT)