

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332167-830

Luminaire Tested: **S123DIW-S775D1030U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332167-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1030U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6358.2 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47						47														
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45	39						39														
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38	33						33														
3	81	71	64	58	74	66	59	54	55	50	46	46	42	39	37	34	32	28						28														
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24						24														
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21						21														
6	62	50	42	36	57	46	39	34	39	34	30	33	29	25	27	24	21	18						18														
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16						16														
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	14						14														
9	50	37	30	25	46	35	28	24	30	24	21	25	21	18	21	18	15	13						13														
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14	12						12														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	1.7
10°-20°	305.3	4.8
20°-30°	451.0	7.1
30°-40°	526.8	8.3
40°-50°	529.6	8.3
50°-60°	465.2	7.3
60°-70°	346.6	5.5
70°-80°	197.5	3.1
80°-90°	60.3	0.9
90°-100°	79.2	1.2
100°-110°	237.0	3.7
110°-120°	403.1	6.3
120°-130°	530.3	8.3
130°-140°	596.0	9.4
140°-150°	585.8	9.2
150°-160°	493.2	7.8
160°-170°	328.3	5.2
170°-180°	115.0	1.8
0°-30°	864.4	13.6
0°-40°	1391.1	21.9
0°-60°	2385.9	37.5
0°-90°	2990.3	47.0
90°-120°	719.4	11.3
90°-150°	2431.5	38.2
90°-180°	3368.0	53.0
0°-180°	6358.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	11	23	27	29	6
95°	56	63	71	74	74	63
105°	215	217	225	226	227	230
115°	406	408	407	408	407	401
125°	594	597	595	591	587	529
135°	771	776	775	772	770	594
145°	935	937	940	938	935	584
155°	1070	1070	1071	1075	1069	493
165°	1166	1163	1163	1168	1162	329
175°	1213	1209	1209	1214	1208	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.7	20.6	20.5	20.5	20.3	20.5	20.8	21.2	21.6	22.0	22.0
90°	0.9	3.1	5.2	7.4	9.4	11.9	14.6	17.4	20.2	22.9	23.8
92.5°	23.1	24.5	26.0	27.4	28.8	30.3	32.0	33.6	35.1	36.7	37.3
95°	56.4	57.8	59.3	60.8	62.3	63.9	65.6	67.3	69.0	70.7	71.5
97.5°	100.1	101.1	102.3	103.4	104.5	105.7	106.9	108.1	109.3	110.6	111.6
100°	129.9	131.1	132.4	133.7	135.0	136.1	137.2	138.3	139.3	140.3	141.0
102.5°	164.3	165.0	165.8	166.5	167.3	168.3	169.8	171.2	172.6	174.0	174.7
105°	214.9	215.3	215.7	216.1	216.6	217.7	219.6	221.5	223.5	225.4	225.4
107.5°	273.7	273.9	274.2	274.5	274.7	275.2	276.0	276.7	277.5	278.2	278.9
110°	310.4	310.8	311.2	311.6	312.1	312.5	312.9	313.3	313.8	314.1	315.0



TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.6	348.8	349.0	349.3	349.6	349.7	349.8	349.9	350.0	350.1	351.1
115°	405.9	406.4	407.1	407.7	408.4	408.5	408.0	407.6	407.2	406.8	407.0
117.5°	463.5	463.9	464.4	464.8	465.2	465.1	464.6	464.0	463.4	463.0	462.9
120°	499.5	500.7	502.0	503.2	504.5	504.6	503.5	502.5	501.4	500.4	500.1
122.5°	536.9	537.8	538.8	539.6	540.5	540.7	540.3	539.7	539.1	538.6	538.0
125°	594.0	594.6	595.2	595.9	596.5	596.6	596.2	595.8	595.3	594.9	594.1
127.5°	646.7	648.0	649.4	650.7	652.1	652.5	652.1	651.6	651.1	650.6	649.5
130°	681.8	683.5	685.2	686.9	688.6	689.1	688.5	687.9	687.2	686.5	685.7
132.5°	716.9	718.6	720.3	722.1	723.8	724.3	723.9	723.4	722.9	722.5	721.4
135°	770.6	771.8	773.2	774.4	775.7	776.2	776.0	775.8	775.6	775.3	774.5
137.5°	820.3	821.3	822.4	823.4	824.5	825.3	825.9	826.4	827.0	827.6	826.6
140°	854.6	855.7	856.8	857.8	858.8	859.5	859.7	860.0	860.2	860.4	860.2
142.5°	886.0	887.0	888.1	889.1	890.2	890.9	891.3	891.6	892.1	892.5	892.2
145°	934.8	935.3	935.7	936.1	936.5	937.1	937.7	938.4	939.0	939.6	939.4
147.5°	977.6	978.4	979.1	980.0	980.7	981.4	981.9	982.6	983.2	983.7	983.7
150°	1007.4	1007.9	1008.2	1008.7	1009.1	1009.6	1009.9	1010.4	1010.8	1011.3	1011.3
152.5°	1031.9	1032.5	1033.0	1033.7	1034.3	1034.6	1034.9	1035.2	1035.5	1035.7	1036.0
155°	1070.4	1070.4	1070.4	1070.4	1070.4	1070.5	1070.7	1071.0	1071.2	1071.4	1072.2
157.5°	1103.3	1103.1	1102.8	1102.5	1102.3	1102.2	1102.4	1102.6	1102.8	1102.9	1103.8
160°	1123.9	1123.5	1123.0	1122.7	1122.2	1122.0	1122.0	1122.0	1122.0	1122.0	1123.0
162.5°	1142.3	1141.7	1141.0	1140.5	1139.9	1139.6	1139.8	1140.0	1140.2	1140.4	1141.4
165°	1165.9	1165.3	1164.7	1164.0	1163.4	1163.1	1163.1	1163.1	1163.1	1163.1	1164.3
167.5°	1184.9	1184.0	1183.2	1182.3	1181.5	1181.1	1181.3	1181.5	1181.7	1181.8	1183.1
170°	1195.5	1194.7	1193.8	1193.0	1192.1	1191.8	1191.8	1191.8	1191.8	1191.8	1193.2
172.5°	1203.9	1203.1	1202.2	1201.4	1200.5	1200.1	1200.1	1200.1	1200.1	1200.1	1201.5
175°	1212.8	1211.9	1211.1	1210.2	1209.4	1208.9	1208.9	1208.9	1208.9	1208.9	1210.2
177.5°	1216.4	1215.7	1215.0	1214.3	1213.6	1213.3	1213.3	1213.3	1213.3	1213.3	1214.3
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6



TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	22.0	22.0	22.0	22.0	22.1	22.1	22.2	22.3
90°	24.6	25.4	26.3	27.0	27.3	27.8	28.2	28.7
92.5°	38.0	38.7	39.4	39.6	39.3	39.1	38.8	38.5
95°	72.4	73.2	74.1	74.5	74.5	74.5	74.5	74.5
97.5°	112.5	113.5	114.5	114.9	114.8	114.8	114.7	114.6
100°	141.7	142.3	142.9	143.5	143.8	144.3	144.7	145.2
102.5°	175.2	175.9	176.5	176.8	176.7	176.6	176.5	176.4
105°	225.4	225.4	225.4	225.6	226.0	226.4	226.9	227.2
107.5°	279.7	280.3	281.0	281.2	281.0	280.7	280.4	280.1
110°	315.8	316.7	317.5	317.7	317.4	316.9	316.5	316.0





TEST NUMBER: P332167-830

CATALOG NUMBER: S123DIW-S775D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.1	353.1	354.1	354.6	354.5	354.4	354.4	354.3
115°	407.2	407.5	407.6	407.6	407.5	407.2	407.0	406.8
117.5°	462.9	462.8	462.8	462.4	461.8	461.3	460.6	460.1
120°	499.9	499.7	499.5	499.2	498.8	498.3	497.9	497.5
122.5°	537.4	536.9	536.4	535.7	535.2	534.6	534.0	533.4
125°	593.2	592.4	591.5	590.7	589.8	589.0	588.1	587.3
127.5°	648.3	647.1	645.9	644.8	643.9	642.9	641.9	640.9
130°	684.9	684.0	683.2	682.0	680.5	679.0	677.6	676.1
132.5°	720.5	719.4	718.4	717.4	716.1	715.0	713.9	712.8
135°	773.6	772.8	771.9	771.4	770.9	770.5	770.1	769.7
137.5°	825.8	824.8	824.0	823.1	822.3	821.5	820.7	819.9
140°	860.0	859.7	859.5	858.7	857.1	855.7	854.2	852.7
142.5°	892.0	891.8	891.6	890.9	889.8	888.6	887.5	886.4
145°	939.2	939.0	938.8	938.2	937.4	936.5	935.7	934.8
147.5°	983.7	983.7	983.7	983.1	981.8	980.5	979.3	978.0
150°	1011.3	1011.3	1011.3	1010.6	1009.4	1008.0	1006.8	1005.5
152.5°	1036.3	1036.7	1037.1	1036.7	1035.6	1034.4	1033.3	1032.3
155°	1073.1	1073.9	1074.8	1074.5	1073.0	1071.5	1070.1	1068.6
157.5°	1104.7	1105.6	1106.5	1106.4	1105.1	1104.0	1102.8	1101.5
160°	1124.2	1125.2	1126.2	1126.3	1125.5	1124.6	1123.8	1122.9
162.5°	1142.5	1143.5	1144.6	1144.4	1143.1	1141.7	1140.4	1139.0
165°	1165.6	1166.9	1168.2	1168.1	1166.6	1165.1	1163.6	1162.2
167.5°	1184.4	1185.7	1187.0	1187.0	1185.7	1184.4	1183.1	1181.8
170°	1194.7	1196.2	1197.7	1197.7	1196.2	1194.7	1193.2	1191.8
172.5°	1202.8	1204.1	1205.4	1205.3	1203.8	1202.3	1200.8	1199.4
175°	1211.4	1212.8	1214.0	1213.9	1212.4	1210.9	1209.5	1208.0
177.5°	1215.3	1216.4	1217.4	1217.3	1216.1	1214.9	1213.7	1212.6
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6

(END OF REPORT)