

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332178-830

Luminaire Tested: **S123DIW-S775D1535U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332178-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D1535U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8775.8 lumens  
Efficiency: N/A  
Efficacy: 128.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	42	42	42
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35
2	86	78	72	67	77	71	66	62	57	53	50	44	42	40	32	31	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	27	25
4	71	61	53	47	64	55	49	43	45	40	36	35	31	29	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	21	19
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	16	15
8	51	39	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12355	12355	12355
5°	12413	12241	12327
10°	12329	12136	12211
15°	12186	11999	12021
20°	12016	11802	11813
25°	11792	11569	11545
30°	11543	11309	11225
35°	11284	11037	10893
40°	11011	10732	10568
45°	10712	10456	10201
50°	10412	10114	9833
55°	10021	9760	9466
60°	9623	9347	9052
65°	9276	8899	8621
70°	8759	8387	8013
75°	8006	7719	7390
80°	7221	6912	6856
85°	6336	6101	5854



TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.1	1.2
10°-20°	305.3	3.5
20°-30°	451.0	5.1
30°-40°	526.8	6.0
40°-50°	529.6	6.0
50°-60°	465.2	5.3
60°-70°	346.6	3.9
70°-80°	197.5	2.3
80°-90°	62.0	0.7
90°-100°	69.0	0.8
100°-110°	328.6	3.7
110°-120°	789.4	9.0
120°-130°	1005.2	11.5
130°-140°	1074.1	12.2
140°-150°	1004.4	11.4
150°-160°	810.1	9.2
160°-170°	522.9	6.0
170°-180°	180.2	2.1
0°-30°	864.4	9.8
0°-40°	1391.1	15.9
0°-60°	2385.9	27.2
0°-90°	2992.0	34.1
90°-120°	1187.0	13.5
90°-150°	4270.6	48.7
90°-180°	5784.0	65.9
0°-180°	8775.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1149	1143	1133	1142	1141	109
15°	1094	1089	1077	1084	1079	308
25°	993	987	974	975	972	457
35°	859	852	840	834	829	537
45°	704	699	687	675	670	543
55°	534	532	520	510	504	478
65°	364	359	349	342	338	359
75°	192	189	186	181	178	206
85°	51	50	49	48	47	56
90°	1	16	34	39	42	7
95°	86	32	44	53	54	106
105°	420	428	309	73	62	445
115°	788	796	809	822	829	777
125°	1110	1121	1127	1130	1133	991
135°	1382	1391	1396	1400	1396	1064
145°	1595	1604	1608	1610	1611	998
155°	1757	1754	1756	1762	1754	809
165°	1853	1849	1847	1857	1849	523
175°	1897	1890	1891	1900	1890	180
180°	1897	1897	1897	1897	1897	



TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1151.7	1151.0	1150.4	1149.6	1149.0	1147.6	1145.7	1143.8	1141.8	1139.9	1141.6
5°	1148.8	1147.6	1146.6	1145.5	1144.3	1142.6	1140.2	1137.8	1135.4	1132.9	1135.2
7.5°	1137.6	1136.4	1135.3	1134.3	1133.1	1131.3	1128.8	1126.3	1123.8	1121.3	1123.3
10°	1128.0	1126.9	1125.9	1124.7	1123.7	1121.7	1118.8	1116.0	1113.1	1110.3	1112.3
12.5°	1115.4	1114.5	1113.6	1112.7	1111.7	1109.9	1107.3	1104.6	1101.9	1099.2	1100.7
15°	1093.5	1092.6	1091.7	1090.9	1090.0	1088.2	1085.2	1082.4	1079.6	1076.8	1078.5
17.5°	1068.0	1066.9	1065.7	1064.6	1063.5	1061.5	1058.7	1055.7	1052.9	1050.1	1051.3
20°	1049.0	1047.7	1046.5	1045.2	1043.9	1041.7	1038.9	1036.0	1033.2	1030.3	1031.2
22.5°	1027.7	1026.4	1025.1	1023.8	1022.5	1020.4	1017.6	1014.7	1011.9	1009.0	1009.7
25°	992.9	991.6	990.2	988.9	987.6	985.5	982.6	979.8	976.9	974.1	974.3
27.5°	955.5	954.2	953.0	951.7	950.5	948.3	945.2	942.2	939.1	935.9	936.1
30°	928.7	927.6	926.5	925.4	924.3	922.2	919.2	916.1	913.0	909.9	909.9
32.5°	901.8	900.4	898.9	897.5	896.1	894.2	891.7	889.4	887.0	884.7	883.4
35°	858.7	857.3	856.0	854.7	853.4	851.3	848.4	845.6	842.7	839.9	838.6
37.5°	814.4	812.8	811.1	809.4	807.8	805.5	802.6	799.7	796.7	793.9	792.3
40°	783.6	782.3	781.0	779.7	778.4	776.2	773.1	770.1	766.9	763.8	762.1
42.5°	752.8	751.3	749.8	748.4	746.9	744.6	741.5	738.4	735.4	732.3	730.6
45°	703.7	702.8	701.9	701.1	700.1	698.3	695.4	692.6	689.8	686.9	684.3
47.5°	654.9	653.7	652.3	651.1	649.8	647.8	645.2	642.5	639.8	637.2	634.5
50°	621.8	620.7	619.5	618.5	617.4	615.4	612.6	609.7	606.8	604.0	601.6
52.5°	587.0	586.3	585.5	584.8	584.0	582.1	579.1	576.1	573.1	570.0	568.0
55°	534.0	533.7	533.5	533.3	533.0	531.5	528.7	525.8	522.9	520.1	517.7
57.5°	483.4	482.7	481.9	481.2	480.4	478.9	476.6	474.3	472.0	469.8	467.6
60°	447.0	446.9	446.7	446.4	446.2	444.8	442.1	439.5	436.9	434.2	432.3
62.5°	414.7	414.2	413.6	413.0	412.5	410.9	408.2	405.6	402.9	400.3	398.3
65°	364.2	363.1	361.9	360.9	359.8	358.2	355.9	353.7	351.6	349.4	347.6
67.5°	310.7	309.7	308.8	307.7	306.8	305.5	303.9	302.2	300.5	298.9	297.3
70°	278.3	277.0	275.7	274.4	273.1	271.7	270.4	269.1	267.8	266.5	264.9
72.5°	244.4	243.4	242.4	241.5	240.5	239.3	237.8	236.3	234.8	233.3	232.0
75°	192.5	191.5	190.7	189.8	189.0	188.1	187.5	186.8	186.2	185.6	184.5
77.5°	146.5	146.0	145.5	145.1	144.5	143.9	143.1	142.3	141.6	140.7	140.0
80°	116.5	115.8	115.2	114.5	113.9	113.3	112.8	112.4	112.0	111.5	111.3
82.5°	87.3	87.1	87.0	86.8	86.7	86.6	86.5	86.4	86.3	86.2	85.9
85°	51.3	50.9	50.4	50.0	49.6	49.4	49.4	49.4	49.4	49.4	48.9
87.5°	20.8	20.9	21.0	21.1	21.2	21.6	22.2	22.8	23.5	24.1	24.2
90°	1.4	4.5	7.6	10.8	13.9	17.5	21.6	25.6	29.8	33.8	35.1
92.5°	26.2	25.4	24.4	23.6	22.7	23.8	26.9	30.0	33.0	36.1	38.1
95°	86.0	73.1	60.3	47.4	34.6	29.9	33.4	36.8	40.2	43.6	45.9
97.5°	172.8	167.0	161.3	155.4	149.7	135.5	113.0	90.5	68.0	45.3	47.9
100°	238.2	244.4	250.6	256.9	263.2	241.9	193.0	144.2	95.4	46.5	49.0
102.5°	312.5	317.1	321.6	326.0	330.5	306.1	252.8	199.4	146.1	92.7	84.9
105°	419.9	423.4	426.8	430.3	433.7	421.3	393.1	365.0	336.8	308.6	253.2
107.5°	533.2	535.9	538.7	541.5	544.2	547.8	552.2	556.8	561.2	565.6	525.0
110°	608.7	611.2	613.7	616.2	618.8	621.7	625.2	628.6	632.1	635.5	625.2



TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	680.9	683.2	685.4	687.7	689.8	692.8	696.2	699.6	703.0	706.5	706.7
115°	787.7	789.6	791.5	793.3	795.2	797.6	800.4	803.1	806.0	808.8	811.9
117.5°	891.1	893.4	895.7	898.1	900.4	902.3	903.7	905.1	906.5	908.0	910.5
120°	955.4	958.2	961.0	963.8	966.7	968.6	969.4	970.3	971.3	972.2	974.8
122.5°	1020.8	1023.0	1025.4	1027.7	1030.0	1031.8	1032.9	1034.2	1035.3	1036.5	1038.3
125°	1110.3	1112.9	1115.4	1117.9	1120.4	1122.3	1123.5	1124.7	1126.1	1127.3	1127.9
127.5°	1197.1	1199.7	1202.2	1204.7	1207.2	1209.2	1210.7	1212.2	1213.7	1215.2	1216.2
130°	1251.2	1253.8	1256.3	1258.8	1261.3	1263.2	1264.4	1265.6	1267.0	1268.2	1269.4
132.5°	1303.2	1305.6	1308.2	1310.6	1313.2	1314.9	1315.9	1316.9	1317.9	1318.9	1320.1
135°	1382.3	1384.2	1386.1	1388.0	1389.9	1391.4	1392.6	1393.9	1395.2	1396.4	1397.3
137.5°	1449.9	1452.4	1454.7	1457.1	1459.4	1461.0	1461.7	1462.4	1463.1	1463.8	1465.3
140°	1495.1	1496.9	1498.8	1500.7	1502.6	1503.9	1504.9	1505.8	1506.7	1507.7	1509.0
142.5°	1536.7	1538.6	1540.5	1542.4	1544.3	1545.7	1546.6	1547.6	1548.5	1549.4	1550.4
145°	1595.1	1597.2	1599.5	1601.7	1603.8	1605.2	1605.9	1606.5	1607.1	1607.8	1608.4
147.5°	1650.0	1651.5	1652.9	1654.4	1655.8	1656.8	1657.5	1658.1	1658.7	1659.3	1660.0
150°	1683.9	1684.8	1685.7	1686.7	1687.6	1688.4	1689.0	1689.7	1690.3	1690.9	1691.5
152.5°	1714.3	1714.8	1715.1	1715.6	1716.1	1716.5	1716.8	1717.2	1717.6	1718.0	1719.1
155°	1757.1	1756.5	1755.9	1755.3	1754.6	1754.4	1754.8	1755.1	1755.4	1755.7	1757.3
157.5°	1790.4	1790.4	1790.3	1790.2	1790.2	1790.0	1789.6	1789.3	1789.0	1788.7	1790.5
160°	1810.7	1810.3	1810.1	1809.8	1809.4	1809.1	1808.8	1808.5	1808.2	1807.9	1809.8
162.5°	1829.9	1829.0	1828.2	1827.4	1826.6	1826.0	1825.7	1825.4	1825.0	1824.8	1826.9
165°	1852.9	1852.0	1851.1	1850.1	1849.2	1848.6	1848.2	1847.9	1847.7	1847.3	1849.8
167.5°	1870.9	1869.7	1868.5	1867.3	1866.0	1865.4	1865.4	1865.4	1865.4	1865.4	1867.8
170°	1881.1	1879.9	1878.6	1877.4	1876.1	1875.5	1875.5	1875.5	1875.5	1875.5	1878.0
172.5°	1887.9	1886.4	1884.9	1883.4	1881.9	1881.2	1881.5	1881.8	1882.0	1882.3	1884.8
175°	1896.6	1895.1	1893.5	1892.0	1890.4	1889.7	1890.1	1890.4	1890.6	1891.0	1893.2
177.5°	1898.8	1897.6	1896.4	1895.2	1893.9	1893.4	1893.7	1893.9	1894.1	1894.4	1896.4
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6



TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8	1147.8
2.5°	1143.4	1145.2	1146.9	1147.7	1147.5	1147.4	1147.2	1147.0
5°	1137.4	1139.5	1141.8	1142.6	1142.2	1141.8	1141.3	1140.9
7.5°	1125.3	1127.3	1129.3	1130.1	1129.8	1129.5	1129.3	1129.1
10°	1114.3	1116.2	1118.1	1119.0	1118.5	1118.0	1117.7	1117.2
12.5°	1102.1	1103.5	1105.0	1105.6	1105.3	1105.0	1104.8	1104.6
15°	1080.2	1081.9	1083.7	1083.9	1082.6	1081.3	1080.1	1078.7
17.5°	1052.5	1053.8	1055.0	1055.4	1054.9	1054.4	1054.0	1053.5
20°	1032.1	1032.9	1033.9	1034.0	1033.3	1032.6	1032.0	1031.3
22.5°	1010.4	1011.2	1011.8	1011.7	1011.0	1010.1	1009.3	1008.4
25°	974.5	974.8	975.0	974.8	974.1	973.5	972.8	972.1
27.5°	936.3	936.5	936.7	936.3	935.6	934.7	933.9	933.0
30°	909.9	909.9	909.9	909.2	907.7	906.1	904.6	903.1
32.5°	882.2	881.0	879.8	878.7	877.9	877.0	876.2	875.4
35°	837.3	835.9	834.6	833.4	832.3	831.2	830.1	829.0
37.5°	790.7	789.1	787.6	786.5	785.7	785.0	784.3	783.6
40°	760.3	758.7	756.9	755.5	754.7	753.8	752.9	752.1
42.5°	728.8	727.0	725.3	724.0	723.1	722.2	721.3	720.5
45°	681.6	679.0	676.4	674.5	673.4	672.3	671.2	670.1
47.5°	632.0	629.4	626.8	625.0	624.1	623.1	622.2	621.1
50°	599.2	596.7	594.4	592.5	591.2	589.8	588.5	587.2
52.5°	565.9	563.8	561.8	560.2	558.8	557.5	556.2	554.9
55°	515.3	512.8	510.5	508.7	507.6	506.5	505.4	504.4
57.5°	465.4	463.4	461.2	459.5	458.2	456.9	455.6	454.4
60°	430.3	428.3	426.3	424.8	423.7	422.6	421.5	420.5
62.5°	396.3	394.4	392.4	391.1	390.3	389.6	388.8	388.0
65°	345.8	344.1	342.3	341.1	340.4	339.8	339.1	338.5
67.5°	295.8	294.3	292.7	291.4	290.6	289.6	288.7	287.8
70°	263.4	261.8	260.3	259.0	257.9	256.8	255.7	254.6
72.5°	230.5	229.2	227.9	226.9	226.3	225.7	225.2	224.6
75°	183.3	182.3	181.2	180.3	179.6	179.0	178.3	177.7
77.5°	139.2	138.5	137.7	137.4	137.4	137.4	137.4	137.4
80°	111.1	110.8	110.7	110.6	110.6	110.6	110.6	110.6
82.5°	85.5	85.1	84.6	84.4	84.3	84.1	83.9	83.7
85°	48.4	48.1	47.6	47.4	47.4	47.4	47.4	47.4
87.5°	24.3	24.3	24.4	24.5	24.7	24.8	24.9	25.1
90°	36.3	37.6	38.8	39.8	40.4	41.0	41.7	42.2
92.5°	40.1	42.1	44.1	45.2	45.6	46.0	46.4	46.8
95°	48.1	50.2	52.4	53.5	53.5	53.5	53.5	53.5
97.5°	50.4	52.9	55.4	56.8	57.1	57.4	57.8	58.1
100°	51.5	54.0	56.6	58.0	58.2	58.5	58.9	59.2
102.5°	77.2	69.5	61.6	58.1	58.6	59.2	59.8	60.3
105°	197.7	142.3	86.9	59.5	60.1	60.8	61.4	62.0
107.5°	484.3	443.7	403.0	361.8	320.1	278.2	236.5	194.7
110°	614.8	604.5	594.2	566.6	521.8	477.0	432.3	387.5





TEST NUMBER: P332178-830

CATALOG NUMBER: S123DIW-S775D1535U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	706.9	707.1	707.3	702.7	693.1	683.7	674.3	664.8
115°	815.1	818.2	821.3	823.5	824.8	826.0	827.3	828.6
117.5°	913.0	915.5	918.0	919.5	919.6	919.9	920.2	920.4
120°	977.3	979.8	982.3	983.5	983.5	983.5	983.5	983.5
122.5°	1040.0	1041.8	1043.6	1044.5	1044.8	1045.0	1045.3	1045.6
125°	1128.5	1129.2	1129.7	1130.4	1131.1	1131.6	1132.3	1132.9
127.5°	1217.2	1218.2	1219.2	1219.4	1218.8	1218.1	1217.5	1216.9
130°	1270.6	1272.0	1273.2	1273.5	1272.9	1272.2	1271.6	1271.0
132.5°	1321.4	1322.7	1323.9	1324.1	1323.2	1322.4	1321.4	1320.6
135°	1398.3	1399.2	1400.1	1400.1	1399.2	1398.3	1397.3	1396.4
137.5°	1466.8	1468.3	1469.8	1470.2	1469.6	1469.0	1468.3	1467.7
140°	1510.2	1511.5	1512.7	1513.1	1512.4	1511.8	1511.2	1510.5
142.5°	1551.4	1552.5	1553.4	1553.5	1552.7	1551.7	1550.9	1550.0
145°	1609.0	1609.7	1610.2	1610.6	1610.6	1610.6	1610.6	1610.6
147.5°	1660.6	1661.2	1661.9	1661.4	1660.0	1658.6	1657.1	1655.7
150°	1692.1	1692.8	1693.4	1693.3	1692.3	1691.4	1690.5	1689.5
152.5°	1720.2	1721.4	1722.5	1722.3	1720.9	1719.4	1718.0	1716.6
155°	1758.9	1760.4	1762.0	1761.8	1759.9	1758.0	1756.1	1754.4
157.5°	1792.4	1794.3	1796.2	1795.9	1793.5	1791.0	1788.6	1786.1
160°	1811.7	1813.5	1815.3	1815.2	1813.0	1810.8	1808.6	1806.5
162.5°	1829.0	1831.2	1833.2	1833.3	1831.5	1829.5	1827.6	1825.6
165°	1852.3	1854.8	1857.4	1857.5	1855.3	1853.1	1850.9	1848.7
167.5°	1870.4	1872.8	1875.4	1875.4	1872.8	1870.4	1867.8	1865.4
170°	1880.5	1883.0	1885.6	1885.6	1883.0	1880.5	1878.0	1875.5
172.5°	1887.3	1889.8	1892.2	1892.2	1889.4	1886.7	1883.9	1881.1
175°	1895.4	1897.5	1899.8	1899.6	1897.1	1894.6	1892.1	1889.6
177.5°	1898.4	1900.4	1902.4	1902.1	1899.6	1897.1	1894.6	1892.2
180°	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6	1896.6

(END OF REPORT)