

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332461-935

Luminaire Tested: **S123RDIW-S1000D1030U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332461-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6344.0 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70		62	61	59		51	50	49	44
2	90	83	77	72	83	77	72	67	65	62	58		55	52	50		46	44	42	37
3	82	73	66	60	76	68	62	56	58	53	49		49	46	43		41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42		44	40	37		37	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37		40	35	32		33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32		36	32	28		30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28		33	28	25		28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25		30	26	22		25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23		28	23	20		23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21		26	21	18		22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.7	2.1
10°-20°	377.5	6.0
20°-30°	543.6	8.6
30°-40°	612.3	9.7
40°-50°	585.8	9.2
50°-60°	479.7	7.6
60°-70°	323.7	5.1
70°-80°	162.8	2.6
80°-90°	46.4	0.7
90°-100°	72.4	1.1
100°-110°	216.5	3.4
110°-120°	368.3	5.8
120°-130°	484.4	7.6
130°-140°	544.4	8.6
140°-150°	535.2	8.4
150°-160°	450.5	7.1
160°-170°	299.9	4.7
170°-180°	105.0	1.7
0°-30°	1056.8	16.7
0°-40°	1669.1	26.3
0°-60°	2734.6	43.1
0°-90°	3267.4	51.5
90°-120°	657.1	10.4
90°-150°	2221.1	35.0
90°-180°	3077.0	48.5
0°-180°	6344.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	10	21	24	26	6
95°	52	58	65	68	68	58
105°	196	198	206	206	208	210
115°	371	373	372	372	372	367
125°	543	545	544	540	536	484
135°	704	709	708	705	703	542
145°	854	856	858	857	854	533
155°	978	978	979	982	976	450
165°	1065	1063	1062	1067	1062	300
175°	1108	1104	1104	1109	1104	105
180°	1110	1110	1110	1110	1110	



TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.6	20.8	18.9	17.0	15.1	14.4	14.9	15.3	15.8	16.4	16.4
90°	0.9	2.8	4.7	6.7	8.6	10.8	13.3	15.9	18.4	20.9	21.7
92.5°	21.1	22.4	23.8	25.1	26.3	27.7	29.2	30.7	32.0	33.5	34.1
95°	51.5	52.8	54.2	55.5	56.9	58.4	59.9	61.5	63.0	64.6	65.3
97.5°	91.4	92.4	93.4	94.5	95.5	96.5	97.6	98.8	99.9	101.0	101.9
100°	118.6	119.8	121.0	122.1	123.3	124.3	125.4	126.3	127.3	128.2	128.8
102.5°	150.1	150.8	151.4	152.1	152.8	153.8	155.1	156.4	157.6	158.9	159.5
105°	196.3	196.7	197.1	197.4	197.9	198.9	200.6	202.3	204.1	205.9	205.9
107.5°	250.0	250.2	250.5	250.7	250.9	251.4	252.1	252.8	253.5	254.2	254.8
110°	283.5	283.9	284.3	284.6	285.1	285.4	285.9	286.2	286.6	287.0	287.7



TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	318.4	318.7	318.8	319.1	319.3	319.4	319.5	319.6	319.7	319.8	320.7
115°	370.7	371.3	371.9	372.5	373.1	373.2	372.7	372.4	372.0	371.6	371.8
117.5°	423.4	423.8	424.2	424.6	425.0	424.9	424.4	423.9	423.4	422.9	422.8
120°	456.2	457.4	458.6	459.7	460.9	461.0	459.9	459.0	458.1	457.1	456.8
122.5°	490.4	491.3	492.1	492.9	493.8	494.0	493.5	493.0	492.5	492.0	491.5
125°	542.6	543.1	543.7	544.3	544.9	545.0	544.6	544.2	543.8	543.5	542.7
127.5°	590.7	591.9	593.2	594.4	595.6	596.1	595.6	595.2	594.8	594.3	593.3
130°	622.8	624.4	625.9	627.5	629.0	629.5	629.0	628.4	627.8	627.2	626.4
132.5°	654.9	656.4	658.0	659.6	661.2	661.7	661.2	660.8	660.4	660.0	659.0
135°	704.0	705.1	706.3	707.4	708.6	709.0	708.9	708.7	708.5	708.3	707.5
137.5°	749.3	750.3	751.2	752.2	753.2	753.9	754.4	754.9	755.4	756.0	755.1
140°	780.7	781.7	782.6	783.6	784.5	785.1	785.3	785.6	785.7	785.9	785.7
142.5°	809.3	810.3	811.2	812.2	813.2	813.8	814.2	814.5	814.9	815.3	815.0
145°	853.9	854.4	854.7	855.1	855.5	856.0	856.6	857.2	857.7	858.3	858.2
147.5°	893.0	893.7	894.4	895.2	895.9	896.5	897.0	897.6	898.1	898.6	898.6
150°	920.2	920.7	921.0	921.4	921.8	922.2	922.6	923.0	923.3	923.8	923.8
152.5°	942.6	943.1	943.7	944.3	944.8	945.1	945.4	945.6	945.9	946.1	946.4
155°	977.8	977.8	977.8	977.8	977.8	977.9	978.1	978.4	978.5	978.7	979.5
157.5°	1007.9	1007.6	1007.4	1007.1	1006.9	1006.9	1007.0	1007.2	1007.4	1007.5	1008.3
160°	1026.7	1026.3	1025.9	1025.5	1025.1	1024.9	1024.9	1024.9	1024.9	1024.9	1025.9
162.5°	1043.4	1042.9	1042.3	1041.8	1041.3	1041.0	1041.2	1041.4	1041.6	1041.7	1042.7
165°	1065.1	1064.5	1063.9	1063.3	1062.7	1062.5	1062.5	1062.5	1062.5	1062.5	1063.6
167.5°	1082.4	1081.6	1080.8	1080.0	1079.3	1078.9	1079.1	1079.3	1079.4	1079.5	1080.7
170°	1092.1	1091.3	1090.5	1089.8	1089.0	1088.6	1088.6	1088.6	1088.6	1088.6	1089.9
172.5°	1099.8	1099.0	1098.2	1097.4	1096.7	1096.3	1096.3	1096.3	1096.3	1096.3	1097.5
175°	1107.8	1107.1	1106.3	1105.5	1104.7	1104.3	1104.3	1104.3	1104.3	1104.3	1105.5
177.5°	1111.1	1110.5	1109.9	1109.2	1108.6	1108.4	1108.4	1108.4	1108.4	1108.4	1109.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	16.3	16.2	16.2	16.1	15.9	15.8	15.7	15.6
90°	22.5	23.2	24.0	24.6	25.0	25.4	25.7	26.2
92.5°	34.7	35.4	36.0	36.2	35.9	35.7	35.5	35.2
95°	66.1	66.9	67.7	68.0	68.0	68.0	68.0	68.0
97.5°	102.8	103.7	104.6	105.0	104.9	104.9	104.8	104.7
100°	129.4	130.0	130.5	131.0	131.4	131.8	132.2	132.6
102.5°	160.1	160.7	161.3	161.5	161.4	161.4	161.3	161.2
105°	205.9	205.9	205.9	206.0	206.5	206.8	207.2	207.6
107.5°	255.5	256.1	256.7	256.8	256.7	256.4	256.1	255.9
110°	288.5	289.3	290.1	290.2	289.9	289.5	289.1	288.7





TEST NUMBER: P332461-935

CATALOG NUMBER: S123RDIW-S1000D1030U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	321.7	322.5	323.5	323.9	323.8	323.7	323.7	323.6
115°	372.0	372.2	372.4	372.4	372.2	372.0	371.8	371.6
117.5°	422.8	422.8	422.8	422.4	421.9	421.4	420.8	420.3
120°	456.7	456.5	456.3	456.0	455.6	455.2	454.9	454.4
122.5°	490.9	490.4	490.0	489.4	488.9	488.4	487.8	487.2
125°	541.9	541.1	540.4	539.6	538.8	538.0	537.3	536.5
127.5°	592.2	591.2	590.0	589.0	588.1	587.3	586.3	585.5
130°	625.6	624.8	624.1	623.0	621.6	620.3	619.0	617.6
132.5°	658.1	657.2	656.3	655.3	654.2	653.2	652.1	651.1
135°	706.7	705.9	705.2	704.6	704.2	703.9	703.4	703.1
137.5°	754.3	753.5	752.7	751.9	751.1	750.4	749.7	749.0
140°	785.6	785.3	785.1	784.4	783.0	781.7	780.3	778.9
142.5°	814.9	814.7	814.5	813.8	812.8	811.8	810.7	809.7
145°	858.0	857.7	857.6	857.0	856.3	855.5	854.7	853.9
147.5°	898.6	898.6	898.6	898.0	896.9	895.7	894.6	893.4
150°	923.8	923.8	923.8	923.2	922.0	920.8	919.7	918.5
152.5°	946.7	947.0	947.4	947.0	946.0	944.9	943.9	943.0
155°	980.2	981.0	981.8	981.5	980.2	978.8	977.5	976.1
157.5°	1009.1	1010.0	1010.7	1010.6	1009.5	1008.5	1007.4	1006.3
160°	1026.9	1027.9	1028.8	1028.9	1028.1	1027.3	1026.6	1025.8
162.5°	1043.6	1044.6	1045.6	1045.4	1044.2	1042.9	1041.7	1040.4
165°	1064.8	1065.9	1067.1	1067.0	1065.7	1064.3	1062.9	1061.6
167.5°	1081.9	1083.1	1084.3	1084.3	1083.1	1081.9	1080.7	1079.5
170°	1091.3	1092.7	1094.1	1094.1	1092.7	1091.3	1089.9	1088.6
172.5°	1098.7	1099.9	1101.1	1101.0	1099.7	1098.3	1096.9	1095.6
175°	1106.6	1107.8	1109.0	1108.9	1107.5	1106.1	1104.8	1103.5
177.5°	1110.2	1111.1	1112.1	1112.0	1110.9	1109.8	1108.7	1107.7
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4

(END OF REPORT)