

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332150-830

Luminaire Tested: **S123DIW-S775D460U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332150-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D460U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4813.6 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64				
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	55				
2	92	85	79	74	87	80	75	70	71	67	63	62	59	56	54	52	50	46				
3	85	75	68	62	79	71	64	59	63	58	54	55	51	48	49	46	43	39				
4	78	67	59	53	73	63	56	50	56	50	46	50	45	42	44	40	37	34				
5	71	60	51	45	67	56	49	43	50	44	40	45	40	36	39	36	33	30				
6	66	54	45	40	62	51	43	38	45	39	35	40	36	32	36	32	29	26				
7	61	49	40	35	57	46	39	33	41	35	31	37	32	28	33	29	26	23				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21				
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19				
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10962	10962	10962	10962
5°	13073	11010	9757	11010
10°	16363	10954	8813	10954
15°	20070	10866	8204	10866
20°	23909	10727	7811	10727
25°	25388	10561	7725	10561
30°	21760	10438	7764	10438
35°	15134	10264	7846	10264
40°	11398	10061	7821	10061
45°	9464	9758	7722	9758
50°	8477	9138	7651	9138
55°	7927	8473	7557	8473
60°	7436	7776	7479	7776
65°	6989	7088	7238	7088
70°	6552	6304	6892	6304
75°	5868	5519	6317	5519
80°	5139	4525	5442	4525
85°	4026	3298	3656	3298



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	2.1
10°-20°	321.7	6.7
20°-30°	539.9	11.2
30°-40°	611.3	12.7
40°-50°	548.2	11.4
50°-60°	442.4	9.2
60°-70°	308.3	6.4
70°-80°	162.0	3.4
80°-90°	41.2	0.9
90°-100°	20.7	0.4
100°-110°	98.8	2.1
110°-120°	237.2	4.9
120°-130°	302.1	6.3
130°-140°	322.8	6.7
140°-150°	301.8	6.3
150°-160°	243.5	5.1
160°-170°	157.1	3.3
170°-180°	54.2	1.1
0°-30°	961.9	20.0
0°-40°	1573.3	32.7
0°-60°	2563.9	53.3
0°-90°	3075.5	63.9
90°-120°	356.7	7.4
90°-150°	1283.4	26.7
90°-180°	1738.0	36.1
0°-180°	4813.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1018	1018	1018	1018	1018	
5°	1210	1019	903	1019	1210	125
15°	1801	975	736	975	1801	520
25°	2138	889	650	889	2138	937
35°	1152	781	597	781	1152	748
45°	622	641	507	641	622	492
55°	422	452	403	452	422	379
65°	274	278	284	278	274	273
75°	141	133	152	133	141	151
85°	33	27	30	27	33	39
90°	13	0	13	0	13	7
95°	16	26	16	26	16	13
105°	19	126	19	126	19	43
115°	249	237	249	237	249	230
125°	340	334	340	334	340	304
135°	420	415	420	415	420	324
145°	484	479	484	479	484	302
155°	527	528	527	528	527	243
165°	556	557	556	557	556	157
175°	568	570	568	570	568	54
180°	570	570	570	570	570	



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1080.8	1080.1	1078.1	1079.7	1076.5	1072.1	1071.8	1067.8	1056.3	1055.6	1052.4
5°	1209.9	1206.0	1205.5	1204.9	1198.1	1188.7	1170.9	1169.4	1145.8	1133.9	1119.6
7.5°	1377.1	1379.1	1372.0	1365.6	1344.5	1330.6	1311.5	1287.1	1258.1	1228.6	1208.9
10°	1497.1	1513.3	1493.2	1479.3	1466.5	1442.3	1414.2	1379.1	1344.2	1303.2	1272.1
12.5°	1625.8	1633.8	1629.8	1616.7	1596.8	1560.0	1510.1	1471.5	1439.3	1371.0	1343.5
15°	1801.0	1831.2	1811.9	1767.5	1768.5	1733.4	1668.3	1596.8	1558.8	1499.0	1417.7
17.5°	1987.7	1991.5	1983.3	1946.4	1921.7	1873.5	1813.4	1744.8	1667.8	1595.5	1509.2
20°	2087.3	2084.2	2067.0	2047.8	2005.4	1967.8	1902.2	1825.7	1727.0	1656.0	1561.7
22.5°	2142.5	2137.6	2129.4	2113.3	2077.9	2037.7	1978.8	1895.2	1801.3	1703.4	1594.5
25°	2137.6	2144.0	2144.9	2140.5	2128.2	2104.0	2057.7	1991.0	1897.2	1771.4	1657.9
27.5°	1944.2	1953.2	1979.6	2003.0	2029.1	2055.8	2052.2	2019.1	1949.7	1841.2	1702.3
30°	1750.7	1731.0	1779.8	1841.5	1883.5	1957.5	1998.9	2001.4	1962.4	1869.2	1733.9
32.5°	1482.2	1504.0	1525.6	1601.5	1693.2	1776.3	1858.8	1925.2	1932.8	1870.8	1752.5
35°	1151.7	1178.8	1218.3	1257.7	1356.5	1441.3	1586.4	1712.7	1813.4	1826.7	1754.2
37.5°	928.0	941.5	966.5	1006.0	1070.5	1171.2	1283.5	1443.1	1588.9	1697.4	1702.1
40°	811.2	815.2	843.3	873.4	925.7	1008.6	1109.7	1250.8	1425.5	1577.1	1640.2
42.5°	723.6	732.3	744.2	773.1	814.7	877.1	971.2	1087.8	1247.9	1422.3	1545.9
45°	621.7	631.6	639.0	658.3	687.9	729.8	795.4	902.0	1023.9	1204.0	1370.3
47.5°	554.4	555.3	560.7	575.2	595.4	626.9	673.3	741.8	853.7	999.7	1170.4
50°	506.2	514.2	516.1	527.4	543.3	566.5	604.9	663.2	755.0	883.3	1040.2
52.5°	472.3	474.7	480.2	488.4	502.2	520.3	553.6	599.3	671.3	780.6	924.9
55°	422.4	422.4	427.8	434.2	442.1	458.4	480.6	514.2	568.9	653.8	773.3
57.5°	376.2	378.6	382.5	384.5	391.2	402.0	420.5	446.0	486.8	552.1	647.1
60°	345.4	349.9	349.4	353.3	359.2	367.6	383.4	404.2	440.6	492.9	572.9
62.5°	318.6	318.3	318.2	322.9	328.9	336.9	347.0	365.0	396.1	442.4	510.5
65°	274.4	273.3	276.8	279.7	281.7	287.7	295.6	311.3	332.1	366.6	419.4
67.5°	235.1	232.2	234.1	235.1	238.5	243.1	250.4	260.2	276.7	304.4	344.2
70°	208.2	205.8	205.3	206.2	209.2	212.6	218.1	227.4	242.8	264.9	294.1
72.5°	180.6	178.9	178.8	181.0	182.4	184.6	188.5	197.1	209.2	225.9	253.1
75°	141.1	141.1	141.1	141.6	143.1	145.1	148.1	152.5	161.8	173.7	191.9
77.5°	105.8	105.7	105.1	105.0	107.2	108.1	108.8	112.9	118.1	126.1	139.4
80°	82.9	80.4	81.4	82.9	83.9	84.4	85.9	86.8	91.3	95.8	105.1
82.5°	61.5	59.5	59.7	62.0	62.2	62.7	64.2	65.5	67.2	71.3	76.3
85°	32.6	32.6	33.1	33.1	33.6	33.1	34.5	35.1	35.1	37.5	40.4
87.5°	14.4	13.6	13.9	14.2	13.9	14.1	14.5	14.8	15.2	15.5	15.6
90°	12.7	12.5	12.3	12.2	12.0	11.7	11.3	10.9	10.6	10.2	9.0
92.5°	14.0	13.9	13.9	13.8	13.6	13.3	12.6	12.1	11.4	10.8	9.9
95°	16.1	16.1	16.1	16.1	16.1	15.7	15.1	14.4	13.8	13.1	12.1
97.5°	17.4	17.3	17.2	17.2	17.1	16.7	15.9	15.2	14.4	13.7	20.5
100°	17.8	17.7	17.6	17.5	17.4	17.0	16.2	15.5	14.7	13.9	28.7
102.5°	18.1	17.9	17.8	17.6	17.4	18.6	20.8	23.2	25.5	27.9	43.9
105°	18.7	18.5	18.3	18.1	17.9	26.1	42.8	59.4	76.1	92.7	101.2
107.5°	58.5	71.1	83.6	96.1	108.8	121.1	133.4	145.5	157.8	169.9	168.6
110°	116.5	129.9	143.4	156.8	170.3	178.5	181.6	184.7	187.8	191.0	189.9



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	199.8	202.6	205.5	208.3	211.1	212.5	212.4	212.4	212.4	212.4	211.3
115°	249.0	248.6	248.3	247.9	247.5	246.9	245.9	245.0	244.0	243.1	242.2
117.5°	276.6	276.5	276.4	276.4	276.3	275.9	275.1	274.4	273.6	272.9	272.5
120°	295.6	295.6	295.6	295.6	295.6	295.2	294.5	293.7	292.9	292.2	291.9
122.5°	314.2	314.1	314.1	314.0	313.9	313.6	313.1	312.5	312.0	311.5	311.1
125°	340.4	340.3	340.1	339.9	339.7	339.5	339.3	339.1	338.9	338.7	338.4
127.5°	365.7	365.9	366.1	366.3	366.5	366.4	366.1	365.8	365.5	365.2	364.8
130°	381.9	382.1	382.3	382.5	382.7	382.6	382.2	381.8	381.4	381.1	380.8
132.5°	396.9	397.1	397.4	397.7	397.9	397.8	397.5	397.1	396.7	396.3	396.1
135°	419.6	419.9	420.2	420.5	420.8	420.8	420.5	420.2	419.9	419.6	419.2
137.5°	441.1	441.3	441.5	441.7	441.9	441.7	441.2	440.8	440.4	439.9	439.7
140°	453.9	454.1	454.3	454.5	454.7	454.6	454.2	453.8	453.5	453.1	452.8
142.5°	465.8	466.1	466.4	466.6	466.8	466.8	466.6	466.3	465.9	465.6	465.3
145°	484.0	484.0	484.0	484.0	484.0	483.9	483.7	483.5	483.3	483.1	483.0
147.5°	497.6	498.0	498.4	498.9	499.3	499.5	499.3	499.1	498.9	498.7	498.5
150°	507.7	508.0	508.3	508.6	508.9	508.9	508.7	508.5	508.3	508.1	507.9
152.5°	515.9	516.3	516.7	517.2	517.6	517.6	517.3	517.0	516.6	516.3	516.1
155°	527.3	527.7	528.3	528.9	529.4	529.5	529.0	528.6	528.1	527.6	527.5
157.5°	536.8	537.5	538.3	538.9	539.7	539.8	539.2	538.7	538.1	537.5	537.6
160°	542.9	543.6	544.2	544.9	545.5	545.5	545.0	544.4	543.8	543.3	543.4
162.5°	548.7	549.2	549.8	550.4	551.0	550.9	550.4	549.7	549.0	548.4	548.5
165°	555.6	556.3	556.9	557.5	558.2	558.2	557.4	556.7	555.9	555.2	555.3
167.5°	560.6	561.4	562.1	562.8	563.5	563.5	562.8	562.1	561.4	560.6	560.6
170°	563.6	564.4	565.1	565.9	566.7	566.7	565.9	565.1	564.4	563.6	563.6
172.5°	565.3	566.2	566.9	567.8	568.6	568.6	567.9	567.1	566.4	565.6	565.6
175°	567.9	568.6	569.4	570.1	570.9	570.9	570.2	569.6	568.9	568.3	568.2
177.5°	568.6	569.4	570.1	570.9	571.7	571.7	571.1	570.5	569.9	569.3	569.2
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1050.0	1046.9	1043.7	1038.2	1033.5	1026.7	1024.7	1022.4	1015.3	1009.0	1004.3
5°	1114.2	1102.3	1085.1	1069.3	1056.5	1039.2	1029.4	1019.0	1004.2	990.8	980.0
7.5°	1181.3	1158.0	1131.1	1102.1	1075.1	1049.0	1028.0	1009.3	988.5	968.9	953.7
10°	1234.5	1201.0	1163.6	1123.0	1088.5	1055.0	1026.8	1002.2	975.5	952.3	933.1
12.5°	1295.3	1245.7	1193.9	1144.8	1103.9	1057.3	1023.3	991.9	961.7	933.8	912.2
15°	1367.3	1304.2	1242.9	1175.4	1113.2	1055.0	1014.6	975.1	940.0	911.3	883.7
17.5°	1432.9	1361.3	1280.6	1198.4	1123.4	1054.4	997.8	953.1	909.3	874.3	846.8
20°	1470.0	1388.6	1297.2	1211.9	1129.0	1052.0	989.9	936.5	889.2	852.2	821.0
22.5°	1501.9	1406.7	1312.2	1221.0	1128.6	1045.7	975.2	920.4	869.0	832.8	799.7
25°	1535.1	1421.1	1326.3	1219.3	1116.2	1030.3	951.3	889.2	837.8	795.4	761.4
27.5°	1563.5	1420.1	1307.7	1192.5	1096.6	1010.6	926.2	859.6	805.1	759.0	724.4
30°	1582.4	1422.1	1288.4	1174.4	1077.7	988.8	906.9	839.8	782.6	735.7	703.1
32.5°	1594.3	1420.9	1270.6	1149.1	1047.6	969.1	886.0	816.5	757.7	711.6	680.2
35°	1601.2	1412.2	1240.0	1096.9	999.2	922.7	853.2	781.1	719.4	676.5	641.0
37.5°	1587.4	1393.9	1204.5	1046.6	939.6	864.3	805.8	744.4	685.4	638.1	607.6
40°	1565.7	1382.1	1176.9	1011.1	898.5	826.0	776.2	716.0	657.7	612.8	584.2
42.5°	1524.2	1358.0	1146.4	971.6	855.9	783.3	737.5	687.2	632.1	589.9	561.4
45°	1423.1	1305.6	1100.9	912.4	793.0	717.9	677.5	641.0	591.2	550.2	525.5
47.5°	1282.7	1226.8	1034.9	849.9	727.3	655.1	613.0	583.6	547.2	514.2	490.5
50°	1185.2	1162.1	990.3	807.3	683.4	612.8	572.4	545.7	519.6	486.5	464.9
52.5°	1072.7	1087.0	938.2	763.1	638.8	569.4	531.3	510.2	486.4	459.3	440.4
55°	914.4	966.1	848.2	688.8	572.4	506.2	470.2	451.5	437.7	417.5	401.1
57.5°	766.0	832.0	750.9	612.4	507.2	450.2	415.6	395.1	386.3	375.7	362.9
60°	678.0	743.1	681.5	561.0	463.4	409.1	378.4	361.2	352.3	344.9	334.0
62.5°	599.5	665.3	613.5	509.0	420.3	369.9	343.4	326.5	319.5	315.7	306.4
65°	491.4	548.2	513.7	427.8	358.7	314.3	290.1	278.3	271.9	270.4	264.5
67.5°	400.0	443.2	418.0	354.9	300.5	262.1	241.6	231.5	226.6	226.1	221.7
70°	340.0	380.4	361.2	304.0	257.1	227.0	209.2	200.3	197.4	196.9	194.4
72.5°	293.4	321.6	306.3	258.5	222.3	195.0	182.0	172.7	169.4	170.0	168.3
75°	217.1	238.4	229.4	196.4	167.3	149.5	138.6	132.7	129.8	131.3	129.3
77.5°	156.2	169.7	161.6	138.7	120.8	107.9	100.0	96.3	93.7	93.6	92.7
80°	117.9	125.8	121.4	107.5	92.7	81.9	75.5	73.0	71.5	71.1	70.6
82.5°	84.0	90.7	85.5	76.0	65.9	59.4	55.8	52.5	51.5	51.7	51.2
85°	42.4	44.9	42.9	37.0	33.1	30.1	28.1	26.7	25.6	26.1	25.2
87.5°	16.1	16.3	14.9	13.1	12.1	10.7	10.6	9.5	9.0	9.1	9.0
90°	7.7	6.5	5.3	4.1	3.2	2.3	1.3	0.4	1.3	2.3	3.2
92.5°	9.0	8.1	7.2	6.8	7.1	7.4	7.6	7.9	7.6	7.4	7.1
95°	11.0	10.0	9.0	10.4	14.2	18.1	22.0	25.8	22.0	18.1	14.2
97.5°	27.1	33.9	40.7	45.0	46.8	48.4	50.1	51.9	50.1	48.4	46.8
100°	43.4	58.1	72.7	79.1	77.2	75.3	73.4	71.5	73.4	75.3	77.2
102.5°	59.9	76.0	92.0	99.3	98.0	96.6	95.3	93.9	95.3	96.6	98.0
105°	109.7	118.1	126.6	130.4	129.3	128.3	127.2	126.2	127.2	128.3	129.3
107.5°	167.3	166.0	164.7	163.5	162.7	161.9	161.1	160.2	161.1	161.9	162.7
110°	188.9	187.8	186.8	186.0	185.2	184.5	183.7	182.9	183.7	184.5	185.2



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	210.3	209.2	208.2	207.4	206.6	205.9	205.3	204.6	205.3	205.9	206.6
115°	241.4	240.5	239.7	238.9	238.4	237.8	237.2	236.7	237.2	237.8	238.4
117.5°	272.0	271.5	271.2	270.6	269.8	269.2	268.5	267.8	268.5	269.2	269.8
120°	291.6	291.3	291.1	290.5	289.6	288.8	287.9	287.1	287.9	288.8	289.6
122.5°	310.8	310.5	310.1	309.5	308.9	308.1	307.5	306.8	307.5	308.1	308.9
125°	338.0	337.6	337.2	336.7	335.9	335.2	334.4	333.7	334.4	335.2	335.9
127.5°	364.3	363.8	363.4	362.8	362.0	361.3	360.5	359.8	360.5	361.3	362.0
130°	380.4	380.0	379.7	379.1	378.3	377.6	376.8	376.1	376.8	377.6	378.3
132.5°	395.8	395.5	395.1	394.6	393.9	393.1	392.4	391.6	392.4	393.1	393.9
135°	418.9	418.5	418.1	417.6	417.1	416.5	415.9	415.4	415.9	416.5	417.1
137.5°	439.5	439.3	439.0	438.6	437.9	437.2	436.5	435.7	436.5	437.2	437.9
140°	452.5	452.2	451.9	451.6	451.0	450.4	449.9	449.3	449.9	450.4	451.0
142.5°	465.1	464.8	464.5	464.1	463.5	463.0	462.4	461.8	462.4	463.0	463.5
145°	482.8	482.6	482.4	482.0	481.4	480.7	480.0	479.4	480.0	480.7	481.4
147.5°	498.3	498.1	497.9	497.6	497.2	496.7	496.3	495.9	496.3	496.7	497.2
150°	507.7	507.6	507.4	507.2	506.9	506.6	506.3	506.1	506.3	506.6	506.9
152.5°	516.0	515.9	515.9	515.8	515.6	515.5	515.3	515.2	515.3	515.5	515.6
155°	527.4	527.4	527.3	527.4	527.5	527.6	527.8	528.0	527.8	527.6	527.5
157.5°	537.7	537.8	537.9	538.0	538.0	538.0	538.0	538.1	538.0	538.0	538.0
160°	543.5	543.6	543.7	543.8	543.8	543.9	544.0	544.1	544.0	543.9	543.8
162.5°	548.6	548.7	548.7	548.9	549.2	549.4	549.7	549.9	549.7	549.4	549.2
165°	555.3	555.4	555.5	555.7	556.0	556.3	556.6	556.9	556.6	556.3	556.0
167.5°	560.6	560.6	560.6	560.8	561.2	561.6	561.9	562.3	561.9	561.6	561.2
170°	563.6	563.6	563.6	563.8	564.2	564.6	565.0	565.3	565.0	564.6	564.2
172.5°	565.5	565.4	565.3	565.5	566.0	566.5	566.9	567.3	566.9	566.5	566.0
175°	568.1	568.0	567.9	568.1	568.5	569.0	569.5	570.0	569.5	569.0	568.5
177.5°	569.1	569.1	569.0	569.1	569.5	569.9	570.2	570.6	570.2	569.9	569.5
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1001.5	998.7	994.8	988.8	984.1	976.6	976.6	977.8	977.8	977.4	976.6
5°	971.1	963.7	954.8	944.4	933.6	922.7	920.8	916.8	913.9	911.9	909.4
7.5°	939.1	925.9	912.9	898.4	885.2	874.3	866.7	860.4	856.3	852.0	848.9
10°	917.3	901.0	885.7	870.4	853.7	840.4	832.0	826.0	821.6	817.7	815.7
12.5°	891.6	873.0	856.1	841.6	823.2	809.5	801.5	798.8	793.5	785.2	780.9
15°	854.1	836.9	816.6	794.5	785.5	768.7	759.4	755.0	752.0	745.6	743.6
17.5°	822.1	799.5	776.7	760.2	743.7	730.1	724.8	719.3	715.4	710.1	708.6
20°	796.4	776.2	755.4	737.7	720.4	705.6	701.2	697.2	693.2	690.8	688.8
22.5°	770.3	750.2	732.9	716.3	698.0	688.2	683.4	679.1	676.3	674.7	672.7
25°	733.8	716.0	696.7	681.9	667.1	660.7	657.7	655.3	653.3	650.8	650.4
27.5°	701.0	681.6	666.0	652.2	641.6	636.2	633.4	632.2	632.6	633.5	634.0
30°	676.5	658.7	645.9	634.0	624.2	619.3	618.8	618.8	620.8	621.2	622.3
32.5°	654.0	639.4	626.6	615.1	607.7	604.3	606.1	606.1	607.8	609.0	610.8
35°	621.2	608.4	598.5	588.7	582.3	583.7	584.8	585.7	588.1	591.2	593.1
37.5°	589.9	578.8	568.5	560.8	557.9	560.5	562.9	565.0	567.9	570.1	572.1
40°	567.4	559.0	549.2	542.2	543.3	544.8	546.8	549.2	551.7	553.2	555.2
42.5°	546.5	537.7	530.3	524.5	525.9	527.8	529.0	530.3	533.1	535.7	537.0
45°	514.6	507.7	500.9	497.4	498.4	499.4	500.3	501.8	504.3	506.2	506.8
47.5°	478.8	474.0	469.4	466.0	467.6	467.2	468.4	471.6	472.4	473.6	476.4
50°	455.9	451.5	446.1	445.1	445.1	445.1	445.5	449.5	449.5	451.5	453.5
52.5°	430.6	427.8	424.3	422.5	421.8	421.8	423.9	425.8	426.6	429.4	431.4
55°	393.2	390.3	387.4	385.9	384.8	385.9	389.8	390.8	393.2	394.7	396.2
57.5°	354.3	352.0	349.7	348.8	348.6	350.0	352.1	355.1	355.7	360.2	362.5
60°	328.7	325.2	323.2	323.2	322.3	326.7	325.6	330.6	331.6	334.5	338.0
62.5°	302.2	297.6	296.7	296.7	298.1	299.4	300.8	302.9	305.6	309.2	312.0
65°	259.6	257.1	260.5	260.0	259.0	262.0	262.0	264.5	267.4	270.9	276.4
67.5°	219.1	217.9	218.2	218.2	219.7	221.4	222.7	224.9	228.5	232.1	235.6
70°	191.9	193.4	191.0	192.9	194.4	194.9	195.9	198.9	202.8	205.3	209.2
72.5°	165.5	165.4	165.7	166.5	168.0	168.8	169.8	173.2	177.6	179.6	182.8
75°	127.3	126.8	128.3	128.3	130.7	131.8	132.7	134.2	138.2	141.1	143.5
77.5°	92.9	93.6	93.2	94.9	94.3	94.4	97.5	99.0	99.3	105.2	106.5
80°	70.0	71.1	71.5	72.0	72.6	71.5	75.0	76.4	76.4	79.9	82.4
82.5°	50.3	50.9	52.2	52.7	52.8	53.8	54.1	55.1	56.4	57.9	61.1
85°	25.2	26.7	27.1	26.7	27.1	26.1	27.6	28.1	28.7	28.7	28.7
87.5°	8.8	9.3	9.2	9.8	9.7	10.4	10.4	9.7	9.8	11.0	9.5
90°	4.1	5.3	6.5	7.7	9.0	10.2	10.6	10.9	11.3	11.7	12.0
92.5°	6.8	7.2	8.1	9.0	9.9	10.8	11.4	12.1	12.6	13.3	13.6
95°	10.4	9.0	10.0	11.0	12.1	13.1	13.8	14.4	15.1	15.7	16.1
97.5°	45.0	40.7	33.9	27.1	20.5	13.7	14.4	15.2	15.9	16.7	17.1
100°	79.1	72.7	58.1	43.4	28.7	13.9	14.7	15.5	16.2	17.0	17.4
102.5°	99.3	92.0	76.0	59.9	43.9	27.9	25.5	23.2	20.8	18.6	17.4
105°	130.4	126.6	118.1	109.7	101.2	92.7	76.1	59.4	42.8	26.1	17.9
107.5°	163.5	164.7	166.0	167.3	168.6	169.9	157.8	145.5	133.4	121.1	108.8
110°	186.0	186.8	187.8	188.9	189.9	191.0	187.8	184.7	181.6	178.5	170.3



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	207.4	208.2	209.2	210.3	211.3	212.4	212.4	212.4	212.4	212.5	211.1
115°	238.9	239.7	240.5	241.4	242.2	243.1	244.0	245.0	245.9	246.9	247.5
117.5°	270.6	271.2	271.5	272.0	272.5	272.9	273.6	274.4	275.1	275.9	276.3
120°	290.5	291.1	291.3	291.6	291.9	292.2	292.9	293.7	294.5	295.2	295.6
122.5°	309.5	310.1	310.5	310.8	311.1	311.5	312.0	312.5	313.1	313.6	313.9
125°	336.7	337.2	337.6	338.0	338.4	338.7	338.9	339.1	339.3	339.5	339.7
127.5°	362.8	363.4	363.8	364.3	364.8	365.2	365.5	365.8	366.1	366.4	366.5
130°	379.1	379.7	380.0	380.4	380.8	381.1	381.4	381.8	382.2	382.6	382.7
132.5°	394.6	395.1	395.5	395.8	396.1	396.3	396.7	397.1	397.5	397.8	397.9
135°	417.6	418.1	418.5	418.9	419.2	419.6	419.9	420.2	420.5	420.8	420.8
137.5°	438.6	439.0	439.3	439.5	439.7	439.9	440.4	440.8	441.2	441.7	441.9
140°	451.6	451.9	452.2	452.5	452.8	453.1	453.5	453.8	454.2	454.6	454.7
142.5°	464.1	464.5	464.8	465.1	465.3	465.6	465.9	466.3	466.6	466.8	466.8
145°	482.0	482.4	482.6	482.8	483.0	483.1	483.3	483.5	483.7	483.9	484.0
147.5°	497.6	497.9	498.1	498.3	498.5	498.7	498.9	499.1	499.3	499.5	499.3
150°	507.2	507.4	507.6	507.7	507.9	508.1	508.3	508.5	508.7	508.9	508.9
152.5°	515.8	515.9	515.9	516.0	516.1	516.3	516.6	517.0	517.3	517.6	517.6
155°	527.4	527.3	527.4	527.4	527.5	527.6	528.1	528.6	529.0	529.5	529.4
157.5°	538.0	537.9	537.8	537.7	537.6	537.5	538.1	538.7	539.2	539.8	539.7
160°	543.8	543.7	543.6	543.5	543.4	543.3	543.8	544.4	545.0	545.5	545.5
162.5°	548.9	548.7	548.7	548.6	548.5	548.4	549.0	549.7	550.4	550.9	551.0
165°	555.7	555.5	555.4	555.3	555.3	555.2	555.9	556.7	557.4	558.2	558.2
167.5°	560.8	560.6	560.6	560.6	560.6	560.6	561.4	562.1	562.8	563.5	563.5
170°	563.8	563.6	563.6	563.6	563.6	563.6	564.4	565.1	565.9	566.7	566.7
172.5°	565.5	565.3	565.4	565.5	565.6	565.6	566.4	567.1	567.9	568.6	568.6
175°	568.1	567.9	568.0	568.1	568.2	568.3	568.9	569.6	570.2	570.9	570.9
177.5°	569.1	569.0	569.1	569.1	569.2	569.3	569.9	570.5	571.1	571.7	571.7
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	973.8	973.5	976.2	974.2	976.2	973.5	973.8	976.6	977.4	977.8	977.8
5°	906.4	908.0	903.0	903.0	903.0	908.0	906.4	909.4	911.9	913.9	916.8
7.5°	846.4	844.2	844.4	841.8	844.4	844.2	846.4	848.9	852.0	856.3	860.4
10°	809.7	806.8	805.8	806.3	805.8	806.8	809.7	815.7	817.7	821.6	826.0
12.5°	779.3	778.7	772.2	772.3	772.2	778.7	779.3	780.9	785.2	793.5	798.8
15°	743.6	734.2	733.2	736.2	733.2	734.2	743.6	743.6	745.6	752.0	755.0
17.5°	707.8	702.9	703.1	701.6	703.1	702.9	707.8	708.6	710.1	715.4	719.3
20°	688.8	685.9	685.4	681.9	685.4	685.9	688.8	688.8	690.8	693.2	697.2
22.5°	671.5	670.5	670.8	666.9	670.8	670.5	671.5	672.7	674.7	676.3	679.1
25°	649.9	652.3	650.4	650.4	650.4	652.3	649.9	650.4	650.8	653.3	655.3
27.5°	635.3	635.2	634.1	634.1	634.1	635.2	635.3	634.0	633.5	632.6	632.2
30°	624.2	623.7	624.7	624.7	624.7	623.7	624.2	622.3	621.2	620.8	618.8
32.5°	613.1	613.9	614.1	614.4	614.1	613.9	613.1	610.8	609.0	607.8	606.1
35°	596.1	596.5	598.0	597.1	598.0	596.5	596.1	593.1	591.2	588.1	585.7
37.5°	573.0	575.2	574.8	575.5	574.8	575.2	573.0	572.1	570.1	567.9	565.0
40°	555.6	557.1	556.6	556.6	556.6	557.1	555.6	555.2	553.2	551.7	549.2
42.5°	537.8	538.9	537.6	536.9	537.6	538.9	537.8	537.0	535.7	533.1	530.3
45°	508.7	507.7	509.3	507.3	509.3	507.7	508.7	506.8	506.2	504.3	501.8
47.5°	476.2	477.1	477.6	479.0	477.6	477.1	476.2	476.4	473.6	472.4	471.6
50°	454.5	457.4	457.4	456.9	457.4	457.4	454.5	453.5	451.5	449.5	449.5
52.5°	433.1	434.5	436.5	436.4	436.5	434.5	433.1	431.4	429.4	426.6	425.8
55°	400.2	401.1	402.2	402.7	402.2	401.1	400.2	396.2	394.7	393.2	390.8
57.5°	366.0	365.6	368.0	368.7	368.0	365.6	366.0	362.5	360.2	355.7	355.1
60°	342.0	342.0	345.9	347.4	345.9	342.0	342.0	338.0	334.5	331.6	330.6
62.5°	316.3	317.9	321.8	319.7	321.8	317.9	316.3	312.0	309.2	305.6	302.9
65°	278.8	282.8	282.3	284.2	282.3	282.8	278.8	276.4	270.9	267.4	264.5
67.5°	239.6	242.0	245.6	245.9	245.6	242.0	239.6	235.6	232.1	228.5	224.9
70°	213.2	215.7	217.6	219.0	217.6	215.7	213.2	209.2	205.3	202.8	198.9
72.5°	187.5	188.8	193.5	191.4	193.5	188.8	187.5	182.8	179.6	177.6	173.2
75°	147.0	150.5	153.4	151.9	153.4	150.5	147.0	143.5	141.1	138.2	134.2
77.5°	108.8	112.2	113.6	112.4	113.6	112.2	108.8	106.5	105.2	99.3	99.0
80°	85.9	85.4	88.3	87.8	88.3	85.4	85.9	82.4	79.9	76.4	76.4
82.5°	63.0	62.5	63.8	64.2	63.8	62.5	63.0	61.1	57.9	56.4	55.1
85°	30.6	32.0	30.1	29.6	30.1	32.0	30.6	28.7	28.7	28.7	28.1
87.5°	9.5	9.6	9.2	8.9	9.2	9.6	9.5	9.5	11.0	9.8	9.7
90°	12.2	12.3	12.5	12.7	12.5	12.3	12.2	12.0	11.7	11.3	10.9
92.5°	13.8	13.9	13.9	14.0	13.9	13.9	13.8	13.6	13.3	12.6	12.1
95°	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	15.7	15.1	14.4
97.5°	17.2	17.2	17.3	17.4	17.3	17.2	17.2	17.1	16.7	15.9	15.2
100°	17.5	17.6	17.7	17.8	17.7	17.6	17.5	17.4	17.0	16.2	15.5
102.5°	17.6	17.8	17.9	18.1	17.9	17.8	17.6	17.4	18.6	20.8	23.2
105°	18.1	18.3	18.5	18.7	18.5	18.3	18.1	17.9	26.1	42.8	59.4
107.5°	96.1	83.6	71.1	58.5	71.1	83.6	96.1	108.8	121.1	133.4	145.5
110°	156.8	143.4	129.9	116.5	129.9	143.4	156.8	170.3	178.5	181.6	184.7



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	208.3	205.5	202.6	199.8	202.6	205.5	208.3	211.1	212.5	212.4	212.4
115°	247.9	248.3	248.6	249.0	248.6	248.3	247.9	247.5	246.9	245.9	245.0
117.5°	276.4	276.4	276.5	276.6	276.5	276.4	276.4	276.3	275.9	275.1	274.4
120°	295.6	295.6	295.6	295.6	295.6	295.6	295.6	295.6	295.2	294.5	293.7
122.5°	314.0	314.1	314.1	314.2	314.1	314.1	314.0	313.9	313.6	313.1	312.5
125°	339.9	340.1	340.3	340.4	340.3	340.1	339.9	339.7	339.5	339.3	339.1
127.5°	366.3	366.1	365.9	365.7	365.9	366.1	366.3	366.5	366.4	366.1	365.8
130°	382.5	382.3	382.1	381.9	382.1	382.3	382.5	382.7	382.6	382.2	381.8
132.5°	397.7	397.4	397.1	396.9	397.1	397.4	397.7	397.9	397.8	397.5	397.1
135°	420.5	420.2	419.9	419.6	419.9	420.2	420.5	420.8	420.8	420.5	420.2
137.5°	441.7	441.5	441.3	441.1	441.3	441.5	441.7	441.9	441.7	441.2	440.8
140°	454.5	454.3	454.1	453.9	454.1	454.3	454.5	454.7	454.6	454.2	453.8
142.5°	466.6	466.4	466.1	465.8	466.1	466.4	466.6	466.8	466.8	466.6	466.3
145°	484.0	484.0	484.0	484.0	484.0	484.0	484.0	484.0	483.9	483.7	483.5
147.5°	498.9	498.4	498.0	497.6	498.0	498.4	498.9	499.3	499.5	499.3	499.1
150°	508.6	508.3	508.0	507.7	508.0	508.3	508.6	508.9	508.9	508.7	508.5
152.5°	517.2	516.7	516.3	515.9	516.3	516.7	517.2	517.6	517.6	517.3	517.0
155°	528.9	528.3	527.7	527.3	527.7	528.3	528.9	529.4	529.5	529.0	528.6
157.5°	538.9	538.3	537.5	536.8	537.5	538.3	538.9	539.7	539.8	539.2	538.7
160°	544.9	544.2	543.6	542.9	543.6	544.2	544.9	545.5	545.5	545.0	544.4
162.5°	550.4	549.8	549.2	548.7	549.2	549.8	550.4	551.0	550.9	550.4	549.7
165°	557.5	556.9	556.3	555.6	556.3	556.9	557.5	558.2	558.2	557.4	556.7
167.5°	562.8	562.1	561.4	560.6	561.4	562.1	562.8	563.5	563.5	562.8	562.1
170°	565.9	565.1	564.4	563.6	564.4	565.1	565.9	566.7	566.7	565.9	565.1
172.5°	567.8	566.9	566.2	565.3	566.2	566.9	567.8	568.6	568.6	567.9	567.1
175°	570.1	569.4	568.6	567.9	568.6	569.4	570.1	570.9	570.9	570.2	569.6
177.5°	570.9	570.1	569.4	568.6	569.4	570.1	570.9	571.7	571.7	571.1	570.5
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	976.6	976.6	984.1	988.8	994.8	998.7	1001.5	1004.3	1009.0	1015.3	1022.4
5°	920.8	922.7	933.6	944.4	954.8	963.7	971.1	980.0	990.8	1004.2	1019.0
7.5°	866.7	874.3	885.2	898.4	912.9	925.9	939.1	953.7	968.9	988.5	1009.3
10°	832.0	840.4	853.7	870.4	885.7	901.0	917.3	933.1	952.3	975.5	1002.2
12.5°	801.5	809.5	823.2	841.6	856.1	873.0	891.6	912.2	933.8	961.7	991.9
15°	759.4	768.7	785.5	794.5	816.6	836.9	854.1	883.7	911.3	940.0	975.1
17.5°	724.8	730.1	743.7	760.2	776.7	799.5	822.1	846.8	874.3	909.3	953.1
20°	701.2	705.6	720.4	737.7	755.4	776.2	796.4	821.0	852.2	889.2	936.5
22.5°	683.4	688.2	698.0	716.3	732.9	750.2	770.3	799.7	832.8	869.0	920.4
25°	657.7	660.7	667.1	681.9	696.7	716.0	733.8	761.4	795.4	837.8	889.2
27.5°	633.4	636.2	641.6	652.2	666.0	681.6	701.0	724.4	759.0	805.1	859.6
30°	618.8	619.3	624.2	634.0	645.9	658.7	676.5	703.1	735.7	782.6	839.8
32.5°	606.1	604.3	607.7	615.1	626.6	639.4	654.0	680.2	711.6	757.7	816.5
35°	584.8	583.7	582.3	588.7	598.5	608.4	621.2	641.0	676.5	719.4	781.1
37.5°	562.9	560.5	557.9	560.8	568.5	578.8	589.9	607.6	638.1	685.4	744.4
40°	546.8	544.8	543.3	542.2	549.2	559.0	567.4	584.2	612.8	657.7	716.0
42.5°	529.0	527.8	525.9	524.5	530.3	537.7	546.5	561.4	589.9	632.1	687.2
45°	500.3	499.4	498.4	497.4	500.9	507.7	514.6	525.5	550.2	591.2	641.0
47.5°	468.4	467.2	467.6	466.0	469.4	474.0	478.8	490.5	514.2	547.2	583.6
50°	445.5	445.1	445.1	445.1	446.1	451.5	455.9	464.9	486.5	519.6	545.7
52.5°	423.9	421.8	421.8	422.5	424.3	427.8	430.6	440.4	459.3	486.4	510.2
55°	389.8	385.9	384.8	385.9	387.4	390.3	393.2	401.1	417.5	437.7	451.5
57.5°	352.1	350.0	348.6	348.8	349.7	352.0	354.3	362.9	375.7	386.3	395.1
60°	325.6	326.7	322.3	323.2	323.2	325.2	328.7	334.0	344.9	352.3	361.2
62.5°	300.8	299.4	298.1	296.7	296.7	297.6	302.2	306.4	315.7	319.5	326.5
65°	262.0	262.0	259.0	260.0	260.5	257.1	259.6	264.5	270.4	271.9	278.3
67.5°	222.7	221.4	219.7	218.2	218.2	217.9	219.1	221.7	226.1	226.6	231.5
70°	195.9	194.9	194.4	192.9	191.0	193.4	191.9	194.4	196.9	197.4	200.3
72.5°	169.8	168.8	168.0	166.5	165.7	165.4	165.5	168.3	170.0	169.4	172.7
75°	132.7	131.8	130.7	128.3	128.3	126.8	127.3	129.3	131.3	129.8	132.7
77.5°	97.5	94.4	94.3	94.9	93.2	93.6	92.9	92.7	93.6	93.7	96.3
80°	75.0	71.5	72.6	72.0	71.5	71.1	70.0	70.6	71.1	71.5	73.0
82.5°	54.1	53.8	52.8	52.7	52.2	50.9	50.3	51.2	51.7	51.5	52.5
85°	27.6	26.1	27.1	26.7	27.1	26.7	25.2	25.2	26.1	25.6	26.7
87.5°	10.4	10.4	9.7	9.8	9.2	9.3	8.8	9.0	9.1	9.0	9.5
90°	10.6	10.2	9.0	7.7	6.5	5.3	4.1	3.2	2.3	1.3	0.4
92.5°	11.4	10.8	9.9	9.0	8.1	7.2	6.8	7.1	7.4	7.6	7.9
95°	13.8	13.1	12.1	11.0	10.0	9.0	10.4	14.2	18.1	22.0	25.8
97.5°	14.4	13.7	20.5	27.1	33.9	40.7	45.0	46.8	48.4	50.1	51.9
100°	14.7	13.9	28.7	43.4	58.1	72.7	79.1	77.2	75.3	73.4	71.5
102.5°	25.5	27.9	43.9	59.9	76.0	92.0	99.3	98.0	96.6	95.3	93.9
105°	76.1	92.7	101.2	109.7	118.1	126.6	130.4	129.3	128.3	127.2	126.2
107.5°	157.8	169.9	168.6	167.3	166.0	164.7	163.5	162.7	161.9	161.1	160.2
110°	187.8	191.0	189.9	188.9	187.8	186.8	186.0	185.2	184.5	183.7	182.9



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	212.4	212.4	211.3	210.3	209.2	208.2	207.4	206.6	205.9	205.3	204.6
115°	244.0	243.1	242.2	241.4	240.5	239.7	238.9	238.4	237.8	237.2	236.7
117.5°	273.6	272.9	272.5	272.0	271.5	271.2	270.6	269.8	269.2	268.5	267.8
120°	292.9	292.2	291.9	291.6	291.3	291.1	290.5	289.6	288.8	287.9	287.1
122.5°	312.0	311.5	311.1	310.8	310.5	310.1	309.5	308.9	308.1	307.5	306.8
125°	338.9	338.7	338.4	338.0	337.6	337.2	336.7	335.9	335.2	334.4	333.7
127.5°	365.5	365.2	364.8	364.3	363.8	363.4	362.8	362.0	361.3	360.5	359.8
130°	381.4	381.1	380.8	380.4	380.0	379.7	379.1	378.3	377.6	376.8	376.1
132.5°	396.7	396.3	396.1	395.8	395.5	395.1	394.6	393.9	393.1	392.4	391.6
135°	419.9	419.6	419.2	418.9	418.5	418.1	417.6	417.1	416.5	415.9	415.4
137.5°	440.4	439.9	439.7	439.5	439.3	439.0	438.6	437.9	437.2	436.5	435.7
140°	453.5	453.1	452.8	452.5	452.2	451.9	451.6	451.0	450.4	449.9	449.3
142.5°	465.9	465.6	465.3	465.1	464.8	464.5	464.1	463.5	463.0	462.4	461.8
145°	483.3	483.1	483.0	482.8	482.6	482.4	482.0	481.4	480.7	480.0	479.4
147.5°	498.9	498.7	498.5	498.3	498.1	497.9	497.6	497.2	496.7	496.3	495.9
150°	508.3	508.1	507.9	507.7	507.6	507.4	507.2	506.9	506.6	506.3	506.1
152.5°	516.6	516.3	516.1	516.0	515.9	515.9	515.8	515.6	515.5	515.3	515.2
155°	528.1	527.6	527.5	527.4	527.4	527.3	527.4	527.5	527.6	527.8	528.0
157.5°	538.1	537.5	537.6	537.7	537.8	537.9	538.0	538.0	538.0	538.0	538.1
160°	543.8	543.3	543.4	543.5	543.6	543.7	543.8	543.8	543.9	544.0	544.1
162.5°	549.0	548.4	548.5	548.6	548.7	548.7	548.9	549.2	549.4	549.7	549.9
165°	555.9	555.2	555.3	555.3	555.4	555.5	555.7	556.0	556.3	556.6	556.9
167.5°	561.4	560.6	560.6	560.6	560.6	560.6	560.8	561.2	561.6	561.9	562.3
170°	564.4	563.6	563.6	563.6	563.6	563.6	563.8	564.2	564.6	565.0	565.3
172.5°	566.4	565.6	565.6	565.5	565.4	565.3	565.5	566.0	566.5	566.9	567.3
175°	568.9	568.3	568.2	568.1	568.0	567.9	568.1	568.5	569.0	569.5	570.0
177.5°	569.9	569.3	569.2	569.1	569.1	569.0	569.1	569.5	569.9	570.2	570.6
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1024.7	1026.7	1033.5	1038.2	1043.7	1046.9	1050.0	1052.4	1055.6	1056.3	1067.8
5°	1029.4	1039.2	1056.5	1069.3	1085.1	1102.3	1114.2	1119.6	1133.9	1145.8	1169.4
7.5°	1028.0	1049.0	1075.1	1102.1	1131.1	1158.0	1181.3	1208.9	1228.6	1258.1	1287.1
10°	1026.8	1055.0	1088.5	1123.0	1163.6	1201.0	1234.5	1272.1	1303.2	1344.2	1379.1
12.5°	1023.3	1057.3	1103.9	1144.8	1193.9	1245.7	1295.3	1343.5	1371.0	1439.3	1471.5
15°	1014.6	1055.0	1113.2	1175.4	1242.9	1304.2	1367.3	1417.7	1499.0	1558.8	1596.8
17.5°	997.8	1054.4	1123.4	1198.4	1280.6	1361.3	1432.9	1509.2	1595.5	1667.8	1744.8
20°	989.9	1052.0	1129.0	1211.9	1297.2	1388.6	1470.0	1561.7	1656.0	1727.0	1825.7
22.5°	975.2	1045.7	1128.6	1221.0	1312.2	1406.7	1501.9	1594.5	1703.4	1801.3	1895.2
25°	951.3	1030.3	1116.2	1219.3	1326.3	1421.1	1535.1	1657.9	1771.4	1897.2	1991.0
27.5°	926.2	1010.6	1096.6	1192.5	1307.7	1420.1	1563.5	1702.3	1841.2	1949.7	2019.1
30°	906.9	988.8	1077.7	1174.4	1288.4	1422.1	1582.4	1733.9	1869.2	1962.4	2001.4
32.5°	886.0	969.1	1047.6	1149.1	1270.6	1420.9	1594.3	1752.5	1870.8	1932.8	1925.2
35°	853.2	922.7	999.2	1096.9	1240.0	1412.2	1601.2	1754.2	1826.7	1813.4	1712.7
37.5°	805.8	864.3	939.6	1046.6	1204.5	1393.9	1587.4	1702.1	1697.4	1588.9	1443.1
40°	776.2	826.0	898.5	1011.1	1176.9	1382.1	1565.7	1640.2	1577.1	1425.5	1250.8
42.5°	737.5	783.3	855.9	971.6	1146.4	1358.0	1524.2	1545.9	1422.3	1247.9	1087.8
45°	677.5	717.9	793.0	912.4	1100.9	1305.6	1423.1	1370.3	1204.0	1023.9	902.0
47.5°	613.0	655.1	727.3	849.9	1034.9	1226.8	1282.7	1170.4	999.7	853.7	741.8
50°	572.4	612.8	683.4	807.3	990.3	1162.1	1185.2	1040.2	883.3	755.0	663.2
52.5°	531.3	569.4	638.8	763.1	938.2	1087.0	1072.7	924.9	780.6	671.3	599.3
55°	470.2	506.2	572.4	688.8	848.2	966.1	914.4	773.3	653.8	568.9	514.2
57.5°	415.6	450.2	507.2	612.4	750.9	832.0	766.0	647.1	552.1	486.8	446.0
60°	378.4	409.1	463.4	561.0	681.5	743.1	678.0	572.9	492.9	440.6	404.2
62.5°	343.4	369.9	420.3	509.0	613.5	665.3	599.5	510.5	442.4	396.1	365.0
65°	290.1	314.3	358.7	427.8	513.7	548.2	491.4	419.4	366.6	332.1	311.3
67.5°	241.6	262.1	300.5	354.9	418.0	443.2	400.0	344.2	304.4	276.7	260.2
70°	209.2	227.0	257.1	304.0	361.2	380.4	340.0	294.1	264.9	242.8	227.4
72.5°	182.0	195.0	222.3	258.5	306.3	321.6	293.4	253.1	225.9	209.2	197.1
75°	138.6	149.5	167.3	196.4	229.4	238.4	217.1	191.9	173.7	161.8	152.5
77.5°	100.0	107.9	120.8	138.7	161.6	169.7	156.2	139.4	126.1	118.1	112.9
80°	75.5	81.9	92.7	107.5	121.4	125.8	117.9	105.1	95.8	91.3	86.8
82.5°	55.8	59.4	65.9	76.0	85.5	90.7	84.0	76.3	71.3	67.2	65.5
85°	28.1	30.1	33.1	37.0	42.9	44.9	42.4	40.4	37.5	35.1	35.1
87.5°	10.6	10.7	12.1	13.1	14.9	16.3	16.1	15.6	15.5	15.2	14.8
90°	1.3	2.3	3.2	4.1	5.3	6.5	7.7	9.0	10.2	10.6	10.9
92.5°	7.6	7.4	7.1	6.8	7.2	8.1	9.0	9.9	10.8	11.4	12.1
95°	22.0	18.1	14.2	10.4	9.0	10.0	11.0	12.1	13.1	13.8	14.4
97.5°	50.1	48.4	46.8	45.0	40.7	33.9	27.1	20.5	13.7	14.4	15.2
100°	73.4	75.3	77.2	79.1	72.7	58.1	43.4	28.7	13.9	14.7	15.5
102.5°	95.3	96.6	98.0	99.3	92.0	76.0	59.9	43.9	27.9	25.5	23.2
105°	127.2	128.3	129.3	130.4	126.6	118.1	109.7	101.2	92.7	76.1	59.4
107.5°	161.1	161.9	162.7	163.5	164.7	166.0	167.3	168.6	169.9	157.8	145.5
110°	183.7	184.5	185.2	186.0	186.8	187.8	188.9	189.9	191.0	187.8	184.7



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	205.3	205.9	206.6	207.4	208.2	209.2	210.3	211.3	212.4	212.4	212.4
115°	237.2	237.8	238.4	238.9	239.7	240.5	241.4	242.2	243.1	244.0	245.0
117.5°	268.5	269.2	269.8	270.6	271.2	271.5	272.0	272.5	272.9	273.6	274.4
120°	287.9	288.8	289.6	290.5	291.1	291.3	291.6	291.9	292.2	292.9	293.7
122.5°	307.5	308.1	308.9	309.5	310.1	310.5	310.8	311.1	311.5	312.0	312.5
125°	334.4	335.2	335.9	336.7	337.2	337.6	338.0	338.4	338.7	338.9	339.1
127.5°	360.5	361.3	362.0	362.8	363.4	363.8	364.3	364.8	365.2	365.5	365.8
130°	376.8	377.6	378.3	379.1	379.7	380.0	380.4	380.8	381.1	381.4	381.8
132.5°	392.4	393.1	393.9	394.6	395.1	395.5	395.8	396.1	396.3	396.7	397.1
135°	415.9	416.5	417.1	417.6	418.1	418.5	418.9	419.2	419.6	419.9	420.2
137.5°	436.5	437.2	437.9	438.6	439.0	439.3	439.5	439.7	439.9	440.4	440.8
140°	449.9	450.4	451.0	451.6	451.9	452.2	452.5	452.8	453.1	453.5	453.8
142.5°	462.4	463.0	463.5	464.1	464.5	464.8	465.1	465.3	465.6	465.9	466.3
145°	480.0	480.7	481.4	482.0	482.4	482.6	482.8	483.0	483.1	483.3	483.5
147.5°	496.3	496.7	497.2	497.6	497.9	498.1	498.3	498.5	498.7	498.9	499.1
150°	506.3	506.6	506.9	507.2	507.4	507.6	507.7	507.9	508.1	508.3	508.5
152.5°	515.3	515.5	515.6	515.8	515.9	515.9	516.0	516.1	516.3	516.6	517.0
155°	527.8	527.6	527.5	527.4	527.3	527.4	527.4	527.5	527.6	528.1	528.6
157.5°	538.0	538.0	538.0	538.0	537.9	537.8	537.7	537.6	537.5	538.1	538.7
160°	544.0	543.9	543.8	543.8	543.7	543.6	543.5	543.4	543.3	543.8	544.4
162.5°	549.7	549.4	549.2	548.9	548.7	548.7	548.6	548.5	548.4	549.0	549.7
165°	556.6	556.3	556.0	555.7	555.5	555.4	555.3	555.3	555.2	555.9	556.7
167.5°	561.9	561.6	561.2	560.8	560.6	560.6	560.6	560.6	560.6	561.4	562.1
170°	565.0	564.6	564.2	563.8	563.6	563.6	563.6	563.6	563.6	564.4	565.1
172.5°	566.9	566.5	566.0	565.5	565.3	565.4	565.5	565.6	565.6	566.4	567.1
175°	569.5	569.0	568.5	568.1	567.9	568.0	568.1	568.2	568.3	568.9	569.6
177.5°	570.2	569.9	569.5	569.1	569.0	569.1	569.1	569.2	569.3	569.9	570.5
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0	570.0



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4	1018.4
2.5°	1071.8	1072.1	1076.5	1079.7	1078.1	1080.1	1080.8
5°	1170.9	1188.7	1198.1	1204.9	1205.5	1206.0	1209.9
7.5°	1311.5	1330.6	1344.5	1365.6	1372.0	1379.1	1377.1
10°	1414.2	1442.3	1466.5	1479.3	1493.2	1513.3	1497.1
12.5°	1510.1	1560.0	1596.8	1616.7	1629.8	1633.8	1625.8
15°	1668.3	1733.4	1768.5	1767.5	1811.9	1831.2	1801.0
17.5°	1813.4	1873.5	1921.7	1946.4	1983.3	1991.5	1987.7
20°	1902.2	1967.8	2005.4	2047.8	2067.0	2084.2	2087.3
22.5°	1978.8	2037.7	2077.9	2113.3	2129.4	2137.6	2142.5
25°	2057.7	2104.0	2128.2	2140.5	2144.9	2144.0	2137.6
27.5°	2052.2	2055.8	2029.1	2003.0	1979.6	1953.2	1944.2
30°	1998.9	1957.5	1883.5	1841.5	1779.8	1731.0	1750.7
32.5°	1858.8	1776.3	1693.2	1601.5	1525.6	1504.0	1482.2
35°	1586.4	1441.3	1356.5	1257.7	1218.3	1178.8	1151.7
37.5°	1283.5	1171.2	1070.5	1006.0	966.5	941.5	928.0
40°	1109.7	1008.6	925.7	873.4	843.3	815.2	811.2
42.5°	971.2	877.1	814.7	773.1	744.2	732.3	723.6
45°	795.4	729.8	687.9	658.3	639.0	631.6	621.7
47.5°	673.3	626.9	595.4	575.2	560.7	555.3	554.4
50°	604.9	566.5	543.3	527.4	516.1	514.2	506.2
52.5°	553.6	520.3	502.2	488.4	480.2	474.7	472.3
55°	480.6	458.4	442.1	434.2	427.8	422.4	422.4
57.5°	420.5	402.0	391.2	384.5	382.5	378.6	376.2
60°	383.4	367.6	359.2	353.3	349.4	349.9	345.4
62.5°	347.0	336.9	328.9	322.9	318.2	318.3	318.6
65°	295.6	287.7	281.7	279.7	276.8	273.3	274.4
67.5°	250.4	243.1	238.5	235.1	234.1	232.2	235.1
70°	218.1	212.6	209.2	206.2	205.3	205.8	208.2
72.5°	188.5	184.6	182.4	181.0	178.8	178.9	180.6
75°	148.1	145.1	143.1	141.6	141.1	141.1	141.1
77.5°	108.8	108.1	107.2	105.0	105.1	105.7	105.8
80°	85.9	84.4	83.9	82.9	81.4	80.4	82.9
82.5°	64.2	62.7	62.2	62.0	59.7	59.5	61.5
85°	34.5	33.1	33.6	33.1	33.1	32.6	32.6
87.5°	14.5	14.1	13.9	14.2	13.9	13.6	14.4
90°	11.3	11.7	12.0	12.2	12.3	12.5	12.7
92.5°	12.6	13.3	13.6	13.8	13.9	13.9	14.0
95°	15.1	15.7	16.1	16.1	16.1	16.1	16.1
97.5°	15.9	16.7	17.1	17.2	17.2	17.3	17.4
100°	16.2	17.0	17.4	17.5	17.6	17.7	17.8
102.5°	20.8	18.6	17.4	17.6	17.8	17.9	18.1
105°	42.8	26.1	17.9	18.1	18.3	18.5	18.7
107.5°	133.4	121.1	108.8	96.1	83.6	71.1	58.5
110°	181.6	178.5	170.3	156.8	143.4	129.9	116.5



TEST NUMBER: P332150-830

CATALOG NUMBER: S123DIW-S775D460U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	212.4	212.5	211.1	208.3	205.5	202.6	199.8
115°	245.9	246.9	247.5	247.9	248.3	248.6	249.0
117.5°	275.1	275.9	276.3	276.4	276.4	276.5	276.6
120°	294.5	295.2	295.6	295.6	295.6	295.6	295.6
122.5°	313.1	313.6	313.9	314.0	314.1	314.1	314.2
125°	339.3	339.5	339.7	339.9	340.1	340.3	340.4
127.5°	366.1	366.4	366.5	366.3	366.1	365.9	365.7
130°	382.2	382.6	382.7	382.5	382.3	382.1	381.9
132.5°	397.5	397.8	397.9	397.7	397.4	397.1	396.9
135°	420.5	420.8	420.8	420.5	420.2	419.9	419.6
137.5°	441.2	441.7	441.9	441.7	441.5	441.3	441.1
140°	454.2	454.6	454.7	454.5	454.3	454.1	453.9
142.5°	466.6	466.8	466.8	466.6	466.4	466.1	465.8
145°	483.7	483.9	484.0	484.0	484.0	484.0	484.0
147.5°	499.3	499.5	499.3	498.9	498.4	498.0	497.6
150°	508.7	508.9	508.9	508.6	508.3	508.0	507.7
152.5°	517.3	517.6	517.6	517.2	516.7	516.3	515.9
155°	529.0	529.5	529.4	528.9	528.3	527.7	527.3
157.5°	539.2	539.8	539.7	538.9	538.3	537.5	536.8
160°	545.0	545.5	545.5	544.9	544.2	543.6	542.9
162.5°	550.4	550.9	551.0	550.4	549.8	549.2	548.7
165°	557.4	558.2	558.2	557.5	556.9	556.3	555.6
167.5°	562.8	563.5	563.5	562.8	562.1	561.4	560.6
170°	565.9	566.7	566.7	565.9	565.1	564.4	563.6
172.5°	567.9	568.6	568.6	567.8	566.9	566.2	565.3
175°	570.2	570.9	570.9	570.1	569.4	568.6	567.9
177.5°	571.1	571.7	571.7	570.9	570.1	569.4	568.6
180°	570.0	570.0	570.0	570.0	570.0	570.0	570.0

(END OF REPORT)