

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332460-830

Luminaire Tested: **S123RDIW-S1000D1030U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332460-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1030U830-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7462.7 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41		
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35	35	35	35	35	35	35		
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30	30	30	30		
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	30	26	26	26	26	26	26	26		
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23	23	23	23		
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20	20	20	20	20		
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18	18	18	18	18	18	18		
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16	16	16	16	16	16	16		
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15	15	15	15	15	15	15		
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	21	17	15	13	13	13	13	13	13	13		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17026	17026	17026
5°	17091	16855	16953
10°	16994	16644	16587
15°	16811	16254	16082
20°	16561	15767	15400
25°	16302	15221	14733
30°	15960	14589	13793
35°	15609	13958	12929
40°	15286	13212	11861
45°	14862	12478	10898
50°	14393	11643	9818
55°	13915	10689	8811
60°	13476	9666	7705
65°	12905	8560	6599
70°	12192	7188	5331
75°	11154	5656	5016
80°	9937	5009	4612
85°	8398	4434	4125



TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.0
10°-20°	413.3	5.5
20°-30°	595.1	8.0
30°-40°	670.3	9.0
40°-50°	641.3	8.6
50°-60°	525.1	7.0
60°-70°	354.3	4.7
70°-80°	178.2	2.4
80°-90°	50.7	0.7
90°-100°	46.3	0.6
100°-110°	220.8	3.0
110°-120°	530.4	7.1
120°-130°	675.4	9.0
130°-140°	721.6	9.7
140°-150°	674.8	9.0
150°-160°	544.3	7.3
160°-170°	351.3	4.7
170°-180°	121.1	1.6
0°-30°	1156.9	15.5
0°-40°	1827.2	24.5
0°-60°	2993.6	40.1
0°-90°	3576.9	47.9
90°-120°	797.5	10.7
90°-150°	2869.2	38.4
90°-180°	3886.0	52.1
0°-180°	7462.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1582	1582	1582	1582	1582	
5°	1582	1575	1560	1571	1569	150
15°	1509	1493	1459	1452	1443	425
25°	1373	1339	1282	1255	1240	631
35°	1188	1140	1062	1009	984	743
45°	976	916	820	749	716	753
55°	742	676	570	498	470	665
65°	507	435	336	276	259	501
75°	268	206	136	124	121	286
85°	68	41	36	34	33	76
90°	1	11	23	26	28	6
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	529	535	543	553	557	522
125°	746	753	757	759	761	666
135°	929	934	938	941	938	715
145°	1072	1078	1080	1082	1082	671
155°	1180	1179	1180	1184	1179	544
165°	1245	1242	1241	1248	1242	352
175°	1274	1270	1270	1276	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1586.9	1585.9	1585.1	1584.1	1583.2	1581.4	1578.7	1575.9	1573.2	1570.5	1572.9
5°	1581.8	1580.3	1578.9	1577.4	1576.0	1573.6	1570.2	1566.8	1563.4	1559.9	1562.5
7.5°	1567.1	1565.6	1564.1	1562.5	1560.9	1557.9	1553.5	1549.1	1544.6	1540.2	1541.6
10°	1554.8	1552.8	1550.8	1548.8	1546.8	1543.2	1538.1	1533.0	1527.9	1522.8	1523.1
12.5°	1537.4	1535.1	1533.0	1530.7	1528.4	1524.2	1518.0	1511.6	1505.4	1499.1	1498.9
15°	1508.6	1505.5	1502.3	1499.2	1496.1	1490.5	1482.5	1474.5	1466.6	1458.6	1457.2
17.5°	1472.4	1468.8	1465.2	1461.5	1457.8	1451.0	1440.8	1430.7	1420.5	1410.3	1407.3
20°	1445.8	1441.2	1436.6	1432.1	1427.5	1419.8	1409.0	1398.2	1387.3	1376.5	1372.8
22.5°	1416.0	1410.8	1405.5	1400.2	1395.1	1386.7	1375.1	1363.6	1352.1	1340.6	1336.0
25°	1372.6	1365.6	1358.4	1351.2	1344.2	1334.0	1320.9	1307.8	1294.7	1281.6	1275.5
27.5°	1320.0	1312.2	1304.3	1296.5	1288.5	1277.3	1262.7	1248.1	1233.5	1219.0	1210.6
30°	1284.1	1275.5	1267.1	1258.5	1249.9	1237.7	1221.7	1205.7	1189.8	1173.8	1164.1
32.5°	1248.2	1238.5	1228.8	1219.1	1209.5	1196.2	1179.3	1162.4	1145.5	1128.6	1118.0
35°	1187.9	1177.6	1167.3	1157.2	1146.9	1132.8	1115.2	1097.5	1079.9	1062.2	1049.9
37.5°	1126.8	1115.4	1104.0	1092.6	1081.2	1066.1	1047.3	1028.3	1009.5	990.6	976.7
40°	1087.9	1075.3	1062.7	1050.2	1037.6	1021.2	1001.1	980.8	960.5	940.3	925.5
42.5°	1043.7	1031.1	1018.6	1006.1	993.5	976.9	955.9	935.0	914.1	893.2	876.9
45°	976.3	963.4	950.6	937.7	924.9	907.6	885.6	863.7	841.7	819.7	803.5
47.5°	908.8	894.7	880.6	866.5	852.4	834.4	812.5	790.5	768.5	746.6	729.0
50°	859.5	846.1	832.7	819.4	805.9	787.7	764.6	741.5	718.4	695.3	677.6
52.5°	815.4	800.9	786.3	771.8	757.2	738.5	715.7	692.8	670.0	647.1	628.7
55°	741.5	727.5	713.5	699.6	685.6	666.5	642.2	618.0	593.8	569.6	553.1
57.5°	673.3	658.0	642.8	627.5	612.4	592.6	568.2	543.8	519.5	495.2	479.6
60°	626.0	610.4	594.7	579.0	563.3	543.7	520.0	496.3	472.7	449.0	433.6
62.5°	578.8	563.2	547.4	531.8	516.1	496.4	472.8	449.1	425.5	401.8	387.3
65°	506.7	491.1	475.3	459.7	444.0	425.1	402.8	380.6	358.4	336.1	322.2
67.5°	434.6	418.8	402.9	387.1	371.3	352.6	331.3	310.0	288.7	267.3	256.9
70°	387.4	372.0	356.7	341.2	325.8	308.2	288.2	268.2	248.3	228.4	218.4
72.5°	340.2	325.1	309.9	294.7	279.6	262.9	244.8	226.7	208.5	190.4	182.2
75°	268.2	254.4	240.7	227.1	213.4	198.7	183.0	167.3	151.7	136.0	133.1
77.5°	202.5	190.0	177.7	165.3	153.0	141.7	131.6	121.5	111.4	101.3	99.8
80°	160.3	148.6	137.0	125.3	113.6	104.8	98.8	92.7	86.8	80.8	79.9
82.5°	120.4	110.3	100.2	90.0	79.9	73.5	70.7	68.0	65.1	62.3	61.5
85°	68.0	61.7	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.8	22.7	20.6	18.6	16.5	15.7	16.2	16.8	17.3	17.9	17.8
90°	0.9	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6
92.5°	17.6	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5
95°	57.8	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8
97.5°	116.0	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1
100°	159.9	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9
102.5°	210.0	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1
105°	282.1	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1
107.5°	358.3	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7
110°	409.0	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0



TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.4	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8
115°	529.2	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5
117.5°	598.7	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7
120°	641.9	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9
122.5°	685.8	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6
125°	746.0	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8
127.5°	804.3	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1
130°	840.7	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9
132.5°	875.5	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9
135°	928.7	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8
137.5°	974.1	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4
140°	1004.5	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8
142.5°	1032.5	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7
145°	1071.7	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6
147.5°	1108.6	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2
150°	1131.3	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4
152.5°	1151.8	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0
155°	1180.5	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6
157.5°	1202.9	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0
160°	1216.5	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9
162.5°	1229.4	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4
165°	1244.9	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8
167.5°	1257.0	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9
170°	1263.9	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7
172.5°	1268.4	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3
175°	1274.2	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0
177.5°	1275.7	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8	1581.8
2.5°	1575.5	1578.0	1580.5	1581.5	1581.0	1580.6	1580.2	1579.7
5°	1565.1	1567.6	1570.2	1571.2	1570.7	1570.1	1569.5	1569.0
7.5°	1543.0	1544.5	1545.9	1546.1	1545.1	1544.2	1543.2	1542.2
10°	1523.3	1523.6	1523.9	1523.3	1521.8	1520.4	1519.0	1517.6
12.5°	1498.7	1498.6	1498.5	1497.5	1495.9	1494.2	1492.6	1490.9
15°	1455.8	1454.3	1452.9	1451.1	1449.2	1447.2	1445.2	1443.2
17.5°	1404.3	1401.3	1398.3	1395.2	1392.3	1389.3	1386.4	1383.4
20°	1369.0	1365.4	1361.7	1358.1	1354.7	1351.2	1347.8	1344.4
22.5°	1331.3	1326.7	1322.1	1318.1	1315.0	1311.8	1308.6	1305.4
25°	1269.6	1263.6	1257.6	1253.0	1249.9	1246.8	1243.7	1240.5
27.5°	1202.3	1194.0	1185.6	1179.1	1174.3	1169.5	1164.7	1160.0
30°	1154.4	1144.7	1135.0	1127.9	1123.3	1118.8	1114.2	1109.7
32.5°	1107.4	1096.8	1086.2	1078.6	1073.7	1068.9	1064.1	1059.3
35°	1037.6	1025.4	1013.1	1004.5	999.4	994.2	989.1	983.9
37.5°	962.8	948.9	935.0	924.8	918.5	912.2	905.9	899.6
40°	910.7	895.9	881.0	870.3	863.7	857.2	850.6	844.1
42.5°	860.7	844.5	828.3	817.3	811.4	805.6	799.7	793.8
45°	787.2	771.0	754.7	743.2	736.3	729.5	722.6	715.9
47.5°	711.2	693.6	675.9	664.0	657.9	651.9	645.7	639.6
50°	660.0	642.2	624.6	612.5	606.0	599.4	592.9	586.3
52.5°	610.4	592.0	573.6	561.5	555.6	549.8	543.9	538.0
55°	536.5	520.0	503.4	492.3	486.6	480.9	475.2	469.5
57.5°	463.9	448.3	432.7	422.4	417.6	412.7	407.9	403.0
60°	418.2	402.8	387.4	377.3	372.5	367.6	362.8	357.9
62.5°	372.8	358.4	343.8	334.0	329.0	324.0	318.9	313.8
65°	308.2	294.2	280.2	271.6	268.5	265.4	262.3	259.1
67.5°	246.5	236.0	225.6	218.7	215.4	212.0	208.6	205.3
70°	208.4	198.4	188.4	181.9	178.7	175.6	172.5	169.4
72.5°	174.1	165.9	157.8	153.1	151.7	150.4	149.1	147.8
75°	130.3	127.4	124.6	122.9	122.3	121.7	121.1	120.6
77.5°	98.3	96.7	95.2	94.2	93.6	93.0	92.5	91.9
80°	79.1	78.2	77.4	76.7	76.2	75.6	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.2	58.1	58.0
85°	34.8	34.2	33.6	33.4	33.4	33.4	33.4	33.4
87.5°	17.7	17.7	17.6	17.5	17.4	17.2	17.2	17.0
90°	24.4	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	27.0	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	32.3	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	34.6	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	51.8	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	325.4	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	413.1	406.1	399.2	380.7	350.6	320.5	290.4	260.3





TEST NUMBER: P332460-830

CATALOG NUMBER: S123RDIW-S1000D1030U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	474.9	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	547.6	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	613.4	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	656.6	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	698.7	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.2	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	817.7	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	853.8	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	887.8	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	985.4	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1014.6	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1042.4	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.0	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1115.7	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1136.9	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1155.7	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1181.7	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1204.3	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1217.1	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1228.8	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1244.4	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1268.0	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1273.4	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1275.4	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)