

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332465-935

Luminaire Tested: **S123RDIW-S1000D1320U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332465-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7207.0 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15553	15553	15553
5°	15612	15397	15486
10°	15524	15204	15152
15°	15357	14848	14692
20°	15128	14403	14068
25°	14892	13904	13459
30°	14579	13328	12599
35°	14259	12750	11811
40°	13964	12069	10835
45°	13575	11399	9954
50°	13147	10637	8967
55°	12710	9764	8049
60°	12312	8831	7037
65°	11790	7819	6029
70°	11138	6565	4869
75°	10189	5165	4579
80°	9081	4575	4209
85°	7669	4051	3767



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.7	1.9
10°-20°	377.5	5.2
20°-30°	543.6	7.5
30°-40°	612.3	8.5
40°-50°	585.8	8.1
50°-60°	479.7	6.7
60°-70°	323.7	4.5
70°-80°	162.8	2.3
80°-90°	47.3	0.7
90°-100°	92.6	1.3
100°-110°	277.2	3.8
110°-120°	471.4	6.5
120°-130°	620.1	8.6
130°-140°	697.0	9.7
140°-150°	685.1	9.5
150°-160°	576.8	8.0
160°-170°	383.9	5.3
170°-180°	134.4	1.9
0°-30°	1056.8	14.7
0°-40°	1669.1	23.2
0°-60°	2734.6	37.9
0°-90°	3268.4	45.3
90°-120°	841.3	11.7
90°-150°	2843.5	39.5
90°-180°	3939.0	54.7
0°-180°	7207.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1445	1445	1445	1445	1445	
5°	1445	1439	1425	1435	1433	137
15°	1378	1364	1332	1326	1318	388
25°	1254	1223	1171	1147	1133	576
35°	1085	1041	970	922	899	679
45°	892	837	749	684	654	688
55°	677	618	520	455	429	607
65°	463	397	307	252	237	458
75°	245	188	124	113	110	261
85°	62	38	33	31	30	70
90°	1	12	27	31	34	7
95°	66	74	83	87	87	74
105°	251	254	264	264	266	269
115°	475	478	476	477	476	469
125°	695	698	696	691	687	619
135°	901	907	907	902	900	694
145°	1093	1096	1099	1098	1093	683
155°	1252	1252	1253	1257	1250	576
165°	1364	1360	1360	1366	1359	384
175°	1418	1414	1414	1420	1413	135
180°	1422	1422	1422	1422	1422	



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1449.6	1448.7	1447.9	1447.1	1446.2	1444.6	1442.1	1439.6	1437.1	1434.6	1436.8
5°	1444.9	1443.6	1442.3	1441.0	1439.7	1437.4	1434.3	1431.2	1428.1	1425.0	1427.3
7.5°	1431.5	1430.1	1428.7	1427.3	1425.9	1423.1	1419.1	1415.1	1411.0	1407.0	1408.3
10°	1420.3	1418.5	1416.6	1414.8	1413.0	1409.7	1405.1	1400.3	1395.7	1391.0	1391.3
12.5°	1404.4	1402.3	1400.3	1398.3	1396.2	1392.3	1386.6	1380.9	1375.2	1369.4	1369.2
15°	1378.1	1375.3	1372.3	1369.5	1366.7	1361.6	1354.3	1346.9	1339.7	1332.4	1331.1
17.5°	1345.1	1341.7	1338.4	1335.1	1331.7	1325.4	1316.1	1306.9	1297.6	1288.3	1285.6
20°	1320.7	1316.6	1312.3	1308.2	1304.0	1297.0	1287.1	1277.2	1267.3	1257.4	1254.0
22.5°	1293.5	1288.7	1283.9	1279.1	1274.4	1266.7	1256.1	1245.6	1235.1	1224.6	1220.4
25°	1253.9	1247.4	1240.9	1234.3	1227.9	1218.6	1206.6	1194.6	1182.7	1170.7	1165.2
27.5°	1205.8	1198.7	1191.5	1184.3	1177.1	1166.8	1153.5	1140.1	1126.8	1113.5	1105.9
30°	1173.0	1165.2	1157.4	1149.6	1141.8	1130.6	1116.0	1101.4	1086.8	1072.3	1063.4
32.5°	1140.2	1131.4	1122.5	1113.6	1104.8	1092.7	1077.3	1061.9	1046.4	1031.0	1021.3
35°	1085.1	1075.7	1066.3	1057.0	1047.7	1034.8	1018.7	1002.5	986.4	970.3	959.1
37.5°	1029.3	1018.9	1008.5	998.1	987.7	973.9	956.7	939.4	922.1	904.9	892.2
40°	993.8	982.3	970.8	959.3	947.9	932.9	914.5	896.0	877.4	858.9	845.4
42.5°	953.4	941.9	930.5	919.0	907.6	892.3	873.2	854.1	835.0	815.9	801.1
45°	891.8	880.0	868.3	856.6	844.9	829.1	809.0	788.9	768.9	748.8	734.0
47.5°	830.2	817.3	804.4	791.5	778.7	762.2	742.2	722.1	702.1	682.0	665.9
50°	785.1	772.9	760.7	748.5	736.2	719.5	698.4	677.3	656.3	635.2	619.0
52.5°	744.9	731.6	718.2	705.0	691.7	674.6	653.8	632.8	612.0	591.1	574.3
55°	677.3	664.6	651.8	639.0	626.3	608.8	586.7	564.6	542.4	520.3	505.2
57.5°	615.0	601.1	587.2	573.3	559.4	541.3	519.0	496.8	474.6	452.4	438.1
60°	571.9	557.6	543.2	528.9	514.5	496.6	475.0	453.4	431.8	410.2	396.1
62.5°	528.7	514.4	500.1	485.8	471.5	453.5	431.9	410.3	388.7	367.0	353.8
65°	462.9	448.6	434.2	419.9	405.6	388.3	368.0	347.7	327.4	307.0	294.3
67.5°	397.0	382.5	368.1	353.6	339.1	322.1	302.6	283.2	263.7	244.2	234.7
70°	353.9	339.8	325.8	311.7	297.6	281.5	263.3	245.0	226.8	208.6	199.5
72.5°	310.7	297.0	283.1	269.2	255.4	240.1	223.6	207.1	190.5	173.9	166.4
75°	245.0	232.4	219.9	207.4	194.9	181.5	167.2	152.8	138.5	124.2	121.6
77.5°	184.9	173.6	162.3	151.0	139.7	129.4	120.2	111.0	101.8	92.6	91.2
80°	146.5	135.8	125.1	114.4	103.8	95.7	90.2	84.7	79.3	73.8	73.0
82.5°	109.9	100.7	91.5	82.2	73.0	67.2	64.6	62.1	59.5	56.9	56.1
85°	62.1	56.4	50.6	44.9	39.2	35.9	35.1	34.4	33.6	32.8	32.3
87.5°	22.7	20.9	19.1	17.3	15.6	15.0	15.6	16.3	16.9	17.6	17.6
90°	1.1	3.6	6.1	8.5	11.0	13.9	17.1	20.3	23.6	26.8	27.8
92.5°	27.0	28.7	30.4	32.1	33.8	35.6	37.4	39.2	41.1	42.9	43.7
95°	65.9	67.6	69.4	71.1	72.8	74.7	76.7	78.7	80.7	82.7	83.6
97.5°	117.0	118.3	119.6	120.9	122.2	123.6	125.0	126.4	127.9	129.3	130.4
100°	151.9	153.3	154.8	156.4	157.8	159.2	160.4	161.7	162.9	164.2	164.9
102.5°	192.1	193.0	193.9	194.8	195.6	196.9	198.5	200.2	201.8	203.5	204.2
105°	251.2	251.8	252.3	252.7	253.2	254.6	256.8	259.1	261.3	263.6	263.6
107.5°	320.0	320.4	320.6	321.0	321.2	321.8	322.7	323.6	324.5	325.4	326.2
110°	362.9	363.4	363.9	364.4	364.9	365.4	365.9	366.4	366.9	367.4	368.4



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	407.6	407.9	408.2	408.5	408.8	409.0	409.1	409.1	409.3	409.4	410.6
115°	474.6	475.4	476.0	476.8	477.6	477.7	477.2	476.7	476.2	475.7	476.0
117.5°	542.1	542.5	543.0	543.5	544.1	544.0	543.3	542.7	542.0	541.4	541.3
120°	584.0	585.5	587.0	588.5	590.0	590.1	588.8	587.6	586.4	585.1	584.9
122.5°	627.8	628.9	630.0	631.1	632.1	632.4	631.7	631.1	630.4	629.8	629.1
125°	694.6	695.3	696.0	696.8	697.6	697.7	697.2	696.7	696.2	695.7	694.7
127.5°	756.2	757.9	759.4	761.0	762.6	763.1	762.6	762.0	761.5	761.0	759.5
130°	797.3	799.3	801.3	803.3	805.3	805.9	805.1	804.4	803.7	802.9	801.9
132.5°	838.4	840.4	842.4	844.4	846.4	847.1	846.5	846.0	845.4	844.9	843.7
135°	901.2	902.7	904.1	905.6	907.1	907.8	907.5	907.2	907.0	906.7	905.8
137.5°	959.2	960.4	961.7	962.9	964.2	965.2	965.8	966.5	967.1	967.8	966.6
140°	999.4	1000.7	1001.9	1003.2	1004.4	1005.1	1005.4	1005.6	1005.9	1006.2	1005.9
142.5°	1036.0	1037.3	1038.5	1039.8	1041.0	1041.9	1042.3	1042.8	1043.2	1043.7	1043.4
145°	1093.2	1093.7	1094.2	1094.8	1095.2	1095.9	1096.6	1097.3	1098.1	1098.8	1098.5
147.5°	1143.2	1144.2	1145.0	1146.0	1146.9	1147.6	1148.3	1149.0	1149.7	1150.4	1150.4
150°	1178.1	1178.6	1179.1	1179.6	1180.1	1180.6	1181.1	1181.6	1182.1	1182.6	1182.6
152.5°	1206.7	1207.4	1208.1	1208.8	1209.4	1210.0	1210.3	1210.6	1210.9	1211.2	1211.6
155°	1251.8	1251.8	1251.8	1251.8	1251.8	1252.0	1252.2	1252.4	1252.7	1252.9	1254.0
157.5°	1290.2	1290.0	1289.6	1289.3	1289.0	1289.0	1289.2	1289.3	1289.6	1289.8	1290.8
160°	1314.3	1313.9	1313.4	1312.9	1312.3	1312.1	1312.1	1312.1	1312.1	1312.1	1313.4
162.5°	1335.8	1335.1	1334.4	1333.7	1333.0	1332.7	1333.0	1333.2	1333.3	1333.5	1334.8
165°	1363.5	1362.7	1362.0	1361.2	1360.6	1360.1	1360.1	1360.1	1360.1	1360.1	1361.6
167.5°	1385.6	1384.6	1383.6	1382.6	1381.6	1381.2	1381.4	1381.6	1381.8	1382.0	1383.5
170°	1398.1	1397.1	1396.1	1395.2	1394.1	1393.6	1393.6	1393.6	1393.6	1393.6	1395.3
172.5°	1407.9	1407.0	1405.9	1405.0	1403.9	1403.4	1403.4	1403.4	1403.4	1403.4	1405.0
175°	1418.2	1417.2	1416.3	1415.2	1414.2	1413.8	1413.8	1413.8	1413.8	1413.8	1415.2
177.5°	1422.5	1421.7	1420.8	1420.0	1419.3	1418.8	1418.8	1418.8	1418.8	1418.8	1420.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9	1444.9
2.5°	1439.2	1441.5	1443.7	1444.7	1444.2	1443.9	1443.5	1443.0
5°	1429.7	1432.0	1434.3	1435.3	1434.8	1434.3	1433.7	1433.2
7.5°	1409.5	1410.8	1412.1	1412.4	1411.4	1410.6	1409.7	1408.8
10°	1391.5	1391.8	1392.1	1391.5	1390.2	1388.9	1387.6	1386.3
12.5°	1369.1	1369.0	1368.8	1368.0	1366.5	1364.9	1363.5	1361.9
15°	1329.8	1328.5	1327.2	1325.6	1323.8	1322.0	1320.2	1318.4
17.5°	1282.8	1280.0	1277.3	1274.5	1271.9	1269.1	1266.4	1263.7
20°	1250.6	1247.2	1243.9	1240.6	1237.5	1234.3	1231.2	1228.1
22.5°	1216.2	1211.9	1207.7	1204.1	1201.3	1198.3	1195.4	1192.5
25°	1159.8	1154.3	1148.8	1144.6	1141.8	1138.9	1136.1	1133.2
27.5°	1098.3	1090.7	1083.1	1077.1	1072.7	1068.3	1063.9	1059.6
30°	1054.6	1045.7	1036.8	1030.4	1026.1	1022.0	1017.8	1013.7
32.5°	1011.6	1001.9	992.2	985.2	980.9	976.5	972.1	967.7
35°	947.9	936.7	925.5	917.6	912.9	908.2	903.5	898.8
37.5°	879.5	866.8	854.1	844.8	839.0	833.3	827.5	821.7
40°	831.9	818.4	804.8	795.0	789.0	783.1	777.1	771.1
42.5°	786.3	771.5	756.6	746.6	741.2	735.9	730.5	725.1
45°	719.1	704.3	689.4	678.9	672.6	666.4	660.1	653.9
47.5°	649.7	633.6	617.4	606.6	601.0	595.5	589.9	584.3
50°	602.9	586.7	570.6	559.5	553.5	547.5	541.6	535.5
52.5°	557.6	540.8	524.0	512.9	507.6	502.2	496.9	491.5
55°	490.1	475.0	459.9	449.7	444.5	439.3	434.1	428.9
57.5°	423.8	409.5	395.3	385.9	381.5	377.0	372.6	368.2
60°	382.0	368.0	353.9	344.7	340.3	335.8	331.4	326.9
62.5°	340.5	327.4	314.1	305.1	300.6	295.9	291.3	286.6
65°	281.5	268.7	256.0	248.1	245.3	242.5	239.6	236.7
67.5°	225.2	215.6	206.1	199.8	196.7	193.6	190.5	187.5
70°	190.4	181.2	172.1	166.2	163.2	160.4	157.6	154.7
72.5°	159.0	151.5	144.1	139.8	138.6	137.4	136.2	135.0
75°	119.0	116.4	113.8	112.3	111.8	111.2	110.6	110.1
77.5°	89.8	88.3	87.0	86.0	85.5	85.0	84.5	83.9
80°	72.2	71.5	70.7	70.1	69.6	69.1	68.4	67.9
82.5°	55.4	54.6	53.8	53.4	53.3	53.2	53.0	53.0
85°	31.8	31.3	30.7	30.5	30.5	30.5	30.5	30.5
87.5°	17.6	17.5	17.5	17.5	17.3	17.2	17.1	17.0
90°	28.8	29.8	30.7	31.5	32.0	32.5	33.0	33.5
92.5°	44.4	45.3	46.1	46.3	46.0	45.7	45.4	45.1
95°	84.6	85.6	86.6	87.1	87.1	87.1	87.1	87.1
97.5°	131.6	132.8	133.9	134.4	134.3	134.2	134.1	134.0
100°	165.7	166.3	167.1	167.7	168.2	168.8	169.3	169.7
102.5°	204.9	205.7	206.5	206.7	206.6	206.6	206.5	206.4
105°	263.6	263.6	263.6	263.8	264.3	264.8	265.3	265.8
107.5°	327.0	327.8	328.6	328.8	328.6	328.2	328.0	327.6
110°	369.4	370.4	371.3	371.6	371.1	370.7	370.1	369.6



TEST NUMBER: P332465-935

CATALOG NUMBER: S123RDIW-S1000D1320U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	411.7	412.9	414.1	414.7	414.6	414.5	414.4	414.3
115°	476.2	476.5	476.7	476.7	476.5	476.2	476.0	475.7
117.5°	541.3	541.2	541.1	540.8	540.1	539.4	538.7	538.0
120°	584.6	584.4	584.2	583.8	583.3	582.8	582.3	581.8
122.5°	628.5	627.8	627.2	626.5	625.9	625.2	624.5	623.8
125°	693.7	692.8	691.7	690.8	689.7	688.7	687.8	686.7
127.5°	758.1	756.7	755.4	754.1	752.9	751.8	750.7	749.5
130°	800.9	800.0	798.9	797.5	795.8	794.1	792.4	790.7
132.5°	842.5	841.3	840.2	838.9	837.5	836.2	834.8	833.5
135°	904.7	903.8	902.8	902.1	901.6	901.0	900.5	900.1
137.5°	965.6	964.6	963.5	962.6	961.7	960.7	959.8	958.8
140°	1005.6	1005.4	1005.1	1004.2	1002.5	1000.7	998.9	997.2
142.5°	1043.2	1042.9	1042.7	1041.9	1040.5	1039.2	1037.8	1036.6
145°	1098.3	1098.1	1097.9	1097.3	1096.2	1095.2	1094.2	1093.2
147.5°	1150.4	1150.4	1150.4	1149.7	1148.2	1146.7	1145.2	1143.8
150°	1182.6	1182.6	1182.6	1181.8	1180.3	1178.9	1177.3	1175.9
152.5°	1211.9	1212.4	1212.7	1212.3	1211.0	1209.7	1208.4	1207.1
155°	1254.9	1255.9	1256.9	1256.5	1254.8	1253.1	1251.3	1249.6
157.5°	1291.8	1292.9	1294.0	1293.7	1292.4	1291.0	1289.6	1288.2
160°	1314.6	1315.9	1317.1	1317.2	1316.2	1315.3	1314.2	1313.2
162.5°	1336.0	1337.3	1338.5	1338.3	1336.8	1335.2	1333.6	1332.0
165°	1363.1	1364.6	1366.1	1366.0	1364.3	1362.5	1360.7	1359.0
167.5°	1385.1	1386.6	1388.2	1388.2	1386.6	1385.1	1383.5	1382.0
170°	1397.1	1398.9	1400.6	1400.6	1398.9	1397.1	1395.3	1393.6
172.5°	1406.5	1408.1	1409.6	1409.5	1407.8	1406.0	1404.3	1402.6
175°	1416.7	1418.2	1419.7	1419.5	1417.8	1416.1	1414.4	1412.6
177.5°	1421.3	1422.5	1423.7	1423.6	1422.1	1420.7	1419.4	1418.0
180°	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6	1421.6

(END OF REPORT)