

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332450-935

Luminaire Tested: **S123RDIW-S1000D460U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332450-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D460U935-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4997.2 lumens  
Efficiency: N/A  
Efficacy: 108.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	103	99	95	91	97	93	90	87	83	81	79	74	72	71	66	64	63	59
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	56	54	51
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	40	37	34
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30
7	63	51	43	37	59	49	41	36	44	38	34	40	35	31	36	32	29	27
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14733	14733	14733	14733
5°	17562	14795	13029	14795
10°	21928	14711	11770	14711
15°	25740	14561	10735	14561
20°	28726	14336	9852	14336
25°	28268	14099	9311	14099
30°	20319	13881	8754	13881
35°	13566	13596	8393	13596
40°	9996	13256	8019	13256
45°	8385	12657	7652	12657
50°	7398	11871	7142	11871
55°	6488	10975	6444	10975
60°	5778	10116	5903	10116
65°	5074	9192	5491	9192
70°	3984	8371	5017	8371
75°	3510	7311	4579	7311
80°	3050	6211	4506	6211
85°	2458	5002	4780	5002



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.6	2.7
10°-20°	420.5	8.4
20°-30°	660.6	13.2
30°-40°	689.3	13.8
40°-50°	589.9	11.8
50°-60°	449.6	9.0
60°-70°	288.2	5.8
70°-80°	138.6	2.8
80°-90°	38.1	0.8
90°-100°	18.9	0.4
100°-110°	90.2	1.8
110°-120°	216.7	4.3
120°-130°	276.0	5.5
130°-140°	294.8	5.9
140°-150°	275.7	5.5
150°-160°	222.4	4.5
160°-170°	143.5	2.9
170°-180°	49.5	1.0
0°-30°	1215.8	24.3
0°-40°	1905.0	38.1
0°-60°	2944.5	58.9
0°-90°	3409.4	68.2
90°-120°	325.9	6.5
90°-150°	1172.4	23.5
90°-180°	1588.0	31.8
0°-180°	4997.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1369	1369	1369	1369	1369	
5°	1625	1369	1206	1369	1625	168
15°	2310	1307	963	1307	2310	655
25°	2380	1187	784	1187	2380	1023
35°	1032	1035	639	1035	1032	677
45°	551	832	503	832	551	433
55°	346	585	343	585	346	313
65°	199	361	216	361	199	196
75°	84	176	110	176	84	90
85°	20	40	39	40	20	23
90°	12	0	12	0	12	6
95°	15	24	15	24	15	12
105°	17	115	17	115	17	39
115°	228	216	228	216	228	210
125°	311	305	311	305	311	278
135°	383	379	383	379	383	296
145°	442	438	442	438	442	276
155°	482	482	482	482	482	222
165°	508	509	508	509	508	143
175°	519	521	519	521	519	49
180°	521	521	521	521	521	



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1457.8	1459.7	1453.6	1452.7	1445.6	1443.7	1443.7	1433.9	1427.8	1419.9	1415.1
5°	1625.4	1634.8	1630.0	1619.5	1602.0	1597.8	1586.7	1569.2	1549.2	1524.6	1512.9
7.5°	1834.7	1847.4	1842.5	1826.3	1807.8	1792.9	1761.6	1732.4	1691.5	1655.6	1625.0
10°	2006.2	1992.8	1982.2	1966.4	1949.4	1921.8	1889.0	1843.9	1791.8	1750.8	1705.1
12.5°	2134.7	2132.4	2119.1	2102.8	2078.8	2052.6	2012.3	1957.4	1896.8	1837.5	1785.2
15°	2309.8	2313.2	2304.5	2287.5	2253.5	2207.3	2146.3	2123.5	2036.7	1972.3	1907.8
17.5°	2430.9	2430.3	2429.1	2405.5	2370.8	2337.9	2281.4	2221.3	2142.8	2051.9	1965.1
20°	2507.8	2502.0	2503.1	2476.8	2451.0	2412.9	2357.8	2270.5	2206.1	2101.2	2011.6
22.5°	2505.9	2504.7	2509.2	2500.2	2481.5	2452.3	2408.9	2335.2	2252.9	2147.1	2046.3
25°	2380.1	2375.4	2403.0	2410.5	2440.4	2445.7	2432.8	2392.4	2314.5	2205.5	2080.7
27.5°	1991.9	1989.3	2040.5	2104.5	2185.6	2248.6	2309.5	2339.0	2314.5	2236.4	2111.3
30°	1634.8	1689.9	1715.6	1808.2	1911.3	2034.4	2142.2	2244.7	2269.9	2235.9	2133.4
32.5°	1357.3	1405.3	1426.8	1506.3	1602.4	1746.5	1908.3	2053.5	2156.0	2182.0	2120.3
35°	1032.4	1033.0	1082.2	1117.4	1206.4	1354.7	1511.7	1706.2	1899.6	2046.1	2061.3
37.5°	823.8	826.7	856.5	891.6	958.4	1036.7	1175.0	1336.8	1560.1	1785.0	1916.8
40°	711.4	716.6	738.9	773.4	821.5	880.6	988.5	1140.8	1327.1	1577.4	1781.8
42.5°	639.1	647.7	659.2	685.8	715.6	770.9	858.2	975.9	1145.3	1381.9	1617.8
45°	550.8	555.4	564.3	576.5	603.5	642.2	700.8	779.9	920.5	1110.9	1347.0
47.5°	485.9	483.4	492.7	502.7	520.6	546.9	586.2	650.7	751.1	903.9	1104.1
50°	441.8	441.2	447.6	455.3	472.3	491.6	523.8	572.5	652.1	778.7	962.1
52.5°	400.5	402.8	407.3	416.8	429.1	444.7	473.6	508.7	577.1	686.4	839.3
55°	345.7	347.5	353.9	359.2	368.0	383.7	401.9	431.3	478.1	554.3	680.3
57.5°	299.3	298.5	304.7	306.0	315.9	328.8	342.9	365.7	399.6	456.2	541.1
60°	268.4	266.6	271.9	276.0	281.3	291.8	303.5	325.8	352.8	394.3	467.0
62.5°	240.2	239.4	243.3	247.4	251.8	261.3	271.2	288.3	309.6	344.7	402.3
65°	199.2	201.0	202.8	204.5	206.8	212.7	222.1	233.8	248.4	273.0	314.6
67.5°	156.5	158.3	158.9	162.6	167.6	171.3	176.9	187.4	197.6	218.3	242.0
70°	126.6	126.0	126.6	128.3	134.7	141.2	148.9	156.4	162.9	177.5	197.4
72.5°	108.7	107.7	109.3	109.6	112.7	114.5	119.3	126.5	134.7	144.7	159.0
75°	84.4	84.4	84.4	84.4	86.7	87.9	89.6	91.4	94.4	99.0	109.6
77.5°	62.3	62.4	63.3	63.9	64.3	65.0	66.1	67.8	68.9	71.4	75.9
80°	49.2	49.8	49.2	49.8	49.8	51.0	51.6	53.3	53.9	56.8	58.6
82.5°	37.0	36.7	37.0	37.6	37.6	38.8	38.9	40.2	40.3	41.8	43.6
85°	19.9	18.8	19.9	19.4	20.5	19.4	19.9	21.1	21.1	21.7	24.0
87.5°	7.0	7.9	7.0	7.4	7.3	7.7	7.7	7.6	8.5	7.9	8.2
90°	11.6	11.5	11.3	11.1	10.9	10.7	10.3	10.0	9.6	9.3	8.2
92.5°	12.8	12.7	12.7	12.6	12.4	12.1	11.5	11.0	10.4	9.9	9.0
95°	14.7	14.7	14.7	14.7	14.7	14.4	13.8	13.2	12.6	12.0	11.0
97.5°	15.9	15.8	15.8	15.7	15.6	15.2	14.6	13.9	13.2	12.5	18.7
100°	16.3	16.2	16.1	16.0	15.9	15.5	14.8	14.1	13.4	12.7	26.2
102.5°	16.5	16.4	16.3	16.1	15.9	17.0	19.0	21.2	23.3	25.5	40.1
105°	17.0	16.9	16.7	16.5	16.4	23.8	39.1	54.2	69.5	84.7	92.5
107.5°	53.5	64.9	76.4	87.8	99.4	110.6	121.8	132.9	144.1	155.2	154.0
110°	106.4	118.6	131.0	143.3	155.6	163.1	165.9	168.8	171.6	174.4	173.5



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	182.5	185.1	187.7	190.3	192.9	194.2	194.1	194.1	194.0	194.0	193.0
115°	227.5	227.1	226.8	226.4	226.1	225.5	224.6	223.8	222.9	222.1	221.3
117.5°	252.7	252.6	252.5	252.4	252.4	252.0	251.3	250.6	249.9	249.3	248.9
120°	270.0	270.0	270.0	270.0	270.0	269.7	269.0	268.3	267.6	266.9	266.7
122.5°	287.1	287.0	286.9	286.8	286.7	286.5	286.0	285.5	285.0	284.6	284.2
125°	311.0	310.8	310.6	310.5	310.3	310.1	310.0	309.8	309.6	309.4	309.1
127.5°	334.1	334.2	334.4	334.6	334.8	334.7	334.4	334.2	333.9	333.6	333.2
130°	348.9	349.0	349.2	349.4	349.6	349.5	349.1	348.8	348.4	348.1	347.8
132.5°	362.6	362.7	363.0	363.3	363.5	363.4	363.1	362.7	362.4	362.1	361.8
135°	383.3	383.6	383.8	384.1	384.4	384.4	384.1	383.8	383.6	383.3	383.0
137.5°	402.9	403.1	403.3	403.5	403.6	403.5	403.0	402.7	402.3	401.8	401.7
140°	414.7	414.8	415.0	415.2	415.3	415.3	414.9	414.6	414.2	413.9	413.6
142.5°	425.5	425.8	426.0	426.2	426.5	426.5	426.2	425.9	425.6	425.3	425.1
145°	442.1	442.1	442.1	442.1	442.1	442.0	441.9	441.7	441.5	441.3	441.2
147.5°	454.5	455.0	455.3	455.7	456.1	456.2	456.1	455.9	455.7	455.6	455.4
150°	463.8	464.1	464.3	464.6	464.9	464.9	464.7	464.5	464.3	464.2	464.0
152.5°	471.2	471.7	472.0	472.4	472.8	472.9	472.5	472.3	471.9	471.7	471.5
155°	481.6	482.1	482.6	483.1	483.6	483.7	483.3	482.8	482.4	482.0	481.9
157.5°	490.3	491.0	491.7	492.3	493.0	493.1	492.6	492.1	491.5	491.0	491.1
160°	495.9	496.5	497.1	497.7	498.3	498.3	497.8	497.3	496.8	496.3	496.4
162.5°	501.2	501.7	502.2	502.7	503.3	503.3	502.7	502.1	501.5	500.9	501.0
165°	507.6	508.2	508.8	509.3	509.9	509.9	509.2	508.5	507.8	507.1	507.2
167.5°	512.1	512.8	513.5	514.1	514.8	514.8	514.1	513.5	512.8	512.1	512.1
170°	514.9	515.6	516.3	516.9	517.6	517.6	516.9	516.3	515.6	514.9	514.9
172.5°	516.4	517.2	517.9	518.7	519.4	519.4	518.8	518.1	517.4	516.7	516.7
175°	518.8	519.4	520.1	520.8	521.5	521.5	520.9	520.3	519.7	519.1	519.0
177.5°	519.4	520.1	520.8	521.5	522.2	522.3	521.7	521.2	520.6	520.0	520.0
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1413.2	1411.9	1405.3	1397.8	1387.9	1381.4	1376.2	1373.5	1365.0	1354.7	1347.6
5°	1500.6	1483.0	1464.3	1441.4	1420.3	1398.6	1385.2	1369.3	1350.0	1328.4	1313.1
7.5°	1594.1	1559.6	1522.5	1484.2	1446.3	1412.4	1382.3	1356.7	1325.9	1294.8	1273.0
10°	1665.9	1615.4	1563.3	1509.9	1461.3	1415.7	1380.4	1345.9	1309.0	1273.2	1246.3
12.5°	1731.0	1664.7	1604.6	1539.0	1476.8	1422.2	1371.6	1330.9	1286.5	1248.4	1217.7
15°	1813.4	1745.5	1672.8	1573.2	1490.6	1421.5	1359.9	1306.7	1252.8	1205.8	1176.0
17.5°	1890.6	1788.3	1690.7	1607.6	1500.2	1413.8	1338.8	1275.0	1215.8	1166.1	1129.4
20°	1922.4	1823.4	1717.4	1611.4	1505.9	1409.2	1321.9	1251.5	1190.1	1133.8	1099.8
22.5°	1941.6	1829.5	1717.9	1603.9	1491.8	1391.4	1305.0	1227.7	1161.0	1107.5	1065.6
25°	1964.0	1830.5	1707.4	1594.9	1480.7	1371.7	1269.1	1187.1	1115.1	1058.2	1013.7
27.5°	1978.8	1821.7	1676.3	1551.2	1435.3	1326.8	1232.8	1145.8	1072.7	1012.6	964.8
30°	1981.7	1814.6	1652.3	1517.0	1399.2	1299.6	1200.0	1116.8	1039.5	975.6	931.1
32.5°	1985.4	1797.3	1620.0	1476.2	1355.6	1257.0	1166.7	1087.3	1008.1	945.1	899.7
35°	1970.0	1787.7	1570.9	1405.7	1285.0	1189.5	1108.0	1034.7	956.8	895.9	849.6
37.5°	1903.3	1749.6	1520.0	1326.2	1200.0	1111.6	1045.2	981.4	909.8	844.1	800.5
40°	1836.3	1712.1	1480.7	1277.9	1146.1	1055.2	995.5	943.4	874.3	812.7	765.9
42.5°	1736.5	1661.0	1443.2	1227.3	1085.1	997.6	947.2	898.4	837.7	775.2	731.2
45°	1553.3	1563.3	1366.4	1146.7	1000.7	912.9	865.4	831.5	777.6	726.0	680.9
47.5°	1323.6	1416.8	1276.3	1060.8	911.8	829.3	787.8	758.2	721.9	671.2	630.1
50°	1173.6	1306.7	1204.1	1003.2	856.1	774.0	733.0	708.9	677.3	637.5	598.2
52.5°	1035.4	1178.2	1116.9	938.9	795.6	720.6	680.5	660.7	635.6	598.1	562.6
55°	844.3	989.0	975.0	842.0	704.9	637.5	607.0	584.8	567.7	539.7	511.5
57.5°	682.9	820.2	827.4	734.2	625.0	558.4	532.2	515.4	504.3	483.0	457.0
60°	581.3	707.2	731.8	661.5	567.7	509.2	483.4	469.9	461.2	444.1	424.2
62.5°	496.9	604.1	632.0	581.3	512.9	458.1	437.9	424.9	419.0	404.3	386.8
65°	380.3	469.3	496.3	468.1	432.4	388.5	372.0	360.9	355.7	347.5	334.6
67.5°	285.9	350.9	380.4	360.6	347.7	319.9	309.5	303.5	298.9	293.2	282.4
70°	229.7	277.8	308.2	302.9	292.4	277.8	270.1	266.0	261.3	256.7	247.3
72.5°	184.7	217.7	246.3	249.0	240.4	237.5	230.7	229.0	226.2	220.6	215.4
75°	122.4	145.3	165.2	172.9	176.3	179.3	176.3	175.8	175.2	170.5	167.6
77.5°	80.2	92.6	105.1	118.1	123.6	127.6	128.5	130.7	129.2	126.7	125.3
80°	61.6	64.5	73.3	84.4	93.2	96.7	99.0	100.2	99.6	99.0	96.7
82.5°	44.7	47.1	51.2	59.1	66.5	72.3	73.7	73.4	74.7	75.1	73.3
85°	24.0	24.6	25.7	26.9	31.1	37.5	39.3	40.5	41.6	41.6	38.1
87.5°	8.9	8.2	9.0	8.7	10.0	10.2	12.9	15.1	15.8	14.0	14.2
90°	7.1	5.9	4.8	3.8	2.9	2.1	1.2	0.3	1.2	2.1	2.9
92.5°	8.2	7.4	6.5	6.2	6.5	6.7	7.0	7.2	7.0	6.7	6.5
95°	10.1	9.1	8.2	9.5	13.0	16.5	20.1	23.6	20.1	16.5	13.0
97.5°	24.8	31.0	37.2	41.1	42.7	44.3	45.8	47.4	45.8	44.3	42.7
100°	39.6	53.0	66.4	72.2	70.5	68.8	67.1	65.3	67.1	68.8	70.5
102.5°	54.8	69.4	84.0	90.7	89.5	88.3	87.0	85.8	87.0	88.3	89.5
105°	100.2	107.9	115.6	119.1	118.1	117.2	116.2	115.3	116.2	117.2	118.1
107.5°	152.8	151.6	150.4	149.4	148.6	147.9	147.1	146.4	147.1	147.9	148.6
110°	172.5	171.6	170.7	169.9	169.2	168.5	167.8	167.1	167.8	168.5	169.2





TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	192.1	191.1	190.2	189.4	188.7	188.1	187.5	186.9	187.5	188.1	188.7
115°	220.5	219.7	219.0	218.3	217.7	217.2	216.7	216.2	216.7	217.2	217.7
117.5°	248.5	248.1	247.7	247.2	246.5	245.9	245.3	244.6	245.3	245.9	246.5
120°	266.4	266.1	265.9	265.4	264.6	263.8	263.0	262.3	263.0	263.8	264.6
122.5°	283.9	283.6	283.3	282.8	282.1	281.5	280.9	280.3	280.9	281.5	282.1
125°	308.8	308.4	308.1	307.5	306.9	306.2	305.5	304.8	305.5	306.2	306.9
127.5°	332.8	332.3	331.9	331.4	330.7	330.0	329.3	328.6	329.3	330.0	330.7
130°	347.5	347.2	346.8	346.3	345.6	344.9	344.2	343.5	344.2	344.9	345.6
132.5°	361.5	361.3	360.9	360.5	359.8	359.1	358.4	357.7	358.4	359.1	359.8
135°	382.6	382.3	381.9	381.5	381.0	380.5	380.0	379.4	380.0	380.5	381.0
137.5°	401.5	401.3	401.1	400.6	400.0	399.3	398.7	398.0	398.7	399.3	400.0
140°	413.4	413.1	412.8	412.5	412.0	411.5	411.0	410.4	411.0	411.5	412.0
142.5°	424.8	424.6	424.3	424.0	423.4	422.9	422.4	421.9	422.4	422.9	423.4
145°	441.0	440.8	440.7	440.3	439.7	439.1	438.5	437.9	438.5	439.1	439.7
147.5°	455.2	455.0	454.9	454.5	454.2	453.7	453.4	453.0	453.4	453.7	454.2
150°	463.8	463.6	463.5	463.3	463.0	462.8	462.5	462.3	462.5	462.8	463.0
152.5°	471.4	471.3	471.2	471.1	471.0	470.9	470.7	470.6	470.7	470.9	471.0
155°	481.8	481.7	481.6	481.7	481.9	482.0	482.2	482.3	482.2	482.0	481.9
157.5°	491.2	491.3	491.4	491.5	491.5	491.5	491.5	491.5	491.5	491.5	491.5
160°	496.5	496.5	496.6	496.7	496.8	496.9	497.0	497.1	497.0	496.9	496.8
162.5°	501.1	501.2	501.3	501.4	501.7	501.9	502.1	502.3	502.1	501.9	501.7
165°	507.3	507.4	507.5	507.6	507.9	508.2	508.4	508.7	508.4	508.2	507.9
167.5°	512.1	512.1	512.1	512.3	512.6	513.0	513.3	513.7	513.3	513.0	512.6
170°	514.9	514.9	514.9	515.1	515.4	515.7	516.1	516.4	516.1	515.7	515.4
172.5°	516.6	516.5	516.4	516.6	517.0	517.5	517.9	518.2	517.9	517.5	517.0
175°	518.9	518.8	518.8	518.9	519.4	519.8	520.2	520.6	520.2	519.8	519.4
177.5°	519.9	519.9	519.8	519.9	520.2	520.6	520.9	521.2	520.9	520.6	520.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1345.3	1339.2	1335.0	1325.6	1319.6	1312.9	1306.4	1310.6	1310.2	1309.7	1309.7
5°	1300.2	1286.7	1274.5	1258.6	1248.6	1236.3	1226.9	1225.8	1228.1	1220.0	1215.2
7.5°	1255.4	1237.0	1219.6	1202.1	1183.6	1168.8	1159.6	1155.2	1149.3	1144.2	1138.9
10°	1224.0	1202.4	1185.3	1163.6	1143.8	1126.2	1115.1	1107.4	1103.3	1099.2	1091.6
12.5°	1191.7	1170.4	1148.8	1124.3	1105.4	1084.9	1076.6	1068.1	1060.2	1055.6	1045.2
15°	1144.4	1116.8	1094.0	1068.2	1047.1	1027.2	1015.5	998.4	996.1	990.2	979.7
17.5°	1096.9	1067.0	1035.4	1016.4	992.6	971.8	954.0	948.3	931.5	925.2	916.0
20°	1059.4	1031.8	1007.8	982.7	948.0	928.7	914.6	907.1	893.5	885.4	879.5
22.5°	1027.0	999.0	971.3	941.8	913.3	891.7	881.4	869.5	862.1	850.7	844.3
25°	980.9	950.4	917.0	885.4	864.9	848.4	832.1	821.5	811.0	805.6	793.9
27.5°	927.2	895.4	864.1	840.1	814.9	798.7	783.9	774.5	761.8	752.9	746.5
30°	897.7	860.1	833.2	811.5	779.3	764.1	752.9	741.2	731.8	722.5	716.0
32.5°	863.4	829.2	803.7	776.9	752.1	735.5	721.1	710.8	702.7	693.9	687.4
35°	809.8	781.1	754.7	727.7	709.6	692.6	675.6	666.8	659.2	651.0	645.1
37.5°	761.2	734.4	709.4	683.8	661.2	647.5	633.8	627.1	616.7	611.2	605.3
40°	731.2	704.9	678.0	653.3	629.9	619.3	607.0	597.1	587.7	583.6	577.1
42.5°	698.4	672.1	649.4	622.8	603.6	589.4	578.0	567.1	560.1	554.1	550.4
45°	649.8	626.4	604.1	577.7	559.6	547.3	534.3	524.4	518.0	513.8	507.4
47.5°	602.6	579.1	556.6	533.6	516.0	501.9	489.0	482.1	473.6	468.6	464.2
50°	568.3	547.3	523.2	502.1	484.6	470.5	459.9	451.2	443.6	437.1	434.2
52.5°	536.9	514.4	493.7	474.1	455.5	439.5	430.0	420.7	415.0	407.6	404.2
55°	485.2	463.5	445.9	426.5	408.4	394.9	383.2	375.0	369.1	360.9	356.3
57.5°	436.5	417.1	396.1	379.4	360.6	349.2	339.5	328.4	321.2	314.8	310.2
60°	403.7	381.4	363.3	347.5	331.1	316.4	307.6	298.9	291.2	284.7	280.7
62.5°	369.5	350.1	332.8	315.6	300.6	287.8	277.6	270.3	263.6	259.4	255.4
65°	317.0	301.8	284.2	270.1	256.1	246.7	238.5	232.0	227.3	224.4	220.9
67.5°	268.7	253.9	238.6	224.8	215.4	208.3	202.9	197.3	195.0	191.2	188.9
70°	237.3	222.1	208.6	198.0	188.6	183.4	179.9	175.8	173.4	168.8	166.4
72.5°	203.1	192.1	182.4	173.7	166.2	161.4	156.9	151.9	148.1	142.9	140.6
75°	160.0	150.0	142.4	136.6	131.8	125.4	118.9	113.7	111.9	110.1	109.6
77.5°	118.5	112.2	106.7	101.7	95.8	91.2	89.8	88.6	88.3	87.3	87.3
80°	93.2	87.3	83.2	77.3	73.8	73.8	73.8	72.7	73.3	73.3	73.3
82.5°	69.2	63.9	61.6	59.5	58.8	59.3	59.3	59.5	59.2	60.1	59.7
85°	35.7	36.3	37.5	36.9	37.5	37.5	38.7	38.1	38.7	37.5	38.7
87.5°	13.9	15.5	16.2	16.9	17.6	17.3	17.8	17.9	18.5	18.5	18.6
90°	3.8	4.8	5.9	7.1	8.2	9.3	9.6	10.0	10.3	10.7	10.9
92.5°	6.2	6.5	7.4	8.2	9.0	9.9	10.4	11.0	11.5	12.1	12.4
95°	9.5	8.2	9.1	10.1	11.0	12.0	12.6	13.2	13.8	14.4	14.7
97.5°	41.1	37.2	31.0	24.8	18.7	12.5	13.2	13.9	14.6	15.2	15.6
100°	72.2	66.4	53.0	39.6	26.2	12.7	13.4	14.1	14.8	15.5	15.9
102.5°	90.7	84.0	69.4	54.8	40.1	25.5	23.3	21.2	19.0	17.0	15.9
105°	119.1	115.6	107.9	100.2	92.5	84.7	69.5	54.2	39.1	23.8	16.4
107.5°	149.4	150.4	151.6	152.8	154.0	155.2	144.1	132.9	121.8	110.6	99.4
110°	169.9	170.7	171.6	172.5	173.5	174.4	171.6	168.8	165.9	163.1	155.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	189.4	190.2	191.1	192.1	193.0	194.0	194.0	194.1	194.1	194.2	192.9
115°	218.3	219.0	219.7	220.5	221.3	222.1	222.9	223.8	224.6	225.5	226.1
117.5°	247.2	247.7	248.1	248.5	248.9	249.3	249.9	250.6	251.3	252.0	252.4
120°	265.4	265.9	266.1	266.4	266.7	266.9	267.6	268.3	269.0	269.7	270.0
122.5°	282.8	283.3	283.6	283.9	284.2	284.6	285.0	285.5	286.0	286.5	286.7
125°	307.5	308.1	308.4	308.8	309.1	309.4	309.6	309.8	310.0	310.1	310.3
127.5°	331.4	331.9	332.3	332.8	333.2	333.6	333.9	334.2	334.4	334.7	334.8
130°	346.3	346.8	347.2	347.5	347.8	348.1	348.4	348.8	349.1	349.5	349.6
132.5°	360.5	360.9	361.3	361.5	361.8	362.1	362.4	362.7	363.1	363.4	363.5
135°	381.5	381.9	382.3	382.6	383.0	383.3	383.6	383.8	384.1	384.4	384.4
137.5°	400.6	401.1	401.3	401.5	401.7	401.8	402.3	402.7	403.0	403.5	403.6
140°	412.5	412.8	413.1	413.4	413.6	413.9	414.2	414.6	414.9	415.3	415.3
142.5°	424.0	424.3	424.6	424.8	425.1	425.3	425.6	425.9	426.2	426.5	426.5
145°	440.3	440.7	440.8	441.0	441.2	441.3	441.5	441.7	441.9	442.0	442.1
147.5°	454.5	454.9	455.0	455.2	455.4	455.6	455.7	455.9	456.1	456.2	456.1
150°	463.3	463.5	463.6	463.8	464.0	464.2	464.3	464.5	464.7	464.9	464.9
152.5°	471.1	471.2	471.3	471.4	471.5	471.7	471.9	472.3	472.5	472.9	472.8
155°	481.7	481.6	481.7	481.8	481.9	482.0	482.4	482.8	483.3	483.7	483.6
157.5°	491.5	491.4	491.3	491.2	491.1	491.0	491.5	492.1	492.6	493.1	493.0
160°	496.7	496.6	496.5	496.5	496.4	496.3	496.8	497.3	497.8	498.3	498.3
162.5°	501.4	501.3	501.2	501.1	501.0	500.9	501.5	502.1	502.7	503.3	503.3
165°	507.6	507.5	507.4	507.3	507.2	507.1	507.8	508.5	509.2	509.9	509.9
167.5°	512.3	512.1	512.1	512.1	512.1	512.1	512.8	513.5	514.1	514.8	514.8
170°	515.1	514.9	514.9	514.9	514.9	514.9	515.6	516.3	516.9	517.6	517.6
172.5°	516.6	516.4	516.5	516.6	516.7	516.7	517.4	518.1	518.8	519.4	519.4
175°	518.9	518.8	518.8	518.9	519.0	519.1	519.7	520.3	520.9	521.5	521.5
177.5°	519.9	519.8	519.9	519.9	520.0	520.0	520.6	521.2	521.7	522.3	522.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1304.1	1303.6	1304.1	1302.2	1304.1	1303.6	1304.1	1309.7	1309.7	1310.2	1310.6
5°	1213.5	1212.9	1211.2	1205.8	1211.2	1212.9	1213.5	1215.2	1220.0	1228.1	1225.8
7.5°	1134.4	1133.6	1128.4	1128.5	1128.4	1133.6	1134.4	1138.9	1144.2	1149.3	1155.2
10°	1087.5	1088.0	1081.1	1076.9	1081.1	1088.0	1087.5	1091.6	1099.2	1103.3	1107.4
12.5°	1042.1	1039.3	1033.7	1029.2	1033.7	1039.3	1042.1	1045.2	1055.6	1060.2	1068.1
15°	982.1	976.2	962.1	963.3	962.1	976.2	982.1	979.7	990.2	996.1	998.4
17.5°	911.4	907.1	906.8	898.6	906.8	907.1	911.4	916.0	925.2	931.5	948.3
20°	870.1	867.2	868.3	860.1	868.3	867.2	870.1	879.5	885.4	893.5	907.1
22.5°	837.8	834.8	829.9	827.3	829.9	834.8	837.8	844.3	850.7	862.1	869.5
25°	790.4	785.7	781.1	784.0	781.1	785.7	790.4	793.9	805.6	811.0	821.5
27.5°	743.1	739.6	734.9	734.3	734.9	739.6	743.1	746.5	752.9	761.8	774.5
30°	713.1	709.6	707.2	704.3	707.2	709.6	713.1	716.0	722.5	731.8	741.2
32.5°	682.6	681.9	677.7	677.1	677.7	681.9	682.6	687.4	693.9	702.7	710.8
35°	642.7	639.3	638.1	638.7	638.1	639.3	642.7	645.1	651.0	659.2	666.8
37.5°	604.9	600.2	598.1	596.0	598.1	600.2	604.9	605.3	611.2	616.7	627.1
40°	577.7	573.1	571.9	570.7	571.9	573.1	577.7	577.1	583.6	587.7	597.1
42.5°	547.3	545.4	544.7	542.6	544.7	545.4	547.3	550.4	554.1	560.1	567.1
45°	505.7	505.1	501.5	502.7	501.5	505.1	505.7	507.4	513.8	518.0	524.4
47.5°	461.8	459.3	456.8	458.4	456.8	459.3	461.8	464.2	468.6	473.6	482.1
50°	431.9	430.7	425.4	426.5	425.4	430.7	431.9	434.2	437.1	443.6	451.2
52.5°	401.8	397.4	395.4	394.7	395.4	397.4	401.8	404.2	407.6	415.0	420.7
55°	352.1	346.9	344.6	343.4	344.6	346.9	352.1	356.3	360.9	369.1	375.0
57.5°	303.4	302.0	300.1	301.4	300.1	302.0	303.4	310.2	314.8	321.2	328.4
60°	274.8	274.8	274.8	274.2	274.8	274.8	274.8	280.7	284.7	291.2	298.9
62.5°	252.8	251.3	250.9	251.8	250.9	251.3	252.8	255.4	259.4	263.6	270.3
65°	219.1	218.5	216.2	215.6	216.2	218.5	219.1	220.9	224.4	227.3	232.0
67.5°	187.4	185.3	184.6	183.7	184.6	185.3	187.4	188.9	191.2	195.0	197.3
70°	163.5	162.3	158.8	159.4	158.8	162.3	163.5	166.4	168.8	173.4	175.8
72.5°	137.7	136.6	135.8	135.0	135.8	136.6	137.7	140.6	142.9	148.1	151.9
75°	109.0	108.4	107.8	110.1	107.8	108.4	109.0	109.6	110.1	111.9	113.7
77.5°	87.3	87.3	87.6	86.7	87.6	87.3	87.3	87.3	87.3	88.3	88.6
80°	73.3	73.3	72.7	72.7	72.7	73.3	73.3	73.3	73.3	73.3	72.7
82.5°	58.7	59.2	59.5	58.6	59.5	59.2	58.7	59.7	60.1	59.2	59.5
85°	38.7	38.1	39.3	38.7	39.3	38.1	38.7	38.7	37.5	38.7	38.1
87.5°	19.5	18.7	18.7	19.2	18.7	18.7	19.5	18.6	18.5	18.5	17.9
90°	11.1	11.3	11.5	11.6	11.5	11.3	11.1	10.9	10.7	10.3	10.0
92.5°	12.6	12.7	12.7	12.8	12.7	12.7	12.6	12.4	12.1	11.5	11.0
95°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.4	13.8	13.2
97.5°	15.7	15.8	15.8	15.9	15.8	15.8	15.7	15.6	15.2	14.6	13.9
100°	16.0	16.1	16.2	16.3	16.2	16.1	16.0	15.9	15.5	14.8	14.1
102.5°	16.1	16.3	16.4	16.5	16.4	16.3	16.1	15.9	17.0	19.0	21.2
105°	16.5	16.7	16.9	17.0	16.9	16.7	16.5	16.4	23.8	39.1	54.2
107.5°	87.8	76.4	64.9	53.5	64.9	76.4	87.8	99.4	110.6	121.8	132.9
110°	143.3	131.0	118.6	106.4	118.6	131.0	143.3	155.6	163.1	165.9	168.8



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	190.3	187.7	185.1	182.5	185.1	187.7	190.3	192.9	194.2	194.1	194.1
115°	226.4	226.8	227.1	227.5	227.1	226.8	226.4	226.1	225.5	224.6	223.8
117.5°	252.4	252.5	252.6	252.7	252.6	252.5	252.4	252.4	252.0	251.3	250.6
120°	270.0	270.0	270.0	270.0	270.0	270.0	270.0	270.0	269.7	269.0	268.3
122.5°	286.8	286.9	287.0	287.1	287.0	286.9	286.8	286.7	286.5	286.0	285.5
125°	310.5	310.6	310.8	311.0	310.8	310.6	310.5	310.3	310.1	310.0	309.8
127.5°	334.6	334.4	334.2	334.1	334.2	334.4	334.6	334.8	334.7	334.4	334.2
130°	349.4	349.2	349.0	348.9	349.0	349.2	349.4	349.6	349.5	349.1	348.8
132.5°	363.3	363.0	362.7	362.6	362.7	363.0	363.3	363.5	363.4	363.1	362.7
135°	384.1	383.8	383.6	383.3	383.6	383.8	384.1	384.4	384.4	384.1	383.8
137.5°	403.5	403.3	403.1	402.9	403.1	403.3	403.5	403.6	403.5	403.0	402.7
140°	415.2	415.0	414.8	414.7	414.8	415.0	415.2	415.3	415.3	414.9	414.6
142.5°	426.2	426.0	425.8	425.5	425.8	426.0	426.2	426.5	426.5	426.2	425.9
145°	442.1	442.1	442.1	442.1	442.1	442.1	442.1	442.1	442.0	441.9	441.7
147.5°	455.7	455.3	455.0	454.5	455.0	455.3	455.7	456.1	456.2	456.1	455.9
150°	464.6	464.3	464.1	463.8	464.1	464.3	464.6	464.9	464.9	464.7	464.5
152.5°	472.4	472.0	471.7	471.2	471.7	472.0	472.4	472.8	472.9	472.5	472.3
155°	483.1	482.6	482.1	481.6	482.1	482.6	483.1	483.6	483.7	483.3	482.8
157.5°	492.3	491.7	491.0	490.3	491.0	491.7	492.3	493.0	493.1	492.6	492.1
160°	497.7	497.1	496.5	495.9	496.5	497.1	497.7	498.3	498.3	497.8	497.3
162.5°	502.7	502.2	501.7	501.2	501.7	502.2	502.7	503.3	503.3	502.7	502.1
165°	509.3	508.8	508.2	507.6	508.2	508.8	509.3	509.9	509.9	509.2	508.5
167.5°	514.1	513.5	512.8	512.1	512.8	513.5	514.1	514.8	514.8	514.1	513.5
170°	516.9	516.3	515.6	514.9	515.6	516.3	516.9	517.6	517.6	516.9	516.3
172.5°	518.7	517.9	517.2	516.4	517.2	517.9	518.7	519.4	519.4	518.8	518.1
175°	520.8	520.1	519.4	518.8	519.4	520.1	520.8	521.5	521.5	520.9	520.3
177.5°	521.5	520.8	520.1	519.4	520.1	520.8	521.5	522.2	522.3	521.7	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1306.4	1312.9	1319.6	1325.6	1335.0	1339.2	1345.3	1347.6	1354.7	1365.0	1373.5
5°	1226.9	1236.3	1248.6	1258.6	1274.5	1286.7	1300.2	1313.1	1328.4	1350.0	1369.3
7.5°	1159.6	1168.8	1183.6	1202.1	1219.6	1237.0	1255.4	1273.0	1294.8	1325.9	1356.7
10°	1115.1	1126.2	1143.8	1163.6	1185.3	1202.4	1224.0	1246.3	1273.2	1309.0	1345.9
12.5°	1076.6	1084.9	1105.4	1124.3	1148.8	1170.4	1191.7	1217.7	1248.4	1286.5	1330.9
15°	1015.5	1027.2	1047.1	1068.2	1094.0	1116.8	1144.4	1176.0	1205.8	1252.8	1306.7
17.5°	954.0	971.8	992.6	1016.4	1035.4	1067.0	1096.9	1129.4	1166.1	1215.8	1275.0
20°	914.6	928.7	948.0	982.7	1007.8	1031.8	1059.4	1099.8	1133.8	1190.1	1251.5
22.5°	881.4	891.7	913.3	941.8	971.3	999.0	1027.0	1065.6	1107.5	1161.0	1227.7
25°	832.1	848.4	864.9	885.4	917.0	950.4	980.9	1013.7	1058.2	1115.1	1187.1
27.5°	783.9	798.7	814.9	840.1	864.1	895.4	927.2	964.8	1012.6	1072.7	1145.8
30°	752.9	764.1	779.3	811.5	833.2	860.1	897.7	931.1	975.6	1039.5	1116.8
32.5°	721.1	735.5	752.1	776.9	803.7	829.2	863.4	899.7	945.1	1008.1	1087.3
35°	675.6	692.6	709.6	727.7	754.7	781.1	809.8	849.6	895.9	956.8	1034.7
37.5°	633.8	647.5	661.2	683.8	709.4	734.4	761.2	800.5	844.1	909.8	981.4
40°	607.0	619.3	629.9	653.3	678.0	704.9	731.2	765.9	812.7	874.3	943.4
42.5°	578.0	589.4	603.6	622.8	649.4	672.1	698.4	731.2	775.2	837.7	898.4
45°	534.3	547.3	559.6	577.7	604.1	626.4	649.8	680.9	726.0	777.6	831.5
47.5°	489.0	501.9	516.0	533.6	556.6	579.1	602.6	630.1	671.2	721.9	758.2
50°	459.9	470.5	484.6	502.1	523.2	547.3	568.3	598.2	637.5	677.3	708.9
52.5°	430.0	439.5	455.5	474.1	493.7	514.4	536.9	562.6	598.1	635.6	660.7
55°	383.2	394.9	408.4	426.5	445.9	463.5	485.2	511.5	539.7	567.7	584.8
57.5°	339.5	349.2	360.6	379.4	396.1	417.1	436.5	457.0	483.0	504.3	515.4
60°	307.6	316.4	331.1	347.5	363.3	381.4	403.7	424.2	444.1	461.2	469.9
62.5°	277.6	287.8	300.6	315.6	332.8	350.1	369.5	386.8	404.3	419.0	424.9
65°	238.5	246.7	256.1	270.1	284.2	301.8	317.0	334.6	347.5	355.7	360.9
67.5°	202.9	208.3	215.4	224.8	238.6	253.9	268.7	282.4	293.2	298.9	303.5
70°	179.9	183.4	188.6	198.0	208.6	222.1	237.3	247.3	256.7	261.3	266.0
72.5°	156.9	161.4	166.2	173.7	182.4	192.1	203.1	215.4	220.6	226.2	229.0
75°	118.9	125.4	131.8	136.6	142.4	150.0	160.0	167.6	170.5	175.2	175.8
77.5°	89.8	91.2	95.8	101.7	106.7	112.2	118.5	125.3	126.7	129.2	130.7
80°	73.8	73.8	73.8	77.3	83.2	87.3	93.2	96.7	99.0	99.6	100.2
82.5°	59.3	59.3	58.8	59.5	61.6	63.9	69.2	73.3	75.1	74.7	73.4
85°	38.7	37.5	37.5	36.9	37.5	36.3	35.7	38.1	41.6	41.6	40.5
87.5°	17.8	17.3	17.6	16.9	16.2	15.5	13.9	14.2	14.0	15.8	15.1
90°	9.6	9.3	8.2	7.1	5.9	4.8	3.8	2.9	2.1	1.2	0.3
92.5°	10.4	9.9	9.0	8.2	7.4	6.5	6.2	6.5	6.7	7.0	7.2
95°	12.6	12.0	11.0	10.1	9.1	8.2	9.5	13.0	16.5	20.1	23.6
97.5°	13.2	12.5	18.7	24.8	31.0	37.2	41.1	42.7	44.3	45.8	47.4
100°	13.4	12.7	26.2	39.6	53.0	66.4	72.2	70.5	68.8	67.1	65.3
102.5°	23.3	25.5	40.1	54.8	69.4	84.0	90.7	89.5	88.3	87.0	85.8
105°	69.5	84.7	92.5	100.2	107.9	115.6	119.1	118.1	117.2	116.2	115.3
107.5°	144.1	155.2	154.0	152.8	151.6	150.4	149.4	148.6	147.9	147.1	146.4
110°	171.6	174.4	173.5	172.5	171.6	170.7	169.9	169.2	168.5	167.8	167.1



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	194.0	194.0	193.0	192.1	191.1	190.2	189.4	188.7	188.1	187.5	186.9
115°	222.9	222.1	221.3	220.5	219.7	219.0	218.3	217.7	217.2	216.7	216.2
117.5°	249.9	249.3	248.9	248.5	248.1	247.7	247.2	246.5	245.9	245.3	244.6
120°	267.6	266.9	266.7	266.4	266.1	265.9	265.4	264.6	263.8	263.0	262.3
122.5°	285.0	284.6	284.2	283.9	283.6	283.3	282.8	282.1	281.5	280.9	280.3
125°	309.6	309.4	309.1	308.8	308.4	308.1	307.5	306.9	306.2	305.5	304.8
127.5°	333.9	333.6	333.2	332.8	332.3	331.9	331.4	330.7	330.0	329.3	328.6
130°	348.4	348.1	347.8	347.5	347.2	346.8	346.3	345.6	344.9	344.2	343.5
132.5°	362.4	362.1	361.8	361.5	361.3	360.9	360.5	359.8	359.1	358.4	357.7
135°	383.6	383.3	383.0	382.6	382.3	381.9	381.5	381.0	380.5	380.0	379.4
137.5°	402.3	401.8	401.7	401.5	401.3	401.1	400.6	400.0	399.3	398.7	398.0
140°	414.2	413.9	413.6	413.4	413.1	412.8	412.5	412.0	411.5	411.0	410.4
142.5°	425.6	425.3	425.1	424.8	424.6	424.3	424.0	423.4	422.9	422.4	421.9
145°	441.5	441.3	441.2	441.0	440.8	440.7	440.3	439.7	439.1	438.5	437.9
147.5°	455.7	455.6	455.4	455.2	455.0	454.9	454.5	454.2	453.7	453.4	453.0
150°	464.3	464.2	464.0	463.8	463.6	463.5	463.3	463.0	462.8	462.5	462.3
152.5°	471.9	471.7	471.5	471.4	471.3	471.2	471.1	471.0	470.9	470.7	470.6
155°	482.4	482.0	481.9	481.8	481.7	481.6	481.7	481.9	482.0	482.2	482.3
157.5°	491.5	491.0	491.1	491.2	491.3	491.4	491.5	491.5	491.5	491.5	491.5
160°	496.8	496.3	496.4	496.5	496.5	496.6	496.7	496.8	496.9	497.0	497.1
162.5°	501.5	500.9	501.0	501.1	501.2	501.3	501.4	501.7	501.9	502.1	502.3
165°	507.8	507.1	507.2	507.3	507.4	507.5	507.6	507.9	508.2	508.4	508.7
167.5°	512.8	512.1	512.1	512.1	512.1	512.1	512.3	512.6	513.0	513.3	513.7
170°	515.6	514.9	514.9	514.9	514.9	514.9	515.1	515.4	515.7	516.1	516.4
172.5°	517.4	516.7	516.7	516.6	516.5	516.4	516.6	517.0	517.5	517.9	518.2
175°	519.7	519.1	519.0	518.9	518.8	518.8	518.9	519.4	519.8	520.2	520.6
177.5°	520.6	520.0	520.0	519.9	519.9	519.8	519.9	520.2	520.6	520.9	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1376.2	1381.4	1387.9	1397.8	1405.3	1411.9	1413.2	1415.1	1419.9	1427.8	1433.9
5°	1385.2	1398.6	1420.3	1441.4	1464.3	1483.0	1500.6	1512.9	1524.6	1549.2	1569.2
7.5°	1382.3	1412.4	1446.3	1484.2	1522.5	1559.6	1594.1	1625.0	1655.6	1691.5	1732.4
10°	1380.4	1415.7	1461.3	1509.9	1563.3	1615.4	1665.9	1705.1	1750.8	1791.8	1843.9
12.5°	1371.6	1422.2	1476.8	1539.0	1604.6	1664.7	1731.0	1785.2	1837.5	1896.8	1957.4
15°	1359.9	1421.5	1490.6	1573.2	1672.8	1745.5	1813.4	1907.8	1972.3	2036.7	2123.5
17.5°	1338.8	1413.8	1500.2	1607.6	1690.7	1788.3	1890.6	1965.1	2051.9	2142.8	2221.3
20°	1321.9	1409.2	1505.9	1611.4	1717.4	1823.4	1922.4	2011.6	2101.2	2206.1	2270.5
22.5°	1305.0	1391.4	1491.8	1603.9	1717.9	1829.5	1941.6	2046.3	2147.1	2252.9	2335.2
25°	1269.1	1371.7	1480.7	1594.9	1707.4	1830.5	1964.0	2080.7	2205.5	2314.5	2392.4
27.5°	1232.8	1326.8	1435.3	1551.2	1676.3	1821.7	1978.8	2111.3	2236.4	2314.5	2339.0
30°	1200.0	1299.6	1399.2	1517.0	1652.3	1814.6	1981.7	2133.4	2235.9	2269.9	2244.7
32.5°	1166.7	1257.0	1355.6	1476.2	1620.0	1797.3	1985.4	2120.3	2182.0	2156.0	2053.5
35°	1108.0	1189.5	1285.0	1405.7	1570.9	1787.7	1970.0	2061.3	2046.1	1899.6	1706.2
37.5°	1045.2	1111.6	1200.0	1326.2	1520.0	1749.6	1903.3	1916.8	1785.0	1560.1	1336.8
40°	995.5	1055.2	1146.1	1277.9	1480.7	1712.1	1836.3	1781.8	1577.4	1327.1	1140.8
42.5°	947.2	997.6	1085.1	1227.3	1443.2	1661.0	1736.5	1617.8	1381.9	1145.3	975.9
45°	865.4	912.9	1000.7	1146.7	1366.4	1563.3	1553.3	1347.0	1110.9	920.5	779.9
47.5°	787.8	829.3	911.8	1060.8	1276.3	1416.8	1323.6	1104.1	903.9	751.1	650.7
50°	733.0	774.0	856.1	1003.2	1204.1	1306.7	1173.6	962.1	778.7	652.1	572.5
52.5°	680.5	720.6	795.6	938.9	1116.9	1178.2	1035.4	839.3	686.4	577.1	508.7
55°	607.0	637.5	704.9	842.0	975.0	989.0	844.3	680.3	554.3	478.1	431.3
57.5°	532.2	558.4	625.0	734.2	827.4	820.2	682.9	541.1	456.2	399.6	365.7
60°	483.4	509.2	567.7	661.5	731.8	707.2	581.3	467.0	394.3	352.8	325.8
62.5°	437.9	458.1	512.9	581.3	632.0	604.1	496.9	402.3	344.7	309.6	288.3
65°	372.0	388.5	432.4	468.1	496.3	469.3	380.3	314.6	273.0	248.4	233.8
67.5°	309.5	319.9	347.7	360.6	380.4	350.9	285.9	242.0	218.3	197.6	187.4
70°	270.1	277.8	292.4	302.9	308.2	277.8	229.7	197.4	177.5	162.9	156.4
72.5°	230.7	237.5	240.4	249.0	246.3	217.7	184.7	159.0	144.7	134.7	126.5
75°	176.3	179.3	176.3	172.9	165.2	145.3	122.4	109.6	99.0	94.4	91.4
77.5°	128.5	127.6	123.6	118.1	105.1	92.6	80.2	75.9	71.4	68.9	67.8
80°	99.0	96.7	93.2	84.4	73.3	64.5	61.6	58.6	56.8	53.9	53.3
82.5°	73.7	72.3	66.5	59.1	51.2	47.1	44.7	43.6	41.8	40.3	40.2
85°	39.3	37.5	31.1	26.9	25.7	24.6	24.0	24.0	21.7	21.1	21.1
87.5°	12.9	10.2	10.0	8.7	9.0	8.2	8.9	8.2	7.9	8.5	7.6
90°	1.2	2.1	2.9	3.8	4.8	5.9	7.1	8.2	9.3	9.6	10.0
92.5°	7.0	6.7	6.5	6.2	6.5	7.4	8.2	9.0	9.9	10.4	11.0
95°	20.1	16.5	13.0	9.5	8.2	9.1	10.1	11.0	12.0	12.6	13.2
97.5°	45.8	44.3	42.7	41.1	37.2	31.0	24.8	18.7	12.5	13.2	13.9
100°	67.1	68.8	70.5	72.2	66.4	53.0	39.6	26.2	12.7	13.4	14.1
102.5°	87.0	88.3	89.5	90.7	84.0	69.4	54.8	40.1	25.5	23.3	21.2
105°	116.2	117.2	118.1	119.1	115.6	107.9	100.2	92.5	84.7	69.5	54.2
107.5°	147.1	147.9	148.6	149.4	150.4	151.6	152.8	154.0	155.2	144.1	132.9
110°	167.8	168.5	169.2	169.9	170.7	171.6	172.5	173.5	174.4	171.6	168.8





TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	187.5	188.1	188.7	189.4	190.2	191.1	192.1	193.0	194.0	194.0	194.1
115°	216.7	217.2	217.7	218.3	219.0	219.7	220.5	221.3	222.1	222.9	223.8
117.5°	245.3	245.9	246.5	247.2	247.7	248.1	248.5	248.9	249.3	249.9	250.6
120°	263.0	263.8	264.6	265.4	265.9	266.1	266.4	266.7	266.9	267.6	268.3
122.5°	280.9	281.5	282.1	282.8	283.3	283.6	283.9	284.2	284.6	285.0	285.5
125°	305.5	306.2	306.9	307.5	308.1	308.4	308.8	309.1	309.4	309.6	309.8
127.5°	329.3	330.0	330.7	331.4	331.9	332.3	332.8	333.2	333.6	333.9	334.2
130°	344.2	344.9	345.6	346.3	346.8	347.2	347.5	347.8	348.1	348.4	348.8
132.5°	358.4	359.1	359.8	360.5	360.9	361.3	361.5	361.8	362.1	362.4	362.7
135°	380.0	380.5	381.0	381.5	381.9	382.3	382.6	383.0	383.3	383.6	383.8
137.5°	398.7	399.3	400.0	400.6	401.1	401.3	401.5	401.7	401.8	402.3	402.7
140°	411.0	411.5	412.0	412.5	412.8	413.1	413.4	413.6	413.9	414.2	414.6
142.5°	422.4	422.9	423.4	424.0	424.3	424.6	424.8	425.1	425.3	425.6	425.9
145°	438.5	439.1	439.7	440.3	440.7	440.8	441.0	441.2	441.3	441.5	441.7
147.5°	453.4	453.7	454.2	454.5	454.9	455.0	455.2	455.4	455.6	455.7	455.9
150°	462.5	462.8	463.0	463.3	463.5	463.6	463.8	464.0	464.2	464.3	464.5
152.5°	470.7	470.9	471.0	471.1	471.2	471.3	471.4	471.5	471.7	471.9	472.3
155°	482.2	482.0	481.9	481.7	481.6	481.7	481.8	481.9	482.0	482.4	482.8
157.5°	491.5	491.5	491.5	491.5	491.4	491.3	491.2	491.1	491.0	491.5	492.1
160°	497.0	496.9	496.8	496.7	496.6	496.5	496.5	496.4	496.3	496.8	497.3
162.5°	502.1	501.9	501.7	501.4	501.3	501.2	501.1	501.0	500.9	501.5	502.1
165°	508.4	508.2	507.9	507.6	507.5	507.4	507.3	507.2	507.1	507.8	508.5
167.5°	513.3	513.0	512.6	512.3	512.1	512.1	512.1	512.1	512.1	512.8	513.5
170°	516.1	515.7	515.4	515.1	514.9	514.9	514.9	514.9	514.9	515.6	516.3
172.5°	517.9	517.5	517.0	516.6	516.4	516.5	516.6	516.7	516.7	517.4	518.1
175°	520.2	519.8	519.4	518.9	518.8	518.8	518.9	519.0	519.1	519.7	520.3
177.5°	520.9	520.6	520.2	519.9	519.8	519.9	519.9	520.0	520.0	520.6	521.2
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6	520.6



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1443.7	1443.7	1445.6	1452.7	1453.6	1459.7	1457.8
5°	1586.7	1597.8	1602.0	1619.5	1630.0	1634.8	1625.4
7.5°	1761.6	1792.9	1807.8	1826.3	1842.5	1847.4	1834.7
10°	1889.0	1921.8	1949.4	1966.4	1982.2	1992.8	2006.2
12.5°	2012.3	2052.6	2078.8	2102.8	2119.1	2132.4	2134.7
15°	2146.3	2207.3	2253.5	2287.5	2304.5	2313.2	2309.8
17.5°	2281.4	2337.9	2370.8	2405.5	2429.1	2430.3	2430.9
20°	2357.8	2412.9	2451.0	2476.8	2503.1	2502.0	2507.8
22.5°	2408.9	2452.3	2481.5	2500.2	2509.2	2504.7	2505.9
25°	2432.8	2445.7	2440.4	2410.5	2403.0	2375.4	2380.1
27.5°	2309.5	2248.6	2185.6	2104.5	2040.5	1989.3	1991.9
30°	2142.2	2034.4	1911.3	1808.2	1715.6	1689.9	1634.8
32.5°	1908.3	1746.5	1602.4	1506.3	1426.8	1405.3	1357.3
35°	1511.7	1354.7	1206.4	1117.4	1082.2	1033.0	1032.4
37.5°	1175.0	1036.7	958.4	891.6	856.5	826.7	823.8
40°	988.5	880.6	821.5	773.4	738.9	716.6	711.4
42.5°	858.2	770.9	715.6	685.8	659.2	647.7	639.1
45°	700.8	642.2	603.5	576.5	564.3	555.4	550.8
47.5°	586.2	546.9	520.6	502.7	492.7	483.4	485.9
50°	523.8	491.6	472.3	455.3	447.6	441.2	441.8
52.5°	473.6	444.7	429.1	416.8	407.3	402.8	400.5
55°	401.9	383.7	368.0	359.2	353.9	347.5	345.7
57.5°	342.9	328.8	315.9	306.0	304.7	298.5	299.3
60°	303.5	291.8	281.3	276.0	271.9	266.6	268.4
62.5°	271.2	261.3	251.8	247.4	243.3	239.4	240.2
65°	222.1	212.7	206.8	204.5	202.8	201.0	199.2
67.5°	176.9	171.3	167.6	162.6	158.9	158.3	156.5
70°	148.9	141.2	134.7	128.3	126.6	126.0	126.6
72.5°	119.3	114.5	112.7	109.6	109.3	107.7	108.7
75°	89.6	87.9	86.7	84.4	84.4	84.4	84.4
77.5°	66.1	65.0	64.3	63.9	63.3	62.4	62.3
80°	51.6	51.0	49.8	49.8	49.2	49.8	49.2
82.5°	38.9	38.8	37.6	37.6	37.0	36.7	37.0
85°	19.9	19.4	20.5	19.4	19.9	18.8	19.9
87.5°	7.7	7.7	7.3	7.4	7.0	7.9	7.0
90°	10.3	10.7	10.9	11.1	11.3	11.5	11.6
92.5°	11.5	12.1	12.4	12.6	12.7	12.7	12.8
95°	13.8	14.4	14.7	14.7	14.7	14.7	14.7
97.5°	14.6	15.2	15.6	15.7	15.8	15.8	15.9
100°	14.8	15.5	15.9	16.0	16.1	16.2	16.3
102.5°	19.0	17.0	15.9	16.1	16.3	16.4	16.5
105°	39.1	23.8	16.4	16.5	16.7	16.9	17.0
107.5°	121.8	110.6	99.4	87.8	76.4	64.9	53.5
110°	165.9	163.1	155.6	143.3	131.0	118.6	106.4



TEST NUMBER: P332450-935

CATALOG NUMBER: S123RDIW-S1000D460U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	194.1	194.2	192.9	190.3	187.7	185.1	182.5
115°	224.6	225.5	226.1	226.4	226.8	227.1	227.5
117.5°	251.3	252.0	252.4	252.4	252.5	252.6	252.7
120°	269.0	269.7	270.0	270.0	270.0	270.0	270.0
122.5°	286.0	286.5	286.7	286.8	286.9	287.0	287.1
125°	310.0	310.1	310.3	310.5	310.6	310.8	311.0
127.5°	334.4	334.7	334.8	334.6	334.4	334.2	334.1
130°	349.1	349.5	349.6	349.4	349.2	349.0	348.9
132.5°	363.1	363.4	363.5	363.3	363.0	362.7	362.6
135°	384.1	384.4	384.4	384.1	383.8	383.6	383.3
137.5°	403.0	403.5	403.6	403.5	403.3	403.1	402.9
140°	414.9	415.3	415.3	415.2	415.0	414.8	414.7
142.5°	426.2	426.5	426.5	426.2	426.0	425.8	425.5
145°	441.9	442.0	442.1	442.1	442.1	442.1	442.1
147.5°	456.1	456.2	456.1	455.7	455.3	455.0	454.5
150°	464.7	464.9	464.9	464.6	464.3	464.1	463.8
152.5°	472.5	472.9	472.8	472.4	472.0	471.7	471.2
155°	483.3	483.7	483.6	483.1	482.6	482.1	481.6
157.5°	492.6	493.1	493.0	492.3	491.7	491.0	490.3
160°	497.8	498.3	498.3	497.7	497.1	496.5	495.9
162.5°	502.7	503.3	503.3	502.7	502.2	501.7	501.2
165°	509.2	509.9	509.9	509.3	508.8	508.2	507.6
167.5°	514.1	514.8	514.8	514.1	513.5	512.8	512.1
170°	516.9	517.6	517.6	516.9	516.3	515.6	514.9
172.5°	518.8	519.4	519.4	518.7	517.9	517.2	516.4
175°	520.9	521.5	521.5	520.8	520.1	519.4	518.8
177.5°	521.7	522.3	522.2	521.5	520.8	520.1	519.4
180°	520.6	520.6	520.6	520.6	520.6	520.6	520.6

(END OF REPORT)