

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332481-935

Luminaire Tested: **S123RDIW-S1165D1030U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332481-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6849.8 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	74	72	65	63	61	54	53	52	47
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	66	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	33	35	32	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23	20
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17963	17963	17963
5°	18031	17782	17884
10°	17930	17559	17500
15°	17736	17149	16967
20°	17472	16635	16247
25°	17199	16057	15543
30°	16839	15392	14551
35°	16469	14725	13641
40°	16127	13939	12513
45°	15678	13164	11496
50°	15185	12285	10357
55°	14681	11277	9295
60°	14219	10198	8129
65°	13616	9032	6963
70°	12862	7582	5624
75°	11761	5964	5294
80°	10488	5281	4866
85°	8855	4681	4347



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.7	2.3
10°-20°	436.0	6.4
20°-30°	627.8	9.2
30°-40°	707.2	10.3
40°-50°	676.5	9.9
50°-60°	554.0	8.1
60°-70°	373.8	5.5
70°-80°	188.1	2.7
80°-90°	53.0	0.8
90°-100°	72.4	1.1
100°-110°	216.5	3.2
110°-120°	368.3	5.4
120°-130°	484.4	7.1
130°-140°	544.4	7.9
140°-150°	535.2	7.8
150°-160°	450.5	6.6
160°-170°	299.9	4.4
170°-180°	105.0	1.5
0°-30°	1220.5	17.8
0°-40°	1927.7	28.1
0°-60°	3158.3	46.1
0°-90°	3773.2	55.1
90°-120°	657.1	9.6
90°-150°	2221.1	32.4
90°-180°	3077.0	44.9
0°-180°	6849.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1669	1669	1669	1669	1669	
5°	1669	1662	1646	1657	1655	158
15°	1592	1575	1539	1532	1523	448
25°	1448	1413	1352	1324	1309	666
35°	1253	1203	1121	1064	1038	784
45°	1030	967	865	790	755	794
55°	782	713	601	525	495	701
65°	535	458	355	291	273	529
75°	283	217	143	131	127	302
85°	72	43	38	35	35	81
90°	1	10	21	24	26	7
95°	52	58	65	68	68	58
105°	196	198	206	206	208	210
115°	371	373	372	372	372	367
125°	543	545	544	540	536	484
135°	704	709	708	705	703	542
145°	854	856	858	857	854	533
155°	978	978	979	982	976	450
165°	1065	1063	1062	1067	1062	300
175°	1108	1104	1104	1109	1104	105
180°	1110	1110	1110	1110	1110	



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1674.2	1673.2	1672.2	1671.3	1670.3	1668.4	1665.5	1662.6	1659.7	1656.8	1659.5
5°	1668.8	1667.2	1665.8	1664.2	1662.8	1660.2	1656.6	1652.9	1649.3	1645.7	1648.5
7.5°	1653.3	1651.7	1650.1	1648.5	1646.8	1643.6	1639.0	1634.3	1629.6	1624.9	1626.4
10°	1640.4	1638.2	1636.2	1634.0	1631.9	1628.2	1622.7	1617.3	1611.9	1606.5	1606.8
12.5°	1622.0	1619.6	1617.2	1614.9	1612.6	1608.1	1601.5	1594.8	1588.2	1581.6	1581.4
15°	1591.6	1588.3	1585.0	1581.7	1578.4	1572.5	1564.1	1555.7	1547.2	1538.9	1537.3
17.5°	1553.4	1549.6	1545.8	1541.9	1538.1	1530.8	1520.1	1509.3	1498.7	1488.0	1484.8
20°	1525.3	1520.5	1515.7	1510.9	1506.1	1498.0	1486.5	1475.1	1463.6	1452.2	1448.3
22.5°	1493.9	1488.3	1482.8	1477.3	1471.8	1462.9	1450.8	1438.6	1426.5	1414.3	1409.5
25°	1448.1	1440.6	1433.1	1425.6	1418.1	1407.4	1393.5	1379.8	1365.9	1352.0	1345.7
27.5°	1392.7	1384.4	1376.1	1367.8	1359.4	1347.6	1332.2	1316.8	1301.4	1286.0	1277.2
30°	1354.8	1345.7	1336.7	1327.7	1318.7	1305.7	1288.9	1272.0	1255.3	1238.4	1228.1
32.5°	1316.9	1306.7	1296.4	1286.2	1276.0	1262.0	1244.1	1226.3	1208.5	1190.8	1179.6
35°	1253.3	1242.4	1231.6	1220.8	1210.0	1195.2	1176.6	1158.0	1139.3	1120.6	1107.7
37.5°	1188.9	1176.8	1164.8	1152.7	1140.7	1124.7	1104.8	1084.9	1065.1	1045.1	1030.4
40°	1147.7	1134.5	1121.2	1108.0	1094.8	1077.5	1056.1	1034.7	1013.4	992.0	976.4
42.5°	1101.1	1087.9	1074.7	1061.4	1048.2	1030.5	1008.5	986.4	964.3	942.3	925.1
45°	1029.9	1016.4	1002.9	989.4	975.8	957.4	934.3	911.1	887.9	864.8	847.7
47.5°	958.7	943.9	929.0	914.2	899.3	880.3	857.1	834.0	810.8	787.7	769.0
50°	906.8	892.7	878.5	864.4	850.2	831.0	806.7	782.3	757.9	733.6	714.9
52.5°	860.2	844.9	829.6	814.2	798.8	779.1	755.0	730.9	706.8	682.7	663.3
55°	782.3	767.5	752.8	738.0	723.3	703.2	677.6	652.0	626.5	600.9	583.5
57.5°	710.2	694.2	678.1	662.1	646.0	625.2	599.5	573.8	548.1	522.5	505.9
60°	660.5	643.9	627.4	610.9	594.3	573.5	548.5	523.7	498.7	473.7	457.4
62.5°	610.6	594.1	577.6	561.0	544.5	523.7	498.8	473.8	448.8	423.9	408.6
65°	534.6	518.1	501.5	485.0	468.5	448.4	425.0	401.5	378.1	354.6	339.8
67.5°	458.6	441.8	425.1	408.4	391.7	372.0	349.6	327.0	304.5	282.1	271.0
70°	408.7	392.5	376.3	360.0	343.8	325.1	304.1	283.0	262.0	240.9	230.4
72.5°	359.0	342.9	326.9	310.9	294.9	277.3	258.2	239.1	220.0	200.9	192.3
75°	282.8	268.5	254.0	239.5	225.2	209.7	193.1	176.5	160.0	143.4	140.4
77.5°	213.5	200.5	187.4	174.4	161.4	149.5	138.9	128.2	117.5	106.9	105.3
80°	169.2	156.9	144.5	132.2	119.9	110.6	104.2	97.9	91.6	85.2	84.4
82.5°	126.9	116.3	105.6	95.0	84.4	77.6	74.6	71.6	68.7	65.8	64.8
85°	71.7	65.1	58.5	51.9	45.3	41.5	40.6	39.7	38.8	37.9	37.3
87.5°	26.2	23.9	21.6	19.4	17.1	16.3	16.8	17.2	17.7	18.3	18.2
90°	0.9	2.8	4.7	6.7	8.6	10.8	13.3	15.9	18.4	20.9	21.7
92.5°	21.1	22.4	23.8	25.1	26.3	27.7	29.2	30.7	32.0	33.5	34.1
95°	51.5	52.8	54.2	55.5	56.9	58.4	59.9	61.5	63.0	64.6	65.3
97.5°	91.4	92.4	93.4	94.5	95.5	96.5	97.6	98.8	99.9	101.0	101.9
100°	118.6	119.8	121.0	122.1	123.3	124.3	125.4	126.3	127.3	128.2	128.8
102.5°	150.1	150.8	151.4	152.1	152.8	153.8	155.1	156.4	157.6	158.9	159.5
105°	196.3	196.7	197.1	197.4	197.9	198.9	200.6	202.3	204.1	205.9	205.9
107.5°	250.0	250.2	250.5	250.7	250.9	251.4	252.1	252.8	253.5	254.2	254.8
110°	283.5	283.9	284.3	284.6	285.1	285.4	285.9	286.2	286.6	287.0	287.7



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	318.4	318.7	318.8	319.1	319.3	319.4	319.5	319.6	319.7	319.8	320.7
115°	370.7	371.3	371.9	372.5	373.1	373.2	372.7	372.4	372.0	371.6	371.8
117.5°	423.4	423.8	424.2	424.6	425.0	424.9	424.4	423.9	423.4	422.9	422.8
120°	456.2	457.4	458.6	459.7	460.9	461.0	459.9	459.0	458.1	457.1	456.8
122.5°	490.4	491.3	492.1	492.9	493.8	494.0	493.5	493.0	492.5	492.0	491.5
125°	542.6	543.1	543.7	544.3	544.9	545.0	544.6	544.2	543.8	543.5	542.7
127.5°	590.7	591.9	593.2	594.4	595.6	596.1	595.6	595.2	594.8	594.3	593.3
130°	622.8	624.4	625.9	627.5	629.0	629.5	629.0	628.4	627.8	627.2	626.4
132.5°	654.9	656.4	658.0	659.6	661.2	661.7	661.2	660.8	660.4	660.0	659.0
135°	704.0	705.1	706.3	707.4	708.6	709.0	708.9	708.7	708.5	708.3	707.5
137.5°	749.3	750.3	751.2	752.2	753.2	753.9	754.4	754.9	755.4	756.0	755.1
140°	780.7	781.7	782.6	783.6	784.5	785.1	785.3	785.6	785.7	785.9	785.7
142.5°	809.3	810.3	811.2	812.2	813.2	813.8	814.2	814.5	814.9	815.3	815.0
145°	853.9	854.4	854.7	855.1	855.5	856.0	856.6	857.2	857.7	858.3	858.2
147.5°	893.0	893.7	894.4	895.2	895.9	896.5	897.0	897.6	898.1	898.6	898.6
150°	920.2	920.7	921.0	921.4	921.8	922.2	922.6	923.0	923.3	923.8	923.8
152.5°	942.6	943.1	943.7	944.3	944.8	945.1	945.4	945.6	945.9	946.1	946.4
155°	977.8	977.8	977.8	977.8	977.8	977.9	978.1	978.4	978.5	978.7	979.5
157.5°	1007.9	1007.6	1007.4	1007.1	1006.9	1006.9	1007.0	1007.2	1007.4	1007.5	1008.3
160°	1026.7	1026.3	1025.9	1025.5	1025.1	1024.9	1024.9	1024.9	1024.9	1024.9	1025.9
162.5°	1043.4	1042.9	1042.3	1041.8	1041.3	1041.0	1041.2	1041.4	1041.6	1041.7	1042.7
165°	1065.1	1064.5	1063.9	1063.3	1062.7	1062.5	1062.5	1062.5	1062.5	1062.5	1063.6
167.5°	1082.4	1081.6	1080.8	1080.0	1079.3	1078.9	1079.1	1079.3	1079.4	1079.5	1080.7
170°	1092.1	1091.3	1090.5	1089.8	1089.0	1088.6	1088.6	1088.6	1088.6	1088.6	1089.9
172.5°	1099.8	1099.0	1098.2	1097.4	1096.7	1096.3	1096.3	1096.3	1096.3	1096.3	1097.5
175°	1107.8	1107.1	1106.3	1105.5	1104.7	1104.3	1104.3	1104.3	1104.3	1104.3	1105.5
177.5°	1111.1	1110.5	1109.9	1109.2	1108.6	1108.4	1108.4	1108.4	1108.4	1108.4	1109.2
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8	1668.8
2.5°	1662.2	1664.8	1667.4	1668.5	1668.0	1667.6	1667.1	1666.6
5°	1651.1	1653.9	1656.6	1657.6	1657.0	1656.4	1655.8	1655.2
7.5°	1627.9	1629.4	1630.9	1631.2	1630.1	1629.1	1628.1	1627.0
10°	1607.1	1607.4	1607.7	1607.1	1605.6	1604.1	1602.6	1601.1
12.5°	1581.2	1581.1	1580.9	1579.9	1578.2	1576.4	1574.7	1573.0
15°	1535.9	1534.3	1532.8	1531.0	1528.9	1526.8	1524.7	1522.6
17.5°	1481.6	1478.3	1475.2	1472.1	1468.9	1465.8	1462.7	1459.5
20°	1444.4	1440.5	1436.6	1432.8	1429.2	1425.6	1422.0	1418.4
22.5°	1404.5	1399.7	1394.8	1390.7	1387.3	1384.0	1380.6	1377.3
25°	1339.5	1333.1	1326.8	1322.0	1318.7	1315.3	1312.1	1308.7
27.5°	1268.4	1259.6	1250.9	1244.0	1238.9	1233.9	1228.8	1223.7
30°	1217.9	1207.7	1197.5	1190.0	1185.2	1180.3	1175.5	1170.7
32.5°	1168.4	1157.2	1146.0	1137.9	1132.8	1127.7	1122.7	1117.7
35°	1094.8	1081.8	1068.9	1059.7	1054.3	1048.9	1043.4	1038.1
37.5°	1015.7	1001.1	986.4	975.7	969.1	962.3	955.7	949.0
40°	960.8	945.1	929.5	918.3	911.3	904.4	897.5	890.5
42.5°	908.1	891.0	873.9	862.3	856.1	849.9	843.7	837.5
45°	830.5	813.4	796.3	784.1	776.9	769.6	762.4	755.2
47.5°	750.4	731.8	713.1	700.6	694.1	687.7	681.2	674.9
50°	696.3	677.6	658.9	646.2	639.3	632.3	625.4	618.5
52.5°	643.9	624.6	605.2	592.4	586.2	580.1	573.9	567.7
55°	566.0	548.5	531.2	519.4	513.4	507.4	501.4	495.3
57.5°	489.5	472.9	456.5	445.7	440.6	435.5	430.3	425.2
60°	441.2	425.0	408.7	398.0	393.0	387.8	382.7	377.6
62.5°	393.3	378.1	362.7	352.5	347.1	341.7	336.4	331.1
65°	325.1	310.4	295.7	286.6	283.4	280.0	276.7	273.4
67.5°	260.0	249.0	238.0	230.7	227.2	223.6	220.1	216.5
70°	219.8	209.3	198.8	191.9	188.6	185.3	181.9	178.7
72.5°	183.7	175.0	166.4	161.4	160.1	158.7	157.3	155.9
75°	137.4	134.4	131.4	129.7	129.1	128.5	127.9	127.3
77.5°	103.7	102.0	100.4	99.3	98.7	98.1	97.5	96.9
80°	83.4	82.6	81.6	80.9	80.3	79.7	79.1	78.5
82.5°	64.0	63.1	62.2	61.6	61.6	61.4	61.3	61.2
85°	36.7	36.1	35.5	35.2	35.2	35.2	35.2	35.2
87.5°	18.1	18.0	17.9	17.8	17.7	17.5	17.3	17.1
90°	22.5	23.2	24.0	24.6	25.0	25.4	25.7	26.2
92.5°	34.7	35.4	36.0	36.2	35.9	35.7	35.5	35.2
95°	66.1	66.9	67.7	68.0	68.0	68.0	68.0	68.0
97.5°	102.8	103.7	104.6	105.0	104.9	104.9	104.8	104.7
100°	129.4	130.0	130.5	131.0	131.4	131.8	132.2	132.6
102.5°	160.1	160.7	161.3	161.5	161.4	161.4	161.3	161.2
105°	205.9	205.9	205.9	206.0	206.5	206.8	207.2	207.6
107.5°	255.5	256.1	256.7	256.8	256.7	256.4	256.1	255.9
110°	288.5	289.3	290.1	290.2	289.9	289.5	289.1	288.7



TEST NUMBER: P332481-935

CATALOG NUMBER: S123RDIW-S1165D1030U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	321.7	322.5	323.5	323.9	323.8	323.7	323.7	323.6
115°	372.0	372.2	372.4	372.4	372.2	372.0	371.8	371.6
117.5°	422.8	422.8	422.8	422.4	421.9	421.4	420.8	420.3
120°	456.7	456.5	456.3	456.0	455.6	455.2	454.9	454.4
122.5°	490.9	490.4	490.0	489.4	488.9	488.4	487.8	487.2
125°	541.9	541.1	540.4	539.6	538.8	538.0	537.3	536.5
127.5°	592.2	591.2	590.0	589.0	588.1	587.3	586.3	585.5
130°	625.6	624.8	624.1	623.0	621.6	620.3	619.0	617.6
132.5°	658.1	657.2	656.3	655.3	654.2	653.2	652.1	651.1
135°	706.7	705.9	705.2	704.6	704.2	703.9	703.4	703.1
137.5°	754.3	753.5	752.7	751.9	751.1	750.4	749.7	749.0
140°	785.6	785.3	785.1	784.4	783.0	781.7	780.3	778.9
142.5°	814.9	814.7	814.5	813.8	812.8	811.8	810.7	809.7
145°	858.0	857.7	857.6	857.0	856.3	855.5	854.7	853.9
147.5°	898.6	898.6	898.6	898.0	896.9	895.7	894.6	893.4
150°	923.8	923.8	923.8	923.2	922.0	920.8	919.7	918.5
152.5°	946.7	947.0	947.4	947.0	946.0	944.9	943.9	943.0
155°	980.2	981.0	981.8	981.5	980.2	978.8	977.5	976.1
157.5°	1009.1	1010.0	1010.7	1010.6	1009.5	1008.5	1007.4	1006.3
160°	1026.9	1027.9	1028.8	1028.9	1028.1	1027.3	1026.6	1025.8
162.5°	1043.6	1044.6	1045.6	1045.4	1044.2	1042.9	1041.7	1040.4
165°	1064.8	1065.9	1067.1	1067.0	1065.7	1064.3	1062.9	1061.6
167.5°	1081.9	1083.1	1084.3	1084.3	1083.1	1081.9	1080.7	1079.5
170°	1091.3	1092.7	1094.1	1094.1	1092.7	1091.3	1089.9	1088.6
172.5°	1098.7	1099.9	1101.1	1101.0	1099.7	1098.3	1096.9	1095.6
175°	1106.6	1107.8	1109.0	1108.9	1107.5	1106.1	1104.8	1103.5
177.5°	1110.2	1111.1	1112.1	1112.0	1110.9	1109.8	1108.7	1107.7
180°	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4	1110.4

(END OF REPORT)