

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332454-830

Luminaire Tested: **S123RDIW-S1000D755U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332454-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D755U830-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6580.3 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	92	84	79	74	85	79	74	70	69	65	61	59	56	54	50	48	46	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	37
4	77	67	59	53	72	63	56	51	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31	28
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	30	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	45	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	26	23	20	18
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16129	16129	16129	16129
5°	19225	16197	14263	16197
10°	24004	16104	12885	16104
15°	28178	15940	11751	15940
20°	31447	15694	10786	15694
25°	30945	15435	10194	15435
30°	22243	15196	9583	15196
35°	14851	14884	9188	14884
40°	10942	14511	8778	14511
45°	9178	13855	8378	13855
50°	8098	12996	7819	12996
55°	7101	12014	7054	12014
60°	6325	11074	6463	11074
65°	5555	10063	6011	10063
70°	4362	9165	5492	9165
75°	3843	8006	5016	8006
80°	3341	6800	4934	6800
85°	2692	5471	5224	5471



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	2.2
10°-20°	460.3	7.0
20°-30°	723.2	11.0
30°-40°	754.5	11.5
40°-50°	645.7	9.8
50°-60°	492.2	7.5
60°-70°	315.5	4.8
70°-80°	151.8	2.3
80°-90°	42.8	0.7
90°-100°	33.9	0.5
100°-110°	161.8	2.5
110°-120°	388.6	5.9
120°-130°	494.8	7.5
130°-140°	528.7	8.0
140°-150°	494.4	7.5
150°-160°	398.8	6.1
160°-170°	257.4	3.9
170°-180°	88.7	1.3
0°-30°	1330.9	20.2
0°-40°	2085.5	31.7
0°-60°	3223.3	49.0
0°-90°	3733.3	56.7
90°-120°	584.3	8.9
90°-150°	2102.1	31.9
90°-180°	2847.0	43.3
0°-180°	6580.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1498	1498	1498	1498	1498	
5°	1779	1499	1320	1499	1779	184
15°	2529	1430	1054	1430	2529	717
25°	2606	1300	858	1300	2606	1120
35°	1130	1133	699	1133	1130	741
45°	603	910	550	910	603	474
55°	378	640	376	640	378	342
65°	218	395	236	395	218	215
75°	92	192	121	192	92	99
85°	22	44	42	44	22	26
90°	21	1	21	1	21	10
95°	26	42	26	42	26	22
105°	30	207	30	207	30	70
115°	408	388	408	388	408	377
125°	558	547	558	547	558	498
135°	687	680	687	680	687	530
145°	793	785	793	785	793	495
155°	864	865	864	865	864	398
165°	910	912	910	912	910	257
175°	930	934	930	934	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1595.9	1597.9	1591.3	1590.3	1582.5	1580.5	1580.5	1569.7	1563.0	1554.3	1549.2
5°	1779.3	1789.6	1784.4	1772.9	1753.7	1749.2	1737.0	1717.8	1695.9	1669.0	1656.1
7.5°	2008.5	2022.4	2017.0	1999.2	1979.1	1962.8	1928.4	1896.5	1851.7	1812.4	1778.9
10°	2196.2	2181.5	2169.9	2152.7	2134.0	2103.8	2067.9	2018.5	1961.5	1916.6	1866.6
12.5°	2336.8	2334.4	2319.8	2302.0	2275.7	2247.0	2202.9	2142.8	2076.4	2011.6	1954.3
15°	2528.6	2532.3	2522.7	2504.1	2466.9	2416.3	2349.6	2324.6	2229.6	2159.1	2088.5
17.5°	2661.2	2660.4	2659.1	2633.4	2595.4	2559.3	2497.5	2431.7	2345.7	2246.3	2151.3
20°	2745.3	2738.9	2740.2	2711.3	2683.1	2641.4	2581.2	2485.6	2415.0	2300.2	2202.1
22.5°	2743.3	2742.0	2746.9	2737.0	2716.5	2684.5	2637.0	2556.4	2466.3	2350.4	2240.0
25°	2605.5	2600.4	2630.5	2638.8	2671.5	2677.3	2663.2	2618.9	2533.6	2414.3	2277.7
27.5°	2180.6	2177.7	2233.7	2303.8	2392.6	2461.5	2528.3	2560.5	2533.6	2448.3	2311.3
30°	1789.6	1849.9	1878.1	1979.4	2092.4	2227.0	2345.0	2457.3	2484.9	2447.7	2335.4
32.5°	1485.8	1538.4	1562.0	1649.0	1754.2	1911.9	2089.1	2248.0	2360.2	2388.7	2321.1
35°	1130.2	1130.9	1184.7	1223.2	1320.7	1483.0	1654.9	1867.8	2079.5	2239.9	2256.5
37.5°	901.8	905.0	937.6	976.0	1049.1	1134.9	1286.3	1463.4	1707.9	1954.1	2098.4
40°	778.7	784.5	808.9	846.7	899.3	964.0	1082.1	1248.9	1452.8	1726.7	1950.6
42.5°	699.6	709.1	721.6	750.7	783.3	844.0	939.4	1068.3	1253.8	1512.8	1771.0
45°	602.9	608.0	617.7	631.1	660.6	703.0	767.1	853.8	1007.7	1216.2	1474.6
47.5°	531.9	529.1	539.3	550.3	569.9	598.7	641.7	712.4	822.2	989.5	1208.7
50°	483.6	483.0	490.0	498.4	517.0	538.2	573.4	626.7	713.9	852.4	1053.2
52.5°	438.5	440.9	445.9	456.3	469.8	486.8	518.5	556.9	631.8	751.4	918.8
55°	378.4	380.4	387.4	393.2	402.8	420.1	440.0	472.1	523.4	606.8	744.7
57.5°	327.6	326.8	333.6	335.0	345.8	360.0	375.3	400.3	437.4	499.5	592.3
60°	293.8	291.8	297.7	302.1	307.9	319.4	332.2	356.7	386.2	431.7	511.2
62.5°	263.0	262.1	266.4	270.8	275.6	286.1	296.9	315.6	338.9	377.3	440.5
65°	218.1	220.0	222.0	223.9	226.4	232.8	243.1	255.9	271.9	298.9	344.4
67.5°	171.4	173.3	174.0	178.0	183.4	187.5	193.7	205.1	216.3	239.0	264.9
70°	138.6	137.9	138.6	140.4	147.5	154.6	163.0	171.3	178.3	194.4	216.1
72.5°	119.0	117.9	119.6	120.0	123.4	125.4	130.6	138.5	147.5	158.4	174.1
75°	92.4	92.4	92.4	92.4	94.9	96.2	98.1	100.1	103.3	108.4	120.0
77.5°	68.2	68.3	69.3	69.9	70.4	71.2	72.4	74.3	75.4	78.1	83.1
80°	53.9	54.5	53.9	54.5	54.5	55.8	56.5	58.3	59.0	62.2	64.2
82.5°	40.5	40.2	40.5	41.2	41.2	42.5	42.6	44.0	44.1	45.8	47.7
85°	21.8	20.5	21.8	21.2	22.4	21.2	21.8	23.1	23.1	23.8	26.3
87.5°	9.3	10.3	9.1	9.6	9.5	10.0	9.9	9.7	10.7	10.0	10.1
90°	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9	17.2	16.7	14.6
92.5°	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7	18.8	17.7	16.2
95°	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7	22.6	21.5	19.8
97.5°	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8	23.6	22.3	33.5
100°	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4	24.1	22.9	46.9
102.5°	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0	41.8	45.6	71.9
105°	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4	124.6	151.9	165.8
107.5°	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4	258.4	278.4	276.3
110°	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7	307.7	312.8	311.1



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0	347.9	347.8	346.1
115°	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2	399.6	398.1	396.7
117.5°	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4	448.2	447.0	446.2
120°	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1	479.8	478.5	478.2
122.5°	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9	511.0	510.2	509.6
125°	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4	555.2	554.9	554.2
127.5°	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2	598.6	598.1	597.4
130°	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5	624.8	624.2	623.6
132.5°	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4	649.8	649.2	648.7
135°	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3	686.7
137.5°	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0	721.2	720.5	720.2
140°	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4	742.7	742.2	741.7
142.5°	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6	763.2	762.7	762.2
145°	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0	791.6	791.4	791.1
147.5°	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4	817.1	816.7	816.4
150°	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9	832.6	832.3	832.0
152.5°	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7	846.1	845.6	845.5
155°	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7	865.0	864.2	864.0
157.5°	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3	881.4	880.4	880.6
160°	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7	890.8	889.9	890.0
162.5°	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3	899.3	898.1	898.3
165°	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7	910.5	909.3	909.5
167.5°	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1	918.1
170°	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1	923.1
172.5°	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0	927.7	926.5	926.3
175°	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9	931.9	930.8	930.7
177.5°	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4	933.4	932.5	932.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1547.1	1545.6	1538.4	1530.2	1519.4	1512.2	1506.6	1503.5	1494.3	1483.0	1475.3
5°	1642.7	1623.4	1603.0	1577.9	1554.8	1531.1	1516.4	1499.0	1477.8	1454.2	1437.5
7.5°	1745.1	1707.3	1666.7	1624.8	1583.3	1546.1	1513.3	1485.2	1451.4	1417.4	1393.5
10°	1823.6	1768.4	1711.4	1652.9	1599.7	1549.7	1511.2	1473.4	1432.9	1393.8	1364.3
12.5°	1894.9	1822.3	1756.5	1684.8	1616.6	1556.9	1501.5	1457.0	1408.3	1366.6	1333.0
15°	1985.2	1910.8	1831.3	1722.2	1631.8	1556.1	1488.7	1430.4	1371.4	1320.0	1287.3
17.5°	2069.6	1957.7	1850.8	1759.8	1642.3	1547.7	1465.6	1395.7	1331.0	1276.6	1236.3
20°	2104.5	1996.1	1880.0	1764.0	1648.5	1542.7	1447.1	1370.1	1302.8	1241.1	1204.0
22.5°	2125.5	2002.8	1880.6	1755.8	1633.0	1523.1	1428.6	1344.0	1270.9	1212.4	1166.5
25°	2150.0	2003.8	1869.2	1746.0	1620.9	1501.6	1389.3	1299.6	1220.7	1158.4	1109.7
27.5°	2166.2	1994.2	1835.0	1698.1	1571.2	1452.5	1349.5	1254.3	1174.3	1108.5	1056.2
30°	2169.4	1986.5	1808.8	1660.7	1531.7	1422.7	1313.6	1222.6	1137.9	1068.0	1019.3
32.5°	2173.4	1967.6	1773.4	1616.0	1484.0	1376.0	1277.2	1190.2	1103.5	1034.6	984.9
35°	2156.5	1957.0	1719.7	1538.8	1406.7	1302.1	1213.0	1132.7	1047.4	980.7	930.1
37.5°	2083.6	1915.3	1664.0	1451.8	1313.6	1216.8	1144.2	1074.3	996.0	924.1	876.3
40°	2010.3	1874.2	1620.9	1398.9	1254.6	1155.2	1089.8	1032.7	957.1	889.7	838.4
42.5°	1900.9	1818.4	1579.9	1343.5	1187.9	1092.1	1036.9	983.4	917.0	848.6	800.4
45°	1700.4	1711.4	1495.8	1255.3	1095.5	999.4	947.3	910.2	851.2	794.8	745.4
47.5°	1449.0	1551.0	1397.1	1161.2	998.2	907.9	862.4	830.0	790.2	734.8	689.8
50°	1284.8	1430.4	1318.1	1098.2	937.2	847.3	802.4	776.1	741.5	697.9	654.9
52.5°	1133.4	1289.8	1222.7	1027.8	870.9	788.8	745.0	723.3	695.8	654.8	615.9
55°	924.3	1082.7	1067.3	921.7	771.7	697.9	664.5	640.2	621.5	590.8	560.0
57.5°	747.6	897.9	905.8	803.7	684.2	611.2	582.6	564.2	552.0	528.8	500.3
60°	636.3	774.2	801.2	724.2	621.5	557.4	529.1	514.4	504.8	486.2	464.4
62.5°	543.9	661.3	691.8	636.4	561.5	501.4	479.4	465.1	458.6	442.6	423.4
65°	416.3	513.8	543.3	512.5	473.3	425.3	407.3	395.1	389.4	380.4	366.3
67.5°	313.0	384.1	416.4	394.7	380.6	350.2	338.8	332.2	327.2	320.9	309.2
70°	251.5	304.1	337.4	331.6	320.1	304.1	295.7	291.2	286.1	281.0	270.7
72.5°	202.2	238.4	269.7	272.6	263.2	260.0	252.6	250.7	247.6	241.5	235.8
75°	134.0	159.1	180.9	189.3	193.0	196.2	193.0	192.5	191.8	186.6	183.4
77.5°	87.8	101.3	115.1	129.3	135.3	139.7	140.7	143.1	141.4	138.6	137.1
80°	67.4	70.6	80.2	92.4	102.0	105.8	108.4	109.7	109.1	108.4	105.8
82.5°	48.9	51.6	56.1	64.7	72.8	79.2	80.7	80.4	81.8	82.2	80.2
85°	26.3	27.0	28.2	29.5	34.0	41.1	43.0	44.3	45.5	45.5	41.7
87.5°	10.7	9.8	10.5	10.1	11.3	11.5	14.3	16.6	17.3	15.6	15.9
90°	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7	2.3	3.8	5.3
92.5°	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9	12.4	12.1	11.6
95°	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3	36.0	29.7	23.4
97.5°	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0	82.2	79.4	76.5
100°	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3	120.3	123.4	126.5
102.5°	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8	156.1	158.3	160.5
105°	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7	208.4	210.1	211.8
107.5°	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4	263.8	265.1	266.6
110°	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6	300.9	302.1	303.3



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2	336.2	337.3	338.5
115°	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7	388.6	389.6	390.5
117.5°	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7	439.8	440.9	442.1
120°	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2	471.6	473.1	474.4
122.5°	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5	503.6	504.7	505.9
125°	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6	547.8	549.0	550.3
127.5°	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3	590.5	591.7	593.0
130°	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9	617.2	618.4	619.6
132.5°	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4	642.6	643.9	645.1
135°	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4	681.4	682.2	683.2
137.5°	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7	714.8	716.0	717.2
140°	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8	736.8	737.7	738.7
142.5°	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4	757.3	758.3	759.2
145°	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1	786.2	787.3	788.3
147.5°	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2	812.8	813.6	814.3
150°	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9	829.2	829.7	830.2
152.5°	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8	844.0	844.2	844.4
155°	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9	864.6	864.3	863.9
157.5°	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3	881.3	881.2	881.2
160°	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3	891.1	891.0	890.8
162.5°	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7	900.3	899.8	899.5
165°	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1	911.6	911.2	910.7
167.5°	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0	920.3	919.7	919.1
170°	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0	925.3	924.7	924.1
172.5°	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3	928.5	927.7	927.1
175°	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6	932.7	932.0	931.2
177.5°	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6	934.1	933.4	932.8
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1472.7	1466.0	1461.4	1451.1	1444.5	1437.3	1430.1	1434.7	1434.3	1433.7	1433.7
5°	1423.3	1408.5	1395.2	1377.8	1366.9	1353.4	1343.1	1341.9	1344.4	1335.5	1330.3
7.5°	1374.3	1354.2	1335.1	1316.0	1295.7	1279.5	1269.4	1264.6	1258.1	1252.5	1246.8
10°	1339.9	1316.3	1297.6	1273.8	1252.1	1232.8	1220.7	1212.3	1207.8	1203.3	1195.0
12.5°	1304.6	1281.3	1257.6	1230.8	1210.0	1187.7	1178.6	1169.2	1160.6	1155.6	1144.2
15°	1252.7	1222.6	1197.6	1169.3	1146.2	1124.5	1111.6	1093.0	1090.4	1084.0	1072.5
17.5°	1200.8	1168.0	1133.5	1112.7	1086.6	1063.8	1044.3	1038.1	1019.7	1012.9	1002.8
20°	1159.7	1129.5	1103.2	1075.7	1037.8	1016.6	1001.3	993.0	978.2	969.2	962.8
22.5°	1124.3	1093.6	1063.3	1031.0	999.8	976.1	964.9	951.9	943.8	931.2	924.3
25°	1073.7	1040.4	1003.8	969.2	946.8	928.8	910.9	899.3	887.8	881.9	869.1
27.5°	1015.0	980.1	945.9	919.6	892.1	874.4	858.1	847.8	834.0	824.3	817.2
30°	982.7	941.6	912.1	888.3	853.1	836.4	824.3	811.4	801.2	790.9	783.8
32.5°	945.2	907.8	879.8	850.5	823.3	805.1	789.4	778.1	769.3	759.6	752.5
35°	886.5	855.1	826.1	796.6	776.7	758.2	739.6	729.9	721.6	712.7	706.2
37.5°	833.3	804.0	776.6	748.6	723.9	708.8	693.8	686.5	675.1	669.1	662.6
40°	800.5	771.7	742.2	715.2	689.6	678.0	664.5	653.7	643.4	638.9	631.8
42.5°	764.6	735.7	710.9	681.8	660.8	645.2	632.7	620.8	613.1	606.5	602.6
45°	711.3	685.7	661.3	632.4	612.6	599.1	584.9	574.1	567.0	562.5	555.4
47.5°	659.7	634.0	609.3	584.1	564.9	549.4	535.4	527.7	518.4	512.9	508.1
50°	622.2	599.1	572.8	549.7	530.5	515.1	503.5	493.9	485.6	478.5	475.3
52.5°	587.8	563.2	540.5	519.0	498.6	481.2	470.7	460.5	454.3	446.2	442.4
55°	531.1	507.4	488.1	466.9	447.0	432.3	419.5	410.5	404.1	395.1	390.0
57.5°	477.9	456.6	433.6	415.3	394.7	382.3	371.6	359.5	351.7	344.6	339.6
60°	442.0	417.5	397.7	380.4	362.4	346.4	336.8	327.2	318.8	311.7	307.3
62.5°	404.4	383.2	364.3	345.4	329.0	315.1	303.9	295.9	288.5	284.0	279.6
65°	347.0	330.4	311.1	295.7	280.3	270.0	261.1	254.0	248.8	245.6	241.9
67.5°	294.2	278.0	261.2	246.1	235.8	228.0	222.1	216.0	213.5	209.3	206.8
70°	259.8	243.1	228.4	216.8	206.5	200.8	196.9	192.5	189.8	184.7	182.2
72.5°	222.3	210.3	199.6	190.1	181.9	176.6	171.7	166.3	162.1	156.5	153.9
75°	175.1	164.2	155.9	149.5	144.3	137.2	130.2	124.4	122.5	120.6	120.0
77.5°	129.7	122.8	116.8	111.3	104.9	99.8	98.3	97.0	96.6	95.6	95.6
80°	102.0	95.6	91.0	84.6	80.8	80.8	80.8	79.6	80.2	80.2	80.2
82.5°	75.8	69.9	67.5	65.1	64.4	64.9	64.9	65.1	64.8	65.8	65.3
85°	39.1	39.8	41.1	40.4	41.1	41.1	42.3	41.7	42.3	41.1	42.3
87.5°	15.7	17.6	18.6	19.4	20.4	20.3	20.9	21.0	21.7	21.8	21.9
90°	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9	18.5	19.1	19.6
92.5°	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7	20.7	21.7	22.2
95°	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7	24.7	25.8	26.4
97.5°	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8	26.0	27.2	28.0
100°	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4	26.6	27.8	28.6
102.5°	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0	34.2	30.3	28.6
105°	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4	70.0	42.8	29.3
107.5°	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4	218.4	198.4	178.1
110°	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7	297.6	292.5	278.9



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0	348.1	348.2	345.8
115°	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2	402.7	404.3	405.4
117.5°	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4	450.6	451.9	452.5
120°	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1	482.3	483.5	484.1
122.5°	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9	512.7	513.7	514.2
125°	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4	555.8	556.1	556.4
127.5°	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2	599.6	600.1	600.2
130°	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5	626.0	626.7	626.9
132.5°	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4	651.0	651.7	651.8
135°	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2	688.7	689.2	689.2
137.5°	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0	722.7	723.5	723.7
140°	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4	743.9	744.6	744.8
142.5°	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6	764.1	764.6	764.7
145°	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0	792.3	792.6	792.8
147.5°	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4	817.7	818.0	817.7
150°	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9	833.2	833.5	833.5
152.5°	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7	847.3	847.8	847.7
155°	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7	866.5	867.3	867.2
157.5°	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3	883.2	884.1	884.0
160°	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7	892.7	893.5	893.5
162.5°	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3	901.4	902.4	902.4
165°	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7	912.9	914.2	914.3
167.5°	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6	921.9	923.1	923.1
170°	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6	926.9	928.1	928.1
172.5°	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0	930.2	931.4	931.3
175°	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9	934.1	935.1	935.0
177.5°	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4	935.4	936.4	936.2
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1427.6	1427.0	1427.6	1425.5	1427.6	1427.0	1427.6	1433.7	1433.7	1434.3	1434.7
5°	1328.4	1327.8	1325.9	1320.0	1325.9	1327.8	1328.4	1330.3	1335.5	1344.4	1341.9
7.5°	1241.8	1241.0	1235.3	1235.4	1235.3	1241.0	1241.8	1246.8	1252.5	1258.1	1264.6
10°	1190.5	1191.1	1183.5	1178.9	1183.5	1191.1	1190.5	1195.0	1203.3	1207.8	1212.3
12.5°	1140.8	1137.7	1131.6	1126.6	1131.6	1137.7	1140.8	1144.2	1155.6	1160.6	1169.2
15°	1075.1	1068.7	1053.2	1054.5	1053.2	1068.7	1075.1	1072.5	1084.0	1090.4	1093.0
17.5°	997.7	993.0	992.7	983.7	992.7	993.0	997.7	1002.8	1012.9	1019.7	1038.1
20°	952.5	949.3	950.6	941.6	950.6	949.3	952.5	962.8	969.2	978.2	993.0
22.5°	917.1	913.9	908.5	905.7	908.5	913.9	917.1	924.3	931.2	943.8	951.9
25°	865.3	860.2	855.1	858.3	855.1	860.2	865.3	869.1	881.9	887.8	899.3
27.5°	813.5	809.6	804.5	803.8	804.5	809.6	813.5	817.2	824.3	834.0	847.8
30°	780.6	776.7	774.2	771.0	774.2	776.7	780.6	783.8	790.9	801.2	811.4
32.5°	747.2	746.5	741.9	741.2	741.9	746.5	747.2	752.5	759.6	769.3	778.1
35°	703.6	699.8	698.5	699.2	698.5	699.8	703.6	706.2	712.7	721.6	729.9
37.5°	662.2	657.0	654.8	652.4	654.8	657.0	662.2	662.6	669.1	675.1	686.5
40°	632.4	627.4	626.0	624.7	626.0	627.4	632.4	631.8	638.9	643.4	653.7
42.5°	599.1	597.0	596.3	594.0	596.3	597.0	599.1	602.6	606.5	613.1	620.8
45°	553.6	552.9	549.0	550.4	549.0	552.9	553.6	555.4	562.5	567.0	574.1
47.5°	505.6	502.8	500.0	501.8	500.0	502.8	505.6	508.1	512.9	518.4	527.7
50°	472.8	471.5	465.7	466.9	465.7	471.5	472.8	475.3	478.5	485.6	493.9
52.5°	439.9	435.0	432.8	432.1	432.8	435.0	439.9	442.4	446.2	454.3	460.5
55°	385.5	379.8	377.2	375.9	377.2	379.8	385.5	390.0	395.1	404.1	410.5
57.5°	332.2	330.5	328.6	330.0	328.6	330.5	332.2	339.6	344.6	351.7	359.5
60°	300.9	300.9	300.9	300.2	300.9	300.9	300.9	307.3	311.7	318.8	327.2
62.5°	276.7	275.1	274.7	275.6	274.7	275.1	276.7	279.6	284.0	288.5	295.9
65°	239.9	239.2	236.7	236.0	236.7	239.2	239.9	241.9	245.6	248.8	254.0
67.5°	205.1	202.8	202.1	201.1	202.1	202.8	205.1	206.8	209.3	213.5	216.0
70°	179.0	177.7	173.8	174.5	173.8	177.7	179.0	182.2	184.7	189.8	192.5
72.5°	150.7	149.5	148.6	147.8	148.6	149.5	150.7	153.9	156.5	162.1	166.3
75°	119.3	118.7	118.0	120.6	118.0	118.7	119.3	120.0	120.6	122.5	124.4
77.5°	95.6	95.6	96.0	94.9	96.0	95.6	95.6	95.6	95.6	96.6	97.0
80°	80.2	80.2	79.6	79.6	79.6	80.2	80.2	80.2	80.2	80.2	79.6
82.5°	64.3	64.8	65.1	64.2	65.1	64.8	64.3	65.3	65.8	64.8	65.1
85°	42.3	41.7	43.0	42.3	43.0	41.7	42.3	42.3	41.1	42.3	41.7
87.5°	23.0	22.0	22.1	22.6	22.1	22.0	23.0	21.9	21.8	21.7	21.0
90°	19.9	20.2	20.5	20.8	20.5	20.2	19.9	19.6	19.1	18.5	17.9
92.5°	22.4	22.6	22.8	23.0	22.8	22.6	22.4	22.2	21.7	20.7	19.7
95°	26.4	26.4	26.4	26.4	26.4	26.4	26.4	26.4	25.8	24.7	23.7
97.5°	28.1	28.3	28.5	28.6	28.5	28.3	28.1	28.0	27.2	26.0	24.8
100°	28.7	28.8	28.9	29.1	28.9	28.8	28.7	28.6	27.8	26.6	25.4
102.5°	28.8	29.1	29.4	29.7	29.4	29.1	28.8	28.6	30.3	34.2	38.0
105°	29.6	29.9	30.3	30.5	30.3	29.9	29.6	29.3	42.8	70.0	97.4
107.5°	157.5	137.0	116.4	95.9	116.4	137.0	157.5	178.1	198.4	218.4	238.4
110°	256.8	234.8	212.7	190.8	212.7	234.8	256.8	278.9	292.5	297.6	302.7



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	341.2	336.6	331.9	327.3	331.9	336.6	341.2	345.8	348.2	348.1	348.0
115°	406.0	406.6	407.2	407.8	407.2	406.6	406.0	405.4	404.3	402.7	401.2
117.5°	452.7	452.8	452.9	453.1	452.9	452.8	452.7	452.5	451.9	450.6	449.4
120°	484.1	484.1	484.1	484.1	484.1	484.1	484.1	484.1	483.5	482.3	481.1
122.5°	514.3	514.3	514.5	514.6	514.5	514.3	514.3	514.2	513.7	512.7	511.9
125°	556.8	557.0	557.3	557.6	557.3	557.0	556.8	556.4	556.1	555.8	555.4
127.5°	599.9	599.6	599.3	599.0	599.3	599.6	599.9	600.2	600.1	599.6	599.2
130°	626.5	626.2	625.9	625.6	625.9	626.2	626.5	626.9	626.7	626.0	625.5
132.5°	651.3	650.9	650.4	650.0	650.4	650.9	651.3	651.8	651.7	651.0	650.4
135°	688.7	688.2	687.8	687.3	687.8	688.2	688.7	689.2	689.2	688.7	688.2
137.5°	723.4	723.0	722.7	722.5	722.7	723.0	723.4	723.7	723.5	722.7	722.0
140°	744.4	744.1	743.9	743.5	743.9	744.1	744.4	744.8	744.6	743.9	743.4
142.5°	764.2	763.8	763.4	762.9	763.4	763.8	764.2	764.7	764.6	764.1	763.6
145°	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.8	792.6	792.3	792.0
147.5°	817.1	816.3	815.7	814.9	815.7	816.3	817.1	817.7	818.0	817.7	817.4
150°	833.0	832.5	832.1	831.6	832.1	832.5	833.0	833.5	833.5	833.2	832.9
152.5°	847.1	846.3	845.6	844.9	845.6	846.3	847.1	847.7	847.8	847.3	846.7
155°	866.3	865.3	864.4	863.5	864.4	865.3	866.3	867.2	867.3	866.5	865.7
157.5°	882.8	881.6	880.4	879.2	880.4	881.6	882.8	884.0	884.1	883.2	882.3
160°	892.4	891.4	890.2	889.2	890.2	891.4	892.4	893.5	893.5	892.7	891.7
162.5°	901.4	900.5	899.6	898.6	899.6	900.5	901.4	902.4	902.4	901.4	900.3
165°	913.2	912.1	911.1	909.9	911.1	912.1	913.2	914.3	914.2	912.9	911.7
167.5°	921.9	920.6	919.4	918.1	919.4	920.6	921.9	923.1	923.1	921.9	920.6
170°	926.9	925.6	924.4	923.1	924.4	925.6	926.9	928.1	928.1	926.9	925.6
172.5°	930.0	928.7	927.3	926.0	927.3	928.7	930.0	931.3	931.4	930.2	929.0
175°	933.8	932.6	931.3	930.1	931.3	932.6	933.8	935.0	935.1	934.1	932.9
177.5°	935.0	933.8	932.6	931.3	932.6	933.8	935.0	936.2	936.4	935.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1430.1	1437.3	1444.5	1451.1	1461.4	1466.0	1472.7	1475.3	1483.0	1494.3	1503.5
5°	1343.1	1353.4	1366.9	1377.8	1395.2	1408.5	1423.3	1437.5	1454.2	1477.8	1499.0
7.5°	1269.4	1279.5	1295.7	1316.0	1335.1	1354.2	1374.3	1393.5	1417.4	1451.4	1485.2
10°	1220.7	1232.8	1252.1	1273.8	1297.6	1316.3	1339.9	1364.3	1393.8	1432.9	1473.4
12.5°	1178.6	1187.7	1210.0	1230.8	1257.6	1281.3	1304.6	1333.0	1366.6	1408.3	1457.0
15°	1111.6	1124.5	1146.2	1169.3	1197.6	1222.6	1252.7	1287.3	1320.0	1371.4	1430.4
17.5°	1044.3	1063.8	1086.6	1112.7	1133.5	1168.0	1200.8	1236.3	1276.6	1331.0	1395.7
20°	1001.3	1016.6	1037.8	1075.7	1103.2	1129.5	1159.7	1204.0	1241.1	1302.8	1370.1
22.5°	964.9	976.1	999.8	1031.0	1063.3	1093.6	1124.3	1166.5	1212.4	1270.9	1344.0
25°	910.9	928.8	946.8	969.2	1003.8	1040.4	1073.7	1109.7	1158.4	1220.7	1299.6
27.5°	858.1	874.4	892.1	919.6	945.9	980.1	1015.0	1056.2	1108.5	1174.3	1254.3
30°	824.3	836.4	853.1	888.3	912.1	941.6	982.7	1019.3	1068.0	1137.9	1222.6
32.5°	789.4	805.1	823.3	850.5	879.8	907.8	945.2	984.9	1034.6	1103.5	1190.2
35°	739.6	758.2	776.7	796.6	826.1	855.1	886.5	930.1	980.7	1047.4	1132.7
37.5°	693.8	708.8	723.9	748.6	776.6	804.0	833.3	876.3	924.1	996.0	1074.3
40°	664.5	678.0	689.6	715.2	742.2	771.7	800.5	838.4	889.7	957.1	1032.7
42.5°	632.7	645.2	660.8	681.8	710.9	735.7	764.6	800.4	848.6	917.0	983.4
45°	584.9	599.1	612.6	632.4	661.3	685.7	711.3	745.4	794.8	851.2	910.2
47.5°	535.4	549.4	564.9	584.1	609.3	634.0	659.7	689.8	734.8	790.2	830.0
50°	503.5	515.1	530.5	549.7	572.8	599.1	622.2	654.9	697.9	741.5	776.1
52.5°	470.7	481.2	498.6	519.0	540.5	563.2	587.8	615.9	654.8	695.8	723.3
55°	419.5	432.3	447.0	466.9	488.1	507.4	531.1	560.0	590.8	621.5	640.2
57.5°	371.6	382.3	394.7	415.3	433.6	456.6	477.9	500.3	528.8	552.0	564.2
60°	336.8	346.4	362.4	380.4	397.7	417.5	442.0	464.4	486.2	504.8	514.4
62.5°	303.9	315.1	329.0	345.4	364.3	383.2	404.4	423.4	442.6	458.6	465.1
65°	261.1	270.0	280.3	295.7	311.1	330.4	347.0	366.3	380.4	389.4	395.1
67.5°	222.1	228.0	235.8	246.1	261.2	278.0	294.2	309.2	320.9	327.2	332.2
70°	196.9	200.8	206.5	216.8	228.4	243.1	259.8	270.7	281.0	286.1	291.2
72.5°	171.7	176.6	181.9	190.1	199.6	210.3	222.3	235.8	241.5	247.6	250.7
75°	130.2	137.2	144.3	149.5	155.9	164.2	175.1	183.4	186.6	191.8	192.5
77.5°	98.3	99.8	104.9	111.3	116.8	122.8	129.7	137.1	138.6	141.4	143.1
80°	80.8	80.8	80.8	84.6	91.0	95.6	102.0	105.8	108.4	109.1	109.7
82.5°	64.9	64.9	64.4	65.1	67.5	69.9	75.8	80.2	82.2	81.8	80.4
85°	42.3	41.1	41.1	40.4	41.1	39.8	39.1	41.7	45.5	45.5	44.3
87.5°	20.9	20.3	20.4	19.4	18.6	17.6	15.7	15.9	15.6	17.3	16.6
90°	17.2	16.7	14.6	12.6	10.7	8.7	6.9	5.3	3.8	2.3	0.7
92.5°	18.8	17.7	16.2	14.7	13.2	11.7	11.2	11.6	12.1	12.4	12.9
95°	22.6	21.5	19.8	18.1	16.4	14.7	17.1	23.4	29.7	36.0	42.3
97.5°	23.6	22.3	33.5	44.5	55.6	66.7	73.7	76.5	79.4	82.2	85.0
100°	24.1	22.9	46.9	71.0	95.0	119.0	129.5	126.5	123.4	120.3	117.3
102.5°	41.8	45.6	71.9	98.1	124.4	150.7	162.7	160.5	158.3	156.1	153.8
105°	124.6	151.9	165.8	179.6	193.5	207.4	213.5	211.8	210.1	208.4	206.7
107.5°	258.4	278.4	276.3	274.0	271.8	269.7	267.9	266.6	265.1	263.8	262.4
110°	307.7	312.8	311.1	309.4	307.7	306.0	304.5	303.3	302.1	300.9	299.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.9	347.8	346.1	344.4	342.7	341.0	339.6	338.5	337.3	336.2	335.2
115°	399.6	398.1	396.7	395.3	394.0	392.6	391.4	390.5	389.6	388.6	387.7
117.5°	448.2	447.0	446.2	445.5	444.8	444.1	443.2	442.1	440.9	439.8	438.7
120°	479.8	478.5	478.2	477.7	477.2	476.7	475.8	474.4	473.1	471.6	470.2
122.5°	511.0	510.2	509.6	509.1	508.4	507.8	507.0	505.9	504.7	503.6	502.5
125°	555.2	554.9	554.2	553.6	553.0	552.4	551.5	550.3	549.0	547.8	546.6
127.5°	598.6	598.1	597.4	596.6	596.0	595.2	594.2	593.0	591.7	590.5	589.3
130°	624.8	624.2	623.6	623.0	622.4	621.8	620.9	619.6	618.4	617.2	615.9
132.5°	649.8	649.2	648.7	648.2	647.7	647.2	646.4	645.1	643.9	642.6	641.4
135°	687.8	687.3	686.7	686.1	685.5	684.9	684.1	683.2	682.2	681.4	680.4
137.5°	721.2	720.5	720.2	719.8	719.4	719.2	718.4	717.2	716.0	714.8	713.7
140°	742.7	742.2	741.7	741.2	740.7	740.3	739.6	738.7	737.7	736.8	735.8
142.5°	763.2	762.7	762.2	761.8	761.3	760.8	760.2	759.2	758.3	757.3	756.4
145°	791.6	791.4	791.1	790.8	790.4	790.1	789.5	788.3	787.3	786.2	785.1
147.5°	817.1	816.7	816.4	816.1	815.9	815.5	815.0	814.3	813.6	812.8	812.2
150°	832.6	832.3	832.0	831.7	831.4	831.0	830.7	830.2	829.7	829.2	828.9
152.5°	846.1	845.6	845.5	845.3	845.1	844.9	844.7	844.4	844.2	844.0	843.8
155°	865.0	864.2	864.0	863.9	863.7	863.6	863.7	863.9	864.3	864.6	864.9
157.5°	881.4	880.4	880.6	880.7	880.9	881.1	881.2	881.2	881.2	881.3	881.3
160°	890.8	889.9	890.0	890.1	890.3	890.5	890.6	890.8	891.0	891.1	891.3
162.5°	899.3	898.1	898.3	898.5	898.6	898.8	899.1	899.5	899.8	900.3	900.7
165°	910.5	909.3	909.5	909.6	909.7	909.9	910.2	910.7	911.2	911.6	912.1
167.5°	919.4	918.1	918.1	918.1	918.1	918.1	918.5	919.1	919.7	920.3	921.0
170°	924.4	923.1	923.1	923.1	923.1	923.1	923.5	924.1	924.7	925.3	926.0
172.5°	927.7	926.5	926.3	926.2	926.1	926.0	926.3	927.1	927.7	928.5	929.3
175°	931.9	930.8	930.7	930.5	930.3	930.2	930.5	931.2	932.0	932.7	933.6
177.5°	933.4	932.5	932.4	932.2	932.1	932.0	932.2	932.8	933.4	934.1	934.6
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1506.6	1512.2	1519.4	1530.2	1538.4	1545.6	1547.1	1549.2	1554.3	1563.0	1569.7
5°	1516.4	1531.1	1554.8	1577.9	1603.0	1623.4	1642.7	1656.1	1669.0	1695.9	1717.8
7.5°	1513.3	1546.1	1583.3	1624.8	1666.7	1707.3	1745.1	1778.9	1812.4	1851.7	1896.5
10°	1511.2	1549.7	1599.7	1652.9	1711.4	1768.4	1823.6	1866.6	1916.6	1961.5	2018.5
12.5°	1501.5	1556.9	1616.6	1684.8	1756.5	1822.3	1894.9	1954.3	2011.6	2076.4	2142.8
15°	1488.7	1556.1	1631.8	1722.2	1831.3	1910.8	1985.2	2088.5	2159.1	2229.6	2324.6
17.5°	1465.6	1547.7	1642.3	1759.8	1850.8	1957.7	2069.6	2151.3	2246.3	2345.7	2431.7
20°	1447.1	1542.7	1648.5	1764.0	1880.0	1996.1	2104.5	2202.1	2300.2	2415.0	2485.6
22.5°	1428.6	1523.1	1633.0	1755.8	1880.6	2002.8	2125.5	2240.0	2350.4	2466.3	2556.4
25°	1389.3	1501.6	1620.9	1746.0	1869.2	2003.8	2150.0	2277.7	2414.3	2533.6	2618.9
27.5°	1349.5	1452.5	1571.2	1698.1	1835.0	1994.2	2166.2	2311.3	2448.3	2533.6	2560.5
30°	1313.6	1422.7	1531.7	1660.7	1808.8	1986.5	2169.4	2335.4	2447.7	2484.9	2457.3
32.5°	1277.2	1376.0	1484.0	1616.0	1773.4	1967.6	2173.4	2321.1	2388.7	2360.2	2248.0
35°	1213.0	1302.1	1406.7	1538.8	1719.7	1957.0	2156.5	2256.5	2239.9	2079.5	1867.8
37.5°	1144.2	1216.8	1313.6	1451.8	1664.0	1915.3	2083.6	2098.4	1954.1	1707.9	1463.4
40°	1089.8	1155.2	1254.6	1398.9	1620.9	1874.2	2010.3	1950.6	1726.7	1452.8	1248.9
42.5°	1036.9	1092.1	1187.9	1343.5	1579.9	1818.4	1900.9	1771.0	1512.8	1253.8	1068.3
45°	947.3	999.4	1095.5	1255.3	1495.8	1711.4	1700.4	1474.6	1216.2	1007.7	853.8
47.5°	862.4	907.9	998.2	1161.2	1397.1	1551.0	1449.0	1208.7	989.5	822.2	712.4
50°	802.4	847.3	937.2	1098.2	1318.1	1430.4	1284.8	1053.2	852.4	713.9	626.7
52.5°	745.0	788.8	870.9	1027.8	1222.7	1289.8	1133.4	918.8	751.4	631.8	556.9
55°	664.5	697.9	771.7	921.7	1067.3	1082.7	924.3	744.7	606.8	523.4	472.1
57.5°	582.6	611.2	684.2	803.7	905.8	897.9	747.6	592.3	499.5	437.4	400.3
60°	529.1	557.4	621.5	724.2	801.2	774.2	636.3	511.2	431.7	386.2	356.7
62.5°	479.4	501.4	561.5	636.4	691.8	661.3	543.9	440.5	377.3	338.9	315.6
65°	407.3	425.3	473.3	512.5	543.3	513.8	416.3	344.4	298.9	271.9	255.9
67.5°	338.8	350.2	380.6	394.7	416.4	384.1	313.0	264.9	239.0	216.3	205.1
70°	295.7	304.1	320.1	331.6	337.4	304.1	251.5	216.1	194.4	178.3	171.3
72.5°	252.6	260.0	263.2	272.6	269.7	238.4	202.2	174.1	158.4	147.5	138.5
75°	193.0	196.2	193.0	189.3	180.9	159.1	134.0	120.0	108.4	103.3	100.1
77.5°	140.7	139.7	135.3	129.3	115.1	101.3	87.8	83.1	78.1	75.4	74.3
80°	108.4	105.8	102.0	92.4	80.2	70.6	67.4	64.2	62.2	59.0	58.3
82.5°	80.7	79.2	72.8	64.7	56.1	51.6	48.9	47.7	45.8	44.1	44.0
85°	43.0	41.1	34.0	29.5	28.2	27.0	26.3	26.3	23.8	23.1	23.1
87.5°	14.3	11.5	11.3	10.1	10.5	9.8	10.7	10.1	10.0	10.7	9.7
90°	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2	17.9
92.5°	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8	19.7
95°	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6	23.7
97.5°	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6	24.8
100°	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1	25.4
102.5°	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8	38.0
105°	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6	97.4
107.5°	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4	238.4
110°	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7	302.7



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9	348.0
115°	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6	401.2
117.5°	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2	449.4
120°	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8	481.1
122.5°	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0	511.9
125°	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2	555.4
127.5°	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6	599.2
130°	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8	625.5
132.5°	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8	650.4
135°	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8	688.2
137.5°	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2	722.0
140°	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7	743.4
142.5°	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2	763.6
145°	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6	792.0
147.5°	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1	817.4
150°	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6	832.9
152.5°	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1	846.7
155°	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0	865.7
157.5°	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4	882.3
160°	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8	891.7
162.5°	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3	900.3
165°	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5	911.7
167.5°	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4	920.6
170°	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4	925.6
172.5°	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7	929.0
175°	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9	932.9
177.5°	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4	934.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4	1498.4
2.5°	1580.5	1580.5	1582.5	1590.3	1591.3	1597.9	1595.9
5°	1737.0	1749.2	1753.7	1772.9	1784.4	1789.6	1779.3
7.5°	1928.4	1962.8	1979.1	1999.2	2017.0	2022.4	2008.5
10°	2067.9	2103.8	2134.0	2152.7	2169.9	2181.5	2196.2
12.5°	2202.9	2247.0	2275.7	2302.0	2319.8	2334.4	2336.8
15°	2349.6	2416.3	2466.9	2504.1	2522.7	2532.3	2528.6
17.5°	2497.5	2559.3	2595.4	2633.4	2659.1	2660.4	2661.2
20°	2581.2	2641.4	2683.1	2711.3	2740.2	2738.9	2745.3
22.5°	2637.0	2684.5	2716.5	2737.0	2746.9	2742.0	2743.3
25°	2663.2	2677.3	2671.5	2638.8	2630.5	2600.4	2605.5
27.5°	2528.3	2461.5	2392.6	2303.8	2233.7	2177.7	2180.6
30°	2345.0	2227.0	2092.4	1979.4	1878.1	1849.9	1789.6
32.5°	2089.1	1911.9	1754.2	1649.0	1562.0	1538.4	1485.8
35°	1654.9	1483.0	1320.7	1223.2	1184.7	1130.9	1130.2
37.5°	1286.3	1134.9	1049.1	976.0	937.6	905.0	901.8
40°	1082.1	964.0	899.3	846.7	808.9	784.5	778.7
42.5°	939.4	844.0	783.3	750.7	721.6	709.1	699.6
45°	767.1	703.0	660.6	631.1	617.7	608.0	602.9
47.5°	641.7	598.7	569.9	550.3	539.3	529.1	531.9
50°	573.4	538.2	517.0	498.4	490.0	483.0	483.6
52.5°	518.5	486.8	469.8	456.3	445.9	440.9	438.5
55°	440.0	420.1	402.8	393.2	387.4	380.4	378.4
57.5°	375.3	360.0	345.8	335.0	333.6	326.8	327.6
60°	332.2	319.4	307.9	302.1	297.7	291.8	293.8
62.5°	296.9	286.1	275.6	270.8	266.4	262.1	263.0
65°	243.1	232.8	226.4	223.9	222.0	220.0	218.1
67.5°	193.7	187.5	183.4	178.0	174.0	173.3	171.4
70°	163.0	154.6	147.5	140.4	138.6	137.9	138.6
72.5°	130.6	125.4	123.4	120.0	119.6	117.9	119.0
75°	98.1	96.2	94.9	92.4	92.4	92.4	92.4
77.5°	72.4	71.2	70.4	69.9	69.3	68.3	68.2
80°	56.5	55.8	54.5	54.5	53.9	54.5	53.9
82.5°	42.6	42.5	41.2	41.2	40.5	40.2	40.5
85°	21.8	21.2	22.4	21.2	21.8	20.5	21.8
87.5°	9.9	10.0	9.5	9.6	9.1	10.3	9.3
90°	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332454-830

CATALOG NUMBER: S123RDIW-S1000D755U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)