

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332480-830

Luminaire Tested: **S123RDIW-S1165D1030U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332480-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1030U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8016.3 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	37
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.1
10°-20°	477.3	6.0
20°-30°	687.3	8.6
30°-40°	774.2	9.7
40°-50°	740.6	9.2
50°-60°	606.5	7.6
60°-70°	409.2	5.1
70°-80°	205.9	2.6
80°-90°	58.0	0.7
90°-100°	46.3	0.6
100°-110°	220.8	2.8
110°-120°	530.4	6.6
120°-130°	675.4	8.4
130°-140°	721.6	9.0
140°-150°	674.8	8.4
150°-160°	544.3	6.8
160°-170°	351.3	4.4
170°-180°	121.1	1.5
0°-30°	1336.1	16.7
0°-40°	2110.3	26.3
0°-60°	3457.4	43.1
0°-90°	4130.5	51.5
90°-120°	797.5	9.9
90°-150°	2869.2	35.8
90°-180°	3886.0	48.5
0°-180°	8016.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	11	23	26	28	7
95°	58	22	29	36	36	71
105°	282	287	207	49	42	299
115°	529	535	543	553	557	522
125°	746	753	757	759	761	666
135°	929	934	938	941	938	715
145°	1072	1078	1080	1082	1082	671
155°	1180	1179	1180	1184	1179	544
165°	1245	1242	1241	1248	1242	352
175°	1274	1270	1270	1276	1270	121
180°	1274	1274	1274	1274	1274	



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.7	26.2	23.7	21.2	18.8	17.7	18.3	18.9	19.4	20.0	19.9
90°	0.9	3.0	5.2	7.3	9.3	11.8	14.5	17.2	20.0	22.7	23.6
92.5°	17.6	17.1	16.4	15.8	15.3	16.0	18.1	20.1	22.1	24.2	25.5
95°	57.8	49.1	40.5	31.9	23.3	20.1	22.4	24.7	27.1	29.3	30.8
97.5°	116.0	112.2	108.3	104.4	100.6	91.0	76.0	60.8	45.6	30.4	32.1
100°	159.9	164.2	168.4	172.6	176.8	162.5	129.7	96.9	64.1	31.2	32.9
102.5°	210.0	213.0	216.0	219.0	222.1	205.7	169.8	134.0	98.1	62.3	57.1
105°	282.1	284.5	286.7	289.1	291.3	283.0	264.1	245.2	226.3	207.4	170.1
107.5°	358.3	360.1	361.9	363.8	365.6	368.1	371.1	374.0	377.0	380.0	352.7
110°	409.0	410.7	412.4	414.1	415.7	417.7	420.0	422.4	424.6	427.0	420.0



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	457.4	458.9	460.4	462.0	463.5	465.4	467.7	470.0	472.4	474.7	474.8
115°	529.2	530.5	531.7	533.0	534.2	535.8	537.7	539.6	541.5	543.4	545.5
117.5°	598.7	600.2	601.8	603.3	604.9	606.1	607.2	608.1	609.1	610.0	611.7
120°	641.9	643.8	645.6	647.5	649.4	650.7	651.3	652.0	652.6	653.2	654.9
122.5°	685.8	687.3	688.9	690.4	692.0	693.1	694.0	694.7	695.6	696.4	697.6
125°	746.0	747.7	749.3	751.0	752.7	754.0	754.8	755.6	756.5	757.3	757.8
127.5°	804.3	806.0	807.7	809.4	811.1	812.4	813.4	814.5	815.4	816.4	817.1
130°	840.7	842.4	844.0	845.7	847.4	848.7	849.5	850.4	851.2	852.1	852.9
132.5°	875.5	877.2	878.8	880.5	882.2	883.4	884.1	884.8	885.4	886.1	886.9
135°	928.7	930.0	931.2	932.5	933.8	934.8	935.7	936.5	937.4	938.2	938.8
137.5°	974.1	975.7	977.3	978.9	980.5	981.6	982.0	982.5	983.0	983.4	984.4
140°	1004.5	1005.7	1007.0	1008.2	1009.5	1010.4	1011.1	1011.7	1012.3	1013.0	1013.8
142.5°	1032.5	1033.7	1035.0	1036.2	1037.6	1038.5	1039.1	1039.7	1040.4	1040.9	1041.7
145°	1071.7	1073.1	1074.6	1076.1	1077.5	1078.5	1078.9	1079.3	1079.8	1080.2	1080.6
147.5°	1108.6	1109.6	1110.5	1111.4	1112.5	1113.1	1113.5	1114.0	1114.4	1114.8	1115.2
150°	1131.3	1131.9	1132.6	1133.2	1133.8	1134.3	1134.7	1135.2	1135.6	1136.0	1136.4
152.5°	1151.8	1152.1	1152.4	1152.6	1152.9	1153.2	1153.5	1153.7	1154.0	1154.2	1155.0
155°	1180.5	1180.1	1179.7	1179.3	1178.8	1178.7	1178.9	1179.1	1179.4	1179.6	1180.6
157.5°	1202.9	1202.9	1202.8	1202.8	1202.7	1202.6	1202.4	1202.1	1201.9	1201.7	1203.0
160°	1216.5	1216.3	1216.1	1215.9	1215.7	1215.4	1215.2	1215.0	1214.8	1214.7	1215.9
162.5°	1229.4	1228.8	1228.3	1227.8	1227.2	1226.8	1226.6	1226.4	1226.2	1226.0	1227.4
165°	1244.9	1244.3	1243.7	1243.0	1242.4	1242.0	1241.7	1241.5	1241.3	1241.1	1242.8
167.5°	1257.0	1256.2	1255.4	1254.5	1253.7	1253.2	1253.2	1253.2	1253.2	1253.2	1254.9
170°	1263.9	1263.0	1262.2	1261.3	1260.5	1260.1	1260.1	1260.1	1260.1	1260.1	1261.7
172.5°	1268.4	1267.3	1266.4	1265.4	1264.3	1263.9	1264.0	1264.2	1264.4	1264.6	1266.3
175°	1274.2	1273.2	1272.1	1271.1	1270.1	1269.6	1269.8	1270.1	1270.3	1270.5	1272.0
177.5°	1275.7	1274.9	1274.1	1273.3	1272.4	1272.1	1272.2	1272.4	1272.5	1272.7	1274.1
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	19.8	19.7	19.6	19.4	19.2	19.0	18.9	18.8
90°	24.4	25.3	26.1	26.7	27.1	27.5	28.0	28.4
92.5°	27.0	28.3	29.6	30.4	30.6	30.9	31.2	31.4
95°	32.3	33.7	35.3	36.0	36.0	36.0	36.0	36.0
97.5°	33.8	35.5	37.2	38.2	38.4	38.5	38.8	39.0
100°	34.6	36.3	38.0	38.9	39.1	39.3	39.6	39.8
102.5°	51.8	46.7	41.4	39.0	39.4	39.8	40.2	40.5
105°	132.9	95.6	58.3	40.0	40.4	40.8	41.2	41.7
107.5°	325.4	298.1	270.8	243.1	215.0	187.0	158.9	130.8
110°	413.1	406.1	399.2	380.7	350.6	320.5	290.4	260.3



TEST NUMBER: P332480-830

CATALOG NUMBER: S123RDIW-S1165D1030U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	474.9	475.0	475.1	472.0	465.7	459.4	453.0	446.7
115°	547.6	549.7	551.9	553.3	554.1	555.0	555.8	556.7
117.5°	613.4	615.1	616.8	617.7	617.8	618.0	618.2	618.4
120°	656.6	658.3	660.0	660.8	660.8	660.8	660.8	660.8
122.5°	698.7	699.9	701.1	701.8	701.9	702.1	702.3	702.5
125°	758.2	758.7	759.0	759.5	759.9	760.3	760.7	761.1
127.5°	817.7	818.4	819.2	819.3	818.8	818.4	818.0	817.6
130°	853.8	854.5	855.4	855.6	855.2	854.8	854.3	853.9
132.5°	887.8	888.6	889.5	889.6	889.0	888.4	887.9	887.2
135°	939.4	940.1	940.7	940.7	940.1	939.4	938.8	938.2
137.5°	985.4	986.5	987.5	987.8	987.3	986.9	986.5	986.1
140°	1014.6	1015.5	1016.3	1016.5	1016.2	1015.7	1015.3	1014.8
142.5°	1042.4	1043.0	1043.7	1043.7	1043.1	1042.5	1042.0	1041.3
145°	1081.0	1081.5	1081.9	1082.0	1082.0	1082.0	1082.0	1082.0
147.5°	1115.7	1116.1	1116.5	1116.3	1115.3	1114.3	1113.3	1112.4
150°	1136.9	1137.3	1137.7	1137.6	1137.0	1136.3	1135.8	1135.1
152.5°	1155.7	1156.5	1157.3	1157.2	1156.1	1155.2	1154.2	1153.3
155°	1181.7	1182.7	1183.8	1183.6	1182.4	1181.2	1179.9	1178.6
157.5°	1204.3	1205.5	1206.7	1206.5	1204.9	1203.3	1201.6	1200.0
160°	1217.1	1218.4	1219.7	1219.6	1218.0	1216.6	1215.1	1213.6
162.5°	1228.8	1230.3	1231.7	1231.7	1230.5	1229.2	1227.9	1226.5
165°	1244.4	1246.1	1247.8	1247.9	1246.5	1245.0	1243.5	1242.1
167.5°	1256.6	1258.3	1260.0	1260.0	1258.3	1256.6	1254.9	1253.2
170°	1263.4	1265.1	1266.8	1266.8	1265.1	1263.4	1261.7	1260.1
172.5°	1268.0	1269.6	1271.3	1271.2	1269.4	1267.5	1265.6	1263.9
175°	1273.4	1274.9	1276.4	1276.3	1274.6	1272.9	1271.2	1269.5
177.5°	1275.4	1276.8	1278.1	1278.0	1276.3	1274.6	1272.9	1271.2
180°	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2	1274.2

(END OF REPORT)