

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332482-830

Luminaire Tested: **S123RDIW-S1165D1320U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332482-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1320U830-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9287.9 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	32	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18627	18627	18627	18627
5°	22204	18707	16473	18707
10°	27725	18600	14882	18600
15°	32543	18409	13572	18409
20°	36318	18125	12457	18125
25°	35739	17826	11772	17826
30°	25690	17550	11067	17550
35°	17152	17190	10611	17190
40°	12638	16759	10138	16759
45°	10601	16002	9677	16002
50°	9354	15011	9031	15011
55°	8203	13874	8146	13874
60°	7304	12790	7464	12790
65°	6413	11624	6943	11624
70°	5035	10584	6342	10584
75°	4438	9245	5793	9245
80°	3856	7854	5697	7854
85°	3112	6311	6039	6311



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.2	1.8
10°-20°	531.7	5.7
20°-30°	835.3	9.0
30°-40°	871.4	9.4
40°-50°	745.8	8.0
50°-60°	568.4	6.1
60°-70°	364.3	3.9
70°-80°	175.3	1.9
80°-90°	50.9	0.5
90°-100°	59.3	0.6
100°-110°	282.7	3.0
110°-120°	679.0	7.3
120°-130°	864.6	9.3
130°-140°	923.8	9.9
140°-150°	863.8	9.3
150°-160°	696.8	7.5
160°-170°	449.7	4.8
170°-180°	155.0	1.7
0°-30°	1537.1	16.5
0°-40°	2408.6	25.9
0°-60°	3722.7	40.1
0°-90°	4313.3	46.4
90°-120°	1020.9	11.0
90°-150°	3673.1	39.5
90°-180°	4975.0	53.6
0°-180°	9287.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1730	1730	1730	1730	1730	
5°	2055	1731	1525	1731	2055	212
15°	2920	1652	1218	1652	2920	828
25°	3009	1501	991	1501	3009	1293
35°	1305	1308	808	1308	1305	856
45°	696	1051	636	1051	696	548
55°	437	739	434	739	437	395
65°	252	456	273	456	252	248
75°	107	222	139	222	107	114
85°	25	51	49	51	25	30
90°	36	1	36	1	36	17
95°	46	74	46	74	46	39
105°	53	361	53	361	53	122
115°	713	678	713	678	713	658
125°	974	955	974	955	974	870
135°	1201	1189	1201	1189	1201	926
145°	1385	1372	1385	1372	1385	865
155°	1509	1511	1509	1511	1509	696
165°	1590	1594	1590	1594	1590	449
175°	1625	1631	1625	1631	1625	155
180°	1631	1631	1631	1631	1631	



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1843.1	1845.5	1837.8	1836.6	1827.7	1825.3	1825.3	1812.9	1805.2	1795.2	1789.2
5°	2055.0	2066.9	2061.0	2047.6	2025.3	2020.2	2006.1	1983.9	1958.7	1927.6	1912.8
7.5°	2319.6	2335.8	2329.6	2308.9	2285.7	2266.9	2227.1	2190.3	2138.5	2093.2	2054.4
10°	2536.6	2519.5	2506.1	2486.1	2464.7	2429.9	2388.4	2331.3	2265.4	2213.6	2155.8
12.5°	2698.9	2696.1	2679.2	2658.6	2628.3	2595.2	2544.2	2474.7	2398.1	2323.2	2257.1
15°	2920.3	2924.7	2913.6	2892.1	2849.1	2790.6	2713.6	2684.7	2575.0	2493.6	2412.1
17.5°	3073.4	3072.6	3071.1	3041.3	2997.5	2955.8	2884.4	2808.4	2709.2	2594.3	2484.5
20°	3170.6	3163.3	3164.8	3131.4	3098.8	3050.6	2981.0	2870.6	2789.2	2656.6	2543.2
22.5°	3168.3	3166.8	3172.4	3161.0	3137.3	3100.4	3045.6	2952.4	2848.5	2714.6	2587.1
25°	3009.2	3003.2	3038.1	3047.7	3085.5	3092.1	3075.8	3024.7	2926.2	2788.4	2630.6
27.5°	2518.5	2515.2	2579.8	2660.7	2763.3	2842.9	2920.0	2957.1	2926.2	2827.5	2669.5
30°	2066.9	2136.5	2169.1	2286.1	2416.5	2572.1	2708.4	2838.0	2869.9	2827.0	2697.3
32.5°	1716.0	1776.8	1804.0	1904.5	2026.0	2208.2	2412.6	2596.2	2725.9	2758.7	2680.7
35°	1305.3	1306.1	1368.3	1412.7	1525.3	1712.8	1911.3	2157.2	2401.7	2586.9	2606.1
37.5°	1041.6	1045.3	1082.9	1127.2	1211.6	1310.8	1485.6	1690.1	1972.5	2256.8	2423.5
40°	899.4	906.0	934.2	977.9	1038.6	1113.4	1249.7	1442.4	1677.9	1994.2	2252.8
42.5°	808.0	818.9	833.4	867.0	904.7	974.8	1085.0	1233.8	1448.0	1747.1	2045.4
45°	696.4	702.3	713.4	729.0	763.0	811.9	886.0	986.0	1163.9	1404.6	1703.1
47.5°	614.3	611.1	622.8	635.5	658.2	691.4	741.1	822.7	949.6	1142.7	1396.0
50°	558.6	557.8	566.0	575.6	597.1	621.5	662.3	723.8	824.5	984.6	1216.4
52.5°	506.4	509.3	515.0	527.0	542.5	562.3	598.9	643.2	729.7	867.8	1061.1
55°	437.1	439.3	447.4	454.1	465.2	485.2	508.2	545.3	604.5	700.8	860.1
57.5°	378.4	377.4	385.2	386.8	399.4	415.8	433.5	462.2	505.2	576.8	684.1
60°	339.3	337.1	343.7	348.9	355.6	368.9	383.7	411.9	446.0	498.6	590.4
62.5°	303.7	302.7	307.6	312.7	318.3	330.4	342.8	364.5	391.4	435.7	508.6
65°	251.8	254.1	256.3	258.5	261.5	268.9	280.8	295.6	314.1	345.3	397.8
67.5°	197.9	200.2	201.0	205.5	211.9	216.5	223.8	237.0	249.8	276.1	305.9
70°	160.0	159.3	160.0	162.2	170.4	178.5	188.1	197.8	205.9	224.4	249.7
72.5°	137.5	136.2	138.1	138.6	142.5	144.8	150.8	159.9	170.4	182.9	201.0
75°	106.7	106.7	106.7	106.7	109.6	111.1	113.4	115.6	119.2	125.2	138.6
77.5°	78.8	79.0	80.0	80.8	81.3	82.2	83.6	85.8	87.1	90.2	96.0
80°	62.2	63.0	62.2	63.0	63.0	64.5	65.2	67.4	68.1	71.8	74.1
82.5°	46.8	46.4	46.8	47.6	47.6	49.0	49.2	50.8	51.0	52.9	55.1
85°	25.2	23.8	25.2	24.4	25.9	24.4	25.2	26.7	26.7	27.4	30.3
87.5°	13.2	14.2	13.0	13.5	13.4	13.8	13.6	13.4	14.3	13.5	13.4
90°	36.4	35.8	35.3	34.8	34.2	33.4	32.3	31.2	30.2	29.1	25.5
92.5°	40.2	39.9	39.6	39.3	38.9	37.9	36.2	34.5	32.7	31.0	28.4
95°	46.1	46.1	46.1	46.1	46.1	45.1	43.3	41.4	39.5	37.6	34.6
97.5°	50.0	49.7	49.4	49.1	48.8	47.6	45.5	43.4	41.2	39.0	58.4
100°	50.9	50.6	50.3	50.0	49.9	48.6	46.5	44.3	42.1	40.0	82.0
102.5°	51.8	51.4	50.9	50.4	50.0	53.1	59.7	66.4	73.0	79.7	125.6
105°	53.3	52.8	52.2	51.7	51.2	74.7	122.4	170.0	217.7	265.4	289.6
107.5°	167.5	203.4	239.3	275.3	311.2	346.7	381.6	416.6	451.5	486.4	482.7
110°	333.3	371.8	410.3	448.8	487.3	511.0	519.9	528.8	537.7	546.6	543.7



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	571.8	579.9	588.1	596.2	604.4	608.3	608.1	608.0	607.8	607.7	604.7
115°	712.7	711.5	710.5	709.4	708.3	706.4	703.7	701.1	698.3	695.7	693.2
117.5°	791.6	791.5	791.2	791.0	790.8	789.6	787.4	785.3	783.2	781.0	779.8
120°	845.9	845.9	845.9	845.9	845.9	844.9	842.7	840.6	838.4	836.2	835.5
122.5°	899.3	899.1	898.8	898.6	898.4	897.6	896.1	894.6	893.1	891.6	890.5
125°	974.4	973.8	973.4	972.8	972.2	971.7	971.2	970.6	970.1	969.6	968.5
127.5°	1046.6	1047.2	1047.7	1048.3	1048.8	1048.7	1047.7	1046.9	1046.0	1045.2	1043.9
130°	1093.2	1093.7	1094.3	1094.8	1095.3	1095.0	1094.0	1092.9	1091.8	1090.7	1089.7
132.5°	1135.9	1136.6	1137.4	1138.1	1138.9	1138.7	1137.6	1136.5	1135.5	1134.3	1133.5
135°	1201.1	1201.8	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1	1200.0
137.5°	1262.3	1262.9	1263.5	1263.9	1264.5	1264.1	1262.8	1261.6	1260.3	1259.0	1258.4
140°	1299.2	1299.8	1300.2	1300.8	1301.4	1301.1	1300.0	1298.9	1297.9	1296.8	1296.0
142.5°	1333.1	1333.9	1334.6	1335.4	1336.1	1336.1	1335.2	1334.4	1333.5	1332.7	1331.8
145°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.0	1384.4	1383.9	1383.4	1382.8	1382.3
147.5°	1424.0	1425.3	1426.5	1427.8	1429.0	1429.4	1428.8	1428.2	1427.8	1427.2	1426.6
150°	1453.1	1454.0	1454.7	1455.6	1456.3	1456.5	1455.9	1455.4	1454.9	1454.3	1453.8
152.5°	1476.4	1477.6	1478.8	1480.1	1481.4	1481.5	1480.5	1479.5	1478.6	1477.6	1477.2
155°	1508.9	1510.5	1512.1	1513.7	1515.3	1515.5	1514.1	1512.8	1511.5	1510.0	1509.9
157.5°	1536.3	1538.3	1540.5	1542.6	1544.6	1544.9	1543.3	1541.7	1540.0	1538.4	1538.7
160°	1553.7	1555.6	1557.5	1559.3	1561.2	1561.4	1559.8	1558.1	1556.5	1554.9	1555.2
162.5°	1570.2	1571.9	1573.6	1575.2	1576.9	1576.8	1575.0	1573.1	1571.3	1569.4	1569.7
165°	1590.1	1592.0	1593.8	1595.7	1597.6	1597.5	1595.3	1593.2	1591.0	1588.8	1589.1
167.5°	1604.4	1606.6	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4	1604.4
170°	1613.1	1615.2	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1	1613.1
172.5°	1618.0	1620.3	1622.7	1625.0	1627.4	1627.6	1625.4	1623.2	1621.1	1618.9	1618.7
175°	1625.2	1627.4	1629.6	1631.7	1633.8	1634.0	1632.1	1630.2	1628.3	1626.5	1626.2
177.5°	1627.4	1629.6	1631.7	1633.9	1636.1	1636.3	1634.6	1632.8	1631.1	1629.4	1629.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1786.9	1785.1	1776.8	1767.3	1754.8	1746.5	1740.0	1736.4	1725.8	1712.8	1703.8
5°	1897.2	1875.0	1851.2	1822.4	1795.7	1768.3	1751.2	1731.3	1706.9	1679.4	1660.2
7.5°	2015.4	1971.9	1925.0	1876.5	1828.6	1785.6	1747.8	1715.2	1676.3	1637.0	1609.5
10°	2106.1	2042.4	1976.5	1909.0	1847.6	1789.8	1745.3	1701.7	1655.0	1609.8	1575.7
12.5°	2188.5	2104.6	2028.6	1945.8	1867.2	1798.1	1734.1	1682.6	1626.5	1578.4	1539.5
15°	2292.8	2206.9	2115.0	1989.0	1884.6	1797.2	1719.4	1652.0	1583.8	1524.6	1486.8
17.5°	2390.3	2261.0	2137.5	2032.5	1896.8	1787.5	1692.6	1612.0	1537.2	1474.3	1427.9
20°	2430.6	2305.4	2171.3	2037.2	1903.8	1781.7	1671.2	1582.3	1504.6	1433.4	1390.5
22.5°	2454.9	2313.1	2171.9	2027.8	1886.1	1759.2	1649.9	1552.2	1467.8	1400.2	1347.3
25°	2483.2	2314.3	2158.7	2016.5	1872.0	1734.3	1604.6	1500.9	1409.8	1337.9	1281.6
27.5°	2501.9	2303.2	2119.3	1961.2	1814.7	1677.4	1558.7	1448.7	1356.3	1280.3	1219.8
30°	2505.4	2294.2	2089.1	1918.0	1769.1	1643.1	1517.2	1412.0	1314.2	1233.4	1177.1
32.5°	2510.2	2272.4	2048.1	1866.4	1713.9	1589.2	1475.1	1374.6	1274.5	1195.0	1137.5
35°	2490.6	2260.2	1986.1	1777.2	1624.6	1503.8	1400.9	1308.2	1209.8	1132.7	1074.2
37.5°	2406.4	2212.1	1921.8	1676.8	1517.2	1405.3	1321.4	1240.7	1150.4	1067.2	1012.1
40°	2321.7	2164.6	1872.0	1615.7	1449.1	1334.2	1258.7	1192.7	1105.3	1027.5	968.3
42.5°	2195.5	2100.1	1824.6	1551.7	1372.0	1261.3	1197.6	1135.8	1059.0	980.1	924.4
45°	1963.9	1976.5	1727.6	1449.7	1265.3	1154.1	1094.2	1051.2	983.1	917.8	860.8
47.5°	1673.5	1791.3	1613.6	1341.1	1152.8	1048.6	996.1	958.6	912.7	848.7	796.6
50°	1483.8	1652.0	1522.4	1268.3	1082.3	978.6	926.7	896.4	856.4	806.0	756.4
52.5°	1309.0	1489.6	1412.1	1187.0	1005.9	911.1	860.4	835.4	803.6	756.2	711.3
55°	1067.5	1250.5	1232.8	1064.5	891.2	806.0	767.5	739.3	717.8	682.3	646.8
57.5°	863.5	1037.0	1046.1	928.2	790.1	706.0	672.8	651.6	637.5	610.8	577.9
60°	734.9	894.2	925.3	836.4	717.8	643.8	611.1	594.1	583.1	561.6	536.3
62.5°	628.2	763.7	799.0	735.0	648.5	579.2	553.6	537.2	529.7	511.1	488.9
65°	480.8	593.4	627.5	591.9	546.7	491.2	470.4	456.4	449.7	439.3	423.0
67.5°	361.6	443.6	481.0	455.9	439.6	404.4	391.2	383.7	377.8	370.7	357.0
70°	290.4	351.1	389.6	383.0	369.7	351.1	341.5	336.3	330.4	324.5	312.6
72.5°	233.5	275.3	311.4	314.8	303.9	300.2	291.7	289.5	286.0	278.8	272.3
75°	154.9	183.7	208.9	218.6	223.0	226.7	223.0	222.3	221.5	215.6	211.9
77.5°	101.5	117.1	132.9	149.4	156.3	161.4	162.5	165.2	163.2	160.1	158.3
80°	77.8	81.5	92.6	106.7	117.8	122.2	125.2	126.7	125.9	125.2	122.2
82.5°	56.5	59.6	64.8	74.6	84.0	91.4	93.2	92.9	94.5	95.0	92.6
85°	30.3	31.1	32.6	34.1	39.3	47.4	49.7	51.1	52.6	52.6	48.2
87.5°	13.9	12.6	13.1	12.4	13.7	13.8	16.8	19.2	20.4	18.5	19.0
90°	22.1	18.6	15.1	12.0	9.3	6.6	3.9	1.2	3.9	6.6	9.3
92.5°	25.7	23.1	20.5	19.5	20.3	21.0	21.8	22.5	21.8	21.0	20.3
95°	31.7	28.7	25.7	29.8	40.8	51.8	62.9	73.9	62.9	51.8	40.8
97.5°	77.9	97.2	116.6	128.8	133.7	138.6	143.6	148.5	143.6	138.6	133.7
100°	124.0	166.1	208.0	226.4	220.9	215.6	210.2	204.8	210.2	215.6	220.9
102.5°	171.5	217.4	263.3	284.4	280.4	276.5	272.7	268.8	272.7	276.5	280.4
105°	313.9	338.1	362.4	373.0	370.0	367.1	364.1	361.2	364.1	367.1	370.0
107.5°	478.8	475.0	471.2	468.1	465.7	463.4	461.0	458.6	461.0	463.4	465.7
110°	540.6	537.7	534.7	532.2	530.0	527.8	525.8	523.6	525.8	527.8	530.0





TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	601.7	598.8	595.8	593.3	591.4	589.5	587.6	585.6	587.6	589.5	591.4
115°	690.8	688.3	686.0	683.9	682.3	680.7	679.1	677.5	679.1	680.7	682.3
117.5°	778.5	777.2	776.0	774.4	772.4	770.4	768.5	766.5	768.5	770.4	772.4
120°	834.6	833.8	833.0	831.4	829.0	826.5	824.2	821.7	824.2	826.5	829.0
122.5°	889.5	888.4	887.4	885.9	883.9	881.9	880.0	878.0	880.0	881.9	883.9
125°	967.4	966.3	965.3	963.7	961.5	959.3	957.2	955.0	957.2	959.3	961.5
127.5°	1042.6	1041.3	1040.0	1038.3	1036.1	1034.0	1031.8	1029.6	1031.8	1034.0	1036.1
130°	1088.6	1087.5	1086.5	1084.9	1082.7	1080.5	1078.4	1076.2	1078.4	1080.5	1082.7
132.5°	1132.7	1131.8	1131.0	1129.4	1127.3	1125.1	1122.9	1120.8	1122.9	1125.1	1127.3
135°	1198.9	1197.8	1196.7	1195.4	1193.7	1192.1	1190.5	1188.9	1190.5	1192.1	1193.7
137.5°	1257.8	1257.2	1256.6	1255.3	1253.2	1251.2	1249.2	1247.1	1249.2	1251.2	1253.2
140°	1295.1	1294.4	1293.5	1292.3	1290.7	1289.1	1287.5	1285.9	1287.5	1289.1	1290.7
142.5°	1331.1	1330.2	1329.5	1328.2	1326.6	1325.0	1323.3	1321.7	1323.3	1325.0	1326.6
145°	1381.8	1381.2	1380.6	1379.5	1377.6	1375.7	1373.9	1372.0	1373.9	1375.7	1377.6
147.5°	1426.1	1425.6	1425.0	1424.2	1422.9	1421.6	1420.4	1419.2	1420.4	1421.6	1422.9
150°	1453.2	1452.7	1452.2	1451.5	1450.7	1449.9	1449.1	1448.3	1449.1	1449.9	1450.7
152.5°	1477.0	1476.7	1476.3	1475.9	1475.6	1475.2	1474.8	1474.4	1474.8	1475.2	1475.6
155°	1509.6	1509.3	1509.0	1509.1	1509.7	1510.2	1510.8	1511.3	1510.8	1510.2	1509.7
157.5°	1539.0	1539.3	1539.5	1539.6	1539.7	1539.8	1539.8	1539.9	1539.8	1539.8	1539.7
160°	1555.5	1555.8	1556.0	1556.2	1556.5	1556.8	1557.1	1557.4	1557.1	1556.8	1556.5
162.5°	1570.0	1570.3	1570.6	1571.0	1571.7	1572.4	1573.1	1573.9	1573.1	1572.4	1571.7
165°	1589.4	1589.7	1590.0	1590.4	1591.3	1592.0	1592.9	1593.7	1592.9	1592.0	1591.3
167.5°	1604.4	1604.4	1604.4	1604.9	1606.0	1607.0	1608.2	1609.2	1608.2	1607.0	1606.0
170°	1613.1	1613.1	1613.1	1613.6	1614.8	1615.8	1616.8	1618.0	1616.8	1615.8	1614.8
172.5°	1618.5	1618.3	1618.1	1618.6	1619.9	1621.2	1622.5	1623.8	1622.5	1621.2	1619.9
175°	1625.9	1625.6	1625.3	1625.9	1627.2	1628.6	1629.9	1631.3	1629.9	1628.6	1627.2
177.5°	1628.9	1628.7	1628.5	1628.9	1630.0	1631.1	1632.1	1633.2	1632.1	1631.1	1630.0
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1700.9	1693.2	1687.9	1676.0	1668.3	1660.0	1651.7	1657.1	1656.4	1655.9	1655.9
5°	1643.9	1626.8	1611.3	1591.3	1578.7	1563.1	1551.2	1549.7	1552.7	1542.4	1536.4
7.5°	1587.2	1564.0	1541.9	1519.8	1496.5	1477.8	1466.0	1460.6	1453.0	1446.6	1440.0
10°	1547.6	1520.1	1498.6	1471.2	1446.0	1423.8	1409.8	1400.1	1395.0	1389.8	1380.2
12.5°	1506.7	1479.9	1452.5	1421.4	1397.5	1371.7	1361.1	1350.4	1340.4	1334.6	1321.4
15°	1446.8	1412.0	1383.1	1350.5	1323.8	1298.6	1283.8	1262.3	1259.3	1252.0	1238.6
17.5°	1386.8	1349.0	1309.2	1285.0	1254.9	1228.7	1206.2	1198.9	1177.7	1169.7	1158.2
20°	1339.4	1304.6	1274.2	1242.4	1198.6	1174.2	1156.4	1146.8	1129.7	1119.4	1111.9
22.5°	1298.4	1263.1	1227.9	1190.8	1154.8	1127.4	1114.4	1099.4	1090.1	1075.5	1067.5
25°	1240.1	1201.6	1159.3	1119.4	1093.4	1072.7	1052.0	1038.6	1025.3	1018.6	1003.8
27.5°	1172.2	1132.0	1092.5	1062.2	1030.3	1009.8	991.1	979.2	963.2	952.0	943.8
30°	1134.9	1087.5	1053.4	1026.1	985.2	966.0	952.0	937.2	925.3	913.4	905.3
32.5°	1091.7	1048.4	1016.1	982.1	950.9	929.8	911.6	898.6	888.5	877.2	869.1
35°	1023.8	987.5	954.1	920.1	897.1	875.6	854.1	843.0	833.4	823.0	815.7
37.5°	962.4	928.5	896.8	864.5	836.0	818.6	801.3	792.8	779.8	772.8	765.3
40°	924.5	891.2	857.1	826.0	796.4	783.1	767.5	754.9	743.0	737.8	729.7
42.5°	883.1	849.7	821.0	787.5	763.2	745.1	730.8	717.0	708.0	700.5	695.9
45°	821.5	791.9	763.7	730.5	707.5	691.9	675.6	663.0	654.9	649.7	641.5
47.5°	761.9	732.3	703.6	674.6	652.3	634.6	618.3	609.5	598.7	592.4	586.8
50°	718.6	691.9	661.6	634.9	612.7	594.8	581.5	570.4	560.8	552.6	548.9
52.5°	678.9	650.4	624.2	599.3	575.9	555.7	543.6	531.9	524.6	515.3	511.0
55°	613.4	586.0	563.7	539.3	516.3	499.3	484.5	474.1	466.7	456.4	450.4
57.5°	551.9	527.4	500.8	479.6	455.9	441.5	429.2	415.2	406.1	397.9	392.2
60°	510.4	482.3	459.3	439.3	418.6	400.0	388.9	377.8	368.2	360.1	354.9
62.5°	467.1	442.5	420.8	399.0	380.0	363.9	351.0	341.7	333.2	328.0	322.8
65°	400.8	381.5	359.3	341.5	323.8	311.9	301.5	293.3	287.5	283.7	279.3
67.5°	339.7	321.0	301.6	284.2	272.3	263.3	256.5	249.5	246.6	241.8	238.8
70°	300.0	280.8	263.7	250.4	238.6	231.9	227.4	222.3	219.2	213.4	210.4
72.5°	256.7	242.8	230.5	219.6	210.1	204.1	198.4	192.0	187.3	180.8	177.8
75°	202.3	189.6	180.0	172.6	166.6	158.5	150.4	143.7	141.5	139.3	138.6
77.5°	149.8	141.8	134.8	128.6	121.2	115.3	113.5	112.0	111.6	110.4	110.4
80°	117.8	110.4	105.2	97.7	93.3	93.3	93.3	91.9	92.6	92.6	92.6
82.5°	87.6	80.8	77.9	75.3	74.4	74.9	74.9	75.3	74.8	76.0	75.4
85°	45.1	45.9	47.4	46.7	47.4	47.4	48.9	48.2	48.9	47.4	48.9
87.5°	18.9	21.4	22.7	23.9	25.3	25.4	26.2	26.4	27.2	27.4	27.6
90°	12.0	15.1	18.6	22.1	25.5	29.1	30.2	31.2	32.3	33.4	34.2
92.5°	19.5	20.5	23.1	25.7	28.4	31.0	32.7	34.5	36.2	37.9	38.9
95°	29.8	25.7	28.7	31.7	34.6	37.6	39.5	41.4	43.3	45.1	46.1
97.5°	128.8	116.6	97.2	77.9	58.4	39.0	41.2	43.4	45.5	47.6	48.8
100°	226.4	208.0	166.1	124.0	82.0	40.0	42.1	44.3	46.5	48.6	49.9
102.5°	284.4	263.3	217.4	171.5	125.6	79.7	73.0	66.4	59.7	53.1	50.0
105°	373.0	362.4	338.1	313.9	289.6	265.4	217.7	170.0	122.4	74.7	51.2
107.5°	468.1	471.2	475.0	478.8	482.7	486.4	451.5	416.6	381.6	346.7	311.2
110°	532.2	534.7	537.7	540.6	543.7	546.6	537.7	528.8	519.9	511.0	487.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	593.3	595.8	598.8	601.7	604.7	607.7	607.8	608.0	608.1	608.3	604.4
115°	683.9	686.0	688.3	690.8	693.2	695.7	698.3	701.1	703.7	706.4	708.3
117.5°	774.4	776.0	777.2	778.5	779.8	781.0	783.2	785.3	787.4	789.6	790.8
120°	831.4	833.0	833.8	834.6	835.5	836.2	838.4	840.6	842.7	844.9	845.9
122.5°	885.9	887.4	888.4	889.5	890.5	891.6	893.1	894.6	896.1	897.6	898.4
125°	963.7	965.3	966.3	967.4	968.5	969.6	970.1	970.6	971.2	971.7	972.2
127.5°	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0	1046.9	1047.7	1048.7	1048.8
130°	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8	1092.9	1094.0	1095.0	1095.3
132.5°	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5	1136.5	1137.6	1138.7	1138.9
135°	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8	1202.7	1203.4	1204.3	1204.3
137.5°	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3	1261.6	1262.8	1264.1	1264.5
140°	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9	1298.9	1300.0	1301.1	1301.4
142.5°	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5	1334.4	1335.2	1336.1	1336.1
145°	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4	1383.9	1384.4	1385.0	1385.3
147.5°	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8	1428.2	1428.8	1429.4	1429.0
150°	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9	1455.4	1455.9	1456.5	1456.3
152.5°	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6	1479.5	1480.5	1481.5	1481.4
155°	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5	1512.8	1514.1	1515.5	1515.3
157.5°	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0	1541.7	1543.3	1544.9	1544.6
160°	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5	1558.1	1559.8	1561.4	1561.2
162.5°	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3	1573.1	1575.0	1576.8	1576.9
165°	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0	1593.2	1595.3	1597.5	1597.6
167.5°	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6	1608.7	1610.8	1613.0	1613.0
170°	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2	1617.4	1619.6	1621.7	1621.7
172.5°	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1	1623.2	1625.4	1627.6	1627.4
175°	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3	1630.2	1632.1	1634.0	1633.8
177.5°	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1	1632.8	1634.6	1636.3	1636.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1648.8	1648.1	1648.8	1646.3	1648.8	1648.1	1648.8	1655.9	1655.9	1656.4	1657.1
5°	1534.2	1533.5	1531.3	1524.6	1531.3	1533.5	1534.2	1536.4	1542.4	1552.7	1549.7
7.5°	1434.2	1433.1	1426.6	1426.8	1426.6	1433.1	1434.2	1440.0	1446.6	1453.0	1460.6
10°	1375.0	1375.6	1366.8	1361.6	1366.8	1375.6	1375.0	1380.2	1389.8	1395.0	1400.1
12.5°	1317.5	1314.1	1306.9	1301.2	1306.9	1314.1	1317.5	1321.4	1334.6	1340.4	1350.4
15°	1241.6	1234.2	1216.4	1217.9	1216.4	1234.2	1241.6	1238.6	1252.0	1259.3	1262.3
17.5°	1152.3	1146.8	1146.5	1136.1	1146.5	1146.8	1152.3	1158.2	1169.7	1177.7	1198.9
20°	1100.1	1096.4	1097.9	1087.5	1097.9	1096.4	1100.1	1111.9	1119.4	1129.7	1146.8
22.5°	1059.2	1055.5	1049.2	1046.0	1049.2	1055.5	1059.2	1067.5	1075.5	1090.1	1099.4
25°	999.4	993.4	987.5	991.2	987.5	993.4	999.4	1003.8	1018.6	1025.3	1038.6
27.5°	939.5	935.1	929.2	928.4	929.2	935.1	939.5	943.8	952.0	963.2	979.2
30°	901.5	897.1	894.2	890.4	894.2	897.1	901.5	905.3	913.4	925.3	937.2
32.5°	863.1	862.1	856.9	856.1	856.9	862.1	863.1	869.1	877.2	888.5	898.6
35°	812.7	808.2	806.7	807.5	806.7	808.2	812.7	815.7	823.0	833.4	843.0
37.5°	764.8	758.8	756.2	753.6	756.2	758.8	764.8	765.3	772.8	779.8	792.8
40°	730.5	724.5	723.0	721.5	723.0	724.5	730.5	729.7	737.8	743.0	754.9
42.5°	691.9	689.6	688.6	686.0	688.6	689.6	691.9	695.9	700.5	708.0	717.0
45°	639.3	638.6	634.1	635.7	634.1	638.6	639.3	641.5	649.7	654.9	663.0
47.5°	583.9	580.6	577.5	579.6	577.5	580.6	583.9	586.8	592.4	598.7	609.5
50°	546.0	544.5	537.8	539.3	537.8	544.5	546.0	548.9	552.6	560.8	570.4
52.5°	508.0	502.4	499.9	499.0	499.9	502.4	508.0	511.0	515.3	524.6	531.9
55°	445.3	438.6	435.5	434.1	435.5	438.6	445.3	450.4	456.4	466.7	474.1
57.5°	383.6	381.8	379.5	381.1	379.5	381.8	383.6	392.2	397.9	406.1	415.2
60°	347.4	347.4	347.4	346.7	347.4	347.4	347.4	354.9	360.1	368.2	377.8
62.5°	319.6	317.8	317.3	318.3	317.3	317.8	319.6	322.8	328.0	333.2	341.7
65°	277.1	276.4	273.3	272.6	273.3	276.4	277.1	279.3	283.7	287.5	293.3
67.5°	237.0	234.2	233.4	232.3	233.4	234.2	237.0	238.8	241.8	246.6	249.5
70°	206.7	205.2	200.8	201.5	200.8	205.2	206.7	210.4	213.4	219.2	222.3
72.5°	174.1	172.6	171.7	170.7	171.7	172.6	174.1	177.8	180.8	187.3	192.0
75°	137.8	137.0	136.3	139.3	136.3	137.0	137.8	138.6	139.3	141.5	143.7
77.5°	110.4	110.4	110.8	109.6	110.8	110.4	110.4	110.4	110.4	111.6	112.0
80°	92.6	92.6	91.9	91.9	91.9	92.6	92.6	92.6	92.6	92.6	91.9
82.5°	74.3	74.8	75.3	74.1	75.3	74.8	74.3	75.4	76.0	74.8	75.3
85°	48.9	48.2	49.7	48.9	49.7	48.2	48.9	48.9	47.4	48.9	48.2
87.5°	28.8	27.8	27.9	28.7	27.9	27.8	28.8	27.6	27.4	27.2	26.4
90°	34.8	35.3	35.8	36.4	35.8	35.3	34.8	34.2	33.4	32.3	31.2
92.5°	39.3	39.6	39.9	40.2	39.9	39.6	39.3	38.9	37.9	36.2	34.5
95°	46.1	46.1	46.1	46.1	46.1	46.1	46.1	46.1	45.1	43.3	41.4
97.5°	49.1	49.4	49.7	50.0	49.7	49.4	49.1	48.8	47.6	45.5	43.4
100°	50.0	50.3	50.6	50.9	50.6	50.3	50.0	49.9	48.6	46.5	44.3
102.5°	50.4	50.9	51.4	51.8	51.4	50.9	50.4	50.0	53.1	59.7	66.4
105°	51.7	52.2	52.8	53.3	52.8	52.2	51.7	51.2	74.7	122.4	170.0
107.5°	275.3	239.3	203.4	167.5	203.4	239.3	275.3	311.2	346.7	381.6	416.6
110°	448.8	410.3	371.8	333.3	371.8	410.3	448.8	487.3	511.0	519.9	528.8



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	596.2	588.1	579.9	571.8	579.9	588.1	596.2	604.4	608.3	608.1	608.0
115°	709.4	710.5	711.5	712.7	711.5	710.5	709.4	708.3	706.4	703.7	701.1
117.5°	791.0	791.2	791.5	791.6	791.5	791.2	791.0	790.8	789.6	787.4	785.3
120°	845.9	845.9	845.9	845.9	845.9	845.9	845.9	845.9	844.9	842.7	840.6
122.5°	898.6	898.8	899.1	899.3	899.1	898.8	898.6	898.4	897.6	896.1	894.6
125°	972.8	973.4	973.8	974.4	973.8	973.4	972.8	972.2	971.7	971.2	970.6
127.5°	1048.3	1047.7	1047.2	1046.6	1047.2	1047.7	1048.3	1048.8	1048.7	1047.7	1046.9
130°	1094.8	1094.3	1093.7	1093.2	1093.7	1094.3	1094.8	1095.3	1095.0	1094.0	1092.9
132.5°	1138.1	1137.4	1136.6	1135.9	1136.6	1137.4	1138.1	1138.9	1138.7	1137.6	1136.5
135°	1203.4	1202.7	1201.8	1201.1	1201.8	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7
137.5°	1263.9	1263.5	1262.9	1262.3	1262.9	1263.5	1263.9	1264.5	1264.1	1262.8	1261.6
140°	1300.8	1300.2	1299.8	1299.2	1299.8	1300.2	1300.8	1301.4	1301.1	1300.0	1298.9
142.5°	1335.4	1334.6	1333.9	1333.1	1333.9	1334.6	1335.4	1336.1	1336.1	1335.2	1334.4
145°	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.3	1385.0	1384.4	1383.9
147.5°	1427.8	1426.5	1425.3	1424.0	1425.3	1426.5	1427.8	1429.0	1429.4	1428.8	1428.2
150°	1455.6	1454.7	1454.0	1453.1	1454.0	1454.7	1455.6	1456.3	1456.5	1455.9	1455.4
152.5°	1480.1	1478.8	1477.6	1476.4	1477.6	1478.8	1480.1	1481.4	1481.5	1480.5	1479.5
155°	1513.7	1512.1	1510.5	1508.9	1510.5	1512.1	1513.7	1515.3	1515.5	1514.1	1512.8
157.5°	1542.6	1540.5	1538.3	1536.3	1538.3	1540.5	1542.6	1544.6	1544.9	1543.3	1541.7
160°	1559.3	1557.5	1555.6	1553.7	1555.6	1557.5	1559.3	1561.2	1561.4	1559.8	1558.1
162.5°	1575.2	1573.6	1571.9	1570.2	1571.9	1573.6	1575.2	1576.9	1576.8	1575.0	1573.1
165°	1595.7	1593.8	1592.0	1590.1	1592.0	1593.8	1595.7	1597.6	1597.5	1595.3	1593.2
167.5°	1610.8	1608.7	1606.6	1604.4	1606.6	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7
170°	1619.6	1617.4	1615.2	1613.1	1615.2	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4
172.5°	1625.0	1622.7	1620.3	1618.0	1620.3	1622.7	1625.0	1627.4	1627.6	1625.4	1623.2
175°	1631.7	1629.6	1627.4	1625.2	1627.4	1629.6	1631.7	1633.8	1634.0	1632.1	1630.2
177.5°	1633.9	1631.7	1629.6	1627.4	1629.6	1631.7	1633.9	1636.1	1636.3	1634.6	1632.8
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1651.7	1660.0	1668.3	1676.0	1687.9	1693.2	1700.9	1703.8	1712.8	1725.8	1736.4
5°	1551.2	1563.1	1578.7	1591.3	1611.3	1626.8	1643.9	1660.2	1679.4	1706.9	1731.3
7.5°	1466.0	1477.8	1496.5	1519.8	1541.9	1564.0	1587.2	1609.5	1637.0	1676.3	1715.2
10°	1409.8	1423.8	1446.0	1471.2	1498.6	1520.1	1547.6	1575.7	1609.8	1655.0	1701.7
12.5°	1361.1	1371.7	1397.5	1421.4	1452.5	1479.9	1506.7	1539.5	1578.4	1626.5	1682.6
15°	1283.8	1298.6	1323.8	1350.5	1383.1	1412.0	1446.8	1486.8	1524.6	1583.8	1652.0
17.5°	1206.2	1228.7	1254.9	1285.0	1309.2	1349.0	1386.8	1427.9	1474.3	1537.2	1612.0
20°	1156.4	1174.2	1198.6	1242.4	1274.2	1304.6	1339.4	1390.5	1433.4	1504.6	1582.3
22.5°	1114.4	1127.4	1154.8	1190.8	1227.9	1263.1	1298.4	1347.3	1400.2	1467.8	1552.2
25°	1052.0	1072.7	1093.4	1119.4	1159.3	1201.6	1240.1	1281.6	1337.9	1409.8	1500.9
27.5°	991.1	1009.8	1030.3	1062.2	1092.5	1132.0	1172.2	1219.8	1280.3	1356.3	1448.7
30°	952.0	966.0	985.2	1026.1	1053.4	1087.5	1134.9	1177.1	1233.4	1314.2	1412.0
32.5°	911.6	929.8	950.9	982.1	1016.1	1048.4	1091.7	1137.5	1195.0	1274.5	1374.6
35°	854.1	875.6	897.1	920.1	954.1	987.5	1023.8	1074.2	1132.7	1209.8	1308.2
37.5°	801.3	818.6	836.0	864.5	896.8	928.5	962.4	1012.1	1067.2	1150.4	1240.7
40°	767.5	783.1	796.4	826.0	857.1	891.2	924.5	968.3	1027.5	1105.3	1192.7
42.5°	730.8	745.1	763.2	787.5	821.0	849.7	883.1	924.4	980.1	1059.0	1135.8
45°	675.6	691.9	707.5	730.5	763.7	791.9	821.5	860.8	917.8	983.1	1051.2
47.5°	618.3	634.6	652.3	674.6	703.6	732.3	761.9	796.6	848.7	912.7	958.6
50°	581.5	594.8	612.7	634.9	661.6	691.9	718.6	756.4	806.0	856.4	896.4
52.5°	543.6	555.7	575.9	599.3	624.2	650.4	678.9	711.3	756.2	803.6	835.4
55°	484.5	499.3	516.3	539.3	563.7	586.0	613.4	646.8	682.3	717.8	739.3
57.5°	429.2	441.5	455.9	479.6	500.8	527.4	551.9	577.9	610.8	637.5	651.6
60°	388.9	400.0	418.6	439.3	459.3	482.3	510.4	536.3	561.6	583.1	594.1
62.5°	351.0	363.9	380.0	399.0	420.8	442.5	467.1	488.9	511.1	529.7	537.2
65°	301.5	311.9	323.8	341.5	359.3	381.5	400.8	423.0	439.3	449.7	456.4
67.5°	256.5	263.3	272.3	284.2	301.6	321.0	339.7	357.0	370.7	377.8	383.7
70°	227.4	231.9	238.6	250.4	263.7	280.8	300.0	312.6	324.5	330.4	336.3
72.5°	198.4	204.1	210.1	219.6	230.5	242.8	256.7	272.3	278.8	286.0	289.5
75°	150.4	158.5	166.6	172.6	180.0	189.6	202.3	211.9	215.6	221.5	222.3
77.5°	113.5	115.3	121.2	128.6	134.8	141.8	149.8	158.3	160.1	163.2	165.2
80°	93.3	93.3	93.3	97.7	105.2	110.4	117.8	122.2	125.2	125.9	126.7
82.5°	74.9	74.9	74.4	75.3	77.9	80.8	87.6	92.6	95.0	94.5	92.9
85°	48.9	47.4	47.4	46.7	47.4	45.9	45.1	48.2	52.6	52.6	51.1
87.5°	26.2	25.4	25.3	23.9	22.7	21.4	18.9	19.0	18.5	20.4	19.2
90°	30.2	29.1	25.5	22.1	18.6	15.1	12.0	9.3	6.6	3.9	1.2
92.5°	32.7	31.0	28.4	25.7	23.1	20.5	19.5	20.3	21.0	21.8	22.5
95°	39.5	37.6	34.6	31.7	28.7	25.7	29.8	40.8	51.8	62.9	73.9
97.5°	41.2	39.0	58.4	77.9	97.2	116.6	128.8	133.7	138.6	143.6	148.5
100°	42.1	40.0	82.0	124.0	166.1	208.0	226.4	220.9	215.6	210.2	204.8
102.5°	73.0	79.7	125.6	171.5	217.4	263.3	284.4	280.4	276.5	272.7	268.8
105°	217.7	265.4	289.6	313.9	338.1	362.4	373.0	370.0	367.1	364.1	361.2
107.5°	451.5	486.4	482.7	478.8	475.0	471.2	468.1	465.7	463.4	461.0	458.6
110°	537.7	546.6	543.7	540.6	537.7	534.7	532.2	530.0	527.8	525.8	523.6



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	607.8	607.7	604.7	601.7	598.8	595.8	593.3	591.4	589.5	587.6	585.6
115°	698.3	695.7	693.2	690.8	688.3	686.0	683.9	682.3	680.7	679.1	677.5
117.5°	783.2	781.0	779.8	778.5	777.2	776.0	774.4	772.4	770.4	768.5	766.5
120°	838.4	836.2	835.5	834.6	833.8	833.0	831.4	829.0	826.5	824.2	821.7
122.5°	893.1	891.6	890.5	889.5	888.4	887.4	885.9	883.9	881.9	880.0	878.0
125°	970.1	969.6	968.5	967.4	966.3	965.3	963.7	961.5	959.3	957.2	955.0
127.5°	1046.0	1045.2	1043.9	1042.6	1041.3	1040.0	1038.3	1036.1	1034.0	1031.8	1029.6
130°	1091.8	1090.7	1089.7	1088.6	1087.5	1086.5	1084.9	1082.7	1080.5	1078.4	1076.2
132.5°	1135.5	1134.3	1133.5	1132.7	1131.8	1131.0	1129.4	1127.3	1125.1	1122.9	1120.8
135°	1201.8	1201.1	1200.0	1198.9	1197.8	1196.7	1195.4	1193.7	1192.1	1190.5	1188.9
137.5°	1260.3	1259.0	1258.4	1257.8	1257.2	1256.6	1255.3	1253.2	1251.2	1249.2	1247.1
140°	1297.9	1296.8	1296.0	1295.1	1294.4	1293.5	1292.3	1290.7	1289.1	1287.5	1285.9
142.5°	1333.5	1332.7	1331.8	1331.1	1330.2	1329.5	1328.2	1326.6	1325.0	1323.3	1321.7
145°	1383.4	1382.8	1382.3	1381.8	1381.2	1380.6	1379.5	1377.6	1375.7	1373.9	1372.0
147.5°	1427.8	1427.2	1426.6	1426.1	1425.6	1425.0	1424.2	1422.9	1421.6	1420.4	1419.2
150°	1454.9	1454.3	1453.8	1453.2	1452.7	1452.2	1451.5	1450.7	1449.9	1449.1	1448.3
152.5°	1478.6	1477.6	1477.2	1477.0	1476.7	1476.3	1475.9	1475.6	1475.2	1474.8	1474.4
155°	1511.5	1510.0	1509.9	1509.6	1509.3	1509.0	1509.1	1509.7	1510.2	1510.8	1511.3
157.5°	1540.0	1538.4	1538.7	1539.0	1539.3	1539.5	1539.6	1539.7	1539.8	1539.8	1539.9
160°	1556.5	1554.9	1555.2	1555.5	1555.8	1556.0	1556.2	1556.5	1556.8	1557.1	1557.4
162.5°	1571.3	1569.4	1569.7	1570.0	1570.3	1570.6	1571.0	1571.7	1572.4	1573.1	1573.9
165°	1591.0	1588.8	1589.1	1589.4	1589.7	1590.0	1590.4	1591.3	1592.0	1592.9	1593.7
167.5°	1606.6	1604.4	1604.4	1604.4	1604.4	1604.4	1604.9	1606.0	1607.0	1608.2	1609.2
170°	1615.2	1613.1	1613.1	1613.1	1613.1	1613.1	1613.6	1614.8	1615.8	1616.8	1618.0
172.5°	1621.1	1618.9	1618.7	1618.5	1618.3	1618.1	1618.6	1619.9	1621.2	1622.5	1623.8
175°	1628.3	1626.5	1626.2	1625.9	1625.6	1625.3	1625.9	1627.2	1628.6	1629.9	1631.3
177.5°	1631.1	1629.4	1629.1	1628.9	1628.7	1628.5	1628.9	1630.0	1631.1	1632.1	1633.2
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1740.0	1746.5	1754.8	1767.3	1776.8	1785.1	1786.9	1789.2	1795.2	1805.2	1812.9
5°	1751.2	1768.3	1795.7	1822.4	1851.2	1875.0	1897.2	1912.8	1927.6	1958.7	1983.9
7.5°	1747.8	1785.6	1828.6	1876.5	1925.0	1971.9	2015.4	2054.4	2093.2	2138.5	2190.3
10°	1745.3	1789.8	1847.6	1909.0	1976.5	2042.4	2106.1	2155.8	2213.6	2265.4	2331.3
12.5°	1734.1	1798.1	1867.2	1945.8	2028.6	2104.6	2188.5	2257.1	2323.2	2398.1	2474.7
15°	1719.4	1797.2	1884.6	1989.0	2115.0	2206.9	2292.8	2412.1	2493.6	2575.0	2684.7
17.5°	1692.6	1787.5	1896.8	2032.5	2137.5	2261.0	2390.3	2484.5	2594.3	2709.2	2808.4
20°	1671.2	1781.7	1903.8	2037.2	2171.3	2305.4	2430.6	2543.2	2656.6	2789.2	2870.6
22.5°	1649.9	1759.2	1886.1	2027.8	2171.9	2313.1	2454.9	2587.1	2714.6	2848.5	2952.4
25°	1604.6	1734.3	1872.0	2016.5	2158.7	2314.3	2483.2	2630.6	2788.4	2926.2	3024.7
27.5°	1558.7	1677.4	1814.7	1961.2	2119.3	2303.2	2501.9	2669.5	2827.5	2926.2	2957.1
30°	1517.2	1643.1	1769.1	1918.0	2089.1	2294.2	2505.4	2697.3	2827.0	2869.9	2838.0
32.5°	1475.1	1589.2	1713.9	1866.4	2048.1	2272.4	2510.2	2680.7	2758.7	2725.9	2596.2
35°	1400.9	1503.8	1624.6	1777.2	1986.1	2260.2	2490.6	2606.1	2586.9	2401.7	2157.2
37.5°	1321.4	1405.3	1517.2	1676.8	1921.8	2212.1	2406.4	2423.5	2256.8	1972.5	1690.1
40°	1258.7	1334.2	1449.1	1615.7	1872.0	2164.6	2321.7	2252.8	1994.2	1677.9	1442.4
42.5°	1197.6	1261.3	1372.0	1551.7	1824.6	2100.1	2195.5	2045.4	1747.1	1448.0	1233.8
45°	1094.2	1154.1	1265.3	1449.7	1727.6	1976.5	1963.9	1703.1	1404.6	1163.9	986.0
47.5°	996.1	1048.6	1152.8	1341.1	1613.6	1791.3	1673.5	1396.0	1142.7	949.6	822.7
50°	926.7	978.6	1082.3	1268.3	1522.4	1652.0	1483.8	1216.4	984.6	824.5	723.8
52.5°	860.4	911.1	1005.9	1187.0	1412.1	1489.6	1309.0	1061.1	867.8	729.7	643.2
55°	767.5	806.0	891.2	1064.5	1232.8	1250.5	1067.5	860.1	700.8	604.5	545.3
57.5°	672.8	706.0	790.1	928.2	1046.1	1037.0	863.5	684.1	576.8	505.2	462.2
60°	611.1	643.8	717.8	836.4	925.3	894.2	734.9	590.4	498.6	446.0	411.9
62.5°	553.6	579.2	648.5	735.0	799.0	763.7	628.2	508.6	435.7	391.4	364.5
65°	470.4	491.2	546.7	591.9	627.5	593.4	480.8	397.8	345.3	314.1	295.6
67.5°	391.2	404.4	439.6	455.9	481.0	443.6	361.6	305.9	276.1	249.8	237.0
70°	341.5	351.1	369.7	383.0	389.6	351.1	290.4	249.7	224.4	205.9	197.8
72.5°	291.7	300.2	303.9	314.8	311.4	275.3	233.5	201.0	182.9	170.4	159.9
75°	223.0	226.7	223.0	218.6	208.9	183.7	154.9	138.6	125.2	119.2	115.6
77.5°	162.5	161.4	156.3	149.4	132.9	117.1	101.5	96.0	90.2	87.1	85.8
80°	125.2	122.2	117.8	106.7	92.6	81.5	77.8	74.1	71.8	68.1	67.4
82.5°	93.2	91.4	84.0	74.6	64.8	59.6	56.5	55.1	52.9	51.0	50.8
85°	49.7	47.4	39.3	34.1	32.6	31.1	30.3	30.3	27.4	26.7	26.7
87.5°	16.8	13.8	13.7	12.4	13.1	12.6	13.9	13.4	13.5	14.3	13.4
90°	3.9	6.6	9.3	12.0	15.1	18.6	22.1	25.5	29.1	30.2	31.2
92.5°	21.8	21.0	20.3	19.5	20.5	23.1	25.7	28.4	31.0	32.7	34.5
95°	62.9	51.8	40.8	29.8	25.7	28.7	31.7	34.6	37.6	39.5	41.4
97.5°	143.6	138.6	133.7	128.8	116.6	97.2	77.9	58.4	39.0	41.2	43.4
100°	210.2	215.6	220.9	226.4	208.0	166.1	124.0	82.0	40.0	42.1	44.3
102.5°	272.7	276.5	280.4	284.4	263.3	217.4	171.5	125.6	79.7	73.0	66.4
105°	364.1	367.1	370.0	373.0	362.4	338.1	313.9	289.6	265.4	217.7	170.0
107.5°	461.0	463.4	465.7	468.1	471.2	475.0	478.8	482.7	486.4	451.5	416.6
110°	525.8	527.8	530.0	532.2	534.7	537.7	540.6	543.7	546.6	537.7	528.8





TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	587.6	589.5	591.4	593.3	595.8	598.8	601.7	604.7	607.7	607.8	608.0
115°	679.1	680.7	682.3	683.9	686.0	688.3	690.8	693.2	695.7	698.3	701.1
117.5°	768.5	770.4	772.4	774.4	776.0	777.2	778.5	779.8	781.0	783.2	785.3
120°	824.2	826.5	829.0	831.4	833.0	833.8	834.6	835.5	836.2	838.4	840.6
122.5°	880.0	881.9	883.9	885.9	887.4	888.4	889.5	890.5	891.6	893.1	894.6
125°	957.2	959.3	961.5	963.7	965.3	966.3	967.4	968.5	969.6	970.1	970.6
127.5°	1031.8	1034.0	1036.1	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0	1046.9
130°	1078.4	1080.5	1082.7	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8	1092.9
132.5°	1122.9	1125.1	1127.3	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5	1136.5
135°	1190.5	1192.1	1193.7	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8	1202.7
137.5°	1249.2	1251.2	1253.2	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3	1261.6
140°	1287.5	1289.1	1290.7	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9	1298.9
142.5°	1323.3	1325.0	1326.6	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5	1334.4
145°	1373.9	1375.7	1377.6	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4	1383.9
147.5°	1420.4	1421.6	1422.9	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8	1428.2
150°	1449.1	1449.9	1450.7	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9	1455.4
152.5°	1474.8	1475.2	1475.6	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6	1479.5
155°	1510.8	1510.2	1509.7	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5	1512.8
157.5°	1539.8	1539.8	1539.7	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0	1541.7
160°	1557.1	1556.8	1556.5	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5	1558.1
162.5°	1573.1	1572.4	1571.7	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3	1573.1
165°	1592.9	1592.0	1591.3	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0	1593.2
167.5°	1608.2	1607.0	1606.0	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6	1608.7
170°	1616.8	1615.8	1614.8	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2	1617.4
172.5°	1622.5	1621.2	1619.9	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1	1623.2
175°	1629.9	1628.6	1627.2	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3	1630.2
177.5°	1632.1	1631.1	1630.0	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1	1632.8
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5	1730.5
2.5°	1825.3	1825.3	1827.7	1836.6	1837.8	1845.5	1843.1
5°	2006.1	2020.2	2025.3	2047.6	2061.0	2066.9	2055.0
7.5°	2227.1	2266.9	2285.7	2308.9	2329.6	2335.8	2319.6
10°	2388.4	2429.9	2464.7	2486.1	2506.1	2519.5	2536.6
12.5°	2544.2	2595.2	2628.3	2658.6	2679.2	2696.1	2698.9
15°	2713.6	2790.6	2849.1	2892.1	2913.6	2924.7	2920.3
17.5°	2884.4	2955.8	2997.5	3041.3	3071.1	3072.6	3073.4
20°	2981.0	3050.6	3098.8	3131.4	3164.8	3163.3	3170.6
22.5°	3045.6	3100.4	3137.3	3161.0	3172.4	3166.8	3168.3
25°	3075.8	3092.1	3085.5	3047.7	3038.1	3003.2	3009.2
27.5°	2920.0	2842.9	2763.3	2660.7	2579.8	2515.2	2518.5
30°	2708.4	2572.1	2416.5	2286.1	2169.1	2136.5	2066.9
32.5°	2412.6	2208.2	2026.0	1904.5	1804.0	1776.8	1716.0
35°	1911.3	1712.8	1525.3	1412.7	1368.3	1306.1	1305.3
37.5°	1485.6	1310.8	1211.6	1127.2	1082.9	1045.3	1041.6
40°	1249.7	1113.4	1038.6	977.9	934.2	906.0	899.4
42.5°	1085.0	974.8	904.7	867.0	833.4	818.9	808.0
45°	886.0	811.9	763.0	729.0	713.4	702.3	696.4
47.5°	741.1	691.4	658.2	635.5	622.8	611.1	614.3
50°	662.3	621.5	597.1	575.6	566.0	557.8	558.6
52.5°	598.9	562.3	542.5	527.0	515.0	509.3	506.4
55°	508.2	485.2	465.2	454.1	447.4	439.3	437.1
57.5°	433.5	415.8	399.4	386.8	385.2	377.4	378.4
60°	383.7	368.9	355.6	348.9	343.7	337.1	339.3
62.5°	342.8	330.4	318.3	312.7	307.6	302.7	303.7
65°	280.8	268.9	261.5	258.5	256.3	254.1	251.8
67.5°	223.8	216.5	211.9	205.5	201.0	200.2	197.9
70°	188.1	178.5	170.4	162.2	160.0	159.3	160.0
72.5°	150.8	144.8	142.5	138.6	138.1	136.2	137.5
75°	113.4	111.1	109.6	106.7	106.7	106.7	106.7
77.5°	83.6	82.2	81.3	80.8	80.0	79.0	78.8
80°	65.2	64.5	63.0	63.0	62.2	63.0	62.2
82.5°	49.2	49.0	47.6	47.6	46.8	46.4	46.8
85°	25.2	24.4	25.9	24.4	25.2	23.8	25.2
87.5°	13.6	13.8	13.4	13.5	13.0	14.2	13.2
90°	32.3	33.4	34.2	34.8	35.3	35.8	36.4
92.5°	36.2	37.9	38.9	39.3	39.6	39.9	40.2
95°	43.3	45.1	46.1	46.1	46.1	46.1	46.1
97.5°	45.5	47.6	48.8	49.1	49.4	49.7	50.0
100°	46.5	48.6	49.9	50.0	50.3	50.6	50.9
102.5°	59.7	53.1	50.0	50.4	50.9	51.4	51.8
105°	122.4	74.7	51.2	51.7	52.2	52.8	53.3
107.5°	381.6	346.7	311.2	275.3	239.3	203.4	167.5
110°	519.9	511.0	487.3	448.8	410.3	371.8	333.3



TEST NUMBER: P332482-830

CATALOG NUMBER: S123RDIW-S1165D1320U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	608.1	608.3	604.4	596.2	588.1	579.9	571.8
115°	703.7	706.4	708.3	709.4	710.5	711.5	712.7
117.5°	787.4	789.6	790.8	791.0	791.2	791.5	791.6
120°	842.7	844.9	845.9	845.9	845.9	845.9	845.9
122.5°	896.1	897.6	898.4	898.6	898.8	899.1	899.3
125°	971.2	971.7	972.2	972.8	973.4	973.8	974.4
127.5°	1047.7	1048.7	1048.8	1048.3	1047.7	1047.2	1046.6
130°	1094.0	1095.0	1095.3	1094.8	1094.3	1093.7	1093.2
132.5°	1137.6	1138.7	1138.9	1138.1	1137.4	1136.6	1135.9
135°	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1
137.5°	1262.8	1264.1	1264.5	1263.9	1263.5	1262.9	1262.3
140°	1300.0	1301.1	1301.4	1300.8	1300.2	1299.8	1299.2
142.5°	1335.2	1336.1	1336.1	1335.4	1334.6	1333.9	1333.1
145°	1384.4	1385.0	1385.3	1385.3	1385.3	1385.3	1385.3
147.5°	1428.8	1429.4	1429.0	1427.8	1426.5	1425.3	1424.0
150°	1455.9	1456.5	1456.3	1455.6	1454.7	1454.0	1453.1
152.5°	1480.5	1481.5	1481.4	1480.1	1478.8	1477.6	1476.4
155°	1514.1	1515.5	1515.3	1513.7	1512.1	1510.5	1508.9
157.5°	1543.3	1544.9	1544.6	1542.6	1540.5	1538.3	1536.3
160°	1559.8	1561.4	1561.2	1559.3	1557.5	1555.6	1553.7
162.5°	1575.0	1576.8	1576.9	1575.2	1573.6	1571.9	1570.2
165°	1595.3	1597.5	1597.6	1595.7	1593.8	1592.0	1590.1
167.5°	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4
170°	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1
172.5°	1625.4	1627.6	1627.4	1625.0	1622.7	1620.3	1618.0
175°	1632.1	1634.0	1633.8	1631.7	1629.6	1627.4	1625.2
177.5°	1634.6	1636.3	1636.1	1633.9	1631.7	1629.6	1627.4
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3

(END OF REPORT)