

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332487-935

Luminaire Tested: **S123RDIW-S1165D1535U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332487-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8520.2 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	34
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17016	17016	17016	17016
5°	20283	17088	15048	17088
10°	25326	16990	13595	16990
15°	29727	16817	12397	16817
20°	33176	16557	11379	16557
25°	32647	16284	10753	16284
30°	23467	16032	10110	16032
35°	15669	15704	9692	15704
40°	11545	15309	9261	15309
45°	9683	14618	8840	14618
50°	8544	13711	8251	13711
55°	7492	12675	7443	12675
60°	6674	11683	6818	11683
65°	5861	10618	6342	10618
70°	4601	9668	5794	9668
75°	4055	8442	5294	8442
80°	3521	7172	5201	7172
85°	2841	5768	5521	5768



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.5	1.8
10°-20°	485.7	5.7
20°-30°	763.0	9.0
30°-40°	796.1	9.3
40°-50°	681.2	8.0
50°-60°	519.2	6.1
60°-70°	332.8	3.9
70°-80°	160.1	1.9
80°-90°	47.3	0.6
90°-100°	107.7	1.3
100°-110°	322.3	3.8
110°-120°	548.1	6.4
120°-130°	721.0	8.5
130°-140°	810.4	9.5
140°-150°	796.6	9.3
150°-160°	670.6	7.9
160°-170°	446.4	5.2
170°-180°	156.3	1.8
0°-30°	1404.1	16.5
0°-40°	2200.2	25.8
0°-60°	3400.7	39.9
0°-90°	3940.9	46.3
90°-120°	978.1	11.5
90°-150°	3306.0	38.8
90°-180°	4579.0	53.7
0°-180°	8520.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1877	1582	1393	1582	1877	194
15°	2668	1509	1112	1509	2668	756
25°	2749	1371	905	1371	2749	1181
35°	1192	1195	738	1195	1192	782
45°	636	960	581	960	636	500
55°	399	675	397	675	399	361
65°	230	417	249	417	230	226
75°	98	203	127	203	98	105
85°	23	47	45	47	23	27
90°	39	1	39	1	39	20
95°	101	77	101	77	101	104
105°	309	292	309	292	309	328
115°	553	552	553	552	553	548
125°	798	808	798	808	798	714
135°	1046	1048	1046	1048	1046	805
145°	1271	1271	1271	1271	1271	793
155°	1453	1455	1453	1455	1453	669
165°	1580	1585	1580	1585	1580	446
175°	1642	1649	1642	1649	1642	156
180°	1653	1653	1653	1653	1653	



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1683.7	1685.8	1678.8	1677.7	1669.6	1667.4	1667.4	1656.0	1649.0	1639.9	1634.4
5°	1877.2	1888.1	1882.7	1870.4	1850.1	1845.4	1832.6	1812.2	1789.2	1760.8	1747.3
7.5°	2118.9	2133.7	2128.0	2109.2	2087.9	2070.8	2034.5	2000.8	1953.5	1912.1	1876.6
10°	2317.1	2301.5	2289.3	2271.1	2251.4	2219.7	2181.8	2129.6	2069.4	2022.1	1969.3
12.5°	2465.4	2462.9	2447.4	2428.6	2400.9	2370.7	2324.1	2260.6	2190.6	2122.2	2061.8
15°	2667.6	2671.7	2661.5	2641.9	2602.6	2549.2	2478.8	2452.5	2352.3	2277.9	2203.4
17.5°	2807.5	2806.8	2805.4	2778.2	2738.2	2700.1	2634.8	2565.4	2474.8	2369.9	2269.6
20°	2896.3	2889.6	2891.0	2860.5	2830.7	2786.7	2723.1	2622.3	2547.9	2426.7	2323.2
22.5°	2894.2	2892.9	2898.0	2887.5	2865.9	2832.2	2782.1	2697.0	2602.0	2479.8	2363.3
25°	2748.8	2743.4	2775.3	2784.0	2818.6	2824.6	2809.7	2763.0	2673.1	2547.2	2403.1
27.5°	2300.6	2297.6	2356.6	2430.5	2524.2	2596.9	2667.4	2701.3	2673.1	2582.9	2438.5
30°	1888.1	1951.6	1981.4	2088.4	2207.4	2349.6	2474.1	2592.5	2621.6	2582.4	2463.9
32.5°	1567.5	1623.1	1648.0	1739.7	1850.7	2017.2	2203.9	2371.6	2490.1	2520.1	2448.8
35°	1192.4	1193.1	1249.9	1290.5	1393.4	1564.6	1745.9	1970.6	2193.9	2363.1	2380.7
37.5°	951.5	954.8	989.2	1029.7	1106.8	1197.4	1357.1	1543.9	1801.8	2061.6	2213.8
40°	821.6	827.6	853.3	893.3	948.7	1017.1	1141.6	1317.6	1532.8	1821.7	2057.9
42.5°	738.1	748.0	761.3	792.0	826.4	890.4	991.1	1127.0	1322.8	1595.9	1868.5
45°	636.1	641.5	651.7	665.9	697.0	741.7	809.3	900.7	1063.2	1283.1	1555.7
47.5°	561.1	558.3	568.9	580.5	601.2	631.6	677.0	751.6	867.5	1043.9	1275.2
50°	510.2	509.5	517.0	525.8	545.4	567.7	605.0	661.2	753.2	899.4	1111.2
52.5°	462.6	465.2	470.5	481.4	495.6	513.7	547.1	587.5	666.6	792.7	969.3
55°	399.2	401.3	408.7	414.8	425.0	443.2	464.3	498.1	552.2	640.2	785.7
57.5°	345.7	344.7	351.9	353.4	364.9	379.8	396.0	422.2	461.5	526.9	624.9
60°	310.0	307.9	314.0	318.7	324.9	337.0	350.5	376.3	407.4	455.5	539.3
62.5°	277.4	276.5	280.9	285.7	290.8	301.8	313.1	332.9	357.6	398.0	464.6
65°	230.1	232.1	234.1	236.2	238.8	245.6	256.5	270.0	287.0	315.4	363.4
67.5°	180.8	182.9	183.6	187.7	193.6	197.8	204.4	216.5	228.2	252.2	279.5
70°	146.2	145.5	146.2	148.2	155.7	163.1	171.9	180.7	188.1	205.0	228.1
72.5°	125.6	124.4	126.1	126.6	130.2	132.2	137.8	146.0	155.7	167.1	183.7
75°	97.5	97.5	97.5	97.5	100.1	101.5	103.6	105.6	108.9	114.3	126.6
77.5°	72.0	72.2	73.1	73.8	74.3	75.1	76.4	78.4	79.6	82.4	87.7
80°	56.8	57.5	56.8	57.5	57.5	58.9	59.6	61.6	62.3	65.6	67.7
82.5°	42.8	42.4	42.8	43.5	43.5	44.8	44.9	46.4	46.6	48.3	50.4
85°	23.0	21.7	23.0	22.3	23.7	22.3	23.0	24.4	24.4	25.1	27.7
87.5°	13.2	14.2	13.0	13.4	13.3	13.7	13.4	13.2	14.0	13.3	13.1
90°	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5	32.3	31.2	27.4
92.5°	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7	50.8	49.9	47.7
95°	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4	97.2	96.1	93.8
97.5°	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0	151.7	150.3	148.7
100°	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6	191.7	190.9	189.4
102.5°	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3	237.5	236.5	234.6
105°	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4	306.4	306.4	303.8
107.5°	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2	379.3	378.3	377.3
110°	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5	428.3	427.1	426.5



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7	477.3	476.0	475.9
115°	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7	553.4	553.1	553.7
117.5°	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3	629.4	629.5	630.2
120°	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8	680.0	680.4	681.7
122.5°	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7	731.5	732.3	733.1
125°	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6	807.7	808.9	809.4
127.5°	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5	883.0	884.7	885.4
130°	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2	932.4	933.5	934.4
132.5°	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6	980.9	982.3	982.9
135°	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0	1053.1	1054.3	1054.6
137.5°	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7	1123.9	1125.2	1124.4
140°	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5
142.5°	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9	1213.1	1213.4	1212.9
145°	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9	1277.3	1277.6	1276.7
147.5°	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9	1374.9	1374.9	1374.3
152.5°	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1	1408.7	1408.2	1407.8
155°	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1	1457.9	1456.7	1456.5
157.5°	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0	1500.8	1499.6	1499.3
160°	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4	1527.0	1525.5	1525.5
162.5°	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3	1552.0	1550.5	1550.2
165°	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8	1583.1	1581.4	1581.4
167.5°	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8	1606.6
170°	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3	1620.3
172.5°	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3	1633.6	1631.8	1631.8
175°	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2	1645.5	1643.7	1643.7
177.5°	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4	1651.1	1649.7	1649.7
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1632.3	1630.6	1623.1	1614.4	1603.0	1595.4	1589.5	1586.2	1576.5	1564.6	1556.4
5°	1733.1	1712.8	1691.1	1664.7	1640.4	1615.3	1599.7	1581.5	1559.2	1534.1	1516.6
7.5°	1841.1	1801.3	1758.4	1714.2	1670.4	1631.2	1596.6	1566.8	1531.3	1495.4	1470.2
10°	1923.9	1865.7	1805.5	1743.9	1687.7	1635.0	1594.3	1554.4	1511.8	1470.5	1439.4
12.5°	1999.2	1922.5	1853.1	1777.4	1705.6	1642.5	1584.1	1537.1	1485.8	1441.8	1406.4
15°	2094.5	2015.9	1932.0	1817.0	1721.6	1641.8	1570.6	1509.1	1446.8	1392.7	1358.1
17.5°	2183.5	2065.4	1952.6	1856.7	1732.7	1632.9	1546.2	1472.6	1404.2	1346.8	1304.3
20°	2220.3	2105.9	1983.5	1861.0	1739.1	1627.5	1526.6	1445.4	1374.4	1309.4	1270.2
22.5°	2242.5	2113.0	1984.0	1852.4	1722.9	1607.0	1507.2	1417.9	1340.8	1279.1	1230.7
25°	2268.4	2114.1	1971.9	1842.0	1710.0	1584.2	1465.8	1371.1	1287.8	1222.2	1170.7
27.5°	2285.4	2103.9	1936.0	1791.6	1657.7	1532.3	1423.8	1323.4	1239.0	1169.5	1114.3
30°	2288.6	2095.8	1908.3	1752.0	1616.0	1501.0	1386.0	1289.9	1200.5	1126.7	1075.3
32.5°	2293.0	2075.8	1871.0	1705.0	1565.6	1451.7	1347.5	1255.7	1164.2	1091.6	1039.1
35°	2275.1	2064.7	1814.3	1623.4	1484.0	1373.7	1279.7	1195.1	1105.1	1034.7	981.3
37.5°	2198.2	2020.7	1755.6	1531.7	1386.0	1283.8	1207.1	1133.3	1050.9	974.9	924.5
40°	2120.8	1977.4	1710.0	1475.9	1323.7	1218.7	1149.8	1089.5	1009.7	938.6	884.5
42.5°	2005.5	1918.4	1666.7	1417.5	1253.3	1152.2	1094.0	1037.5	967.4	895.3	844.4
45°	1794.0	1805.5	1578.1	1324.3	1155.8	1054.3	999.5	960.3	898.0	838.4	786.4
47.5°	1528.7	1636.3	1474.0	1225.1	1053.1	957.9	909.9	875.6	833.7	775.2	727.7
50°	1355.5	1509.1	1390.7	1158.6	988.7	894.0	846.5	818.8	782.3	736.2	691.0
52.5°	1195.8	1360.7	1290.0	1084.3	918.9	832.2	785.9	763.1	734.1	690.8	649.8
55°	975.2	1142.3	1126.1	972.4	814.1	736.2	701.1	675.4	655.7	623.3	590.8
57.5°	788.8	947.3	955.6	847.9	721.8	644.9	614.6	595.2	582.4	557.9	527.9
60°	671.3	816.8	845.2	764.1	655.7	588.1	558.3	542.7	532.6	513.0	489.9
62.5°	573.9	697.7	729.9	671.4	592.4	529.1	505.8	490.8	483.9	466.9	446.6
65°	439.2	542.1	573.2	540.7	499.4	448.7	429.7	416.9	410.8	401.3	386.4
67.5°	330.3	405.2	439.4	416.5	401.6	369.5	357.4	350.5	345.1	338.6	326.1
70°	265.3	320.7	355.9	349.8	337.7	320.7	311.9	307.2	301.8	296.4	285.6
72.5°	213.3	251.5	284.5	287.6	277.6	274.2	266.5	264.5	261.2	254.7	248.7
75°	141.5	167.8	190.8	199.7	203.7	207.1	203.7	203.0	202.3	196.9	193.6
77.5°	92.7	106.9	121.4	136.5	142.8	147.4	148.4	150.9	149.1	146.3	144.6
80°	71.0	74.5	84.6	97.5	107.6	111.7	114.3	115.7	115.0	114.3	111.7
82.5°	51.6	54.4	59.2	68.2	76.7	83.5	85.2	84.9	86.4	86.8	84.6
85°	27.7	28.4	29.8	31.2	35.9	43.3	45.4	46.7	48.0	48.0	44.0
87.5°	13.4	12.1	12.4	11.8	12.8	12.7	15.4	17.6	18.7	17.1	17.7
90°	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3	4.2	7.1	10.0
92.5°	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4	33.4	35.3	37.3
95°	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6	78.6	80.7	82.7
97.5°	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0	137.6	139.1	140.6
100°	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6	178.3	180.0	181.8
102.5°	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3	224.4	225.4	226.4
105°	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1	292.7	293.3	293.9
107.5°	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1	372.5	372.8	373.2
110°	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0	422.6	423.1	423.7





TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9	474.2	474.6	474.9
115°	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8	552.7	553.5	554.4
117.5°	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3	630.8	631.4	632.0
120°	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1	680.8	682.5	684.2
122.5°	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0	731.2	732.5	733.7
125°	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5	808.4	809.3	810.2
127.5°	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3	881.1	883.0	884.8
130°	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0	929.4	931.6	933.9
132.5°	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8	977.1	979.4	981.7
135°	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8	1049.5	1051.2	1052.9
137.5°	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3	1116.7	1118.2	1119.6
140°	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0	1163.5	1164.9	1166.3
142.5°	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6	1206.0	1207.5	1208.9
145°	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1	1271.7	1272.2	1272.8
147.5°	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2	1330.2	1331.3	1332.4
150°	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8	1370.4	1370.9	1371.5
152.5°	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0	1403.8	1404.6	1405.4
155°	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1	1499.8	1499.4	1499.1
160°	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2	1527.6	1527.0	1526.4
162.5°	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1	1552.3	1551.4	1550.7
165°	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3	1584.4	1583.6	1582.7
167.5°	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0	1609.8	1608.7	1607.5
170°	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5	1624.4	1623.2	1622.0
172.5°	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9	1635.8	1634.6	1633.5
175°	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9	1647.8	1646.6	1645.5
177.5°	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8	1652.9	1652.0	1651.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1553.8	1546.7	1541.9	1531.0	1524.0	1516.4	1508.8	1513.7	1513.1	1512.6	1512.6
5°	1501.7	1486.1	1471.9	1453.6	1442.1	1427.9	1417.0	1415.7	1418.4	1408.9	1403.5
7.5°	1449.9	1428.7	1408.5	1388.4	1367.0	1350.0	1339.2	1334.2	1327.3	1321.5	1315.4
10°	1413.7	1388.6	1369.0	1343.9	1320.9	1300.6	1287.8	1279.0	1274.3	1269.5	1260.8
12.5°	1376.3	1351.9	1326.8	1298.5	1276.6	1253.0	1243.4	1233.6	1224.4	1219.2	1207.1
15°	1321.6	1289.9	1263.4	1233.6	1209.3	1186.3	1172.8	1153.1	1150.4	1143.7	1131.4
17.5°	1266.8	1232.3	1195.9	1173.8	1146.3	1122.4	1101.8	1095.2	1075.8	1068.5	1058.0
20°	1223.5	1191.7	1164.0	1134.9	1094.9	1072.6	1056.4	1047.6	1032.0	1022.5	1015.7
22.5°	1186.1	1153.8	1121.7	1087.8	1054.9	1029.8	1018.0	1004.3	995.7	982.5	975.2
25°	1132.8	1097.6	1059.0	1022.5	998.8	979.9	961.0	948.7	936.6	930.5	917.0
27.5°	1070.8	1034.1	998.0	970.3	941.2	922.5	905.3	894.5	879.9	869.6	862.1
30°	1036.7	993.4	962.3	937.3	900.0	882.4	869.6	856.1	845.2	834.4	827.0
32.5°	997.2	957.7	928.2	897.2	868.7	849.4	832.8	820.9	811.7	801.3	793.9
35°	935.2	902.1	871.6	840.5	819.5	799.9	780.2	770.1	761.3	751.8	745.1
37.5°	879.2	848.2	819.2	789.7	763.7	747.8	731.9	724.2	712.3	705.9	699.0
40°	844.6	814.1	783.0	754.6	727.5	715.3	701.1	689.6	678.7	674.0	666.6
42.5°	806.7	776.2	749.9	719.4	697.2	680.6	667.5	655.0	646.8	639.9	635.7
45°	750.4	723.4	697.7	667.3	646.3	632.1	617.2	605.6	598.2	593.5	586.0
47.5°	695.9	668.9	642.7	616.2	595.9	579.7	564.8	556.8	546.9	541.1	536.1
50°	656.4	632.1	604.3	580.0	559.6	543.4	531.2	521.1	512.3	504.8	501.4
52.5°	620.2	594.2	570.2	547.4	526.1	507.6	496.5	485.9	479.2	470.7	466.8
55°	560.3	535.3	515.0	492.7	471.7	456.1	442.6	433.1	426.4	416.9	411.5
57.5°	504.1	481.7	457.4	438.1	416.5	403.3	392.1	379.3	371.0	363.5	358.3
60°	466.2	440.6	419.6	401.3	382.4	365.4	355.2	345.1	336.3	328.9	324.2
62.5°	426.7	404.2	384.4	364.5	347.2	332.4	320.6	312.1	304.4	299.6	294.9
65°	366.1	348.5	328.2	311.9	295.8	284.9	275.4	267.9	262.6	259.2	255.1
67.5°	310.3	293.3	275.5	259.6	248.7	240.5	234.3	227.9	225.2	220.8	218.2
70°	274.1	256.5	240.9	228.8	217.9	211.8	207.8	203.0	200.3	194.9	192.2
72.5°	234.5	221.8	210.6	200.6	191.9	186.4	181.2	175.4	171.1	165.1	162.4
75°	184.8	173.2	164.5	157.6	152.2	144.8	137.4	131.3	129.2	127.3	126.6
77.5°	136.8	129.5	123.1	117.4	110.7	105.3	103.7	102.3	101.9	100.8	100.8
80°	107.6	100.8	96.1	89.3	85.2	85.2	85.2	83.9	84.6	84.6	84.6
82.5°	80.0	73.8	71.2	68.8	67.9	68.4	68.4	68.8	68.4	69.4	68.9
85°	41.2	41.9	43.3	42.6	43.3	43.3	44.7	44.0	44.7	43.3	44.7
87.5°	17.7	20.0	21.3	22.6	23.8	24.1	24.9	25.1	25.8	26.1	26.3
90°	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5	34.6	35.8	36.7
92.5°	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7	52.6	53.6	53.8
95°	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4	99.5	100.7	101.3
97.5°	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0	154.3	155.7	156.3
100°	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6	193.5	194.3	195.0
102.5°	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3	239.2	240.0	240.4
105°	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4	306.4	306.4	306.7
107.5°	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2	381.1	382.0	382.3
110°	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5	430.6	431.8	432.0



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7	480.1	481.5	482.2
115°	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7	554.0	554.2	554.2
117.5°	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3	629.3	629.2	628.8
120°	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8	679.5	679.2	678.7
122.5°	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7	730.0	729.3	728.5
125°	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6	805.4	804.3	803.1
127.5°	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5	879.9	878.2	876.8
130°	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2	930.1	928.9	927.3
132.5°	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6	978.2	976.8	975.3
135°	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0	1050.8	1049.6	1048.8
137.5°	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7	1121.5	1120.3	1119.1
140°	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.5
142.5°	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9	1212.5	1212.3	1211.3
145°	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9	1276.7	1276.4	1275.7
147.5°	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6	1337.6	1337.6	1336.7
150°	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9	1374.9	1374.9	1374.1
152.5°	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1	1409.5	1410.1	1409.5
155°	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1	1460.2	1461.4	1460.9
157.5°	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0	1503.2	1504.4	1504.3
160°	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4	1529.9	1531.3	1531.5
162.5°	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3	1554.8	1556.3	1556.1
165°	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8	1586.6	1588.3	1588.2
167.5°	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9
170°	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4
172.5°	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3	1637.1	1638.9	1638.8
175°	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2	1648.9	1650.6	1650.5
177.5°	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4	1653.8	1655.2	1655.1
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1506.1	1505.5	1506.1	1503.9	1506.1	1505.5	1506.1	1512.6	1512.6	1513.1	1513.7
5°	1401.4	1400.8	1398.8	1392.7	1398.8	1400.8	1401.4	1403.5	1408.9	1418.4	1415.7
7.5°	1310.1	1309.2	1303.2	1303.4	1303.2	1309.2	1310.1	1315.4	1321.5	1327.3	1334.2
10°	1256.0	1256.6	1248.5	1243.8	1248.5	1256.6	1256.0	1260.8	1269.5	1274.3	1279.0
12.5°	1203.5	1200.4	1193.9	1188.6	1193.9	1200.4	1203.5	1207.1	1219.2	1224.4	1233.6
15°	1134.2	1127.4	1111.2	1112.5	1111.2	1127.4	1134.2	1131.4	1143.7	1150.4	1153.1
17.5°	1052.6	1047.6	1047.3	1037.8	1047.3	1047.6	1052.6	1058.0	1068.5	1075.8	1095.2
20°	1005.0	1001.5	1002.9	993.4	1002.9	1001.5	1005.0	1015.7	1022.5	1032.0	1047.6
22.5°	967.6	964.1	958.5	955.5	958.5	964.1	967.6	975.2	982.5	995.7	1004.3
25°	912.9	907.5	902.1	905.4	902.1	907.5	912.9	917.0	930.5	936.6	948.7
27.5°	858.2	854.2	848.8	848.1	848.8	854.2	858.2	862.1	869.6	879.9	894.5
30°	823.5	819.5	816.8	813.4	816.8	819.5	823.5	827.0	834.4	845.2	856.1
32.5°	788.4	787.6	782.7	782.0	782.7	787.6	788.4	793.9	801.3	811.7	820.9
35°	742.4	738.3	736.9	737.6	736.9	738.3	742.4	745.1	751.8	761.3	770.1
37.5°	698.6	693.2	690.8	688.4	690.8	693.2	698.6	699.0	705.9	712.3	724.2
40°	667.3	661.9	660.5	659.1	660.5	661.9	667.3	666.6	674.0	678.7	689.6
42.5°	632.1	629.9	629.0	626.6	629.0	629.9	632.1	635.7	639.9	646.8	655.0
45°	584.0	583.3	579.3	580.7	579.3	583.3	584.0	586.0	593.5	598.2	605.6
47.5°	533.4	530.4	527.5	529.4	527.5	530.4	533.4	536.1	541.1	546.9	556.8
50°	498.8	497.4	491.3	492.7	491.3	497.4	498.8	501.4	504.8	512.3	521.1
52.5°	464.1	458.9	456.7	455.8	456.7	458.9	464.1	466.8	470.7	479.2	485.9
55°	406.7	400.6	397.9	396.6	397.9	400.6	406.7	411.5	416.9	426.4	433.1
57.5°	350.4	348.8	346.6	348.1	346.6	348.8	350.4	358.3	363.5	371.0	379.3
60°	317.4	317.4	317.4	316.7	317.4	317.4	317.4	324.2	328.9	336.3	345.1
62.5°	292.0	290.3	289.8	290.8	289.8	290.3	292.0	294.9	299.6	304.4	312.1
65°	253.1	252.4	249.7	249.0	249.7	252.4	253.1	255.1	259.2	262.6	267.9
67.5°	216.5	214.0	213.2	212.2	213.2	214.0	216.5	218.2	220.8	225.2	227.9
70°	188.8	187.4	183.4	184.1	183.4	187.4	188.8	192.2	194.9	200.3	203.0
72.5°	159.0	157.6	156.9	155.9	156.9	157.6	159.0	162.4	165.1	171.1	175.4
75°	125.9	125.2	124.5	127.3	124.5	125.2	125.9	126.6	127.3	129.2	131.3
77.5°	100.8	100.8	101.3	100.1	101.3	100.8	100.8	100.8	100.8	101.9	102.3
80°	84.6	84.6	83.9	83.9	83.9	84.6	84.6	84.6	84.6	84.6	83.9
82.5°	67.8	68.4	68.8	67.7	68.8	68.4	67.8	68.9	69.4	68.4	68.8
85°	44.7	44.0	45.4	44.7	45.4	44.0	44.7	44.7	43.3	44.7	44.0
87.5°	27.5	26.5	26.6	27.3	26.6	26.5	27.5	26.3	26.1	25.8	25.1
90°	37.2	37.8	38.4	38.9	38.4	37.8	37.2	36.7	35.8	34.6	33.5
92.5°	53.5	53.1	52.8	52.4	52.8	53.1	53.5	53.8	53.6	52.6	51.7
95°	101.3	101.3	101.3	101.3	101.3	101.3	101.3	101.3	100.7	99.5	98.4
97.5°	156.2	156.0	155.9	155.8	155.9	156.0	156.2	156.3	155.7	154.3	153.0
100°	195.6	196.2	196.7	197.3	196.7	196.2	195.6	195.0	194.3	193.5	192.6
102.5°	240.3	240.1	240.0	240.0	240.0	240.1	240.3	240.4	240.0	239.2	238.3
105°	307.3	307.9	308.4	309.0	308.4	307.9	307.3	306.7	306.4	306.4	306.4
107.5°	381.9	381.6	381.3	380.9	381.3	381.6	381.9	382.3	382.0	381.1	380.2
110°	431.4	430.9	430.3	429.7	430.3	430.9	431.4	432.0	431.8	430.6	429.5



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	482.1	481.9	481.8	481.6	481.8	481.9	482.1	482.2	481.5	480.1	478.7
115°	554.0	553.7	553.4	553.1	553.4	553.7	554.0	554.2	554.2	554.0	553.7
117.5°	627.9	627.2	626.4	625.5	626.4	627.2	627.9	628.8	629.2	629.3	629.3
120°	678.2	677.6	677.0	676.4	677.0	677.6	678.2	678.7	679.2	679.5	679.8
122.5°	727.7	726.9	726.1	725.2	726.1	726.9	727.7	728.5	729.3	730.0	730.7
125°	801.9	800.8	799.6	798.5	799.6	800.8	801.9	803.1	804.3	805.4	806.6
127.5°	875.5	874.1	872.8	871.4	872.8	874.1	875.5	876.8	878.2	879.9	881.5
130°	925.3	923.3	921.3	919.2	921.3	923.3	925.3	927.3	928.9	930.1	931.2
132.5°	973.8	972.2	970.6	969.1	970.6	972.2	973.8	975.3	976.8	978.2	979.6
135°	1048.2	1047.6	1047.1	1046.5	1047.1	1047.6	1048.2	1048.8	1049.6	1050.8	1052.0
137.5°	1118.0	1117.0	1115.9	1114.7	1115.9	1117.0	1118.0	1119.1	1120.3	1121.5	1122.7
140°	1165.4	1163.5	1161.4	1159.4	1161.4	1163.5	1165.4	1167.5	1168.6	1169.0	1169.2
142.5°	1209.8	1208.2	1206.7	1205.1	1206.7	1208.2	1209.8	1211.3	1212.3	1212.5	1212.9
145°	1274.5	1273.4	1272.2	1271.1	1272.2	1273.4	1274.5	1275.7	1276.4	1276.7	1276.9
147.5°	1335.0	1333.3	1331.5	1329.7	1331.5	1333.3	1335.0	1336.7	1337.6	1337.6	1337.6
150°	1372.3	1370.6	1368.9	1367.2	1368.9	1370.6	1372.3	1374.1	1374.9	1374.9	1374.9
152.5°	1408.0	1406.5	1405.0	1403.5	1405.0	1406.5	1408.0	1409.5	1410.1	1409.5	1409.1
155°	1458.9	1456.9	1454.8	1452.9	1454.8	1456.9	1458.9	1460.9	1461.4	1460.2	1459.1
157.5°	1502.6	1501.0	1499.3	1497.8	1499.3	1501.0	1502.6	1504.3	1504.4	1503.2	1502.0
160°	1530.3	1529.1	1528.0	1526.8	1528.0	1529.1	1530.3	1531.5	1531.3	1529.9	1528.4
162.5°	1554.2	1552.4	1550.5	1548.7	1550.5	1552.4	1554.2	1556.1	1556.3	1554.8	1553.3
165°	1586.1	1584.2	1582.1	1580.1	1582.1	1584.2	1586.1	1588.2	1588.3	1586.6	1584.8
167.5°	1612.2	1610.4	1608.6	1606.8	1608.6	1610.4	1612.2	1613.9	1613.9	1612.2	1610.4
170°	1626.4	1624.4	1622.4	1620.3	1622.4	1624.4	1626.4	1628.4	1628.4	1626.4	1624.4
172.5°	1636.8	1634.8	1632.7	1630.7	1632.7	1634.8	1636.8	1638.8	1638.9	1637.1	1635.3
175°	1648.5	1646.4	1644.4	1642.4	1644.4	1646.4	1648.5	1650.5	1650.6	1648.9	1647.2
177.5°	1653.5	1651.8	1650.3	1648.6	1650.3	1651.8	1653.5	1655.1	1655.2	1653.8	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1508.8	1516.4	1524.0	1531.0	1541.9	1546.7	1553.8	1556.4	1564.6	1576.5	1586.2
5°	1417.0	1427.9	1442.1	1453.6	1471.9	1486.1	1501.7	1516.6	1534.1	1559.2	1581.5
7.5°	1339.2	1350.0	1367.0	1388.4	1408.5	1428.7	1449.9	1470.2	1495.4	1531.3	1566.8
10°	1287.8	1300.6	1320.9	1343.9	1369.0	1388.6	1413.7	1439.4	1470.5	1511.8	1554.4
12.5°	1243.4	1253.0	1276.6	1298.5	1326.8	1351.9	1376.3	1406.4	1441.8	1485.8	1537.1
15°	1172.8	1186.3	1209.3	1233.6	1263.4	1289.9	1321.6	1358.1	1392.7	1446.8	1509.1
17.5°	1101.8	1122.4	1146.3	1173.8	1195.9	1232.3	1266.8	1304.3	1346.8	1404.2	1472.6
20°	1056.4	1072.6	1094.9	1134.9	1164.0	1191.7	1223.5	1270.2	1309.4	1374.4	1445.4
22.5°	1018.0	1029.8	1054.9	1087.8	1121.7	1153.8	1186.1	1230.7	1279.1	1340.8	1417.9
25°	961.0	979.9	998.8	1022.5	1059.0	1097.6	1132.8	1170.7	1222.2	1287.8	1371.1
27.5°	905.3	922.5	941.2	970.3	998.0	1034.1	1070.8	1114.3	1169.5	1239.0	1323.4
30°	869.6	882.4	900.0	937.3	962.3	993.4	1036.7	1075.3	1126.7	1200.5	1289.9
32.5°	832.8	849.4	868.7	897.2	928.2	957.7	997.2	1039.1	1091.6	1164.2	1255.7
35°	780.2	799.9	819.5	840.5	871.6	902.1	935.2	981.3	1034.7	1105.1	1195.1
37.5°	731.9	747.8	763.7	789.7	819.2	848.2	879.2	924.5	974.9	1050.9	1133.3
40°	701.1	715.3	727.5	754.6	783.0	814.1	844.6	884.5	938.6	1009.7	1089.5
42.5°	667.5	680.6	697.2	719.4	749.9	776.2	806.7	844.4	895.3	967.4	1037.5
45°	617.2	632.1	646.3	667.3	697.7	723.4	750.4	786.4	838.4	898.0	960.3
47.5°	564.8	579.7	595.9	616.2	642.7	668.9	695.9	727.7	775.2	833.7	875.6
50°	531.2	543.4	559.6	580.0	604.3	632.1	656.4	691.0	736.2	782.3	818.8
52.5°	496.5	507.6	526.1	547.4	570.2	594.2	620.2	649.8	690.8	734.1	763.1
55°	442.6	456.1	471.7	492.7	515.0	535.3	560.3	590.8	623.3	655.7	675.4
57.5°	392.1	403.3	416.5	438.1	457.4	481.7	504.1	527.9	557.9	582.4	595.2
60°	355.2	365.4	382.4	401.3	419.6	440.6	466.2	489.9	513.0	532.6	542.7
62.5°	320.6	332.4	347.2	364.5	384.4	404.2	426.7	446.6	466.9	483.9	490.8
65°	275.4	284.9	295.8	311.9	328.2	348.5	366.1	386.4	401.3	410.8	416.9
67.5°	234.3	240.5	248.7	259.6	275.5	293.3	310.3	326.1	338.6	345.1	350.5
70°	207.8	211.8	217.9	228.8	240.9	256.5	274.1	285.6	296.4	301.8	307.2
72.5°	181.2	186.4	191.9	200.6	210.6	221.8	234.5	248.7	254.7	261.2	264.5
75°	137.4	144.8	152.2	157.6	164.5	173.2	184.8	193.6	196.9	202.3	203.0
77.5°	103.7	105.3	110.7	117.4	123.1	129.5	136.8	144.6	146.3	149.1	150.9
80°	85.2	85.2	85.2	89.3	96.1	100.8	107.6	111.7	114.3	115.0	115.7
82.5°	68.4	68.4	67.9	68.8	71.2	73.8	80.0	84.6	86.8	86.4	84.9
85°	44.7	43.3	43.3	42.6	43.3	41.9	41.2	44.0	48.0	48.0	46.7
87.5°	24.9	24.1	23.8	22.6	21.3	20.0	17.7	17.7	17.1	18.7	17.6
90°	32.3	31.2	27.4	23.7	19.9	16.2	12.8	10.0	7.1	4.2	1.3
92.5°	50.8	49.9	47.7	45.5	43.5	41.3	39.3	37.3	35.3	33.4	31.4
95°	97.2	96.1	93.8	91.4	89.1	86.9	84.7	82.7	80.7	78.6	76.6
97.5°	151.7	150.3	148.7	147.0	145.3	143.6	142.1	140.6	139.1	137.6	136.0
100°	191.7	190.9	189.4	188.0	186.5	185.1	183.5	181.8	180.0	178.3	176.6
102.5°	237.5	236.5	234.6	232.7	230.8	228.9	227.5	226.4	225.4	224.4	223.3
105°	306.4	306.4	303.8	301.2	298.6	296.0	294.5	293.9	293.3	292.7	292.1
107.5°	379.3	378.3	377.3	376.3	375.2	374.2	373.5	373.2	372.8	372.5	372.1
110°	428.3	427.1	426.5	426.0	425.4	424.8	424.3	423.7	423.1	422.6	422.0



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	477.3	476.0	475.9	475.7	475.6	475.5	475.3	474.9	474.6	474.2	473.9
115°	553.4	553.1	553.7	554.2	554.8	555.4	555.3	554.4	553.5	552.7	551.8
117.5°	629.4	629.5	630.2	630.9	631.7	632.4	632.5	632.0	631.4	630.8	630.3
120°	680.0	680.4	681.7	683.2	684.7	686.1	686.0	684.2	682.5	680.8	679.1
122.5°	731.5	732.3	733.1	733.7	734.5	735.3	735.0	733.7	732.5	731.2	730.0
125°	807.7	808.9	809.4	810.0	810.6	811.1	811.1	810.2	809.3	808.4	807.5
127.5°	883.0	884.7	885.4	886.0	886.6	887.3	886.7	884.8	883.0	881.1	879.3
130°	932.4	933.5	934.4	935.2	936.1	936.9	936.3	933.9	931.6	929.4	927.0
132.5°	980.9	982.3	982.9	983.6	984.2	984.9	984.0	981.7	979.4	977.1	974.8
135°	1053.1	1054.3	1054.6	1054.8	1055.2	1055.4	1054.7	1052.9	1051.2	1049.5	1047.8
137.5°	1123.9	1125.2	1124.4	1123.6	1122.9	1122.1	1121.0	1119.6	1118.2	1116.7	1115.3
140°	1169.5	1169.8	1169.5	1169.2	1169.0	1168.6	1167.8	1166.3	1164.9	1163.5	1162.0
142.5°	1213.1	1213.4	1212.9	1212.4	1211.9	1211.3	1210.4	1208.9	1207.5	1206.0	1204.6
145°	1277.3	1277.6	1276.7	1275.8	1275.0	1274.1	1273.4	1272.8	1272.2	1271.7	1271.1
147.5°	1337.6	1337.6	1336.7	1335.9	1335.2	1334.3	1333.4	1332.4	1331.3	1330.2	1329.2
150°	1374.9	1374.9	1374.3	1373.8	1373.2	1372.6	1372.1	1371.5	1370.9	1370.4	1369.8
152.5°	1408.7	1408.2	1407.8	1407.5	1407.1	1406.8	1406.2	1405.4	1404.6	1403.8	1403.0
155°	1457.9	1456.7	1456.5	1456.1	1455.9	1455.6	1455.4	1455.4	1455.4	1455.4	1455.4
157.5°	1500.8	1499.6	1499.3	1499.1	1498.9	1498.7	1498.7	1499.1	1499.4	1499.8	1500.1
160°	1527.0	1525.5	1525.5	1525.5	1525.5	1525.5	1525.9	1526.4	1527.0	1527.6	1528.2
162.5°	1552.0	1550.5	1550.2	1550.1	1549.8	1549.5	1549.9	1550.7	1551.4	1552.3	1553.1
165°	1583.1	1581.4	1581.4	1581.4	1581.4	1581.4	1581.8	1582.7	1583.6	1584.4	1585.3
167.5°	1608.6	1606.8	1606.6	1606.4	1606.1	1605.9	1606.4	1607.5	1608.7	1609.8	1611.0
170°	1622.4	1620.3	1620.3	1620.3	1620.3	1620.3	1620.9	1622.0	1623.2	1624.4	1625.5
172.5°	1633.6	1631.8	1631.8	1631.8	1631.8	1631.8	1632.4	1633.5	1634.6	1635.8	1636.9
175°	1645.5	1643.7	1643.7	1643.7	1643.7	1643.7	1644.3	1645.5	1646.6	1647.8	1648.9
177.5°	1651.1	1649.7	1649.7	1649.7	1649.7	1649.7	1650.1	1651.1	1652.0	1652.9	1653.8
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1589.5	1595.4	1603.0	1614.4	1623.1	1630.6	1632.3	1634.4	1639.9	1649.0	1656.0
5°	1599.7	1615.3	1640.4	1664.7	1691.1	1712.8	1733.1	1747.3	1760.8	1789.2	1812.2
7.5°	1596.6	1631.2	1670.4	1714.2	1758.4	1801.3	1841.1	1876.6	1912.1	1953.5	2000.8
10°	1594.3	1635.0	1687.7	1743.9	1805.5	1865.7	1923.9	1969.3	2022.1	2069.4	2129.6
12.5°	1584.1	1642.5	1705.6	1777.4	1853.1	1922.5	1999.2	2061.8	2122.2	2190.6	2260.6
15°	1570.6	1641.8	1721.6	1817.0	1932.0	2015.9	2094.5	2203.4	2277.9	2352.3	2452.5
17.5°	1546.2	1632.9	1732.7	1856.7	1952.6	2065.4	2183.5	2269.6	2369.9	2474.8	2565.4
20°	1526.6	1627.5	1739.1	1861.0	1983.5	2105.9	2220.3	2323.2	2426.7	2547.9	2622.3
22.5°	1507.2	1607.0	1722.9	1852.4	1984.0	2113.0	2242.5	2363.3	2479.8	2602.0	2697.0
25°	1465.8	1584.2	1710.0	1842.0	1971.9	2114.1	2268.4	2403.1	2547.2	2673.1	2763.0
27.5°	1423.8	1532.3	1657.7	1791.6	1936.0	2103.9	2285.4	2438.5	2582.9	2673.1	2701.3
30°	1386.0	1501.0	1616.0	1752.0	1908.3	2095.8	2288.6	2463.9	2582.4	2621.6	2592.5
32.5°	1347.5	1451.7	1565.6	1705.0	1871.0	2075.8	2293.0	2448.8	2520.1	2490.1	2371.6
35°	1279.7	1373.7	1484.0	1623.4	1814.3	2064.7	2275.1	2380.7	2363.1	2193.9	1970.6
37.5°	1207.1	1283.8	1386.0	1531.7	1755.6	2020.7	2198.2	2213.8	2061.6	1801.8	1543.9
40°	1149.8	1218.7	1323.7	1475.9	1710.0	1977.4	2120.8	2057.9	1821.7	1532.8	1317.6
42.5°	1094.0	1152.2	1253.3	1417.5	1666.7	1918.4	2005.5	1868.5	1595.9	1322.8	1127.0
45°	999.5	1054.3	1155.8	1324.3	1578.1	1805.5	1794.0	1555.7	1283.1	1063.2	900.7
47.5°	909.9	957.9	1053.1	1225.1	1474.0	1636.3	1528.7	1275.2	1043.9	867.5	751.6
50°	846.5	894.0	988.7	1158.6	1390.7	1509.1	1355.5	1111.2	899.4	753.2	661.2
52.5°	785.9	832.2	918.9	1084.3	1290.0	1360.7	1195.8	969.3	792.7	666.6	587.5
55°	701.1	736.2	814.1	972.4	1126.1	1142.3	975.2	785.7	640.2	552.2	498.1
57.5°	614.6	644.9	721.8	847.9	955.6	947.3	788.8	624.9	526.9	461.5	422.2
60°	558.3	588.1	655.7	764.1	845.2	816.8	671.3	539.3	455.5	407.4	376.3
62.5°	505.8	529.1	592.4	671.4	729.9	697.7	573.9	464.6	398.0	357.6	332.9
65°	429.7	448.7	499.4	540.7	573.2	542.1	439.2	363.4	315.4	287.0	270.0
67.5°	357.4	369.5	401.6	416.5	439.4	405.2	330.3	279.5	252.2	228.2	216.5
70°	311.9	320.7	337.7	349.8	355.9	320.7	265.3	228.1	205.0	188.1	180.7
72.5°	266.5	274.2	277.6	287.6	284.5	251.5	213.3	183.7	167.1	155.7	146.0
75°	203.7	207.1	203.7	199.7	190.8	167.8	141.5	126.6	114.3	108.9	105.6
77.5°	148.4	147.4	142.8	136.5	121.4	106.9	92.7	87.7	82.4	79.6	78.4
80°	114.3	111.7	107.6	97.5	84.6	74.5	71.0	67.7	65.6	62.3	61.6
82.5°	85.2	83.5	76.7	68.2	59.2	54.4	51.6	50.4	48.3	46.6	46.4
85°	45.4	43.3	35.9	31.2	29.8	28.4	27.7	27.7	25.1	24.4	24.4
87.5°	15.4	12.7	12.8	11.8	12.4	12.1	13.4	13.1	13.3	14.0	13.2
90°	4.2	7.1	10.0	12.8	16.2	19.9	23.7	27.4	31.2	32.3	33.5
92.5°	33.4	35.3	37.3	39.3	41.3	43.5	45.5	47.7	49.9	50.8	51.7
95°	78.6	80.7	82.7	84.7	86.9	89.1	91.4	93.8	96.1	97.2	98.4
97.5°	137.6	139.1	140.6	142.1	143.6	145.3	147.0	148.7	150.3	151.7	153.0
100°	178.3	180.0	181.8	183.5	185.1	186.5	188.0	189.4	190.9	191.7	192.6
102.5°	224.4	225.4	226.4	227.5	228.9	230.8	232.7	234.6	236.5	237.5	238.3
105°	292.7	293.3	293.9	294.5	296.0	298.6	301.2	303.8	306.4	306.4	306.4
107.5°	372.5	372.8	373.2	373.5	374.2	375.2	376.3	377.3	378.3	379.3	380.2
110°	422.6	423.1	423.7	424.3	424.8	425.4	426.0	426.5	427.1	428.3	429.5





TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	474.2	474.6	474.9	475.3	475.5	475.6	475.7	475.9	476.0	477.3	478.7
115°	552.7	553.5	554.4	555.3	555.4	554.8	554.2	553.7	553.1	553.4	553.7
117.5°	630.8	631.4	632.0	632.5	632.4	631.7	630.9	630.2	629.5	629.4	629.3
120°	680.8	682.5	684.2	686.0	686.1	684.7	683.2	681.7	680.4	680.0	679.8
122.5°	731.2	732.5	733.7	735.0	735.3	734.5	733.7	733.1	732.3	731.5	730.7
125°	808.4	809.3	810.2	811.1	811.1	810.6	810.0	809.4	808.9	807.7	806.6
127.5°	881.1	883.0	884.8	886.7	887.3	886.6	886.0	885.4	884.7	883.0	881.5
130°	929.4	931.6	933.9	936.3	936.9	936.1	935.2	934.4	933.5	932.4	931.2
132.5°	977.1	979.4	981.7	984.0	984.9	984.2	983.6	982.9	982.3	980.9	979.6
135°	1049.5	1051.2	1052.9	1054.7	1055.4	1055.2	1054.8	1054.6	1054.3	1053.1	1052.0
137.5°	1116.7	1118.2	1119.6	1121.0	1122.1	1122.9	1123.6	1124.4	1125.2	1123.9	1122.7
140°	1163.5	1164.9	1166.3	1167.8	1168.6	1169.0	1169.2	1169.5	1169.8	1169.5	1169.2
142.5°	1206.0	1207.5	1208.9	1210.4	1211.3	1211.9	1212.4	1212.9	1213.4	1213.1	1212.9
145°	1271.7	1272.2	1272.8	1273.4	1274.1	1275.0	1275.8	1276.7	1277.6	1277.3	1276.9
147.5°	1330.2	1331.3	1332.4	1333.4	1334.3	1335.2	1335.9	1336.7	1337.6	1337.6	1337.6
150°	1370.4	1370.9	1371.5	1372.1	1372.6	1373.2	1373.8	1374.3	1374.9	1374.9	1374.9
152.5°	1403.8	1404.6	1405.4	1406.2	1406.8	1407.1	1407.5	1407.8	1408.2	1408.7	1409.1
155°	1455.4	1455.4	1455.4	1455.4	1455.6	1455.9	1456.1	1456.5	1456.7	1457.9	1459.1
157.5°	1499.8	1499.4	1499.1	1498.7	1498.7	1498.9	1499.1	1499.3	1499.6	1500.8	1502.0
160°	1527.6	1527.0	1526.4	1525.9	1525.5	1525.5	1525.5	1525.5	1525.5	1527.0	1528.4
162.5°	1552.3	1551.4	1550.7	1549.9	1549.5	1549.8	1550.1	1550.2	1550.5	1552.0	1553.3
165°	1584.4	1583.6	1582.7	1581.8	1581.4	1581.4	1581.4	1581.4	1581.4	1583.1	1584.8
167.5°	1609.8	1608.7	1607.5	1606.4	1605.9	1606.1	1606.4	1606.6	1606.8	1608.6	1610.4
170°	1624.4	1623.2	1622.0	1620.9	1620.3	1620.3	1620.3	1620.3	1620.3	1622.4	1624.4
172.5°	1635.8	1634.6	1633.5	1632.4	1631.8	1631.8	1631.8	1631.8	1631.8	1633.6	1635.3
175°	1647.8	1646.6	1645.5	1644.3	1643.7	1643.7	1643.7	1643.7	1643.7	1645.5	1647.2
177.5°	1652.9	1652.0	1651.1	1650.1	1649.7	1649.7	1649.7	1649.7	1649.7	1651.1	1652.4
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8	1580.8
2.5°	1667.4	1667.4	1669.6	1677.7	1678.8	1685.8	1683.7
5°	1832.6	1845.4	1850.1	1870.4	1882.7	1888.1	1877.2
7.5°	2034.5	2070.8	2087.9	2109.2	2128.0	2133.7	2118.9
10°	2181.8	2219.7	2251.4	2271.1	2289.3	2301.5	2317.1
12.5°	2324.1	2370.7	2400.9	2428.6	2447.4	2462.9	2465.4
15°	2478.8	2549.2	2602.6	2641.9	2661.5	2671.7	2667.6
17.5°	2634.8	2700.1	2738.2	2778.2	2805.4	2806.8	2807.5
20°	2723.1	2786.7	2830.7	2860.5	2891.0	2889.6	2896.3
22.5°	2782.1	2832.2	2865.9	2887.5	2898.0	2892.9	2894.2
25°	2809.7	2824.6	2818.6	2784.0	2775.3	2743.4	2748.8
27.5°	2667.4	2596.9	2524.2	2430.5	2356.6	2297.6	2300.6
30°	2474.1	2349.6	2207.4	2088.4	1981.4	1951.6	1888.1
32.5°	2203.9	2017.2	1850.7	1739.7	1648.0	1623.1	1567.5
35°	1745.9	1564.6	1393.4	1290.5	1249.9	1193.1	1192.4
37.5°	1357.1	1197.4	1106.8	1029.7	989.2	954.8	951.5
40°	1141.6	1017.1	948.7	893.3	853.3	827.6	821.6
42.5°	991.1	890.4	826.4	792.0	761.3	748.0	738.1
45°	809.3	741.7	697.0	665.9	651.7	641.5	636.1
47.5°	677.0	631.6	601.2	580.5	568.9	558.3	561.1
50°	605.0	567.7	545.4	525.8	517.0	509.5	510.2
52.5°	547.1	513.7	495.6	481.4	470.5	465.2	462.6
55°	464.3	443.2	425.0	414.8	408.7	401.3	399.2
57.5°	396.0	379.8	364.9	353.4	351.9	344.7	345.7
60°	350.5	337.0	324.9	318.7	314.0	307.9	310.0
62.5°	313.1	301.8	290.8	285.7	280.9	276.5	277.4
65°	256.5	245.6	238.8	236.2	234.1	232.1	230.1
67.5°	204.4	197.8	193.6	187.7	183.6	182.9	180.8
70°	171.9	163.1	155.7	148.2	146.2	145.5	146.2
72.5°	137.8	132.2	130.2	126.6	126.1	124.4	125.6
75°	103.6	101.5	100.1	97.5	97.5	97.5	97.5
77.5°	76.4	75.1	74.3	73.8	73.1	72.2	72.0
80°	59.6	58.9	57.5	57.5	56.8	57.5	56.8
82.5°	44.9	44.8	43.5	43.5	42.8	42.4	42.8
85°	23.0	22.3	23.7	22.3	23.0	21.7	23.0
87.5°	13.4	13.7	13.3	13.4	13.0	14.2	13.2
90°	34.6	35.8	36.7	37.2	37.8	38.4	38.9
92.5°	52.6	53.6	53.8	53.5	53.1	52.8	52.4
95°	99.5	100.7	101.3	101.3	101.3	101.3	101.3
97.5°	154.3	155.7	156.3	156.2	156.0	155.9	155.8
100°	193.5	194.3	195.0	195.6	196.2	196.7	197.3
102.5°	239.2	240.0	240.4	240.3	240.1	240.0	240.0
105°	306.4	306.4	306.7	307.3	307.9	308.4	309.0
107.5°	381.1	382.0	382.3	381.9	381.6	381.3	380.9
110°	430.6	431.8	432.0	431.4	430.9	430.3	429.7



TEST NUMBER: P332487-935

CATALOG NUMBER: S123RDIW-S1165D1535U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	480.1	481.5	482.2	482.1	481.9	481.8	481.6
115°	554.0	554.2	554.2	554.0	553.7	553.4	553.1
117.5°	629.3	629.2	628.8	627.9	627.2	626.4	625.5
120°	679.5	679.2	678.7	678.2	677.6	677.0	676.4
122.5°	730.0	729.3	728.5	727.7	726.9	726.1	725.2
125°	805.4	804.3	803.1	801.9	800.8	799.6	798.5
127.5°	879.9	878.2	876.8	875.5	874.1	872.8	871.4
130°	930.1	928.9	927.3	925.3	923.3	921.3	919.2
132.5°	978.2	976.8	975.3	973.8	972.2	970.6	969.1
135°	1050.8	1049.6	1048.8	1048.2	1047.6	1047.1	1046.5
137.5°	1121.5	1120.3	1119.1	1118.0	1117.0	1115.9	1114.7
140°	1169.0	1168.6	1167.5	1165.4	1163.5	1161.4	1159.4
142.5°	1212.5	1212.3	1211.3	1209.8	1208.2	1206.7	1205.1
145°	1276.7	1276.4	1275.7	1274.5	1273.4	1272.2	1271.1
147.5°	1337.6	1337.6	1336.7	1335.0	1333.3	1331.5	1329.7
150°	1374.9	1374.9	1374.1	1372.3	1370.6	1368.9	1367.2
152.5°	1409.5	1410.1	1409.5	1408.0	1406.5	1405.0	1403.5
155°	1460.2	1461.4	1460.9	1458.9	1456.9	1454.8	1452.9
157.5°	1503.2	1504.4	1504.3	1502.6	1501.0	1499.3	1497.8
160°	1529.9	1531.3	1531.5	1530.3	1529.1	1528.0	1526.8
162.5°	1554.8	1556.3	1556.1	1554.2	1552.4	1550.5	1548.7
165°	1586.6	1588.3	1588.2	1586.1	1584.2	1582.1	1580.1
167.5°	1612.2	1613.9	1613.9	1612.2	1610.4	1608.6	1606.8
170°	1626.4	1628.4	1628.4	1626.4	1624.4	1622.4	1620.3
172.5°	1637.1	1638.9	1638.8	1636.8	1634.8	1632.7	1630.7
175°	1648.9	1650.6	1650.5	1648.5	1646.4	1644.4	1642.4
177.5°	1653.8	1655.2	1655.1	1653.5	1651.8	1650.3	1648.6
180°	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8	1652.8

(END OF REPORT)