

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332476-830

Luminaire Tested: **S123RDIW-S1165D755U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332476-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6976.4 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	34	31
6	65	53	45	39	61	50	43	38	44	39	34	39	34	31	34	30	27
7	60	48	40	35	56	46	38	33	40	35	30	36	31	27	31	27	24
8	56	44	36	31	52	42	34	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19664	19664	19664
5°	19739	19466	19578
10°	19627	19223	19158
15°	19417	18773	18574
20°	19126	18211	17786
25°	18828	17579	17016
30°	18434	16850	15929
35°	18029	16119	14933
40°	17654	15260	13699
45°	17163	14411	12584
50°	16623	13447	11338
55°	16071	12344	10175
60°	15565	11164	8900
65°	14905	9885	7623
70°	14080	8299	6156
75°	12876	6529	5793
80°	11480	5783	5331
85°	9695	5125	4755



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	2.5
10°-20°	477.3	6.8
20°-30°	687.3	9.9
30°-40°	774.2	11.1
40°-50°	740.6	10.6
50°-60°	606.5	8.7
60°-70°	409.2	5.9
70°-80°	205.9	3.0
80°-90°	57.1	0.8
90°-100°	33.9	0.5
100°-110°	161.8	2.3
110°-120°	388.6	5.6
120°-130°	494.8	7.1
130°-140°	528.7	7.6
140°-150°	494.4	7.1
150°-160°	398.8	5.7
160°-170°	257.4	3.7
170°-180°	88.7	1.3
0°-30°	1336.1	19.2
0°-40°	2110.3	30.2
0°-60°	3457.4	49.6
0°-90°	4129.5	59.2
90°-120°	584.3	8.4
90°-150°	2102.1	30.1
90°-180°	2847.0	40.8
0°-180°	6976.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1827	1827	1827	1827	1827	
5°	1827	1819	1802	1814	1812	173
15°	1742	1725	1685	1677	1667	491
25°	1585	1547	1480	1450	1433	729
35°	1372	1316	1227	1165	1136	858
45°	1128	1058	947	865	827	870
55°	856	781	658	575	542	768
65°	585	502	388	319	299	579
75°	310	238	157	143	139	330
85°	78	48	42	39	38	88
90°	1	8	17	19	21	6
95°	42	16	22	26	26	52
105°	207	210	152	36	30	219
115°	388	392	398	405	408	383
125°	547	552	555	556	558	488
135°	680	684	687	689	687	524
145°	785	790	791	793	793	491
155°	865	864	864	867	864	398
165°	912	910	909	914	910	258
175°	934	930	931	935	930	89
180°	934	934	934	934	934	



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1832.8	1831.6	1830.6	1829.6	1828.5	1826.4	1823.3	1820.0	1816.9	1813.7	1816.7
5°	1826.8	1825.1	1823.5	1821.8	1820.2	1817.4	1813.5	1809.5	1805.5	1801.6	1804.6
7.5°	1809.9	1808.2	1806.4	1804.6	1802.8	1799.3	1794.2	1789.0	1784.0	1778.8	1780.5
10°	1795.7	1793.4	1791.1	1788.8	1786.5	1782.3	1776.4	1770.5	1764.5	1758.7	1759.0
12.5°	1775.6	1773.0	1770.4	1767.8	1765.3	1760.4	1753.1	1745.9	1738.6	1731.4	1731.2
15°	1742.4	1738.7	1735.1	1731.5	1727.9	1721.5	1712.2	1703.0	1693.7	1684.6	1682.9
17.5°	1700.5	1696.4	1692.1	1687.9	1683.8	1675.7	1664.1	1652.3	1640.6	1628.9	1625.4
20°	1669.7	1664.5	1659.3	1654.0	1648.7	1639.8	1627.3	1614.8	1602.2	1589.8	1585.5
22.5°	1635.4	1629.3	1623.2	1617.2	1611.2	1601.5	1588.2	1574.9	1561.6	1548.2	1542.9
25°	1585.3	1577.1	1568.9	1560.6	1552.4	1540.7	1525.5	1510.4	1495.2	1480.1	1473.2
27.5°	1524.6	1515.5	1506.4	1497.3	1488.2	1475.3	1458.4	1441.5	1424.7	1407.8	1398.2
30°	1483.1	1473.2	1463.3	1453.4	1443.6	1429.4	1411.0	1392.5	1374.1	1355.7	1344.4
32.5°	1441.6	1430.4	1419.2	1408.0	1396.8	1381.5	1362.0	1342.5	1323.0	1303.5	1291.3
35°	1372.0	1360.1	1348.2	1336.4	1324.6	1308.4	1288.0	1267.6	1247.2	1226.7	1212.6
37.5°	1301.5	1288.3	1275.1	1261.9	1248.8	1231.2	1209.5	1187.7	1165.9	1144.1	1128.0
40°	1256.4	1241.9	1227.4	1213.0	1198.4	1179.5	1156.1	1132.7	1109.4	1086.0	1068.8
42.5°	1205.4	1190.9	1176.5	1162.0	1147.5	1128.1	1104.0	1079.8	1055.6	1031.5	1012.8
45°	1127.5	1112.7	1097.9	1083.1	1068.2	1048.1	1022.8	997.4	972.0	946.7	927.9
47.5°	1049.5	1033.3	1017.0	1000.8	984.5	963.7	938.3	912.9	887.6	862.3	841.9
50°	992.7	977.2	961.7	946.2	930.8	909.7	883.1	856.4	829.7	803.0	782.6
52.5°	941.7	924.9	908.1	891.4	874.5	852.9	826.5	800.1	773.7	747.3	726.1
55°	856.4	840.2	824.1	807.9	791.8	769.8	741.8	713.8	685.8	657.8	638.8
57.5°	777.5	760.0	742.3	724.8	707.2	684.4	656.3	628.1	600.0	571.9	553.8
60°	723.0	704.9	686.8	668.7	650.5	627.8	600.5	573.3	545.9	518.6	500.8
62.5°	668.5	650.4	632.3	614.2	596.1	573.3	546.0	518.7	491.3	464.0	447.3
65°	585.2	567.1	549.0	530.9	512.8	490.9	465.2	439.5	413.9	388.1	372.0
67.5°	502.0	483.6	465.3	447.0	428.8	407.3	382.7	358.0	333.4	308.8	296.7
70°	447.4	429.7	411.9	394.1	376.4	355.9	332.9	309.8	286.8	263.7	252.2
72.5°	392.9	375.4	357.9	340.4	322.8	303.6	282.7	261.7	240.8	219.9	210.5
75°	309.6	293.9	278.1	262.2	246.5	229.5	211.4	193.2	175.1	157.0	153.7
77.5°	233.8	219.5	205.2	191.0	176.6	163.6	152.0	140.3	128.7	117.1	115.3
80°	185.2	171.7	158.2	144.7	131.2	121.0	114.0	107.2	100.3	93.3	92.4
82.5°	138.9	127.3	115.6	104.0	92.4	84.9	81.7	78.4	75.2	72.0	71.0
85°	78.5	71.3	64.0	56.8	49.6	45.4	44.5	43.5	42.5	41.5	40.8
87.5°	28.6	26.0	23.4	20.8	18.2	17.2	17.5	17.9	18.4	18.8	18.6
90°	0.7	2.3	3.8	5.3	6.9	8.7	10.7	12.6	14.6	16.7	17.2
92.5°	12.9	12.4	12.1	11.6	11.2	11.7	13.2	14.7	16.2	17.7	18.8
95°	42.3	36.0	29.7	23.4	17.1	14.7	16.4	18.1	19.8	21.5	22.6
97.5°	85.0	82.2	79.4	76.5	73.7	66.7	55.6	44.5	33.5	22.3	23.6
100°	117.3	120.3	123.4	126.5	129.5	119.0	95.0	71.0	46.9	22.9	24.1
102.5°	153.8	156.1	158.3	160.5	162.7	150.7	124.4	98.1	71.9	45.6	41.8
105°	206.7	208.4	210.1	211.8	213.5	207.4	193.5	179.6	165.8	151.9	124.6
107.5°	262.4	263.8	265.1	266.6	267.9	269.7	271.8	274.0	276.3	278.4	258.4
110°	299.6	300.9	302.1	303.3	304.5	306.0	307.7	309.4	311.1	312.8	307.7



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	335.2	336.2	337.3	338.5	339.6	341.0	342.7	344.4	346.1	347.8	347.9
115°	387.7	388.6	389.6	390.5	391.4	392.6	394.0	395.3	396.7	398.1	399.6
117.5°	438.7	439.8	440.9	442.1	443.2	444.1	444.8	445.5	446.2	447.0	448.2
120°	470.2	471.6	473.1	474.4	475.8	476.7	477.2	477.7	478.2	478.5	479.8
122.5°	502.5	503.6	504.7	505.9	507.0	507.8	508.4	509.1	509.6	510.2	511.0
125°	546.6	547.8	549.0	550.3	551.5	552.4	553.0	553.6	554.2	554.9	555.2
127.5°	589.3	590.5	591.7	593.0	594.2	595.2	596.0	596.6	597.4	598.1	598.6
130°	615.9	617.2	618.4	619.6	620.9	621.8	622.4	623.0	623.6	624.2	624.8
132.5°	641.4	642.6	643.9	645.1	646.4	647.2	647.7	648.2	648.7	649.2	649.8
135°	680.4	681.4	682.2	683.2	684.1	684.9	685.5	686.1	686.7	687.3	687.8
137.5°	713.7	714.8	716.0	717.2	718.4	719.2	719.4	719.8	720.2	720.5	721.2
140°	735.8	736.8	737.7	738.7	739.6	740.3	740.7	741.2	741.7	742.2	742.7
142.5°	756.4	757.3	758.3	759.2	760.2	760.8	761.3	761.8	762.2	762.7	763.2
145°	785.1	786.2	787.3	788.3	789.5	790.1	790.4	790.8	791.1	791.4	791.6
147.5°	812.2	812.8	813.6	814.3	815.0	815.5	815.9	816.1	816.4	816.7	817.1
150°	828.9	829.2	829.7	830.2	830.7	831.0	831.4	831.7	832.0	832.3	832.6
152.5°	843.8	844.0	844.2	844.4	844.7	844.9	845.1	845.3	845.5	845.6	846.1
155°	864.9	864.6	864.3	863.9	863.7	863.6	863.7	863.9	864.0	864.2	865.0
157.5°	881.3	881.3	881.2	881.2	881.2	881.1	880.9	880.7	880.6	880.4	881.4
160°	891.3	891.1	891.0	890.8	890.6	890.5	890.3	890.1	890.0	889.9	890.8
162.5°	900.7	900.3	899.8	899.5	899.1	898.8	898.6	898.5	898.3	898.1	899.3
165°	912.1	911.6	911.2	910.7	910.2	909.9	909.7	909.6	909.5	909.3	910.5
167.5°	921.0	920.3	919.7	919.1	918.5	918.1	918.1	918.1	918.1	918.1	919.4
170°	926.0	925.3	924.7	924.1	923.5	923.1	923.1	923.1	923.1	923.1	924.4
172.5°	929.3	928.5	927.7	927.1	926.3	926.0	926.1	926.2	926.3	926.5	927.7
175°	933.6	932.7	932.0	931.2	930.5	930.2	930.3	930.5	930.7	930.8	931.9
177.5°	934.6	934.1	933.4	932.8	932.2	932.0	932.1	932.2	932.4	932.5	933.4
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8	1826.8
2.5°	1819.6	1822.5	1825.3	1826.6	1826.0	1825.5	1825.0	1824.4
5°	1807.5	1810.5	1813.5	1814.6	1813.9	1813.3	1812.6	1811.9
7.5°	1782.1	1783.8	1785.4	1785.6	1784.5	1783.4	1782.3	1781.1
10°	1759.3	1759.6	1760.0	1759.3	1757.7	1756.1	1754.4	1752.8
12.5°	1731.0	1730.8	1730.6	1729.6	1727.7	1725.7	1723.8	1721.9
15°	1681.3	1679.6	1678.0	1676.0	1673.7	1671.4	1669.1	1666.8
17.5°	1621.9	1618.3	1614.9	1611.5	1608.0	1604.6	1601.2	1597.7
20°	1581.2	1576.9	1572.6	1568.5	1564.5	1560.6	1556.7	1552.7
22.5°	1537.6	1532.3	1526.9	1522.4	1518.7	1515.0	1511.4	1507.7
25°	1466.3	1459.3	1452.5	1447.2	1443.6	1439.9	1436.3	1432.7
27.5°	1388.6	1378.9	1369.3	1361.8	1356.2	1350.8	1345.2	1339.6
30°	1333.2	1322.1	1310.9	1302.7	1297.4	1292.1	1286.9	1281.6
32.5°	1279.0	1266.8	1254.5	1245.7	1240.1	1234.5	1229.1	1223.5
35°	1198.4	1184.3	1170.2	1160.1	1154.1	1148.2	1142.3	1136.4
37.5°	1111.9	1095.9	1079.8	1068.1	1060.8	1053.5	1046.2	1038.9
40°	1051.8	1034.6	1017.6	1005.2	997.6	990.0	982.5	974.9
42.5°	994.1	975.3	956.7	944.0	937.2	930.4	923.6	916.8
45°	909.2	890.4	871.7	858.4	850.5	842.5	834.6	826.7
47.5°	821.4	801.1	780.6	766.9	759.9	752.8	745.7	738.8
50°	762.2	741.8	721.3	707.4	699.8	692.2	684.7	677.1
52.5°	704.9	683.7	662.5	648.5	641.7	635.0	628.2	621.4
55°	619.6	600.5	581.5	568.6	562.0	555.4	548.8	542.2
57.5°	535.8	517.7	499.7	487.9	482.3	476.7	471.1	465.5
60°	483.0	465.2	447.4	435.7	430.2	424.5	419.0	413.4
62.5°	430.6	413.9	397.1	385.9	379.9	374.1	368.3	362.4
65°	355.9	339.8	323.7	313.8	310.2	306.5	302.9	299.3
67.5°	284.6	272.6	260.5	252.6	248.7	244.8	240.9	237.0
70°	240.6	229.1	217.6	210.1	206.4	202.8	199.2	195.6
72.5°	201.0	191.6	182.2	176.7	175.2	173.7	172.2	170.7
75°	150.4	147.1	143.8	141.9	141.3	140.6	140.0	139.3
77.5°	113.5	111.7	109.9	108.7	108.0	107.4	106.7	106.0
80°	91.3	90.4	89.4	88.6	87.9	87.3	86.6	86.0
82.5°	70.0	69.1	68.1	67.5	67.4	67.2	67.1	67.0
85°	40.2	39.5	38.8	38.5	38.5	38.5	38.5	38.5
87.5°	18.5	18.3	18.2	18.0	17.8	17.6	17.4	17.2
90°	17.9	18.5	19.1	19.6	19.9	20.2	20.5	20.8
92.5°	19.7	20.7	21.7	22.2	22.4	22.6	22.8	23.0
95°	23.7	24.7	25.8	26.4	26.4	26.4	26.4	26.4
97.5°	24.8	26.0	27.2	28.0	28.1	28.3	28.5	28.6
100°	25.4	26.6	27.8	28.6	28.7	28.8	28.9	29.1
102.5°	38.0	34.2	30.3	28.6	28.8	29.1	29.4	29.7
105°	97.4	70.0	42.8	29.3	29.6	29.9	30.3	30.5
107.5°	238.4	218.4	198.4	178.1	157.5	137.0	116.4	95.9
110°	302.7	297.6	292.5	278.9	256.8	234.8	212.7	190.8



TEST NUMBER: P332476-830

CATALOG NUMBER: S123RDIW-S1165D755U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	348.0	348.1	348.2	345.8	341.2	336.6	331.9	327.3
115°	401.2	402.7	404.3	405.4	406.0	406.6	407.2	407.8
117.5°	449.4	450.6	451.9	452.5	452.7	452.8	452.9	453.1
120°	481.1	482.3	483.5	484.1	484.1	484.1	484.1	484.1
122.5°	511.9	512.7	513.7	514.2	514.3	514.3	514.5	514.6
125°	555.4	555.8	556.1	556.4	556.8	557.0	557.3	557.6
127.5°	599.2	599.6	600.1	600.2	599.9	599.6	599.3	599.0
130°	625.5	626.0	626.7	626.9	626.5	626.2	625.9	625.6
132.5°	650.4	651.0	651.7	651.8	651.3	650.9	650.4	650.0
135°	688.2	688.7	689.2	689.2	688.7	688.2	687.8	687.3
137.5°	722.0	722.7	723.5	723.7	723.4	723.0	722.7	722.5
140°	743.4	743.9	744.6	744.8	744.4	744.1	743.9	743.5
142.5°	763.6	764.1	764.6	764.7	764.2	763.8	763.4	762.9
145°	792.0	792.3	792.6	792.8	792.8	792.8	792.8	792.8
147.5°	817.4	817.7	818.0	817.7	817.1	816.3	815.7	814.9
150°	832.9	833.2	833.5	833.5	833.0	832.5	832.1	831.6
152.5°	846.7	847.3	847.8	847.7	847.1	846.3	845.6	844.9
155°	865.7	866.5	867.3	867.2	866.3	865.3	864.4	863.5
157.5°	882.3	883.2	884.1	884.0	882.8	881.6	880.4	879.2
160°	891.7	892.7	893.5	893.5	892.4	891.4	890.2	889.2
162.5°	900.3	901.4	902.4	902.4	901.4	900.5	899.6	898.6
165°	911.7	912.9	914.2	914.3	913.2	912.1	911.1	909.9
167.5°	920.6	921.9	923.1	923.1	921.9	920.6	919.4	918.1
170°	925.6	926.9	928.1	928.1	926.9	925.6	924.4	923.1
172.5°	929.0	930.2	931.4	931.3	930.0	928.7	927.3	926.0
175°	932.9	934.1	935.1	935.0	933.8	932.6	931.3	930.1
177.5°	934.4	935.4	936.4	936.2	935.0	933.8	932.6	931.3
180°	933.6	933.6	933.6	933.6	933.6	933.6	933.6	933.6

(END OF REPORT)