

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332401-830

Luminaire Tested: **S123RDIW-S340D1030U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332401-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D1030U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4594.9 lumens  
Efficiency: N/A  
Efficacy: 120.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27				
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23				
2	85	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14				
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13				
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11				
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	9	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	1.1
10°-20°	141.5	3.1
20°-30°	203.7	4.4
30°-40°	229.5	5.0
40°-50°	219.5	4.8
50°-60°	179.8	3.9
60°-70°	121.3	2.6
70°-80°	61.0	1.3
80°-90°	19.7	0.4
90°-100°	79.2	1.7
100°-110°	237.0	5.2
110°-120°	403.1	8.8
120°-130°	530.3	11.5
130°-140°	596.0	13.0
140°-150°	585.8	12.8
150°-160°	493.2	10.7
160°-170°	328.3	7.1
170°-180°	115.0	2.5
0°-30°	396.1	8.6
0°-40°	625.5	13.6
0°-60°	1024.8	22.3
0°-90°	1226.9	26.7
90°-120°	719.4	15.7
90°-150°	2431.5	52.9
90°-180°	3368.0	73.3
0°-180°	4594.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	11	23	27	29	5
95°	56	63	71	74	74	63
105°	215	217	225	226	227	230
115°	406	408	407	408	407	401
125°	594	597	595	591	587	529
135°	771	776	775	772	770	594
145°	935	937	940	938	935	584
155°	1070	1070	1071	1075	1069	493
165°	1166	1163	1163	1168	1162	329
175°	1213	1209	1209	1214	1208	115
180°	1216	1216	1216	1216	1216	



TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.6	8.2	7.7	7.4	6.9	7.0	7.5	8.0	8.6	9.1	9.2
90°	0.9	3.1	5.2	7.4	9.4	11.9	14.6	17.4	20.2	22.9	23.8
92.5°	23.1	24.5	26.0	27.4	28.8	30.3	32.0	33.6	35.1	36.7	37.3
95°	56.4	57.8	59.3	60.8	62.3	63.9	65.6	67.3	69.0	70.7	71.5
97.5°	100.1	101.1	102.3	103.4	104.5	105.7	106.9	108.1	109.3	110.6	111.6
100°	129.9	131.1	132.4	133.7	135.0	136.1	137.2	138.3	139.3	140.3	141.0
102.5°	164.3	165.0	165.8	166.5	167.3	168.3	169.8	171.2	172.6	174.0	174.7
105°	214.9	215.3	215.7	216.1	216.6	217.7	219.6	221.5	223.5	225.4	225.4
107.5°	273.7	273.9	274.2	274.5	274.7	275.2	276.0	276.7	277.5	278.2	278.9
110°	310.4	310.8	311.2	311.6	312.1	312.5	312.9	313.3	313.8	314.1	315.0



TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.6	348.8	349.0	349.3	349.6	349.7	349.8	349.9	350.0	350.1	351.1
115°	405.9	406.4	407.1	407.7	408.4	408.5	408.0	407.6	407.2	406.8	407.0
117.5°	463.5	463.9	464.4	464.8	465.2	465.1	464.6	464.0	463.4	463.0	462.9
120°	499.5	500.7	502.0	503.2	504.5	504.6	503.5	502.5	501.4	500.4	500.1
122.5°	536.9	537.8	538.8	539.6	540.5	540.7	540.3	539.7	539.1	538.6	538.0
125°	594.0	594.6	595.2	595.9	596.5	596.6	596.2	595.8	595.3	594.9	594.1
127.5°	646.7	648.0	649.4	650.7	652.1	652.5	652.1	651.6	651.1	650.6	649.5
130°	681.8	683.5	685.2	686.9	688.6	689.1	688.5	687.9	687.2	686.5	685.7
132.5°	716.9	718.6	720.3	722.1	723.8	724.3	723.9	723.4	722.9	722.5	721.4
135°	770.6	771.8	773.2	774.4	775.7	776.2	776.0	775.8	775.6	775.3	774.5
137.5°	820.3	821.3	822.4	823.4	824.5	825.3	825.9	826.4	827.0	827.6	826.6
140°	854.6	855.7	856.8	857.8	858.8	859.5	859.7	860.0	860.2	860.4	860.2
142.5°	886.0	887.0	888.1	889.1	890.2	890.9	891.3	891.6	892.1	892.5	892.2
145°	934.8	935.3	935.7	936.1	936.5	937.1	937.7	938.4	939.0	939.6	939.4
147.5°	977.6	978.4	979.1	980.0	980.7	981.4	981.9	982.6	983.2	983.7	983.7
150°	1007.4	1007.9	1008.2	1008.7	1009.1	1009.6	1009.9	1010.4	1010.8	1011.3	1011.3
152.5°	1031.9	1032.5	1033.0	1033.7	1034.3	1034.6	1034.9	1035.2	1035.5	1035.7	1036.0
155°	1070.4	1070.4	1070.4	1070.4	1070.4	1070.5	1070.7	1071.0	1071.2	1071.4	1072.2
157.5°	1103.3	1103.1	1102.8	1102.5	1102.3	1102.2	1102.4	1102.6	1102.8	1102.9	1103.8
160°	1123.9	1123.5	1123.0	1122.7	1122.2	1122.0	1122.0	1122.0	1122.0	1122.0	1123.0
162.5°	1142.3	1141.7	1141.0	1140.5	1139.9	1139.6	1139.8	1140.0	1140.2	1140.4	1141.4
165°	1165.9	1165.3	1164.7	1164.0	1163.4	1163.1	1163.1	1163.1	1163.1	1163.1	1164.3
167.5°	1184.9	1184.0	1183.2	1182.3	1181.5	1181.1	1181.3	1181.5	1181.7	1181.8	1183.1
170°	1195.5	1194.7	1193.8	1193.0	1192.1	1191.8	1191.8	1191.8	1191.8	1191.8	1193.2
172.5°	1203.9	1203.1	1202.2	1201.4	1200.5	1200.1	1200.1	1200.1	1200.1	1200.1	1201.5
175°	1212.8	1211.9	1211.1	1210.2	1209.4	1208.9	1208.9	1208.9	1208.9	1208.9	1210.2
177.5°	1216.4	1215.7	1215.0	1214.3	1213.6	1213.3	1213.3	1213.3	1213.3	1213.3	1214.3
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6



TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	9.3	9.4	9.5	9.6	9.6	9.6	9.6	9.6
90°	24.6	25.4	26.3	27.0	27.3	27.8	28.2	28.7
92.5°	38.0	38.7	39.4	39.6	39.3	39.1	38.8	38.5
95°	72.4	73.2	74.1	74.5	74.5	74.5	74.5	74.5
97.5°	112.5	113.5	114.5	114.9	114.8	114.8	114.7	114.6
100°	141.7	142.3	142.9	143.5	143.8	144.3	144.7	145.2
102.5°	175.2	175.9	176.5	176.8	176.7	176.6	176.5	176.4
105°	225.4	225.4	225.4	225.6	226.0	226.4	226.9	227.2
107.5°	279.7	280.3	281.0	281.2	281.0	280.7	280.4	280.1
110°	315.8	316.7	317.5	317.7	317.4	316.9	316.5	316.0





TEST NUMBER: P332401-830

CATALOG NUMBER: S123RDIW-S340D1030U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	352.1	353.1	354.1	354.6	354.5	354.4	354.4	354.3
115°	407.2	407.5	407.6	407.6	407.5	407.2	407.0	406.8
117.5°	462.9	462.8	462.8	462.4	461.8	461.3	460.6	460.1
120°	499.9	499.7	499.5	499.2	498.8	498.3	497.9	497.5
122.5°	537.4	536.9	536.4	535.7	535.2	534.6	534.0	533.4
125°	593.2	592.4	591.5	590.7	589.8	589.0	588.1	587.3
127.5°	648.3	647.1	645.9	644.8	643.9	642.9	641.9	640.9
130°	684.9	684.0	683.2	682.0	680.5	679.0	677.6	676.1
132.5°	720.5	719.4	718.4	717.4	716.1	715.0	713.9	712.8
135°	773.6	772.8	771.9	771.4	770.9	770.5	770.1	769.7
137.5°	825.8	824.8	824.0	823.1	822.3	821.5	820.7	819.9
140°	860.0	859.7	859.5	858.7	857.1	855.7	854.2	852.7
142.5°	892.0	891.8	891.6	890.9	889.8	888.6	887.5	886.4
145°	939.2	939.0	938.8	938.2	937.4	936.5	935.7	934.8
147.5°	983.7	983.7	983.7	983.1	981.8	980.5	979.3	978.0
150°	1011.3	1011.3	1011.3	1010.6	1009.4	1008.0	1006.8	1005.5
152.5°	1036.3	1036.7	1037.1	1036.7	1035.6	1034.4	1033.3	1032.3
155°	1073.1	1073.9	1074.8	1074.5	1073.0	1071.5	1070.1	1068.6
157.5°	1104.7	1105.6	1106.5	1106.4	1105.1	1104.0	1102.8	1101.5
160°	1124.2	1125.2	1126.2	1126.3	1125.5	1124.6	1123.8	1122.9
162.5°	1142.5	1143.5	1144.6	1144.4	1143.1	1141.7	1140.4	1139.0
165°	1165.6	1166.9	1168.2	1168.1	1166.6	1165.1	1163.6	1162.2
167.5°	1184.4	1185.7	1187.0	1187.0	1185.7	1184.4	1183.1	1181.8
170°	1194.7	1196.2	1197.7	1197.7	1196.2	1194.7	1193.2	1191.8
172.5°	1202.8	1204.1	1205.4	1205.3	1203.8	1202.3	1200.8	1199.4
175°	1211.4	1212.8	1214.0	1213.9	1212.4	1210.9	1209.5	1208.0
177.5°	1215.3	1216.4	1217.4	1217.3	1216.1	1214.9	1213.7	1212.6
180°	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6	1215.6

(END OF REPORT)