

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332404-830

Luminaire Tested: **S123RDIW-S340D1320U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332404-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U830-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6202.5 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	28	28	28
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24
2	83	76	70	66	73	67	63	59	51	48	45	36	34	33	22	21	20
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	18
4	69	59	52	46	61	53	46	41	40	36	32	29	26	24	18	16	15
5	63	53	45	39	56	47	40	35	36	31	28	26	23	20	16	14	13
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12
7	54	42	35	29	47	38	31	27	29	24	21	21	18	16	13	12	10
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9
9	46	35	28	23	41	31	25	21	24	20	17	17	15	12	11	10	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	0.8
10°-20°	141.5	2.3
20°-30°	203.7	3.3
30°-40°	229.5	3.7
40°-50°	219.5	3.5
50°-60°	179.8	2.9
60°-70°	121.3	2.0
70°-80°	61.0	1.0
80°-90°	20.7	0.3
90°-100°	59.3	1.0
100°-110°	282.7	4.6
110°-120°	679.0	10.9
120°-130°	864.6	13.9
130°-140°	923.8	14.9
140°-150°	863.8	13.9
150°-160°	696.8	11.2
160°-170°	449.7	7.3
170°-180°	155.0	2.5
0°-30°	396.1	6.4
0°-40°	625.5	10.1
0°-60°	1024.8	16.5
0°-90°	1227.9	19.8
90°-120°	1020.9	16.5
90°-150°	3673.1	59.2
90°-180°	4975.0	80.2
0°-180°	6202.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	1	14	29	34	36	5
95°	74	28	38	46	46	91
105°	361	368	265	63	53	383
115°	678	685	696	707	713	669
125°	955	964	970	972	974	853
135°	1189	1196	1201	1204	1201	915
145°	1372	1380	1383	1385	1385	858
155°	1511	1509	1510	1515	1509	696
165°	1594	1590	1589	1598	1590	450
175°	1631	1626	1626	1634	1625	155
180°	1631	1631	1631	1631	1631	



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.7	8.4	8.0	7.7	7.4	7.5	8.3	9.0	9.7	10.4	10.6
90°	1.2	3.9	6.6	9.3	12.0	15.1	18.6	22.1	25.5	29.1	30.2
92.5°	22.5	21.8	21.0	20.3	19.5	20.5	23.1	25.7	28.4	31.0	32.7
95°	73.9	62.9	51.8	40.8	29.8	25.7	28.7	31.7	34.6	37.6	39.5
97.5°	148.5	143.6	138.6	133.7	128.8	116.6	97.2	77.9	58.4	39.0	41.2
100°	204.8	210.2	215.6	220.9	226.4	208.0	166.1	124.0	82.0	40.0	42.1
102.5°	268.8	272.7	276.5	280.4	284.4	263.3	217.4	171.5	125.6	79.7	73.0
105°	361.2	364.1	367.1	370.0	373.0	362.4	338.1	313.9	289.6	265.4	217.7
107.5°	458.6	461.0	463.4	465.7	468.1	471.2	475.0	478.8	482.7	486.4	451.5
110°	523.6	525.8	527.8	530.0	532.2	534.7	537.7	540.6	543.7	546.6	537.7



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	585.6	587.6	589.5	591.4	593.3	595.8	598.8	601.7	604.7	607.7	607.8
115°	677.5	679.1	680.7	682.3	683.9	686.0	688.3	690.8	693.2	695.7	698.3
117.5°	766.5	768.5	770.4	772.4	774.4	776.0	777.2	778.5	779.8	781.0	783.2
120°	821.7	824.2	826.5	829.0	831.4	833.0	833.8	834.6	835.5	836.2	838.4
122.5°	878.0	880.0	881.9	883.9	885.9	887.4	888.4	889.5	890.5	891.6	893.1
125°	955.0	957.2	959.3	961.5	963.7	965.3	966.3	967.4	968.5	969.6	970.1
127.5°	1029.6	1031.8	1034.0	1036.1	1038.3	1040.0	1041.3	1042.6	1043.9	1045.2	1046.0
130°	1076.2	1078.4	1080.5	1082.7	1084.9	1086.5	1087.5	1088.6	1089.7	1090.7	1091.8
132.5°	1120.8	1122.9	1125.1	1127.3	1129.4	1131.0	1131.8	1132.7	1133.5	1134.3	1135.5
135°	1188.9	1190.5	1192.1	1193.7	1195.4	1196.7	1197.8	1198.9	1200.0	1201.1	1201.8
137.5°	1247.1	1249.2	1251.2	1253.2	1255.3	1256.6	1257.2	1257.8	1258.4	1259.0	1260.3
140°	1285.9	1287.5	1289.1	1290.7	1292.3	1293.5	1294.4	1295.1	1296.0	1296.8	1297.9
142.5°	1321.7	1323.3	1325.0	1326.6	1328.2	1329.5	1330.2	1331.1	1331.8	1332.7	1333.5
145°	1372.0	1373.9	1375.7	1377.6	1379.5	1380.6	1381.2	1381.8	1382.3	1382.8	1383.4
147.5°	1419.2	1420.4	1421.6	1422.9	1424.2	1425.0	1425.6	1426.1	1426.6	1427.2	1427.8
150°	1448.3	1449.1	1449.9	1450.7	1451.5	1452.2	1452.7	1453.2	1453.8	1454.3	1454.9
152.5°	1474.4	1474.8	1475.2	1475.6	1475.9	1476.3	1476.7	1477.0	1477.2	1477.6	1478.6
155°	1511.3	1510.8	1510.2	1509.7	1509.1	1509.0	1509.3	1509.6	1509.9	1510.0	1511.5
157.5°	1539.9	1539.8	1539.8	1539.7	1539.6	1539.5	1539.3	1539.0	1538.7	1538.4	1540.0
160°	1557.4	1557.1	1556.8	1556.5	1556.2	1556.0	1555.8	1555.5	1555.2	1554.9	1556.5
162.5°	1573.9	1573.1	1572.4	1571.7	1571.0	1570.6	1570.3	1570.0	1569.7	1569.4	1571.3
165°	1593.7	1592.9	1592.0	1591.3	1590.4	1590.0	1589.7	1589.4	1589.1	1588.8	1591.0
167.5°	1609.2	1608.2	1607.0	1606.0	1604.9	1604.4	1604.4	1604.4	1604.4	1604.4	1606.6
170°	1618.0	1616.8	1615.8	1614.8	1613.6	1613.1	1613.1	1613.1	1613.1	1613.1	1615.2
172.5°	1623.8	1622.5	1621.2	1619.9	1618.6	1618.1	1618.3	1618.5	1618.7	1618.9	1621.1
175°	1631.3	1629.9	1628.6	1627.2	1625.9	1625.3	1625.6	1625.9	1626.2	1626.5	1628.3
177.5°	1633.2	1632.1	1631.1	1630.0	1628.9	1628.5	1628.7	1628.9	1629.1	1629.4	1631.1
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	10.7	10.8	10.9	11.0	11.0	11.1	11.1	11.1
90°	31.2	32.3	33.4	34.2	34.8	35.3	35.8	36.4
92.5°	34.5	36.2	37.9	38.9	39.3	39.6	39.9	40.2
95°	41.4	43.3	45.1	46.1	46.1	46.1	46.1	46.1
97.5°	43.4	45.5	47.6	48.8	49.1	49.4	49.7	50.0
100°	44.3	46.5	48.6	49.9	50.0	50.3	50.6	50.9
102.5°	66.4	59.7	53.1	50.0	50.4	50.9	51.4	51.8
105°	170.0	122.4	74.7	51.2	51.7	52.2	52.8	53.3
107.5°	416.6	381.6	346.7	311.2	275.3	239.3	203.4	167.5
110°	528.8	519.9	511.0	487.3	448.8	410.3	371.8	333.3



TEST NUMBER: P332404-830

CATALOG NUMBER: S123RDIW-S340D1320U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	608.0	608.1	608.3	604.4	596.2	588.1	579.9	571.8
115°	701.1	703.7	706.4	708.3	709.4	710.5	711.5	712.7
117.5°	785.3	787.4	789.6	790.8	791.0	791.2	791.5	791.6
120°	840.6	842.7	844.9	845.9	845.9	845.9	845.9	845.9
122.5°	894.6	896.1	897.6	898.4	898.6	898.8	899.1	899.3
125°	970.6	971.2	971.7	972.2	972.8	973.4	973.8	974.4
127.5°	1046.9	1047.7	1048.7	1048.8	1048.3	1047.7	1047.2	1046.6
130°	1092.9	1094.0	1095.0	1095.3	1094.8	1094.3	1093.7	1093.2
132.5°	1136.5	1137.6	1138.7	1138.9	1138.1	1137.4	1136.6	1135.9
135°	1202.7	1203.4	1204.3	1204.3	1203.4	1202.7	1201.8	1201.1
137.5°	1261.6	1262.8	1264.1	1264.5	1263.9	1263.5	1262.9	1262.3
140°	1298.9	1300.0	1301.1	1301.4	1300.8	1300.2	1299.8	1299.2
142.5°	1334.4	1335.2	1336.1	1336.1	1335.4	1334.6	1333.9	1333.1
145°	1383.9	1384.4	1385.0	1385.3	1385.3	1385.3	1385.3	1385.3
147.5°	1428.2	1428.8	1429.4	1429.0	1427.8	1426.5	1425.3	1424.0
150°	1455.4	1455.9	1456.5	1456.3	1455.6	1454.7	1454.0	1453.1
152.5°	1479.5	1480.5	1481.5	1481.4	1480.1	1478.8	1477.6	1476.4
155°	1512.8	1514.1	1515.5	1515.3	1513.7	1512.1	1510.5	1508.9
157.5°	1541.7	1543.3	1544.9	1544.6	1542.6	1540.5	1538.3	1536.3
160°	1558.1	1559.8	1561.4	1561.2	1559.3	1557.5	1555.6	1553.7
162.5°	1573.1	1575.0	1576.8	1576.9	1575.2	1573.6	1571.9	1570.2
165°	1593.2	1595.3	1597.5	1597.6	1595.7	1593.8	1592.0	1590.1
167.5°	1608.7	1610.8	1613.0	1613.0	1610.8	1608.7	1606.6	1604.4
170°	1617.4	1619.6	1621.7	1621.7	1619.6	1617.4	1615.2	1613.1
172.5°	1623.2	1625.4	1627.6	1627.4	1625.0	1622.7	1620.3	1618.0
175°	1630.2	1632.1	1634.0	1633.8	1631.7	1629.6	1627.4	1625.2
177.5°	1632.8	1634.6	1636.3	1636.1	1633.9	1631.7	1629.6	1627.4
180°	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3	1631.3

(END OF REPORT)