

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332393-830

Luminaire Tested: **S123RDIW-S340D460U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332393-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S340D460U830-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2731.4 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 23  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45				45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				38
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33				33
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	29	27	24	21				21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15				15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16	14				14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5829	5829	5829
5°	5851	5770	5804
10°	5818	5698	5678
15°	5756	5565	5506
20°	5669	5399	5271
25°	5582	5211	5044
30°	5464	4994	4721
35°	5344	4778	4427
40°	5233	4523	4061
45°	5087	4271	3731
50°	4928	3985	3361
55°	4763	3659	3016
60°	4613	3309	2637
65°	4419	2932	2259
70°	4173	2458	1825
75°	3818	1938	1718
80°	3403	1717	1574
85°	2878	1519	1408



TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	1.9
10°-20°	141.5	5.2
20°-30°	203.7	7.5
30°-40°	229.5	8.4
40°-50°	219.5	8.0
50°-60°	179.8	6.6
60°-70°	121.3	4.4
70°-80°	61.0	2.2
80°-90°	17.7	0.6
90°-100°	35.4	1.3
100°-110°	106.0	3.9
110°-120°	180.3	6.6
120°-130°	237.2	8.7
130°-140°	266.6	9.8
140°-150°	262.1	9.6
150°-160°	220.6	8.1
160°-170°	146.9	5.4
170°-180°	51.4	1.9
0°-30°	396.1	14.5
0°-40°	625.5	22.9
0°-60°	1024.8	37.5
0°-90°	1224.9	44.8
90°-120°	321.8	11.8
90°-150°	1087.6	39.8
90°-180°	1507.0	55.2
0°-180°	2731.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	542	542	542	542	542	
5°	542	539	534	538	537	51
15°	516	511	499	497	494	145
25°	470	458	439	430	425	216
35°	407	390	364	345	337	254
45°	334	314	281	256	245	258
55°	254	231	195	170	161	228
65°	174	149	115	94	89	172
75°	92	71	47	42	41	98
85°	23	14	12	11	11	26
90°	0	5	10	12	13	3
95°	25	28	32	33	33	28
105°	96	97	101	101	102	103
115°	182	183	182	182	182	180
125°	266	267	266	264	263	237
135°	345	347	347	345	344	266
145°	418	419	420	420	418	261
155°	479	479	479	481	478	220
165°	522	520	520	522	520	147
175°	542	541	541	543	540	52
180°	544	544	544	544	544	



TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	543.3	542.9	542.6	542.3	542.1	541.4	540.5	539.5	538.6	537.6	538.5
5°	541.5	541.0	540.5	540.1	539.5	538.8	537.5	536.4	535.2	534.0	534.9
7.5°	536.5	535.9	535.5	534.9	534.4	533.4	531.9	530.4	528.8	527.3	527.7
10°	532.3	531.6	530.9	530.3	529.5	528.3	526.6	524.8	523.0	521.3	521.4
12.5°	526.3	525.6	524.8	524.1	523.3	521.8	519.6	517.6	515.4	513.2	513.1
15°	516.5	515.4	514.3	513.2	512.2	510.3	507.6	504.8	502.1	499.4	498.9
17.5°	504.1	502.8	501.6	500.3	499.1	496.7	493.2	489.7	486.4	482.9	481.8
20°	494.9	493.4	491.8	490.3	488.7	486.1	482.4	478.6	474.9	471.3	470.0
22.5°	484.7	483.0	481.2	479.4	477.6	474.8	470.8	466.8	462.9	458.9	457.3
25°	470.0	467.5	465.1	462.6	460.1	456.7	452.2	447.7	443.2	438.8	436.7
27.5°	451.9	449.2	446.5	443.8	441.1	437.3	432.3	427.3	422.3	417.3	414.4
30°	439.6	436.7	433.8	430.8	427.9	423.7	418.2	412.7	407.3	401.8	398.5
32.5°	427.3	424.0	420.7	417.4	414.1	409.5	403.7	397.9	392.2	386.3	382.8
35°	406.7	403.1	399.6	396.2	392.7	387.9	381.8	375.7	369.7	363.6	359.5
37.5°	385.8	381.8	378.0	374.1	370.1	365.0	358.5	352.0	345.6	339.1	334.4
40°	372.4	368.2	363.8	359.6	355.2	349.6	342.7	335.7	328.9	321.9	316.9
42.5°	357.3	353.0	348.7	344.4	340.2	334.4	327.3	320.1	312.9	305.8	300.2
45°	334.2	329.8	325.5	321.0	316.6	310.7	303.2	295.7	288.1	280.6	275.0
47.5°	311.1	306.3	301.4	296.6	291.8	285.7	278.1	270.6	263.2	255.6	249.6
50°	294.3	289.6	285.1	280.5	275.9	269.7	261.7	253.8	245.9	238.0	232.0
52.5°	279.2	274.2	269.2	264.2	259.2	252.8	245.0	237.1	229.3	221.5	215.3
55°	253.8	249.0	244.3	239.5	234.7	228.2	219.9	211.6	203.3	195.0	189.4
57.5°	230.5	225.3	220.1	214.8	209.6	202.8	194.5	186.2	177.9	169.6	164.2
60°	214.3	209.0	203.6	198.2	192.8	186.2	178.0	169.9	161.8	153.7	148.5
62.5°	198.1	192.7	187.4	182.1	176.7	169.9	161.8	153.7	145.6	137.5	132.6
65°	173.5	168.1	162.8	157.4	152.0	145.5	137.9	130.3	122.7	115.1	110.3
67.5°	148.8	143.4	137.9	132.5	127.1	120.7	113.4	106.1	98.8	91.5	87.9
70°	132.6	127.3	122.1	116.8	111.6	105.5	98.7	91.8	85.0	78.1	74.7
72.5°	116.5	111.3	106.1	100.9	95.7	90.0	83.8	77.6	71.4	65.1	62.4
75°	91.8	87.1	82.4	77.8	73.0	68.1	62.7	57.3	51.9	46.6	45.6
77.5°	69.3	65.0	60.8	56.6	52.4	48.5	45.1	41.6	38.2	34.7	34.2
80°	54.9	50.9	46.9	42.9	38.9	35.9	33.8	31.8	29.7	27.7	27.3
82.5°	41.2	37.7	34.3	30.8	27.3	25.2	24.2	23.3	22.3	21.3	21.0
85°	23.3	21.1	18.9	16.9	14.7	13.5	13.2	12.9	12.6	12.3	12.1
87.5°	8.5	7.8	7.2	6.5	5.8	5.7	5.8	6.1	6.4	6.6	6.6
90°	0.5	1.4	2.4	3.3	4.2	5.3	6.5	7.8	9.0	10.3	10.7
92.5°	10.4	11.0	11.6	12.3	12.9	13.6	14.3	15.0	15.7	16.4	16.7
95°	25.2	25.8	26.5	27.2	27.9	28.6	29.3	30.1	30.8	31.6	32.0
97.5°	44.8	45.2	45.7	46.3	46.8	47.2	47.8	48.4	48.9	49.5	49.9
100°	58.1	58.6	59.2	59.8	60.3	60.9	61.4	61.8	62.3	62.8	63.1
102.5°	73.4	73.8	74.2	74.5	74.8	75.3	76.0	76.5	77.2	77.9	78.1
105°	96.1	96.3	96.5	96.7	96.9	97.4	98.2	99.1	99.9	100.8	100.8
107.5°	122.4	122.5	122.6	122.7	122.9	123.1	123.5	123.8	124.1	124.5	124.8
110°	138.8	139.0	139.2	139.4	139.6	139.8	140.0	140.2	140.3	140.5	140.9



TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.9	156.0	156.2	156.3	156.4	156.5	156.5	156.6	156.6	156.6	157.0
115°	181.5	181.8	182.1	182.4	182.7	182.8	182.6	182.4	182.2	182.0	182.1
117.5°	207.4	207.5	207.7	207.9	208.1	208.0	207.8	207.5	207.4	207.1	207.1
120°	223.4	223.9	224.5	225.1	225.6	225.7	225.3	224.8	224.3	223.9	223.8
122.5°	240.2	240.5	241.0	241.4	241.8	241.9	241.7	241.4	241.2	240.9	240.6
125°	265.7	266.0	266.3	266.6	266.8	266.8	266.6	266.5	266.3	266.1	265.7
127.5°	289.3	289.8	290.5	291.1	291.7	291.9	291.7	291.4	291.2	291.1	290.5
130°	305.0	305.8	306.5	307.3	308.0	308.2	307.9	307.6	307.4	307.1	306.7
132.5°	320.7	321.4	322.3	323.0	323.8	324.0	323.8	323.6	323.4	323.2	322.7
135°	344.7	345.3	345.8	346.4	346.9	347.2	347.1	347.0	346.9	346.9	346.5
137.5°	366.9	367.4	367.9	368.3	368.8	369.2	369.4	369.7	369.9	370.1	369.8
140°	382.3	382.8	383.2	383.7	384.2	384.5	384.6	384.7	384.7	384.8	384.7
142.5°	396.3	396.8	397.3	397.8	398.2	398.5	398.7	398.9	399.1	399.2	399.1
145°	418.2	418.4	418.6	418.8	419.0	419.1	419.4	419.7	420.0	420.3	420.2
147.5°	437.3	437.6	438.0	438.3	438.7	438.9	439.2	439.5	439.8	440.1	440.1
150°	450.6	450.8	451.0	451.2	451.4	451.6	451.8	451.9	452.1	452.3	452.3
152.5°	461.6	461.8	462.1	462.3	462.6	462.8	462.9	463.1	463.2	463.3	463.4
155°	478.8	478.8	478.8	478.8	478.8	478.9	479.0	479.1	479.2	479.3	479.7
157.5°	493.5	493.4	493.3	493.1	493.0	493.0	493.1	493.2	493.2	493.3	493.7
160°	502.8	502.6	502.4	502.2	502.0	501.9	501.9	501.9	501.9	501.9	502.4
162.5°	511.0	510.7	510.4	510.1	509.9	509.8	509.8	509.9	510.0	510.1	510.6
165°	521.5	521.2	520.9	520.7	520.4	520.3	520.3	520.3	520.3	520.3	520.8
167.5°	530.0	529.6	529.2	528.9	528.5	528.3	528.4	528.5	528.6	528.6	529.2
170°	534.8	534.4	534.0	533.7	533.3	533.1	533.1	533.1	533.1	533.1	533.8
172.5°	538.6	538.2	537.8	537.4	537.0	536.8	536.8	536.8	536.8	536.8	537.4
175°	542.4	542.1	541.7	541.3	540.9	540.7	540.7	540.7	540.7	540.7	541.3
177.5°	544.1	543.8	543.5	543.2	542.9	542.7	542.7	542.7	542.7	542.7	543.2
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8



TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	541.5	541.5	541.5	541.5	541.5	541.5	541.5	541.5
2.5°	539.3	540.2	541.1	541.4	541.3	541.1	540.9	540.8
5°	535.8	536.7	537.5	537.9	537.7	537.5	537.3	537.2
7.5°	528.3	528.8	529.2	529.3	529.0	528.7	528.3	528.0
10°	521.5	521.6	521.7	521.5	521.0	520.6	520.0	519.5
12.5°	513.1	513.0	513.0	512.6	512.1	511.5	511.0	510.4
15°	498.3	497.9	497.4	496.8	496.2	495.4	494.7	494.1
17.5°	480.8	479.8	478.7	477.7	476.6	475.6	474.7	473.6
20°	468.7	467.4	466.2	465.0	463.7	462.6	461.5	460.2
22.5°	455.8	454.2	452.6	451.3	450.2	449.1	448.0	447.0
25°	434.6	432.6	430.6	429.0	427.9	426.9	425.7	424.7
27.5°	411.6	408.8	406.0	403.7	402.0	400.4	398.8	397.1
30°	395.2	391.9	388.6	386.2	384.6	383.0	381.4	379.8
32.5°	379.1	375.5	371.8	369.2	367.6	366.0	364.3	362.7
35°	355.2	351.0	346.9	343.8	342.1	340.4	338.6	336.9
37.5°	329.6	324.8	320.1	316.6	314.4	312.3	310.1	307.9
40°	311.8	306.7	301.6	297.9	295.7	293.5	291.2	289.0
42.5°	294.6	289.2	283.6	279.8	277.8	275.8	273.8	271.7
45°	269.5	263.9	258.4	254.4	252.1	249.8	247.4	245.1
47.5°	243.5	237.4	231.4	227.3	225.3	223.2	221.0	219.0
50°	225.9	219.9	213.9	209.7	207.5	205.2	202.9	200.7
52.5°	209.0	202.6	196.4	192.3	190.2	188.2	186.2	184.2
55°	183.7	178.0	172.4	168.5	166.6	164.7	162.7	160.7
57.5°	158.8	153.4	148.2	144.6	143.0	141.3	139.7	138.0
60°	143.2	137.9	132.6	129.1	127.5	125.8	124.2	122.5
62.5°	127.6	122.7	117.7	114.3	112.6	110.9	109.1	107.4
65°	105.5	100.8	96.0	93.0	91.9	90.9	89.8	88.7
67.5°	84.4	80.8	77.2	74.8	73.7	72.6	71.4	70.3
70°	71.4	68.0	64.5	62.3	61.2	60.1	59.0	58.0
72.5°	59.6	56.8	54.0	52.4	51.9	51.5	51.1	50.6
75°	44.6	43.6	42.6	42.0	41.8	41.7	41.5	41.3
77.5°	33.6	33.1	32.6	32.2	32.0	31.9	31.7	31.5
80°	27.1	26.8	26.5	26.3	26.0	25.8	25.6	25.4
82.5°	20.7	20.5	20.2	20.0	20.0	19.9	19.9	19.9
85°	11.9	11.7	11.5	11.4	11.4	11.4	11.4	11.4
87.5°	6.6	6.6	6.6	6.6	6.5	6.5	6.5	6.4
90°	11.0	11.4	11.8	12.1	12.3	12.4	12.6	12.8
92.5°	17.0	17.3	17.6	17.7	17.6	17.4	17.3	17.2
95°	32.3	32.7	33.1	33.3	33.3	33.3	33.3	33.3
97.5°	50.3	50.8	51.2	51.4	51.4	51.4	51.3	51.3
100°	63.3	63.6	63.9	64.2	64.4	64.6	64.8	64.9
102.5°	78.4	78.7	79.0	79.1	79.1	79.0	79.0	78.9
105°	100.8	100.8	100.8	100.9	101.1	101.3	101.5	101.7
107.5°	125.1	125.4	125.6	125.7	125.6	125.5	125.5	125.4
110°	141.3	141.7	142.0	142.1	141.9	141.8	141.6	141.4





TEST NUMBER: P332393-830

CATALOG NUMBER: S123RDIW-S340D460U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.5	158.0	158.4	158.6	158.5	158.5	158.5	158.4
115°	182.2	182.3	182.4	182.4	182.3	182.2	182.1	182.0
117.5°	207.1	207.0	207.0	206.9	206.6	206.3	206.0	205.8
120°	223.7	223.6	223.5	223.3	223.1	222.9	222.7	222.5
122.5°	240.4	240.2	239.9	239.7	239.4	239.1	238.8	238.6
125°	265.3	264.9	264.6	264.2	263.8	263.4	263.1	262.7
127.5°	290.0	289.5	288.9	288.4	288.0	287.6	287.1	286.7
130°	306.3	305.9	305.6	305.1	304.4	303.8	303.1	302.4
132.5°	322.3	321.8	321.3	320.8	320.4	319.8	319.3	318.8
135°	346.1	345.7	345.3	345.1	344.9	344.7	344.5	344.3
137.5°	369.4	369.0	368.5	368.2	367.8	367.5	367.1	366.7
140°	384.7	384.6	384.5	384.1	383.4	382.8	382.1	381.4
142.5°	399.0	398.9	398.8	398.5	398.0	397.5	397.0	396.4
145°	420.1	420.0	419.9	419.7	419.3	419.0	418.6	418.2
147.5°	440.1	440.1	440.1	439.8	439.2	438.6	438.0	437.4
150°	452.3	452.3	452.3	452.0	451.5	450.9	450.3	449.8
152.5°	463.5	463.7	463.9	463.7	463.3	462.7	462.2	461.8
155°	480.0	480.4	480.8	480.6	479.9	479.3	478.6	478.0
157.5°	494.2	494.6	494.9	494.8	494.4	493.8	493.2	492.8
160°	502.8	503.3	503.8	503.8	503.4	503.0	502.7	502.3
162.5°	511.0	511.5	512.0	511.9	511.3	510.7	510.1	509.4
165°	521.4	522.0	522.5	522.5	521.8	521.1	520.5	519.8
167.5°	529.8	530.4	530.9	530.9	530.4	529.8	529.2	528.6
170°	534.4	535.1	535.7	535.7	535.1	534.4	533.8	533.1
172.5°	538.0	538.6	539.1	539.1	538.5	537.8	537.2	536.5
175°	541.9	542.4	543.0	543.0	542.3	541.7	541.0	540.4
177.5°	543.7	544.1	544.5	544.5	543.9	543.5	542.9	542.3
180°	543.8	543.8	543.8	543.8	543.8	543.8	543.8	543.8

(END OF REPORT)